

## SOT-323 Plastic-Encapsulate MOSFETS

### ● Features

- $V_{DS}=60V$
- $I_D=115mA$
- $R_{DS(on)}@V_{GS}=10V < 5.0\Omega$
- $R_{DS(on)}@V_{GS}=5.0V < 7.0\Omega$
- Trench Power MV MOSFET technology
- Voltage controlled small signal switch
- Fast Switching Speed

**Drain-source Voltage**

60 V

**Drain Current**

0.115 Ampere


### ● Applications

- Battery operated systems
- Solid-state relays
- Direct logic-level interface: TTL/CMOS



### ● Mechanical Data

- Case: SOT-323
- Molding compound meets UL 94V-0 flammability rating, RoHS-compliant, halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750, Method 2026

SOT-323



### ● Reference News



### ● Maximum Ratings (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	VALUE
Drain-source Voltage	$V_{DS}$	V	60
Gate-source Voltage	$V_{GS}$	V	$\pm 20$
Drain Current	$I_D$	mA	115
Pulsed Drain Current <sup>(1)</sup>	$I_{DM}$	mA	800
Total Power Dissipation @ $T_A=25^\circ C$	$P_D$	mW	200
Thermal Resistance Junction-to-Ambient @ Steady State <sup>(2)</sup>	$R_{\theta JA}$	$^\circ C / W$	357
Junction and Storage Temperature Range	$T_J, T_{STG}$	$^\circ C$	-55 ~ +150

Note :

(1) Pulse test ; Pulse width  $\leq 300\mu s$ , duty cycle  $\leq 2\%$

(2) Device mounted on FR-4 PCB, 1 inch x 0.85 inch x 0.062 inch.

### ● Ordering Information

PACKAGE	PACKAGE CODE	UNIT WEIGHT(g)	REEL(pcs)	BOX(pcs)	CARTON(pcs)	DELIVERY MODE
SOT-323	R1	0.005	3000	45000	180000	7"

### ● Static Parameter Characteristics (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Drain-Source Breakdown Voltage	$BV_{DSS}$	$V_{GS}=0V, I_D=250\mu A$	V	60	—	—
Zero Gate Voltage Drain Current	$I_{DSS}$	$V_{DS}=60V, V_{GS}=0V$	nA	—	—	80
Gate-Body Leakage Current	$I_{GSS}$	$V_{DS}=0V, V_{GS}=\pm 20V$	nA	—	—	$\pm 100$
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS}=V_{GS}, I_D=250\mu A$	V	1.0	1.6	2.5
On-state Drain Current	$I_{D(ON)}$	$V_{GS}=10V, V_{DS}=7V$	mA	500	—	—
Static Drain-Source On-Resistance	$R_{DS(ON)}$	$V_{GS}=10V, I_D=500mA$	$\Omega$	—	0.9	5.0
		$V_{GS}=5V, I_D=50mA$		—	1.1	7.0
Drain-source On-voltage	$V_{DS(ON)}$	$V_{GS}=10V, I_D=500mA$	V	—	—	3.75
		$V_{GS}=5V, I_D=50mA$		—	—	0.375
Diode Forward Voltage	$V_{SD}$	$I_S=115mA, V_{GS}=0V$	V	0.55	—	1.2
Forward Transconductance	$g_{fs}$	$V_{DS}=10V, I_D=200mA$	ms	80	—	—






### ● Dynamic Parameters (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Input Capacitance	$C_{iss}$	$V_{DS}=25V, V_{GS}=0V, f=1MHz$	pF	—	—	50
Output Capacitance	$C_{oss}$			—	—	25
Reverse Transfer Capacitance	$C_{rss}$			—	—	5.0

### ● Switching Parameters (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Turn-on Delay Time	$t_{D(on)}$	$V_{DD}=25V, R_L=50\Omega,$ $V_{GEN}=10V, I_D=500mA$ $R_{GEN}=25\Omega,$	ns	—	—	20
Turn-off Delay Time	$t_{D(off)}$			—	—	40

● Ratings And Characteristics Curves ( $T_a=25^\circ\text{C}$  Unless otherwise specified)



## ● Package Outline Dimensions (SOT-323)

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	0.90	1.10	0.035	0.043
A1	-	0.10	-	0.004
A2	0.90	1.00	0.035	0.039
b	0.15	0.40	0.012	0.020
c	0.10	0.25	0.004	0.010
D	1.80	2.20	0.071	0.087
E	1.15	1.35	0.045	0.053
E1	2.15	2.45	0.085	0.096
e	0.650TYP		0.026TYP	
e1	1.20	1.40	0.047	0.055
L	0.525REF		0.021REF	
L1	0.26	0.46	0.010	0.018
$\theta$	-	8°	-	8°

## ● Suggested Pad Layout

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
J	0.65	0.75	0.026	0.030
K	0.85	0.95	0.033	0.037
M	1.85	1.95	0.073	0.077
N	1.25	1.35	0.049	0.053