


# 1.5mm-travel Vertical Type SPEF Series


Part number			SPEF210101
Changeover timing			Non shorting
Travel			1.5mm
Total travel			2.7mm
Operating force			3N
Mounting method			PC board
Poles-Positions			1-pole, 2-position
Operation			Latching
Terminal type			Reflow
Operating temperature range			-40℃ to +85℃
Rating (max.)/(min.) (Resistive load)			1A 14.5V DC/50µA 3V DC
Electrical performance	Contact resistance (Initial performance/After lifetime)		100mΩ max./100mΩ max.
	Insulation resistance		3MΩ min. 100V DC
	Voltage proof		100V AC for 1 minute
Mechanical performance	Actuator strength	Operating direction	90N
		Pulling direction	30N
Durability	Operating life with load (at max. rated load)		30,000 cycles 100mΩ max.
Environmental performance	Cold		-40℃ 96h
	Dry heat		85℃ 96h
	Damp heat		40℃, 90 to 95%RH 96h

Minimum order unit (pcs.)	Japan	660
	Export	1,320
	Export	1,520


# Dimensions



# Land Dimensions




### Circuit Diagram



Viewed from direction A in the dimensions.

## **Packing Specifications**

#### Taping



Number of packages (pcs.)	s 1 reel	165
	1 case / Japan	660
	1 case / export packing	1,320
Tape width (mm)		32
Export package measurements (mm)		403×403×360

### Soldering Conditions

#### **Example of Reflow Soldering Condition**


1. Heating method

Double heating method with infrared heater.

2. Temperature measurement

Thermocouple 0.1 to 0.2  $\Phi$  CA (K) or CC (T) at soldering portion (copper foil surface). A heat resisting tape should be used for fixed measurement.

3. Temperature profile



(1) The condition mentioned above is the temperature on the mounting surface of a PC board. There are cases where the PC board's temperature greatly differs from that of the switch, depending on the PC board's material, size, thickness, etc. The above-stated conditions shall also apply to switch surface temperatures.

(2) Soldering conditions differ depending on reflow soldering machines. Prior verification of soldering condition is highly recommended.

#### **Reference for Hand Soldering**

Soldering temperature	350±10℃
Soldering time	3s max.

#### Notes are common to this series/models.

- 1. This site catalog shows only outline specifications. When using the products, please obtain formal specifications for supply.
- 2. Please place purchase orders per minimum order unit (integer).
- This products can be used in vehicles.
  Although these products are designed to perform over a wide operating temperature range, please ensure that you receive and read the formal delivery specifications before use.