

## FAST SWITCHING DIODES

## 1SS355

## FEATURES

Small surface mounting type.

High Speed.( $t_{rr}=1.2\text{ns}$  Typ.)

High reliability with high surge current handling capability.



## MARKING: A

MAXIMUM RATINGS (TA=25°C unless otherwise noted)

Parameter	Symbol	Value	Units
Non-Repetitive Peak reverse voltage	$V_{RM}$	90	V
DC Blocking	$V_R$	80	V
Forward Continuous Current	$I_{FM}$	225	mA
Average Rectified Output Current	$I_o$	100	mA
Surge current (1s)	$I_{surge}$	500	mA
Junction temperature	$T_j$	125	°C
Storage temperature	$T_{STG}$	--55-125	°C

ELECTRICAL CHARACTERISTICS (Tamb=25°C unless otherwise specified)

Parameter	Symbol	Min	Typ	Max	Unit	Conditions
Forward voltage	$V_F$			1.2	V	$I_F=100\text{mA}$
Reverse current	$I_R$			0.1	$\mu\text{A}$	$V_R=80\text{ V}$
Capacitance between terminals	$C_T$			3	pF	$V_R=0\text{V}, f=1\text{MHz}$
Reverse Recovery Time	$t_{rr}$			4	ns	$I_F=10\text{mA} \quad V=6\text{ V} \quad R_L=100\Omega$

**1SS355 Typical Characteristics**
