



SCHOTTKY DIODES
BAT54/A/C/S
FEATURES


Extremely Fast Switching Speed

MARKING:



BAT54 : KL1



BAT54A : KL2



BAT54C : KL3



BAT54S : KL4



MAXIMUM RATINGS (TA=25°C unless otherwise noted)

Parameter	Symbol	Limits			Unit
Peak Repetitive Peak reverse voltage	VR _{RM}				V
Working Peak Reverse Voltage	VR _{WM}	30			V
DC Blocking Voltage	V _R				
Forward Continuous Current	I _{FM}	200			mA
Power Dissipation	P _D	200			mW
Storage temperature	T _{STG}	-55-150			°C

ELECTRICAL CHARACTERISTICS (Tamb=25 °C unless otherwise specified)

Parameter	Symbol	Min.	Typ.	Max.	Unit	Conditions
Reverse Breakdown Voltage	V(BR)R	30			V	IR=100μA
Forward voltage	VF1			0.24	V	IF=0.1mA
	VF2			0.32	V	IF=1mA
	VF3			0.40	V	IF=10mA
	VF4			0.50	V	IF=30mA
	VF5			1	V	IF=100mA
Reverse current	I _R			2	μA	VR=25V
Diode Capacitance	C _D			10	pF	VR=1V,f=1MHz
Reverse Recovery Time	t _{rr}			5	nS	IF=IR=10mA, I _{rr} =0.1XIR,RL=100

BAT54/A/C/S Typical Characteristics
