



项目	零件名称	数量	材质	处理/备注
1	SHELL	1	STAINLESS	Ni:50u"
2	Molding HOUSING	2	L.C.P	(Black)
3	GND SPRING	2	STAINLESS	Ni:50u"
4	Insert molding 12PIN	2	L.C.P	(Black)
5	CONTACT	24	COPPER ALLOY	Contact area: gold flash, Solder tails: Tn100u", Ni:50u"
6	PCB	1		

**: SPECIFICATION**  
**MATERIAL**  
 See drawing  
**STANDARD DATA**  
 Operating temperature: -10°C ~ +60°C  
 Storage temperature: -20°C ~ +85°C  
**ELECTRICAL**  
 Insulator resistance: 100Mohms Min.  
 Withstanding voltage: 100 VAC / minute  
 Contact resistance: initial 40mohms Max;  
 after 50mohms Max.  
**MECHANICAL**  
 Mating force: 5~20N  
 Umating force: 8~20N  
 Durability: 5000 cycles Min.

**产品图**  
 PRODUCT CHART DWG

公差一览表 TOLERANCE UNLESS OTHERWISE		单位 UNITS	MM	制图 DRAWING	Z-Y-B	产品料号 PRODUCT PART NO.	角法 VIEW	版本 VER
X	±0.25	X'	±5'	审核			USP-3.1 公头/双面POP板转micro无边	
.X	±0.20	.X'	±2'	核准				
.XX	±0.15	.XX'	±1'	核准	郭治富			A0
.XXX	±0.10	.XXX'	±0.5'	核准				
		日期 DATE	2015.07.14	核准 APPD				