







NOTE:
 1. Operating Force: 180gf±50gf
 2. Travel : 2.0±0.2mm



PCB Layout (Pattern Side)



Circuit Diagram



| NO. | Operating Type | Part No. |
|-----|-----------------------|-------------|
| 1 | Push To Lock | K8-5851D-L1 |
| 2 | Push No Lock | K8-5851D-N1 |
| 3 | Push No Sound No Lock | K8-5851D-NN |

| ITEM | PART NAME | TER'NO. | QTY. | MATERIAL | FINISHING | REMARK |
|------|----------------|---------|------|-----------------|----------------|--------|
| ⑦ | Terminal | — | 6 | Brass strip | Plating silver | — |
| ⑥ | Contact | — | 2 | Phosphor bronze | Plating silver | — |
| ⑤ | Spring | — | 1 | SUS | Natural | — |
| ④ | Base | — | 1 | Nylon | Gray | — |
| ③ | Crochet Needle | — | 1 | SUS | Natural | — |
| ② | Cover | — | 1 | POM | Black | — |
| ① | KNOB | — | 1 | POM | White | — |

| APPROVALS | | DATE | TITLE: | |
|-----------|-----------|------------|---------------------|--|
| DRAWN | J.X.Zhong | 2013/10/16 | PUSHBUTTON SWITCHS | |
| CHECKED | | | ELECTRONICS CO.,LTD | |

| ECN NO. | REV. | DATE. | DESCRIPTION. | CHANGE. | CHECK. | APPRO. | TOLERANCES ARE | ANGLE | UNIT: | SCALE: | PROJ: |
|---------|------|-------|--------------|---------|--------|--------|----------------|-------|-------|--------|--------------|
| — | A | — | NEW | — | — | — | 30°±0.1° | ±0.30 | mm | 1:1 | PROJ: 1 OF 1 |
| — | — | — | — | — | — | — | 10°~30° | ±0.20 | — | — | — |
| — | — | — | — | — | — | — | 5°~10° | ±0.15 | — | — | — |
| — | — | — | — | — | — | — | ~5 | ±0.10 | — | — | — |