

LESD8D12T5G ESD PROTECTION DIODE

Discription

The LESD8D12T5G is designed to protect voltage sensitive components from ESD. Excellent clamping capability, low leakage, and fast response time provide best in class protection on designs that are exposed to ESD. Because of its small size, it is suited for use in cellular phones, MP3 players, digital cameras and many other portable applications where board space is at a premium.


Applications

- | Cellular phones audio
- | MP3 players
- | Digital cameras
- | Portable applications
- | mobile telephone

Features

- | Small Body Outline Dimensions:
0.039" x 0.024"(1.0 mm x 0.60 mm)
- | Low Body Height: 0.020" (0.50 mm) Max
- | Stand-off Voltage: 3.3 V – 12 V
- | Low Leakage
- | Response Time is Typically < 1 ns
- | ESD Rating of Class 3 (> 16 kV) per Human Body Model
- | IEC61000-4-2 Level 4 ESD Protection
- | We declare that the material of product compliance with RoHS requirements.
- | S- Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable.

LESD8D12T5G
S-LESD8D12T5G



Ordering information

Device	Marking	Shipping
LESD8D12T1G S-LESD8D12T1G	H	5000/Tape&Reel
LESD8D12T3G S-LESD8D12T3G	H	8000/Tape&Reel
LESD8D12T5G S-LESD8D12T5G	H	10000/Tape&Reel

MAXIMUM RATINGS

Rating	Symbol	Value	Unit
IEC 61000-4-2 (ESD) Air Contact Contact discharge		±15 ±8	kV kV
ESD Voltage Per Human Body Model		16	kV
Total Power Dissipation on FR-5 Board (Note 1) @ T _A =25°C	PD	150	Mw
Junction and Storage Temperature Range	T _J ,T _{STG}	-55 to 150	°C
Lead Solder Temperature – Maximum (10 Second Duration)	TL	260	°C

Stresses exceeding Maximum Ratings may damage the device. Maximum Rating are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.


1. FR-5 = 1.0*0.75*0.62 in.

LESD8D12T5G , S-LESD8D12T5G

ELECTRICAL CHARACTERISTICS

(T_A = 25°C unless otherwise noted)

Symbol	Parameter
I _{PP}	Maximum Reverse Peak Pulse Current
V _C	Clamping Voltage @ I _{PP}
V _{RWM}	Working Peak Reverse Voltage
I _R	Maximum Reverse Leakage Current @ V _{RWM}
V _{BR}	Breakdown Voltage @ I _T
I _T	Test Current
I _F	Forward Current
V _F	Forward Voltage @ I _F
P _{pk}	Peak Power Dissipation
C	Max. Capacitance @V _R = 0 and f = 1 MHz



Uni-Directional TVS

ELECTRICAL CHARACTERISTICS (T_A=25°C unless otherwise noted, V_F=0.9V Max. @ I_F=10Ma for all types)

Device	V _{RWM} (V)	I _R (μA) @ V _{RWM}	V _{BR} (V) @ I _T (Note 2)	I _T (mA)	I _{PP} (A) (Note 3)	V _C (V) @ Max I _{PP} (Note 3)	P _{PK} (W) (8*20 μs)	C (pF)
	Max	Max	Min		Max	Max	Typ	Typ
LESD8D3.3T5G	3.3	2.5	5.0	1.0	9.8	10.4	102	80
LESD8D5.0T5G	5.0	1.0	6.2	1.0	8.7	12.3	107	65
LESD8D12T5G	12	1.0	13.3	1.0	5.9	23.7	140	30

Other voltage available upon request.

- V_{BR} is measured with a pulse test current I_T at an ambient temperature of 25°C
- Surge current waveform per Figure 3.

LESD8D12T5G , S-LESD8D12T5G

TYPICAL CHARACTERISTICS




Figure 1. Typical Breakdown Voltage versus Temperature




Fig 2. Typical Leakage Current versus Temperature




Figure 3. 8*20 μs Pulse Waveform




Figure 4. Positive 8kV contact per IEC 61000-4-2-LESD8D12T5G





Fig 5. Negative 8kV contact per IEC 61000-4-2-LESD8D12T5G


LESD8D12T5G , S-LESD8D12T5G

OUTLINE AND DIMENSIONS

SOD882




SOD882			
Dim	Min	Typ	Max
D	0.95	1.00	1.05
E	0.55	0.60	0.65
e	-	0.64	-
L	0.44	0.49	0.54
b	0.20	0.25	0.30
A	0.43	0.48	0.53
A1	0	-	0.05
A3	0.127REF.		
All Dimensions in mm			



SOLDERING FOOTPRINT

SOD882



Dimensions	(mm)
c	0.70
G	0.30
X	0.40
X1	1.10
Y	0.70