




MB2F THRU MB10F

Voltage Range - 200 to 1000 Volts Current - 1.0 Ampere

SINGLE PHASE GLASS PASSIVATED BRIDGE RECTIFIERS

Features

- ◆ Glass passivated die construction
- ◆ Low forward voltage drop
- ◆ High current capability
- ◆ High surge current capability
- ◆ Designed for surface mount application
- ◆ Plastic material-UL flammability 94V-0



Mechanical Data


Case : JEDEC MBF Molded plastic body

Terminals : Solder plated, solderable per MIL-STD-750, Method 2026

Polarity : Polarity symbol marking on body

Mounting Position : Any

Weight : 0.0026 ounce, 0.075 grams



Dimensions in inches and (millimeters)

Maximum Ratings And Electrical Characteristics

Ratings at 25 °C ambient temperature unless otherwise specified.






Single phase half-wave 60Hz, resistive or inductive load, for capacitive load current derate by 20%.

Parameter	SYMBOLS	MDD	MDD	MDD	MDD	MDD	UNITS
		MB2F	MB4F	MB6F	MB8F	MB10F	
Marking Code							
Maximum repetitive peak reverse voltage	V_{RRM}	200	400	600	800	1000	V
Maximum RMS voltage	V_{RMS}	140	280	420	560	700	V
Maximum DC blocking voltage	V_{DC}	200	400	600	800	1000	V
Maximum average forward rectified current at $T_C=125^\circ C$	$I_{F(AV)}$	1.0					A
Peak forward surge current, 8.3ms single half sine-wave superimposed on rated load (JEDEC Method)	I_{FSM}	35					A
Maximum instantaneous forward voltage drop per leg at 0.5A	V_F	1.1					V
Maximum DC reverse current at rated DC blocking voltage	I_R	5 0.5					μA mA
Typical junction capacitance	C_J	13					pF
Typical thermal resistance(NOTE3)	$R_{\theta JA}$	60					$^\circ C/W$
Operating temperature range	T_J	-55 to +150					$^\circ C$
storage temperature range	T_{STG}	-55 to +150					$^\circ C$

NOTES:1. On glass epoxy P.C.B. mounted on 0.05x0.05"(1.3x1.3mm) pads
 2. On aluminum substrate P.C.B. with on area of 0.8"x0.8"(20x20mm) mounted on 0.05X0.05"(1.3X1.3mm) solder pad
 3. Measured at 1.0MHz and applied reverse voltage of 4.0 volts.




Ratings And Characteristic Curves



The curve above is for reference only.



Suggested Pad Layout



Dim	Min
P1	6.00
P2	2.40
Q1	1.84
Q2	1.20

Important Notice and Disclaimer

Microdiode Electronics (Jiangsu) reserves the right to make changes to this document and its products and specifications at any time without notice. Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.

Microdiode Electronics (Jiangsu) makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Microdiode Electronics (Jiangsu) assume any liability for application assistance or customer product design. Microdiode Electronics (Jiangsu) does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application.

No license is granted by implication or otherwise under any intellectual property rights of Microdiode Electronics (Jiangsu).

Microdiode Electronics (Jiangsu) products are not authorized for use as critical components in life support