

Product Search Data Sheet

Note: This datasheet may be out of date

Please download the latest datasheet of DLP11SN241HL2#from the official website of Murata Manufacturing

Co., Ltd. https://www.murata.com/en-us/products/productdetail?partno=DLP11SN241HL2%23

DLP11SN241HL2#

"#" indicates a package specification code.

In Production RoHS REACH

< List of part numbers with package codes > DLP11SN241HL2B DLP11SN241HL2L

Appearance & Shape			Features
	(1) (2) (3) (4) (4) (2) (3) (3) (3) (4) (4) (4) (4) (4) (4) (4) (4) (5) (5) (4) (5) (5) (5) (5) (5) (6) (6) (7)	0.3±0.1 Part Number DLP11S 0.82±0.1 DLP11R 0.5±0.1 DLP11T 0.3±0.05 : Electrode (in mm)	 Small size and tight dimensional tolerance Size: 1.25x1.0x0.82mm Tolerance: +-0.1mm Useful impedance line-up from 67 ohm to 330 ohm DLP11S series enables noise suppression for differential signal line without distortion in high-speed signal transmission due to its high coupling DLP11SN_HL2, DLP11SAseries match with line impedance High Cutoff Frequency is suitable for high speed differential signal line such as HDMI. Cutoff Frequency: 6GHz (DLP11SAseries)
Applications			Applications Common mode noise suppression of high speed differential signal lines for USB, IEEE1394, LVDS 1. Note PCs, PDAs
Other Usage For general			2. Cellular phones 3. Digital Still Cameras, Digital Video Cameras

Packaging Information

Packaging	Specifications	Minimum Order Quantity
В	Bulk(Bag)	500
L	180mm Embossed Tape	3000

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering





Note: This datasheet may be out of date

Please download the latest datasheet of DLP11SN241HL2#from the official website of Murata Manufacturing

Co., Ltd. https://www.murata.com/en-us/products/productdetail?partno=DLP11SN241HL2%23

DLP11SN241HL2#

"#" indicates a package specification code.

Specifications

Shape	SMD	Operating Temperature Range	-40℃ to 85℃
Size Code (in mm)	1210	Mass(typ.)	0.005g
Size Code (in inch)	0504	Number of Circuit	1
Length	1.25mm	Operating Temperature Range(Self- temperature rise is included)	No
Length Tolerance	±0.1mm		
Width	1.0mm		
Width Tolerance	±0.1mm		
Thickness	0.82mm		
Thickness Tolerance	±0.1mm		
Common Mode Impedance (at 100MHz)	240Ω		
Common Mode Impedance (at 100MHz) Tolerance	±20%		
Rated Current	100mA		
Rated Voltage	5Vdc		
Withstanding Voltage	12.5Vdc		
DC Resistance(max.)	4.38Ω		
DC Resistance	3.5Ω±25%		
Insulation Resistance(min.)	100ΜΩ		

2 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering

Note: This datasheet may be out of date

Please download the latest datasheet of DLP11SN241HL2#from the official website of Murata Manufacturing Co., Ltd.


https://www.murata.com/en-us/products/productdetail?partno=DLP11SN241HL2%23


DLP11SN241HL2#

"#" indicates a package specification code.




INNOVATOR IN FLEC






Impedance-Frequency Characteristics (Main Items)



Impedance-Frequency Characteristics

Differential Mode Transmission Characteristics (Typical Value)



Equivalent Circuit

3 of 3

Attention

 This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
 This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

