Note: This datasheet may be out of date

Please download the latest datasheet of LFB182G45SG9A213 from the official website of Murata Manufacturing

Co., Ltd.

https://www.murata.com/en-eu/products/productdetail?partno=LFB182G45SG9A213

# LFB182G45SG9A213












### Appearance & Shape







(in mr



Ultra-small, low-profiled, lightweight chip filters based on ceramic multilayer technology.

Extremely ultra-small band-bass filters.

- 1. Ultra-small, low-profiled, lightweight band-pass filters.
- 2. Absolutely no adjustment required.
- 3. Reflow solderable.
- 4. Available in tape and reel packagings for automatic mounting.
- 5. Available in the 2400MHz to 2500MHz frequency range.

### Packaging Information

Packaging	Specifications	Minimum Order Quantity
-	180mm Paper Tape	4000

1 of 3

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



URL: https://www.murata.com/

Last updated : 2018/05/24

Note: This datasheet may be out of date

Please download the latest datasheet of LFB182G45SG9A213 from the official website of Murata Manufacturing

 $\underline{\text{Co., Ltd.}} \\ \text{https://www.murata.com/en-eu/products/productdetail?partno=LFB182G45SG9A213} \\$ 

## LFB182G45SG9A213



Applications	WLAN BT	
Nominal Center Frequency(fo)	2450.00MHz	
Bandwidth(BW)	fo±50.00MHz	
Insertion Loss in BW I)	2.2dB max. (at 25°C)	
Insertion Loss in BW II)	2.5dB max. (-40 to +85°C)	
Attenuation(Absolute Value) I)	24dB min. at 880.00 to 960.00MHz	
Attenuation(Absolute Value) II)	20dB min. at 1710.00 to 1990.00MHz	
Attenuation(Absolute Value) III)	15.5dB min. at 4800.00 to 5000.00MHz	
Attenuation(Absolute Value) IV)	19.5dB min. at 7200.00 to 7500.00MHz	
Ripple(max.)	1.5dB	
VSWR(max.)	2.1	
Characteristic Impedance(Nom.)	50Ω	
Power Capacity	500mW	
Operating Temperature Range	-40℃ to 85℃	
L x W (size)	1.60x0.80mm	
Thickness(max.)	0.7mm	

2 of 3

### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



URL: https://www.murata.com/


Note: This datasheet may be out of date


Please download the latest datasheet of LFB182G45SG9A213 from the official website of Murata Manufacturing

Co., Ltd. https://www.murata.com/en-eu/products/productdetail?partno=LFB182G45SG9A213

## LFB182G45SG9A213







Frequency Characteristics

Spurious Response

3 of 3

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering

