



Note: This datasheet may be out of date Please download the latest datasheet of NCP18WM474E03RB from the official website of Murata Manufacturing

https://www.murata.com/en-us/products/productdetail?partno=NCP18WM474E03RB

NCP18WM474E03RB












Appearance & Shape










- 1. Excellent solderability and high stability in environment
- 2. Excellent long time aging stability
- 3. High accuracy in resistance and B-constant
- 4. Flow / Reflow soldering possible
- 5. Same B-Constant in the same resistance in the three sizes (0805 size / 0603 size / 0402 size)

Easy to use smaller size in the circuits

- 6. Lead is not contained in the product.
- 7. NCP series are recognized by UL/cUL (UL1434, File No.E137188).







Packaging Information

Packaging	Specifications	Minimum Order Quantity
RB	180mm Paper Tape	4000

1 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



URL: https://www.murata.com/

Last updated : 2018/03/12



Note: This datasheet may be out of date

 $\underline{ \text{Please download the latest datasheet of NCP18WM474E03RB from the official website of Murata Manufacturing} \\$

Co., Ltd. https://www.murata.com/en-us/products/productdetail?partno=NCP18WM474E03RB

NCP18WM474E03RB



Resistance (25°C)	470kΩ	
Resistance Value Tolerance (at 25°C)	±3%	
B-Constant (25/50°C)	4500K	
B-Constant (25/50°C) Tolerance	±3%	
B-Constant(25/80°C)(Reference Value)	4571K	
B-Constant(25/85°C)(Reference Value)	4582K	
B-Constant(25/100°C)(Reference Value)	4614K	
Permissive Operating Current (25°C)	0.04mA	
Rated Electric Power (25°C)	100.0mW	
Typical Dissipation Constant (25°C)	1mW/℃	
Operating Temperature Range	-40°C to 125°C	
Size Code (in mm)	1.6x0.8mm	
Size Code (in inch)	0.6x0.3inch	
Shape	SMD	
Mass	0.0047g	

2 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



URL: https://www.murata.com/

Last updated :2018/03/12


Note: This datasheet may be out of date

 $\underline{ \text{Please download the latest datasheet of NCP18WM474E03RB from the official website of Murata Manufacturing} \\$

Co., Ltd. https://www.murata.com/en-us/products/productdetail?partno=NCP18WM474E03RB

NCP18WM474E03RB





Resistance-Temperature Characteristics

3 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



URL: https://www.murata.com/