

ON Semiconductor®

# J111 / J112 / J113 / MMBFJ111 / MMBFJ112 / MMBFJ113 N-Channel Switch

#### **Features**

- This device is designed for low level analog switching, sample and hold circuits and chopper stabilized amplifiers.
- Sourced from process 51
- Source & Drain are interchangeable.



Figure 1. J111 / J112 / J113 Device Package




Figure 2. MMBFJ111 / MMBFJ112 / MMBFJ113
Device Package

# **Ordering Information**

Part Number	Top Mark	Package	Packing Method
J111	J111	TO-92 3L	Bulk
J111-D26Z	J111	TO-92 3L	Tape and Reel
J111-D74Z	J111	TO-92 3L	Ammo
J112	J112	TO-92 3L	Bulk
J112-D26Z	J112	TO-92 3L	Tape and Reel
J112-D27Z	J112	TO-92 3L	Tape and Reel
J112-D74Z	J112	TO-92 3L	Ammo
J113	J113	TO-92 3L	Bulk
J113-D74Z	J113	TO-92 3L	Ammo
J113-D75Z	J113	TO-92 3L	Ammo
MMBFJ111	6P	SOT-23 3L	Tape and Reel
MMBFJ112	6R	SOT-23 3L	Tape and Reel
MMBFJ113	6S	SOT-23 3L	Tape and Reel

# **Absolute Maximum Ratings**(1), (2)

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only. Values are at  $T_A = 25^{\circ}\text{C}$  unless otherwise noted.

Symbol	Parameter	Value	Unit
$V_{DG}$	Drain-Gate Voltage	35	V
$V_{GS}$	Gate-Source Voltage	-35	V
I <sub>GF</sub>	Forward Gate Current	50	mA
T <sub>J</sub> , T <sub>STG</sub>	Operating and Storage Junction Temperature Range	-55 to 150	°C

#### Notes:

- 1. These ratings are based on a maximum junction temperature of 150°C.
- 2. These are steady-state limits. ON Semiconductor should be consulted on applications involving pulsed or low-duty-cycle operations.

#### **Thermal Characteristics**

Values are at  $T_A = 25$ °C unless otherwise noted.

		Ma		
Symbol	Parameter	J111 / J112 / J113 <sup>(3)</sup>	MMBFJ111 / MMBFJ112 / MMBFJ113 <sup>(4)</sup>	Unit
P <sub>D</sub>	Total Device Dissipation	625	350	mW
	Derate Above 25°C	5.0	2.8	mW/°C
$R_{\theta JC}$	Thermal Resistance, Junction-to-Case	125		°C/W
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient	200	357	°C/W

#### Notes:

- 3. PCB size: FR-4, 76 mm x 114 mm x 1.57 mm (3.0 inch x 4.5 inch x 0.062 inch) with minimum land pattern size.
- 4. Device mounted on FR-4 PCB 36mm × 18mm × 1.5mm; mounting pad for the collector lead minimum 6cm<sup>2</sup>.

#### **Electrical Characteristics**

Values are at  $T_A = 25^{\circ}C$  unless otherwise noted.

Symbol	Parameter Conditions		Min.	Max.	Unit	
Off Charac	teristics			•	•	•
V <sub>(BR)GSS</sub>	Gate-Source Breakdown Voltage	$I_G = -1.0 \mu\text{A},  V_{DS} = 0$		-35		V
I <sub>GSS</sub>	Gate Reverse Current	V <sub>GS</sub> = -15 V, V <sub>DS</sub> = 0			-1.0	nA
V <sub>GS</sub> (off)	Gate-Source Cut-Off Voltage	$V_{DS} = 15 \text{ V}, I_{D} = 1.0 \mu\text{A}$	111	-3.0	-10.0	V
			112	-1.0	-5.0	
			113	-0.5	-3.0	
I <sub>D</sub> (off)	Drain Cutoff Leakage Current	V <sub>DS</sub> = 5.0 V, V <sub>GS</sub> = -10 V			1.0	nA
On Charac	teristics					
	Zero-Gate Voltage Drain Current <sup>(5)</sup>	V <sub>DS</sub> = 15 V, V <sub>GS</sub> = 0	111	20		mA
$I_{DSS}$			112	5.0		
			113	2.0		
r <sub>DS</sub> (on)	Drain-Source On Resistance	$V_{DS} \le 0.1 \text{ V}, V_{GS} = 0$	111		30	Ω
			112		50	
			113		100	
Small Sign	nal Characteristics		•			
C <sub>dg</sub> (on) C <sub>sg</sub> (on)	Drain-Gate &Source-Gate On Capacitance	$V_{DS} = 0, V_{GS} = 0, f = 1.0 \text{ MHz}$			28	pF
C <sub>dg</sub> (off)	Drain-Gate Off Capacitance	V <sub>DS</sub> = 0, V <sub>GS</sub> = -10 V, f = 1.0 MHz			5.0	pF
C <sub>sg</sub> (off)	Source-Gate Off Capacitance	V <sub>DS</sub> = 0, V <sub>GS</sub> = -10 V, f = 1.0 MHz		5.0	pF	

#### Note:

5. Pulse test: pulse width  $\leq 300~\mu s,$  duty cycle  $\leq 2\%.$ 

## **Typical Performance Characteristics**




Figure 3. Common Drain-Source




Figure 5. Transfer Characteristics





Figure 7. Transfer Characteristics



**Figure 4. Parameter Interactions** 




Figure 6. Transfer Characteristics




Figure 8. Transfer Characteristics

#### **Typical Performance Characteristics** (Continued)




Figure 9. On Resistance vs. Drain Current




Figure 11. Transconductance vs. Drain Current




Figure 13. Capacitance vs. Voltage




Figure 10. Normalized Drain Resistance vs. Bias Voltage




Figure 12. Output Conductance vs. Drain Current




Figure 14. Noise Voltage vs. Frequency

# **Typical Performance Characteristics** (Continued)




Figure 15. Noise Voltage vs. Current




Figure 16. Power Dissipation vs.
Ambient Temperature




Figure 17. Switching Turn-On Time vs. Gate-Source Voltage




Figure 18. Switching Turn-Off Time vs. Drain Current

# **Physical Dimensions**







Figure 19. 3-Lead, TO-92, JEDEC TO-92 Compliant Straight Lead Configuration, Bulk Type

# Physical Dimensions (Continued)







NOTES: UNLESS OTHERWISE SPECIFIED

- DRAWING CONFORMS TO JEDEC MS-013, VARIATION AC.
  ALL DIMENSIONS ARE IN MILLIMETERS.
  DRAWING CONFORMS TO ASME Y14.5M-2009.
  DRAWING FILENAME: MKT-ZA03FREV3.
  ON SEMICONDUCTOR B. C. D.

Figure 20. 3-Lead, TO-92, Molded, 0.2 In Line Spacing Lead Form, Ammo, Tape and Reel Type

## Physical Dimensions (Continued) 0.95 2.92±0.20 3 1.40 1.30+0.20 2.20 2 0.60 0.37 (0.29) -0.95 ⊕ 0.20∭ A B -1.00 1.90 1.90 LAND PATTERN RECOMMENDATION SEE DETAIL A -1.20 MAX (0.93)0.10 C 2.40±0.30 NOTES: UNLESS OTHERWISE SPECIFIED **GAGE PLANE** A) REFERENCE JEDEC REGISTRATION TO-236, VARIATION AB, ISSUE H. B) ALL DIMENSIONS ARE IN MILLIMETERS. 0.23 C) DIMENSIONS ARE INCLUSIVE OF BURRS, 0.25 MOLD FLASH AND TIE BAR EXTRUSIONS. D) DIMENSIONING AND TOLERANCING PER ASME Y14.5M - 1994. 0.20 MIN SEATING E) DRAWING FILE NAME: MA03DREV10 **PLANE** (0.55)**DETAIL A** SCALE: 2X

Figure 21. 3-LEAD, SOT23, JEDEC TO-236, LOW PROFILE

ON Semiconductor and III) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <a href="www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages.

Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

#### **PUBLICATION ORDERING INFORMATION**

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support:

Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative