## **General Purpose Transistors**

### **PNP Silicon**

#### **Features**

- S Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant

#### **MAXIMUM RATINGS**

Rating	Symbol	Value	Unit
Collector - Emitter Voltage	V <sub>CEO</sub>	-60	Vdc
Collector - Base Voltage	V <sub>CBO</sub>	-60	Vdc
Emitter-Base Voltage	V <sub>EBO</sub>	-5.0	Vdc
Collector Current – Continuous	I <sub>C</sub>	-600	mAdc
Collector Current – Peak (Note 3)	I <sub>CM</sub>	-1200	mAdc

#### THERMAL CHARACTERISTICS

Characteristic	Symbol	Max	Unit		
Total Device Dissipation – FR–5 Board (Note 1) @T <sub>A</sub> = 25°C Derate above 25°C	P <sub>D</sub>	225 1.8	mW mW/°C		
Thermal Resistance, Junction-to-Ambient	$R_{\theta JA}$	556	°C/W		
Total Device Dissipation – Alumina Substrate, (Note 2) @T <sub>A</sub> = 25°C Derate above 25°C	P <sub>D</sub>	300 2.4	mW mW/°C		
Thermal Resistance, Junction-to-Ambient	$R_{\theta JA}$	417	°C/W		
Total Device Dissipation – Heat Spreader or equivalent, (Note 4) $@T_A = 25^{\circ}C$	P <sub>D</sub>	350	mW		
Thermal Resistance, Junction-to-Ambient	$R_{\theta JA}$	357	°C/W		
Junction and Storage Temperature	T <sub>J</sub> , T <sub>stq</sub>	-55 to +150	°C		


Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

- 1. FR-5 =  $1.0 \times 0.75 \times 0.062$  in.
- 2. Alumina =  $0.4 \times 0.3 \times 0.024$  in. 99.5% alumina.
- 3. Reference SOA curve.
- 4. Heat Spreader or equivalent = 450 mm<sup>2</sup>, 2 oz.



#### ON Semiconductor®

#### www.onsemi.com





SOT-23 (TO-236AB) CASE 318 STYLE 6

#### **MARKING DIAGRAM**



2F = Device Code M = Date Code\* ■ = Pb-Free Package

(Note: Microdot may be in either location)
\*Date Code orientation and/or overbar may vary depending upon manufacturing location.

#### **ORDERING INFORMATION**


Device	Package	Shipping <sup>†</sup>
MMBT2907ALT1G	SOT-23	3000 / Tape &
SMMBT2907ALT1G	(Pb-Free)	Reel
MMBT2907ALT3G	SOT-23	10,000 / Tape &
SMMBT2907ALT3G	(Pb-Free)	Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

## $\textbf{ELECTRICAL CHARACTERISTICS} \ (T_A = 25^{\circ}\text{C unless otherwise noted})$

Charac	Symbol	Min	Max	Unit	
OFF CHARACTERISTICS			•	•	'
Collector-Emitter Breakdown Voltage (No $(I_C = -1.0 \text{ mAdc}, I_B = 0)$ $(I_C = -10 \text{ mAdc}, I_B = 0)$	te 5)	V <sub>(BR)CEO</sub>	-60 -60	- -	Vdc
Collector – Base Breakdown Voltage (I <sub>C</sub> :	= –10 μAdc, I <sub>E</sub> = 0)	V <sub>(BR)CBO</sub>	-60	_	Vdc
Emitter – Base Breakdown Voltage (I <sub>E</sub> = -	-10 μAdc, I <sub>C</sub> = 0)	V <sub>(BR)EBO</sub>	-5.0	_	Vdc
Collector Cutoff Current (V <sub>CE</sub> = −30 Vdc,	$V_{EB(off)} = -0.5 \text{ Vdc}$	I <sub>CEX</sub>	-	-50	nAdc
Collector Cutoff Current $(V_{CB} = -50 \text{ Vdc}, I_E = 0)$ $(V_{CB} = -50 \text{ Vdc}, I_E = 0, T_A = 125^{\circ}\text{C})$	I <sub>CBO</sub>	- -	-0.010 -10	μAdc	
Base Cutoff Current (V <sub>CE</sub> = -30 Vdc, V <sub>EI</sub>	B(off) = -0.5  Vdc	I <sub>BL</sub>	-	-50	nAdc
ON CHARACTERISTICS					
DC Current Gain $ \begin{aligned} &(I_C = -0.1 \text{ mAdc, } V_{CE} = -10 \text{ Vdc}) \\ &(I_C = -1.0 \text{ mAdc, } V_{CE} = -10 \text{ Vdc}) \\ &(I_C = -10 \text{ mAdc, } V_{CE} = -10 \text{ Vdc}) \\ &(I_C = -150 \text{ mAdc, } V_{CE} = -10 \text{ Vdc}) \\ &(I_C = -500 \text{ mAdc, } V_{CE} = -10 \text{ Vdc}) \end{aligned} $	te 5)	h <sub>FE</sub>	75 100 100 100 50	- - - 300	-
Collector – Emitter Saturation Voltage (Not $(I_C = -150 \text{ mAdc}, I_B = -15 \text{ mAdc})$ (Not $(I_C = -500 \text{ mAdc}, I_B = -50 \text{ mAdc})$	*	V <sub>CE(sat)</sub>	- -	-0.4 -1.6	Vdc
Base – Emitter Saturation Voltage (Note 5) $ (I_C = -150 \text{ mAdc}, I_B = -15 \text{ mAdc}) $ $ (I_C = -500 \text{ mAdc}, I_B = -50 \text{ mAdc}) $		V <sub>BE(sat)</sub>	- -	-1.3 -2.6	Vdc
SMALL-SIGNAL CHARACTERISTICS					
Current – Gain – Bandwidth Product (Notes 5, 6), (I <sub>C</sub> = –50 mAdc, V <sub>CE</sub> = –20 Vdc, f = 100 MHz)		f <sub>T</sub>	200	_	MHz
Output Capacitance (V <sub>CB</sub> = -10 Vdc, I <sub>E</sub> = 0, f = 1.0 MHz)		C <sub>obo</sub>	-	8.0	pF
Input Capacitance (V <sub>EB</sub> = -2.0 Vdc, I <sub>C</sub> = 0, f = 1.0 MHz)		C <sub>ibo</sub>	-	30	
SWITCHING CHARACTERISTICS					
Turn-On Time		t <sub>on</sub>	-	45	
Delay Time	$(V_{CC} = -30 \text{ Vdc}, I_{C} = -150 \text{ mAdc}, I_{B1} = -15 \text{ mAdc})$	t <sub>d</sub>	-	10	]
Rise Time	,	t <sub>r</sub>	_	40	]
Turn-Off Time		t <sub>off</sub>	-	100	ns
Storage Time $(V_{CC} = -6.0 \text{ Vdc}, I_C = -150 \text{ mAdc})$ $I_{B1} = I_{B2} = -15 \text{ mAdc})$		ts	-	80	
Fall Time	-51 -52 -5 (35)	t <sub>f</sub>	_	30	

- 5. Pulse Test: Pulse Width  $\leq$  300  $\mu$ s, Duty Cycle  $\leq$  2.0%.
- 6.  $f_T$  is defined as the frequency at which  $|h_{fe}|$  extrapolates to unity.








Figure 2. Storage and Fall Time Test Circuit

#### TYPICAL CHARACTERISTICS




Figure 3. DC Current Gain




Figure 4. Collector Saturation Region




Figure 5. Turn-On Time





Figure 6. Turn-Off Time

# TYPICAL SMALL-SIGNAL Characteristics NOISE FIGURE


 $V_{CE} = 10 \text{ Vdc}, T_A = 25^{\circ}\text{C}$ 



8.0 NF, NOISE FIGURE (dB) 6.0  $I_C = -50 \mu A$ -100 μA -500 μA 4.0 1.0 mA 2.0 100 200 2.0 k 50 k **5**0 1.0 k 5.0 k 10 k 20 k R<sub>s</sub>, SOURCE RESISTANCE (OHMS)

Figure 7. Frequency Effects

Figure 8. Source Resistance Effects







Figure 9. Capacitances

Figure 10. Current-Gain - Bandwidth Product







Figure 11. Collector Emitter Saturation Voltage vs. Collector Current

Figure 12. Base Emitter Saturation Voltage vs.
Collector Current

# TYPICAL SMALL-SIGNAL Characteristics NOISE FIGURE

 $V_{CE}$  = 10 Vdc,  $T_A$  = 25°C



+0.5

0

R<sub>0</sub>VC for V<sub>CE(sat)</sub>

-1.5

-2.0

R<sub>0</sub>VB for V<sub>BE</sub>

-2.5

-0.1 -0.2 -0.5 -1.0 -2.0 -5.0 -10 -20 -500

I<sub>C</sub>, COLLECTOR CURRENT (mA)

Figure 13. Base Emitter Voltage vs. Collector Current

Figure 14. Temperature Coefficients





Figure 15. Safe Operating Area

#### PACKAGE DIMENSIONS

#### SOT-23 (TO-236) CASE 318-08 **ISSUE AP**



NOTES:

- DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982
- 1902.
  CONTROLLING DIMENSION: INCH.
  MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH
  THICKNESS. MINIMUM LEAD THICKNESS IS THE MINIMUM THICKNESS OF BASE MATERIAL
- DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH,


FRO	INOSICINA	ILYIMETE	RS			
DIM	MIN	NOM	MAX	MIN	NOM	MAX
Α	0.89	1.00	1.11	0.035	0.040	0.044
A1	0.01	0.06	0.10	0.001	0.002	0.004
b	0.37	0.44	0.50	0.015	0.018	0.020
С	0.09	0.13	0.18	0.003	0.005	0.007
D	2.80	2.90	3.04	0.110	0.114	0.120
E	1.20	1.30	1.40	0.047	0.051	0.055
е	1.78	1.90	2.04	0.070	0.075	0.081
L	0.10	0.20	0.30	0.004	0.008	0.012
L1	0.35	0.54	0.69	0.014	0.021	0.029
HE	2.10	2.40	2.64	0.083	0.094	0.104
θ	0°		10°	0°		10°

STYLE 6: PIN 1. BASE

2. **EMITTER** 

- COLLECTOR

#### **SOLDERING FOOTPRINT\***



\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and the (III) are registered trademarks of Semiconductor Components Industries, LLC (SCILLC) or its subsidiaries in the United States and/or other countries. SCILLC owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of SCILLC's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

#### **PUBLICATION ORDERING INFORMATION**

#### LITERATURE FULFILLMENT

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada

Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910 Japan Customer Focus Center

Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative