# Single Non-Inverting Buffer with Open Drain Output

The NL17SZ07 is a high performance single non–inverting buffer with open drain outputs operating from a 1.65 to 5.5 V supply.

The Output stage is open drain with Over Voltage Tolerance. This allows the NL17SZ07 to be used to interface 5.0 V circuits to circuits of any voltage between 0 and +7.0 V.

# Features

- Tiny SOT-353, SOT-553 and SOT-953 Packages
- Extremely High Speed:  $t_{PD}$  2.5 ns (typical) at  $V_{CC}$  = 5 V
- Designed for 1.65 V to 5.5 V  $V_{CC}$  Operation, CMOS Compatible
- Over Voltage Tolerant Inputs  $V_{IN}$  may be Between 0 and 7.0 V for  $V_{CC}$  Between 0.5 and 5.5 V
- TTL Compatible Interface Capability with 5.0 V TTL Logic with  $V_{CC}$  = 2.7 V to 3.6 V
- LVCMOS Compatible
- 24 mA Output Sink Capability, Pullup may be between 0 and 7.0 V
- Near Zero Static Supply Current Substantially Reduces System Power Requirements
- Chip Complexity: FET = 20
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant



Figure 1. Pinout



Figure 2. Logic Symbol



# **ON Semiconductor®**

www.onsemi.com



6 = Specific Device Code M = Month Code

# ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 5 of this data sheet.

## **PIN ASSIGNMENT** (SOT-353 / SOT-553)

Pin	Function
1	NC
2	IN A
3	GND
4	OUT Y
5	V <sub>CC</sub>

# **PIN ASSIGNMENT (SOT-953)**

Pin	Function
1	IN A
2	GND
3	NC
4	OUT Y
5	V <sub>CC</sub>

#### **FUNCTION TABLE**

Input	Output
Α	Y
L	L
Н	Z

## MAXIMUM RATINGS

Symbol	Cha	racteristics	Value	Unit
V <sub>CC</sub>	DC Supply Voltage		-0.5 to +7.0	V
VI	DC Input Voltage		$-0.5 \le V_{l} \le +7.0$	V
Vo	DC Output Voltage (SOT-953 Pack	(Note 1)	–0.5 to V <sub>CC</sub> + 0.5	V
	DC Output Voltage (SOT–353 / SOT–553 Packages)	Active Mode, LOW State (Note 1) Tri–State Mode Power–Down Mode (V <sub>CC</sub> = 0 V)	-0.5 to V <sub>CC</sub> + 0.5 -0.5 to +7.0 -0.5 to +7.0	
I <sub>OK</sub>	DC Output Diode Current (SOT–953 Package) (SOT–353 / SOT–553 Packages)	$V_O < GND, V_O > V_{CC}$ $V_O < GND$	±50 -50	mA
I <sub>IK</sub>	DC Input Diode Current	-50	mA	
Ι <sub>Ο</sub>	DC Output Sink Current	±50	mA	
I <sub>CC</sub>	DC Supply Current per Supply Pin	±100	mA	
I <sub>GND</sub>	DC Ground Current per Ground Pin		±100	mA
T <sub>STG</sub>	Storage Temperature Range		-65 to +150	°C
PD	Power Dissipation in Still Air	SOT-353 SOT-553	186 135	mW
$\theta_{JA}$	Thermal Resistance	SOT-353 SOT-553	350 496	°C/W
TL	Lead Temperature, 1 mm from Case	for 10 Seconds	260	°C
TJ	Junction Temperature Under Bias		+150	°C
I <sub>Latch-Up</sub>	Latch–Up Performance A	bove $V_{CC}$ and Below GND at 85°C (Note 5)	±100	mA
MSL	Moisture Sensitivity		Level 1	
F <sub>R</sub>	Flammability Rating	Oxygen Index: 28 to 34	UL 94 V–0 @ 0.125 in	
ESD	ESD Classification	Human Body Model (Note 3) Machine Model (Note 4) Charged Device Model (Note 5)	2000 200 N/A	V V

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.
I<sub>O</sub> absolute maximum rating must be observed.
Tested to EIA/JESD22-A114-A, rated to EIA/JESD22-A114-B.
Tested to EIA/JESD22-A115-A, rated to EIA/JESD22-A115-A.

4. Tested to JESD22-C101-A.

5. Tested to EIA/JESD78.

# **RECOMMENDED OPERATING CONDITIONS**

Symbol	I Parameter		Min	Max	Unit
V <sub>CC</sub>	Supply Voltage	Operating Data Retention Only	1.65 1.5	5.5 5.5	V
VI	Input Voltage		0	5.5	V
Vo	Output Voltage (SOT-953 Package)		0	V <sub>CC</sub>	V
	Output Voltage (SOT-353 / SOT-553 Packages)	Active Mode, LOW State Tri–State Mode Power–Down Mode (V <sub>CC</sub> = 0 V)	0 0 0	V <sub>CC</sub> 5.5 5.5	
T <sub>A</sub>	Operating Free–Air Temperature		-55	+125	°C
Δt/ΔV	Input Transition Rise or Fall Rate	$V_{CC} = 2.5 V \pm 0.2 V V_{CC} = 3.0 V \pm 0.3 V V_{CC} = 5.0 V \pm 0.5 V$	0 0 0	20 10 5	ns/V

Functional operation above the stresses listed in the Recommended Operating Ranges is not implied. Extended exposure to stresses beyond the Recommended Operating Ranges limits may affect device reliability.

#### DC ELECTRICAL CHARACTERISTICS

			$T_{A} = 25^{\circ}C$ $-55^{\circ}C \le T_{A} \le 125^{\circ}C$		<sub>λ</sub> ≤ 125°C				
Symbol	Parameter	Condition	VCC (V)	Min	Тур	Max	Min	Max	Unit
V <sub>IH</sub>	High–Level Input Voltage		1.65 to 1.95 2.3 to 5.5	0.75 V <sub>CC</sub> 0.7 V <sub>CC</sub>			0.75 V <sub>CC</sub> 0.7 V <sub>CC</sub>		V
VIL	Low–Level Input Voltage		1.65 to 1.95 2.3 to 5.5			0.25 V <sub>CC</sub> 0.3 V <sub>CC</sub>		0.25 V <sub>CC</sub> 0.3 V <sub>CC</sub>	V
I <sub>LKG</sub>	Z–State Output Leakage Current	$V_{IN} = V_{IH}$ $V_{OUT} = V_{CC}$ or GND	2.3 to 5.5			±5.0		±10.0	μΑ
V <sub>OL</sub>	Low–Level Output	I <sub>OL</sub> = 100 μA	1.65 to 5.5		0.0	0.1		0.1	V
	$V_{IN} = V_{IL}$	I <sub>OL</sub> = 4 mA	1.65		0.08	0.24		0.24	
		I <sub>OL</sub> = 8 mA	2.3		0.20	0.3		0.3	
		I <sub>OL</sub> = 12 mA	2.7		0.22	0.4		0.4	
		I <sub>OL</sub> = 16 mA	3.0		0.28	0.4		0.4	
		I <sub>OL</sub> = 24 mA	3.0		0.38	0.55		0.55	
		I <sub>OL</sub> = 32 mA	4.5		0.42	0.55		0.55	
I <sub>IN</sub>	Input Leakage Current	$V_{IN} = 5.5 \text{ V or GND}$	0 to 5.5			±0.1		±1.0	μΑ
I <sub>OFF</sub>	Power Off Leakage Current (SOT-353/ SOT-553 Packages)	V <sub>IN</sub> = 5.5 V or V <sub>OUT</sub> = 5.5 V	0			1		10	μΑ
I <sub>CC</sub>	Quiescent Supply Current	$V_{IN} = 5.5 \text{ V or GND}$	5.5			1		10	μΑ
I <sub>CCT</sub>	Quiescent Supply Current	V <sub>IN</sub> = 3.0 V	3.6			10		100	μΑ

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

				Г	A = 25°	C	–55°C ≤T,	<sub>A</sub> ≤ 125°C	
Symbol	Parameter	Condition	V <sub>CC</sub> (V)	Min	Тур	Max	Min	Max	Unit
t <sub>PZL</sub>	Propagation Delay	$R_{L=} R_1 = 500 \Omega, C_L = 50 pF$	$1.8\pm0.15$	0.8	5.3	11.6	0.8	12.0	ns
	(Figure 3 and 4)		$2.5\pm0.2$	1.2	3.7	5.8	1.2	6.4	
			$3.3\pm0.3$	0.8	2.9	4.4	0.8	4.8	
			$5.0\pm0.5$	0.5	2.3	3.5	0.5	3.9	
t <sub>PLZ</sub>	Propagation Delay	$R_{L=} R_1 = 500 \Omega, C_L = 50 pF$	$1.8\pm0.15$	0.8	5.3	11.6	0.8	1.20	ns
	(Figure 3 and 4)		$2.5\pm0.2$	1.2	2.8	5.8	1.2	6.4	
			$3.3\pm0.3$	0.8	2.1	4.4	0.8	4.8	
			$5.0\pm0.5$	0.5	1.4	3.5	0.5	3.9	

# AC ELECTRICAL CHARACTERISTICS $t_R$ = $t_F$ = 2.5 ns; $C_L$ = 50 pF; $R_L$ = 500 $\Omega$

# **CAPACITIVE CHARACTERISTICS**

Symbol	Parameter	Condition	Typical	Unit
C <sub>IN</sub>	Input Capacitance	$V_{CC}$ = 5.5 V, $V_{I}$ = 0 V or $V_{CC}$	>2.5	pF
C <sub>OUT</sub>	Output Capacitance	$V_{CC}$ = 5.5 V, $V_{I}$ = 0 V or $V_{CC}$	4.0	pF
C <sub>PD</sub>	Power Dissipation Capacitance (Note 6)	10 MHz, $V_{CC}$ = 5.5 V, $V_{I}$ = 0 V or $V_{CC}$	4.0	pF

6.  $C_{PD}$  is defined as the value of the internal equivalent capacitance which is calculated from the operating current consumption without load. Average operating current can be obtained by the equation:  $I_{CC(OPR)} = C_{PD} \bullet V_{CC} \bullet f_{in} + I_{CC}$ .  $C_{PD}$  is used to determine the no–load dynamic power consumption;  $P_D = C_{PD} \bullet V_{CC} \bullet f_{in} + I_{CC} \bullet V_{CC}$ .







 $R_T = Z_{OUT}$  of pulse generator (typically 50  $\Omega$ )

Figure 4. Test Circuit

# **DEVICE ORDERING INFORMATION**

Device	Package	Shipping <sup>†</sup>
NL17SZ07DFT2G	SOT-353/SC70-5/SC-88A (Pb-Free)	3000 / Tape & Reel
NL17SZ07XV5T2G	SOT-553 (Pb-Free)	4000 / Tape & Reel
NL17SZ07P5T5G	SOT–953 (Pb–Free)	8000 / Tape & Reel

+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

# PACKAGE DIMENSIONS

SC-88A (SC-70-5/SOT-353) CASE 419A-02 ISSUE L







NOTES: 1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982. 2. CONTROLLING DIMENSION: INCH. 3. 419A-01 OBSOLETE. NEW STANDARD 419A-02. 4. DIMENSIONS A AND B DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS.

	INCHES		MILLIN	IETERS
DIM	MIN	MAX	MIN	MAX
Α	0.071	0.087	1.80	2.20
В	0.045	0.053	1.15	1.35
С	0.031	0.043	0.80	1.10
D	0.004	0.012	0.10	0.30
G	0.026	BSC	0.65 BSC	
Н		0.004		0.10
ſ	0.004	0.010	0.10	0.25
K	0.004	0.012	0.10	0.30
Ν	0.008 REF		0.20	REF
s	0.079	0.087	2.00	2.20

**SOLDER FOOTPRINT\*** 



\*For additional information on our Pb–Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

# PACKAGE DIMENSIONS

SOT-553 **XV5 SUFFIX** CASE 463B ISSUE C



NOTES: 1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982. 2. CONTROLLING DIMENSION: MILLIMETERS 3. MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH THICKNESS OF MATERIAL. INCHES

	MILLIMETERS				INCHES	
DIM	MIN	NOM	MAX	MIN	NOM	MAX
Α	0.50	0.55	0.60	0.020	0.022	0.024
b	0.17	0.22	0.27	0.007	0.009	0.011
С	0.08	0.13	0.18	0.003	0.005	0.007
D	1.55	1.60	1.65	0.061	0.063	0.065
Е	1.15	1.20	1.25	0.045	0.047	0.049
е	0.50 BSC				0.020 BSC	<u>,</u>
L	0.10	0.20	0.30	0.004	0.008	0.012
ΗE	1.55	1.60	1.65	0.061	0.063	0.065

#### **SOLDERING FOOTPRINT\***

HE

С



\*For additional information on our Pb–Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

#### PACKAGE DIMENSIONS

SOT-953 CASE 527AE ISSUE E



TOP VIEW





NOTES: 1. DIMENSIONING AND TOLERANCING PER ASME Y14 5M 1994

 Minerol AND TOELIKARDING FER AD Y14.5M, 1994.
 CONTROLLING DIMENSION: MILLIMETERS
 MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH. MINIMUM LEAD THICKNESS IS THE

- FINISH. MINIMUM LEAD THICKNESS IS THE MINIMUM THICKNESS OF THE BASE MATERIAL. 4. DIMENSIONS D AND E DO NOT INCLUDE MOLD
- 4. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS.

	MILLIMETERS				
DIM	MIN	NOM	MAX		
Α	0.34	0.37	0.40		
b	0.10	0.15	0.20		
С	0.07	0.12	0.17		
D	0.95	1.00	1.05		
Е	0.75	0.80	0.85		
е		0.35 BS	С		
HE	0.95	1.00	1.05		
L	0.175 REF				
L2	0.05	0.10	0.15		
L3			0.15		

#### **SOLDERING FOOTPRINT\***



\*For additional information on our Pb–Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and the intervent and the inter

#### PUBLICATION ORDERING INFORMATION

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303–675–2175 or 800–344–3860 Toll Free USA/Canada Fax: 303–675–2176 or 800–344–3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support:

Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81–3–5817–1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative