



Spring-Cage Feed-Through Terminal Blocks ST

Article description	ST 1,5 *
Article no.	3031076 *
EC-TYPE EXAMINATION CERTIFICATE IECEX-CERTIFICATE	KEMA 01ATEX2129 U * IECEX KEM 06.0043U *
Marking	 Ex eb IIC KEMA 01ATEX2129 U IECEX KEM 06.0043U
Assembly on mounting rails	NS 35 acc. to EN 60715-TH 35
Stripping length	10 mm
Assembly instructions	See page 2
Operating temperature range	-60 °C ... +110 °C



Technical data according to IEC/EN 60079-7 (increased safety „e“)

Rated insulation voltage	400 V	
Rated voltage	440 V	
Nominal current	17,5 A (ΔT 40 K)	17,5 A (ΔT 45 K)
Max. rated current	17,5 A (ΔT 40 K)	17,5 A (ΔT 45 K)
Temperature rise	33 K (17,7 A / 1,5 mm ²)	38 K (18,9 A / 1,5 mm ²)
Contact resistance	1,43 m Ω	
Connection capacity		
Rated cross-section	1,5 mm ²	AWG 16
Max. conductor cross-section	1,5 mm ²	AWG 16
Connectable conductor cross-section	0,08 - 1,5 mm ² rigid 0,08 - 1,5 mm ² flexible	AWG 28 - 16 AWG 28 - 16

Data of insulation material

Description	PA 6.6
Creep resistance acc. to IEC 60112 / material group	CTI 600 / I

Accessories	Description	Article no.	
Cover	D-ST 2,5	3030417	
Partition plate	ATP-ST 4	3030721	
Jumper	FBS 2-4	3030116	Max. 17 A / 1,5 mm ² ΔT 40 K Max. 17,5 A / 1,5 mm ² ΔT 45 K
	FBS 3-4	3030129	
	FBS 4-4	3030132	
	FBS 5-4	3030145	
	FBS 10-4	3030158	
	FBS 20-4	3030352	

* valid for colour variants

Important assembly instructions – increased safety „e“

The Protective Conductor Terminal Blocks is suitable for use in enclosures in Atmospheres with flammable gases or combustible dust. For flammable gases these enclosures must satisfy the requirements according to IEC/EN 60079-0 and IEC/EN 60079-7. For combustible dust these enclosures must satisfy the relevant requirements according to IEC/EN 60079-31.


When assembling with other certified series and sizes of terminal blocks and using accessories designed for the purpose, the required creepage distances and clearances have to be observed.

When using the jumpers to achieve a skipped bridging the rated voltage is reduced to 352 V.
When using cut-to-length plug-in bridges data and examples of use have to be observed as enclosure.

If conductors with smaller cross section than the rated cross section are used, the assigned lower current has to be specified in the EC-Type Examination Certificate of the complete apparatus.

The Terminal Blocks may be used, based on the self-heating when used at the nominal current and at ambient temperatures of -60 °C to +40 °C at the mounting position in electrical apparatus, e.g. junction and connection boxes, for temperature class T6. When the Terminal Blocks are used in electrical apparatus of temperature classes T1 up to T5, the highest temperature of the insulating material shall not exceed the maximum value of the operating temperature range.

The Terminal Blocks and their appropriate accessories have to be assembled as specified below.



Operational instructions – Intrinsic safety “i”

IEC/EN 60079-14 Clause 12 describes modular terminal blocks as simple apparatus when used in intrinsically-safe circuits. Testing by a notified body and marking is not required. If terminal blocks be identifiable as part of an intrinsically circuit are marked by a colour, the colour used shall be **light blue**.

Testing for compliance to intrinsically safe requirements including clearance, creepage, and solid insulation distances specified in IEC/EN 60079-0 and IEC/EN 60079-11 have been performed for circuits up to **60 V**.

Compliance with distance requirements of IEC/EN 60079-14 Clause 12.2.3 for the connection of separated intrinsically-safe circuit accessories is met. A minimum distance of 50 mm to separate clamping units of intrinsically-safe and non intrinsically-safe circuits is required through the use of a separating plate or similar device.

Attestation of Conformity

The above mentioned product is in line with the provisions of the below marked directive and their modification directive(s):

2014/34/EU ATEX Directive

Compliance with Essential Health and Safety Requirements has been assured by compliance with:


EN 60079-0:2012	EN 60079-7:2007
IEC 60079-0:2011 (Ed.6)	IEC 60079-7:2006 (Ed.4)

The conformity with the provisions of the ATEX directive were certified by

Notified Body:	DEKRA Certification B.V.
Address:	Utrechtseweg 310, NL-6812 AR Arnhem, The Netherlands [Ident.-No.: 0344]
Certificate: (No., Date)	KEMA 01ATEX2129 U, 2012-11-30

Blomberg, 2016-04-20



A. Gerhard Leßmann
Business Unit Industrial Cabinet
Connectivity
Ex-Representative



Ralf Berndt
Business Unit Industrial Cabinet
Connectivity
Vice President

This attestation certifies the conformity with the indicated directive, it does not, however, covenant any characteristics. The instructions for safety and installation have to be observed.

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstraße 8
32825 Blomberg
Germany


 +49 – (0) 52 35 – 3-00

 +49 – (0) 52 35 – 3-4 12 00

 www.phoenixcontact.com

Enclosure

Notes on the application of cut-to-length plug-in bridges



Depending on the separating plate between directly facing plug-in bridges, the rated voltages reduces to

- 1) 220V with D-ST 2,5
- 2) 275 V with ATP-ST 4

when using cut-to-length plug-in bridges.

Other combinations as presented are not permissible and therefore not covered by the certificate.