

MB1S THRU MB10S

0.8A SURFACE MOUNT GLASS PASSIVATED BRIDGE RECTIFIER

FEATURES:


- Glass Passivated Chip Junction
- Reverse Voltage 100 to 1000 V
- Forward Current 0.8 A
- High Surge Current Capability
- Designed for Surface Mount Application

MECHANICAL DATA

- Case: MBS
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight: 100mg /0.0035oz

PINNING

PIN	DESCRIPTION	
1	Input Pin (~)	
2	Input Pin (~)	
3	Output Anode (+)	
4	Output Cathode(-)	



Maximum Ratings and Electrical characteristics

Ratings at 25 °C ambient temperature unless otherwise specified. Single phase half-wave 60 Hz, resistive or inductive load, for capacitive load current derate by 20 %.

Parameter		Symbols	MB1S	MB2S	MB4S	MB6S	MB8S	MB10S	Units
Maximum Repetitive Peak Reverse Voltage		Vrrm	100	200	400	600	800	1000	V
Maximum RMS voltage		V _{RMS}	70	140	280	420	560	700	V
Maximum DC Blocking Voltage		V _{DC}	100	200	400	600	800	1000	V
Average Rectified Output Current at Ta = $50 ^{\circ}\text{C}$		Io	0.8						
Peak Forward Surge Current 8.3 ms Single Half Sine Wave Superimposed on Rated Load (JEDEC Method)		Ifsm	30						
Maximum Forward Voltage	at 0.4 A at 0.8 A	VF	1.0				v		
Maximum DC Reverse Current at Rated DC Blocking Voltage	@T _A =25 °C @T _A =125 °C	Ir	5 40					μA	
Typical Junction Capacitance (Note1)		Cj	13						pF
Typical Thermal Resistance (Note2)		R _{0JA}	95						
		Rejl	30						
Operating and Storage Temperati	Tj, Tstg	-55 ~ +150						°C	

Note: 1. Measured at 1MHz and applied reverse voltage of 4 V D.C.

2. Mounted on glass epoxy PC board with $4{\times}(5{\times}5mm^2$) copper pad.


SHIKE MAKE CONSCIOUS PRODUCT

CONSCIOUS PRODUCTS BEGIN WITH CONSCIOUS PEOPLE







MB1S THRU MB10S












Fig.2 Typical Reverse Characteristics





Fig.4 Typical Junction Capacitance



SHIKE MAKE CONSCIOUS PRODUCT CONSCIOUS PRODUCTS BEGIN WITH CONSCIOUS PEOPLE







MB1S THRU MB10S


PACKAGE OUTLINE

Plastic surface mounted package; 4 leads






MBS mechanical data



UNIT		А	С	D	E	Η _ε	d	e	L	L ₁	а	Z
mm	max	2.6	0.22	5.0	4.1	7.0	2.7	0.7	1.7	1.1	0.2	
	min	2.2	0.15	4.5	3.6	6.4	2.3	0.5	1.3	0.5		7∘
	max	102	8.7	197	161	276	106	28	67	43	8	(
mil	min	94	5.9	177	142	252	91	20	51	20		

The recommended mounting pad size



Marking

Type number	Marking code					
MB1S	MB1S					
MB2S	MB2S					
MB4S	MB4S					
MB6S	MB6S					
MB8S	MB8S					
MB10S	MB10S					

SHIKE MAKE CONSCIOUS PRODUCT CONSCIOUS PRODUCTS BEGIN WITH CONSCIOUS PEOPLE

