


Hybrid Conductive Polymer Type / Radial Lead Type

RoHS compliance

HEH Series

105°C
High Voltage, Long Life




- 105°C 4,000 to 10,000hours
- Laminated case
- Solvent proof (within 2 minutes)

HET (On the web)
↑ 135°C
HEP (On the web)
↑ 125°C
HEH

Specifications

Items	Condition	Specifications								
Rated voltage (V)	—	16	25	35	40	50	63	80	100	
Surge voltage (V)	Room temperature	20	32	44	50	63	79	100	125	
Category temperature range (°C)	—	-55 to +105								
Capacitance tolerance (%)	120Hz/20°C	M : ±20								
Dissipation Factor (tan δ)	tan δ (max) 120Hz/20°C	0.16								
Leakage current (LC)	μA/after 2minutes (max)	The greater value of either 0.05CV or 100								
Endurance	105°C rated voltage applied (With the rated ripple current)	Test	16V	φ6.3 : 4,000hours, D≥φ8 : 7,000hours						
			25V _s	φ6.3 : 5,000hours, D≥φ8 : 10,000hours						
		ΔC/C	Within ±30% of the initial value							
		tan δ	Less than 200% of the specified value							
		ESR	Less than 200% of the specified value							
		LC	Less than the specified value							

Marking, Dimensions



Size, ESR, Rated Ripple Current

μF	V	16		25		35		40	
27								6.3x7.2	70 1250
47						6.3x7.2	60 1300		
56								8x9.5	32 1750
68				6.3x7.2	45 1400				
100						8x9.5	30 1800	10x9.5	24 2400
120	6.3x7.2	40 1500						10x11.5	18 2750
150				8x9.5	27 1900	10x9.5	23 2470		
220						10x11.5	17 2830		
270	8x9.5	26 2000		10x9.5	22 2530				
330				10x11.5	16 2900				
470	10x9.5	21 2600							
560	10x11.5	15 3000							

μF	V	50		63		80		100	
10				6.3x7.2	100 1060			10x9.5	80 1450
12						10x9.5	70 1600	10x9.5	80 1450
15	6.3x7.2	80 1200				10x9.5	70 1600	10x11.5	60 1660
18						10x11.5	50 1830		
22				8x9.5	40 1560				
33				8x9.5 ★	40 1560				
				10x9.5	30 2100				
47	8x9.5	35 1670		10x9.5	30 2100				
56	10x9.5	25 2320		10x11.5	22 2400				
82	10x11.5	19 2650							

Please refer to page 19 for ripple current frequency coefficients.
★S type

Rated ripple current
mA Arms (100kHz, 105°C)

Case size: φDxL (mm)
ESR (mΩ) max at 100kHz, 20°C

Part number

