

# 晶创和立科技

## **GL3549**

### MINIATURE CADMIUM SULPHIDE PHOTOCONDUCTIVE CELL




## **FEATURES**


Miniature open frame package Epoxy coated Moisture resistant Spectral response similar to the human eye Applications include dusk-dawn lighting control

### LIGHT DEPENDENT RESISTOR

CDS 光敏电阻尺寸图 • 3 系列

单位: .....





Dimensions in millimetres

## SPECIFICATION AND PERFORMANCE

Model	Vmax (VDC)	Pmax (mW)	Ambient temp( )	Spectral peak (nm)	Light Resistance at 10Lux (Kl,)	Dark Resistance (Ml,)	Gamm a value at 100- 10Lux	Response Time (ms)	
								Rise Time	Decay time
GL3549	150	100	-30~+70	540	50-100	20	0.7	20	30

## **Measuring Conditions**

### 1. Light resistance:

Measured at 10 Lux with standard light A (2854K color temperature) and 2hr illumination at 400-600 lux prior to testing.

#### 2. Dark Resistance:

Measured 10 senconds after closed 10 lux.

### 3. Gamma Characteristic:

Between 10 lux ande 100 lux and given by  ${}^{\downarrow}\tilde{A} = Ig(R10/R100)$ 

R10、R100 Cell resistance at 10 lux and 100 lux.


The error of  $|\tilde{A}| = 0.1$ .


### 4. Pmax:

Max. power dissipation at ambient temperature of 25 .

#### 5. Vmax:

Max. voltage in darkness that may be applied to the cell continuously.





照度-阻值特性图

SHENZHEN JINGCHUANGHELI TECHNOLOGY CO., LTD.

Tel:+86-755-33693441 Fax:+86-755-33693443

Http://www.szjchl.com E-mail:heli@szjchl.com