



### SPECIFICATIONS

#### 1.ELECTRICAL

● Contact rating	0.1A, 30VDC
● Contact resistance	50mWMax.
● Insulation resistance	100MWMin. at 250VDC
● Dielectric strength	250VAC Min. for 60 sec.



**2P ON-OFF**

⑤	Terminal	—	2	Brass	ag Plated	—
④	Contact	—	2	Phosphor Bronze	ag Plated	—
③	Base	—	1	Poly		—
②	Cover	—	1	Pa66		—
①	Keystake	—	1	Daicel		—
ITEM	PAPT NAMF	TER,NO	QTY	MATERIAL	FINISHING	REMARK

					ANGLAR	±5°	DSND		DATE		SCALE: N/A	MODEL TYPE:		
Δx					X.X	±0.2mm	DWN		DATE		VIEW:	KEY SWITCH		
Δx					X.XX	±0.1mm	CHKD		DATE		UNIT: mm/in	PART NO.:		
Δx					X.XXX	±0.05mm	APPD		DATE		SIZE: A4	DWG NO.:		
MARK	DESCRIPTION				DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES				<b>XKB11E01</b>		
REVISIONS							XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT	SHEET	REVISION
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn												1.0g	1/1	A0