SCDS003O - NOVEMBER 1992 - REVISED JULY 2004

- **5-**Ω Switch Connection Between Two Ports
- TTL-Compatible Input Levels

description/ordering information

The 'CBT3383 devices provide ten bits of high-speed TTL-compatible bus switching or exchanging. The low on-state resistance of the switch allows connections to be made with minimal propagation delay.

The devices operate as a 10-bit bus switch or a 5-bit bus exchanger, which provides swapping of the A and B pairs of signals. The bus-exchange function is selected when BX is high. The switches are connected when $\overline{\text{BE}}$ is low.

| SN54CBT3383 JT OR W PACKAGE | | | | | | | | | |
|-----------------------------|-----------------------------------|--|--|--|--|--|--|--|--|
| SN74CBT3383 | . DB, DBQ, DGV, DW, OR PW PACKAGE | | | | | | | | |
| | | | | | | | | | |

| (TOP VIEW) | | | | | | | | | | | |
|------------|---|----|---|----|---|-----------------|--|--|--|--|--|
| BE | d | 1 | Ο | 24 | þ | V _{CC} | | | | | |
| 1B1 | C | 2 | | 23 | þ | 5B2 | | | | | |
| 1A1 | | 3 | | 22 | þ | 5A2 | | | | | |
| 1A2 | Q | 4 | | 21 | p | 5A1 | | | | | |
| 1B2 | Q | 5 | | 20 | p | 5B1 | | | | | |
| 2B1 | Q | 6 | | 19 | p | 4B2 | | | | | |
| 2A1 | Q | 7 | | 18 | p | 4A2 | | | | | |
| 2A2 | Q | 8 | | 17 | | 4A1 | | | | | |
| 2B2 | Q | 9 | | 16 | P | 4B1 | | | | | |
| 3B1 | Q | 10 | | 15 | P | 3B2 | | | | | |
| 3A1 | Q | 11 | | 14 | μ | 3A2 | | | | | |
| GND | q | 12 | | 13 | Ρ | ΒX | | | | | |

ORDERING INFORMATION

| TA | PACKAGE | Et. | ORDERABLE PART NUMBER | TOP-SIDE MARKING |
|----------------|-------------------|---------------|--------------------------|---------------------|
| | SOIC - DW | Tube | SN74CBT3383DW | CDT0000 |
| −40°C to 85°C | SOIC - DW | Tape and reel | SN74CBT3383DWR | CBT3383 |
| | SSOP – DB | Tape and reel | SN74CBT3383DBR | CU383 |
| | SSOP (QSOP) – DBQ | Tape and reel | SN74CBT3383DBQR | CBT3383 |
| | TOOOD DW/ | Tube | SN74CBT3383PW | 011000 |
| | TSSOP – PW | Tape and reel | SN74CBT3383PWR | CU383 |
| | TVSOP – DGV | Tape and reel | SN74CBT3383DGVR | CU383 |
| 55°C to 125°C | CDIP – JT | Tube | SNJ54CBT3383JT | SNJ54CBT3383JT |
| –55°C to 125°C | CFP – W | Tube | SNJ54CBT3383W | SNJ54CBT3383W |

[†] Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at www.ti.com/sc/package.

FUNCTION TABLE

| INP | UTS | INPUTS/OUTPUTS | | | | | |
|-----|-----|----------------|---------|--|--|--|--|
| BE | вх | 1A1-5A1 | 1A2–5A2 | | | | |
| L | L | 1B1–5B1 | 1B2–5B2 | | | | |
| L | Н | 1B2–5B2 | 1B1–5B1 | | | | |
| Н | Х | Z | Z | | | | |



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.


PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.



 $Copyright @ 2004, \ Texas \ Instruments \ Incorporated \\ On products \ compliant to \ MIL-PRF-3853, all \ parameters \ are tested \\ unless \ other \ products, \$

SCDS003O - NOVEMBER 1992 - REVISED JULY 2004

logic diagram (positive logic)



absolute maximum ratings over operating free-air temperature range (unless otherwise noted)[†]

| $\begin{array}{l} \mbox{Supply voltage range, V}_{CC} \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ $ | | –0.5 V to 7 V 128 mA –50 mA |
|---|--------------|-----------------------------------|
| Package thermal impedance, θ_{JA} (see Note 2) | : DB package | 63°C/W |
| | DBQ package | 61°C/W |
| | DGV package | |
| | DW package | 46°C/W |
| | PW package | 88°C/W |
| Storage temperature range, T _{stg} | | –65°C to 150°C |

[†] Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

NOTES: 1. The input and output negative-voltage ratings may be exceeded if the input and output clamp-current ratings are observed.

2. The package thermal impedance is calculated in accordance with JESD 51-7.



SCDS003O - NOVEMBER 1992 - REVISED JULY 2004

recommended operating conditions (see Note 3)

| | | SN54CB | T3383 | SN74CB | T3383 | |
|----------------|----------------------------------|--------|-------|--------|-------|------|
| | | MIN | MAX | MIN | MAX | UNIT |
| VCC | Supply voltage | 4.5 | 5.5 | 4.5 | 5.5 | V |
| VIH | High-level control input voltage | 2 | | 2 | | V |
| VIL | Low-level control input voltage | | 0.8 | | 0.8 | V |
| Τ _Α | Operating free-air temperature | -55 | 125 | 0 | 70 | °C |

NOTE 3: All unused control inputs of the device must be held at V_{CC} or GND to ensure proper device operation. Refer to the TI application report, Implications of Slow or Floating CMOS Inputs, literature number SCBA004.

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

| | | _ | | 0110 | SN | 54CBT33 | 883 | SN7 | 74CBT33 | 83 | |
|---------------------|----------------|--|---------------------------|--------------------------------|----|---------|------|-----|---------|------|------|
| PARAMETER TE | | | EST CONDITI | STCONDITIONS | | | MAX | MIN | TYP† | MAX | UNIT |
| VIK | | $V_{CC} = 4.5 \text{ V}, \qquad I_{I} = -18 \text{ mA}$ | | | | | -1.2 | | | -1.2 | V |
| lj | | $V_{CC} = 5.5 V,$ | V _I = 5.5 V or | GND | | | ±5 | | | ±1 | μΑ |
| ICC | | $V_{CC} = 5.5 V,$ | IO = 0, | $V_I = V_{CC} \text{ or } GND$ | | | 50 | | | 50 | μΑ |
| ∆ICC [‡] | Control inputs | V_{CC} = 5.5 V, One input at 3.4 V, Other inputs at V_{CC} or GND | | | | | 2.5 | | | 2.5 | mA |
| 0 | Control innuto | $V_{I} = 3 V \text{ or } 0$ | | | | | | | 3 | | - 5 |
| Ci | Control inputs | V _I = 2.5 V | | | | | 5 | | | | pF |
| 0 | | $V_{O} = 3 V \text{ or } 0,$ | $\overline{BE} = V_{CC}$ | | | | | | 6 | | - 5 |
| C _{io(OFF} | -) | $V_{O} = 2.5 V$, $\overline{BE} = V_{CC}$ | | | | | 6 | | | | pF |
| | | | N 0 | I _I = 64 mA | | 5 | 9.2 | | 5 | 7 | |
| ron§ | | $V_{CC} = 4.5 V$ | $V_{I} = 0$ | Ij = 30 mA | | | | | 5 | 7 | Ω |
| | | | V _I = 2.4 V, | lj = 15 mA | | 10 | 17 | | 10 | 15 | |

[†] All typical values are at $V_{CC} = 5 \text{ V}$, $T_A = 25^{\circ}\text{C}$.

[‡] This is the increase in supply current for each input that is at the specified TTL voltage level, rather than V_{CC} or GND.

§ Measured by the voltage drop between the input terminal and the output terminal at the indicated current through the switch. On-state resistance is determined by the lowest voltage of the two (A or B) terminals.


switching characteristics over recommended operating free-air temperature range, $C_L = 50 \text{ pF}$ (unless otherwise noted) (see Figure 1)

| DADAMETED | FROM | то | SN54CE | T3383 | SN74CB | | | |
|-------------------|---------|----------|--------|-------|--------|------|------|--|
| PARAMETER | (INPUT) | (OUTPUT) | MIN | MAX | MIN | MAX | UNIT | |
| t _{pd} ¶ | A or B | B or A | | 1.5 | | 0.25 | ns | |
| ^t pd | BX | A or B | 1 | 10.2 | 1 | 9.2 | ns | |
| ten | BE | A or B | 1 | 10.8 | 1 | 8.6 | ns | |
| ^t dis | BE | A or B | 1 | 8.2 | 1 | 7.5 | ns | |

The propagation delay is the calculated RC time constant of the typical on-state resistance of the switch and the specified load capacitance, when driven by an ideal voltage source (zero output impedance).



SCDS003O - NOVEMBER 1992 - REVISED JULY 2004



PARAMETER MEASUREMENT INFORMATION

NOTES: A. CL includes probe and jig capacitance.

B. Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control.

- C. All input pulses are supplied by generators having the following characteristics: PRR \leq 10 MHz, Z_O = 50 Ω , t_r \leq 2.5 ns, t_f \leq 2.5 ns.
- D. The outputs are measured one at a time, with one transition per measurement.
- E. t_{PLZ} and t_{PHZ} are the same as t_{dis} .
- F. t_{PZL} and t_{PZH} are the same as t_{en} .
- G. tPLH and tPHL are the same as tpd.

Figure 1. Load Circuit and Voltage Waveforms





10-Jun-2014

PACKAGING INFORMATION

| Orderable Device | Status | Package Type | Package Drawing | Pins | Package Qty | Eco Plan (2) | Lead/Ball Finish (6) | MSL Peak Temp | Op Temp (°C) | Device Marking (4/5) | Samples |
|------------------|----------|--------------|--------------------|------|----------------|----------------------------|-------------------------|---------------------|--------------|---------------------------------------|---------|
| 5962-9668801QKA | ACTIVE | CFP | W | 24 | 1 | TBD | A42 | N / A for Pkg Type | -55 to 125 | 5962-9668801QK A SNJ54CBT3383W | Samples |
| 5962-9668801QLA | ACTIVE | CDIP | JT | 24 | 1 | TBD | A42 | N / A for Pkg Type | -55 to 125 | 5962-9668801QL A SNJ54CBT3383JT | Samples |
| SN74CBT3383DBLE | OBSOLETE | SSOP | DB | 24 | | TBD | Call TI | Call TI | -40 to 85 | | |
| SN74CBT3383DBQR | ACTIVE | SSOP | DBQ | 24 | 2500 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-2-260C-1 YEAR | -40 to 85 | CBT3383 | Samples |
| SN74CBT3383DBR | ACTIVE | SSOP | DB | 24 | 2000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM | -40 to 85 | CU383 | Samples |
| SN74CBT3383DGVR | ACTIVE | TVSOP | DGV | 24 | 2000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM | -40 to 85 | CU383 | Samples |
| SN74CBT3383DW | ACTIVE | SOIC | DW | 24 | 25 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM | -40 to 85 | CBT3383 | Samples |
| SN74CBT3383DWR | ACTIVE | SOIC | DW | 24 | 2000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM | -40 to 85 | CBT3383 | Samples |
| SN74CBT3383DWRG4 | ACTIVE | SOIC | DW | 24 | 2000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM | -40 to 85 | CBT3383 | Samples |
| SN74CBT3383PW | ACTIVE | TSSOP | PW | 24 | 60 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM | -40 to 85 | CU383 | Samples |
| SN74CBT3383PWLE | OBSOLETE | TSSOP | PW | 24 | | TBD | Call TI | Call TI | -40 to 85 | | |
| SN74CBT3383PWR | ACTIVE | TSSOP | PW | 24 | 2000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM | -40 to 85 | CU383 | Samples |
| SN74CBT3383PWRG4 | ACTIVE | TSSOP | PW | 24 | 2000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM | -40 to 85 | CU383 | Samples |
| SNJ54CBT3383JT | ACTIVE | CDIP | JT | 24 | 1 | TBD | A42 | N / A for Pkg Type | -55 to 125 | 5962-9668801QL A SNJ54CBT3383JT | Samples |
| SNJ54CBT3383W | ACTIVE | CFP | W | 24 | 1 | TBD | A42 | N / A for Pkg Type | -55 to 125 | 5962-9668801QK A SNJ54CBT3383W | Samples |

⁽¹⁾ The marketing status values are defined as follows: **ACTIVE:** Product device recommended for new designs.





www.ti.com

10-Jun-2014

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect. NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design. PREVIEW: Device has been announced but is not in production. Samples may or may not be available. OBSOLETE: TI has discontinued the production of the device.

⁽²⁾ Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.

TBD: The Pb-Free/Green conversion plan has not been defined.

Pb-Free (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes. **Pb-Free (RoHS Exempt):** This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

⁽⁶⁾ Lead/Ball Finish - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer:The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF SN54CBT3383, SN74CBT3383 :

• Catalog: SN74CBT3383

• Military: SN54CBT3383

NOTE: Qualified Version Definitions:



www.ti.com

PACKAGE OPTION ADDENDUM

10-Jun-2014

- Catalog TI's standard catalog product
- Military QML certified for Military and Defense Applications

PACKAGE MATERIALS INFORMATION

www.ti.com

Texas Instruments

TAPE AND REEL INFORMATION





QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE




| Device | Package Type | Package Drawing | | SPQ | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-----------------|-----------------|--------------------|----|------|--------------------------|--------------------------|------------|------------|------------|------------|-----------|------------------|
| SN74CBT3383DBQR | SSOP | DBQ | 24 | 2500 | 330.0 | 16.4 | 6.5 | 9.0 | 2.1 | 8.0 | 16.0 | Q1 |
| SN74CBT3383DBR | SSOP | DB | 24 | 2000 | 330.0 | 16.4 | 8.2 | 8.8 | 2.5 | 12.0 | 16.0 | Q1 |
| SN74CBT3383DGVR | TVSOP | DGV | 24 | 2000 | 330.0 | 12.4 | 6.9 | 5.6 | 1.6 | 8.0 | 12.0 | Q1 |
| SN74CBT3383DWR | SOIC | DW | 24 | 2000 | 330.0 | 24.4 | 10.75 | 15.7 | 2.7 | 12.0 | 24.0 | Q1 |
| SN74CBT3383PWR | TSSOP | PW | 24 | 2000 | 330.0 | 16.4 | 6.95 | 8.3 | 1.6 | 8.0 | 16.0 | Q1 |

TEXAS INSTRUMENTS

www.ti.com

PACKAGE MATERIALS INFORMATION

26-Jan-2013



*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Length (mm) | Width (mm) | Height (mm) |
|-----------------|--------------|-----------------|------|------|-------------|------------|-------------|
| SN74CBT3383DBQR | SSOP | DBQ | 24 | 2500 | 367.0 | 367.0 | 38.0 |
| SN74CBT3383DBR | SSOP | DB | 24 | 2000 | 367.0 | 367.0 | 38.0 |
| SN74CBT3383DGVR | TVSOP | DGV | 24 | 2000 | 367.0 | 367.0 | 35.0 |
| SN74CBT3383DWR | SOIC | DW | 24 | 2000 | 367.0 | 367.0 | 45.0 |
| SN74CBT3383PWR | TSSOP | PW | 24 | 2000 | 367.0 | 367.0 | 38.0 |

MECHANICAL DATA

MCER004A - JANUARY 1995 - REVISED JANUARY 1997

JT (R-GDIP-T**)

CERAMIC DUAL-IN-LINE

24 LEADS SHOWN




NOTES: A. All linear dimensions are in inches (millimeters).

- B. This drawing is subject to change without notice.
- C. This package can be hermetically sealed with a ceramic lid using glass frit.
- D. Index point is provided on cap for terminal identification.
- E. Falls within MIL STD 1835 GDIP3-T24, GDIP4-T28, and JEDEC MO-058 AA, MO-058 AB



CERAMIC DUAL FLATPACK

W (R-GDFP-F24)



NOTES: A. All linear dimensions are in inches (millimeters).

- This drawing is subject to change without notice. В.
- C. This package can be hermetically sealed with a ceramic lid using glass frit.
- D. Index point is provided on cap for terminal identification only.
 E. Falls within Mil-Std 1835 GDFP2-F20



MECHANICAL DATA

PLASTIC SMALL-OUTLINE

MPDS006C - FEBRUARY 1996 - REVISED AUGUST 2000

DGV (R-PDSO-G**)

24 PINS SHOWN



NOTES: A. All linear dimensions are in millimeters.

B. This drawing is subject to change without notice.

- C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15 per side.
- D. Falls within JEDEC: 24/48 Pins MO-153

14/16/20/56 Pins – MO-194



DW (R-PDSO-G24)

PLASTIC SMALL OUTLINE



NOTES: A. All linear dimensions are in inches (millimeters). Dimensioning and tolerancing per ASME Y14.5M-1994.

B. This drawing is subject to change without notice.

C. Body dimensions do not include mold flash or protrusion not to exceed 0.006 (0,15).

D. Falls within JEDEC MS-013 variation AD.



DBQ (R-PDSO-G24)

PLASTIC SMALL-OUTLINE PACKAGE




NOTES: A. All linear dimensions are in inches (millimeters).

B. This drawing is subject to change without notice.

C. Body dimensions do not include mold flash or protrusion not to exceed 0.006 (0,15) per side.

D. Falls within JEDEC MO-137 variation AE.





NOTES:

- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Publication IPC-7351 is recommended for alternate designs.
- D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Example stencil design based on a 50% volumetric metal load solder paste. Refer to IPC-7525 for other stencil recommendations.



PW (R-PDSO-G24)

PLASTIC SMALL OUTLINE



NOTES:


A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M-1994.
 B. This drawing is subject to change without notice.

Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0,15 each side.

Body width does not include interlead flash. Interlead flash shall not exceed 0,25 each side.

E. Falls within JEDEC MO-153





All linear dimensions are in millimeters. A.

- B. This drawing is subject to change without notice.
- C. Publication IPC-7351 is recommended for alternate design.
- D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC-7525 for other stencil recommendations. E. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.



MECHANICAL DATA

MSSO002E - JANUARY 1995 - REVISED DECEMBER 2001

DB (R-PDSO-G**)

PLASTIC SMALL-OUTLINE

28 PINS SHOWN



NOTES: A. All linear dimensions are in millimeters.

- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion not to exceed 0,15.
- D. Falls within JEDEC MO-150



IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have *not* been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

| Products | | Applications | |
|------------------------------|--------------------------|-------------------------------|-----------------------------------|
| Audio | www.ti.com/audio | Automotive and Transportation | www.ti.com/automotive |
| Amplifiers | amplifier.ti.com | Communications and Telecom | www.ti.com/communications |
| Data Converters | dataconverter.ti.com | Computers and Peripherals | www.ti.com/computers |
| DLP® Products | www.dlp.com | Consumer Electronics | www.ti.com/consumer-apps |
| DSP | dsp.ti.com | Energy and Lighting | www.ti.com/energy |
| Clocks and Timers | www.ti.com/clocks | Industrial | www.ti.com/industrial |
| Interface | interface.ti.com | Medical | www.ti.com/medical |
| Logic | logic.ti.com | Security | www.ti.com/security |
| Power Mgmt | power.ti.com | Space, Avionics and Defense | www.ti.com/space-avionics-defense |
| Microcontrollers | microcontroller.ti.com | Video and Imaging | www.ti.com/video |
| RFID | www.ti-rfid.com | | |
| OMAP Applications Processors | www.ti.com/omap | TI E2E Community | e2e.ti.com |
| Wireless Connectivity | www.ti.com/wirelessconne | ectivity | |

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2014, Texas Instruments Incorporated