TEXAS INSTRUMENTS www.ti.com

FEATURES


- Isolation in Power-Down Mode, V₊ = 0
- Specified Break-Before-Make Switching
- Low ON-State Resistance (1 Ω)
- Control Inputs Are 5.5-V Tolerant
- Low Charge Injection
- Excellent ON-State Resistance Matching
- Low Total Harmonic Distortion (THD)
- 1.65-V to 5.5-V Single-Supply Operation
- Latch-Up Performance Exceeds 100 mA Per JESD 78, Class II
- ESD Performance Tested Per JESD
 - 2000-V Human-Body Model (A114-B, Class II)
 - 1000-V Charged-Device Model (C101)

APPLICATIONS

- Cell Phones
- PDAs
- Portable Instrumentation
- Audio and Video Signal Routing
- Low-Voltage Data-Acquisition Systems
- Communication Circuits
- Modems
- Hard Drives
 - Computer Peripherals
 - Wireless Terminals and Peripherals

DESCRIPTION

The TS5A4624 is a single-pole double-throw (SPDT) analog switch that is designed to operate from 1.65 V to 5.5 V. The device offers low ON-state resistance and excellent ON-state resistance matching with the break-before-make feature, to prevent signal distortion during the transferring of a signal from one channel to another. The device has an excellent total harmonic distortion (THD) performance and consumes very low power. These features make this device suitable for portable audio applications.



Switches are shown for logic 0 input.

FUNCTION TABLE

IN	NC TO COM, COM TO NC	NO TO COM, COM TO NO
L	ON	OFF
Н	OFF	ON



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

2:1 Multiplexer/ Demultiplexer (1 × SPDT)
1
1.1 Ω
0.1 Ω
0.15 Ω
20 ns/15 ns
12 ns
–20 pC
100 MHz
–65 dB at 1 MHz
–66 dB at 1 MHz
0.01%
±20 nA
0.1 μΑ
6-pin DCK

SUMMARY OF CHARACTERISTICS⁽¹⁾

(1) $V_+ = 5 V, T_A = 25^{\circ}C$

ORDERING INFORMATION

TA		PACKAGE ⁽¹⁾		ORDERABLE PART NUMBER	TOP-SIDE MARKING ⁽²⁾
-40°C to	o 85°C	SOT (SC-70) – DCK	Tape and reel	TS5A4624DCKR	JW_

(1) Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at www.ti.com/sc/package.

(2) DCK: The actual top-side marking has one additional character that designates the assembly/test site.

Absolute Minimum and Maximum Ratings⁽¹⁾⁽²⁾

over operating free-air temperature range (unless otherwise noted)

			MIN	MAX	UNIT
V ₊	Supply voltage range ⁽³⁾		-0.5	6.5	V
V _{NO} V _{NC} V _{COM}	Analog voltage range ⁽³⁾⁽⁴⁾⁽⁵⁾	Analog voltage range ⁽³⁾⁽⁴⁾⁽⁵⁾			
Ι _Κ	Analog port diode current	$V_{NC}, V_{NO}, V_{COM} < 0$	-50		mA
I _{NO}	On-state switch current		-200	200	
I _{NC} I _{COM}	On-state peak switch current ⁽⁶⁾	V_{NO} , V_{NC} , $V_{COM} = 0$ to V_+	-400	400	mA
VI	Digital input voltage range ⁽³⁾⁽⁴⁾		-0.5	6.5	V
I _{IK}	Digital input clamp current	V ₁ < 0	-50		mA
I+	Continuous current through V_{+}			100	mA
I _{GND}	Continuous current through GND		-100	100	mA
θ_{JA}	Package thermal impedance ⁽⁷⁾			259	°C/W
T _{stg}	Storage temperature range		-65	150	°C

(1) Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

(2) The algebraic convention, whereby the most negative value is a minimum and the most positive value is a maximum

(3) All voltages are with respect to ground, unless otherwise specified.

(4) The input and output voltage ratings may be exceeded if the input and output clamp-current ratings are observed.

(5) This value is limited to 5.5 V maximum.

(6) Pulse at 1-ms duration < 10% duty cycle

(7) The package thermal impedance is calculated in accordance with JESD 51-7.

TS5A4624 1-Ω SPDT ANALOG SWITCH 5-V/3.3-V SINGLE-CHANNEL 2:1 MULTIPLEXER/DEMULTIPLEXER SLYS014A-DECEMBER 2005-REVISED AUGUST 2006



Electrical Characteristics for 5-V Supply⁽¹⁾

 $V_{+} = 4.5 \text{ V}$ to 5.5 V, $T_{A} = -40^{\circ}\text{C}$ to 85°C (unless otherwise noted)

PARAMETER	SYMBOL	TEST CONDITION	S	TA	٧.	MIN	TYP	MAX	UNIT
Analog Switch									
Analog signal range	V _{COM} , V _{NO} , V _{NC}					0		V ₊	V
Peak ON resistance	r _{peak}	$\begin{array}{l} 0 \leq (V_{NO} \text{ or } V_{NC}) \leq V_{+}, \\ I_{COM} = -100 \text{ mA}, \end{array}$	Switch ON, See Figure 13	25°C Full	4.5 V		0.8	1.1 1.5	Ω
ON-state resistance	r _{on}	V_{NO} or $V_{NC} = 2.5$ V, $I_{COM} = -100$ mA,	Switch ON, See Figure 13	25°C Full	4.5 V		0.7	0.9 1.1	Ω
ON-state				25°C			0.05	0.1	
resistance match between channels	Δr_{on}	V_{NO} or V_{NC} = 2.5 V, I_{COM} = -100 mA,	Switch ON, See Figure 13	Full	4.5 V			0.1	Ω
ON-state		$\begin{array}{l} 0 \leq (V_{NO} \text{ or } V_{NC}) \leq V_{+}, \\ I_{COM} = -100 \text{ mA}, \end{array}$	Switch ON, See Figure 13	25°C			0.15		
resistance flatness	r _{on(flat)}	$V_{NO} \text{ or } V_{NC} = 1 \text{ V}, 1.5 \text{ V}, 2.5 \text{ V},$	Switch ON,	25°C	4.5 V		0.1	0.25	Ω
		$I_{COM} = -100 \text{ mA},$	See Figure 13	Full				0.25	
		V_{NC} or $V_{NO} = 1 V$,		25°C		-20	2	20	
NC, NO OFF leakage current	I _{NC(OFF)} , I _{NO(OFF)}	$V_{COM} = 1 V \text{ to } 4.5 V,$ or $V_{NC} \text{ or } V_{NO} = 4.5 V,$ $V_{COM} = 1 V \text{ to } 4.5 V,$	Switch OFF, See Figure 14	Full	5.5 V	-100		100	nA
ounon	I _{NC(PWROFF)} ,	V_{NC} or $V_{NO} = 0$ to 5.5 V,	Switch OFF,	25°C	0 V	-1	0.2	1	^
	I _{NO(PWROFF)}	$V_{COM} = 5.5 V \text{ to } 0,$	See Figure 14	Full	0 0	-20		20	μA
NC, NO	I _{NC(ON)} ,	V_{NC} or V_{NO} = 1 V, V_{COM} = Open,	Switch ON.	25°C		-20	2	20	
ON leakage current	I _{NO(ON)}	or V_{NC} or V_{NO} = 4.5 V, V_{COM} = Open,	See Figure 15	Full	5.5 V	-100		100	nA
СОМ		V_{NC} or $V_{NO} = 0$ to 5.5 V,	Switch OFF,	25°		-1	0.1	1	
OFF leakage current	I _{COM(PWROFF)}	$V_{COM} = 5.5 V \text{ to } 0,$	See Figure 14	Full	0 V	-20		20	μA
COM		V_{NC} or V_{NO} = Open, V_{COM} = 1 V,	Switch ON.	25°C		-20	2	20	
ON leakage current	I _{COM(ON)}	or V_{NC} or V_{NO} = Open, V_{COM} = 4.5 V,	See Figure 15	Full	5.5 V	-100		100	nA
Digital Input (IN)									
Input logic high	V _{IH}			Full		2.4		5.5	V
Input logic low	V _{IL}			Full		0		0.8	V
Input leakage current	I _{IH} , I _{IL}	V ₁ = 5.5 V or 0		25°C	5.5 V	-2		2	nA
ourront				Full		100		100	

SLYS014A-DECEMBER 2005-REVISED AUGUST 2006

Electrical Characteristics for 5-V Supply⁽¹⁾ (Continued)

 $V_{+} = 4.5$ V to 5.5 V, $T_{A} = -40^{\circ}$ C to 85°C (unless otherwise noted)

PARAMETER	SYMBOL	TEST CON	DITIONS	TA	V.	MIN	TYP	MAX	UNIT
Dynamic	-	L							
			0 05 5	25°C	5 V	4	12	22	
Turn-on time	t _{ON}		C _L = 35 pF, See Figure 17	Full	4.5 V to 5.5 V	2		25	ns
			0 05 -5	25°C	5 V	1	5	8	
Turn-off time	t _{OFF}		C _L = 35 pF, See Figure 17	Full	4.5 V to 5.5 V	1		10	ns
Due als hafana			0 05 - 5	25°C	5 V	1	8	13	
Break-before- make time	t _{BBM}		C _L = 35 pF, See Figure 18	Full	4.5 V to 5.5 V	1		15	ns
Charge injection	Q _C	$V_{GEN} = 0,$ $R_{GEN} = 0,$	C _L = 1 nF, See Figure 22	25°C	5 V		15.5		рС
NC, NO OFF capacitance	C _{NC(OFF)} , C _{NO(OFF)}	V_{NC} or $V_{NO} = V_{+}$ or GND, Switch OFF,	See Figure 16	25°C	5 V		18		pF
NC, NO ON capacitance	C _{NC(ON)} , C _{NO(ON)}	V_{NC} or $V_{NO} = V_{+}$ or GND, Switch ON,	See Figure 16	25°C	5 V		55		pF
COM ON capacitance	C _{COM(ON)}	V _{COM} = V ₊ or GND, Switch ON,	See Figure 16	25°C	5 V		55		pF
Digital input capacitance	CI	$V_{I} = V_{+}$ or GND,	See Figure 16	25°C	5 V		2		pF
Bandwidth	BW	$R_{L} = 50 \Omega$, Switch ON,	See Figure 19	25°C	5 V		90		MHz
OFF isolation	O _{ISO}	$R_L = 50 \Omega,$ f = 1 MHz,	Switch OFF, See Figure 20	25°C	5 V		-63		dB
Crosstalk	X _{TALK}	$R_{L} = 50 \ \Omega,$ f = 1 MHz,	Switch ON, See Figure 21	25°C	5 V		-63		dB
Total harmonic distortion	THD	$R_{L} = 600 \ \Omega,$ $C_{L} = 50 \ pF,$	f = 200 Hz to 20 kHz, See Figure 23	25°C	5 V		0.004		%
Supply	•	-		·				ľ	
Positive supply		V = V or CND	Switch ON or OFF	25°C	5 5 V		10	50	n 1
current	I+	$V_1 = V_+$ or GND,	Switch ON or OFF	Full	5.5 V			500	nA

TS5A4624 1-Ω SPDT ANALOG SWITCH 5-V/3.3-V SINGLE-CHANNEL 2:1 MULTIPLEXER/DEMULTIPLEXER SLYS014A-DECEMBER 2005-REVISED AUGUST 2006



Electrical Characteristics for 3.3-V Supply⁽¹⁾

 $V_{+} = 3 \text{ V}$ to 3.6 V, $T_{A} = -40^{\circ}\text{C}$ to 85°C (unless otherwise noted)

PARAMETER	SYMBOL	TEST CONDITIONS	6	T _A	V.	MIN	TYP	MAX	UNIT
Analog Switch	I					1			
Analog signal range	V _{COM} , V _{NO} , V _{NC}					0		V+	V
Peak ON resistance	r _{peak}	$\begin{array}{l} 0 \leq (V_{NO} \text{ or } V_{NC}) \leq V_{+}, \\ I_{COM} = -100 \text{ mA}, \end{array}$	Switch ON, See Figure 13	25°C Full	3 V		1.3	1.6 2	Ω
ON-state resistance	r _{on}	V_{NO} or $V_{NC} = 2 V$, $I_{COM} = -100 \text{ mA}$,	Switch ON, See Figure 13	25°C Full	3 V		1.2	1.5 1.7	Ω
ON-state resistance match	Δr _{on}	V _{NO} or V _{NC} = 2 V, 0.8 V, I _{COM} = -100 mA,	Switch ON, See Figure 13	25°C	3 V		0.1	0.15	Ω
between channels				Full				0.15	
ON-state		$\begin{array}{l} 0 \leq (V_{NO} \text{ or } V_{NC}) \leq V_{+}, \\ I_{COM} = -100 \text{ mA}, \end{array}$	Switch ON, See Figure 13	25°C	0.14		0.2		
resistance flatness	r _{on(flat)}	V_{NO} or V_{NC} = 2 V, 0.8 V, I _{COM} = -100 mA,	Switch ON, See Figure 13	25°C Full	3 V		0.15	0.3	Ω
		V_{NC} or $V_{NO} = 1 V$, $V_{COM} = 1 V$ to 3 V,		25°C		-20	2	20	
NC, NO OFF leakage	I _{NC(OFF)} , I _{NO(OFF)}	or V_{NC} or $V_{\text{NO}} = 3 \text{ V}, V_{\text{COM}} = 1 \text{ V to } 3 \text{ V},$	Switch OFF, See Figure 14	Full	3.6 V	-50		50	nA
current	I _{NC(PWROFF)} , I _{NO(PWROFF)}	V_{NC} or $V_{NO} = 0$ to 3.6 V, $V_{COM} = 3.6$ V to 0,	Switch OFF, See Figure 14	25°C Full	0 V	-1 -15	0.2	1 15	μA
NC, NO	. ,	V_{NC} or V_{NO} = 1 V, V_{COM} = Open,	Cwitch ON	25°C		-10	2	10	
ON leakage current	I _{NC(ON)} , I _{NO(ON)}	or V_{NC} or $V_{NO} = 3 V$, $V_{COM} = Open$,	Switch ON, See Figure 15	Full	3.6 V	-20		20	nA
COM		V_{NC} or $V_{NO} = 3.6$ V to 0,	Switch OFF,	25°	0 V	-1	0.2	1	
OFF leakage current	I _{COM} (PWROFF)	$V_{COM} = 0$ to 3.6 V,	See Figure 14	Full	0 0	-15		15	μA
COM	_	V_{NC} or V_{NO} = Open, V_{COM} = 1 V,	Switch ON,	25°C		-10	2	10	
ON leakage current	I _{COM(ON)}	or V_{NC} or V_{NO} = Open, V_{COM} = 3 V,	See Figure 15	Full	3.6 V	-20		20	nA
Digital Input (IN)				-		,			
Input logic high	V _{IH}			Full		2.4		5.5	V
Input logic low	V _{IL}			Full		0		0.8	V
Input leakage current	I _{IH} , I _{IL}	V _I = 5.5 V or 0		25°C Full	3.6 V	-2 -100		2 100	nA

SLYS014A-DECEMBER 2005-REVISED AUGUST 2006

Electrical Characteristics for 3.3-V Supply⁽¹⁾ (Continued)

 $V_{+} = 3 \text{ V}$ to 3.6 V, $T_{A} = -40^{\circ}\text{C}$ to 85°C (unless otherwise noted)

PARAMETER	SYMBOL	TEST CON	DITIONS	TA	V.	MIN	TYP	MAX	UNIT
Dynamic				1					
			0 05 -5	25°C	3.3 V	4	16	25	
Turn-on time	t _{ON}	$V_{COM} = V_+,$ $R_L = 50 \Omega,$	C _L = 35 pF, See Figure 17	Full	3 V to 3.6 V	2		27	ns
			$C_1 = 35 \text{ pF},$	25°C	3.3 V	1	5.5	8	
Turn-off time	t _{OFF}	$V_{COM} = V_+,$ $R_L = 50 \Omega,$	See Figure 17	Full	3 V to 3.6 V	1		11	ns
Break-before-			0 05 -5	25°C	3.3 V	2	12	20	
make time	t _{BBM}		C _L = 35 pF, See Figure 18	Full	3 V to 3.6 V	2		25	ns
Charge injection	Q _C	V _{GEN} = 0, R _{GEN} = 0,	C _L = 1 nF, See Figure 22	25°C	3.3 V		9		рС
NC, NO OFF capacitance	$\begin{array}{c} C_{NC(OFF)},\\ C_{NO(OFF)} \end{array}$	V_{NC} or V_{NO} = V ₊ or GND, Switch OFF,	See Figure 16	25°C	3.3 V		18		pF
NC, NO ON capacitance	C _{NC(ON)} , C _{NO(ON)}	V_{NC} or $V_{NO} = V_{+}$ or GND, Switch ON,	See Figure 16	25°C	3.3 V		55		pF
COM ON capacitance	C _{COM(ON)}	$V_{COM} = V_{+}$ or GND, Switch ON,	See Figure 16	25°C	3.3 V		55		pF
Digital input capacitance	Cl	$V_I = V_+ \text{ or GND},$	See Figure 16	25°C	3.3 V		2		pF
Bandwidth	BW	$R_L = 50 \Omega$, Switch ON,	See Figure 19	25°C	3.3 V		90		MHz
OFF isolation	O _{ISO}	$R_L = 50 \Omega,$ f = 1 MHz,	Switch OFF, See Figure 20	25°C	3.3 V		-63		dB
Crosstalk	X _{TALK}	$R_L = 50 \Omega,$ f = 1 MHz,	Switch ON, See Figure 21	25°C	3.3 V		-63		dB
Total harmonic distortion	THD	$R_L = 600 \ \Omega,$ $C_L = 50 \ pF,$	f = 20 Hz to 20 kHz, See Figure 23	25°C	3.3 V		0.01		%
Supply				u.					
Positive supply	1		Switch ON or OFF	25°C	3.6 V		10	50	n۸
current	I+	$V_1 = V_+$ or GND,	Switch ON or OFF	Full	3.0 V			100	nA

TS5A4624 1-Ω SPDT ANALOG SWITCH 5-V/3.3-V SINGLE-CHANNEL 2:1 MULTIPLEXER/DEMULTIPLEXER SLYS014A-DECEMBER 2005-REVISED AUGUST 2006



Electrical Characteristics for 2.5-V Supply⁽¹⁾

 V_{\star} = 2.3 V to 2.7, T_{A} = –40°C to 85°C (unless otherwise noted)

PARAMETER	SYMBOL	TEST CONDITIONS	6	TA	V.	MIN	TYP	MAX	UNIT
Analog Switch		·		·					
Analog signal range	V _{COM} , V _{NO} , V _{NC}					0		V ₊	V
Peak ON resistance	r _{peak}	$\begin{array}{l} 0 \leq (V_{NO} \text{ or } V_{NC}) \leq V_{\star}, \\ I_{COM} = -8 \ \text{mA}, \end{array}$	Switch ON, See Figure 13	25°C Full	2.3 V		1.8	2.5 2.7	Ω
ON-state resistance	r _{on}	V_{NO} or V_{NC} = 1.8 V, I_{COM} = -8 mA,	Switch ON, See Figure 13	25°C Full	2.3 V		1.5	2 2.4	Ω
ON-state				25°C			0.15	0.2	
resistance match between channels	Δr_{on}	V_{NO} or V_{NC} = 1.8 V, I_{COM} = -8 mA,	Switch ON, See Figure 13	Full	2.3 V			0.2	Ω
ON-state		$\begin{array}{l} 0 \leq (V_{NO} \text{ or } V_{NC}) \leq V_{+}, \\ I_{COM} = -8 \text{ mA}, \end{array}$	Switch ON, See Figure 13	25°C			0.6		
resistance flatness	r _{on(flat)}	V_{NO} or $V_{NC} = 0.8$ V, 1.8 V, I _{COM} = -8 mA,	Switch ON, See Figure 13	25°C Full	2.3 V		0.6	1	Ω
		V_{NC} or $V_{NO} = 0.5 V$,		25°C		-20	2	20	
NC, NO OFF leakage current	I _{NC(OFF)} , I _{NO(OFF)}	$ \begin{array}{l} V_{COM} = 0.5 \ V \ \text{to} \ 2.3 \ \text{V}, \\ \text{or} \\ V_{NC} \ \text{or} \ V_{NO} = 2.3 \ \text{V}, \\ V_{COM} = 0.5 \ \text{V} \ \text{to} \ 2.3 \ \text{V}, \end{array} $	Switch OFF, See Figure 14	Full	2.7 V	-50		50	nA
ourion	I _{NC(PWROFF)} , I _{NO(PWROFF)}	V_{NC} or $V_{NO} = 0$ to 3.6 V, $V_{COM} = 3.6$ V to 0,	Switch OFF, See Figure 14	25°C Full	0 V	-1 -10	0.1	1 10	μA
NC, NO		V_{NC} or $V_{NO} = 0.5 V$, $V_{COM} = Open$,	Quitate ON	25°C		-10	2	10	
ON leakage current	I _{NC(ON)} , I _{NO(ON)}	or V_{NC} or V_{NO} = 2.2 V, V_{COM} = Open,	Switch ON, See Figure 15	Full	2.7 V	-20		20	nA
COM		V_{NC} or $V_{NO} = 2.7$ V to 0,	Switch OFF,	25°	0.14	-1	0.1	10	
OFF leakage current	I _{COM(PWROFF)}	$V_{COM} = 0$ to 2.7 V,	See Figure 14	Full	0 V	-10		10	μA
COM		V_{NC} or V_{NO} = Open, V_{COM} = 0.5 V,	Switch ON,	25°C		-10	2	10	
ON leakage current	I _{COM(ON)}	or V_{NC} or V_{NO} = Open, V_{COM} = 2.2 V,	See Figure 15	Full	2.7 V	-20		20	nA
Digital Input (IN)									
Input logic high	VIH			Full		1.8		5.5	V
Input logic low	VIL			Full		0		0.6	V
Input leakage current	I _{IH} , I _{IL}	V _I = 5.5 V or 0		25°C	2.7 V	-2		2	nA
Current				Full		20		20	

SLYS014A-DECEMBER 2005-REVISED AUGUST 2006

Electrical Characteristics for 2.5-V Supply⁽¹⁾ (Continued)

 $V_{+} = 2.3 \text{ V}$ to 2.7, $T_{A} = -40^{\circ}\text{C}$ to 85°C (unless otherwise noted)

PARAMETER	SYMBOL	TEST CON	DITIONS	TA	٧,	MIN	TYP	MAX	UNIT
Dynamic	1								
			0 05 5	25°C	2.5 V	10	22	32	
Turn-on time	t _{ON}	$V_{\text{COM}} = V_+,$ R _L = 50 Ω,	C _L = 35 pF, See Figure 17	Full	2.3 V to 2.7 V	8		35	ns
		M = M	$C_{1} = 35 \text{ pF},$	25°C	2.5 V	3	6	11	
Turn-off time	t _{OFF}	$V_{\text{COM}} = V_+,$ R _L = 50 Ω,	See Figure 17	Full	2.3 V to 2.7 V	2		12	ns
Draals hafana			0 05 -5	25°C	2.5 V	5	19	30	
Break-before- make time	t _{BBM}		C _L = 35 pF, See Figure 18	Full	2.3 V to 2.7 V	5		35	ns
Charge injection	Q _C	V _{GEN} = 0, R _{GEN} = 0,	C _L = 1 nF, See Figure 22	25°C	2.5 V		-7		рС
NC, NO OFF capacitance	C _{NC(OFF)} , C _{NO(OFF)}	V_{NC} or V_{NO} = V ₊ or GND, Switch OFF,	See Figure 16	25°C	2.5 V		18		pF
NC, NO ON capacitance	C _{NC(ON)} , C _{NO(ON)}	V_{NC} or $V_{NO} = V_{+}$ or GND, Switch ON,	See Figure 16	25°C	2.5 V		55		pF
COM ON capacitance	C _{COM(ON)}	$V_{COM} = V_+$ or GND, Switch ON,	See Figure 16	25°C	2.5 V		55		pF
Digital input capacitance	CI	$V_I = V_+ \text{ or GND},$	See Figure 16	25°C	2.5 V		2		pF
Bandwidth	BW	$R_L = 50 \Omega$, Switch ON,	See Figure 19	25°C	2.5 V		90		MHz
OFF isolation	O _{ISO}	$ \begin{array}{l} R_{L} = 50 \ \Omega, \\ f = 1 \ MHz, \end{array} $	Switch OFF, See Figure 20	25°C	2.5 V		-63		dB
Crosstalk	X _{TALK}	$R_{L} = 50 \ \Omega,$ f = 1 MHz,	Switch ON, See Figure 21	25°C	2.5 V		-63		dB
Total harmonic distortion	THD	$R_L = 600 \Omega,$ $C_L = 50 pF,$	f = 20 Hz to 20 kHz, See Figure 23	25°C	2.5 V		0.02		%
Supply									
Positive supply	1	V = V or CND	Switch ON or OFF	25°C	271		10	20	20
current	I+	$V_1 = V_+ \text{ or GND},$	Switch ON of OFF	Full	2.7 V			150	nA

TS5A4624 1-Ω SPDT ANALOG SWITCH 5-V/3.3-V SINGLE-CHANNEL 2:1 MULTIPLEXER/DEMULTIPLEXER SLYS014A-DECEMBER 2005-REVISED AUGUST 2006



Electrical Characteristics for 1.8-V Supply⁽¹⁾

 V_{+} = 1.65 V to 1.95 V, T_{A} = -40°C to 85°C (unless otherwise noted)

PARAMETER	SYMBOL	TEST CON	DITIONS	TA	V.	MIN	TYP	MAX	UNIT
Analog Switch									
Analog signal range	V _{COM} , V _{NO} , V _{NC}					0		V+	V
Peak ON resistance	r _{peak}	$\begin{array}{l} 0 \leq (V_{NO} \mbox{ or } V_{NC}) \leq V_{+}, \\ I_{COM} = -2 \mbox{ mA}, \end{array}$	Switch ON, See Figure 13	25°C Full	1.65 V		5	15	Ω
ON-state resistance	r _{on}	V_{NO} or V_{NC} = 1.5 V, I _{COM} = -2 mA,	Switch ON, See Figure 13	25°C Full	1.65 V		2	2.5 3.5	Ω
ON-state				25°C			0.15	0.4	
resistance match between channels	Δr_{on}	V_{NO} or V_{NC} = 1.5 V, I_{COM} = -2 mA,	Switch ON, See Figure 13	Full	1.65 V			0.4	Ω
ON-state		$\begin{array}{l} 0 \leq (V_{NO} \text{ or } V_{NC}) \leq V_{+}, \\ I_{COM} = -8 \text{ mA}, \end{array}$	Switch ON, See Figure 13	25°C			5		
resistance flatness	r _{on(flat)}	V _{NO} or V _{NC} = 0.6 V, 1.5 V,	Switch ON,	25°C	1.65 V		4.5		Ω
namess		$I_{COM} = -2 \text{ mA},$	See Figure 13	Full	-				[
		V_{NC} or $V_{NO} = 0.3 V$,		25°C		-5	2	5	
NC, NO OFF leakage current	I _{NC(OFF)} , I _{NO(OFF)}		Switch OFF, See Figure 14	Full	1.95 V	-20		20	nA
ourion	I _{NC(PWROFF)} ,	V_{NC} or $V_{NO} = 0$ to 1.95 V,	Switch OFF,	25°C	0.14	-1	0.1	1	
	I _{NO(PWROFF)}	$V_{COM} = 1.95 V \text{ to } 0,$	See Figure 14	Full	0 V	-5		5	μA
		V_{NC} or V_{NO} = 0.3 V,		25°C		-5	2	5	
NC, NO ON leakage current	I _{NC(ON)} , I _{NO(ON)}	$ \begin{array}{l} V_{COM} = Open, \\ or \\ V_{NC} \mbox{ or } V_{NO} = 1.65 \mbox{ V}, \\ V_{COM} = Open, \end{array} $	Switch ON, See Figure 15	Full	1.95 V	-20		20	nA
COM		V_{NC} or V_{NO} = 1.95 V to 0,	Switch OFF,	25°		-1	0.1	1	
OFF leakage current	I _{COM(PWROFF)}	$V_{COM} = 0$ to 1.95 V,	See Figure 14	Full	0 V	-5		5	μA
		V _{NC} or V _{NO} = Open,		25°C		-5	2	5	
COM ON leakage current	I _{COM(ON)}	$\begin{array}{l} V_{COM}=0.3 \ V, \\ or \\ V_{NC} \ or \ V_{NO}=Open, \\ V_{COM}=1.65 \ V, \end{array}$	Switch ON, See Figure 15	Full	1.95 V	-20		20	nA
Digital Input (IN)									
Input logic high	V _{IH}			Full		1.5		5.5	V
Input logic low	VIL			Full		0		0.6	V
Input leakage				25°C	1.05.1/	-2		2	۳Å
current	I _{IH} , I _{IL}	$V_{I} = 5.5 V \text{ or } 0$		Full	1.95 V	20		20	nA

SLYS014A-DECEMBER 2005-REVISED AUGUST 2006

Electrical Characteristics for 1.8-V Supply⁽¹⁾ (Continued)


 $V_{+} = 1.65$ V to 1.95 V, $T_{A} = -40^{\circ}$ C to 85°C (unless otherwise noted)

PARAMETER	SYMBOL	TEST CON	DITIONS	T _A	۷,	MIN	TYP	MAX	UNIT
Dynamic		1		1					
		., .,	0 05 F	25°C	1.8 V	17	35	65	
Turn-on time	t _{ON}		C _L = 35 pF, See Figure 17	Full	1.65 V to 1.95 V	15		70	ns
			0 25 55	25°C	1.8 V	3	7	13	
Turn-off time	t _{OFF}	$V_{COM} = V_+,$ R _L = 50 Ω,	C _L = 35 pF, See Figure 17	Full	1.65 V to 1.95 V	2		15	ns
Day als hafaas			0 05 - 5	25°C	1.8 V	15	33	60	
Break-before- make time	t _{BBM}		C _L = 35 pF, See Figure 18	Full	1.65 V to 1.95 V	15		65	ns
Charge injection	Q _C	$V_{GEN} = 0,$ R _{GEN} = 0,	C _L = 1 nF, See Figure 22	25°C	1.8 V		4		рС
NC, NO OFF capacitance	C _{NC(OFF)} , C _{NO(OFF)}	V_{NC} or $V_{NO} = V_{+}$ or GND, Switch OFF,	See Figure 16	25°C	1.8 V		18		pF
NC, NO ON capacitance	C _{NC(ON)} , C _{NO(ON)}	V_{NC} or $V_{NO} = V_{+}$ or GND, Switch ON,	See Figure 16	25°C	1.8 V		55		pF
COM ON capacitance	C _{COM(ON)}	$V_{COM} = V_+$ or GND, Switch ON,	See Figure 16	25°C	1.8 V		55		pF
Digital input capacitance	CI	$V_{I} = V_{+}$ or GND,	See Figure 16	25°C	1.8 V		2		pF
Bandwidth	BW	$R_L = 50 \Omega$, Switch ON,	See Figure 19	25°C	1.8 V		90		MHz
OFF isolation	O _{ISO}	$R_L = 50 \Omega,$ f = 1 MHz,	Switch OFF, See Figure 20	25°C	1.8 V		63		dB
Crosstalk	X _{TALK}	$R_L = 50 \Omega,$ f = 1 MHz,	Switch ON, See Figure 21	25°C	1.8 V		63		dB
Total harmonic distortion	THD	$R_L = 600 \Omega,$ $C_L = 50 pF,$	f = 20 Hz to 20 kHz, See Figure 23	25°C	1.8 V		0.05		%
Supply									
Positive supply			Quitab ON as OFF	25°C	4.05.1/		5	15	
current	I+	$V_{I} = V_{+}$ or GND,	Switch ON or OFF	Full	1.95 V			50	μA




SLYS014A-DECEMBER 2005-REVISED AUGUST 2006


TYPICAL PERFORMANCE




SLYS014A-DECEMBER 2005-REVISED AUGUST 2006











SLYS014A-DECEMBER 2005-REVISED AUGUST 2006

TYPICAL PERFORMANCE (continued)




Figure 13. Current vs Temperature (V₊ = 5 V)

TS5A4624 1-Ω SPDT ANALOG SWITCH 5-V/3.3-V SINGLE-CHANNEL 2:1 MULTIPLEXER/DEMULTIPLEXER SLYS014A-DECEMBER 2005-REVISED AUGUST 2006

PIN DESCRIPTION

PIN NO.	NAME	DESCRIPTION
1	IN	Digital control to connect COM to NO
2	V ₊	Power supply
3	GND	Digital ground
4	NC	Normally closed
5	COM	Common
6	NO	Normally open



SLYS014A-DECEMBER 2005-REVISED AUGUST 2006

PARAMETER DESCRIPTION

SYMBOL	DESCRIPTION							
V _{COM}	Voltage at COM							
V _{NC}	Voltage at NC							
V _{NO}	Voltage at NO							
r _{on}	Resistance between COM and NC or COM and NO ports when the channel is ON							
r _{peak}	Peak ON-state resistance over a specified voltage range							
Δr_{on}	Difference of r _{on} between channels							
	Difference between the maximum and minimum value of r_{on} in a channel over the specified range of conditions							
r _{on(flat)}								
I _{NC(OFF)}	Leakage current measured at the NC port, with the corresponding channel (NC to COM) in the OFF state under worst-case input and output conditions							
I _{NC(PWROFF)}	Leakage current measured at the NC port during the power-down condition, $V_{+} = 0$							
I _{NO(OFF)}	Leakage current measured at the NO port, with the corresponding channel (NO to COM) in the OFF state under worst-case input and output conditions							
I _{NO(PWROFF)}	Leakage current measured at the NO port during the power-down condition, $V_{+} = 0$							
I _{NC(ON)}	Leakage current measured at the NC port, with the corresponding channel (NC to COM) in the ON state and the output (COM) being open							
I _{NO(ON)}	Leakage current measured at the NO port, with the corresponding channel (NO to COM) in the ON state and the output (COM) being open							
I _{COM(ON)}	Leakage current measured at the COM port, with the corresponding channel (COM to NO or COM to NC) in the ON state and the output (NC or NO) being open							
I _{COM(PWROFF)}	Leakage current measured at the COM port during the power-down condition, $V_{+} = 0$							
V _{IH}	Minimum input voltage for logic high for the control input (IN)							
V _{IL}	Maximum input voltage for logic low for the control input (IN)							
VI	Voltage at IN							
<u>الل</u> ا, ا _{لل}	Leakage current measured at IN							
t _{ON}	Turn-on time for the switch. This parameter is measured under the specified range of conditions and by the propagation delay between the digital control (IN) signal and analog outputs (COM, NC, or NO) signal when the switch is turning ON.							
t _{OFF}	Turn-off time for the switch. This parameter is measured under the specified range of conditions and by the propagation delay between the digital control (IN) signal and analog outputs (COM, NC, or NO) signal when the switch is turning OFF.							
t _{BBM}	Break-before-make time. This parameter is measured under the specified range of conditions and by the propagation delay between the output of two adjacent analog channels (NC and NO) when the control signal changes state.							
Q _C	Charge injection is a measurement of unwanted signal coupling from the control (IN) input to the analog (NC, NC or COM) output. This is measured in coulomb (C) and measured by the total charge induced due to switching of the control input. Charge injection, $Q_C = C_L \times \Delta V_O$, C_L is the load capacitance and ΔVO is the change in analog output voltage.							
C _{NC(OFF)}	Capacitance at the NC port when the corresponding channel (NC to COM) is OFF							
C _{NO(OFF)}	Capacitance at the NO port when the corresponding channel (NO to COM) is OFF							
C _{NC(ON)}	Capacitance at the NC port when the corresponding channel (NC to COM) is ON							
C _{NO(ON)}	Capacitance at the NO port when the corresponding channel (NO to COM) is ON							
C _{COM(ON)}	Capacitance at the COM port when the corresponding channel (COM to NC or COM to NO) is ON							
C _{IN}	Capacitance of IN							
OISO	OFF isolation of the switch is a measurement OFF-state switch impedance. This is measured in dB in a specific frequency, with the corresponding channel (NC to COM or NO to COM) in the OFF state.							
X _{TALK}	Crosstalk is a measurement of unwanted signal coupling from an ON channel to an OFF channel (NC to NO or N to NC). This is measured in a specific frequency and in dB.							
BW	Bandwidth of the switch. This is the frequency in which the gain of an ON channel is -3 dB below the DC gain.							
THD	Total harmonic distortion describes the signal distortion caused by the analog switch. This is defined as the ratio root mean square (RMS) value of the second, third, and higher harmonic to the absolute magnitude of the fundamental harmonic.							

PARAMETER MEASUREMENT INFORMATION







Figure 14. ON-State Resistance (ron)











SLYS014A-DECEMBER 2005-REVISED AUGUST 2006



Texas

STRUMENTS www.ti.com

Figure 17. Capacitance (C₁, C_{COM(ON)}, C_{NC(OFF)}, C_{NO(OFF)}, C_{NC(ON)}, C_{NO(ON)})




(1) All input pulses are supplied by generators having the following characteristics: PRR \leq 10 MHz, Z_O = 50 Ω , t_r < 5 ns, t_f < 5 ns.

(2) C_L includes probe and jig capacitance.

Figure 18. Turn-On (t_{ON}) and Turn-Off Time (t_{OFF})

SLYS014A-DECEMBER 2005-REVISED AUGUST 2006



- (1) All input pulses are supplied by generators having the following characteristics: PRR \leq 10 MHz, Z_O = 50 Ω , t_r < 5 ns, t_f < 5 ns.
- (2) C_L includes probe and jig capacitance.

Figure 19. Break-Before-Make Time (t_{BBM})




Figure 20. Bandwidth (BW)





Figure 21. OFF Isolation (OISO)

SLYS014A-DECEMBER 2005-REVISED AUGUST 2006




ł,

Texas

INSTRUMENTS www.ti.com

Figure 22. Crosstalk (X_{TALK})




(1) All input pulses are supplied by generators having the following characteristics: PRR \leq 10 MHz, Z_O = 50 Ω , t_r < 5 ns, t_f < 5 ns.

(2) C_L includes probe and jig capacitance.


Figure 23. Charge Injection (Q_C)



SLYS014A-DECEMBER 2005-REVISED AUGUST 2006



(1) C_L includes probe and jig capacitance.





10-Jun-2014

PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead/Ball Finish (6)	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
TS5A4624DCKR	ACTIVE	SC70	DCK	6	3000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 85	(JWF ~ JWR)	Samples
TS5A4624DCKRE4	ACTIVE	SC70	DCK	6	3000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 85	(JWF ~ JWR)	Samples
TS5A4624DCKRG4	ACTIVE	SC70	DCK	6	3000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 85	(JWF ~ JWR)	Samples
TS5A4624DCKT	ACTIVE	SC70	DCK	6	250	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 85	JWR	Samples
TS5A4624DCKTG4	ACTIVE	SC70	DCK	6	250	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 85	JWR	Samples

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.

TBD: The Pb-Free/Green conversion plan has not been defined.

Pb-Free (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

Pb-Free (RoHS Exempt): This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.



www.ti.com

PACKAGE OPTION ADDENDUM

10-Jun-2014

⁽⁶⁾ Lead/Ball Finish - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer:The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

PACKAGE MATERIALS INFORMATION

www.ti.com

Texas Instruments

TAPE AND REEL INFORMATION





QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



All dimensions are nominal												
Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TS5A4624DCKR	SC70	DCK	6	3000	178.0	9.0	2.4	2.5	1.2	4.0	8.0	Q3
TS5A4624DCKR	SC70	DCK	6	3000	180.0	8.4	2.41	2.41	1.2	4.0	8.0	Q3
TS5A4624DCKT	SC70	DCK	6	250	180.0	8.4	2.41	2.41	1.2	4.0	8.0	Q3

TEXAS INSTRUMENTS

www.ti.com

PACKAGE MATERIALS INFORMATION

3-Aug-2017



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TS5A4624DCKR	SC70	DCK	6	3000	180.0	180.0	18.0
TS5A4624DCKR	SC70	DCK	6	3000	202.0	201.0	28.0
TS5A4624DCKT	SC70	DCK	6	250	202.0	201.0	28.0

DCK (R-PDSO-G6)

PLASTIC SMALL-OUTLINE PACKAGE



- NOTES: A. All linear dimensions are in millimeters.
 - B. This drawing is subject to change without notice.
 - C. Body dimensions do not include mold flash or protrusion. Mold flash and protrusion shall not exceed 0.15 per side.
 - D. Falls within JEDEC MO-203 variation AB.



LAND PATTERN DATA



NOTES:

- A. All linear dimensions are in millimeters.B. This drawing is subject to change without notice.
- C. Customers should place a note on the circuit board fabrication drawing not to alter the center solder mask defined pad.
- D. Publication IPC-7351 is recommended for alternate designs.
- E. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Example stencil design based on a 50% volumetric metal load solder paste. Refer to IPC-7525 for other stencil recommendations.



IMPORTANT NOTICE

Texas Instruments Incorporated (TI) reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete.

TI's published terms of sale for semiconductor products (http://www.ti.com/sc/docs/stdterms.htm) apply to the sale of packaged integrated circuit products that TI has qualified and released to market. Additional terms may apply to the use or sale of other types of TI products and services.

Reproduction of significant portions of TI information in TI data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such reproduced documentation. Information of third parties may be subject to additional restrictions. Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyers and others who are developing systems that incorporate TI products (collectively, "Designers") understand and agree that Designers remain responsible for using their independent analysis, evaluation and judgment in designing their applications and that Designers have full and exclusive responsibility to assure the safety of Designers' applications and compliance of their applications (and of all TI products used in or for Designers' applications) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to their applications, Designer has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any applications that include TI products, Designer will thoroughly test such applications and the functionality of such TI products as used in such applications.

TI's provision of technical, application or other design advice, quality characterization, reliability data or other services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using TI Resources in any way, Designer (individually or, if Designer is acting on behalf of a company, Designer's company) agrees to use any particular TI Resource solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

Designer is authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNER AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

Unless TI has explicitly designated an individual product as meeting the requirements of a particular industry standard (e.g., ISO/TS 16949 and ISO 26262), TI is not responsible for any failure to meet such industry standard requirements.

Where TI specifically promotes products as facilitating functional safety or as compliant with industry functional safety standards, such products are intended to help enable customers to design and create their own applications that meet applicable functional safety standards and requirements. Using products in an application does not by itself establish any safety features in the application. Designers must ensure compliance with safety-related requirements and standards applicable to their applications. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equipment includes, without limitation, all medical devices identified by the U.S. Food and Drug Administration as Class III devices and equivalent classifications outside the U.S.

TI may expressly designate certain products as completing a particular qualification (e.g., Q100, Military Grade, or Enhanced Product). Designers agree that it has the necessary expertise to select the product with the appropriate qualification designation for their applications and that proper product selection is at Designers' own risk. Designers are solely responsible for compliance with all legal and regulatory requirements in connection with such selection.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's noncompliance with the terms and provisions of this Notice.

> Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated