

LOW DROPOUT LINEAR REGULATOR

Description

The AZ1117 is a low dropout three-terminal regulator.

The AZ1117 has been optimized for low voltage where transient response and minimum input voltage are critical. It provides current limit and thermal shutdown. Its circuit includes a trimmed bandgap reference to assure output voltage accuracy to be within ±1%. On-chip thermal shutdown provides protection against a combination of high current and ambient temperature that would create excessive junction temperature.


The AZ1117 is available in 1.2V, 1.5V, 1.8V, 2.5V, 3.3V, 5.0V fixed output voltage versions and ADJ output voltage version. The fixed versions integrate the adjust resistors. It is also available in an adjustable version which can set the output voltage with two external resistors.


The AZ1117 is available in the industry-standard SOT-223 and SOT-89 power packages.


Features

- Current Limit: 1.0A (Typ.)
- Output Noise from 10Hz to 10KHz: 0.003% of Vout
- PSRR at I_{OUT} = 300mA and f = 120Hz: 70dB
- Output Voltage Accuracy: ±1%
- On-chip Thermal Shutdown
- Maximum Quiescent Current: I_{QMAX} = 6mA
- Operation Junction Temperature: -20 to +125°C

Pin Assignments









Applications

- USB Device
- Add-on Card
- DVD Player
- PC Motherboard




Typical Applications Circuit





Functional Block Diagram







Absolute Maximum Ratings (Note 1)

Symbol	Parameter	Rati	ng	Unit	
V _{IN}	Input Voltage	18	3	V	
TJ	Operating Junction Temperature Range	+15	50	°C	
T _{STG}	Storage Temperature Range	-65 to	°C		
	T. 15 (A)	SOT-223	150	°C004	
θ _{JA}	Thermal Resistance (No Heatsink)	SOT-89	210	°C/W	
T _{LEAD}	Lead Temperature (Soldering, 10sec)	+26	60	°C	

Notes:

1. Stresses greater than those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "Recommended Operating Conditions" is not implied. Exposure to "Absolute Maximum Ratings" for extended periods may affect device reliability.

Recommended Operating Conditions

Symbol	Parameter	Min	Max	Unit
VIN	Input Voltage	_	15	V
TJ	Operating Junction Temperature Range	-20	+125	°C





AZ1117

Electrical Characteristics

AZ1117-ADJ Electrical Characteristics (Operating Conditions: $V_{IN} = V_{OUT} + 2V$, $I_{OUT} = 10$ mA, $T_J = +25$ °C, unless otherwise specified. (P \leq maximum power dissipation). Limits appearing in **Boldface** type apply over the entire junction temperature range for operation, -20°C to +125°C.)

Symbol	Parameter	Con	ditions	Min	Тур	Max	Unit
.,	2.4	_		1.238	1.250	1.262	.,
V _{REF}	Reference Voltage	1.5V ≤ V _{IN} -V _{OUT} ≤ 10V		1.225	1.250	1.270	V
	L'as Damidation	15// // //	1.5V ≤ V _{IN} -V _{OUT} ≤ 10V		0.001	0.1	0/
V _{RLINE}	Line Regulation	1.5V \(\text{VIN-VOUT}\)			_	0.2	%
V _{RLOAD}	Load Regulation	_		_	0.4	1.0	%
.,	2	$\Delta V_{REF} = 1\%$,	SOT-223	_	1.2	1.3	.,
V _{DROP}	Dropout Voltage	I _{OUT} = 0.8A	SOT-89	_	1.2	-	V
I _{LIMIT}	Current Limit	_		0.85	1	1.15	Α
_	Adjust Pin Current	-		_	60	120	μA
_	Adjust Pin Current Change	1.5V ≤ V _{IN} -V _{OUT} :	1.5V ≤ V _{IN} -V _{OUT} ≤ 10V		0.2	5	μA
_	Minimum Load Current	1.5V ≤ V _{IN} -V _{OUT} :	≤ 10V	_	1.7	5	mA
PSRR	Ripple Rejection	$f = 120Hz, C_{OUT} = V_{IN}-V_{OUT} = 3V, I_{O}$		_	70	_	dB
_	Temperature Stability	_		-	0.5	-	%
_	RMS Output Noise (% of V _{OUT})	T _A = +25°C, 10Hz	z ≤ f ≤ 10kHz	-	0.003	-	%
_	Thermal Shutdown	Junction Tempera	Junction Temperature		+160	-	°C
_	Thermal Shutdown Hysteresis	-		_	+16	-	°C
	The second Descriptions	SOT-223		-	33	-	0000
θ _{JC}	Thermal Resistance	SOT-89	SOT-89		39	_	°C/W





AZ1117-1.2 Electrical Characteristics (Operating Conditions: $V_{IN} \le 10V$, $I_{OUT} = 10mA$, $T_J = +25^{\circ}C$, unless otherwise specified. (P \le maximum power dissipation). Limits appearing in **Boldface** type apply over the entire junction temperature range for operation, $-20^{\circ}C$ to $+125^{\circ}C$.)

Symbol	Parameter	Con	ditions	Min	Тур	Max	Unit
.,	0	_		1.176	1.2	1.224	.,
V _О Т	Output Voltage	3.2V ≤ V _{IN} ≤ 10V	,	1.152	1.2	1.228	V
		4.50		_	0.5	6	
V _{RLINE}	Line Regulation	1.5V ≤ V _{IN} -V _{OUT}	≤ 10V	_	-	10	mV
V_{RLOAD}	Load Regulation	_		_	2	15	mV
		$\Delta V_{OUT} = 1\%$	SOT-223	_	1.2	1.3	
V _{DROP}	Dropout Voltage	I _{OUT} = 0.8A	SOT-89	_	1.2	-	V
I _{LIMIT}	Current Limit	_		0.85	1	1.15	Α
IQ	Quiescent Current	I _{OUT} = 0		_	4	6	mA
PSRR	Ripple Rejection	f = 120Hz, C _{OUT} V _{IN} -V _{OUT} = 3V, I _O		-	70	ı	dB
_	Temperature Stability	_		_	0.5	ı	%
_	RMS Output Noise (% of V _{OUT})	$T_A = +25^{\circ}C, 10H$	z ≤ f ≤ 10kHz		0.003	-	%
_	Thermal Shutdown	Junction Temper	ature	_	+160	-	°C
_	Thermal Shutdown Hysteresis	-		_	+16	-	°C
	T. 15	SOT-223	SOT-223		- 33	-	
θ _{JC}	Thermal Resistance	SOT-89		_	39	-	°C/W





AZ1117-1.5 Electrical Characteristics (Operating Conditions: $V_{IN} \le 10V$, $I_{OUT} = 10mA$, $T_J = +25^{\circ}C$, unless otherwise specified. (P \le maximum power dissipation). Limits appearing in **Boldface** type apply over the entire junction temperature range for operation, $-20^{\circ}C$ to $+125^{\circ}C$.)

Symbol	Parameter	Cor	ditions	Min	Тур	Max	Unit
.,	2	_		1.485	1.5	1.515	.,
Vout	Output Voltage	3.5V ≤ V _{IN} ≤ 10V	,	1.470	1.5	1.530	V
				_	0.5	6	
V _{RLINE}	Line Regulation	1.5V ≤ V _{IN} -V _{OUT}	≤ 10V	_	_	10	mV
V _{RLOAD}	Load Regulation	-		_	2	15	mV
		$\Delta V_{OUT} = 1\%$	SOT-223	_	1.2	1.3	
V _{DROP}	Dropout Voltage	I _{OUT} = 0.8A	SOT-89	_	1.2	_	V
I _{LIMIT}	Current Limit	-	•	0.85	1	1.15	Α
IQ	Quiescent Current	I _{OUT} = 0		_	4	6	mA
PSRR	Ripple Rejection	f = 120Hz, C _{OUT} V _{IN} -V _{OUT} = 3V, I _O		-	70	_	dB
_	Temperature Stability	_		_	0.5	-	%
_	RMS Output Noise (% of V _{OUT})	T _A = +25°C, 10H	z ≤ f ≤ 10kHz		0.003	-	%
_	Thermal Shutdown	Junction Temper	ature	_	+160	-	°C
_	Thermal Shutdown Hysteresis	-		_	+16	-	°C
		SOT-223	SOT-223		- 33	_	
θ _{JC}	Thermal Resistance	SOT-89	SOT-89		39	_	°C/W





AZ1117-1.8 Electrical Characteristics (Operating Conditions: $V_{IN} \le 10V$, $I_{OUT} = 10$ mA, $T_J = +25$ °C, unless otherwise specified. (P \le maximum power dissipation). Limits appearing in **Boldface** type apply over the entire junction temperature range for operation, -20°C to +125°C.)

Symbol	Parameter	Con	ditions	Min	Тур	Max	Unit
		_		1.782	1.8	1.818	
Vouт	Output Voltage	3.8V ≤ V _{IN} ≤ 10V		1.764	1.8	1.836	V
		4 = 14 . 14		_	0.5	6	
V _{RLINE}	Line Regulation	1.5V ≤ V _{IN} -V _{OUT}	≤ 10V	_	-	10	mV
V _{RLOAD}	Load Regulation	_		_	2	15	mV
		$\Delta V_{OUT} = 1\%$	SOT-223	_	1.2	1.3	
V _{DROP}	Dropout Voltage	I _{OUT} = 0.8A	SOT-89	_	1.2	-	V
I _{LIMIT}	Current Limit	_		0.85	1	1.15	Α
ΙQ	Quiescent Current	I _{OUT} = 0		_	4	6	mA
PSRR	Ripple Rejection	$f = 120Hz$, C_{OUT} : V_{IN} - $V_{OUT} = 3V$, I_{OUT}		_	70	_	dB
-	Temperature Stability	_		_	0.5	_	%
_	RMS Output Noise (% of V _{OUT})	T _A = +25°C, 10H	z ≤ f ≤ 10kHz		0.003	-	%
_	Thermal Shutdown	Junction Temperature		_	+160	_	°C
_	Thermal Shutdown Hysteresis	-		_	+16	_	°C
		SOT-223		_	33	_	
θ _{JC}	Thermal Resistance	SOT-89		_	39	-	°C/W





AZ1117-2.5 Electrical Characteristics (Operating Conditions: $V_{IN} \le 10V$, $I_{OUT} = 10mA$, $T_J = +25^{\circ}C$, unless otherwise specified. (P \le maximum power dissipation). Limits appearing in **Boldface** type apply over the entire junction temperature range for operation, $-20^{\circ}C$ to $+125^{\circ}C$.)

Symbol	Parameter	Con	ditions	Min	Тур	Max	Unit
		_		2.475	2.5	2.525	.,
V _{оит}	Output Voltage	4.5V ≤ V _{IN} ≤ 10V		2.455	2.5	2.545	V
				_	0.5	6	
V _{RLINE}	Line Regulation	1.5V ≤ V _{IN} -V _{OUT} ≤ 10V		_	-	10	mV
V _{RLOAD}	Load Regulation	_		_	2	15	mV
	_	$\Delta V_{OUT} = 1\%,$	SOT-223	_	1.2	1.3	
V _{DROP}	Dropout Voltage	I _{OUT} = 0.8A	SOT-89	_	1.2	_	V
I _{LIMIT}	Current Limit	-	•	0.85	1	1.15	Α
IQ	Quiescent Current	I _{OUT} = 0		_	4	6	mA
PSRR	Ripple Rejection	f = 120Hz, C _{OUT} : V _{IN} -V _{OUT} = 3V, I _O		-	70	_	dB
-	Temperature Stability	_		_	0.5	_	%
_	RMS Output Noise (% of V _{OUT})	$T_A = +25^{\circ}C$, 10Hz	z≤f≤10kHz		0.003	_	%
_	Thermal Shutdown	Junction Temper	ature	_	+160	_	°C
_	Thermal Shutdown Hysteresis	-		_	+16	-	°C
	T. 15	SOT-223		_	33	-	00.044
θ _{JC}	Thermal Resistance	SOT-89		_	39	_	°C/W





AZ1117-3.3 Electrical Characteristics (Operating Conditions: $V_{IN} \le 10V$, $I_{OUT} = 10$ mA, $T_J = +25$ °C, unless otherwise specified. (P \le maximum power dissipation). Limits appearing in **Boldface** type apply over the entire junction temperature range for operation, -20°C to +125°C.)

Symbol	Parameter	Con	ditions	Min	Тур	Max	Unit
	2	_		3.267	3.3	3.333	.,
Vouт	Output Voltage	5.3V ≤ V _{IN} ≤ 10V	,	3.235	3.3	3.365	V
		4 = 14 . 14 . 14		_	0.5	6	
V _{RLINE}	Line Regulation	1.5V ≤ V _{IN} -V _{OUT}	≤ 10V	_	-	10	mV
V _{RLOAD}	Load Regulation	_		-	2	15	mV
	_	$\Delta V_{OUT} = 1\%$	SOT-223	_	1.2	1.3	
V _{DROP}	Dropout Voltage	I _{OUT} = 0.8A	SOT-89	_	1.2	-	V
I _{LIMIT}	Current Limit	_		0.85	1	1.15	Α
IQ	Quiescent Current	I _{OUT} = 0		_	4	6	mA
PSRR	Ripple Rejection	f = 120Hz, C _{OUT} V _{IN} -V _{OUT} = 3V, I _O		-	70	-	dB
_	Temperature Stability	_		_	0.5	_	%
_	RMS Output Noise (% of V _{OUT})	T _A = +25°C, 10H	z ≤ f ≤ 10kHz		0.003	-	%
_	Thermal Shutdown	Junction Temper	Junction Temperature		+160	-	°C
_	Thermal Shutdown Hysteresis	-		-	+16	-	°C
		SOT-223	SOT-223		33	_	
θ _{JC}	Thermal Resistance	SOT-89		_	39	-	°C/W






AZ1117-5.0 Electrical Characteristics (Operating Conditions: $V_{IN} \le 10V$, $I_{OUT} = 10mA$, $T_J = +25^{\circ}C$, unless otherwise specified. (P \le maximum power dissipation). Limits appearing in **Boldface** type apply over the entire junction temperature range for operation, $-20^{\circ}C$ to $+125^{\circ}C$.)

Symbol	Parameter	Con	ditions	Min	Тур	Max	Unit
.,	2	_		4.950	5.0	5.050	.,
Vout	Output Voltage	6.5V ≤ V _{IN} ≤ 10V	,	4.900	5.0	5.100	V
				_	0.5	6	
V _{RLINE}	Line Regulation	1.5V ≤ V _{IN} -V _{OUT}	≤ 10V	_	-	10	mV
V _{RLOAD}	Load Regulation	_		-	2	15	mV
		$\Delta V_{OUT} = 1\%$	SOT-223	-	1.2	1.3	
V _{DROP}	Dropout Voltage	$I_{OUT} = 0.8A$	SOT-89	-	1.2	_	V
I _{LIMIT}	Current Limit	_		0.85	1	1.15	Α
IQ	Quiescent Current	I _{OUT} = 0		_	4	6	mA
PSRR	Ripple Rejection	f = 120Hz, C _{OUT} V _{IN} -V _{OUT} = 3V, I _O		-	70	_	dB
_	Temperature Stability	_		_	0.5	_	%
_	RMS Output Noise (% of V _{OUT})	T _A = +25°C, 10H	z ≤ f ≤ 10kHz		0.003	-	%
_	Thermal Shutdown	Junction Temper	ature	_	+160	-	°C
_	Thermal Shutdown Hysteresis	-		_	+16	-	°C
		SOT-223	SOT-223		33	_	°C/W
θ _{JC}	Thermal Resistance	SOT-89	SOT-89		39	_	




Performance Characteristics


Line Regulation vs. Junction Temperature




Load Regulation vs. Junction Temperature




Reference Voltage vs. Junction Temperature




Output Voltage vs. Junction Temperature



Minimum Load Current vs. Junction Temperature




Adjust Pin Current vs. Junction Temperature






Performance Characteristics (Cont.)


Dropout Voltage vs. Output Current




Power Dissipation vs. Case Temperature




Line Transient Response




Load Transient Response



PSRR vs. Frequency



Current Limit vs. Junction Temperature








Performance Characteristics (Cont.)


Dropout Voltage vs. Junction Temperature








Ordering Information




Package	Temperature Range	Part Number	Marking ID	Packing
		AZ1117H-ADJTRG1	GH17K	Tape & Reel
		AZ1117H-1.2TRG1	GH17P	Tape & Reel
		AZ1117H-1.5TRG1	GH17Q	Tape & Reel
SOT-223	-20 to +125°C	AZ1117H-1.8TRG1	GH17L	Tape & Reel
		AZ1117H-2.5TRG1	GH17N	Tape & Reel
		AZ1117H-3.3TRG1	GH17M	Tape & Reel
		AZ1117H-5.0TRG1	GH17R	Tape & Reel
		AZ1117R-ADJTRG1	G31F	Tape & Reel
		AZ1117R-1.2TRG1	G31G	Tape & Reel
		AZ1117R-1.5TRG1	G31H	Tape & Reel
SOT-89	-20 to +125°C	AZ1117R-1.8TRG1	G31J	Tape & Reel
		AZ1117R-2.5TRG1	G31K	Tape & Reel
		AZ1117R-3.3TRG1	G31L	Tape & Reel
		AZ1117R-5.0TRG1	G31M	Tape & Reel






Package Outline Dimensions (All dimensions in mm(inch).)

(1) Package Type: SOT-223













Package Outline Dimensions (Cont. All dimensions in mm(inch).)


(2) Package Type: SOT-89












Option 2



Suggested Pad Layout

(1) Package Type: SOT-223




Dimensions	Z	G	X1	X2	Υ	E1	E2
	(mm)/(inch)						
Value	8.400/0.331	4.000/0.157	1.200/0.047	3.500/0.138	2.200/0.087	2.300/0.091	4.600/0.181



Suggested Pad Layout (Cont.)

(2) Package Type: SOT-89



Dimensions	Z	X	X1	X2	Υ	Y1	E
	(mm)/(inch)						
Value	4.600/0.181	0.550/0.022	1.850/0.073	0.800/0.031	1.300/0.051	1.475/0.058	1.500/0.059



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2015, Diodes Incorporated

www.diodes.com