SDLS049B – DECEMBER 1983 – REVISED FEBRUARY 2002


- Operation From Very Slow Edges
- Improved Line-Receiving Characteristics
- High Noise Immunity

#### description


Each circuit functions as an inverter, but because of the Schmitt action, it has different input threshold levels for positive-going  $(V_{T+})$  and negative-going  $(V_{T-})$  signals.

These circuits are temperature compensated and can be triggered from the slowest of input ramps and still give clean, jitter-free output signals.

SN5414, SN54LS14...J OR W PACKAGE SN7414...D, N, OR NS PACKAGE SN74LS14...D, DB, OR N PACKAGE (TOP VIEW)



SN54LS14 . . . FK PACKAGE (TOP VIEW)



NC - No internal connection

#### ORDERING INFORMATION

TA	PACI	(AGE†	ORDERABLE PART NUMBER	TOP-SIDE MARKING
	PDIP – N	Tube	SN7414N	SN7414N
	PDIP - N	Tube	SN74LS14N	SN74LS14N
0°C to 70°C		Tube	SN7414D	7414
	SOIC - D	Tape and reel	SN7414DR	7414
	3010 - D	Tube	SN74LS14D	LS14
		Tape and reel	SN74LS14DR	L314
	SOP – NS	Tape and reel	SN7414NSR	SN7414
	SSOP – DB	Tape and reel	SN74LS14DBR	LS14
		Tube	SN5414J	SN5414J
	CDIP – J	Tube	SNJ5414J	SNJ5414J
	CDIF = J	Tube	SN54LS14J	SN54LS14J
–55°C to 125°C		Tube	SNJ54LS14J	SNJ54LS14J
	CFP – W	Tube	SNJ5414W	SNJ5414W
L	CIF - W	Tube	SNJ54LS14W	SNJ54LS14W
	LCCC – FK	Tube	SNJ54LS14FK	SNJ54LS14FK


<sup>†</sup> Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at www.ti.com/sc/package.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.




## logic diagram (positive logic)



Pin numbers shown are for the D, DB, J, N, NS, and W packages.



## schematic





#### absolute maximum ratings over operating free-air temperature (unless otherwise noted)†

Supply voltage, V <sub>CC</sub> (see Note 1)	
Input voltage: '14	5.5 V
'LS14	7 V
Package thermal impedance, θ <sub>JA</sub> (see Note 2): D package	e 86°C/W
DB packa	ge 96°C/W
N package	e 80°C/W
NS packa	ge 76°C/W
Storage temperaturerange, T <sub>stg</sub>	–65°C to 150°C

<sup>†</sup> Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

- NOTES: 1. Voltage values are with respect to network ground terminal.
  - 2. The package termal impedance is calculated in accordance with JESD 51-7

#### recommended operating conditions

			SN5414		,	SN7414		UNIT
		MIN	NOM	MAX	MIN	NOM	MAX	UNIT
Vcc	Supply voltage	4.5	5	5.5	4.75	5	5.25	V
ІОН	High-level output current			-0.8			-0.8	mA
l <sub>OL</sub>	Low-level output current			16			16	mA
TA	Operating free-air temperature	-55		125	0		70	°C

# electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

PARAMETER		TEST CONDI	TIONS‡		SN5414 SN7414		UNIT
				MIN	TYP§	MAX	
V <sub>T+</sub>	V <sub>CC</sub> = 5 V			1.5	1.7	2	V
$V_{T-}$	V <sub>CC</sub> = 5 V			0.6	0.9	1.1	V
Hysteresis (V <sub>T+</sub> – V <sub>T</sub> )	V <sub>CC</sub> = 5 V			0.4	0.8		V
VIK	V <sub>CC</sub> = MIN,	I <sub>I</sub> = -12 mA				-1.5	V
VOH	V <sub>CC</sub> = MIN,	$V_{I} = 0.6 V$ ,	$I_{OH} = -0.8 \text{ mA}$	2.4	3.4		V
V <sub>OL</sub>	$V_{CC} = MIN,$	$V_I = 2 V$ ,	I <sub>OL</sub> = 16 mA		0.2	0.4	V
I <sub>T+</sub>	$V_{CC} = 5 V$ ,	$V_I = V_{T+}$			-0.43		mA
I <sub>T</sub> _	$V_{CC} = 5 V$ ,	$V_I = V_{T-}$			-0.56		mA
lį	$V_{CC} = MAX$ ,	V <sub>I</sub> = 5.5 V				1	mA
I <sub>IH</sub>	$V_{CC} = MAX$ ,	$V_{IH} = 2.4 \text{ V}$				40	μΑ
I <sub>IL</sub>	$V_{CC} = MAX$ ,	$V_{IL} = 0.4 V$			-0.8	-1.2	mA
los¶	$V_{CC} = MAX$			-18		-55	mA
Іссн	V <sub>CC</sub> = MAX				22	36	mA
ICCL	$V_{CC} = MAX$				39	60	mA

<sup>‡</sup> For conditions shown as MIN or MAX, use the appropriate value specified under recommended operating conditions.



<sup>§</sup> All typical values are at  $V_{CC} = 5 \text{ V}$ ,  $T_A = 25^{\circ}\text{C}$ .

<sup>¶</sup> Not more than one output should be shorted at a time.

#### SDLS049B - DECEMBER 1983 - REVISED FEBRUARY 2002

# switching characteristics, $V_{CC} = 5 \text{ V}$ , $T_A = 25^{\circ}\text{C}$ (see Figure 1)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	TEST CONDITIONS		SN5414 SN7414			
	(INPOT)	(001701)		MIN	TYP	MAX		
<sup>t</sup> PLH	Α	V	$R_L = 400 \Omega$ , $C_L = 15 pF$		15	22	ns	
t <sub>PHL</sub>		1	111 - 400 22, OL - 10 PI		15	22	113	

## recommended operating conditions

		S	N54LS14	1	S	UNIT		
		MIN	NOM	MAX	MIN	NOM	MAX	UNIT
Vcc	Supply voltage	4.5	5	5.5	4.75	5	5.25	V
ІОН	High-level output current			-0.4			-0.4	mA
loL	Low-level output current			4			8	mA
TA	Operating free-air temperature	-55		125	0		70	°C

# electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

DADAMETED		TEST SOUDITI	ovet	s	N54LS1	4	S	N74LS1	4	UNIT
PARAMETER		TEST CONDITI	MIN	TYP‡	MAX	MIN	TYP‡	MAX	UNII	
V <sub>T+</sub>	V <sub>CC</sub> = 5 V			1.4	1.6	1.9	1.4	1.6	1.9	V
V <sub>T</sub>	V <sub>CC</sub> = 5 V			0.5	0.8	1	0.5	0.8	1	V
Hysteresis (V <sub>T+</sub> – V <sub>T</sub> –)	V <sub>CC</sub> = 5 V			0.4	0.8		0.4	0.8		٧
VIK	$V_{CC} = MIN,$	I <sub>I</sub> = -18 mA				-1.5			-1.5	V
Vон	$V_{CC} = MIN,$	$V_{I} = 0.5 V$ ,	$I_{OH} = -0.4 \text{ mA}$	2.5	3.4		2.7	3.4		V
Vol	V <sub>CC</sub> = MIN,	V <sub>I</sub> = -1.9 V	I <sub>OL</sub> = 4 mA		0.25	0.4		0.25	0.4	V
VOL	VCC = IVIIIA,	V  = -1.9 V	$I_{OL} = 8 \text{ mA}$					0.35	0.5	V
I <sub>T+</sub>	$V_{CC} = 5 V$ ,	$V_I = V_{T+}$			-0.14			-0.14		mA
I <sub>T</sub> _	$V_{CC} = 5 V$ ,	$V_I = V_{T-}$			-0.18			-0.18		mA
IĮ	$V_{CC} = MAX$ ,	V <sub>I</sub> = 7 V				0.1			0.1	mA
lін	$V_{CC} = MAX$ ,	$V_{IH} = 2.7 V$				20			20	μΑ
I <sub>IL</sub>	$V_{CC} = MAX$ ,	$V_{IL} = 0.4 V$				-0.4			-0.4	mA
los§	$V_{CC} = MAX$			-20		-100	-20		-100	mA
ІССН	$V_{CC} = MAX$				8.6	16		8.6	16	mA
<sup>I</sup> CCL	$V_{CC} = MAX$				12	21		12	21	mA

<sup>†</sup> For conditions shown as MIN or MAX, use the appropriate value specified under recommended operating conditions.

# switching characteristics, $V_{CC} = 5 \text{ V}$ , $T_A = 25^{\circ}\text{C}$ (see Figure 2)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	TEST CONDITIONS	MIN	TYP	MAX	UNIT
<sup>t</sup> PLH	Δ	V	$R_1 = 2 k\Omega$ , $C_1 = 15 pF$		15	22	ns
tpHL		1	11 - 2 1/22, OL - 10 PI		15	22	113



<sup>‡</sup> All typical values are at  $V_{CC} = 5 \text{ V}$ ,  $T_A = 25^{\circ}\text{C}$ .

<sup>§</sup> Not more than one output should be shorted at a time, and duration of the short-circuit should not exceed one second.

#### SDLS049B - DECEMBER 1983 - REVISED FEBRUARY 2002

#### PARAMETER MEASUREMENT INFORMATION **SERIES 54/74 DEVICES** Vcc ○ $R_{\mathsf{L}}$ Test Test **Point** S1 ۷сс **Point** From Output VCC **Under Test** (see Note B) (see Note A) From Output $R_{\mathsf{L}}$ 1 k $\Omega$ **Under Test** (see Note B) From Output Test **Under Test Point** (see Note A) (see Note A) S2 **LOAD CIRCUIT** LOAD CIRCUIT **LOAD CIRCUIT** FOR 2-STATE TOTEM-POLE OUTPUTS FOR OPEN-COLLECTOR OUTPUTS **FOR 3-STATE OUTPUTS High-Level Timing** 1.5 V **Pulse** Input th Low-Level Data **Pulse** Input **VOLTAGE WAVEFORMS VOLTAGE WAVEFORMS PULSE DURATIONS SETUP AND HOLD TIMES** Output 3 V Control .5 V (low-level enabling) Input 1.5 V 0 V **tPZL tPLZ tPLH tPHL** Waveform 1 ≈1.5 V In-Phase − VoH (see Notes C Output and D) (see Note D) Vol <sup>t</sup>PHZ tPZH -<sup>t</sup>PHL Waveform 2 V<sub>OH</sub> - 0.5 V Out-of-Phase ۷он (see Notes C 1.5 V Output 1.5 V 1.5 V and D) (see Note D) · VOL

NOTES: A. C<sub>I</sub> includes probe and jig capacitance.

B. All diodes are 1N3064 or equivalent.

**VOLTAGE WAVEFORMS** 

**PROPAGATION DELAY TIMES** 

- C. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.
- D. S1 and S2 are closed for tpLH, tpHL, tpHZ, and tpLZ; S1 is open and S2 is closed for tpZH; S1 is closed and S2 is open for tpZL.

**VOLTAGE WAVEFORMS** 


**ENABLE AND DISABLE TIMES, 3-STATE OUTPUTS** 

- E. All input pulses are supplied by generators having the following characteristics: PRR  $\leq$  1 MHz,  $Z_O \approx 50 \Omega$ ;  $t_r$  and  $t_f \leq$  7 ns for Series 54/74 devices and  $t_r$  and  $t_f \le 2.5$  ns for Series 54S/74S devices.
- F. The outputs are measured one at a time with one input transition per measurement.

Figure 1. Load Circuits and Voltage Waveforms



# PARAMETER MEASUREMENT INFORMATION SERIES 54LS/74LS DEVICES



- NOTES: A.  $C_L$  includes probe and jig capacitance.
  - B. All diodes are 1N3064 or equivalent.
  - C. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.
  - D. S1 and S2 are closed for tpLH, tpHZ, and tpLZ; S1 is open and S2 is closed for tpZH; S1 is closed and S2 is open for tpZL.
  - E. Phase relationships between inputs and outputs have been chosen arbitrarily for these examples.
  - F. All input pulses are supplied by generators having the following characteristics: PRR  $\leq$  1 MHz,  $Z_O \approx 50~\Omega$ ,  $t_f \leq$  1.5 ns,  $t_f \leq$  2.6 ns.
  - G. The outputs are measured one at a time with one input transition per measurement.

Figure 2. Load Circuits and Voltage Waveforms





SDLS049B - DECEMBER 1983 - REVISED FEBRUARY 2002

#### TYPICAL CHARACTERISTICS OF '14 CIRCUITS'

#### POSITIVE-GOING THRESHOLD VOLTAGE FREE-AIR TEMPERATURE 1.70 $V_{CC} = 5 V$ V<sub>T+</sub> – Positive-Going Threshold Voltage – V 1.69 1.68 1.67 1.66 1.65 1.64 1.63 1.62 1.61 1.60 25 50 75 100 **–75 –50** -25 0 125 $T_A$ – Free-Air Temperature – $^{\circ}C$

Figure 3








<sup>†</sup> Data for temperatures below 0°C and above 70°C and supply voltage below 4.75 V and above 5.25 V are applicable for SN5414 only.




#### TYPICAL CHARACTERISTICS OF '14 CIRCUITS'











<sup>†</sup> Data for temperatures below 0°C and above 70°C and supply voltage below 4.75 V and above 5.25 V are applicable for SN5414 only.




#### TYPICAL CHARACTERISTICS OF 'LS14 CIRCUITS'

## POSITIVE-GOING THRESHOLD VOLTAGE FREE-AIR TEMPERATURE 1.70 $V_{CC} = 5 V$ VT+ - Positive-Going Threshold Voltage - V 1.69 1.68 1.67 1.66 1.65 1.64 1.63 1.62 1.61 1.60 -75 -50 25 50 75 100 125 T<sub>A</sub> - Free-Air Temperature - °C Figure 10








<sup>†</sup> Data for temperatures below 0°C and above 70°C and supply voltage below 4.75 V and above 5.25 V are applicable for SN5414 only.



#### TYPICAL CHARACTERISTICS OF 'LS14 CIRCUITS'





<sup>†</sup> Data for temperatures below 0°C and above 70°C and supply voltage below 4.75 V and above 5.25 V are applicable for SN5414 only.





SDLS049B - DECEMBER 1983 - REVISED FEBRUARY 2002


#### **TYPICAL APPLICATION DATA**














**Pulse Stretcher** 







17-Dec-2015

#### **PACKAGING INFORMATION**

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead/Ball Finish (6)	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Sample
5962-9665801Q2A	ACTIVE	LCCC	FK	20	1	TBD	POST-PLATE	N / A for Pkg Type	-55 to 125	5962- 9665801Q2A SNJ54LS 14FK	Sample
5962-9665801QCA	ACTIVE	CDIP	J	14	1	TBD	A42	N / A for Pkg Type	-55 to 125	5962-9665801QC A SNJ54LS14J	Sample
5962-9665801QDA	ACTIVE	CFP	W	14	1	TBD	A42	N / A for Pkg Type	-55 to 125	5962-9665801QD A SNJ54LS14W	Sample
5962-9665801VDA	ACTIVE	CFP	W	14	1	TBD	A42	N / A for Pkg Type	-55 to 125	5962-9665801VD A SNV54LS14W	Sample
JM38510/31302BCA	ACTIVE	CDIP	J	14	1	TBD	A42	N / A for Pkg Type	-55 to 125	JM38510/ 31302BCA	Sample
M38510/31302BCA	ACTIVE	CDIP	J	14	1	TBD	A42	N / A for Pkg Type	-55 to 125	JM38510/ 31302BCA	Sample
SN5414J	ACTIVE	CDIP	J	14	1	TBD	A42	N / A for Pkg Type	-55 to 125	SN5414J	Sample
SN54LS14J	ACTIVE	CDIP	J	14	1	TBD	A42	N / A for Pkg Type	-55 to 125	SN54LS14J	Sample
SN7414D	ACTIVE	SOIC	D	14	50	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	7414	Sample
SN7414DG4	ACTIVE	SOIC	D	14	50	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	7414	Sample
SN7414DR	ACTIVE	SOIC	D	14	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	7414	Sample
SN7414N	ACTIVE	PDIP	N	14	25	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type	0 to 70	SN7414N	Sample
SN7414N3	OBSOLETI	E PDIP	N	14		TBD	Call TI	Call TI	0 to 70		
SN7414NE4	ACTIVE	PDIP	N	14	25	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type	0 to 70	SN7414N	Sample
SN7414NSR	ACTIVE	SO	NS	14	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	SN7414	Sample
SN74LS14D	ACTIVE	SOIC	D	14	50	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	LS14	Sample





www.ti.com

17-Dec-2015

Orderable Device	Status	Package Type		Pins		Eco Plan	Lead/Ball Finish	MSL Peak Temp	Op Temp (°C)	Device Marking	Samples
	(1)		Drawing		Qty	(2)	(6)	(3)		(4/5)	
SN74LS14DBR	ACTIVE	SSOP	DB	14	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	LS14	Samples
SN74LS14DBRG4	ACTIVE	SSOP	DB	14	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	LS14	Samples
SN74LS14DE4	ACTIVE	SOIC	D	14	50	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	LS14	Samples
SN74LS14DG4	ACTIVE	SOIC	D	14	50	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	LS14	Samples
SN74LS14DR	ACTIVE	SOIC	D	14	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	LS14	Samples
SN74LS14DRE4	ACTIVE	SOIC	D	14	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	LS14	Samples
SN74LS14DRG4	ACTIVE	SOIC	D	14	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	LS14	Samples
SN74LS14N	ACTIVE	PDIP	N	14	25	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type	0 to 70	SN74LS14N	Samples
SN74LS14N3	OBSOLETI	E PDIP	N	14		TBD	Call TI	Call TI	0 to 70		
SN74LS14NE4	ACTIVE	PDIP	N	14	25	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type	0 to 70	SN74LS14N	Samples
SN74LS14NSR	ACTIVE	so	NS	14	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	74LS14	Samples
SNJ5414J	ACTIVE	CDIP	J	14	1	TBD	A42	N / A for Pkg Type	-55 to 125	SNJ5414J	Samples
SNJ5414W	ACTIVE	CFP	W	14	1	TBD	A42	N / A for Pkg Type	-55 to 125	SNJ5414W	Samples
SNJ54LS14FK	ACTIVE	LCCC	FK	20	1	TBD	POST-PLATE	N / A for Pkg Type	-55 to 125	5962- 9665801Q2A SNJ54LS 14FK	Samples
SNJ54LS14J	ACTIVE	CDIP	J	14	1	TBD	A42	N / A for Pkg Type	-55 to 125	5962-9665801QC A SNJ54LS14J	Samples
SNJ54LS14W	ACTIVE	CFP	W	14	1	TBD	A42	N / A for Pkg Type	-55 to 125	5962-9665801QD A SNJ54LS14W	Samples

<sup>(1)</sup> The marketing status values are defined as follows: **ACTIVE:** Product device recommended for new designs.

#### PACKAGE OPTION ADDENDUM



17-Dec-2015

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.

**TBD:** The Pb-Free/Green conversion plan has not been defined.

**Pb-Free** (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes. **Ph-Free** (RoHS Exempt): This component has a RoHS exemption for either 1) lead-based flip-chip solder humps used between the die and package, or 2) lead-based die adhesive used between

**Pb-Free (RoHS Exempt):** This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead/Ball Finish Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

#### OTHER QUALIFIED VERSIONS OF SN5414, SN54LS14, SN54LS14-SP, SN7414, SN74LS14:

Catalog: SN7414, SN74LS14, SN54LS14

Military: SN5414, SN54LS14

Space: SN54LS14-SP





17-Dec-2015

#### NOTE: Qualified Version Definitions:


- Catalog TI's standard catalog product
- Military QML certified for Military and Defense Applications
- Space Radiation tolerant, ceramic packaging and qualified for use in Space-based application

# PACKAGE MATERIALS INFORMATION


www.ti.com 14-Jul-2012

## TAPE AND REEL INFORMATION

#### **REEL DIMENSIONS**



#### **TAPE DIMENSIONS**



A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

#### TAPE AND REEL INFORMATION

\*All dimensions are nominal

"All dimensions are nominal												
Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
SN7414DR	SOIC	D	14	2500	330.0	16.4	6.5	9.0	2.1	8.0	16.0	Q1
SN7414NSR	SO	NS	14	2000	330.0	16.4	8.2	10.5	2.5	12.0	16.0	Q1
SN74LS14DBR	SSOP	DB	14	2000	330.0	16.4	8.2	6.6	2.5	12.0	16.0	Q1
SN74LS14DR	SOIC	D	14	2500	330.0	16.4	6.5	9.0	2.1	8.0	16.0	Q1
SN74LS14NSR	SO	NS	14	2000	330.0	16.4	8.2	10.5	2.5	12.0	16.0	Q1

www.ti.com 14-Jul-2012



\*All dimensions are nominal

7. difference are normal							
Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
SN7414DR	SOIC	D	14	2500	367.0	367.0	38.0
SN7414NSR	SO	NS	14	2000	367.0	367.0	38.0
SN74LS14DBR	SSOP	DB	14	2000	367.0	367.0	38.0
SN74LS14DR	SOIC	D	14	2500	367.0	367.0	38.0
SN74LS14NSR	SO	NS	14	2000	367.0	367.0	38.0

## 14 LEADS SHOWN



- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- C. This package is hermetically sealed with a ceramic lid using glass frit.
- D. Index point is provided on cap for terminal identification only on press ceramic glass frit seal only.
- E. Falls within MIL STD 1835 GDIP1-T14, GDIP1-T16, GDIP1-T18 and GDIP1-T20.

# W (R-GDFP-F14)

## CERAMIC DUAL FLATPACK



- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- C. This package can be hermetically sealed with a ceramic lid using glass frit.
- D. Index point is provided on cap for terminal identification only.
- E. Falls within MIL STD 1835 GDFP1-F14



# FK (S-CQCC-N\*\*)

## LEADLESS CERAMIC CHIP CARRIER

28 TERMINAL SHOWN



- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- C. This package can be hermetically sealed with a metal lid.
- D. Falls within JEDEC MS-004



# N (R-PDIP-T\*\*)

## PLASTIC DUAL-IN-LINE PACKAGE

16 PINS SHOWN



- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
- The 20 pin end lead shoulder width is a vendor option, either half or full width.



# D (R-PDSO-G14)

## PLASTIC SMALL OUTLINE



- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.006 (0,15) each side.
- Body width does not include interlead flash. Interlead flash shall not exceed 0.017 (0,43) each side.
- E. Reference JEDEC MS-012 variation AB.



# D (R-PDSO-G14)

# PLASTIC SMALL OUTLINE



- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Publication IPC-7351 is recommended for alternate designs.
- D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC-7525 for other stencil recommendations.
- E. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.



## **MECHANICAL DATA**

## NS (R-PDSO-G\*\*)

# 14-PINS SHOWN

#### PLASTIC SMALL-OUTLINE PACKAGE



- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.



## DB (R-PDSO-G\*\*)

## PLASTIC SMALL-OUTLINE

#### **28 PINS SHOWN**



NOTES: A. All linear dimensions are in millimeters.

B. This drawing is subject to change without notice.

C. Body dimensions do not include mold flash or protrusion not to exceed 0,15.

D. Falls within JEDEC MO-150

#### IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have *not* been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

#### Products Applications

Audio www.ti.com/audio Automotive and Transportation www.ti.com/automotive **Amplifiers** amplifier.ti.com Communications and Telecom www.ti.com/communications **Data Converters** dataconverter.ti.com Computers and Peripherals www.ti.com/computers **DLP® Products** www.dlp.com Consumer Electronics www.ti.com/consumer-apps DSP dsp.ti.com **Energy and Lighting** www.ti.com/energy Clocks and Timers www.ti.com/clocks Industrial www.ti.com/industrial Interface interface.ti.com Medical www.ti.com/medical Logic Security www.ti.com/security logic.ti.com

Power Mgmt power.ti.com Space, Avionics and Defense www.ti.com/space-avionics-defense

Microcontrollers microcontroller.ti.com Video and Imaging www.ti.com/video

RFID www.ti-rfid.com

OMAP Applications Processors www.ti.com/omap TI E2E Community e2e.ti.com

Wireless Connectivity www.ti.com/wirelessconnectivity