OCTAL E1 SHORT HAUL LINE INTERFACE UNIT

FEATURES

- Fully integrated octal E1 short haul line interface which supports 120 Ω E1 twisted pair and 75 Ω E1 coaxial applications
- Selectable Single Rail mode or Dual Rail mode and AMI or HDB3 encoder/decoder
- Built-in transmit pre-equalization meets G.703
- Selectable transmit/receive jitter attenuator meets ETSI CTR12/ 13, ITU G.736, G.742 and G.823 specifications
- SONET/SDH optimized jitter attenuator meets ITU G.783 mapping jitter specification

FUNCTIONAL BLOCK DIAGRAM

- Digital/Analog LOS detector meets ITU G.775 and ETS 300 233
- ITU G.772 non-intrusive monitoring for in-service testing for any one of channel 1 to channel 7

- Low impedance transmit drivers with high-Z
- Selectable hardware and parallel/serial host interface
- Local and Remote Loopback test functions
- Hitless Protection Switching (HPS) for 1 to 1 protection without relays
- JTAG boundary scan for board test
- 3.3 V supply with 5 V tolerant I/O
- Low power consumption
- Operating temperature range: -40°C to +85°C
- Available in 144-pin Thin Quad Flat Pack (TQFP) and 160-pin Plastic Ball Grid Array (PBGA) packages Green package options available




Figure-1 Block Diagram

1

IDT and the IDT logo are trademarks of Integrated Device Technology, Inc.

January 21, 2010

© 2010- Integrated Device Technology, Inc.

DESCRIPTION

The IDT82V2058 is a single chip, 8-channel E1 short haul PCM transceiver with a reference clock of 2.048 MHz. The IDT82V2058 contains 8 transmitters and 8 receivers.


All the receivers and transmitters can be programmed to work either in Single Rail mode or Dual Rail mode. HDB3 or AMI encoder/decoder is selectable in Single Rail mode. Pre-encoded transmit data in NRZ format can be accepted when the device is configured in Dual Rail mode. The receivers perform clock and data recovery by using integrated digital phase-locked loop. As an option, the raw sliced data (no retiming) can be output on the receive data pins. Transmit equalization is implemented with low-impedance output drivers that provide shaped waveforms to the transformer, guaranteeing template conformance.

A jitter attenuator is integrated in the IDT82V2058 and can be switched into either the transmit path or the receive path for all channels. The jitter attenuation performance meets ETSI CTR12/13, ITU G.736, G.742 and G.823 specifications.

The IDT82V2058 offers hardware control mode and software control mode. Software control mode works with either serial host interface or parallel host interface. The latter works via an Intel/Motorola compatible 8-bit parallel interface for both multiplexed or non-multiplexed applications. Hardware control mode uses multiplexed pins to select different operation modes when the host interface is not available to the device.

The IDT82V2058 also provides loopback and JTAG boundary scan testing functions. Using the integrated monitoring function, the IDT82V2058 can be configured as a 7-channel transceiver with non-intrusive protected monitoring points.

The IDT82V2058 can be used for SDH/SONET multiplexers, central office or PBX, digital access cross connects, digital radio base stations, remote wireless modules and microwave transmission systems.



PIN CONFIGURATIONS

Figure-2 TQFP144 Package Pin Assignment

INDUSTRIAL TEMPERATURE RANGES




Figure-3 PBGA160 Package Pin Assignment

1 PIN DESCRIPTION

Table-1 Pin Description

| Name Type | | Pin No. | | Description | | |
|-----------|--------|-----------------|-----|---|--|--|
| Name | туре | TQFP144 PBGA160 | | Description | | |
| | | I | I | Transmit and Receive Line Interface | | |
| TTIP0 | | 45 | N5 | | | |
| TTIP1 | | 52 | L5 | | | |
| TTIP2 | | 57 | L10 | | | |
| TTIP3 | | 64 | N10 | | | |
| TTIP4 | | 117 | B10 | | | |
| TTIP5 | | 124 | D10 | | | |
| TTIP6 | | 129 | D5 | TTIPn/TRINGn: Transmit Bipolar Tip/Ring for Channel 0~7 | | |
| TTIP7 | Analog | 136 | B5 | These pins are the differential line driver outputs. They will be in high-Z if pin OE is low or the correspond- | | |
| TRING0 | Output | 46 | P5 | ing pin TCLKn is low (pin OE is global control, while pin TCLKn is per-channel control). In host mode, each | | |
| TRING1 | | 51 | M5 | pin can be in high-Z by programming a '1' to the corresponding bit in register OE ⁽¹⁾ . | | |
| TRING2 | | 58 | M10 | | | |
| TRING3 | | 63 | P10 | | | |
| TRING4 | | 118 | A10 | | | |
| TRING5 | | 123 | C10 | | | |
| TRING6 | | 130 | C5 | | | |
| TRING7 | | 135 | A5 | | | |
| RTIP0 | | 48 | P7 | | | |
| RTIP1 | | 55 | M7 | | | |
| RTIP2 | | 60 | M8 | | | |
| RTIP3 | | 67 | P8 | | | |
| RTIP4 | | 120 | A8 | | | |
| RTIP5 | | 127 | C8 | | | |
| RTIP6 | | 132 | C7 | | | |
| RTIP7 | Analog | 139 | A7 | RTIPn/RRINGn: Receive Bipolar Tip/Ring for Channel 0~7 | | |
| RRING0 | Input | 49 | N7 | These pins are the differential line receiver inputs. | | |
| RRING1 | | 54 | L7 | | | |
| RRING2 | | 61 | L8 | | | |
| RRING3 | | 66 | N8 | | | |
| RRING4 | | 121 | B8 | | | |
| RRING5 | | 126 | D8 | | | |
| RRING6 | | 133 | D7 | | | |
| RRING7 | | 138 | B7 | | | |

¹. Register name is indicated by bold capital letter. For example, **OE** indicates Output Enable Register.

| News | T | Pin | No. | Description | | | | | | |
|--|----------|---|--|---|---|--|---|--|--|--|
| Name | Туре | TQFP144 | PBGA160 | İ | Description | | | | | |
| | | | | Transmit a | nd Receive Digita | Data Interfa | ace | | | |
| TD0/TDP0 TD1/TDP1 TD2/TDP2 TD3/TDP3 TD4/TDP4 TD5/TDP5 TD6/TDP6 TD7/TDP7 BPVI0/TDN0 BPVI1/TDN1 BPVI2/TDN2 BPVI3/TDN3 BPVI4/TDN4 BPVI5/TDN5 BPVI6/TDN6 BPVI7/TDN7 | I | 37 30 80 73 108 101 8 1 1 38 31 79 72 109 102 7 144 | N2 L2 L13 N13 B13 D13 D2 B2 N3 L3 L12 N12 B12 D12 D3 B3 | When the d sampled int before being Bipolar viola 14) with AW TDn the sam TDPn/TDN When the d on this pin. mode is as Pulling pin | o the device on the g transmitted to the alion insertion is availl enabled. A low-to me polarity as the p n: Positive/Negativ evice is in Dual Rai Data on TDPn/TDN the follow: TDPn 0 0 1 1 1 TDNn high for more | rtion for Ch iil mode, the falling edges line. rtion for Ch iilable in Sing high transitic revious pulse re Transmit Mode, the N n are sample TDNn 0 1 0 1 1 0 1 1 0 | NRZ data to be transmitted is input on this pin. Data on TDn is of TCLKn, and encoded by AMI or HDB3 line code rules annel 0~7 gle Rail mode 2 (see Table-2 on page 13 and Table-3 on page on on this pin will make the next logic one to be transmitted on e, and violate the AMI rule. This is for testing. Data for Channel 0~7 IRZ data to be transmitted for positive/negative pulse is input ed on the falling edges of TCLKn. The line code in dual rail Output Pulse Space Negative Pulse Space Secutive TCLK clock cycles will configure the corresponding 2 on page 13 and Table-3 on page 14). | | | |
| TCLK0 TCLK1 TCLK2 TCLK3 TCLK4 TCLK5 TCLK6 TCLK7 | 1 | 36 29 81 74 107 100 9 2 | N1 L1 L14 N14 B14 D1 B1 | TCLKn: Tra The clock o pled into the Pulling TCL Ones (TAO clock refere If TCLKn is become hig | ansmit Clock for C f 2.048 MHz for trans the device on the fallin Kn high for more th S) state (when MCI nce. low, the correspond h-Z. | hannel 0~7 Ismit is input Ig edges of T an 16 MCLK K is clocked ling transmit in and MCLK Normal op Transmit / Transmit / TCLKn is (\geq 16 TCL The receiv is high, all MCLK is lo | on this pin. The transmit data at TDn/TDPn or TDNn is sam- TCLKn. cycles, the corresponding transmitter is set in Transmit All). In TAOS state, the TAOS generator adopts MCLK as the channel is set into power down state, while driver output ports a result in different transmit mode. It is summarized as the fol- Transmit Mode veration All Ones (TAOS) signals to the line side in the corresponding hannel. sponding transmit channel is set into power down state. clocked Normal operation high Transmit All Ones (TAOS) signals to the line side K1) in the corresponding transmit channel. low Corresponding transmit channel is set into power | | | |

| Nama | Turne | Pin | No. | Description |
|--|-------------|--|--|--|
| Name | Туре | TQFP144 | PBGA160 | Description |
| RD0/RDP0 RD1/RDP1 RD2/RDP2 RD3/RDP3 RD4/RDP4 RD5/RDP5 RD6/RDP6 RD7/RDP7 CV0/RDN0 CV1/RDN1 CV2/RDN2 CV3/RDN3 CV4/RDN4 CV5/RDN5 CV6/RDN6 CV7/RDN7 | O High-Z | 40 33 77 70 111 104 5 142 41 34 76 69 112 105 4 141 | P2 M2 M13 P13 A13 C13 C2 A2 P3 M3 M12 P12 A12 C12 C3 A3 | RDn: Receive Data for Channel 0~7 In Single Rail mode, the received NRZ data is output on this pin. The data is decoded by AMI or HDB3 line code rule. CVn: Code Violation for Channel 0~7 In Single Rail mode, the bipolar violation, code violation and excessive zeros will be reported by driving pin CVn high for a full clock cycle. However, only bipolar violation is indicated when AMI decoder is selected. RDPn/RDNn: Positive/Negative Receive Data for Channel 0~7 In Dual Rail Mode with clock recovery, these pins output the NRZ data. A high signal on RDPn indicates the receipt of a positive pulse on RTIPn/RRINGn while a high signal on RDNn indicates the receipt of a negative pulse on RTIPn/RRINGn. The output data at RDn or RDPn/RDNn are clocked out on the falling edges of RCLK when the CLKE input is low, or are clocked out on the rising edges of RCLK when CLKE is high. In Dual Rail Mode without clock recovery, these pins output the raw RZ sliced data. In this data recovery mode, the active polarity of RDPn/RDNn is determined by pin CLKE. When pin CLKE is low, RDPn/RDNn is active low. When pin CLKE is high, RDPn/RDNn is active high. In hardware mode, RDn or RDPn/RDNn will remain active during LOS. In host mode, these pins will either remain active or insert alarm indication signal (AIS) into the receive path, determined by bit AISE in register GCF. RDn or RDPn/RDNn is set into high-Z when the corresponding receiver is powered down. |
| RCLK0 RCLK1 RCLK2 RCLK3 RCLK4 RCLK5 RCLK6 RCLK7 | O High-Z | 39 32 78 71 110 103 6 143 | P1 M1 P14 A14 C14 C1 A1 | RCLKn: Receive Clock for Channel 0~7 In clock recovery mode, this pin outputs the recovered clock from signal received on RTIPn/RRINGn. The received data are clocked out of the device on the rising edges of RCLKn if pin CLKE is high, or on falling edges of RCLKn if pin CLKE is low. In data recovery mode, RCLKn is the output of an internal exclusive OR (XOR) which is connected with RDPn and RDNn. The clock is recovered from the signal on RCLKn. If Receiver n is powered down, the corresponding RCLKn is in high-Z. |
| MCLK | I | 10 | E1 | MCLK: Master Clock This is an independent, free running reference clock. A clock of 2.048 MHz is supplied to this pin as the clock reference of the device for normal operation. In receive path, when MCLK is high, the device slices the incoming bipolar line signal into RZ pulse (Data Recovery mode). When MCLK is low, all the receivers are powered down, and the output pins RCLKn, RDPn and RDNn are switched to high-Z. In transmit path, the operation mode is decided by the combination of MCLK and TCLKn (see TCLKn pin description for details). NOTE: Wait state generation via RDY/ACK is not available if MCLK is not provided. |
| LOS0 LOS1 LOS2 LOS3 LOS4 LOS5 LOS6 LOS7 | 0 | 42 35 75 68 113 106 3 140 | K4 K3 K12 K11 E11 E12 E3 E4 | LOSn: Loss of Signal Output for Channel 0-7 A high level on this pin indicates the loss of signal when there is no transition over a specified period of time or no enough ones density in the received signal. The transition will return to low automatically when there is enough transitions over a specified period of time with a certain ones density in the received sig- nal. The LOS assertion and desertion criteria are described in 2.3.4 Loss of Signal (LOS) Detection. |

INDUSTRIAL TEMPERATURE RANGES

| | - | Pin | No. | Description | | | | |
|--------------------|-----------------------------|---------|---------|---|--|---|-----------------------------|--|
| Name | Туре | TQFP144 | PBGA160 | | | Description | | |
| | 1 | | | Hardware/Ho | ost Control Inter | face | | |
| | | | | MODE2: Control M | | | | |
| | | | | The signal on this p | in determines wh | ich control mode is selected to control | I the device: | |
| | | | | MODE | E2 | Control Interface | | |
| | | | | Low | 1 | Hardware Mode | | |
| | | | | VDDIC | 0/2 | Serial Host Interface | | |
| | | | | High | า | Parallel Host Interface | | |
| MODE2 | I (Pulled to VDDIO/2) | 11 | E2 | Serial host Interface Parallel host Interface device supports mu | e pins include \overline{CS} ce pins include \overline{C} | E[2:0], LP[7:0], CODE, CLKE, JAS and , SCLK, SDI, SDO and INT. S, A[4:0], D[7:0], WR/DS, RD/R/W, AL t interface as follows (<i>refer to MODE1</i> | _E/AS, INT and RDY/ACK. The | |
| | | | | below for details): | | | | |
| | | | | MODE[2:0] | | Host Interface | | |
| | | | | 100 | | on-multiplexed Motorola Mode Interfac | | |
| | | | | 101 | | Non-multiplexed Intel Mode Interface | | |
| | | | | 110 | | Multiplexed Motorola Mode Interface | | |
| | | | | 111 | | Multiplexed Intel Mode Interface | | |
| MODE0/CODE | I | 88 | H12 | In parallel host mode, the parallel interface operates with separate address bus and data bus when this pin is low, and operates with multiplexed address and data bus when this pin is high. In serial host mode or hardware mode, this pin should be grounded. MODE0: Control Mode Select 0 In parallel host mode, the parallel host interface is configured for Motorola compatible hosts when this pin is low, or for Intel compatible hosts when this pin is high. CODE: Line Code Rule Select In hardware control mode, the HDB3 encoder/decoder is enabled when this pin is low, and AMI encoder/ decoder is enabled when this pin is high. The selections affect all the channels. In serial host mode, this pin should be grounded. | | | | |
| CS /JAS | l (Pulled to VDDIO/2) | 87 | J11 | CS: Chip Select (Active Low) In host mode, this pin is asserted low by the host to enable host interface. A high to low transition to occur on this pin for each read/write operation and the level must not return to high until the operatiover. JAS: Jitter Attenuator Select In hardware control mode, this pin globally determines the Jitter Attenuator position: JAS Jitter Attenuator (JA) Configuration Low JA in transmit path VDDIO/2 JA not used High JA in receive path | | | | |

| | - | Pin | No. | | | | | |
|-------------------------|--------------------|---------|---------|--|--|--|--|--|
| Name | Туре | TQFP144 | PBGA160 | Description | | | | |
| SCLK/ALE/AS | I | 86 | J12 | SCLK: Shift Clock In serial host mode, the signal on this pin is the shift clock for the serial interface. Data on pin SDO is clocked out on falling edges of SCLK if pin CLKE is high, or on rising edges of SCLK if pin CLKE is low. Data on pin SDI is always sampled on rising edges of SCLK. ALE: Address Latch Enable In parallel Intel multiplexed host mode, the address on AD[4:0] is sampled into the device on the falling edges of ALE (signals on AD[7:5] are ignored). In non-multiplexed host mode, ALE should be pulled high. AS: Address Strobe (Active Low) In parallel Motorola multiplexed host mode, the address on AD[4:0] is latched into the device on the falling edges of AS (signals on AD[7:5] are ignored). In non-multiplexed host mode, AS should be pulled high. NOTE: This pin is ignored in hardware control mode. | | | | |
| RD/R/W | I | 85 | J13 | RD: Read Strobe (Active Low) In parallel Intel multiplexed or non-multiplexed host mode, this pin is active low for read operation. R/W: Read/Write Select In parallel Motorola multiplexed or non-multiplexed host mode, the pin is active low for write operation and high for read operation. NOTE: This pin is ignored in hardware control mode. | | | | |
| SDI/WR/DS | I | 84 | J14 | SDI: Serial Data Input In serial host mode, this pin input the data to the serial interface. Data on this pin is sampled on the rising edges of SCLK. \overline{WR} : Write Strobe (Active Low) In parallel Intel host mode, this pin is active low during write operation. The data on D[7:0] (in non-multiplexed mode) or AD[7:0] (in multiplexed mode) is sampled into the device on the rising edges of \overline{WR} . \overline{DS} : Data Strobe (Active Low) In parallel Motorola host mode, this pin is active low. During a write operation ($R/\overline{W} = 0$), the data on D[7:0] (in non-multiplexed mode) or AD[7:0] (in multiplexed mode) is sampled into the device on the rising edges of \overline{DS} . During a read operation ($R/\overline{W} = 1$), the data is driven to D[7:0] (in non-multiplexed mode) or AD[7:0] (in nultiplexed mode) by the device on the rising edges of \overline{DS} . In parallel Motorola non-multiplexed host mode, the address information on the 5 bits of address bus A[4:0] are latched into the device on the falling edges of \overline{DS} . NOTE: This pin is ignored in hardware control mode. | | | | |
| SDO/RDY/ ACK | 0 | 83 | K14 | SDO: Serial Data Output In serial host mode, the data is output on this pin. In serial write operation, SDO is in high impedance for the first 8 SCLK clock cycles and driven low for the remaining 8 SCLK clock cycles. In serial read operation, SDO is in high-Z only when SDI is in address/command byte. Data on pin SDO is clocked out of the device on the falling edges of SCLK if pin CLKE is high, or on the rising edges of SCLK if pin CLKE is low. RDY: Ready Output In parallel Intel host mode, the high level of this pin reports to the host that bus cycle can be completed, while low reports the host must insert wait states. ACK: Acknowledge Output (Active Low) In parallel Motorola host mode, the low level of this pin indicates that valid information on the data bus is ready for a read operation or acknowledges the acceptance of the written data during a write operation. | | | | |
| ĪNT | O Open Drain | 82 | K13 | INT: Interrupt (Active Low) This is an open drain, active low interrupt output. Three sources may cause the interrupt . Refer to 2.18 Interrupt Handling for details. | | | | |

| Nama | Turn | Pin No. | | Description | | | | |
|--|--------|----------------|----------------|---|--|----------------------|--|--|
| Name | Туре | TQFP144 | PBGA160 | Description | | | | |
| | | | | LPn: Loopback Select 7~0 In hardware control mode, pin LPn configures the corresponding channel in different loopback mode, as follows: | | | | |
| | | | | LPn | Loopback Configuration | 7 | | |
| LP7/D7/AD7 | | 28 | K1 | Low | Remote Loopback | | | |
| LP6/D6/AD6 | | 27 | J1 | VDDIO/2 | No loopback | - | | |
| LP5/D5/AD5 | I/O | 26 | J2 | High | Analog Loopback | | | |
| LP4/D4/AD4 | | 25 | J3 | Refer to 2.16 Loopback M | ode for details | | | |
| LP3/D3/AD3 | 11 | 24 | J4 | | | | | |
| LP2/D2/AD2 LP1/D1/AD1 LP0/D0/AD0 | High-Z | 23 22 21 | H2 H3 G2 | | ode, these pins are the bi-directional data bus. | | | |
| | | | | ADn: Address/Data Bus In multiplexed host mode, | 7~0 these pins are the multiplexed bi-directional address/data b | US. | | |
| | | | | In serial host mode, these | pins should be grounded. | | | |
| | | | | In hardware control mode, A4 must be connected to GND. MC[3:0] are used to select one transmitter or receiver of channel 1 to 7 for non-intrusive monitoring. Channel 0 is used as the monitoring channel. If a transmitter is monitored, signals on the corresponding pins TTIPn and TRINGn are internally transmitted to RTIP0 and RRING0. If a receiver is monitored, signals on the corresponding pins RTIPn and RRINGn are internally transmitted to RTIP0 and RRING0. If a receiver is monitored, signals on the corresponding pins RTIPn and RRINGn are internally transmitted to RTIP0 and RRING0. The monitored is then output to RDP0 and RDN0 pins. In host mode operation, the signals monitored by channel 0 can be routed to TTIP0/RING0 by activating the remote loopback in this channel. Refer to 2.19 G.772 Monitoring for more details. Performance Monitor Configuration determined by MC[3:0] is shown below. Note that if MC[2:0] = 000, the device is in normal operation of all the channels. | | | | |
| | | | | | | | | |
| | | | | MC[3:0] | Monitoring Configuration | | | |
| | | | - 4 | 0000 | Normal operation without monitoring Monitor Receiver 1 | | | |
| A4 | | 12 | F4 | 0010 | Monitor Receiver 2 | | | |
| MC3/A3 | | 13 | F3 | 0010 | Monitor Receiver 3 | | | |
| MC2/A2 | I | 14 | F2 | 0100 | Monitor Receiver 4 | | | |
| MC1/A1 | | 15 | F1 | 0101 | Monitor Receiver 5 | | | |
| MC0/A0 | | 16 | G3 | 0110 | Monitor Receiver 6 | | | |
| | | | | 0111 | Monitor Receiver 7 | | | |
| | | | | 1000 | Normal operation without monitoring | | | |
| | | | | 1001 | Monitor Transmitter 1 | | | |
| | | | | 1010 1011 | Monitor Transmitter 2 Monitor Transmitter 3 | | | |
| | | | | 1100 | Monitor Transmitter 4 | | | |
| | | | | 1101 | Monitor Transmitter 5 | | | |
| | | | | 1110 | Monitor Transmitter 6 | | | |
| | | | | 1111 | Monitor Transmitter 7 | | | |
| | | | | | he parallel host interface operates with separate address an n is the address bus of the host interface. | nd data bus. In this | | |
| OE | I | 114 | E14 | | e ve all driver output into high-Z for redundancy application wi condition, all other internal circuits remain active. | ithout external | | |

| | - | Pin | No. | | | | |
|--|--------------|--|--|--|--|--|--|
| Name | Туре | TQFP144 | PBGA160 | Description | | | |
| CLKE | I | 115 | E13 | CLKE: Clock Edge Select The signal on this pin determines the active edge of RCLKn and SCLK in clock recovery mode, or deter- mines the active level of RDPn and RDNn in the data recovery mode. See 2.2 Clock Edges on page 14 for details. | | | |
| | • | | | JTAG Signals | | | |
| TRST | l Pull-up | 95 | G12 | TRST: JTAG Test Port Reset (Active Low) This is the active low asynchronous reset to the JTAG Test Port. This pin has an internal pull-up resistor and it can be left open. | | | |
| TMS | l Pull-up | 96 | F11 | TMS: JTAG Test Mode Select The signal on this pin controls the JTAG test performance and is clocked into the device on the rising edges of TCK. This pin has an internal pull-up resistor and it can be left open. | | | |
| тск | I | 97 | F14 | TCK: JTAG Test Clock This pin input the clock of the JTAG Test. The data on TDI and TMS are clocked into the device on th ing edges of TCK, while the data on TDO is clocked out of the device on the falling edges of TCK. This should be connected to GNDIO or VDDIO pin when unused. | | | |
| TDO | O High-Z | 98 | F13 | TDO: JTAG Test Data Output This pin output the serial data of the JTAG Test. The data on TDO is clocked out of the device on the ing edges of TCK. TDO is a high-Z output signal. It is active only when scanning of data is out. This p should be left float when unused. | | | |
| TDI | l Pull-up | 99 | F12 | TDI: JTAG Test Data Input This pin input the serial data of the JTAG Test. The data on TDI is clocked into the device on the rising edges of TCK. This pin has an internal pull-up resistor and it can be left open. | | | |
| | 1 | | 1 | Power Supplies and Grounds | | | |
| VDDIO | - | 17 92 | G1 G14 | 3.3 V I/O Power Supply | | | |
| GNDIO | - | 18 91 | G4 G11 | I/O GND | | | |
| VDDT0 VDDT1 VDDT2 VDDT3 VDDT4 VDDT5 VDDT6 VDDT7 | - | 44 53 56 65 116 125 128 137 | N4, P4 L4, M4 L11, M11 N11, P11 A11, B11 C11, D11 C4, D4 A4, B4 | 3.3 V/5 V Power Supply for Transmitter Driver All VDDT pins must be connected to 3.3 V or all VDDT must be connected to 5 V. It is not allowed to leave any of the VDDT pins open (not-connected) even if the channel is not used. | | | |
| GNDT0 GNDT1 GNDT2 GNDT3 GNDT4 GNDT5 GNDT6 GNDT7 | - | 47 50 59 62 119 122 131 134 | N6, P6 L6, M6 L9, M9 N9, P9 A9, B9 C9, D9 C6, D6 A6, B6 | Analog GND for Transmitter Driver | | | |
| VDDD VDDA | - | 19 90 | H1 H14 | 3.3 V Digital/Analog Core Power Supply | | | |

INDUSTRIAL TEMPERATURE RANGES

| Name | Туре | Pin No. | | Description | | | |
|-----------------|-------------|----------|------------|---|--|--|--|
| TQFP144 PBGA160 | Description | | | | | | |
| GNDD GNDA | - | 20 89 | H4 H11 | Digital/Analog Core GND | | | |
| | | | | Others | | | |
| IC | 0 | 93 94 | G13 H13 | IC: Internal Connection Internal use. Leave it float for normal operation. | | | |

2 FUNCTIONAL DESCRIPTION

2.1 OVERVIEW

The IDT82V2058 is a fully integrated octal short-haul line interface unit, which contains eight transmit and receive channels for use in E1 applications. The receiver performs clock and data recovery. As an option, the raw sliced data (no retiming) can be output to the system. Transmit equalization is implemented with low-impedance output drivers that provide shaped waveforms to the transformer, guaranteeing template conformance. A selectable jitter attenuator may be placed in the receive path or the transmit path. Moreover, multiple testing functions, such as error detection, loopback and JTAG boundary scan are also provided. The device is optimized for flexible software control through a serial or parallel host mode interface. Hardware control is also available. Figure-1 on page 1 shows one of the eight identical channels operation.

2.1.1 SYSTEM INTERFACE

The system interface of each channel can be configured to operate in different modes:

- 1. Single rail interface with clock recovery.
- 2. Dual rail interface with clock recovery.
- 3. Dual rail interface with data recovery (that is, with raw data slicing only and without clock recovery).


Each signal pin on system side has multiple functions depending on which operation mode the device is in.

The Dual Rail interface consists of TDPn¹, TDNn, TCLKn, RDPn, RDNn and RCLKn. Data transmitted from TDPn and TDNn appears on TTIPn and TRINGn at the line interface; data received from the RTIPn and RRINGn at the line interface are transferred to RDPn and RDNn while the recovered clock extracting from the received data stream outputs on RCLKn. In Dual Rail operation, the clock/data recovery mode is selectable. Dual Rail interface with clock recovery shown in Figure-4 is a default configuration mode. Dual Rail interface with data recovery is shown in Figure-5. Pin RDPn and RDNn, are raw RZ slice outputs and internally connected to an EXOR which is fed to the RCLKn output for external clock recovery applications.

In Single Rail mode, data transmitted from TDn appears on TTIPn and TRINGn at the line interface. Data received from the RTIPn and RRINGn at the line interface appears on RDn while the recovered clock extracting from the received data stream outputs on RCLKn. When the device is in single rail interface, the selectable AMI or HDB3 line encoder/decoder is available and any code violation in the received data will be indicated at the CVn pin. The Single Rail mode has 2 sub-modes: Single Rail Mode 1 and Single Rail Mode 2. Single Rail Mode 1, whose interface is composed of TDn, TCLKn, RDn, CVn and RCLKn, is realized by pulling pin TDNn high for more than 16 consecutive TCLK cycles. Single Rail Mode 2, whose interface is composed of TDn, TCLKn, RDn, CVn, RCLKn and BPVIn, is realized by setting bit CRS in register **e-CRS**² and bit SING in register **e-SING**. The difference between them is that, in the latter mode bipolar violation can be inserted via pin BPVIn if AMI line code is selected.

The configuration of the Hardware Mode System Interface is summarized in Table-2. The configuration of the Host Mode System Interface is summarized in Table-3.

² The first letter 'e-' indicates expanded register.





Note: The grey blocks are bypassed and the dotted blocks are selectable.

Figure-4 Dual Rail Interface with Clock Recovery

INDUSTRIAL TEMPERATURE RANGES

^{1.} The footprint 'n' (n = 0 - 7) indicates one of the eight channels.










Figure-6 Single Rail Mode



| Pin MCLK | Pin TDNn | Interface |
|----------|------------------|--|
| Clocked | High (≥ 16 MCLK) | Single Rail Mode 1 |
| Clocked | Pulse | Dual Rail mode with Clock Recovery |
| High | Pulse | Dual Rail mode with Data Recovery. Receive just slices the incoming data. Transmit is determined by the status of TCLKn. |
| Low | Pulse | Receiver is powered down. Transmit is determined by the status of TCLKn. |

| Pin MCLK | Pin TDNn | CRSn in e-CRS | SINGn in e-SING | Interface |
|----------|----------|---------------|-----------------|--|
| Clocked | High | 0 | 0 | Single Rail Mode 1 |
| Clocked | Pulse | 0 | 1 | Single Rail Mode 2 |
| Clocked | Pulse | 0 | 0 | Dual Rail mode with Clock Recovery |
| Clocked | Pulse | 1 | 0 | Dual Rail mode with Data Recovery. Receive just slices the incoming data. Transmit is determined by the status of TCLKn. |
| High | Pulse | - | - | Dual Rail mode with Data Recovery. Receive just slices the incoming data. Transmit is determined by the status of TCLKn. |
| Low | Pulse | - | - | Receiver is powered down. Transmit is determined by the status of TCLKn. |

Table-3 System Interface Configuration (In Host Mode)

Table-4 Active Clock Edge and Active Level

| Pin CLKE | Pin RDn/F | RDPn and CVn/RD | Nn | Pin SDO | | |
|----------|--------------|-----------------|---------------|---------|-------------|--|
| | Clock Recove | ry | Slicer Output | | | |
| High | RCLKn | Active High | Active High | SCLK | Active High | |
| Low | RCLKn | Active High | Active Low | SCLK | Active High | |

2.2 CLOCK EDGES

The active edge of RCLKn and SCLK are selectable. If pin CLKE is high, the active edge of RCLKn is the rising edge, as for SCLK, that is falling edge. On the contrary, if CLKE is low, the active edge of RCLK is the falling edge and that of SCLK is rising edge. Pins RDn/RDPn, CVn/RDNn and SDO are always active high, and those output signals are clocked out on the active edge of RCLKn and SCLK respectively. See Table-4 Active Clock Edge and Active Level on page 14 for details. However, in dual rail mode without clock recovery, pin CLKE is used to set the active level for RDPn/RDNn raw slicing output: High for active high polarity and low for active low. It should be noted that data on pin SDI are always active high and are sampled on the rising edges of SCLK. The data on pin TDn/TDPn or BPVIn/TDNn are also always active high but are sampled on the falling edges of TCLKn, despite the level on CLKE.

2.3 RECEIVER

In receive path, the line signals couple into RRINGn and RTIPn via a transformer and are converted into RZ digital pulses by a data slicer. Adaptation for attenuation is achieved using an integral peak detector that sets the slicing levels. Clock and data are recovered from the received RZ digital pulses by a digital phase-locked loop that provides jitter accommodation. After passing through the selectable jitter attenuator, the recovered data are decoded using HDB3 or AMI line code rules and clocked out of pin RDn in single rail mode, or presented on RDPn/RDNn in an undecoded dual rail NRZ format. Loss of signal, alarm indication signal, line code violation and excessive zeros are detected. These various changes in status may be enabled to generate interrupts.

2.3.1 PEAK DETECTOR AND SLICER

The slicer determines the presence and polarity of the received pulses. In data recovery mode, the raw positive slicer output appears on RDPn while the negative slicer output appears on RDNn. In clock and data recovery mode, the slicer output is sent to Clock and Data Recovery circuit for abstracting retimed data and optional decoding. The slicer circuit has a built-in peak detector from which the slicing threshold is derived. The slicing threshold is default to 50% (typical) of the peak value.

Signals with an attenuation of up to 12 dB (from 2.4 V) can be recovered by the receiver. To provide immunity from impulsive noise, the peak detectors are held above a minimum level of 0.150 V typically, despite the received signal level.

2.3.2 CLOCK AND DATA RECOVERY

The Clock and Data Recovery is accomplished by Digital Phase Locked Loop (DPLL). The DPLL is clocked 16 times of the received clock rate, i.e. 32.768 MHz in E1 mode. The recovered data and clock from DPLL is then sent to the selectable Jitter Attenuator or decoder for further processing.

The clock recovery and data recovery mode can be selected on a per channel basis by setting bit CRSn in register **e-CRS**. When bit CRSn is defaulted to '0', the corresponding channel operates in data and clock recovery mode. The recovered clock is output on pin RCLKn and retimed NRZ data are output on pin RDPn/RDNn in dual rail mode or on RDn in single rail mode. When bit CRSn is set to '1', dual rail mode with data recovery is enabled in the corresponding channel and the clock recovery is bypassed. In this condition, the analog line signals are converted to RZ digital bit streams on the RDPn/RDNn pins and internally connected to an EXOR which is fed to the RCLKn output for external clock recovery applications.

If MCLK is pulled high, all the receivers will enter the dual rail mode with data recovery. In this case, register **e-CRS** is ignored.

2.3.3 HDB3/AMI LINE CODE RULE

Selectable HDB3 and AMI line coding/decoding is provided when the device is configured in single rail mode. HDB3 rules is enabled by setting bit CODE in register **GCF** to '0' or pulling pin CODE low. AMI rule is enabled by setting bit CODE in register **GCF** to '1' or pulling pin CODE high. The settings affect all eight channels.

Individual line code rule selection for each channel, if needed, is available by setting bit SINGn in register **e-SING** to '1' (to activate bit CODEn in register **e-CODE**) and programming bit CODEn to select line code rules in the corresponding channel: '0' for HDB3, while '1' for AMI. In this case, the value in bit CODE in register **GCF** or pin CODE for global control is unaffected in the corresponding channel and only affect in other channels.

In dual rail mode, the decoder/encoder are bypassed. Bit CODE in register **GCF**, bit CODEn in register **e-CODE** and pin CODE are ignored.

Table-5 Configuration of the Line Code Rule

The configuration of the line code rule is summarized in Table-5.

2.3.4 LOSS OF SIGNAL (LOS) DETECTION

The Loss of Signal Detector monitors the amplitude and density of the received signal on receiver line before the transformer (measured on port A, B shown in Figure-10). The loss condition is reported by pulling pin LOSn high. At the same time, LOS alarm registers track LOS condition. When LOS is detected or cleared, an interrupt will generate if not masked. In host mode, the detection supports ITU G.775 and ETSI 300 233. In hardware mode, it supports the ITU G.775.

Table-6 summarizes the conditions of LOS in clock recovery mode.

During LOS, the RDPn/RDNn continue to output the sliced data when bit AISE in register **GCF** is set to '0' or output all ones as AIS (alarm indication signal) when bit AISE is set to '1'. The RCLKn is replaced by MCLK only if the bit AISE is set.

| Hardware Mode | | | Host Mode | | | | | | |
|---------------|----------------------|--|-------------|-----------------|-----------------|----------------------|--|--|--|
| CODE | Line Code Rule | | CODE in GCF | CODEn in e-CODE | SINGn in e-SING | Line Code Rule | | | |
| | | | 0 | 0/1 | 0 | All channels in HDB3 | | | |
| Low | All channels in HDB3 | | 0 | 0 | 1 | | | | |
| | | | 1 | 0/1 | 0 | All channels in AMI | | | |
| | | | 1 | 1 | 1 | | | | |
| High | All channels in AMI | | 0 | 1 | 1 | CHn in AMI | | | |
| | | | 1 | 0 | 1 | CHn in HDB3 | | | |

Table-6 LOS Condition in Clock Recovery Mode

| | | Standard | | | | | |
|----------------|--------------------------|--|--|--------|--|--|--|
| | | G.775 | ETSI 300 233 | LOSn | | | |
| LOS | Continuous Intervals | 32 | 2048 (1 ms) | High | | | |
| Detected | Amplitude ⁽¹⁾ | below typical 200 mVp | below typical 200 mVp | riigii | | | |
| LOS Cleared | Density | 12.5% (4 marks in a sliding 32-bit period) with no more than 15 continuous zeros | 12.5% (4 marks in a sliding 32-bit period) with no more than 15 continuous zeros | Low | | | |
| | Amplitude ⁽¹⁾ | exceed typical 250 mVp | exceed typical 250 mVp | | | | |

^{1.} LOS levels at device (RTIPn, RRINGn) with all ones signal. For more detail regarding the LOS parameters, please refer to Receiver Characteristics on page 42.

2.3.5 ALARM INDICATION SIGNAL (AIS) DETECTION

Alarm Indication Signal is available only in host mode with clock recovery, as shown in Table-7.

2.3.6 ERROR DETECTION

The device can detect excessive zeros, bipolar violation and HDB3 code violation, as shown in Figure-7 and Figure-8. All the three kinds of errors are reported in both host mode and hardware mode with HDB3 line code rule used. In host mode, the **e-CZER** and **e-CODV** are used to

determine whether excessive zeros and code violation are reported respectively. When the device is configured in AMI decoding mode, only bipolar violation can be reported.

The error detection is available only in single rail mode in which the pin CVn/RDNn is used as error report output (CVn pin).

The configuration and report status of error detection are summarized in Table-8.

Table-7 AIS Condition

| | ITU G.775 (Register LAC defaulted to '0') | ETSI 300 233 (Register LAC set to '1') |
|--------------|--|--|
| AIS Detected | Less than 3 zeros contained in each of two consecutive 512-bit stream are received | Less than 3 zeros contained in a 512-bit stream are received |
| AIS Cleared | 3 or more zeros contained in each of two consecutive 512-bit stream are received | 3 or more zeros contained in a 512-bit stream are received |

INDUSTRIAL TEMPERATURE RANGES

Table-8 Error Detection

| Ha | | |
|-----------|--|----|
| Line Code | Pin CVn Reports | Li |
| AMI | Bipolar Violation | |
| HDB3 | Bipolar Violation + Code Violation + Excessive Zeros | |

| | Host Mode | | | | | | | | | | | |
|-----------|-----------------|-----------------|--|--|--|--|--|--|--|--|--|--|
| Line Code | CODVn in e-CODV | CZERn in e-CZER | Pin CVn Reports | | | | | | | | | |
| AMI | - | - | Bipolar Violation | | | | | | | | | |
| | 0 | 0 | Bipolar Violation + Code Violation | | | | | | | | | |
| HDB3 | 0 | 1 | Bipolar Violation + Code Violation + Excessive Zeros | | | | | | | | | |
| TIDDS | 1 | 0 | Bipolar Violation | | | | | | | | | |
| | 1 | 1 | Bipolar Violation + Excessive Zeros | | | | | | | | | |




Figure-7 AMI Bipolar Violation




Figure-8 HDB3 Code Violation & Excessive Zeros

2.4 TRANSMITTER

In transmit path, data in NRZ format are clocked into the device on TDn and encoded by AMI or HDB3 line code rules when single rail mode is configured or pre-encoded data in NRZ format are input on TDPn and TDNn when dual rail mode is configured. The data are sampled into the device on falling edges of TCLKn. Jitter attenuator, if enabled, is

provided with a FIFO through which the data to be transmitted are passing. A low jitter clock is generated by an integral digital phaselocked loop and is used to read data from the FIFO. The shape of the pulses should meet the E1 pulse template after the signal passes through different cable lengths or types. Bipolar violation, for diagnosis, can be inserted on pin BPVIn if AMI line code rule is enabled.

INDUSTRIAL TEMPERATURE RANGES

2.4.1 WAVEFORM SHAPER

E1 pulse template, specified in ITU-T G.703, is shown in Figure-9. The device has built-in transmit waveform templates for cable of 75 Ω or 120 Ω .

The built-in waveform shaper uses an internal high frequency clock which is 16XMCLK as the clock reference. This function will be bypassed when MCLK is unavailable.




Figure-9 CEPT Waveform Template

2.4.2 BIPOLAR VIOLATION INSERTION

When configured in Single Rail Mode 2 with AMI line code enabled, pin TDNn/BPVIn is used as BPVI input. A low-to-high transition on this pin inserts a bipolar violation on the next available mark in the transmit data stream. Sampling occurs on the falling edges of TCLK. But in TAOS (Transmit All Ones) with Analog Loopback and Remote Loopback, the BPVI is disabled. In TAOS with Digital Loopback, the BPVI is looped back to the system side, so the data to be transmitted on TTIPn and TRINGn are all ones with no bipolar violation.

2.5 JITTER ATTENUATOR

The jitter attenuator can be selected to work either in transmit path or in receive path or not used. The selection is accomplished by setting pin JAS in hardware mode or configuring bits JACF[1:0] in register **GCF** in host mode, which affects all eight channels.

For applications which require line synchronization, the line clock needed to be extracted for the internal synchronization, the jitter attenuator is set in the receive path. Another use of the jitter attenuator is to provide clock smoothing in the transmit path for applications such as synchronous/asynchronous demultiplexing applications. In these applications, TCLK will have an instantaneous frequency that is higher than the nominal E1 data rate and in order to set the average long-term TCLK frequency within the transmit line rate specifications, periods of TCLK are suppressed (gapped).

The jitter attenuator integrates a FIFO which can accommodate a gapped TCLK. In host mode, the FIFO length can be 32 X 2 or 64 X 2 bits by programming bit JADP in **GCF**. In hardware mode, it is fixed to 64 X 2 bits. The FIFO length determines the maximum permissible gap width (see Table-9 Gap Width Limitation). Exceeding these values will cause FIFO overflow or underflow. The data is 16 or 32 bits' delay through the jitter attenuator in the corresponding transmit or receive path. The constant delay feature is crucial for the applications requiring "hitless" switching.

Table-9 Gap Width Limitation

| FIFO Length | Max. Gap Width |
|-------------|----------------|
| 64 bit | 56 UI |
| 32 bit | 28 UI |

In host mode, bit JABW in GCF determines the jitter attenuator 3 dB corner frequency (fc). In hardware mode, the fc is fixed to 1.7 Hz. Generally, the lower the fc is, the higher the attenuation. However, lower fc comes at the expense of increased acquisition time. Therefore, the optimum fc is to optimize both the attenuation and the acquisition time. In addition, the longer FIFO length results in an increased throughput delay and also influences the 3 dB corner frequency. Generally, it's recommended to use the lower corner frequency and the shortest FIFO length that can still meet jitter attenuation requirements.


The output jitter meets ITU-T G.736, ITU-T G.742, ITU-T G.783 and ETSI CTR 12/13.

2.6 LINE INTERFACE CIRCUITRY

The transmit and receive interface RTIPn/RRINGn and TTIPn/ TRINGn connections provide a matched interface to the cable. Figure-10 shows the appropriate external components to connect with the cable for one transmit/receive channel. Table-10 summarizes the component values based on the specific application.

Table-10 External Components Values

| Component | 75 Ω Coax | 120 Ω Twisted Pair |
|----------------|--|--|
| R _T | $9.5\Omega\pm1\%$ | $9.5\Omega\pm1\%$ |
| R _R | 9.31 $\Omega\pm$ 1% | $15\Omega\pm1\%$ |
| Ср | 220 | 00 pF |
| D1 - D4 | Nihon Inter Electronics - EP05 E0 Motorola - MBR0540T1 | Q03L, 11EQS03L, C10QS04, EC10QS03L; |



NOTE:

1. Pulse T1124 transformer is recommended to be used in Standard (STD) operating temperature range (0°C to 70°C), while Pulse T1114 transformer is recommended to be used in Extended (EXT) operating temperature range is -40°C to +85°C. See Transformer Specifications Table for details.

2. Typical value. Adjust for actual board parasitics to obtain optimum return loss.

3. Common decoupling capacitor for all VDDT and GNDT pins. One per chip.

Figure-10 External Transmit/Receive Line Circuitry

2.7 TRANSMIT DRIVER POWER SUPPLY

All transmit driver power supplies must be 5.0 V or 3.3 V.

Despite the power supply voltage, the 75 Ω /120 Ω lines are driven through a pair of 9.5 Ω series resistors and a 1:2 transformer.

Table-11 Transformer Specifications⁽¹⁾

| | Electrical Specification @ 25°C | | | | | | | | | | | | | |
|-----------|---------------------------------|-----------------------------|---------|---------------------|---------|------------------------|---------|---------------------------|---------|--------------------|--|--|--|--|
| Part No. | | Turns Ratio (Pri: sec ± 2%) | | OCL @ 25°C (mH MIN) | | L_{L} (μ H MAX) | | C _{w/w} (pF MAX) | | Package/Schematic | | | | |
| STD Temp. | EXT Temp. | Transmit | Receive | Transmit | Receive | Transmit | Receive | Transmit | Receive | r dokage/oonematie | | | | |
| T1124 | T1114 | 1:2CT | 1CT:2 | 1.2 | 1.2 | .6 | .6 | 35 | 35 | TOU/3 | | | | |

^{1.} Pulse T1124 transformer is recommended to be used in Standard (STD) operating temperature range (0°C to 70°C), while Pulse T1114 transformer is recommended to be used in Extended (EXT) operating temperature range is -40°C to +85°C.

2.8 POWER DRIVER FAILURE MONITOR

An internal power Driver Failure Monitor (DFMON), parallel connected with TTIPn and TRINGn, can detect short circuit failure between TTIPn and TRINGn pins. Bit SCPB in register **GCF** decides whether the output driver short circuit protection is enabled. When the short circuit protection is enabled, the driver output current is limited to a typical value: 180 mAp. Also, register **DF**, **DFI** and **DFM** will be available. When DFMON will detect a short circuit, register **DF** will be set. With a short circuit failure detected and short circuit protection enabled, register **DFI** will be set and an interrupt will be generated on pin INT.

2.9 TRANSMIT LINE SIDE SHORT CIRCUIT FAILURE DETECTION

A pair of 9.5 Ω serial resistors connect with TTIPn and TRINGn pins and limit the output current. In this case, the output current is a limited value which is always lower than the typical line short circuit current 180 mAp, even if the transmit line side is shorted.

Refer to Table-10 External Components Values for details.

2.10 LINE PROTECTION

In transmit side, the Schottky diodes D1~D4 are required to protect the line driver and improve the design robustness. In receive side, the series resistors of 1 k Ω are used to protect the receiver against current surges coupled in the device. The series resistors do not affect the receiver sensitivity, since the receiver impedance is as high as 120 k Ω typically.

2.11 HITLESS PROTECTION SWITCHING (HPS)

The IDT82V2058 transceivers include an output driver with high-Z feature for E1 redundancy applications. This feature reduces the cost of redundancy protection by eliminating external relays. Details of HPS are described in relative Application Note.

2.12 SOFTWARE RESET

Writing register **RS** will cause software reset by initiating about 1 μ s reset cycle. This operation set all the registers to their default value.

2.13 POWER ON RESET

During power up, an internal reset signal sets all the registers to default values. The power-on reset takes at least 10 μ s, starting from when the power supply exceeds 2/3 VDDA.

2.14 POWER DOWN

Each transmit channel will be powered down by pulling pin TCLKn low for more than 64 MCLK cycles (if MCLK is available) or about 30 μ s (if MCLK is not available). In host mode, each transmit channel will also be powered down by setting bit TPDNn in register **e-TPDN** to '1'.

All the receivers will be powered down when MCLK is low. When MCLK is clocked or high, setting bit RPDNn in register **e-RPDN** to '1' will configure the corresponding receiver to be powered down.

2.15 INTERFACE WITH 5 V LOGIC

The IDT82V2058 can interface directly with 5 V TTL family devices. The internal input pads are tolerant to 5 V output from TTL and CMOS family devices.

2.16 LOOPBACK MODE

The device provides four different diagnostic loopback configurations: Digital Loopback, Analog Loopback, Remote Loopback and Dual Loopback. In host mode, these functions are implemented by programming the registers **DLB**, **ALB** and **RLB** respectively. In hardware mode, only Analog Loopback and Remote Loopback can be selected by pin LPn.

2.16.1 DIGITAL LOOPBACK

By programming the bits of register **DLB**, each channel of the device can be configured in Local Digital Loopback. In this configuration, the data and clock to be transmitted, after passing the encoder, are looped back to Jitter Attenuator (if enabled) and decoder in the receive path, then output on RCLKn, RDn/RDPn and CVn/RDNn. The data to be transmitted are still output on TTIPn and TRINGn while the data received on RTIPn and RRINGn are ignored. The Loss Detector is still in use. Figure-11 shows the process. During Digital Loopback, the received signal on the receive line is still monitored by the LOS Detector (See 2.3.4 Loss of Signal (LOS) Detection for details). In case of a LOS condition and AIS insertion enabled, all ones signal will be output on RDPn/RDNn. With ATAO enabled, all ones signal will be also output on TTIPn/TRINGn. AIS insertion can be enabled by setting AISE bit in register **GCF** and ATAO can be enabled by setting register **ATAO** (default disabled).

2.16.2 ANALOG LOOPBACK

By programming the bits of register **ALB** or pulling pin LPn high, each channel of the device can be configured in Analog Loopback. In this configuration, the data to be transmitted output from the line driver are internally looped back to the slicer and peak detector in the receive path and output on RCLKn, RDn/RDPn and CVn/RDNn. The data to be transmitted are still output on TTIPn and TRINGn while the data received on RTIPn and RRINGn are ignored. The LOS Detector (See 2.3.4 Loss of Signal (LOS) Detection for details) is still in use and monitors the internal looped back data. If a LOS condition on TDPn/TDNn is expected during Analog Loopback, ATAO should be disabled (default). Figure-12 shows the process.

The TTIPn and RTIPn, TRINGn and RRINGn cannot be connected directly to do the external analog loopback test. Line impedance loading is required to conduct the external analog loopback test.

2.16.3 REMOTE LOOPBACK

By programming the bits of register **RLB** or pulling pin LPn low, each channel of the device can be set in Remote Loopback. In this configuration, the data and clock recovered by the clock and data recovery circuits are looped to waveform shaper and output on TTIPn and TRINGn. The jitter attenuator is also included in loopback when enabled in the transmit or receive path. The received data and clock are still output on RCLKn, RDn/RDPn and CVn/RDNn while the data to be transmitted on TCLKn, TDn/TDPn and BPVIn/TDNn are ignored. The LOs Detector is still in use. Figure-13 shows the process.

2.16.4 DUAL LOOPBACK

Dual Loopback mode is set by setting bit DLBn in register **DLB** and bit RLBn in register **RLB** to '1'. In this configuration, after passing the encoder, the data and clock to be transmitted are looped back to decoder directly and output on RCLKn, RDn/RDPn and CVn/RDNn. The recovered data from RTIPn and RRINGn are looped back to waveform shaper through JA (if selected) and output on TTIPn and TRINGn. The LOS Detector is still in use. Figure-14 shows the process.

2.16.5 TRANSMIT ALL ONES (TAOS)

In hardware mode, the TAOS mode is set by pulling pin TCLKn high for more than 16 MCLK cycles. In host mode, TAOS mode is set by programming register **TAO**. In addition, automatic TAOS signals are inserted by setting register **ATAO** when Loss of Signal occurs. Note that the TAOS generator adopts MCLK as a timing reference. In order to assure that the output frequency is within specified limits, MCLK must have the applicable stability.

The TAOS mode, the TAOS mode with Digital Loopback and the TAOS mode with Analog Loopback are shown in Figure-15, Figure-16 and Figure-17.

INDUSTRIAL TEMPERATURE RANGES




Figure-11 Digital Loopback




Figure-12 Analog Loopback




Figure-13 Remote Loopback






Figure-14 Dual Loopback












Figure-17 TAOS with Analog Loopback


2.17 HOST INTERFACE

The host interface provides access to read and write the registers in the device. The interface consists of serial host interface and parallel host interface. By pulling pin MODE2 to VDDIO/2 or high, the device can be set to work in serial mode and in parallel mode respectively.

2.17.1 PARALLEL HOST INTERFACE

The interface is compatible with Motorola and Intel host. Pins MODE1 and MODE0 are used to select the operating mode of the parallel host interface. When pin MODE1 is pulled low, the host uses separate address bus and data bus. When high, multiplexed address/ data bus is used. When pin MODE0 is pulled low, the parallel host interface is configured for Motorola compatible hosts. When pin MODE0 is pulled high, the parallel host interface is configured for Intel compatible hosts. See Table-1 Pin Description for more details. The host interface pins in each operation mode is tabulated in Table-12:

MODE[2:0] Host Interface Generic Control, Data and Output Pin 100 Non-multiplexed Motorola interface CS, ACK, DS, R/W, AS, A[4:0], D[7:0], INT 101 Non-multiplexed Intel interface CS, RDY, WR, RD, ALE, A[4:0], D[7:0], INT 110 Multiplexed Motorola interface CS, ACK, DS, R/W, AS, AD[7:0], INT 111 Multiplexed Intel interface CS, RDY, WR, RD, ALE, AD[7:0], INT



2. Ignored.

Figure-18 Serial Host Mode Timing

2.17.2 SERIAL HOST INTERFACE

By pulling pin MODE2 to VDDIO/2, the device operates in the serial host Mode. In this mode, the registers are accessible through a 16-bit word which contains an 8-bit command/address byte (bit R/W and 5-address-bit A1~A5, A6 and A7 bits are ignored) and a subsequent 8-bit

data byte (D7~D0), as shown in Figure-18. When bit R/\overline{W} is set to '1', data is read out from pin SDO. When bit R/\overline{W} is set to '0', data on pin SDI is written into the register whose address is indicated by address bits A5~A1. See Figure-18 Serial Host Mode Timing.

Table-12 Parallel Host Interface Pins

INDUSTRIAL TEMPERATURE RANGES

2.18 INTERRUPT HANDLING

2.18.1 INTERRUPT SOURCES

There are three kinds of interrupt sources:

- Status change in register LOS. The analog/digital loss of signal detector continuously monitors the received signal to update the specific bit in register LOS which indicates presence or absence of a LOS condition.
- Status change in register DF. The automatic power driver circuit continuously monitors the output drivers signal to update the specific bit in register DFM which indicates presence or absence of an output driver short circuit condition.
- Status change in register AIS. The AIS detector monitors the received signal to update the specific bit in register AIS which indicates presence or absence of a AIS condition.




Figure-19 Interrupt Service Routine

2.18.2 INTERRUPT ENABLE

The IDT82V2058 provides a latched interrupt output (INT) and the four kinds of interrupts are all reported by this pin. When the Interrupt Mask register (**LOSM**, **DFM** and **AISM**) is set to '1', the Interrupt Status register (**LOSI**, **DFI** and **AISI**) is enabled respectively. Whenever there is a transition ('0' to '1' or '1' to '0') in the corresponding status register, the Interrupt Status register will change into '1', which means an interrupt occurs, and there will be a high to low transition on INT pin. An external pull-up resistor of approximately 10 k Ω is required to support the wire-OR operation of INT. When any of the three Interrupt Mask registers is set to '0' (the power-on default value is '0'), the corresponding Interrupt Status register is disabled and the transition on status register is ignored.

2.18.3 INTERRUPT CLEARING

When an interrupt occurs, the Interrupt Status registers: LOSI, DFI and AISI, are read to identify the interrupt source. These registers will be cleared to '0' after the corresponding status registers: LOS, DF and AIS are read. The Status registers will be cleared once the corresponding conditions are met.

Pin INT is pulled high when there is no pending interrupt left. The interrupt handling in the interrupt service routine is showed in Figure-19.

2.19 G.772 MONITORING

The eight channels of IDT82V2058 can all be configured to work as regular transceivers. In applications using only seven channels (channels 1 to 7), channel 0 is configured to non-intrusively monitor any of the other channels' inputs or outputs on the line side. The monitoring is non-intrusive per ITU-T G.772. Figure-20 shows the Monitoring Principle. The receiver path or transmitter path to be monitored is configured by pins MC[3:0] in hardware mode or by register **PMON** in host mode.

The monitored signal goes through the clock and data recovery circuit of channel 0. The monitored clock can output on RCLK0 which can be used as a timing interfaces derived from E1 signal. The monitored data can be observed digitally at the output pins RCLK0, RD0/RDP0 and RDN0. LOS detector is still in use in channel 0 for the monitored signal.

In monitoring mode, channel 0 can be configured in Remote Loopback. The signal which is being monitored will output on TTIP0 and TRING0. The output signal can then be connected to a standard test equipment with an E1 electrical interface for non-intrusive monitoring.




Figure-20 Monitoring Principle

INDUSTRIAL TEMPERATURE RANGES

3 PROGRAMMING INFORMATION

3.1 REGISTER LIST AND MAP

There are 21 primary registers (including an Address Pointer Control Register and 8 expanded registers in the device).

Whatever the control interface is, 5 address bits are used to set the registers. In non-multiplexed parallel interface mode, the five dedicated address bits are A[4:0]. In multiplexed parallel interface mode, AD[4:0] carries the address information. In serial interface mode, A[5:1] are used to address the register.

Table-13 Primary Register List

The Register **ADDP**, addressed as 11111 or 1F Hex, switches between primary registers bank and expanded registers bank.

By setting the register **ADDP** to 'AAH', the 5 address bits point to the expanded register bank, that is, the expanded registers are available. By clearing register **ADDP**, the primary registers are available.

Primary Registers, whose addresses are 10H, 11H, 16H to 1EH, are reserved. Expanded registers, whose addresses are 08H to 1EH, are used for test and must be set to '0' (default).

| | Addres | s | Deviator | DAA | Freelansten | | | |
|-----|------------------------|--------------------------|----------|-----|---|--|--|--|
| Hex | Serial Interface A7-A1 | Parallel Interface A7-A0 | Register | R/W | Explanation | | | |
| 00 | XX00000 | XXX00000 | ID | R | Device ID Register | | | |
| 01 | XX00001 | XXX00001 | ALB | R/W | Analog Loopback Configuration Register | | | |
| 02 | XX00010 | XXX00010 | RLB | R/W | Remote Loopback Configuration Register | | | |
| 03 | XX00011 | XXX00011 | TAO | R/W | Transmit All Ones Configuration Register | | | |
| 04 | XX00100 | XXX00100 | LOS | R | Loss of Signal Status Register | | | |
| 05 | XX00101 | XXX00101 | DF | R | Driver Fault Status Register | | | |
| 06 | XX00110 | XXX00110 | LOSM | R/W | LOS Interrupt Mask Register | | | |
| 07 | XX00111 | XXX00111 | DFM | R/W | Driver Fault Interrupt Mask Register | | | |
| 08 | XX01000 | XXX01000 | LOSI | R | LOS Interrupt Status Register | | | |
| 09 | XX01001 | XXX01001 | DFI | R | Driver Fault Interrupt Status Register | | | |
| 0A | XX01010 | XXX01010 | RS | W | Software Reset Register | | | |
| 0B | XX01011 | XXX01011 | PMON | R/W | Performance Monitor Configuration Register | | | |
| 0C | XX01100 | XXX01100 | DLB | R/W | Digital Loopback Configuration Register | | | |
| 0D | XX01101 | XXX01101 | LAC | R/W | LOS/AIS Criteria Configuration Register | | | |
| 0E | XX01110 | XXX01110 | ATAO | R/W | Automatic TAOS Configuration Register | | | |
| 0F | XX01111 | XXX01111 | GCF | R/W | Global Configuration Register | | | |
| 10 | XX10000 | XXX10000 | | | Reserved | | | |
| 11 | XX10001 | XXX10001 | | | | | | |
| 12 | XX10010 | XXX10010 | OE | R/W | Output Enable Configuration Register | | | |
| 13 | XX10011 | XXX10011 | AIS | R | AIS Status Register | | | |
| 14 | XX10100 | XXX10100 | AISM | R/W | AIS Interrupt Mask Register | | | |
| 15 | XX10101 | XXX10101 | AISI | R | AIS Interrupt Status Register | | | |
| 16 | XX10110 | XXX10110 | | | | | | |
| 17 | XX10111 | XXX10111 | | | | | | |
| 18 | XX11000 | XXX11000 | | | | | | |
| 19 | XX11001 | XXX11001 | | | | | | |
| 1A | XX11010 | XXX11010 | | | Reserved | | | |
| 1B | XX11011 | XXX11011 | | | | | | |
| 1C | XX11100 | XXX11100 | | | | | | |
| 1D | XX11101 | XXX11101 | | | | | | |
| 1E | XX11110 | XXX11110 | | | | | | |
| 1F | XX11111 | XXX11111 | ADDP | R/W | Address pointer control Register for switching between primary register bank and expanded register bank | | | |

Table-14 Expanded (Indirect Address Mode) Register List

| | Addre | SS | Register | R/W | Explanation | | | | |
|----------|------------------------|--------------------------|----------|--|---|--|--|--|--|
| Hex | Serial Interface A7-A1 | Parallel Interface A7-A0 | regiotei | | Explanation | | | | |
| 00 | XX00000 | XXX00000 | e-SING | R/W | Single Rail Mode Setting Register | | | | |
| 01 | XX00001 | XXX00001 | e-CODE | R/W Encoder/Decoder Selection Register | | | | | |
| 02 | XX00010 | XXX00010 | e-CRS | R/W | Clock Recovery Enable/Disable Register | | | | |
| 03 | XX00011 | XXX00011 | e-RPDN | R/W | Receiver n Powerdown Enable/Disable Register | | | | |
| 04 | XX00100 | XXX00100 | e-TPDN | R/W | Transmitter n Powerdown Enable/Disable Register | | | | |
| 05 | XX00101 | XXX00101 | e-CZER | R/W | Consecutive Zero Detect Enable/Disable Register | | | | |
| 06 | XX00110 | XXX00110 | e-CODV | R/W | Code Violation Detect Enable/Disable Register | | | | |
| 07 | XX00111 | XXX00111 | e-EQUA | R/W | Enable Equalizer Enable/Disable Register | | | | |
| 08 | XX01000 | XXX01000 | | | | | | | |
| 09 | XX01001 | XXX01001 | | | | | | | |
| 0A | XX01010 | XXX01010 | | | | | | | |
| 0B | XX01011 | XXX01011 | | | | | | | |
| 0C | XX01100 | XXX01100 | | | | | | | |
| 0D | XX01101 | XXX01101 | | | | | | | |
| 0E | XX01110 | XXX01110 | | | | | | | |
| 0F | XX01111 | XXX01111 | | | | | | | |
| 10 | XX10000 | XXX10000 | | | | | | | |
| 11 | XX10001 | XXX10001 | | | | | | | |
| 12 | XX10010 | XXX10010 | | | T 1 | | | | |
| 13 14 | XX10011 XX10100 | XXX10011 XXX10100 | | | Test | | | | |
| 14 | XX10100 XX10101 | XXX10100 XXX10101 | | | | | | | |
| 16 | XX10101 XX10110 | XXX10101 XXX10110 | | | | | | | |
| 17 | XX10110 XX10111 | XXX10110 XXX10111 | | | | | | | |
| 18 | XX10111 XX11000 | XXX10111 XXX11000 | | | | | | | |
| 19 | XX11000 | XXX11000 | | | | | | | |
| 1Ă | XX11010 | XXX11010 | | | | | | | |
| 1B | XX11011 | XXX11011 | | | | | | | |
| 10 | XX11100 | XXX11100 | | | | | | | |
| 1D | XX11101 | XXX11101 | | | | | | | |
| 1E | XX11110 | XXX11110 | | | | | | | |
| 1F | XX11111 | XXX11111 | ADDP | R/W | Address pointer control register for switching between primary register bank and expanded register bank | | | | |

Table-15 Primary Register Map

| Register | Address R/W Default | Bit 7 | Bit 6 | Bit 5 | Bit 4 | Bit 3 | Bit 2 | Bit 1 | Bit 0 |
|----------|---------------------------|--------|--------|--------|--------|--------|--------|--------|--------|
| ID | 00H | ID 7 | ID 6 | ID 5 | ID 4 | ID 3 | ID 2 | ID 1 | ID 0 |
| | R | R | R | R | R | R | R | R | R |
| | Default | 0 | 0 | 0 | 1 | 0 | 0 | 0 | 0 |
| ALB | 01H | ALB 7 | ALB 6 | ALB 5 | ALB 4 | ALB 3 | ALB 2 | ALB 1 | ALB 0 |
| | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W |
| | Default | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
| RLB | 02H | RLB 7 | RLB 6 | RLB 5 | RLB 4 | RLB 3 | RLB 2 | RLB 1 | RLB 0 |
| | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W |
| | Default | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
| TAO | 03H | TAO 7 | TAO 6 | TAO 5 | TAO 4 | TAO 3 | TAO 2 | TAO 1 | TAO 0 |
| | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W |
| | Default | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
| LOS | 04H | LOS 7 | LOS 6 | LOS 5 | LOS 4 | LOS 3 | LOS 2 | LOS 1 | LOS 0 |
| | R | R | R | R | R | R | R | R | R |
| | Default | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
| DF | 05H | DF 7 | DF 6 | DF 5 | DF 4 | DF 3 | DF 2 | DF 1 | DF 0 |
| | R | R | R | R | R | R | R | R | R |
| | Default | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
| LOSM | 06H | LOSM 7 | LOSM 6 | LOSM 5 | LOSM 4 | LOSM 3 | LOSM 2 | LOSM 1 | LOSM 0 |
| | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W |
| | Default | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
| DFM | 07H | DFM 7 | DFM 6 | DFM 5 | DFM 4 | DFM 3 | DFM 2 | DFM 1 | DFM 0 |
| | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W |
| | Default | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
| LOSI | 08H | LOSI 7 | LOSI 6 | LOSI 5 | LOSI 4 | LOSI 3 | LOSI 2 | LOSI 1 | LOSI 0 |
| | R | R | R | R | R | R | R | R | R |
| | Default | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
| DFI | 09H | DFI 7 | DFI 6 | DFI 5 | DFI 4 | DFI 3 | DFI 2 | DFI 1 | DFI 0 |
| | R | R | R | R | R | R | R | R | R |
| | Default | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
| RS | 0AH | RS 7 | RS 6 | RS 5 | RS 4 | RS 3 | RS 2 | RS 1 | RS 0 |
| | W | W | W | W | W | W | W | W | W |
| | Default | 1 | 1 | 1 | 1 | 1 | 1 | 1 | 1 |
| PMON | 0BH | - | - | - | - | MC 3 | MC 2 | MC 1 | MC 0 |
| | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W |
| | Default | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
| DLB | 0CH | DLB 7 | DLB 6 | DLB 5 | DLB 4 | DLB 3 | DLB 2 | DLB 1 | DLB 0 |
| | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W |
| | Default | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
| LAC | 0DH | LAC 7 | LAC 6 | LAC 5 | LAC 4 | LAC 3 | LAC 2 | LAC 1 | LAC 0 |
| | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W |
| | Default | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
| ATAO | 0EH | ATAO 7 | ATAO 6 | ATAO 5 | ATAO 4 | ATAO 3 | ATAO 2 | ATAO 1 | ATAO 0 |
| | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W |
| | Default | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
| GCF | 0FH | - | AISE | SCPB | CODE | JADP | JABW | JACF 1 | JACF 0 |
| | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W |
| | Default | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |

| Register | Address R/W Default | Bit 7 | Bit 6 | Bit 5 | Bit 4 | Bit 3 | Bit 2 | Bit 1 | Bit 0 |
|----------|---------------------------|--------|--------|--------|--------|--------|--------|--------|--------|
| OE | 12 Hex | OE 7 | OE 6 | OE 5 | OE 4 | OE 3 | OE 2 | OE 1 | OE 0 |
| | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W |
| | Default | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
| AIS | 13 Hex | AIS 7 | AIS 6 | AIS 5 | AIS 4 | AIS 3 | AIS 2 | AIS 1 | AIS 0 |
| | R | R | R | R | R | R | R | R | R |
| | Default | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
| AISM | 14 Hex | AISM 7 | AISM 6 | AISM 5 | AISM 4 | AISM 3 | AISM 2 | AISM 1 | AISM 0 |
| | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W |
| | Default | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
| AISI | 15 Hex | AISI 7 | AISI 6 | AISI 5 | AISI 4 | AISI 3 | AISI 2 | AISI 1 | AISI 0 |
| | R | R | R | R | R | R | R | R | R |
| | Default | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
| ADDP | 1F Hex | ADDP 7 | ADDP 6 | ADDP 5 | ADDP 4 | ADDP 3 | ADDP 2 | ADDP 1 | ADDP 0 |
| | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W |
| | Default | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |

Table-15 Primary Register Map (Continued)

Table-16 Expanded (Indirect Address Mode) Register Map

| Register | Address R/W Default | Bit 7 | Bit 6 | Bit 5 | Bit 4 | Bit 3 | Bit 2 | Bit 1 | Bit 0 |
|----------|---------------------------|--------------------|--------------------|--------------------|--------------------|--------------------|--------------------|-----------------|--------------------|
| e-SING | 00H | SING 7 | SING 6 | SING 5 | SING 4 | SING 3 | SING 2 | SING 1 | SING 0 |
| | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W |
| | Default | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
| e-CODE | 01H R/W Default | CODE 7 R/W 0 | CODE 6 R/W 0 | CODE 5 R/W 0 | CODE 4 R/W 0 | CODE 3 R/W 0 | CODE 2 R/W 0 | CODE 1 R/W 0 | CODE 0 R/W 0 |
| e-CRS | 02H | CRS 7 | CRS 6 | CRS 5 | CRS 4 | CRS 3 | CRS 2 | CRS 1 | CRS 0 |
| | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W |
| | Default | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
| e-RPDN | 03H | RPDN 7 | RPDN 6 | RPDN 5 | RPDN 4 | RPDN 3 | RPDN 2 | RPDN 1 | RPDN 0 |
| | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W |
| | Default | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
| e-TPDN | 04H | TPDN 7 | TPDN 6 | TPDN 5 | TPDN 4 | TPDN 3 | TPDN 2 | TPDN 1 | TPDN 0 |
| | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W |
| | Default | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
| e-CZER | 05H | CZER 7 | CZER 6 | CZER 5 | CZER 4 | CZER 3 | CZER 2 | CZER 1 | CZER 0 |
| | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W |
| | Default | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
| e-CODV | 06H | CODV 7 | CODV 6 | CODV 5 | CODV 4 | CODV 3 | CODV 2 | CODV 1 | CODV 0 |
| | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W |
| | Default | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
| e-EQUA | 07H | EQUA 7 | EQUA 6 | EQUA 5 | EQUA 4 | EQUA 3 | EQUA 2 | EQUA 1 | EQUA 0 |
| | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W |
| | Default | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
| ADDP | 1FH | ADDP 7 | ADDP 6 | ADDP 5 | ADDP 4 | ADDP 3 | ADDP 2 | ADDP 1 | ADDP 0 |
| | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W |
| | Default | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |

3.2 REGISTER DESCRIPTION

3.2.1 PRIMARY REGISTERS

ID: Device ID Register (R, Address = 00H)

| Symbol | Position | Default | Description |
|---------|----------|---------|--|
| ID[7:0] | ID.7-0 | 10H | An 8-bit word is pre-set into the device as the identification and revision number. This number is different with the functional changes and is mask programmed. |

ALB: Analog Loopback Configuration Register (R/W, Address = 01H)

| Symbol | Position | Default | Description |
|----------|----------|---------|---|
| ALB[7:0] | ALB.7-0 | 00H | 0 = Normal operation. (Default) 1 = Analog Loopback enabled. |

RLB: Remote Loopback Configuration Register (R/W, Address = 02H)

| Symbol | Position | Default | Description |
|----------|----------|---------|---|
| RLB[7:0] | RLB.7-0 | 00H | 0 = Normal operation. (Default) 1 = Remote Loopback enabled. |

TAO: Transmit All Ones Configuration Register (R/W, Address = 03H)

| Symbol | Position | Default | Description |
|----------|----------|---------|---|
| TAO[7:0] | TAO.7-0 | 00H | 0 = Normal operation. (Default) 1 = Transmit all ones. |

LOS: Loss of Signal Status Register (R, Address = 04H)

| Symbol | Position | Default | Description |
|----------|----------|---------|---|
| LOS[7:0] | LOS.7-0 | 00H | 0 = Normal operation. (Default) 1 = Loss of signal detected. |

DF: Driver Fault Status Register (R, Address = 05H)

| Symbol | Position | Default | Description |
|---------|----------|---------|---|
| DF[7:0] | DF.7-0 | 00H | 0 = Normal operation. (Default) 1 = Driver fault detected. |

LOSM: Loss of Signal Interrupt Mask Register (R/W, Address = 06H)

| Symbol | Position | Default | Description |
|-----------|----------|---------|--|
| LOSM[7:0] | LOSM.7-0 | 00H | 0 = LOS interrupt is not allowed. (Default) 1 = LOS interrupt is allowed. |

DFM: Driver Fault Interrupt Mask Register (R/W, Address = 07H)

| Symbol | Position | Default | Description |
|----------|----------|---------|--|
| DFM[7:0] | DFM.7-0 | 00H | 0 = Driver fault interrupt not allowed. (Default) 1 = Driver fault interrupt allowed. |

LOSI: Loss of Signal Interrupt Status Register (R, Address = 08H)

| S | Symbol | Position | Default | Description |
|----|----------|----------|---------|---|
| LC | OSI[7:0] | LOSI.7-0 | 00H | 0 = (Default). Or after a LOS read operation. 1 = Any transition on LOSn (Corresponding LOSMn is set to '1'). |

DFI: Driver Fault Interrupt Status Register (R, Address = 09H)

| Symbol | Position | Default | Description |
|----------|----------|---------|--|
| DFI[7:0] | DFI.7-0 | 00H | 0 = (Default). Or after a DF read operation. 1 = Any transition on DFn (Corresponding DFMn is set to '1'). |

RS: Software Reset Register (W, Address = 0AH)

| Symbol | Position | Default | Description |
|---------|----------|---------|---|
| RS[7:0] | RS.7-0 | FFH | Writing to this register will not change the content in this register but initiate a 1 µs reset cycle, which means all the registers in the device are set to their default values. |

PMON: Performance Monitor Configuration Register (R/W, Address = 0BH)

| Symbol | Position | Default | Description |
|---------|----------|---------|---|
| - | PMON.7-4 | 0000 | 0 = Normal operation. (Default) 1 = Reserved. |
| MC[3:0] | PMON.3-0 | 0000 | 0000 = Normal operation without monitoring (Default)0001 = Monitor Receiver 10010 = Monitor Receiver 20011 = Monitor Receiver 30100 = Monitor Receiver 40101 = Monitor Receiver 50110 = Monitor Receiver 60111 = Monitor Receiver 71000 = Normal operation without monitoring1001 = Monitor Transmitter 11010 = Monitor Transmitter 21011 = Monitor Transmitter 31100 = Monitor Transmitter 41101 = Monitor Transmitter 51110 = Monitor Transmitter 61111 = Monitor Transmitter 7 |

DLB: Digital Loopback Configuration Register (R/W, Address = 0CH)

| Symbol | Position | Default | Description |
|----------|----------|---------|--|
| DLB[7:0] | DLB.7-0 | 00H | 0 = Normal operation. (Default) 1 = Digital Loopback enabled. |

LAC: LOS/AIS Criteria Configuration Register (R/W, Address = 0DH)

| Symbol | Position | Default | Description |
|----------|----------|---------|---|
| LAC[7:0] | LAC.7-0 | 00H | 0 = G.775 (Default) 1 = ETSI 300 233 |

ATAO: Automatic TAOS Configuration Register (R/W, Address = 0EH)

| Symbol | Position | Default | Description |
|-----------|----------|---------|---|
| ATAO[7:0] | ATAO.7-0 | 00H | 0 = No automatic transmit all ones. (Default) 1 = Automatic transmit all ones to the line side during LOS. |

| Symbol | Position | Default | Description |
|-----------|----------|---------|--|
| - | GCF.7 | 0 | 0 = Normal operation. 1 = Reserved. |
| AISE | GCF.6 | 0 | 0 = AIS insertion to the system side disabled on LOS. 1 = AIS insertion to the system side enabled on LOS. |
| SCPB | GCF.5 | 0 | 0 = Short circuit protection is enabled. 1 = Short circuit protection is disabled. |
| CODE | GCF.4 | 0 | 0 = HDB3 encoder/decoder enabled. 1 = AMI encoder/decoder enabled. |
| JADP | GCF.3 | 0 | Jitter Attenuator Depth Select 0 = 32-bit FIFO (Default) 1 = 64-bit FIFO |
| JABW | GCF.2 | 0 | Jitter Transfer Function Bandwidth Select 0 = 1.7 Hz 1 = 6.6 Hz |
| JACF[1:0] | GCF.1-0 | 00 | Jitter Attenuator Configuration 00 = JA not used. (Default) 01 = JA in transmit path 10 = JA not used. 11 = JA in receive path |

GCF: Global Configuration Register (R/W, Address = 0FH)

OE: Output Enable Configuration Register (R/W, Address = 12H)

| Symbol | Position | Default | Description |
|---------|----------|---------|--|
| OE[7:0] | OE.7-0 | 00H | 0 = Transmit drivers enabled. (Default) 1 = Transmit drivers in high-Z. |

AIS: Alarm Indication Signal Status Register (R, Address = 13H)

| Symbol | Position | Default | Description |
|----------|----------|---------|--|
| AIS[7:0] | AIS.7-0 | 00H | 0 = Normal operation. (Default) 1 = AIS detected. |

AISM: Alarm Indication Signal Interrupt Mask Register (R/W, Address = 14H)

| Symbo | Positio | n Default | Description |
|---------|----------|-----------|--|
| AISM[7: |] AISM.7 | 0 00H | 0 = AIS interrupt is not allowed. (Default) 1 = AIS interrupt is allowed. |

AISI: Alarm Indication Signal Interrupt Status Register (R, Address = 15H)

| Symbol | Position | Default | Description |
|-----------|----------|---------|---|
| AISI[7:0] | AISI.7-0 | 00H | 0 = (Default), or after an AIS read operation 1 = Any transition on AISn . (Corresponding AISMn is set to '1'.) |

ADDP: Address Pointer Control Register (R/W, Address = 1F H)

| Symbol | Position | Default | Description |
|-----------|----------|---------|---|
| ADDP[7:0] | ADDP.7-0 | 00H | Two kinds of configuration in this register can be set to switch between primary register bank and expanded register bank. When power up, the address pointer will point to the top address of primary register bank automatically. 00H = The address pointer points to the top address of primary register bank (default). AAH = The address pointer points to the top address of expanded register bank. |

3.2.2 EXPANDED REGISTER DESCRIPTION

e-SING: Single Rail Mode Setting Register (R/W, Expanded Address = 00H)

| Symbol | Position | Default | Description |
|-----------|----------|---------|--|
| SING[7:0] | SING.7-0 | 00H | 0 = Pin TDNn selects single rail mode or dual rail mode. (Default) 1 = Single rail mode enabled (with CRSn=0) |

e-CODE: Encoder/Decoder Selection Register (R/W, Expanded Address = 01H)

| Symbol | Position | Default | Description |
|-----------|----------|---------|--|
| CODE[7:0] | CODE.7-0 | 00H | CODEn selects AMI or HDB3 encoder/decoder on a per channel basis with SINGn = 1 and CRSn = 0. 0 = HDB3 encoder/decoder enabled. (Default) 1 = AMI encoder/decoder enabled. |

e-CRS: Clock Recovery Enable/Disable Selection Register (R/W, Expanded Address = 02H)

| Symbol | Position | Default | Description |
|----------|----------|---------|---|
| CRS[7:0] | CRS.7-0 | 00H | 0 = Clock recovery enabled. (Default) 1 = Clock recovery disabled. |

e-RPDN: Receiver n Powerdown Register (R/W, Expanded Address = 03H)

| Symbol | Position | Default | | | | |
|-----------|----------|---------|--|--|--|--|
| RPDN[7:0] | RPDN.7-0 | 00H | 0 = Normal operation. (Default) 1 = Receiver n is powered down. | | | |

e-TPDN: Transmitter n Powerdown Register (R/W, Expanded Address = 04H)

| TRANKT ON TRANKT OF T | | bol Position Default | Symbol |
|--|----|----------------------|-----------|
| IPDN[7:0] IPDN.7-0 00H 1 = Transmitter n is powered down ⁽¹⁾ (the corresponding transmit output driver enters a low power high-Z mode). |). | N[7:0] TPDN.7-0 00H | TPDN[7:0] |

^{1.} Transmitter n is powered down when either pin TCLKn is pulled low or TPDNn is set to '1

e-CZER: Consecutive Zero Detect Enable/Disable Register (R/W, Expanded Address = 05H)

| Symbol | Position | Default | Description | | | |
|-----------|----------|---------|--|--|--|--|
| CZER[7:0] | CZER.7-0 | 00H | 0 = Excessive zeros detect disabled. (Default) 1 = Excessive zeros detect enabled for HDB3 decoder in single rail mode. | | | |

e-CODV: Code Violation Detect Enable/Disable Register (R/W, Expanded Address = 06H)

| Symbol | Position | Default | Description | | | |
|-----------|----------|---------|---|--|--|--|
| CODV[7:0] | CODV.7-0 | 00H | 0 = Code Violation Detect enable for HDB3 decoder in single rail mode. (Default) 1 = Code Violation Detect disabled. | | | |

e-EQUA: Receive Equalizer Enable/Disable Register (R/W, Expanded Address = 07H)

| Γ | Symbol | Position | Default | Description | | | |
|---|-----------|----------|---------|--|--|--|--|
| | EQUA[7:0] | EQUA.7-0 | 00H | 0 = Normal operation. (Default) 1 = Equalizer in Receiver n is enabled, which can improve the receive performance when transmission length is more than 200 m. | | | |

4 IEEE STD 1149.1 JTAG TEST ACCESS PORT

The IDT82V2058 supports the digital Boundary Scan Specification as described in the IEEE 1149.1 standards.

The boundary scan architecture consists of data and instruction registers plus a Test Access Port (TAP) controller. Control of the TAP is achieved through signals applied to the TMS and TCK pins. Data is shifted into the registers via the TDI pin, and shifted out of the registers via the TDO pin. JTAG test data are clocked at a rate determined by JTAG test clock.

The JTAG boundary scan registers includes BSR (Boundary Scan Register), IDR (Device Identification Register), BR (Bypass Register) and IR (Instruction Register). These will be described in the following pages. Refer to Figure-21 for architecture.

4.1 JTAG INSTRUCTIONS AND INSTRUCTION REG-ISTER (IR)

The IR with instruction decode block is used to select the test to be executed or the data register to be accessed or both.

The instructions are shifted in LSB first to this 3-bit register. See Table-17 Instruction Register Description on page 34 for details of the codes and the instructions related.




Figure-21 JTAG Architecture

Table-17 Instruction Register Description

| IR Code | Instruction | Comments | | | | |
|---------|----------------|--|--|--|--|--|
| 000 | Extest | The external test instruction allows testing of the interconnection to other devices. When the current instruction is the EXTEST instruction, the boundary scan register is placed between TDI and TDO. The signal on the input pins can be sampled by loading the boundary scan register using the Capture-DR state. The sampled values can then be viewed by shifting the boundary scan register using the Shift-DR state. The signal on the output pins can be controlled by loading patterns shifted in through input TDI into the boundary scan register using the Update-DR state. | | | | |
| 100 | Sample/Preload | The sample instruction samples all the device inputs and outputs. For this instruction, the boundary scan register is placed between TDI and TDO. The normal path between IDT82V2058 logic and the I/O pins is maintained. Primary device inputs and outputs can be sampled by loading the boundary scan register using the Capture-DR state. The sampled values can then be viewed by shifting the boundary scan register using the Shift-DR state. | | | | |
| 110 | ldcode | The identification instruction is used to connect the identification register between TDI and TDO. The device's identifica- tion code can then be shifted out using the Shift-DR state. | | | | |
| 111 | Bypass | The bypass instruction shifts data from input TDI to output TDO with one TCK clock period delay. The instruction is used to bypass the device. | | | | |

Table-18 Device Identification Register Description

| Bit No. | Comments |
|---------|-----------------|
| 0 | Set to '1' |
| 1~11 | Producer Number |
| 12~27 | Part Number |
| 28~31 | Device Revision |

4.2 JTAG DATA REGISTER

4.2.1 DEVICE IDENTIFICATION REGISTER (IDR)

The IDR can be set to define the producer number, part number and the device revision, which can be used to verify the proper version or revision number that has been used in the system under test. The IDR is 32 bits long and is partitioned as in Table-18. Data from the IDR is shifted out to TDO LSB first.

Table-19 Boundary Scan Register Description

4.2.2 BYPASS REGISTER (BR)

The BR consists of a single bit. It can provide a serial path between the TDI input and TDO output, bypassing the BSR to reduce test access times.

4.2.3 BOUNDARY SCAN REGISTER (BSR)

The BSR can apply and read test patterns in parallel to or from all the digital I/O pins. The BSR is a 98 bits long shift register and is initialized and read using the instruction EXTEST or SAMPLE/PRELOAD. Each pin is related to one or more bits in the BSR. Please refer to Table-19 for details of BSR bits and their functions.

| Bit No. | Bit Symbol | Pin Signal | Туре | Comments |
|---------|------------|------------|------|----------|
| 0 | POUT0 | LP0 | I/O | |
| 1 | PIN0 | LP0 | I/O | |
| 2 | POUT1 | LP1 | I/O | |
| 3 | PIN1 | LP1 | I/O | |
| 4 | POUT2 | LP2 | I/O | |
| 5 | PIN2 | LP2 | I/O | |
| 6 | POUT3 | LP3 | I/O | |
| 7 | PIN3 | LP3 | I/O | |
| 8 | POUT4 | LP4 | I/O | |
| 9 | PIN4 | LP4 | I/O | |
| 10 | POUT5 | LP5 | I/O | |
| 11 | PIN5 | LP5 | I/O | |
| 12 | POUT6 | LP6 | I/O | |
| 13 | PIN6 | LP6 | I/O | |
| 14 | POUT7 | LP7 | I/O | |
| 15 | PIN7 | LP7 | I/O | |

Table-19 Boundary Scan Register Description (Continued)

| Bit No. | Bit Symbol | Pin Signal | Туре | Comments |
|---------|------------|------------|------|---|
| | | | | Controls pins LP[7:0]. |
| 16 | PIOS | N/A | - | When '0', the pins are configured as outputs. The output values to the pins are set in POUT 7~0. When '1', the pins are high-Z. The input values to the pins are read in PIN 7~0. |
| 17 | TCLK1 | TCLK1 | I | |
| 18 | TDP1 | TDP1 | l | |
| 19 | TDN1 | TDN1 | l | |
| 20 | RCLK1 | RCLK1 | 0 | |
| 21 | RDP1 | RDP1 | 0 | |
| 22 | RDN1 | RDN1 | 0 | |
| 23 | HZEN1 | N/A | - | Controls pin RDP1, RDN1 and RCLK1. When '0', the outputs are enabled on the pins. When '1', the pins are high-Z. |
| 24 | LOS1 | LOS1 | 0 | |
| 25 | TCLK0 | TCLK0 | l | |
| 26 | TDP0 | TDP0 | | |
| 27 | TDN0 | TDN0 | | |
| 28 | RCLK0 | RCLK0 | 0 | |
| 29 | RDP0 | RDP0 | 0 | |
| 30 | RDN0 | RDN0 | 0 | |
| 31 | HZEN0 | N/A | - | Controls pin RDP0, RDN0 and RCLK0. When '0', the outputs are enabled on the pins. When '1', the pins are high-Z. |
| 32 | LOS0 | LOS0 | 0 | |
| 33 | MODE1 | MODE1 | | |
| 34 | LOS3 | LOS3 | 0 | |
| 35 | RDN3 | RDN3 | 0 | |
| 36 | RDP3 | RDP3 | 0 | |
| 37 | HZEN3 | N/A | - | Controls pin RDP3, RDN3 and RCLK3. When '0', the outputs are enabled on the pins. When '1', the pins are high-Z. |
| 38 | RCLK3 | RCLK3 | 0 | |
| 39 | TDN3 | TDN3 | | |
| 40 | TDP3 | TDP3 | | |
| 41 | TCLK3 | TCLK3 | | |
| 42 | LOS2 | LOS2 | 0 | |
| 43 | RDN2 | RDN2 | 0 | |
| 44 | RDP2 | RDP2 | 0 | |
| 45 | HZEN2 | N/A | - | Controls pin RDP2, RDN2 and RCLK2. When '0', the outputs are enabled on the pins. When '1', the pins are high-Z. |
| 46 | RCLK2 | RCLK2 | 0 | |
| 47 | TDN2 | TDN2 | I | |
| 48 | TDP2 | TDP2 | I | |
| 49 | TCLK2 | TCLK2 | | |
| 50 | INT | ĪNT | 0 | |
| 51 | ACK | ACK | 0 | |
| 52 | SDORDYS | N/A | - | Control pin ACK. When '0', the output is enabled on pin \overline{ACK} . When '1', the pin is high-Z. |
| 53 | WRB | DS | | |
| 54 | RDB | R/W | I | |
| 55 | ALE | ALE | I | |
| 56 | CSB | CS | | |

Table-19 Boundary Scan Register Description (Continued)

| Bit No. | Bit Symbol | Pin Signal | Туре | Comments |
|---------|------------|------------|------|--|
| 57 | MODE0 | MODE0 | | |
| 58 | TCLK5 | TCLK5 | | |
| 59 | TDP5 | TDP5 | | |
| 60 | TDN5 | TDN5 | I | |
| 61 | RCLK5 | RCLK5 | 0 | |
| 62 | RDP5 | RDP5 | 0 | |
| 63 | RDN5 | RDN5 | 0 | |
| 64 | HZEN5 | N/A | - | Controls pin RDP5, RDN5 and RCLK5. When '0', the outputs are enabled on the pins. When '1', the pins are high-Z. |
| 65 | LOS5 | LOS5 | 0 | |
| 66 | TCLK4 | TCLK4 | I | |
| 67 | TDP4 | TDP4 | | |
| 68 | TDN4 | TDN4 | | |
| 69 | RCLK4 | RCLK4 | 0 | |
| 70 | RDP4 | RDP4 | 0 | |
| 71 | RDN4 | RDN4 | 0 | |
| 72 | HZEN4 | N/A | - | Controls pin RDP4, RDN4 and RCLK4. When '0', the outputs are enabled on the pins. When '1', the pins are high-Z. |
| 73 | LOS4 | LOS4 | 0 | |
| 74 | OE | OE | | |
| 75 | CLKE | CLKE | | |
| 76 | LOS7 | LOS7 | 0 | |
| 77 | RDN7 | RDN7 | 0 | |
| 78 | RDP7 | RDP7 | 0 | |
| 79 | HZEN7 | N/A | - | Controls pin RDP7, RDN7 and RCLK7. When '0', the outputs are enabled on the pins. When '1', the pins are high-Z. |
| 80 | RCLK7 | RCLK7 | 0 | |
| 81 | TDN7 | TDN7 | I | |
| 82 | TDP7 | TDP7 | | |
| 83 | TCLK7 | TCLK7 | | |
| 84 | LOS6 | LOS6 | 0 | |
| 85 | RDN6 | RDN6 | 0 | |
| 86 | RDP6 | RDP6 | 0 | |
| 87 | HZEN6 | N/A | - | Controls pin RDP6, RDN6 and RCLK6. When '0', the outputs are enabled on the pins. When '1', the pins are high-Z. |
| 88 | RCLK6 | RCLK6 | 0 | |
| 89 | TDN6 | TDN6 | I | |
| 90 | TDP6 | TDP6 | I | |
| 91 | TCLK6 | TCLK6 | I | |
| 92 | MCLK | MCLK | I | |
| 93 | MODE2 | MODE2 | I | |
| 94 | A4 | A4 | | |
| 95 | A3 | A3 | I | |
| 96 | A2 | A2 | | |
| 97 | A1 | A1 | | |
| 98 | A0 | A0 | | |

4.3 TEST ACCESS PORT CONTROLLER

The TAP controller is a 16-state synchronous state machine. Figure-22 shows its state diagram A description of each state follows. Note that the figure contains two main branches to access either the data or

Table-20 TAP Controller State Description

instruction registers. The value shown next to each state transition in this figure states the value present at TMS at each rising edge of TCK. Refer to Table-20 for details of the state description.

| State | Description |
|------------------|---|
| Test Logic Reset | In this state, the test logic is disabled. The device is set to normal operation. During initialization, the device initializes the instruction register with the IDCODE instruction. Regardless of the original state of the controller, the controller enters the Test-Logic-Reset state when the TMS input is held high for at least 5 rising edges of TCK. The controller remains in this state while TMS is high. The device processor automatically enters this state at power-up. |
| Run-Test/Idle | This is a controller state between scan operations. Once in this state, the controller remains in the state as long as TMS is held low. The instruction register and all test data registers retain their previous state. When TMS is high and a rising edge is applied to TCK, the controller moves to the Select-DR state. |
| Select-DR-Scan | This is a temporary controller state and the instruction does not change in this state. The test data register selected by the current instruction retains its previous state. If TMS is held low and a rising edge is applied to TCK when in this state, the controller moves into the Capture-DR state and a scan sequence for the selected test data register is initiated. If TMS is held high and a rising edge applied to TCK, the controller moves to the Select-IR-Scan state. |
| Capture-DR | In this state, the Boundary Scan Register captures input pin data if the current instruction is EXTEST or SAMPLE/PRELOAD. The instruction does not change in this state. The other test data registers, which do not have parallel input, are not changed. When the TAP controller is in this state and a rising edge is applied to TCK, the controller enters the Exit1-DR state if TMS is high or the Shift-DR state if TMS is low. |
| Shift-DR | In this controller state, the test data register connected between TDI and TDO as a result of the current instruction shifts data on stage toward its serial output on each rising edge of TCK. The instruction does not change in this state. When the TAP controller is in this state and a rising edge is applied to TCK, the controller enters the Exit1-DR state if TMS is high or remains in the Shift-DR state if TMS is low. |
| Exit1-DR | This is a temporary state. While in this state, if TMS is held high, a rising edge applied to TCK causes the controller to enter the Update-DR state, which terminates the scanning process. If TMS is held low and a rising edge is applied to TCK, the controller enters the Pause-DR state. The test data register selected by the current instruction retains its previous value and the instruction does not change during this state. |
| Pause-DR | The pause state allows the test controller to temporarily halt the shifting of data through the test data register in the serial path between TDI and TDO. For example, this state could be used to allow the tester to reload its pin memory from disk during application of a long test sequence. The test data register selected by the current instruction retains its previous value and the instruction does not change during this state. The controller remains in this state as long as TMS is low. When TMS goes high and a rising edge is applied to TCK, the controller moves to the Exit2-DR state. |
| Exit2-DR | This is a temporary state. While in this state, if TMS is held high, a rising edge applied to TCK causes the controller to enter the Update-DR state, which terminates the scanning process. If TMS is held low and a rising edge is applied to TCK, the controller enters the Shift-DR state. The test data register selected by the current instruction retains its previous value and the instruction does not change during this state. |
| Update-DR | The Boundary Scan Register is provided with a latched parallel output to prevent changes while data is shifted in response to the EXTEST and SAMPLE/PRELOAD instructions. When the TAP controller is in this state and the Boundary Scan Register is selected, data is latched into the parallel output of this register from the shift-register path on the falling edge of TCK. The data held at the latched parallel output changes only in this state. All shift-register stages in the test data register selected by the current instruction retain their previous value and the instruction does not change during this state. |
| Select-IR-Scan | This is a temporary controller state. The test data register selected by the current instruction retains its previous state. If TMS is held low and a rising edge is applied to TCK when in this state, the controller moves into the Capture-IR state, and a scan sequence for the instruction register is initiated. If TMS is held high and a rising edge is applied to TCK, the controller moves to the Test-Logic-Reset state. The instruction does not change during this state. |
| Capture-IR | In this controller state, the shift register contained in the instruction register loads a fixed value of '100' on the rising edge of TCK. This supports fault-isolation of the board-level serial test data path. Data registers selected by the current instruction retain their value and the instruction does not change during this state. When the controller is in this state and a rising edge is applied to TCK, the controller enters the Exit1-IR state if TMS is held high, or the Shift-IR state if TMS is held low. |
| Shift-IR | In this state, the shift register contained in the instruction register is connected between TDI and TDO and shifts data one stage towards its serial output on each rising edge of TCK. The test data register selected by the current instruction retains its previous value and the instruction does not change during this state. When the controller is in this state and a rising edge is applied to TCK, the controller enters the Exit1-IR state if TMS is held high, or remains in the Shift-IR state if TMS is held low. |

INDUSTRIAL TEMPERATURE RANGES

Table-20 TAP Controller State Description (Continued)

| State | Description |
|-----------|---|
| Exit1-IR | This is a temporary state. While in this state, if TMS is held high, a rising edge applied to TCK causes the controller to enter the Update-IR state, which terminates the scanning process. If TMS is held low and a rising edge is applied to TCK, the controller enters the Pause-IR state. The test data register selected by the current instruction retains its previous value and the instruction does not change during this state. |
| Pause-IR | The pause state allows the test controller to temporarily halt the shifting of data through the instruction register. The test data register selected by the current instruction retains its previous value and the instruction does not change during this state. The controller remains in this state as long as TMS is low. When TMS goes high and a rising edge is applied to TCK, the controller moves to the Exit2-IR state. |
| Exit2-IR | This is a temporary state. While in this state, if TMS is held high, a rising edge applied to TCK causes the controller to enter the Update-IR state, which terminates the scanning process. If TMS is held low and a rising edge is applied to TCK, the controller enters the Shift-IR state. The test data register selected by the current instruction retains its previous value and the instruction does not change during this state. |
| Update-IR | The instruction shifted into the instruction register is latched into the parallel output from the shift-register path on the falling edge of TCK. When the new instruction has been latched, it becomes the current instruction. The test data registers selected by the current instruction retain their previous value. |




Figure-22 JTAG State Diagram

ABSOLUTE MAXIMUM RATING

| Symbol | Parameter | Min | Мах | Unit |
|----------------|---|---------|------------------------|--------|
| VDDA, VDDD | Core Power Supply | -0.5 | 4.0 | V |
| VDDIO0, VDDIO1 | I/O Power Supply | -0.5 | 4.0 | V |
| VDDT0-7 | Transmit Power Supply | -0.5 | 7.0 | V |
| | Input Voltage, any digital pin | GND-0.5 | 5.5 | V |
| Vin | Input Voltage ⁽¹⁾ , RTIPn pins and RRINGn pins | GND-0.5 | VDDA+ 0.5 VDDD+ 0.5 | V V |
| | ESD Voltage, any pin ⁽²⁾ | 2000 | | V |
| | Transient Latch-up Current, any pin | | 100 | mA |
| lin | Input Current, any digital pin ⁽³⁾ | -10 | 10 | mA |
| | DC Input Current, any analog pin ⁽³⁾ | | ±100 | mA |
| Pd | Maximum Power Dissipation in package | | 1.6 | W |
| Tc | Case Temperature | | 120 | °C |
| Ts | Storage Temperature | -65 | +150 | °C |

CAUTION: Exceeding these values may cause permanent damage. Functional operation under these conditions is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

^{1.} Referenced to ground

^{2.} Human body model

^{3.} Constant input current

RECOMMENDED OPERATING CONDITIONS

| Symbol | Parameter | Min | Тур | Max | Unit |
|--------------------|---|------|-----|------|------|
| VDDA, VDDD | Core Power Supply | 3.13 | 3.3 | 3.47 | V |
| VDDIO | I/O Power Supply | 3.13 | 3.3 | 3.47 | V |
| VDDT | Transmitter Supply | | | | |
| | 3.3 V | 3.13 | 3.3 | 3.47 | V |
| | 5 V | 4.75 | 5.0 | 5.25 | V |
| T _A | Ambient Operating Temperature | -40 | 25 | 85 | °C |
| RL | Output load at TTIPn pins and TRINGn pins | 25 | | | W |
| I _{VDD} | Average Core Power Supply Current ⁽¹⁾ | | 40 | 60 | mA |
| I _{VDDIO} | I/O Power Supply Current ⁽²⁾ | | 15 | 25 | mA |
| I _{VDDT} | Average transmitter power supply current, E1 mode ^{(1), (3)} | | | | |
| | 75 Ω 50% ones density data: | | | 125 | mA |
| | 100% ones density data: | | | 220 | mA |
| | 120 Ω 50% ones density data: | | | 100 | mA |
| | 100% ones density data: | | | 200 | mA |

¹ Maximum power and current consumption over the full operating temperature and power supply voltage range. Includes all channels.

^{2.} Digital output is driving 50 pF load, digital input is within 10% of the supply rails.

^{3.} Power consumption includes power absorbed by line load and external transmitter components.

POWER CONSUMPTION

| Symbol | Parameter | Min | Тур | Max ⁽¹⁾⁽²⁾ | Unit |
|--------|-------------------------|-----|------|-----------------------|------|
| | E1, 3.3 V, 75 Ω Load | | | | |
| | 50% ones density data: | - | 612 | - | mW |
| | 100% ones density data: | - | 1050 | 1125 | mW |
| | E1, 3.3 V, 120 Ω Load | | | | |
| | 50% ones density data: | - | 526 | - | mW |
| | 100% ones density data: | - | 880 | 940 | mW |
| | E1, 5.0 V, 75 Ω Load | | | | |
| | 50% ones density data: | - | 835 | - | mW |
| | 100% ones density data: | - | 1510 | 1610 | mW |
| | E1, 5.0 V, 120 Ω Load | | | | |
| | 50% ones density data: | - | 710 | - | mW |
| | 100% ones density data: | - | 1240 | 1330 | mW |

¹ Maximum power and current consumption over the full operating temperature and power supply voltage range. Includes all channels.

^{2.} Power consumption includes power absorbed by line load and external transmitter components.

DC CHARACTERISTICS

| Symbol | Parameter | Min | Тур | Max | Unit |
|-----------------|--|---------------------------------------|---------------------|-------------------------|------|
| V _{IL} | Input Low Level Voltage | | | | |
| | MODE2, JAS and LPn pins | | | $\frac{1}{3}$ VDDIO-0.2 | V |
| | All other digital inputs pins | | | 0.8 | V |
| V _{IM} | Input Mid Level Voltage | | | | |
| | MODE2, JAS and LPn pins | 1/3 VDDIO+0.2 | $\frac{1}{2}$ VDDIO | $\frac{2}{3}$ VDDIO-0.2 | V |
| VIH | Input High Voltage | , , , , , , , , , , , , , , , , , , , | | | |
| | MODE2, JAS and LPn pins | $\frac{2}{3}$ VDDIO+ 0.2 | | | V |
| | All other digital inputs pins | 2.0 | | | V |
| V _{OL} | Output Low level Voltage ⁽¹⁾ (lout = 1.6 mA) | | | 0.4 | V |
| V _{OH} | Output High level Voltage ⁽¹⁾ (lout = 400 μ A) | 2.4 | | VDDIO | V |
| V _{MA} | Analog Input Quiescent Voltage (RTIPn/RRINGn pin while floating) | 1.33 | 1.4 | 1.47 | V |
| Ι _Η | Input High Level Current (MODE2, JAS and LPn pin) | | | 50 | μA |
| ١L | Input Low Level Current (MODE2, JAS and LPn pin) | | | 50 | μA |
| l _l | Input Leakage Current | | | | |
| | TMS, TDI and TRST pins | | | 50 | μΑ |
| | All other digital input pins | -10 | | 10 | μΑ |
| I _{ZL} | High-Z Leakage Current | -10 | | 10 | μΑ |
| Z _{OH} | Output High-Z on TTIPn pins and TRINGn pins | 150 | | | kΩ |

¹. Output drivers will output CMOS logic levels into CMOS loads.

TRANSMITTER CHARACTERISTICS

| Symbol | | Parameter | Min | Тур | Max | Unit |
|--------------------|---|--|----------------|-------------|--------------|----------------|
| V _{o-p} | Output Pulse Amplitudes ⁽¹⁾ 75 Ω load 120 Ω load | | 2.14 2.7 | 2.37 3.0 | 2.6 3.3 | V V |
| V _{o-s} | Zero (space) Level 75 Ω load 120 Ω load | | -0.237 -0.3 | | 0.237 0.3 | V V |
| | Transmit Amplitude Variation with supp | ly | -1 | | +1 | % |
| | Difference between pulse sequences for | r 17 consecutive pulses | | | 200 | mV |
| T _{PW} | Output Pulse Width at 50% of nominal a | amplitude | 232 | 244 | 256 | ns |
| | Ratio of the amplitudes of Positive and | Negative Pulses at the center of the pulse interval | 0.95 | | 1.05 | |
| RTX | Transmit Return Loss ⁽²⁾ | | | | | 1 |
| | 75 Ω | 51 kHz – 102 kHz 102 kHz – 2.048 MHz 2.048 MHz – 3.072 MHz | 15 15 15 | | | dB dB dB |
| | 120 Ω | 51 kHz – 102 kHz 102 kHz – 2.048 MHz 2.048 MHz – 3.072 MHz | 15 15 15 | | | dB dB dB |
| JTX _{P-P} | Intrinsic Transmit Jitter (TCLK is jitter fr | ee, JA enabled) | | | | |
| | 20 Hz – 100 kHz | | | 0.050 | | U.I. |
| Td | Transmit Path Delay (JA is disabled) | | | | | |
| | Single Rail Dual Rail | | | 8 3 | | U.I. U.I. |
| I _{SC} | Line Short Circuit Current ⁽³⁾ | | | 180 | | mAp |

^{1.} Measured at the line output ports

^{2.} Test at IDT82V2058 evaluation board

^{3.} Measured on device, between TTIPn and TRINGn

RECEIVER CHARACTERISTICS

| Symbol | Parameter | Min | Тур | Max | Unit |
|--------------------|---|----------------|------------|---------|----------------|
| ATT | Permissible Cable Attenuation (@1024 kHz) | | | 15 | dB |
| IA | Input Amplitude | 0.1 | | 0.9 | Vp |
| SIR | Signal to Interference Ratio Margin ⁽¹⁾ | -15 | | | dB |
| SRE | Data Decision Threshold (refer to peak input voltage) | | 50 | | % |
| | Data Slicer Threshold | | 150 | | mV |
| | Analog Loss Of Signal ⁽²⁾ Declare/Clear: | 120/150 | 200/250 | 280/350 | mVp |
| | Allowable consecutive zeros before LOS G.775: ETSI 300 233: | | 32 2048 | | |
| | LOS Reset Clock Recovery Mode | 12.5 | | | % ones |
| JRX _{p-p} | Peak to Peak Intrinsic Receive Jitter (JA disabled) | | | 0.0625 | U.I. |
| JTRX | Jitter Tolerance | | | | |
| | 1 Hz – 20 Hz | 18.0 | | | U.I. |
| | 20 Hz – 2.4 kHz | 1.5 | | | U.I. |
| | 18 kHz – 100 kHz | 0.2 | | | U.I. |
| ZDM | Receiver Differential Input Impedance | | 120 | | kΩ |
| ZCM | Receiver Common Mode Input Impedance to GND | 10 | | | kΩ |
| RRX | Receive Return Loss 51 kHz – 102 kHz 102 kHz – 2.048 MHz 2.048 MHz – 3.072 MHz | 20 20 20 | | | dB dB dB |
| | Receive Path Delay Dual rail Single rail | | 3 8 | | U.I. U.I. |

^{1.} Per G.703, O.151 @ 6 dB cable attenuation

² Measured on device, between RTIP and RRING, all ones signal.

JITTER ATTENUATOR CHARACTERISTICS

| Symbol | Parameter | Min | Тур | Max | Unit |
|--------|--|--------------------------------|-------------------|------|----------------------|
| f_3dB | Jitter Transfer Function Corner Frequency (–3 dB) | | | | |
| Host m | Host mode: 32/64 bit FIFO JABW = 0: JABW = 1: Hardware mode | | 1.7 6.6 1.7 | | Hz Hz Hz |
| | Jitter Attenuator ⁽¹⁾ | | | | |
| | @ 3 Hz @ 40 Hz @ 400 Hz @ 100 kHz | -0.5 -0.5 +19.5 +19.5 | | | dB dB dB dB |
| td | Jitter Attenuator Latency Delay 32 bit FIFO: 64 bit FIFO: | | 16 32 | | U.I. U.I. |
| | Input Jitter Tolerance before FIFO Overflow Or Underflow 32 bit FIFO: 64 bit FIFO: | | 28 56 | | U.I. U.I. |
| | Output Jitter in Remote Loopback ⁽²⁾ | | | 0.11 | U.I. |

^{1.} Per G.736, see Figure-38 on page 52.

^{2.} Per ETSI CTR12/13 output jitter.

TRANSCEIVER TIMING CHARACTERISTICS

| Symbol | Parameter | Min | Тур | Мах | Unit |
|---------------|--|------|-------|-----|------|
| | MCLK Frequency | | 2.048 | | MHz |
| | MCLK Tolerance | -100 | | 100 | ppm |
| | MCLK Duty Cycle | 40 | | 60 | % |
| Transmit path | | | | | |
| | TCLK Frequency | | 2.048 | | MHz |
| | TCLK Tolerance | -50 | | +50 | ppm |
| | TCLK Duty Cycle | 10 | | 90 | % |
| t1 | Transmit Data Setup Time | 40 | | | ns |
| t2 | Transmit Data Hold Time | 40 | | | ns |
| | Delay Time of OE Low to Driver High-Z | | | 1 | μs |
| | Delay Time of TCLK Low to Driver High-Z | 40 | 44 | 48 | μs |
| Receive path | | | | | |
| | Clock Recovery Capture Range ⁽¹⁾ | | ± 80 | | ppm |
| | RCLK Duty Cycle ⁽²⁾ | 40 | 50 | 60 | % |
| t4 | RCLK Pulse Width ⁽²⁾ | 457 | 488 | 519 | ns |
| t5 | RCLK Pulse Width Low Time | 203 | 244 | 285 | ns |
| t6 | RCLK Pulse Width High Time | 203 | 244 | 285 | ns |
| | Rise/Fall Time ⁽³⁾ | 5 | | 30 | ns |
| t7 | Receive Data Setup Time | 200 | 244 | | ns |
| t8 | Receive Data Hold Time | 200 | 244 | | ns |
| t9 | RDPn/RDNn Pulse Width (MCLK = High) ⁽⁴⁾ | 200 | 244 | | ns |

^{1.} Relative to nominal frequency, MCLK = \pm 100 ppm

² RCLK duty cycle widths will vary depending on extent of received pulse jitter displacement. Maximum and minimum RCLK duty cycles are for worst case jitter conditions (0.2 UI displacement for E1 per ITU G.823).

 $^{3.}$ For all digital outputs. C load = 15 pF

^{4.} Clock recovery is disabled in this mode.




Figure-23 Transmit System Interface Timing




Figure-24 Receive System Interface Timing

JTAG TIMING CHARACTERISTICS

| Symbol | Parameter | Min | Тур | Max | Unit | Comments |
|--------|--|-----|-----|-----|------|----------|
| t1 | TCK Period | 200 | | | ns | |
| t2 | TMS to TCK setup Time TDI to TCK Setup Time | 50 | | | ns | |
| t3 | TCK to TMS Hold Time TCK to TDI Hold Time | 50 | | | ns | |
| t4 | TCK to TDO Delay Time | | | 100 | ns | |





Figure-25 JTAG Interface Timing

PARALLEL HOST INTERFACE TIMING CHARACTERISTICS

INTEL MODE READ TIMING CHARACTERISTICS

| Symbol | Parameter | Min | Тур | Max | Unit | Comments |
|--------|---|-----|-----|-----|------|----------|
| t1 | Active RD Pulse Width | 90 | | | ns | (1) |
| t2 | Active CS to Active RD Setup Time | 0 | | | ns | |
| t3 | Inactive RD to Inactive CS Hold Time | 0 | | | ns | |
| t4 | Valid Address to Inactive ALE Setup Time (in Multiplexed Mode) | 5 | | | ns | |
| t5 | Invalid RD to Address Hold Time (in Non-Multiplexed Mode) | 0 | | | ns | |
| t6 | Active RD to Data Output Enable Time | 7.5 | | 15 | ns | |
| t7 | Inactive RD to Data High-Z Delay Time | 7.5 | | 15 | ns | |
| t8 | Active CS to RDY delay time | 6 | | 12 | ns | |
| t9 | Inactive CS to RDY High-Z Delay Time | 6 | | 12 | ns | |
| t10 | Inactive RD to Inactive INT Delay Time | | | 20 | ns | |
| t11 | Address Latch Enable Pulse Width (in Multiplexed Mode) | 10 | | | ns | |
| t12 | Address Latch Enable to RD Setup Time (in Multiplexed Mode) | 0 | | | ns | |
| t13 | Address Setup time to Valid Data Time (in Non-Multiplexed Mode) | 18 | | 32 | ns | |
| t14 | Inactive RD to Active RDY Delay Time | 10 | | 15 | ns | |
| t15 | Active RD to Active RDY Delay Time | 30 | | 85 | ns | |
| t16 | Inactive ALE to Address Hold Time (in Multiplexed Mode) | 5 | | | ns | |

^{1.} The t1 is determined by the start time of the valid data when the RDY signal is not used.










Figure-27 Multiplexed Intel Mode Read Timing


INTEL MODE WRITE TIMING CHARACTERISTICS

| Symbol | Parameter | Min | Тур | Max | Unit | Comments |
|--------|--|-----|-----|-----|------|----------|
| t1 | Active WR Pulse Width | 90 | | | ns | (1) |
| t2 | Active CS to Active WR Setup Time | 0 | | | ns | |
| t3 | Inactive WR to Inactive CS Hold Time | 0 | | | ns | |
| t4 | Valid Address to Latch Enable Setup Time (in Multiplexed Mode) | 5 | | | ns | |
| t5 | Invalid WR to Address Hold Time (in Non-Multiplexed Mode) | 2 | | | ns | |
| t6 | Valid Data to Inactive WR Setup Time | 5 | | | ns | |
| t7 | Inactive WR to Data Hold Time | 10 | | | ns | |
| t8 | Active CS to Inactive RDY Delay Time | 6 | | 12 | ns | |
| t9 | Active WR to Active RDY Delay Time | 30 | | 85 | ns | |
| t10 | Inactive WR to Inactive RDY Delay Time | 10 | | 15 | ns | |
| t11 | Invalid CS to RDY High-Z Delay Time | 6 | | 12 | ns | |
| t12 | Address Latch Enable Pulse Width (in Multiplexed Mode) | 10 | | | ns | |
| t13 | Inactive ALE to WR Setup Time (in Multiplexed Mode) | 0 | | | ns | |
| t14 | Inactive ALE to Address hold time (in Multiplexed Mode) | 5 | | | ns | |
| t15 | Address setup time to Inactive WR time (in Non-Multiplexed Mode) | 5 | | | ns | |

^{1.} The t1 can be 15 ns when RDY signal is not used.









MOTOROLA MODE READ TIMING CHARACTERISTICS

| Symbol | Parameter | Min | Тур | Max | Unit | Comments |
|--------|--|-----|-----|-----|------|----------|
| t1 | Active DS Pulse Width | 90 | | | ns | (1) |
| t2 | Active CS to Active DS Setup Time | 0 | | | ns | |
| t3 | Inactive $\overline{\text{DS}}$ to Inactive $\overline{\text{CS}}$ Hold Time | 0 | | | ns | |
| t4 | Valid R/ \overline{W} to Active \overline{DS} Setup Time | 0 | | | ns | |
| t5 | Inactive $\overline{\text{DS}}$ to R/ $\overline{\text{W}}$ Hold Time | 0.5 | | | ns | |
| t6 | Valid Address to Active DS Setup Time (in Non-Multiplexed Mode) | 5 | | | ns | |
| t7 | Active DS to Address Hold Time (in Non-Multiplexed Mode) | 10 | | | ns | |
| t8 | Active DS to Data Valid Delay Time (in Non-Multiplexed Mode) | 20 | | 35 | ns | |
| t9 | Active DS to Data Output Enable Time | 7.5 | | 15 | ns | |
| t10 | Inactive DS to Data High-Z Delay Time | 7.5 | | 15 | ns | |
| t11 | Active DS to Active ACK Delay Time | 30 | | 85 | ns | |
| t12 | Inactive DS to Inactive ACK Delay Time | 10 | | 15 | ns | |
| t13 | Inactive DS to Invalid INT Delay Time | | | 20 | ns | |
| t14 | Active AS to Active DS Setup Time (in Multiplexed Mode) | 5 | | | ns | |

^{1.} The t1 is determined by the start time of the valid data when the ACK signal is not used.





Figure-30 Non-Multiplexed Motorola Mode Read Timing





MOTOROLA MODE WRITE TIMING CHARACTERISTICS

| Symbol | Parameter | Min | Тур | Max | Unit | Comments |
|--------|---|-----|-----|-----|------|----------|
| t1 | Active DS Pulse Width | 90 | | | ns | (1) |
| t2 | Active CS to Active DS Setup Time | 0 | | | ns | |
| t3 | Inactive DS to Inactive CS Hold Time | 0 | | | ns | |
| t4 | Valid R/ \overline{W} to Active \overline{DS} Setup Time | 10 | | | ns | |
| t5 | Inactive $\overline{\text{DS}}$ to R/W Hold Time | 0 | | | ns | |
| t6 | Valid Address to Active DS Setup Time (in Non-Multiplexed Mode) | 10 | | | ns | |
| t7 | Valid DS to Address Hold Time (in Non-Multiplexed Mode) | 10 | | | ns | |
| t8 | Valid Data to Inactive DS Setup Time | 5 | | | ns | |
| t9 | Inactive DS to Data Hold Time | 10 | | | ns | |
| t10 | Active DS to Active ACK Delay Time | 30 | | 85 | ns | |
| t11 | Inactive DS to Inactive ACK Delay Time | 10 | | 15 | ns | |
| t12 | Active AS to Active DS (in Multiplexed Mode) | 0 | | | ns | |
| t13 | Inactive DS to Inactive AS Hold Time (in Multiplexed Mode) | 15 | | | ns | |

¹ The t1 can be 15ns when the ACK signal is not used.





Figure-32 Non-Multiplexed Motorola Mode Write Timing





SERIAL HOST INTERFACE TIMING CHARACTERISTICS

| Symbol | Parameter | Min | Тур | Max | Unit | Comments |
|--------|--|-----|-----|-----|------|--------------|
| t1 | SCLK High Time | 25 | | | ns | |
| t2 | SCLK Low Time | 25 | | | ns | |
| t3 | Active CS to SCLK Setup Time | 10 | | | ns | |
| t4 | Last SCLK Hold Time to Inactive CS Time | 50 | | | ns | |
| t5 | CS Idle Time | 50 | | | ns | |
| t6 | SDI to SCLK Setup Time | 5 | | | ns | |
| t7 | SCLK to SDI Hold Time | 5 | | | ns | |
| t8 | Rise/Fall Time (any pin) | | | 100 | ns | |
| t9 | SCLK Rise and Fall Time | | | 50 | ns | |
| t10 | SCLK to SDO Valid Delay Time | | 25 | 35 | ns | Load = 50 pF |
| t11 | SCLK Falling Edge to SDO High-Z Hold Time (CLKE = 0) or \overline{CS} Rising Edge to SDO High-Z Hold Time (CLKE = 1) | | 100 | | ns | |







Figure-34 Serial Interface Write Timing








JITTER TOLERANCE PERFORMANCE



Test condition: PRBS 2^15-1; Line code rule HDB3 is used.

Figure-37 Jitter Tolerance Performance


JITTER TRANSFER PERFORMANCE



Test condition: PRBS 2^15-1; Line code rule HDB3 is used.

Figure-38 Jitter Transfer Performance

ORDERING INFORMATION



DATASHEET DOCUMENT HISTORY

| 11/04/2001 | pgs. 2, 3, 10, 17 |
|------------|--|
| 11/20/2001 | pgs. 5, 6, 11, 13, 16, 17, 24, 26, 31, 38, 39, 40, 50 |
| 11/28/2001 | pgs. 5, 24, 26, 31 |
| 11/29/2001 | pgs. 5 |
| 12/05/2001 | pgs. 9 |
| 01/24/2002 | pgs. 2, 3, 9, 14, 39, 40 |
| 02/21/2002 | pgs. 14, 16, 41 |
| 03/25/2002 | pgs. 1, 2, 52 |
| 04/17/2002 | pgs. 17 |
| 05/07/2002 | pgs. 14, 44, 45, 48 |
| 01/15/2003 | pgs. 1, 52 |
| 04/12/2005 | pgs. 1, 5 to 8, 10, 11, 14, 15, 18, 19, 29, 30, 40 to 43, 47 to 53 |
| 09/14/2009 | pg. 40 |
| 01/21/2010 | pg. 8 |
| 10/10/2014 | pg. removed DA package information |
| | |



CORPORATE HEADQUARTERS 6024 Silver Creek Valley Road San Jose, CA 95138 www.idt.com

for SALES: 1-800-345-7015 or 408-284-8200 fax: 408-284-2775

for Tech Support: 408-360-1552 email:telecomhelp@idt.com

IDT and the IDT logo are trademarks of Integrated Device Technology, Inc.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

IDT (Integrated Device Technology):

<u>82V2058BBG</u> <u>82V2058DAG</u> <u>82V2058LDAG</u> <u>82V2058LDA</u> <u>82V2058DA</u> <u>82V2058XDAG</u> <u>82V2058LBB</u> 82V2058LBBG