

PHOTOCOUPLER

PS2562-1,PS2562L-1,PS2562L1-1,PS2562L2-1

HIGH ISOLATION VOLTAGE DARLINGTON TRANSISTOR TYPE MULTI PHOTOCOUPLER SERIES

-NEPOC Series-

DESCRIPTION

The PS2562-1 is optically coupled isolators containing a GaAs light emitting diode and an NPN silicon darlington connected phototransistor.

The PS2562-1 is in a plastic DIP (Dual In-line Package) and the PS2562L-1 is lead bending type (Gull-wing) for surface mount.

The PS2562L1-1 is lead bending type for long creepage distance.

The PS2562L2-1 is lead bending type for long creepage distance (Gull-wing) for surface mount.

FEATURES

- High isolation voltage (BV = 5 000 Vr.m.s.)
- High current transfer ratio (CTR = 2 000% TYP.)
- High-speed switching (t_r, t_f = 100 μs TYP.)
- Ordering number of tape product: PS2562L-1-F3 : 2 000 pcs/reel

: PS2562L2-1-E3: 1 000 pcs/reel


<R> • Safety standards

<R>

- UL approved: No. E72422
- CSA approved: No. CA 101391 (CA5A, CAN/CSA-C22.2 60065, 60950)
- BSI approved: No. 7112/7420SEMKO approved: No. 903238
- NEMKO approved: No. P09210868
- DEMKO approved: No. 314999
- FIMKO approved: No. FI 25119
- DIN EN60747-5-2 (VDE0884 Part2) approved: No. 40008862 (option)

APPLICATIONS


- · Power supply
- · Telephone/FAX.
- FA/OA equipment
- Programmable logic controller




The information in this document is subject to change without notice. Before using this document, please confirm that this is the latest version.

<R> PACKAGE DIMENSIONS (UNIT: mm)


DIP Type




Lead Bending Type (Gull-Wing)



Long Creepage Distance




Long Creepage Distance (Gull-Wing)



<R> PHOTOCOUPLER CONSTRUCTION

Parameter	Unit (MIN.)		
Air Distance	7 mm		
Outer Creepage Distance	7 mm		
Inner Creepage Distance	4 mm		
Isolation Thickness	0.4 mm		

<R> MARKING EXAMPLE



<R> ORDERING INFORMATION

Part Number	Order Number	Solder Plating Specification	Packing Style	Safety Standard Approval	Application Part Number ^{*1}
PS2562-1	PS2562-1-A	Pb-Free	Magazine case 100 pcs	Standard products	PS2562-1
PS2562L-1	PS2562L-1-A			(UL, CSA, BSI,	
PS2562L1-1	PS2562L1-1-A			SEMKO, NEMKO,	
PS2562L2-1	PS2562L2-1-A			DEMKO, FIMKO	
PS2562L-1-F3	PS2562L-1-F3-A		Embossed Tape 2 000 pcs/reel	approved)	
PS2562L2-1-E3	PS2562L2-1-E3-A		Embossed Tape 1 000 pcs/reel		
PS2562-1-V	PS2562-1-V-A		Magazine case 100 pcs	DIN EN60747-5-2	
PS2562L-1-V	PS2562L-1-V-A			(VDE0884 Part2)	
PS2562L1-1-V	PS2562L1-1-V-A			approved products	
PS2562L2-1-V	PS2562L2-1-V-A			(option)	
PS2562L-1-V-F3	PS2562L-1-V-F3-A		Embossed Tape 2 000 pcs/reel		
PS2562L2-1-V-E3	PS2562L2-1-V-E3-A		Embossed Tape 1 000 pcs/reel		

^{*1} For the application of the Safety Standard, following part number should be used.

ABSOLUTE MAXIMUM RATINGS (TA = 25°C, unless otherwise specified)

	Parameter		Ratings	Unit	
Diode	Reverse Voltage	VR	6	V	
	Forward Current (DC)	lF	80	mA	
	Power Dissipation Derating	⊿P₀/°C	1.5	mW/°C	
	Power Dissipation	Po	150	mW	
	Peak Forward Current	IFP	1	Α	
Transistor	Collector to Emitter Voltage	Vceo	40	V	
	Emitter to Collector Voltage	Veco	6	V	
	Collector Current	lc	200	mA	
	Power Dissipation Derating	⊿Pc/°C	2.0	mW/°C	
	Power Dissipation	Pc	200	mW	
Isolation Voltage ^{*2}		BV	5 000	Vr.m.s.	
Operating Ambient Temperature		TA	-55 to +100	°C	
Storage Temperature		T _{stg}	-55 to +150	°C	

^{*1} PW = 100 μ s, Duty Cycle = 1%

^{*2} AC voltage for 1 minute at T_A = 25°C, RH = 60% between input and output. Pins 1-2 shorted together, 3-4 shorted together.


ELECTRICAL CHARACTERISTICS (TA = 25°C)

	Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
Diode	Forward Voltage	VF	IF = 10 mA		1.17	1.4	V
	Reverse Current	lR	V _R = 5 V			5	μΑ
	Terminal Capacitance	Ct	V = 0 V, f = 1.0 MHz		50		pF
Transistor	Collector to Emitter Dark Current	Iceo	VcE = 40 V, IF = 0 mA			400	nA
Coupled	Current Transfer Ratio	CTR	IF = 1 mA, VCE = 2 VDC	200	2 000		%
	Collector Saturation Voltage	VCE (sat)	IF = 1 mA, Ic = 2 mA			1.0	V
	Isolation Resistance	R _{I-O}	Vi-o = 1.0 kVDC	10 ¹¹			Ω
	Isolation Capacitance	C _{I-O}	V = 0 V, f = 1.0 MHz		0.5		pF
	Rise Time ¹²	t r	Vcc = 10 V, Ic = 10 mA, R _L = 100 Ω		100		μs
	Fall Time'2	tf			100		

*1 CTR rank


K : 2 000 to (%) L : 700 to 3 400 (%) M : 200 to 1 000 (%)

*2 Test circuit for switching time




TYPICAL CHARACTERISTICS (TA = 25°C, unless otherwise specified)






FORWARD CURRENT vs.




COLLECTOR TO EMITTER DARK CURRENT vs. AMBIENT TEMPERATURE




Remark The graphs indicate nominal characteristics.


TRANSISTOR POWER DISSIPATION vs. AMBIENT TEMPERATURE




COLLECTOR CURRENT vs. COLLECTOR TO EMITTER VOLTAGE




COLLECTOR CURRENT vs. COLLECTOR SATURATION VOLTAGE




NORMALIZED CURRENT TRANSFER RATIO vs. AMBIENT TEMPERATURE



SWITCHING TIME vs. LOAD RESISTANCE




SWITCHING TIME vs. LOAD RESISTANCE




Remark The graphs indicate nominal characteristics.


CURRENT TRANSFER RATIO vs. FORWARD CURRENT



CURRENT TRANSFER RATIO vs. FORWARD CURRENT




FREQUENCY RESPONSE




LONG TERM CTR DEGRADATION 1.2 $I_F = 1 \text{ mA}$ 1.0 CTR (Relative Value) T_A = 25°C 8.0 T_A = 60°C 0.6 0.4 0.2 10⁴ 10⁵ 10 10² 10³ 10⁶ Time (Hr)

Remark The graph indicates nominal characteristics.

<R> TAPING SPECIFICATIONS (UNIT: mm)





NOTES ON HANDLING

1. Recommended soldering conditions

(1) Infrared reflow soldering

Peak reflow temperature
 260°C or below (package surface temperature)


Time of peak reflow temperature
 Time of temperature higher than 220°C
 10 seconds or less
 60 seconds or less

Time to preheat temperature from 120 to 180°C 120±30 s
 Number of reflows Three

Flux
 Rosin flux containing small amount of chlorine (The flux with a

maximum chlorine content of 0.2 Wt% is recommended.)

Recommended Temperature Profile of Infrared Reflow



(2) Wave soldering

• Temperature 260°C or below (molten solder temperature)

• Time 10 seconds or less

Preheating conditions 120°C or below (package surface temperature)

Number of times
 One (Allowed to be dipped in solder including plastic mold portion.)

• Flux Rosin flux containing small amount of chlorine (The flux with a maximum chlorine

content of 0.2 Wt% is recommended.)

(3) Soldering by soldering iron

Peak temperature (lead part temperature) 350°C or below
 Time (each pins) 3 seconds or less

Flux
 Rosin flux containing small amount of chlorine (The flux with a

maximum chlorine content of 0.2 Wt% is recommended.)

(a) Soldering of leads should be made at the point 1.5 to 2.0 mm from the root of the lead.

(b) Please be sure that the temperature of the package would not be heated over 100°C.

(4) Cautions

Fluxes

Avoid removing the residual flux with freon-based and chlorine-based cleaning solvent.

2. Cautions regarding noise

Be aware that when voltage is applied suddenly between the photocoupler's input and output or between collector-emitters at startup, the output transistor may enter the on state, even if the voltage is within the absolute maximum ratings.

3. Measurement conditions of current transfer ratios (CTR), which differ according to photocoupler

Check the setting values before use, since the forward current conditions at CTR measurement differ according to product.

When using products other than at the specified forward current, the characteristics curves may differ from the standard curves due to CTR value variations or the like. Therefore, check the characteristics under the actual operating conditions and thoroughly take variations or the like into consideration before use.

USAGE CAUTIONS

- 1. Protect against static electricity when handling.
- 2. Avoid storage at a high temperature and high humidity.

<R> SPECIFICATION OF VDE MARKS LICENSE DOCUMENT

Parameter	Symbol	Speck	Unit
Climatic test class (IEC 60068-1/DIN EN 60068-1)		55/100/21	
Dielectric strength maximum operating isolation voltage Test voltage (partial discharge test procedure a for type test and random test) $U_{pr} = 1.5 \times U_{IORM}$, $P_d < 5 \ pC$	UIORM Upr	890 1 335	V _{peak} V _{peak}
Test voltage (partial discharge test procedure b for all devices test) $U_{pr} = 1.875 \times U_{\text{IORM}}, P_{\text{d}} < 5 \; \text{pC}$	Upr	1 669	Vpeak
Highest permissible overvoltage	Utr	8 000	V _{peak}
Degree of pollution (DIN EN 60664-1 VDE0110 Part 1)		2	
Comparative tracking index (IEC 60112/DIN EN 60112 (VDE 0303 Part 11))	СТІ	175	
Material group (DIN EN 60664-1 VDE0110 Part 1)		III a	
Storage temperature range	Tstg	-55 to +150	°C
Operating temperature range	TA	-55 to +100	°C
Isolation resistance, minimum value $V_{IO} = 500 \ V \ dc \ at \ T_A = 25 \ ^{\circ}C$ $V_{IO} = 500 \ V \ dc \ at \ T_A \ MAX. \ at \ least \ 100 \ ^{\circ}C$	Ris MIN. Ris MIN.	10 ¹² 10 ¹¹	Ω Ω
Safety maximum ratings (maximum permissible in case of fault, see thermal derating curve) Package temperature	Tsi	175	°C
Current (input current I _F , Psi = 0) Power (output or total power dissipation)	lsi Psi	400 700	mA mW
Isolation resistance $V_{IO} = 500 \text{ V}$ dc at $T_A = 175 ^{\circ}\text{C}$ (Tsi)	Ris MIN.	10°	Ω

Caution

GaAs Products

This product uses gallium arsenide (GaAs).

GaAs vapor and powder are hazardous to human health if inhaled or ingested, so please observe the following points.

- Follow related laws and ordinances when disposing of the product. If there are no applicable laws and/or ordinances, dispose of the product as recommended below.
 - Commission a disposal company able to (with a license to) collect, transport and dispose of materials that contain arsenic and other such industrial waste materials.
- 2. Exclude the product from general industrial waste and household garbage, and ensure that the product is controlled (as industrial waste subject to special control) up until final disposal.
- Do not burn, destroy, cut, crush, or chemically dissolve the product.
- Do not lick the product or in any way allow it to enter the mouth.

NOTICE

- 1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. California Eastern Laboratories and Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
- 2. California Eastern Laboratories has used reasonable care in preparing the information included in this document, but California Eastern Laboratories does not warrant that such information is error free. California Eastern Laboratories and Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
- 3. California Eastern Laboratories and Renesas Electronics do not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of California Eastern Laboratories or Renesas Electronics or others.
- 4. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part. California Eastern Laboratories and Renesas Electronics assume no responsibility for any losses incurred by you or third parties arising from such alteration, modification, copy or otherwise misappropriation of Renesas Electronics product.
- 5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below. "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots etc. "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; and safety equipment etc. Renesas Electronics products are neither intended nor authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems, surgical implantations etc.), or may cause serious property damages (nuclear reactor control systems, military equipment etc.). You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application for which it is not intended. California Eastern Laboratories and Renesas Electronics product for which the product is not intended by California Eastern Laboratories or Renesas Electronics.
- 6. You should use the Renesas Electronics products described in this document within the range specified by California Eastern Laboratories, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. California Eastern Laboratories shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
- 7. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or systems manufactured by you.
- 8. Please contact a California Eastern Laboratories sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. California Eastern Laboratories and Renesas Electronics assume no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
- 9. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You should not use Renesas Electronics products or technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. When exporting the Renesas Electronics products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations.
- 10. It is the responsibility of the buyer or distributor of California Eastern Laboratories, who distributes, disposes of, or otherwise places the Renesas Electronics product with a third party, to notify such third party in advance of the contents and conditions set forth in this document, California Eastern Laboratories and Renesas Electronics assume no responsibility for any losses incurred by you or third parties as a result of unauthorized use of Renesas Electronics products.
- 11. This document may not be reproduced or duplicated in any form, in whole or in part, without prior written consent of California Eastern Laboratories.
- 12. Please contact a California Eastern Laboratories sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.
- NOTE 1: "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.
- NOTE 2: "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.
- NOTE 3: Products and product information are subject to change without notice.

CEL Headquarters • 4590 Patrick Henry Drive, Santa Clara, CA 95054 • Phone (408) 919-2500 • www.cel.com

For a complete list of sales offices, representatives and distributors,
Please visit our website: www.cel.com/contactus