REF3212, REF3220 REF3225. REF3230

REF3225, REF3230 REF3233, REF3240

SBVS058C -JUNE 2005-REVISED AUGUST 2011

4ppm/°C, 100µA, SOT23-6 SERIES VOLTAGE REFERENCE

Check for Samples: REF3212, REF3220, REF3225, REF3230, REF3233, REF3240

FEATURES

www.ti.com

• Excellent Specified Drift Performance:

7ppm/°C (max) at 0°C to +125°C

20ppm/°C (max) at -40°C to +125°C

Microsize Package: SOT23-6High Output Current: ±10mA

High Accuracy: 0.01%

Low Quiescent Current: 100µA

Low Dropout: 5mV


APPLICATIONS

Portable Equipment

· Data Acquisition Systems

Medical Equipment

Test Equipment



DESCRIPTION

The REF32xx is a very low drift, micropower, low-dropout, precision voltage reference family available in the tiny SOT23-6 package.

The small size and low power consumption ($120\mu A$ max) of the REF32xx make it ideal for portable and battery-powered applications. This reference is stable with any capacitive load.

The REF32xx can be operated from a supply as low as 5mV above the output voltage, under no load conditions. All models are specified for the wide temperature range of -40°C to $+125^{\circ}\text{C}$.

AVAILABLE OUTPUT VOLTAGES

| PRODUCT | VOLTAGE |
|---------|---------|
| REF3212 | 1.25V |
| REF3220 | 2.048V |
| REF3225 | 2.5V |
| REF3230 | 3.0V |
| REF3233 | 3.3V |
| REF3240 | 4.096 |

All trademarks are the property of their respective owners.





This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

PACKAGE INFORMATION(1)

| PRODUCT | OUTPUT VOLTAGE | PACKAGE-LEAD | PACKAGE DESIGNATOR | PACKAGE MARKING |
|---------|----------------|--------------|-----------------------|-----------------|
| REF3212 | 1.25V | SOT23-6 | DBV | R32A |
| REF3220 | 2.048V | SOT23-6 | DBV | R32B |
| REF3225 | 2.5V | SOT23-6 | DBV | R32C |
| REF3230 | 3.0V | SOT23-6 | DBV | R32D |
| REF3233 | 3.3V | SOT23-6 | DBV | R32E |
| REF3240 | 4.096 | SOT23-6 | DBV | R32F |

⁽¹⁾ For the most current package and ordering information see the Package Option Addendum at the end of this document, or visit the device product folder at www.ti.com.

ABSOLUTE MAXIMUM RATINGS(1)

Over operating free-air temperature range (unless otherwise noted).

| | | REF32xx | UNIT |
|-----------------------|----------------------------|-------------|------|
| Input voltage | | +7.5 | V |
| Output short-cir | cuit | Continuous | |
| Operating temperature | | -55 to +135 | °C |
| Storage temperature | | -65 to +150 | °C |
| Junction tempe | rature | +150 | °C |
| | Human body model (HBM) | 4 | kV |
| ESD ratings | Charged device model (CDM) | 1 | kV |
| | Machine model (MM) | 400 | V |

⁽¹⁾ Stresses above these ratings may cause permanent damage. Exposure to absolute maximum conditions for extended periods may degrade device reliability. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those specified is not implied.

PIN CONFIGURATION

DBV PACKAGE SOT23-6 (TOP VIEW)



NOTE:: The location of pin 1 on the REF32xx is determined by orienting the package marking as shown in the diagram above.

PIN DESCRIPTIONS

| PIN | | | |
|--------|-----|---------------|--|
| NAME | NO. | FUNCTION | DESCRIPTION |
| ENABLE | 3 | Digital input | This pin enables and disables the device |
| GND_F | 1 | Analog output | Ground connection of the device |
| GND_S | 2 | Analog input | Ground sense at the load |
| IN | 4 | Analog input | Positive supply voltage |
| OUT_F | 6 | Analog output | Output of Reference Voltage |
| OUT_S | 5 | Analog input | Sense connection at the load |





ELECTRICAL CHARACTERISTICS

Boldface limits apply over the listed temperature range.

At $T_A = +25$ °C, $I_{LOAD} = 0$ mA, and $V_{IN} = 5$ V, unless otherwise noted.

| | | RE | F32xx | | | |
|----------------------------------|-------------------|--------|-------|--------|----------------------|--|
| PARAMETER | CONDITIONS | MIN | TYP | MAX | UNIT | |
| | REF3212 (1.25V) | | | | | |
| OUTPUT VOLTAGE, V _{OUT} | | 1.2475 | 1.25 | 1.2525 | V | |
| Initial accuracy | | -0.2 | 0.01 | 0.2 | % | |
| NOISE | | | | | | |
| Output voltage noise | f = 0.1Hz to 10Hz | | 17 | | μV_{PP} | |
| Voltage noise | f = 10Hz to 10kHz | | 24 | | μV_{RMS} | |
| | REF3220 (2.048V) | | | | | |
| OUTPUT VOLTAGE, V _{OUT} | | 2.044 | 2.048 | 2.052 | V | |
| Initial accuracy | | -0.2 | 0.01 | 0.2 | % | |
| NOISE | | | | | | |
| Output voltage noise | f = 0.1Hz to 10Hz | | 27 | | μV_{PP} | |
| Voltage noise | f = 10Hz to 10kHz | | 39 | | μV_{RMS} | |
| | REF3225 (2.5V) | | | | | |
| OUTPUT VOLTAGE, V _{OUT} | | 2.495 | 2.50 | 2.505 | V | |
| Initial accuracy | | -0.2 | 0.01 | 0.2 | % | |
| NOISE | | | | | | |
| Output voltage noise | f = 0.1Hz to 10Hz | | 33 | | μV_{PP} | |
| Voltage noise | f = 10Hz to 10kHz | | 48 | | μV_{RMS} | |
| | REF3230 (3V) | | | | | |
| OUTPUT VOLTAGE, V _{OUT} | | 2.994 | 3 | 3.006 | V | |
| Initial accuracy | | -0.2 | 0.01 | 0.2 | % | |
| NOISE | | | | | | |
| Output voltage noise | f = 0.1Hz to 10Hz | | 39 | | μV_{PP} | |
| Voltage noise | f = 10Hz to 10kHz | | 57 | | μV_{RMS} | |
| | REF3233 (3.3V) | | | | | |
| OUTPUT VOLTAGE, V _{OUT} | | 3.293 | 3.3 | 3.307 | V | |
| Initial accuracy | | -0.2 | 0.01 | 0.2 | % | |
| NOISE | | | | | | |
| Output voltage noise | f = 0.1Hz to 10Hz | | 43 | | μV_{PP} | |
| Voltage noise | f = 10Hz to 10kHz | | 63 | | μV_{RMS} | |
| | REF3240 (4.096V) | . " | | 1 | | |
| OUTPUT VOLTAGE, V _{OUT} | | 4.088 | 4.096 | 4.104 | V | |
| Initial accuracy | | -0.2 | 0.01 | 0.2 | % | |
| NOISE | | | | | | |
| Output voltage noise | f = 0.1Hz to 10Hz | | 53 | | μV_{PP} | |
| Voltage noise | f = 10Hz to 10kHz | | 78 | | μV_{RMS} | |



ELECTRICAL CHARACTERISTICS (continued)

Boldface limits apply over the listed temperature range.

At $T_A = +25$ °C, $I_{LOAD} = 0$ mA, and $V_{IN} = 5$ V, unless otherwise noted.

| | | | R | EF32xx | | |
|--------------------------------|-----------------------|---|--|--------|----------|------------|
| PARAMETER | | CONDITIONS | MIN | TYP | MAX | UNIT |
| | REF32 | 12 / REF3220 / REF3225 / REF3230 / REF3233 / | REF3240 | | <u>.</u> | |
| OUTPUT VOLTAGE TEMP DRIFT | dV _{OUT} /dT | | | | | |
| | | $0^{\circ}C \leq T_{A} \leq +125^{\circ}C$ | | 4 | 7 | ppm/°C |
| | | -40°C ≤ T _A ≤ +125°C | | 10.5 | 20 | ppm/°C |
| LONG-TERM STABILITY | | 0 to 1000h | | 55 | | ppm |
| LINE REGULATION | | $V_{OUT} + 0.05^{(1)} \le V_{IN} \le 5.5V$ | -65 | 15 | +65 | ppm/V |
| LOAD REGULATION ⁽²⁾ | dV_{OUT}/dI_{LOAD} | | | | | |
| Sourcing | | $0mA < I_{LOAD} < 10mA, V_{IN} = V_{OUT} + 250mV^{(1)}$ | -40 | 3 | 40 | μV/mA |
| Sinking | | $-10\text{mA} < I_{LOAD} < 0\text{mA}, V_{IN} = V_{OUT} + 100\text{mV}^{(1)}$ | -60 | 20 | 60 | μV/mA |
| THERMAL HYSTERESIS (3) | dT | | | | | |
| First cycle | | | | 100 | | ppm |
| Additional cycles | | | | 25 | | ppm |
| DROPOUT VOLTAGE ⁽¹⁾ | $V_{IN} - V_{OUT}$ | 0°C ≤ T _A ≤ +125°C | | 5 | 50 | mV |
| OUTPUT CURRENT | I _{LOAD} | $V_{IN} = V_{OUT} + 250 \text{mV}^{(1)}$ | -10 | | 10 | mA |
| SHORT-CIRCUIT CURRENT | I _{sc} | | | | | |
| Sourcing | | | | 50 | | mA |
| Sinking | | | | 40 | | mA |
| TURN-ON SETTLING TIME | | To 0.1% at $V_{IN} = 5V$ with $C_L = 0$ | | 60 | | μs |
| ENABLE/SHUTDOWN(4) | | | | | | |
| | V_L | Reference in Shutdown mode | 0 | | 0.7 | V |
| | V_{H} | Reference is active | 1.5 | | V_{IN} | V |
| POWER SUPPLY | | I _L = 0 | | | | |
| Voltage | V_{IN} | | V _{OUT} + 0.05 ⁽¹⁾ | | 5.5 | V |
| Current | ΙQ | ENABLE > 1.5V | | 100 | 120 | μΑ |
| Over temperature | | 0°C ≤ T _A ≤ +125°C | | 115 | 135 | μ Α |
| Shutdown | Is | ENABLE < 0.7V | | 0.1 | 1 | μΑ |
| TEMPERATURE RANGE | - | | | | | |
| Specified | | | -40 | | +125 | °C |
| Operating | | | -55 | | +135 | °C |
| Storage | | | -65 | | +150 | °C |
| Thermal resistance, SOT23-6 | θ_{JA} | | | 200 | | °C/W |

The minimum supply voltage for the REF3212 is 1.8V.

Load regulation is using force and sense lines; see the *Load Regulation* section for more information. Thermal hysteresis procedure is explained in more detail in the Applications Information TBD section.

If the rise time of the input voltage is less than or equal to 2ms, the ENABLE and IN pins can be tied together. For rise times greater than 2ms, see the *Supply Voltage* section.



TYPICAL CHARACTERISTICS

At $T_A = +25$ °C, $I_{LOAD} = 0$ mA, $V_{IN} = +5$ V power supply, and REF3225 used for typical characteristics, unless otherwise noted.




Figure 1.




Figure 2.






Figure 3.




Figure 4.

Load Current (mA)

QUIESCENT CURRENT vs TEMPERATURE




Figure 5.

POWER-SUPPLY REJECTION RATIO vs FREQUENCY




Figure 6.



TYPICAL CHARACTERISTICS (continued)

At $T_A = +25$ °C, $I_{LOAD} = 0$ mA, $V_{IN} = +5$ V power supply, and REF3225 used for typical characteristics, unless otherwise noted.

OUTPUT VOLTAGE vs INPUT VOLTAGE (REF3212)




Figure 7.

2.505 2.504

OUTPUT VOLTAGE vs LOAD CURRENT




Figure 8.

0.1Hz TO 10Hz NOISE




Figure 9.

OUTPUT VOLTAGE INITIAL ACCURACY




Figure 10.

STEP RESPONSE C_L = 0pF, 5V STARTUP




Figure 11.

STEP RESPONSE




Figure 12.



TYPICAL CHARACTERISTICS (continued)

At $T_A = +25$ °C, $I_{LOAD} = 0$ mA, $V_{IN} = +5$ V power supply, and REF3225 used for typical characteristics, unless otherwise noted.




Figure 13.





Figure 14.






Figure 15.




Figure 16.

LOAD TRANSIENT $C_L = 0$ pF, ± 1 mA OUTPUT PULSE




Figure 17.





Figure 18.

TYPICAL CHARACTERISTICS (continued)

At $T_A = +25$ °C, $I_{LOAD} = 0$ mA, $V_{IN} = +5$ V power supply, and REF3225 used for typical characteristics, unless otherwise noted.



THEORY OF OPERATION

GENERAL DESCRIPTION

The REF32xx is a family of CMOS, precision bandgap voltage references. Figure 20 shows the basic bandgap topology. Transistors Q_1 and Q_2 are biased so that the current density of Q_1 is greater than that of Q_2 . The difference of the two base-emitter voltages (Vbe₁ – Vbe₂) has a positive temperature coefficient and is forced across resistor R_1 . This voltage is amplified and added to the base-emitter voltage of Q_2 , which has a negative temperature coefficient. The resulting output voltage is virtually independent of temperature.




Figure 20. Simplified Schematic of Bandgap Reference

APPLICATION INFORMATION

The REF32xx does not require a load capacitor and is stable with any capacitive load. Figure 21 shows typical connections required for operation of the REF32xx. A supply bypass capacitor of 0.47µF is recommended.




Figure 21. Typical Operating Connections for the RFF3225

SUPPLY VOLTAGE

The REF32xx family of references features an extremely low dropout voltage. With the exception of the REF3212, which has a minimum supply requirement of 1.8V, these references can be operated with a supply of only 5mV above the output voltage in an unloaded condition. For loaded conditions, a typical dropout voltage versus load is shown in the Typical Characteristic curves.



The REF32xx also features a low quiescent current of $100\mu A$, with a maximum quiescent current over temperature of just $135\mu A$. The quiescent current typically changes less than $2\mu A$ over the entire supply range, as shown in Figure 22.




Figure 22. Supply Current vs Supply Voltage

Supply voltages below the specified levels can cause the REF32xx to momentarily draw currents greater than the typical quiescent current. This momentary current draw can be prevented by using a power supply with a fast rising edge and low output impedance.

For optimal startup when the IN pin and ENABLE pin are tied together, keep the input voltage rise time less than or equal to 2ms. For rise times greater than 2ms, the ENABLE pin must be kept below 0.7V until the voltage at the IN pin has reached the minimum operating voltage. One way to control the voltage at the ENABLE pin is with an additional RC filter, such as that shown in Figure 23. The RC filter must hold the voltage at the ENABLE pin below the threshold voltage until the voltage at the input pin has reached the minimum operating voltage.




Figure 23. Application Circuit to Control the REF32xx ENABLE Pin

The RC filter in Figure 23 can be used as a starting point for the REF3240. The values for R_1 and C_1 have been calculated so that the voltage at the ENABLE pin reaches 0.7V after the input voltage has reached 4.15V; Table 1 lists these values. For output voltage options other than 4.096V, the RC filter can be made faster.

Table 1. Recommended R₁ and C₁ Values for the REF3240

| RISE TIME | R ₁ VALUE | C ₁ VALUE |
|-----------|----------------------|----------------------|
| 2ms | 150kΩ | 100nF |
| 5ms | 150kΩ | 220nF |
| 10ms | 330kΩ | 220nF |
| 20ms | 390kΩ | 330nF |
| 50ms | 680kΩ | 470nF |
| 100ms | 680kΩ | 1000nF |

In this document, rise time is defined as the time until an exponential input signal reaches 90% of its final voltage. For example, the 2ms value shown in Table 1 is valid for an end value of 5V.

If the input voltage has a different shape or the end value is not 5V, then the time until the minimum dropout voltage has been reached should be used to decide if the IN and ENABLE pins can be tied together. Table 2 lists these times.

Table 2. Minimum Dropout Voltage Times

| DEVICE | TIME |
|---------|-------|
| REF3212 | 0.4ms |
| REF3220 | 0.5ms |
| REF3225 | 0.7ms |
| REF3230 | 0.9ms |
| REF3233 | 1.0ms |
| REF3240 | 1.6ms |

Note that because the leakage current of the EN pin is in the range of a few nA, it can be disregarded in most applications.

SHUTDOWN

The REF32xx can be placed in a low-power mode by pulling the ENABLE/SHUTDOWN pin low. When in Shutdown mode, the output of the REF32xx becomes a resistive load to ground. The value of the load depends on the model, and ranges from approximately $100k\Omega$ to $400k\Omega.$



THERMAL HYSTERESIS

Thermal hysteresis for the REF32xx is defined as the change in output voltage after operating the device at +25°C, cycling the device through the specified temperature range, and returning to +25°C. It can be expressed as:

$$V_{HYST} = \left(\frac{V_{PRE} - V_{POST}}{V_{NOM}}\right) \times 10^{6} (ppm)$$

Where:

 V_{HYST} = thermal hysteresis (in units of ppm).

 V_{NOM} = the specified output voltage.

V_{PRE} = output voltage measured at +25°C pretemperature cycling.

V_{POST} = output voltage measured after the device has been cycled through the specified temperature range of -40°C to +125°C and returned to +25°C. (1)

TEMPERATURE DRIFT

The REF32xx is designed to exhibit minimal drift error, which is defined as the change in output voltage over varying temperature. The drift is calculated using the box method, as described by Equation 2:

Drift =
$$\left(\frac{V_{OUTMAX} - V_{OUTMIN}}{V_{OUT} \times \text{Temp Range}}\right) \times 10^6 \text{(ppm)}$$
 (2)

The REF32xx features a typical drift coefficient of 4ppm/°C from 0°C to +125°C—the primary temperature range for many applications. For the extended industrial temperature range of -40°C to +125°C, the REF32xx family drift increases to a typical value of 10.5ppm/°C.

NOISE PERFORMANCE

Typical 0.1Hz to 10Hz voltage noise can be seen in the Typical Characteristic curve, 0.1Hz to 10Hz Voltage Noise. The noise voltage of the REF32xx increases with output voltage and operating temperature. Additional filtering can be used to improve output noise levels, although care should be taken to ensure the output impedance does not degrade AC performance.

LONG-TERM STABILITY

Long-term stability refers to the change of the output voltage of a reference over a period of months or years. This effect lessens as time progresses, as is shown by the long-term stability Typical Characteristic curves. The typical drift value for the REF32xx is 55ppm from 0 to 1000 hours. This parameter is characterized by measuring 30 units at regular intervals for a period of 1000 hours.

LOAD REGULATION

Load regulation is defined as the change in output voltage as a result of changes in load current. The load regulation of the REF32xx is measured using force and sense contacts, as shown in Figure 24.




Figure 24. Accurate Load Regulation of REF32xx

The force and sense lines can be used to effectively eliminate the impact of contact and trace resistance, resulting in accurate voltage at the load. By connecting the force and sense lines at the load, the REF32xx compensates for the contact and trace resistances because it measures and adjusts the voltage actually delivered at the load.

The GND_S pin is connected to the internal ground of the device through ESD protection diodes. Because of that connection, the maximum differential voltage between the GND_S and GND_F pins must be kept below 200mV to prevent these dioes from unintentionally turning on.




APPLICATION CIRCUITS

NEGATIVE REFERENCE VOLTAGE

For applications requiring a negative and positive reference voltage, the REF32xx and OPA735 can be used to provide a dual-supply reference from a ± 5 V supply. Figure 25 shows the REF3225 used to provide a ± 2.5 V supply reference voltage. The low drift performance of the REF32xx complements the low offset voltage and zero drift of the OPA735 to provide an accurate solution for split-supply applications. Care must be taken to match the temperature coefficients of R₁ and R₂.

DATA ACQUISITION

Data acquisition systems often require stable voltage references to maintain accuracy. The REF32xx family features stability and a wide range of voltages suitable for most microcontrollers and data converters. Figure 26, Figure 27, and Figure 28 show basic data acquisition systems.



NOTE:: Bypass capacitor is not shown.

Figure 25. REF3225 Combined with OPA735 to Create Positive and Negative Reference Voltages




Figure 26. Basic Data Acquisition System 1






Figure 27. Basic Data Acquisition System 2




Figure 28. REF3240 Provides an Accurate Reference for Driving the ADS8381





REVISION HISTORY

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

| CI | nanges from Revision B (February 2006) to Revision C | Page |
|----|---|------|
| • | Added Pin Descriptions table | 2 |
| • | Added note to Enable/Shutdown parameter | 4 |
| • | Changed the minimum voltage for Enable/Shutdown with reference active from (0.75 × V _{IN}) to 1.5 | 4 |
| • | Changed Current test condition from from (0.75 × V _{IN}) to (1.5V) | 4 |
| • | Added text, two tables, and one figure to Supply Voltage section | 8 |
| • | Changed pin 3 in Figure 24 from SHDN to ENABLE (typo) | 10 |
| • | Added paragraph to Load Regulation section | 10 |





30-Mar-2017

PACKAGING INFORMATION

| Orderable Device | Status | Package Type | Package Drawing | Pins | Package Qty | Eco Plan | Lead/Ball Finish | MSL Peak Temp | Op Temp (°C) | Device Marking (4/5) | Samples |
|------------------|--------|--------------|--------------------|------|----------------|----------------------------|------------------|---------------------|--------------|----------------------|---------|
| REF3212AIDBVR | ACTIVE | SOT-23 | DBV | 6 | 3000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-2-260C-1 YEAR | -40 to 125 | R32A | Samples |
| REF3212AIDBVT | ACTIVE | SOT-23 | DBV | 6 | 250 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-2-260C-1 YEAR | -40 to 125 | R32A | Samples |
| REF3212AIDBVTG4 | ACTIVE | SOT-23 | DBV | 6 | 250 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-2-260C-1 YEAR | -40 to 125 | R32A | Samples |
| REF3220AIDBVR | ACTIVE | SOT-23 | DBV | 6 | 3000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-2-260C-1 YEAR | -40 to 125 | R32B | Samples |
| REF3220AIDBVT | ACTIVE | SOT-23 | DBV | 6 | 250 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-2-260C-1 YEAR | -40 to 125 | R32B | Samples |
| REF3220AIDBVTG4 | ACTIVE | SOT-23 | DBV | 6 | 250 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-2-260C-1 YEAR | -40 to 125 | R32B | Samples |
| REF3225AIDBVR | ACTIVE | SOT-23 | DBV | 6 | 3000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-2-260C-1 YEAR | -40 to 125 | R32C | Samples |
| REF3225AIDBVRG4 | ACTIVE | SOT-23 | DBV | 6 | 3000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-2-260C-1 YEAR | -40 to 125 | R32C | Samples |
| REF3225AIDBVT | ACTIVE | SOT-23 | DBV | 6 | 250 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-2-260C-1 YEAR | -40 to 125 | R32C | Samples |
| REF3225AIDBVTG4 | ACTIVE | SOT-23 | DBV | 6 | 250 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-2-260C-1 YEAR | -40 to 125 | R32C | Samples |
| REF3230AIDBVR | ACTIVE | SOT-23 | DBV | 6 | 3000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-2-260C-1 YEAR | -40 to 125 | R32D | Samples |
| REF3230AIDBVRG4 | ACTIVE | SOT-23 | DBV | 6 | 3000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-2-260C-1 YEAR | -40 to 125 | R32D | Samples |
| REF3230AIDBVT | ACTIVE | SOT-23 | DBV | 6 | 250 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-2-260C-1 YEAR | -40 to 125 | R32D | Samples |
| REF3230AIDBVTG4 | ACTIVE | SOT-23 | DBV | 6 | 250 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-2-260C-1 YEAR | -40 to 125 | R32D | Samples |
| REF3233AIDBVR | ACTIVE | SOT-23 | DBV | 6 | 3000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-2-260C-1 YEAR | -40 to 125 | R32E | Samples |
| REF3233AIDBVRG4 | ACTIVE | SOT-23 | DBV | 6 | 3000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-2-260C-1 YEAR | -40 to 125 | R32E | Samples |
| REF3233AIDBVT | ACTIVE | SOT-23 | DBV | 6 | 250 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-2-260C-1 YEAR | -40 to 125 | R32E | Samples |



PACKAGE OPTION ADDENDUM

30-Mar-2017

| Orderable Device | Status | Package Type | _ | Pins | _ | Eco Plan | Lead/Ball Finish | MSL Peak Temp | Op Temp (°C) | Device Marking | Samples |
|------------------|--------|--------------|---------|------|------|----------------------------|------------------|---------------------|--------------|----------------|---------|
| | (1) | | Drawing | | Qty | (2) | (6) | (3) | | (4/5) | |
| REF3233AIDBVTG4 | ACTIVE | SOT-23 | DBV | 6 | 250 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-2-260C-1 YEAR | -40 to 125 | R32E | Samples |
| REF3240AIDBVR | ACTIVE | SOT-23 | DBV | 6 | 3000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-2-260C-1 YEAR | -40 to 125 | R32F | Samples |
| REF3240AIDBVRG4 | ACTIVE | SOT-23 | DBV | 6 | 3000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-2-260C-1 YEAR | -40 to 125 | R32F | Samples |
| REF3240AIDBVT | ACTIVE | SOT-23 | DBV | 6 | 250 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-2-260C-1 YEAR | -40 to 125 | R32F | Samples |
| REF3240AIDBVTG4 | ACTIVE | SOT-23 | DBV | 6 | 250 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-2-260C-1 YEAR | -40 to 125 | R32F | Samples |

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.

TBD: The Pb-Free/Green conversion plan has not been defined.

Pb-Free (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes. **Pb-Free** (RoHS Exempt): This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead/Ball Finish Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.



PACKAGE OPTION ADDENDUM

30-Mar-2017

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF REF3212, REF3220, REF3225, REF3230, REF3240:

Enhanced Product: REF3212-EP, REF3220-EP, REF3225-EP, REF3230-EP, REF3240-EP

NOTE: Qualified Version Definitions:

• Enhanced Product - Supports Defense, Aerospace and Medical Applications

DBV (R-PDSO-G6)

PLASTIC SMALL-OUTLINE PACKAGE



NOTES:

- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion. Mold flash and protrusion shall not exceed 0.15 per side.
- D. Leads 1,2,3 may be wider than leads 4,5,6 for package orientation.
- Falls within JEDEC MO-178 Variation AB, except minimum lead width.



DBV (R-PDSO-G6)

PLASTIC SMALL OUTLINE



NOTES:

- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Customers should place a note on the circuit board fabrication drawing not to alter the center solder mask defined pad.
- D. Publication IPC-7351 is recommended for alternate designs.
- E. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Example stencil design based on a 50% volumetric metal load solder paste. Refer to IPC-7525 for other stencil recommendations.



IMPORTANT NOTICE

Texas Instruments Incorporated (TI) reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete.

TI's published terms of sale for semiconductor products (http://www.ti.com/sc/docs/stdterms.htm) apply to the sale of packaged integrated circuit products that TI has qualified and released to market. Additional terms may apply to the use or sale of other types of TI products and services.

Reproduction of significant portions of TI information in TI data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such reproduced documentation. Information of third parties may be subject to additional restrictions. Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyers and others who are developing systems that incorporate TI products (collectively, "Designers") understand and agree that Designers remain responsible for using their independent analysis, evaluation and judgment in designing their applications and that Designers have full and exclusive responsibility to assure the safety of Designers' applications and compliance of their applications (and of all TI products used in or for Designers' applications) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to their applications, Designer has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any applications that include TI products, Designer will thoroughly test such applications and the functionality of such TI products as used in such applications.

TI's provision of technical, application or other design advice, quality characterization, reliability data or other services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using TI Resources in any way, Designer (individually or, if Designer is acting on behalf of a company, Designer's company) agrees to use any particular TI Resource solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

Designer is authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNER AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

Unless TI has explicitly designated an individual product as meeting the requirements of a particular industry standard (e.g., ISO/TS 16949 and ISO 26262), TI is not responsible for any failure to meet such industry standard requirements.

Where TI specifically promotes products as facilitating functional safety or as compliant with industry functional safety standards, such products are intended to help enable customers to design and create their own applications that meet applicable functional safety standards and requirements. Using products in an application does not by itself establish any safety features in the application. Designers must ensure compliance with safety-related requirements and standards applicable to their applications. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equipment includes, without limitation, all medical devices identified by the U.S. Food and Drug Administration as Class III devices and equivalent classifications outside the U.S.

TI may expressly designate certain products as completing a particular qualification (e.g., Q100, Military Grade, or Enhanced Product). Designers agree that it has the necessary expertise to select the product with the appropriate qualification designation for their applications and that proper product selection is at Designers' own risk. Designers are solely responsible for compliance with all legal and regulatory requirements in connection with such selection.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's non-compliance with the terms and provisions of this Notice.