


# Single-Supply, Fixed G = 2, High Speed, Video Amplifier with Charge Pump

### **Data Sheet**

## ADA4859-3

#### **FEATURES**

Integrated charge pump Supply range: 3 V to 5.5 V Output range: -3.3 V to -1.8 V 50 mA maximum output current at -3 V for external use **High speed amplifiers** -3 dB bandwidth: 195 MHz Slew rate: 740 V/µs 0.1 dB gain flatness: 60 MHz 0.1% settling time: 20 ns Low power Total quiescent current: 38 mA **Power-down feature** High input common-mode voltage range -1.8 V to +3.8 V at +5 V supply **Current feedback architecture** Differential gain error: 0.01% Differential phase error: 0.02° Available in 16-lead LFCSP



#### **APPLICATIONS**

Professional video Consumer video Imaging Active filters

#### **GENERAL DESCRIPTION**

The ADA4859-3 (triple) is a single-supply, high speed current feedback amplifier with an integrated charge pump that eliminates the need for negative supplies in order to output negative voltages or output a 0 V level for video applications. The 195 MHz, large signal -3 dB bandwidth at a fixed gain of 2, as well as the 740 V/µs slew rate, make this amplifier ideal for high resolution professional and consumer video applications. The amplifier also has a wide input common-mode voltage range that extends from 1.8 V below ground to 1.2 V below the positive rail at 5 V supply.

This triple video amplifier is designed to operate on supply voltages of 3.3 V to 5 V, using only 38 mA total quiescent current, including the charge pump. To further reduce the power consumption, it is equipped with a power-down feature that lowers the total supply current to as low as 2 mA when the amplifier is not being used. Even in power-down mode, the charge pump can be used to power external components. The maximum output current for external use is 50 mA at -3 V.

The ADA4859-3 is available in a 16-lead LFCSP, and it is designed to work over the industrial temperature range of  $-40^{\circ}$ C to  $+105^{\circ}$ C.

Rev. A

#### **Document Feedback**

Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.

One Technology Way, P.O. Box 9106, Norwood, MA 02062-9106, U.S.A. Tel: 781.329.4700 ©2008–2012 Analog Devices, Inc. All rights reserved. Technical Support www.analog.com

### TABLE OF CONTENTS

Features	. 1
Applications	. 1
Connection Diagram	. 1
General Description	. 1
Revision History	. 2
Specifications	. 3
Absolute Maximum Ratings	. 5
Maximum Power Dissipation	. 5
ESD Caution	. 5
Pin Configuration and Function Descriptions	. 6
Typical Performance Characteristics	. 7

### **REVISION HISTORY**

11/12—Rev. 0 to Rev. A	
Changes to Power-Down Section14	ŀ

11/08—Revision 0: Initial Version

Theory of Operation 1	2
Overview 1	2
Charge Pump Operation1	2
Applications Information1	3
Using the ADA4859-3 in Gains Equal to +1, -1 1	3
Video Line Driver 1	4
Power-Down 1	4
Layout Considerations1	4
Power Supply Bypassing1	4
Outline Dimensions 1	5
Ordering Guide1	5

### **SPECIFICATIONS**

 $\rm T_{A}$  = 25°C,  $\rm V_{S}$  = 5 V, G = 2,  $\rm R_{F}$  = 550  $\rm \Omega,$   $\rm R_{L}$  = 150  $\rm \Omega,$  unless otherwise noted.

#### Table 1.

Parameter	Conditions	Min	Тур	Max	Unit
DYNAMIC PERFORMANCE					
–3 dB Bandwidth	$V_{out} = 0.1 V p - p$		265		MHz
	$V_{OUT} = 2 V p - p$		195		MHz
Bandwidth for 0.1 dB Flatness	$V_{0 T} = 2 V p - p, C_1 = 6 pF$		60		MHz
Slew Rate	$V_{OUT} = 2 V \text{ step}$		740		V/µs
Settling Time to 0.1%	$V_{OUT} = 2 V \text{ step}$		20		ns
NOISE/DISTORTION PERFORMANCE					
Harmonic Distortion (HD2/HD3)	$f_{c} = 1 \text{ MHz}, V_{o} = 2 \text{ V p-p}$		-84/-93		dBc
	$f_c = 5 \text{ MHz}, V_o = 2 \text{ V p-p}$		-70/-83		dBc
Crosstalk	f = 5 MHz		-80		dBc
Total Output Noise	f = 1 MHz		17		nV/√Hz
Input Current Noise	f = 1 MHz		2		pA/√Hz
Differential Gain Error			0.01		%
Differential Phase Error			0.02		Degrees
DC PERFORMANCE					
Output Offset Voltage		-25	+9	+25	mV
+Input Bias Current		-2	+0.7	+2	μA
Closed-Loop Gain		1.9	2	2.1	V/V
INPUT CHARACTERISTICS					
Input Resistance	+IN		15		MΩ
Input Capacitance	+IN		1.5		рF
Input Common-Mode Voltage Range		-1.8		+3.8	V
OUTPUT CHARACTERISTICS					
Output Voltage Swing		-1.4 to +3.6	-1.7 to +3.8		V
Output Overdrive Recovery Time	Rise/fall, $f = 5 MHz$		15		ns
Maximum Linear Output Current @ $V_0 = 1 V_{PEAK}$	$f_c = 1 \text{ MHz}, \text{HD2} \le -50 \text{ dBc}$		19		mA
POWER-DOWN					
Input Voltage	Enabled		1.9		V
	Powered down		2		V
Bias Current		-0.1		+0.1	μA
Turn-On Time			0.5		μs
Turn-Off Time			2		μs
POWER SUPPLY					1
Operating Range		3		5.5	V
Total Quiescent Current					
Amplifier		15	17	21	mA
Charge Pump			21		mA
Total Quiescent Current When Powered Down					
Amplifier		0.15	0.25	0.3	mA
Charge Pump			4		mA
Positive Power Supply Rejection Ratio	Referred to output		-55	-50	dB
Negative Power Supply Rejection Ratio	Referred to output		-51	-47	dB
Charge Pump Output Voltage	-	-3.2	-3	-2.5	V
Charge Pump Sink Current				150	mA

 $\rm T_{A}$  = 25°C,  $\rm V_{S}$  = 3.3 V, G = 2,  $\rm R_{F}$  = 550  $\Omega,$   $\rm R_{L}$  = 150  $\Omega,$  unless otherwise noted.

#### Table 2.

Parameter	Conditions	Min	Тур	Max	Unit
DYNAMIC PERFORMANCE					
–3 dB Bandwidth	V <sub>out</sub> = 0.1 V p-p		260		MHz
	$V_{OUT} = 2 V p - p$		165		MHz
Bandwidth for 0.1 dB Flatness	$V_{OUT} = 2 V p - p, C_{L} = 6 pF$		65		MHz
Slew Rate	$V_{OUT} = 2 V$ step, $R_L = 150 \Omega$		530		V/µs
Settling Time to 0.1%	$V_{OUT} = 2 V \text{ step}$		20		ns
NOISE/DISTORTION PERFORMANCE					
Total Harmonic Distortion	$f_c = 1 \text{ MHz}, V_o = 2 \text{ V p-p}$		-84/-86		dBc
	$f_c = 5 \text{ MHz}, V_o = 2 \text{ V p-p}$		-73/-77		dBc
Crosstalk	f = 5 MHz		-80		dBc
Total Output Noise	f = 1 MHz		17		nV/√Hz
Input Current Noise	f = 1 MHz		2		pA/√Hz
Differential Gain Error			0.02		%
Differential Phase Error			0.03		Degrees
DC PERFORMANCE					
Output Offset Voltage		-25	+9	+25	mV
+Input Bias Current		-2	+0.7	+2	μA
Closed-Loop Gain		1.9	2	2.1	V/V
INPUT CHARACTERISTICS					
Input Resistance	+IN		15		MΩ
Input Capacitance	+IN		1.5		рF
Input Common-Mode Voltage Range		-0.9		+2.2	v
OUTPUT CHARACTERISTICS					
Output Voltage Swing		-0.7 to +2.1	-1 to +2.3		v
Output Overdrive Recovery Time	Rise/fall, $f = 5 MHz$		15		ns
Maximum Linear Output Current @ $V_0 = 1 V_{PEAK}$	$f_c = 1 \text{ MHz}, \text{HD2} \le -50 \text{ dBc}$		18		mA
POWER-DOWN					
Input Voltage	Enabled		1.25		v
	Powered down		1.35		v
Bias Current		-0.1		+0.1	μA
Turn-On Time			0.5		μs
Turn-Off Time			2		μs
POWER SUPPLY					1
Operating Range		3		5.5	v
Total Quiescent Current		5		5.5	
Amplifier		14	17	20	mA
Charge Pump			19		mA
Total Quiescent Current When Powered Down					
Amplifier		0.15	0.25	0.3	mA
Charge Pump		0.15	2	0.5	mA
Positive Power Supply Rejection Ratio	Referred to output		-54	-50	dB
Negative Power Supply Rejection Ratio	Referred to output		-54 -50	-30 -47	dB
Charge Pump Output Voltage		-2.1	-30 -2	-47 -1.8	V
Charge Pump Sink Current		-2.1	-2	-1.8 45	
Charge Pump Sink Current				40	mA

### **ABSOLUTE MAXIMUM RATINGS**

#### Table 3.

Parameter	Rating
Supply Voltage	6V
Internal Power Dissipation <sup>1</sup>	
16-Lead LFCSP	See Figure 2
Input Voltage (Common-Mode)	$(-V_{s} - 0.2 \text{ V})$ to $(+V_{s} - 1.8 \text{ V})$
Differential Input Voltage	±Vs
Output Short-Circuit Duration	Observe power derating curves
Storage Temperature Range	–65°C to +125°C
Operating Temperature Range	-40°C to +105°C
Lead Temperature (Soldering, 10 sec)	300°C

<sup>1</sup> Specification is for device in free air.

Stresses above those listed under Absolute Maximum Ratings may cause permanent damage to the device. This is a stress rating only; functional operation of the device at these or any other conditions above those indicated in the operational section of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

### MAXIMUM POWER DISSIPATION

The maximum power that can be safely dissipated by the ADA4859-3 is limited by the associated rise in junction temperature. The maximum safe junction temperature for plastic encapsulated devices is determined by the glass transition temperature of the plastic, approximately 150°C. Temporarily exceeding this limit may cause a shift in parametric performance due to a change in the stresses exerted on the die by the package. Exceeding a junction temperature of 175°C for an extended period can result in device failure.

To ensure proper operation, it is necessary to observe the maximum power derating curves in Figure 2.





Figure 2. Maximum Power Dissipation vs. Ambient Temperature

#### ESD CAUTION



**ESD** (electrostatic discharge) sensitive device. Charged devices and circuit boards can discharge without detection. Although this product features patented or proprietary protection circuitry, damage may occur on devices subjected to high energy ESD. Therefore, proper ESD precautions should be taken to avoid performance degradation or loss of functionality.

### **PIN CONFIGURATION AND FUNCTION DESCRIPTIONS**



### Table 4. Pin Function Descriptions

Pin No.	Mnemonic	Description
1	+V <sub>s</sub>	Positive Supply for Charge Pump.
2	C1_a	Charge Pump Capacitor Side a.
3	C1_b	Charge Pump Capacitor Side b.
4	СРО	Charge Pump Output.
5	+V <sub>s</sub>	Positive Supply.
6	+IN3	Noninverting Input 3.
7	-IN3	Inverting Input 3.
8	OUT3	Output 3.
9	PD	Power Down.
10	OUT2	Output 2.
11	-IN2	Inverting Input 2.
12	+IN2	Noninverting Input 2.
13	NC	No Connect.
14	+IN1	Noninverting Input 1.
15	-IN1	Inverting Input 1.
16	OUT1	Output 1.
17 (EPAD)	Exposed Pad (EPAD)	The exposed pad must be connected to the ground plane.

### **TYPICAL PERFORMANCE CHARACTERISTICS**

 $V_{s} = 5 V$ , G = 2,  $R_{F} = 550 \Omega$ ,  $R_{L} = 150 \Omega$ , large signal  $V_{OUT} = 2 V p$ -p, small signal  $V_{OUT} = 0.1 V p$ -p, and  $T = 25^{\circ}C$ , unless otherwise noted.




Figure 4. Small Signal Frequency Response vs. Supply Voltage





Figure 5. Large Signal 0.1 dB Flatness vs. Supply Voltage










Figure 7. Large Signal Frequency Response vs. Supply Voltage











### Data Sheet




Figure 16. Small Signal Transient Response vs. Capacitive Load





Figure 17. Small Signal Transient Response vs. Supply Voltage,  $C_L = 4 \, pF$ 









Figure 19. Large Signal Transient Response vs. Capacitive Load








ADA4859-3





Rev. A | Page 10 of 16

### **Data Sheet**

### ADA4859-3







# THEORY OF OPERATION


The ADA4859-3 is a fixed gain of two, current feedback amplifier designed for exceptional performance as a triple video amplifier. Its specifications make it especially suitable for SD and HD video applications. The ADA4859-3 provides HD video output on a single supply as low as 3.0 V while only consuming 13 mA per amplifier. It also features a power-down pin (PD) that reduces the quiescent current to 4 mA when activated.

The ADA4859-3 can be used in applications that require both ac- and dc-coupled inputs and outputs. The output stage on the ADA4859-3 is capable of driving 2 V p-p video signals into two doubly terminated video loads (150  $\Omega$  each) on a single 5 V supply. The input range of the ADA4859-3 includes ground, whereas the output range is limited by the output headroom set by the voltage drop across two diodes from each rail, which occurs 1.2 V from the positive and negative supply rails.

### **CHARGE PUMP OPERATION**

The on-board charge pump creates a negative supply for the amplifier. It provides different negative voltages depending on the power supply voltage. For a +5 V supply, the negative supply generated is equal to -3 V with 150 mA of output supply current, and for a +3.3 V supply, the negative supply is equal to -2 V with 45 mA of output supply current.

Figure 30 shows the charging cycle when the supply voltage,  $+V_s$ , charges C1 through  $\Phi_1$  to ground. During this cycle, C1 quickly charges to reach the  $+V_s$  voltage. The discharge cycle then begins with switching  $\Phi_1$  off and switching  $\Phi_2$  on, as shown in Figure 31. When C1 = C2, the charge in C1 is divided between the two capacitors and slowly increases the voltage in C2 until it reaches a predetermined voltage (-3 V for the +5 V supply and -2 V for the +3.3 V supply). The typical charge pump charging and discharging frequency is 550 kHz with a 150  $\Omega$  load and no input signal. This frequency changes with the load current, and it can get much slower if the amplifier is powered down and no external current is used.





The ADA4859-3 specifications make it especially suitable for SD and HD video applications. It also allows dc-coupled video signal with its black level set to 0 V and its sync tip down to -300 mV for YPbPr video.

The charge pump is always on, even when the power-down pin (PD) is enabled and the amplifier is off. However, it would be in an idle state if the negative current were not used. Each amplifier needs -6.3 mA of current, which totals -19 mA for all three amplifiers. This means additional negative current may be available by the charge pump for external use. Pin 4 (CPO) is the charge pump output, which provides access to the negative supply generated by the charge pump. Placing a 1  $\mu$ F charge capacitor at the CPO pin is essential to hold the charge and regulate the ripple.

If the negative supply is used to power another device in the system, it is only possible for the 5 V supply operation. In the 3.3 V supply operation, the charge pump output current is very limited. The capacitor at the CPO pin, which regulates the ripple of the negative voltage, can be used as a coupling capacitor for the external device. However, the charge pump current should be limited to a maximum of 50 mA for external use. When powering down the ADA4859-3, the charge pump is not affected and its output voltage and current remain available for external use.

### APPLICATIONS INFORMATION USING THE ADA4859-3 IN GAINS EQUAL TO +1, -1


The ADA4859-3 was designed to offer outstanding video performance, simplify applications, and minimize board area.

The ADA4859-3 is a triple amplifier with on-chip feedback and gain set resistors. The gain is fixed internally at G = +2. The inclusion of the on-chip resistors not only simplifies the design of the application but also eliminates six surface-mount resistors, saving valuable board space and lowering assembly costs. Although the ADA4859-3 has a fixed gain of G = +2, it can be used in other gain configurations, such as G = -1 and G = +1.

#### **Unity-Gain Operation**

#### **Option 1**

There are two options for obtaining unity gain (G = +1). The first is shown in Figure 32. In this configuration, the –IN input pin is tied to the output. (Feedback is provided through the two internal 550  $\Omega$  resistors in parallel), and the input is applied to the noninverting input. The noise gain for this configuration is 1.




#### **Option 2**

Another option exists for running the ADA4859-3 as a unitygain amplifier. In this configuration, the noise gain is +2, see Figure 33. The frequency response and transient response for this configuration closely match the gain of +2 plots because the noise gains are equal. This method does have twice the noise gain of Option 1; however, in applications that do not require low noise, Option 2 offers less peaking and ringing. By tying the inputs together, the net gain of the amplifier becomes +1. Equation 1 shows the transfer characteristic for the schematic shown in Figure 33.

$$V_{OUT} = V_{IN} \left( \frac{-R_F}{R_G} \right) + V_{IN} \left( \frac{R_F + R_G}{R_G} \right)$$
(1)

which simplifies to  $V_{OUT} = V_{IN}$ .



#### Inverting Unity-Gain Operation

In this configuration, the noninverting input is tied to ground and the input signal is applied to the inverting input. The noise gain for this configuration is +2, see Figure 34.





Figure 34. Inverting Configuration (G = -1)

Figure 35 shows the small signal frequency response for both gain of +1 (Option 1 and Option 2) and gain of -1 configurations. It is clear that the G = +1 Option 2 has better flatness and no peaking compared to Option 1.



#### **VIDEO LINE DRIVER**

The ADA4859-3 was designed to excel in video driver applications. Figure 36 shows a typical schematic for a video driver operating on bipolar supplies.




Figure 36. Video Driver Schematic

In applications that require multiple video loads be driven simultaneously, the ADA4859-3 can deliver. Figure 37 shows the ADA4859-3 configured with two video loads, and Figure 38 shows the large signal performance for multiple video loads.




Figure 37. Video Driver Schematic for Two Video Loads




Figure 38. Large Signal Frequency Response for Various Loads

#### **POWER-DOWN**

The ADA4859-3 is equipped with a PD (power-down) pin for all three amplifiers. This allows the user the ability to reduce the quiescent supply current when an amplifier is not active. The power-down threshold levels are derived from ground level. The amplifiers are powered down when the voltage applied to the PD pin is greater than a certain voltage from ground. In a 5 V supply application, the voltage is greater than 2 V, and in a 3.3 V supply application, the voltage is greater than 1.5 V. The amplifier is enabled whenever the PD pin is connected to ground. If the PD pin is not used, it is best to connect it to ground. Note that the power-down feature does not control the charge pump output voltage and current.

#### Table 5. Power-Down Voltage Control

Tuble 511 6 wer 2 6 wir voltage Control				
PD Pin	5 V	3.3 V		
Not Active	<1.5 V	<1 V		
Active	>2 V	>1.5 V		

#### LAYOUT CONSIDERATIONS

As is the case with all high speed applications, careful attention to printed circuit board (PCB) layout details prevents associated board parasitics from becoming problematic. Proper RF design technique is mandatory. The PCB should have a ground plane covering all unused portions of the component side of the board to provide a low impedance return path. Removing the ground plane on all layers from the area near the input and output pins reduces stray capacitance. Locate termination resistors and loads as close as possible to their respective inputs and outputs. Keep input and output traces as far apart as possible to minimize coupling (crosstalk) through the board. Adherence to microstrip or stripline design techniques for long signal traces (greater than about 1 inch) is recommended.

#### **POWER SUPPLY BYPASSING**

Careful attention must be paid to bypassing the power supply pins of the ADA4859-3. Use high quality capacitors with low equivalent series resistance (ESR), such as multilayer ceramic capacitors (MLCCs), to minimize supply voltage ripple and power dissipation. A large, usually tantalum, 10  $\mu$ F to 47  $\mu$ F capacitor located in proximity to the ADA4859-3 is required to provide good decoupling for lower frequency signals. In addition, locate 0.1 µF MLCC decoupling capacitors as close to each of the power supply pins as is physically possible, no more than 1/8-inch away. The ground returns should terminate immediately into the ground plane. Locating the bypass capacitor return close to the load return minimizes ground loops and improves performance.

### **OUTLINE DIMENSIONS**




Figure 39.16-Lead Lead Frame Chip Scale Package [LFCSP\_VQ] 4 mm × 4 mm Body, Very Thin Quad (CP-16-4) Dimensions shown in millimeters

#### **ORDERING GUIDE**

Model <sup>1</sup>	Temperature Range	Package Description	Package Option	Ordering Quantity
ADA4859-3ACPZ-R2	-40°C to +105°C	16-Lead LFCSP_VQ	CP-16-4	250
ADA4859-3ACPZ-R7	-40°C to +105°C	16-Lead LFCSP_VQ	CP-16-4	1,500
ADA4859-3ACPZ-RL	–40°C to +105°C	16-Lead LFCSP_VQ	CP-16-4	5,000
ADA4859-3ACP-EBZ		Evaluation Board		

<sup>1</sup> Z = RoHS Compliant Part.

### **Data Sheet**

### NOTES



www.analog.com

©2008–2012 Analog Devices, Inc. All rights reserved. Trademarks and registered trademarks are the property of their respective owners. D07715-0-11/12(A)