











TPS3803-01-Q1 TPS3803G15-Q1, TPS3805H33-Q1

SGLS228C - DECEMBER 2003 - REVISED SEPTEMBER 2015

TPS380x-Q1 Voltage Detectors

Features

- **Qualified for Automotive Applications**
- Single Voltage Detector (TPS3803): Adjustable and 1.5 V
- Dual Voltage Detector (TPS3805): Adjustable and
- High ±1.5% Threshold Voltage Accuracy
- Supply Current: 3 μ A Typical at $V_{DD} = 3.3 \text{ V}$
- Push/Pull Reset Output (TPS3805). Open-Drain Reset Output (TPS3803)
- Temperature Range: -40°C to 125°C
- 5-Pin SC-70 Package

Applications

- Applications Using DSPs, Microcontrollers, or Microprocessors
- Advanced Driver Assistance Systems
- Automotive Infotainment
- Automotive Cluster

3 Description

The TPS3803-Q1 and TPS3805-Q1 families of supervisory circuits provide circuit initialization and timing supervision, primarily for DSPs and processorbased systems.

The TPS3803G15-Q1 device has a fixed-sense threshold voltage V_{IT} set by an internal voltage divider, whereas the TPS3803-01-Q1 has an adjustable SENSE input that can be configured by two external resistors. In addition to the fixed sense threshold monitored at V_{DD}, the TPS3805-Q1 devices provide a second adjustable SENSE input. RESET is asserted in case either of the two voltages drops below V_{IT}.

During power on, RESET is asserted when supply voltage V_{DD} becomes higher than 0.8 V. Thereafter, the supervisory circuit monitors V_{DD} (and/or SENSE) and keeps RESET active as long as V_{DD} or SENSE remains below the threshold voltage VIT. As soon as V_{DD} (SENSE) rises above the threshold voltage V_{IT}, RESET is deasserted again. The product spectrum is designed for 1.5-V, 3.3-V, and adjustable supply voltages.

The devices are available in a 5-pin SC-70 package. The TPS3803-Q1 and TPS3805-Q1 devices are characterized for operation over a temperature range of -40°C to 125°C.

Device Information⁽¹⁾

| PART NUMBER | PACKAGE | BODY SIZE (NOM) |
|---------------|-----------|-------------------|
| TPS3803-01-Q1 | | |
| TPS3803G15-Q1 | SC-70 (5) | 2.00 mm × 1.25 mm |
| TPS3805H33-Q1 | | |

(1) For all available packages, see the orderable addendum at the end of the data sheet.

Typical Application Schematic






Table of Contents

| 1 | Features 1 | | 8.2 Functional Block Diagrams | 9 |
|---|--------------------------------------|----|--|----|
| 2 | Applications 1 | | 8.3 Feature Description | 9 |
| 3 | Description 1 | | 8.4 Device Functional Modes | 11 |
| 4 | Revision History2 | 9 | Application and Implementation | 12 |
| 5 | Device Comparison Table3 | | 9.1 Application Information | 12 |
| 6 | Pin Configuration and Functions | | 9.2 Typical Applications | 12 |
| 7 | Specifications4 | 10 | Power Supply Recommendations | 14 |
| • | 7.1 Absolute Maximum Ratings | 11 | Layout | 15 |
| | 7.1 Absolute Maximum Ratings | | 11.1 Layout Guidelines | |
| | 7.3 Recommended Operating Conditions | | 11.2 Layout Examples | 15 |
| | 7.4 Thermal Information | 12 | Device and Documentation Support | 17 |
| | 7.5 Electrical Characteristics 5 | | 12.1 Device Support | |
| | 7.6 Timing Requirements | | 12.2 Related Links | |
| | 7.7 Switching Characteristics | | 12.3 Community Resources | |
| | 7.8 Dissipation Ratings | | 12.4 Trademarks | |
| | 7.9 Typical Characteristics | | 12.5 Electrostatic Discharge Caution | 17 |
| 8 | Detailed Description9 | | 12.6 Glossary | |
| U | 8.1 Overview | 13 | Mechanical, Packaging, and Orderable Information | |

4 Revision History


NOTE: Page numbers for previous revisions may differ from page numbers in the current version.



5 Device Comparison Table

| DEVICE | THRESH | HOLD VOLTAGE | RESET OUTPUT TYPE |
|---------------|-----------------|--------------|-------------------|
| DEVICE | V _{DD} | SENSE | RESET OUTFOILITE |
| TPS3803-01-Q1 | NA | 1.226 V | Open-Drain |
| TPS3803G15-Q1 | 1.4 V | NA | Open-Drain |
| TPS3805H33-Q1 | 3.05 V | 1.226 V | Push-Pull |

6 Pin Configuration and Functions



NC - No connection

(1) SENSE on TPS3803-01, TPS3805H33 NC on TPS3803G15

Pin Functions

| PIN | | 1/0 | DESCRIPTION | |
|-----------------------|-----|-----|--|--|
| NAME | NO. | I/O | DESCRIPTION | |
| GND | 2 | I | Ground | |
| RESET | 3 | 0 | Active-low reset output (TPS3803-Q1: open drain, TPS3805-Q1: push/pull) | |
| SENSE | 5 | I | Adjustable sense input | |
| NC | 1 | _ | No internal connection | |
| NC (TPS3803G15-Q1) | 5 | _ | No internal connection | |
| V_{DD} | 4 | I | Input supply voltage, fixed sense input for TPS3803G15-Q1 and TPS3805-Q1 | |



7 Specifications

7.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)⁽¹⁾

| | | | MIN | MAX | UNIT |
|---------------------|----------------------------------|-----------------------------|-------------|--------------|------|
| V_{DD} | Supply voltage ⁽²⁾ | | 7 | 7 | V |
| | Voltage applied to all other pir | ns ⁽²⁾ | -0.3 | 7 | V |
| I_{OL} | Maximum low-level output cur | rent | | 5 | mA |
| I _{OH} | Maximum high-level output cu | rrent | | -5 | mA |
| I_{IK} | Input clamp current | $V_I < 0$ or $V_I > V_{DD}$ | | ±10 | mA |
| I_{OK} | Output clamp current | $V_O < 0$ or $V_O > V_{DD}$ | | ±10 | mA |
| P_{D} | Continuous total power dissipa | ation | See Dissipa | tion Ratings | |
| T_A | Operating free-air temperature | 9 | -40 | 125 | °C |
| T _{solder} | Soldering temperature | | | 260 | °C |
| T _{stg} | Storage temperature | | -65 | 150 | °C |

⁽¹⁾ Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

7.2 ESD Ratings

| | | | VALUE | UNIT |
|--|---|--|-------|------|
| V _(ESD) Electrostatic discharge | Electrostatic | Human body model (HBM), per AEC Q100-002 (1) | ±2000 | V |
| | discharge Charged-device model (CDM), per AEC | Charged-device model (CDM), per AEC Q100-011 | ±1000 | V |

⁽¹⁾ AEC Q100-002 indicates that HBM stressing shall be in accordance with the ANSI/ESDA/JEDEC JS-001 specification.

7.3 Recommended Operating Conditions

| | | MIN | MAX | UNIT |
|----------------|--------------------------------|-----|----------------|------|
| V_{DD} | Supply voltage | 1.3 | 6 | V |
| VI | Input voltage | 0 | $V_{DD} + 0.3$ | V |
| T _A | Operating free-air temperature | -40 | 125 | °C |

7.4 Thermal Information

| | w | TPS3803x-Q1 TPS3805x-Q1 | |
|-----------------------|--|----------------------------|------|
| | THERMAL METRIC ⁽¹⁾ | DCK (SC-70) | UNIT |
| | | 5 PINS | |
| $R_{\theta JA}$ | Junction-to-ambient thermal resistance | 246.6 | °C/W |
| $R_{\theta JC(top)}$ | Junction-to-case (top) thermal resistance | 68.2 | °C/W |
| $R_{\theta JB}$ | Junction-to-board thermal resistance | 78.4 | °C/W |
| Ψ_{JT} | Junction-to-top characterization parameter | 0.9 | °C/W |
| ΨЈВ | Junction-to-board characterization parameter | 77.7 | °C/W |
| R _{0JC(bot)} | Junction-to-case (bottom) thermal resistance | N/A | °C/W |

For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report, SPRA953.

⁽²⁾ All voltage values are with respect to GND. For reliable operation, the device should not be continuously operated at 7 V for more than t = 1000 h.



7.5 Electrical Characteristics

over operating free-air temperature range (unless otherwise noted)

| | PARAM | ETER | TEST CONDITIONS | MIN | TYP | MAX | UNIT | |
|-----------------|--|---------------------|--|-----------------------|-------|-------|-------|--|
| | | | $V_{DD} = 1.5 \text{ V}, I_{OH} = -0.5 \text{ mA}$ | | | | | |
| V_{OH} | High-level output voltag | e (TPS3805 only) | $V_{DD} = 3.3 \text{ V}, I_{OH} = -1 \text{ mA}$ | 0.8 × V _{DD} | | | V | |
| | | | $V_{DD} = 6 \text{ V}, I_{OH} = -1.5 \text{ mA}$ | | | | | |
| | | | $V_{DD} = 1.5 \text{ V}, I_{OL} = 1 \text{ mA}$ | | | | | |
| V_{OL} | Low-level output voltage | е | $V_{DD} = 3.3 \text{ V}, I_{OL} = 2 \text{ mA}$ | | | 0.3 | V | |
| | | | $V_{DD} = 6 \text{ V}, I_{OL} = 3 \text{ mA}$ | | | | | |
| | Power-up reset voltage | (1) | $V_{IT} > 1.5 \text{ V}, T_A = 25^{\circ}\text{C}$ | 0.8 | | | V | |
| | Power-up reset voltage | | $V_{IT} \le 1.5 \text{ V}, T_A = 25^{\circ}\text{C}$ | 1 | | | \ \ \ | |
| | Negative-going input threshold voltage (2) | SENSE | | 1.2 | 1.226 | 1.244 | | |
| V_{IT} | | TPS3803G15 | | 1.379 | 1.4 | 1.421 | V | |
| | | TPS3805H33 | | 3.004 | 3.05 | 3.096 | | |
| V | Lhustorooio | | 1.2 V < V _{IT} < 2.5 V | | 15 | | mV | |
| V_{hys} | Hysteresis | | 2.5 V < V _{IT} < 3.5 V | | 30 | | - mv | |
| I | Input current | SENSE | | -25 | | 25 | nA | |
| I _{OH} | High-level output current at RESET | Open drain only | $V_{DD} = V_{IT} + 0.2 \text{ V}, V_{OH} = V_{DD}$ | | | 300 | nA | |
| | | TPS3803-01 | V 22V Output upperpeted | | 2 | 4 | | |
| | Cupply gurrant | TPS3805, TPS3803G15 | V _{DD} = 3.3 V, Output unconnected | | 3 | 5 | μΑ | |
| I _{DD} | Supply current | TPS3803-01 | V 0V 0 1 1 | | 2 | 4 | | |
| | | TPS3805, TPS3803G15 | V _{DD} = 6 V, Output unconnected | | 4 | 6 | | |
| Cı | Input capacitance | | V _I = 0 V to V _{DD} | | 1 | | pF | |

7.6 Timing Requirements

 R_L = 1 MΩ, C_L = 50 pF, T_A = $-40^{\circ}C$ to 125°C (unless otherwise noted)

| | | | | MIN | MAX | UNIT |
|----------------|----------------|--------------------------|--|-----|-----|------|
| t _w | Pulse duration | V _{DD} SENSE | $V_{IH} = 1.05 \times V_{IT}, V_{IL} = 0.95 \times V_{IT}$ | 5.5 | | μs |

7.7 Switching Characteristics

 R_L = 1 M Ω , C_L = 50 pF, T_A = -40°C to 125°C (unless otherwise noted)

| | PARAMET | ER | TEST CONDITIONS | MIN | TYP | MAX | UNIT |
|------------------|--|--|--|-----|-----|-----|------|
| t _{PHL} | Propagation (delay) time, high-to-low-level output | V _{DD} to RESET delay SENSE to RESET delay | $V_{IH} = 1.05 \times V_{IT}, V_{IL} = 0.95 \times V_{IT}$ | | 5 | 100 | μs |
| t _{PLH} | Propagation (delay) time, low-to-high-level output | V _{DD} to RESET delay SENSE to RESET delay μΑ | $V_{IH} = 1.05 \times V_{IT}, V_{IL} = 0.95 \times V_{IT}$ | | 5 | 100 | μs |

7.8 Dissipation Ratings

| PACKAGE | POWER RATING | DERATING FACTOR | POWER RATING | POWER RATING |
|---------|-----------------------|-----------------------------|-----------------------|-----------------------|
| | T _A < 25°C | ABOVE T _A = 25°C | T _A = 70°C | T _A = 85°C |
| DCK | 321 mW | 2.6 mW/°C | 206 mW | 167 mW |

⁽¹⁾ The lowest supply voltage at which $\overline{\text{RESET}}$ ($V_{OL}(\text{max}) = 0.2 \text{ V}$, $I_{OL} = 50 \text{ µA}$) becomes active. $t_r(V_{DD}) \ge 15 \text{ µs/V}$. (2) To ensure the best stability of the threshold voltage, place a bypass capacitor (ceramic, 0.1-µF) near the supply terminals.





Figure 1. Timing Requirements



7.9 Typical Characteristics







Figure 2. TPS3805H33-Q1 Supply Current vs Supply Voltage

Figure 3. TPS3803-01-Q1 Supply Current vs Supply Voltage







Figure 4. Low-Level Output Voltage vs Low-Level Output Current

Figure 5. Low-Level Output Voltage vs Low-Level Output Current






Figure 6. Low-Level Output Voltage vs Low-Level Output Current

Figure 7. Low-Level Output Voltage vs Low-Level Output Current



Typical Characteristics (continued)




Figure 8. TPS3805H33-Q1 High-Level Output Voltage vs High-Level Output Current




Figure 9. TPS3805H33-Q1 High-Level Output Voltage vs High-Level Output Current




Figure 10. TPS3805H33-Q1 High-Level Output Voltage vs High-Level Output Current




Figure 11. TPS3805H33-Q1 High-Level Output Voltage vs High-Level Output Current




Figure 12. TPS3803-01-Q1 Normalized Input Threshold Voltage vs Free-Air Temperature At Sense




8 Detailed Description

8.1 Overview

The TPS380x-Q1 devices are low-current supervisory circuits used to monitor system voltages above 1.226 V. The devices assert an active low RESET signal when V_{DD} , SENSE, or both voltages drop below a preset threshold. The RESET output remains low until the V_{DD} , SENSE, or both voltages return above their thresholds. The devices are also designed to be immune to short negative transients on the V_{DD} and SENSE pins.

8.2 Functional Block Diagrams



8.3 Feature Description

8.3.1 V_{DD} and SENSE Monitoring

The V_{DD} and SENSE inputs provide a pin at which a system voltage can be monitored. If the voltage on this pin drops below V_{IT} , RESET is asserted low. The comparator has a built-in hysteresis to ensure smooth RESET assertions and de-assertions. Refer to the *Device Comparison Table* to determine the V_{DD} and SENSE voltage thresholds for each device. The adjustable version TPS3803-01-Q1 can be used to monitor any voltage rail down to 1.226 V using the circuit shown in Figure 13, where V_{IT} is the Vin threshold voltage.



Feature Description (continued)




Figure 13. Using Adjustable Version

8.3.2 Transient Immunity

The TPS380x-Q1 devices are immune to short negative transients on the V_{DD} and SENSE pins. Sensitivity to transients is dependent on threshold overdrive as shown in Figure 15 and Figure 16. These graphs show the duration that the transient is below V_{IT} compared to the magnitude of the voltage drop below V_{IT} , called the threshold overdrive voltage. Any combination of transient duration and overdrive voltage which lies above the curves will result in RESET being asserted low. Any transient which lies below the curves will be ignored by the device.




Figure 14. Overdrive Voltage




Figure 15. Minimum Pulse Duration at V_{DD} vs V_{DD} Threshold Overdrive Voltage




Figure 16. Minimum Pulse Duration at Sense vs Sense
Threshold Overdrive Voltage



8.4 Device Functional Modes

TPS3803-01-Q1 and TPS3803G15-Q1 monitor only one supply, which is SENSE and V_{DD} respectively. When that supply is above the V_{IT} threshold, RESET will be high. Otherwise, RESET will be low. TPS3805H33-Q1 monitors both V_{DD} and SENSE. When both V_{DD} and SENSE are above the V_{IT} threshold, RESET will be high. Otherwise, RESET will be low.

Table 1. Function and Truth Table

| TPS3803-01-Q1 | | | | | | | |
|-------------------------|-------|--|--|--|--|--|--|
| SENSE > V _{IT} | RESET | | | | | | |
| 0 | L | | | | | | |
| 1 | Н | | | | | | |

Table 2. Function and Truth Table

| TPS3803G15-Q1 | | | | | | |
|-------------------|-------|--|--|--|--|--|
| $V_{DD} > V_{IT}$ | RESET | | | | | |
| 0 | L | | | | | |
| 1 | Н | | | | | |

Table 3. Function and Truth Table

| TPS3805H33-Q1 | | | | | | | | |
|-------------------|-------------------------|-------|--|--|--|--|--|--|
| $V_{DD} > V_{IT}$ | SENSE > V _{IT} | RESET | | | | | | |
| 0 | 0 | L | | | | | | |
| 0 | 1 | L | | | | | | |
| 1 | 0 | L | | | | | | |
| 1 | 1 | Н | | | | | | |



9 Application and Implementation

NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

9.1 Application Information

The TPS380x-Q1 voltage supervisor devices are designed to assert an active-low \overline{RESET} signal when V_{DD} and/or SENSE drop below a voltage threshold V_{IT}. The \overline{RESET} signal remains low until the voltages return above their respective thresholds. The TPS3803G15-Q1 and TPS3805H33-Q1 are fixed-voltage options, while the TPS3803-01-Q1 is adjustable and can be used to monitor any voltage above 1.226 V. The TPS3803G15-Q1 and TPS3803-01-Q1 have an open-drain output, requiring an external pull-up on the \overline{RESET} line.

9.2 Typical Applications

9.2.1 TPS3803G15-Q1




Figure 17. TPS3803G15 Typical Application

9.2.1.1 Design Requirements

When a single 1.5-V supply rail needs to be monitored, TPS3803G15-Q1 should be used. When a single voltage higher than 1.226 V needs to be monitored, TPS3803-01-Q1 should be used. When a 3.3-V supply and second supply above 1.226 V needs to be monitored, TPS3805H33-Q1 should be used.

9.2.1.2 Detailed Design Procedure

To monitor a single 1.5-V supply with TPS3803G15-Q1, connect the 1.5-V supply directly to V_{DD} . The \overline{RESET} output should be connected to the reset of the microcontroller with a pull-up resistor from the \overline{RESET} output to V_{DD} .

To monitor a single supply using TPS3803-01-Q1, connect the supply to V_{DD} with a resistor divider to scale down the voltage at the SENSE pin. The resistor values must be chosen to satisfy Equation 1:

$$V_{IT}' = (1 + R1/R2) \times 1.226$$

where

• V_{IT} is the V_{DD} threshold voltage.

(1)


For example, if TPS3803-01-Q1 should monitor a 2.5-V supply and the desired threshold voltage is 2.2 V, R1 and R2 values could be 24 k Ω and 30- k Ω respectively. A 1-nf to 10-nF decoupling capacitor is recommended to be placed close to the SENSE input.



Typical Applications (continued)

To monitor two supplies using TPS3805H33-Q1, connect the 3.3-V supply directly to V_{DD} , and the second supply through a resistor divider to the SENSE pin. The SENSE pin should have a 1-nf to 10-nF decoupling capacitor close to the pin.

9.2.1.3 Application Curves



9.2.2 TPS3803-01-Q1




Figure 20. TPS3803-01-Q1 Typical Application

9.2.2.1 Design Requirements

Please refer to *Design Requirements* for this device's design requirements.



Typical Applications (continued)

9.2.3 TPS3805H33-Q1




Figure 21. TPS3805H33-Q1 Typical Application

9.2.3.1 Design Requirements

Please refer to *Design Requirements* for this device's design requirements.

10 Power Supply Recommendations

The TPS380x-Q1 devices are designed to operate from an input supply from 1.3 V to 6 V. TI recommends to place a $0.1-\mu F$ capacitor near the V_{DD} pin.




11 Layout

11.1 Layout Guidelines

TI recommends to place the 0.1- μ F decoupling capacitor close to the V_{DD} pin. The V_{DD} trace should be able to carry 6 μ A without a significant drop in voltage. Avoid a long trace from the SENSE pin to the resistor divider.

11.2 Layout Examples



Denotes GND Via

Figure 22. TPS3803G15-Q1 Layout Example




Figure 23. TPS3803-01-Q1 Layout Example



Layout Examples (continued)





Figure 24. TPS3805H33-Q1 Layout Example



12 Device and Documentation Support

12.1 Device Support

12.1.1 Device Nomenclature



12.2 Related Links

The table below lists quick access links. Categories include technical documents, support and community resources, tools and software, and quick access to sample or buy.

Table 4. Related Links

| PARTS | PRODUCT FOLDER | SAMPLE & BUY | TECHNICAL DOCUMENTS | TOOLS & SOFTWARE | SUPPORT & COMMUNITY |
|---------------|----------------|--------------|---------------------|---------------------|---------------------|
| TPS3803-01-Q1 | Click here | Click here | Click here | Click here | Click here |
| TPS3803G15-Q1 | Click here | Click here | Click here | Click here | Click here |
| TPS3805H33-Q1 | Click here | Click here | Click here | Click here | Click here |

12.3 Community Resources

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

TI E2E™ Online Community *TI's Engineer-to-Engineer (E2E) Community.* Created to foster collaboration among engineers. At e2e.ti.com, you can ask questions, share knowledge, explore ideas and help solve problems with fellow engineers.

Design Support *TI's Design Support* Quickly find helpful E2E forums along with design support tools and contact information for technical support.

12.4 Trademarks

E2E is a trademark of Texas Instruments.

All other trademarks are the property of their respective owners.

12.5 Electrostatic Discharge Caution



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

12.6 Glossary

SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.



13 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

Submit Documentation Feedback





22-Dec-2016

PACKAGING INFORMATION

| Orderable Device | Status | Package Type | _ | Pins | Package | Eco Plan | Lead/Ball Finish | MSL Peak Temp | Op Temp (°C) | Device Marking | Samples |
|-------------------|--------|--------------|---------|------|---------|----------------------------|----------------------------|--------------------|--------------|----------------|---------|
| | (1) | | Drawing | | Qty | (2) | (6) | (3) | | (4/5) | |
| 2T03-01QDCKRG4Q1 | ACTIVE | SC70 | DCK | 5 | 3000 | Green (RoHS & no Sb/Br) | CU NIPDAUAG | Level-1-260C-UNLIM | -40 to 125 | AWJ | Samples |
| 2T03G15QDCKRG4Q | ACTIVE | SC70 | DCK | 5 | 3000 | Green (RoHS & no Sb/Br) | CU NIPDAUAG | Level-1-260C-UNLIM | -40 to 125 | AXU | Samples |
| 2T05H33QDCKRG4Q | ACTIVE | SC70 | DCK | 5 | 3000 | Green (RoHS & no Sb/Br) | CU NIPDAU CU NIPDAUAG | Level-1-260C-UNLIM | -40 to 125 | AWZ | Samples |
| TPS3803-01QDCKRQ1 | ACTIVE | SC70 | DCK | 5 | 3000 | Green (RoHS & no Sb/Br) | CU NIPDAUAG | Level-1-260C-UNLIM | -40 to 125 | AWJ | Samples |
| TPS3803G15QDCKRQ1 | ACTIVE | SC70 | DCK | 5 | 3000 | Green (RoHS & no Sb/Br) | CU NIPDAU CU NIPDAUAG | Level-1-260C-UNLIM | -40 to 125 | AXU | Samples |
| TPS3805H33QDCKRQ1 | ACTIVE | SC70 | DCK | 5 | 3000 | Green (RoHS & no Sb/Br) | CU NIPDAU CU NIPDAUAG | Level-1-260C-UNLIM | -40 to 125 | AWZ | Samples |

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.

TBD: The Pb-Free/Green conversion plan has not been defined.

Pb-Free (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes. **Pb-Free** (RoHS Exempt): This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

(3) MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

(4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.



PACKAGE OPTION ADDENDUM

22-Dec-2016

(6) Lead/Ball Finish - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF TPS3803-01-Q1, TPS3803-Q1, TPS3805H33-Q1:

- Catalog: TPS3803-01, TPS3803, TPS3805H33
- Enhanced Product: TPS3803-01-EP, TPS3803-EP, TPS3805H33-EP

NOTE: Qualified Version Definitions:

- Catalog TI's standard catalog product
- Enhanced Product Supports Defense, Aerospace and Medical Applications

PACKAGE MATERIALS INFORMATION

www.ti.com 3-Aug-2017

TAPE AND REEL INFORMATION





| A0 | <u> </u> |
|----|---|
| B0 | Dimension designed to accommodate the component length |
| K0 | Dimension designed to accommodate the component thickness |
| W | Overall width of the carrier tape |
| P1 | Pitch between successive cavity centers |

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

| Device | Package Type | Package Drawing | | | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-------------------|-----------------|--------------------|---|------|--------------------------|--------------------------|------------|------------|------------|------------|-----------|------------------|
| TPS3803G15QDCKRQ1 | SC70 | DCK | 5 | 3000 | 180.0 | 8.4 | 2.47 | 2.3 | 1.25 | 4.0 | 8.0 | Q3 |

PACKAGE MATERIALS INFORMATION

www.ti.com 3-Aug-2017



*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Length (mm) | Width (mm) | Height (mm) |
|-------------------|--------------|-----------------|------|------|-------------|------------|-------------|
| TPS3803G15QDCKRQ1 | SC70 | DCK | 5 | 3000 | 202.0 | 201.0 | 28.0 |

DCK (R-PDSO-G5)

PLASTIC SMALL-OUTLINE PACKAGE



NOTES: A. All linear dimensions are in millimeters.

- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion. Mold flash and protrusion shall not exceed 0.15 per side.
- D. Falls within JEDEC MO-203 variation AA.



DCK (R-PDSO-G5)

PLASTIC SMALL OUTLINE



NOTES:

- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Customers should place a note on the circuit board fabrication drawing not to alter the center solder mask defined pad.
- D. Publication IPC-7351 is recommended for alternate designs.
- E. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Example stencil design based on a 50% volumetric metal load solder paste. Refer to IPC-7525 for other stencil recommendations.



IMPORTANT NOTICE

Texas Instruments Incorporated (TI) reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete.

TI's published terms of sale for semiconductor products (http://www.ti.com/sc/docs/stdterms.htm) apply to the sale of packaged integrated circuit products that TI has qualified and released to market. Additional terms may apply to the use or sale of other types of TI products and services.

Reproduction of significant portions of TI information in TI data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such reproduced documentation. Information of third parties may be subject to additional restrictions. Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyers and others who are developing systems that incorporate TI products (collectively, "Designers") understand and agree that Designers remain responsible for using their independent analysis, evaluation and judgment in designing their applications and that Designers have full and exclusive responsibility to assure the safety of Designers' applications and compliance of their applications (and of all TI products used in or for Designers' applications) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to their applications, Designer has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any applications that include TI products, Designer will thoroughly test such applications and the functionality of such TI products as used in such applications.

TI's provision of technical, application or other design advice, quality characterization, reliability data or other services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using TI Resources in any way, Designer (individually or, if Designer is acting on behalf of a company, Designer's company) agrees to use any particular TI Resource solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

Designer is authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNER AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

Unless TI has explicitly designated an individual product as meeting the requirements of a particular industry standard (e.g., ISO/TS 16949 and ISO 26262), TI is not responsible for any failure to meet such industry standard requirements.

Where TI specifically promotes products as facilitating functional safety or as compliant with industry functional safety standards, such products are intended to help enable customers to design and create their own applications that meet applicable functional safety standards and requirements. Using products in an application does not by itself establish any safety features in the application. Designers must ensure compliance with safety-related requirements and standards applicable to their applications. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equipment includes, without limitation, all medical devices identified by the U.S. Food and Drug Administration as Class III devices and equivalent classifications outside the U.S.

TI may expressly designate certain products as completing a particular qualification (e.g., Q100, Military Grade, or Enhanced Product). Designers agree that it has the necessary expertise to select the product with the appropriate qualification designation for their applications and that proper product selection is at Designers' own risk. Designers are solely responsible for compliance with all legal and regulatory requirements in connection with such selection.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's non-compliance with the terms and provisions of this Notice.