SGLS141A - DECEMBER 2002 - REVISED JANUARY 2007


- Qualified for Automotive Applications
- Customer-Specific Configuration Control Can Be Supported Along With Major-Change Approval
- ESD Protection Exceeds 2000 V Per MIL-STD-883, Method 3015; Exceeds 200 V Using Machine Model (C = 200 pF, R = 0)
- Supply Current of 220 nA (Typ)
- Precision Supply Voltage Supervision Range: 1.8 V, 2.5 V, 3.0 V, 3.3 V
- Power-On Reset Generator With Selectable Delay Time of 10 ms or 200 ms
- Push/Pull RESET Output (TPS3836), RESET Output (TPS3837), or Open-Drain RESET Output (TPS3838)
- Manual Reset
- 5-Pin SOT-23 Package
- Temperature Range: -40°C to 125°C


#### description

The TPS3836, TPS3837, TPS3838 families of supervisory circuits provide circuit initialization and timing supervision, primarily for DSP and processor-based systems.

Applications Include

- Applications Using Automotive Low-Power DSPs, Microcontrollers, or Microprocessors
- Battery-Powered Equipment
- Intelligent Instruments
- Wireless Communication Systems
- Automotive Systems





During power on,  $\overline{RESET}$  is asserted when the supply voltage  $V_{DD}$  becomes higher than 1.1 V. Thereafter, the supervisory circuit monitors  $V_{DD}$  and keeps  $\overline{RESET}$  output active as long as  $V_{DD}$  remains below the threshold voltage  $V_{IT}$ . An internal timer delays the return of the output to the inactive state (high) to ensure proper system reset. The delay time starts after  $V_{DD}$  has risen above the threshold voltage  $V_{IT}$ .

When CT is connected to GND a fixed delay time of typical 10 ms is asserted. When connected to  $V_{DD}$  the delay time is typically 200 ms.

When the supply voltage drops below the threshold voltage V<sub>IT</sub>, the output becomes active (low) again.

All the devices of this family have a fixed-sense threshold voltage V<sub>IT</sub> set by an internal voltage divider.

The TPS3836 has an active-low push-pull RESET output. The TPS3837 has active-high push-pull RESET, and TPS3838 integrates an active-low open-drain RESET output.




Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.



SGLS141A - DECEMBER 2002 - REVISED JANUARY 2007

#### description (continued)




The product spectrum is designed for supply voltages of 1.8 V, 2.5 V, 3 V, and 3.3 V. The circuits are available in a 5-pin SOT-23 package. The TPS3836-Q-Q1, TPS3837-Q-Q1, TPS3838-Q-Q1 families are characterized for operation over a temperature range of  $-40^{\circ}$ C to  $125^{\circ}$ C.

#### PACKAGE INFORMATION

T <sub>A</sub>	DEVICE NAME	THRESHOLD VOLTAGE	SYMBOL
	TPS3836E18QDBVRQ1 <sup>†</sup>	1.71 V	PDNQ
	TPS3836J25QDBVRQ1 <sup>†</sup>	2.25 V	PDSQ
	TPS3836H30QDBVRQ1 <sup>†</sup>	2.79 V	PHRQ
	TPS3836L30QDBVRQ1 <sup>†</sup>	2.64 V	PCAQ
	TPS3836K33QDBVRQ1 <sup>†</sup>	2.93 V	PDTQ
	TPS3837E18QDBVRQ1 <sup>†</sup>	1.71 V	PDOQ
-40°C to 125°C	TPS3837J25QDBVRQ1 <sup>†</sup>	2.25 V	PDRQ
	TPS3837L30QDBVRQ1 <sup>†</sup>	2.64 V	PCBQ
	TPS3837K33QDBVRQ1 <sup>†</sup>	2.93 V	PDUQ
	TPS3838E18QDBVRQ1 <sup>†</sup>	1.71 V	PDQQ
	TPS3838J25QDBVRQ1 <sup>†</sup>	2.25 V	PDPQ
	TPS3838L30QDBVRQ1 <sup>†</sup>	2.64 V	PCCQ
	TPS3838K33QDBVRQ1 <sup>†</sup>	2.93 V	PDVQ

<sup>&</sup>lt;sup>†</sup> DBVR indicates tape and reel of 3000 parts.

#### **ORDERING INFORMATION**






SGLS141A - DECEMBER 2002 - REVISED JANUARY 2007

#### **FUNCTION TABLE TPS3836, TPS3837, TPS3838**

MR	$V_{DD} > V_{IT}$	RESET <sup>†</sup>	RESET <sup>‡</sup>
L	0	L	Н
L	1	L	Н
Н	0	L	Н
Н	1	Н	L

<sup>†</sup> TPS3836 and TPS3838


# functional block diagram



<sup>‡</sup> TPS3837

SGLS141A - DECEMBER 2002 - REVISED JANUARY 2007

#### timing diagram



SGLS141A - DECEMBER 2002 - REVISED JANUARY 2007

### absolute maximum ratings over operating free-air temperature range (unless otherwise noted)†

Supply voltage, V <sub>DD</sub> (see Note 1)	
All other pins (see Note 1)	–0.3 V to 7 V
Maximum low output current, I <sub>OL</sub>	5 mA
Maximum high output current, IOH	–5 mA
Input clamp current, $I_{IK}$ ( $V_I < 0$ or $V_I > V_{DD}$ )	±10 mA
Output clamp current, $I_{OK}$ ( $V_O < 0$ or $V_O > V_{DD}$ )	±10 mA
Continuous total power dissipation	See Dissipation Rating Table
Operating free-air temperature range, T <sub>A</sub>	–40°C to 125°C
Storage temperature range, T <sub>stg</sub>	–65°C to 150°C
Soldering temperature	

<sup>†</sup> Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

NOTE 1: All voltage values are with respect to GND. For reliable operation, the device must not be operated at 7 V for more than t=1000 h continuously

#### **DISSIPATION RATING TABLE**

PACKAGE	T <sub>A</sub> <25°C	DERATING FACTOR	T <sub>A</sub> = 70°C	T <sub>A</sub> = 85°C	T <sub>A</sub> = 125°C
	POWER RATING	ABOVE T <sub>A</sub> = 25°C	POWER RATING	POWER RATING	POWER RATING
DBV	437 mW	3.5 mW/°C	280 mW	227 mW	87 mW

#### recommended operating conditions at specified temperature range

	MIN	MAX	UNIT
Supply voltage, V <sub>DD</sub>	1.6	6	V
Input voltage, V <sub>I</sub>	0	$V_{DD} + 0.3$	V
High-level input voltage, V <sub>IH</sub>	$0.7 \times V_{DD}$		V
Low-level input voltage, V <sub>IL</sub>		$0.3 \times V_{DD}$	V
Input transition rise and fall rate at $\overline{\text{MR}}$ , $\Delta t/\Delta V$		100	ns/V
Operating free-air temperature range, T <sub>A</sub>	-40	125	°C



SGLS141A - DECEMBER 2002 - REVISED JANUARY 2007

#### electrical characteristics over recommended operating conditions (unless otherwise noted)

	PARAMETER		TEST CO	ONDITION	MIN	TYP	MAX	UNIT
		RESET	$V_{DD} = 3.3 \text{ V},$	I <sub>OH</sub> = -2 mA				
.,	I Park Town Law March College	(TPS3836)	V <sub>DD</sub> = 6 V,	$I_{OH} = -3 \text{ mA}$	0.8×			.,
V <sub>OH</sub>	High-level output voltage	RESET	$V_{DD} = 1.8 \text{ V},$	$I_{OH} = -1 \text{ mA}$	$V_{DD}$			V
		(TPS3837)	$V_{DD} = 3.3 \text{ V},$	$I_{OL} = -2 \text{ mA}$				
		RESET	$V_{DD} = 1.8 V,$	I <sub>OL</sub> = 1 mA				
\ ,	Law lawel autout valtage	(TPS3836/8)	$V_{DD} = 3.3 \text{ V},$	$I_{OL} = 2 \text{ mA}$			0.4	
V <sub>OL</sub>	Low-level output voltage	RESET	$V_{DD} = 3.3 \text{ V},$	$I_{OL} = 2 \text{ mA}$			0.4	V
		(TPS3837)	$V_{DD} = 6 V$ ,	$I_{OL} = 3 \text{ mA}$				V V V V μA ηA ηA ηA ηA μA κΩ ρF
	Davis vin vasat valta aa	TPS3836/8	$V_{DD} \ge 1.1 V$ ,	$I_{OL} = 50 \mu A$			0.2	
	Power-up reset voltage (see Note 2)	TPS3837	V <sub>DD</sub> ≥ 1.1 V,	I <sub>OH</sub> = -50 μA	0.8 × V <sub>DD</sub>			V
		TPS383xE18			1.64	1.71	1.76	
V <sub>IT</sub>		TPS383xJ25	=		2.16	2.25	2.30	
	Negative-going input threshold voltage (see Note 3)	TPS383xH30	=		2.70	2.79	2.85	V
	voltage (see Note 3)	TPS383xL30	=	2.54 2.64	2.64	2.71		
		TPS383xK33	=		2.82	2.93	3.10	
			1.7 V < V <sub>IT</sub> < 2.5 V			30		
V <sub>hys</sub>	Hysteresis at V <sub>DD</sub> input		2.5 V < V <sub>IT</sub> < 3.5 V			40		mV
			3.5 V < V <sub>IT</sub> < 5 V			50		
l <sub>iH</sub>	High-level input current	MR (see Note 4)	$\overline{\text{MR}} = 0.7 \times V_{\text{DD}},$	V <sub>DD</sub> = 6 V	-40	-60	-100	μΑ
		СТ	$CT = V_{DD} = 6 V$		-25		25	nA
I <sub>IL</sub>	Low-level input current	MR (see Note 4)	MR = 0 V,	V <sub>DD</sub> = 6 V	-130	-200	-340	μΑ
	·	СТ	CT = 0 V,	V <sub>DD</sub> = 6 V	-25		25	nA
I <sub>OH</sub>	High-level output current	TPS3838	$V_{DD} = V_{IT} + 0.2 V,$	$V_{OH} = V_{DD}$			25	nA
			$V_{DD} > V_{IT}$	V <sub>DD</sub> < 3 V		220	500	4
I <sub>DD</sub>	Supply current		$V_{DD} > V_{IT}$	V <sub>DD</sub> > 3 V		250	550	nA
			V <sub>DD</sub> < V <sub>IT</sub>			10	25	μΑ
	Internal pullup resistor at MR					30		kΩ
C <sub>I</sub>	Input capacitance at MR, CT		$V_I = 0 V \text{ to } V_{DD}$			5		pF

NOTES: 2. The lowest voltage at which  $\overline{RESET}$  output becomes active.  $t_r$ ,  $V_{DD} \ge 15 \,\mu s/V$ 

3. To ensure best stability of the threshold voltage, a bypass capacitor (ceramic, 0.1 µF) should be placed near the supply terminal.

4. If manual reset is unused,  $\overline{\text{MR}}$  should be connected to  $V_{DD}$  to minimize current consumption.

SGLS141A - DECEMBER 2002 - REVISED JANUARY 2007

# timing requirements at R<sub>L</sub> = 1 M $\Omega$ , C<sub>L</sub> = 50 pF, T<sub>A</sub> = 25 $^{\circ}$ C

	PARAMETER		TEST	CONDITIONS	MIN	TYP	MAX	UNIT
		at V <sub>DD</sub>	$V_{IH} = V_{IT} + 0.2 V,$	$V_{IL} = V_{IT} - 0.2 V$	6			μs
t <sub>w</sub>	Pulse width		$V_{DD} \ge V_{IT} + 0.2 \text{ V},$ $V_{IH} = 0.7 \times V_{DD}$	$V_{IL} = 0.3 \times V_{DD,}$	1			μs

# switching characteristics at R<sub>L</sub> = 1 M $\Omega$ , C<sub>L</sub> = 50 pF, T<sub>A</sub> = 25 $^{\circ}$ C

	PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
	Delivering		$\begin{split} & V_{DD} \geq V_{IT} + 0.2 \text{ V,} \\ & \overline{MR} = 0.7 \times V_{DD}, \\ & \text{CT} = \text{GND,} \\ & \text{See timing diagram} \end{split}$	5	10	15	
t <sub>d</sub>	Delay time		$\begin{split} &V_{DD} \geq V_{IT} + 0.2 \text{ V,} \\ &\overline{MR} = 0.7 \times V_{DD}, \\ &CT = V_{DD} \text{ ,} \\ &\text{See timing diagram} \end{split}$	100	200	300	ms
t <sub>PHL</sub>	Propagation (delay) time, high-to-low-level output	V <sub>DD</sub> to RESET delay	$V_{IL} = V_{IT} - 0.2 V,$ $V_{IH} = V_{IT} + 0.2 V$			10	μs
		(TPS3836, TPS3838)	V <sub>IL</sub> = 1.6 V			50	
t <sub>PLH</sub>	Propagation (delay) time, low-to-high-level output	V <sub>DD</sub> to RESET delay	$V_{IL} = V_{IT} - 0.2 \text{ V},$ $V_{IH} = V_{IT} + 0.2 \text{ V}$			10	μs
		(TPS3837)	V <sub>IL</sub> = 1.6 V			50	
t <sub>PHL</sub>	Propagation (delay) time, high-to-low-level output	MR to RESET delay (TPS3836, TPS3838)	$V_{DD} \ge V_{IT} + 0.2 \text{ V},$ $V_{IL} = 0.3 \times V_{DD},$			0.1	μs
t <sub>PLH</sub>	Propagation (delay) time, low-to-high-level output	MR to RESET delay (TPS3837)	$V_{IL} = 0.7 \times V_{DD}$			0.1	μs


#### **TYPICAL CHARACTERISTICS**


## **Table of Graphs**


			FIGURE
$I_{DD}$	Supply current	vs Supply voltage	1
$I_{MR}$	Manual reset current	vs Manual reset voltage	2
$V_{OL}$	Low-level output voltage	vs Low-level output current	3
$V_{OH}$	High-level output voltage	vs High-level output current	4
	Normalized reset threshold voltage	vs Free-air temperature	5
	Minimum pulse duration at V <sub>DD</sub>	vs V <sub>DD</sub> Threshold overdrive	6


#### SGLS141A - DECEMBER 2002 - REVISED JANUARY 2007

#### TYPICAL CHARACTERISTICS










HIGH-LEVEL OUTPUT VOLTAGE

SGLS141A - DECEMBER 2002 - REVISED JANUARY 2007

#### TYPICAL CHARACTERISTICS

# NORMALIZED RESET THRESHOLD VOLTAGE

## FREE-AIR TEMPERATURE



# MINIMUM PULSE DURATION AT $\ensuremath{\text{V}_{\text{DD}}}$

# V<sub>DD</sub> THRESHOLD OVERDRIVE




Figure 6







13-Oct-2017

#### PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead/Ball Finish (6)	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
2U3838K33QDBVRG4Q1	ACTIVE	SOT-23	DBV	5	3000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 125	PDVQ	Samples
TPS3836J25QDBVRQ1	ACTIVE	SOT-23	DBV	5	3000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 125	PDSQ	Samples
TPS3836K33QDBVRQ1	ACTIVE	SOT-23	DBV	5	3000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 125	PDTQ	Samples
TPS3836L30QDBVRQ1	ACTIVE	SOT-23	DBV	5	3000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 125	PCAQ	Samples
TPS3838K33QDBVRQ1	ACTIVE	SOT-23	DBV	5	3000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 125	PDVQ	Samples

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead/Ball Finish Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.



### **PACKAGE OPTION ADDENDUM**

13-Oct-2017

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

#### OTHER QUALIFIED VERSIONS OF TPS3836-Q1, TPS3838-Q1:

■ Catalog: TPS3836, TPS3838

■ Enhanced Product: TPS3836-EP

NOTE: Qualified Version Definitions:

- Catalog TI's standard catalog product
- Enhanced Product Supports Defense, Aerospace and Medical Applications

# **PACKAGE MATERIALS INFORMATION**

www.ti.com 12-Oct-2017

#### TAPE AND REEL INFORMATION





	Dimension designed to accommodate the component width
B0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers


#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



#### \*All dimensions are nominal

"All dimensions are nominal												
Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
2U3838K33QDBVRG4Q1	SOT-23	DBV	5	3000	180.0	9.0	3.15	3.2	1.4	4.0	8.0	Q3
TPS3836J25QDBVRQ1	SOT-23	DBV	5	3000	180.0	9.0	3.15	3.2	1.4	4.0	8.0	Q3
TPS3836K33QDBVRQ1	SOT-23	DBV	5	3000	180.0	9.0	3.15	3.2	1.4	4.0	8.0	Q3
TPS3836L30QDBVRQ1	SOT-23	DBV	5	3000	180.0	9.0	3.15	3.2	1.4	4.0	8.0	Q3
TPS3838K33QDBVRQ1	SOT-23	DBV	5	3000	180.0	9.0	3.15	3.2	1.4	4.0	8.0	Q3

www.ti.com 12-Oct-2017



\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
2U3838K33QDBVRG4Q1	SOT-23	DBV	5	3000	182.0	182.0	20.0
TPS3836J25QDBVRQ1	SOT-23	DBV	5	3000	182.0	182.0	20.0
TPS3836K33QDBVRQ1	SOT-23	DBV	5	3000	182.0	182.0	20.0
TPS3836L30QDBVRQ1	SOT-23	DBV	5	3000	182.0	182.0	20.0
TPS3838K33QDBVRQ1	SOT-23	DBV	5	3000	182.0	182.0	20.0



Images above are just a representation of the package family, actual package may vary. Refer to the product data sheet for package details.

4073253/P





SMALL OUTLINE TRANSISTOR



#### NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

  2. This drawing is subject to change without notice.

  3. Reference JEDEC MO-178.



SMALL OUTLINE TRANSISTOR



NOTES: (continued)

- 4. Publication IPC-7351 may have alternate designs.
- 5. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SMALL OUTLINE TRANSISTOR



NOTES: (continued)

- 6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 7. Board assembly site may have different recommendations for stencil design.



#### **IMPORTANT NOTICE**

Texas Instruments Incorporated (TI) reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete.

TI's published terms of sale for semiconductor products (http://www.ti.com/sc/docs/stdterms.htm) apply to the sale of packaged integrated circuit products that TI has qualified and released to market. Additional terms may apply to the use or sale of other types of TI products and services.

Reproduction of significant portions of TI information in TI data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such reproduced documentation. Information of third parties may be subject to additional restrictions. Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyers and others who are developing systems that incorporate TI products (collectively, "Designers") understand and agree that Designers remain responsible for using their independent analysis, evaluation and judgment in designing their applications and that Designers have full and exclusive responsibility to assure the safety of Designers' applications and compliance of their applications (and of all TI products used in or for Designers' applications) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to their applications, Designer has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any applications that include TI products, Designer will thoroughly test such applications and the functionality of such TI products as used in such applications.

TI's provision of technical, application or other design advice, quality characterization, reliability data or other services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using TI Resources in any way, Designer (individually or, if Designer is acting on behalf of a company, Designer's company) agrees to use any particular TI Resource solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

Designer is authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNER AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

Unless TI has explicitly designated an individual product as meeting the requirements of a particular industry standard (e.g., ISO/TS 16949 and ISO 26262), TI is not responsible for any failure to meet such industry standard requirements.

Where TI specifically promotes products as facilitating functional safety or as compliant with industry functional safety standards, such products are intended to help enable customers to design and create their own applications that meet applicable functional safety standards and requirements. Using products in an application does not by itself establish any safety features in the application. Designers must ensure compliance with safety-related requirements and standards applicable to their applications. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equipment includes, without limitation, all medical devices identified by the U.S. Food and Drug Administration as Class III devices and equivalent classifications outside the U.S.

TI may expressly designate certain products as completing a particular qualification (e.g., Q100, Military Grade, or Enhanced Product). Designers agree that it has the necessary expertise to select the product with the appropriate qualification designation for their applications and that proper product selection is at Designers' own risk. Designers are solely responsible for compliance with all legal and regulatory requirements in connection with such selection.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's non-compliance with the terms and provisions of this Notice.