

www.ti.com


SCDS185C – JANUARY 2005 – REVISED SEPTEMBER 2012

10-Ω SPST ANALOG SWITCH

Check for Samples: TS5A1066

FEATURES

- Low ON-State Resistance (10 Ω)
- Control Inputs Are 5.5-V Tolerant
- Low Charge Injection
- Low Total Harmonic Distortion (THD)
- 1.65-V to 5.5-V Single-Supply Operation
- Latch-Up Performance Exceeds 100 mA Per JESD 78, Class II
- ESD Performance Tested Per JESD 22
 - 2000-V Human-Body Model (A114-B, Class II)
 - 1000-V Charged-Device Model (C101)



DESCRIPTION/ORDERING INFORMATION

The TS5A1066 is a single-pole single-throw (SPST) analog switch that is designed to operate from 1.65 V to 5.5 V. This device can handle both digital and analog signals, and signals up to V_+ (peak) can be transmitted in either direction.

| Configuration | Single-Pole, Single-Throw Demultiplexer (1 × SPST) |
|--|--|
| Number of channels | 1 |
| ON-state resistance (ron) | 7.5 Ω |
| ON-state resistance flatness (ron(flat)) | 2.5 Ω |
| Turn-on/turn-off time (t _{ON} /t _{OFF}) | 9.5 ns/2 ns |
| Charge injection (Q _C) | 1 pC |
| Bandwidth (BW) | 400 MHz |
| OFF isolation (O _{ISO}) | –68 dB at 10 MHz |
| Total harmonic distortion (THD) | 0.14% |
| Leakage current (I _{COM(OFF)} | ±0.1 μΑ |
| Power-supply current (I+) | 0.05 µA |
| Package options | 5-pin DSBGA, SOT-23, or SC-70 |

Table 1. SUMMARY OF CHARACTERISTICS



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

SCDS185C – JANUARY 2005 – REVISED SEPTEMBER 2012

www.ti.com

STRUMENTS

XAS

Table 2. ORDERING INFORMATION

| T _A | PACKAGE ⁽¹⁾ | | ORDERABLE PART NUMBER | TOP-SIDE MARKING ⁽²⁾ |
|----------------|--|---------------|-----------------------|---------------------------------|
| –40°C to 85°C | NanoFree™ – WCSP (DSBGA) 0.23-mm Large Bump – YZP (Pb- free) | Tape and reel | TS5A1066YZPR | JD_ |
| | SOT (SOT-23) – DBV | Tape and reel | TS5A1066DBVR | JAD_ |
| | SOT (SC-70) – DCK | Tape and reel | TS5A1066DCKR | JD_ |

(1) Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at www.ti.com/sc/package.

(2) DBV/DCK: The actual top-side marking has one additional character that designates the assembly/test site. YZP: The actual top-side marking has three preceding characters to denote year, month, and sequence code, and one following character to designate the assembly/test site. Pin 1 identifier indicates solder-bump composition (1 = SnPb, • = Pb-free).

| FUNCTIC | FUNCTION TABLE | | | | | | | | |
|---------|-------------------------|--|--|--|--|--|--|--|--|
| IN | NO TO COM, COM TO NO | | | | | | | | |
| L | OFF | | | | | | | | |
| Н | ON | | | | | | | | |

Absolute Minimum and Maximum Rating^{(1) (2)}

over operating free-air temperature range (unless otherwise noted)

| | | | MIN | MAX | UNIT |
|-------------------------------------|---|--|------|----------------------|------|
| V+ | Supply voltage range ⁽³⁾ | | -0.5 | 6.5 | V |
| V _{NO} V _{COM} | Analog voltage range ^{(3) (4) (5)} | | -0.5 | V ₊ + 0.5 | V |
| Ι _Κ | Analog port diode current | V_{NO} , $V_{COM} < 0$ or V_{NO} , $V_{COM} > V_{+}$ | -50 | 50 | mA |
| I _{NO} I _{COM} | On-state switch current | V_{NO} , $V_{COM} = 0$ to V_{+} | -50 | 50 | mA |
| VI | Digital input voltage range ⁽³⁾ ⁽⁴⁾ | | -0.5 | 6.5 | V |
| I _{IK} | Digital input clamp current | V _I < 0 | -50 | | mA |
| I₊ I _{GND} | Continuous current through each V_{+} or GND | | -100 | 100 | mA |
| | | DBV package | | 206 | |
| θ_{JA} | Package thermal impedance ⁽⁶⁾ | DCK package | | 252 | °C/W |
| | | YZP package | | 132 | |
| T _{stg} | Storage temperature range | | -65 | 150 | °C |

(1) Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

(2) The algebraic convention, whereby the most negative value is a minimum and the most positive value is a maximum.

(3) All voltages are with respect to ground, unless otherwise specified.

(4) The input and output voltage ratings may be exceeded if the input and output clamp-current ratings are observed.

(5) This value is limited to 5.5 V maximum.

(6) The package thermal impedance is calculated in accordance with JESD 51-7.



SCDS185C - JANUARY 2005 - REVISED SEPTEMBER 2012

www.ti.com

Electrical Characteristics for 5-V Supply⁽¹⁾

 $V_{+} = 4.5 \text{ V}$ to 5.5 V, $T_{A} = -40^{\circ}\text{C}$ to 85°C (unless otherwise noted)

| PARAMETER | SYMBOL | TEST (| CONDITIONS | TA | ۷, | MIN | TYP | MAX | UNIT |
|-------------------------------|-----------------------------------|---|------------------------------|----------|--------|------------------|------|--------------------|------|
| Analog Switch | | | | | | | | | |
| Analog signal range | V_{COM}, V_{NO} | | | | | 0 | | V+ | V |
| ON-state | r | $0 \le V_{NO} \le V_+,$ | Switch ON, | 25°C | 4.5 V | | 7.5 | 10 | Ω |
| resistance | r _{on} | $I_{COM} = -30 \text{ mA},$ | See Figure 13 | Full | 4.5 V | | | 12 | 12 |
| ON-state | | $0 \leq V_{NO} \leq V_{+},$ | Switch ON, | 25°C | 4 5 14 | | 2.5 | 5 | 0 |
| resistance flatness | r _{on(flat)} | $I_{\rm COM} = -30$ mA, | See Figure 13 | Full | 4.5 V | | | 6 | Ω |
| | | $V_{NO} = 1 V$, | | 25°C | | -0.2 | 0.1 | 0.2 | |
| NO OFF leakage current | I _{NO(OFF)} | $V_{COM} = 4.5 \text{ V},$ or $V_{NO} = 4.5 \text{ V},$ $V_{COM} = 1 \text{ V},$ | Switch OFF, See Figure 14 | Full | 5.5 V | -2 | | 2 | μA |
| | | $V_{COM} = 1 V,$ | | 25°C | | -0.1 | 0.05 | 0.1 | |
| COM OFF leakage current | I _{COM(OFF)} | $V_{NO} = 4.5 \text{ V},$ or $V_{COM} = 4.5 \text{ V},$ $V_{NO} = 1 \text{ V},$ | Switch OFF, See Figure 14 | Full | 5.5 V | -0.2 | | 0.2 | μA |
| | | $V_{NO} = 1 V,$ | | 25°C | | -0.2 | 0.1 | 0.2 | |
| NO ON leakage current | I _{NO(ON)} | $V_{COM} = Open,$ or $V_{NO} = 4.5 V,$ $V_{COM} = Open,$ | Switch ON, See Figure 15 | Full | 5.5 V | -2 | | 2 | μA |
| | | $V_{COM} = 1 V,$ | | 25°C | | -0.1 | 0.05 | 0.1 | |
| COM ON leakage current | I _{COM(ON)} | $V_{NO} = Open,$ or $V_{COM} = 4.5 V,$ $V_{NO} = Open,$ | Switch ON, See Figure 15 | Full | 5.5 V | -0.2 | | 0.2 | μA |
| Digital Control | Input (IN) | | | <u>.</u> | | | | | |
| Input logic high | V _{IH} | | | Full | | $V_+ \times 0.7$ | | 5.5 | V |
| Input logic low | VIL | | | Full | | 0 | | $V_{+} \times 0.3$ | V |
| Input leakage | I _{IH} , I _{IL} | V ₁ = 5.5 V or 0 | | 25°C | 5.5 V | -0.1 | 0.05 | 0.1 | μA |
| current | 'IH, IL | vi – 0.0 v 0i 0 | | Full | 5.5 v | -1 | | 1 | μΛ |

(1) The algebraic convention is used in this data sheet; the most negative value is shown in the minimum column.

SCDS185C – JANUARY 2005–REVISED SEPTEMBER 2012

www.ti.com

NSTRUMENTS

Texas

Electrical Characteristics for 5-V Supply⁽¹⁾ (continued)

 $V_{+} = 4.5 \text{ V}$ to 5.5 V, $T_{A} = -40^{\circ}\text{C}$ to 85°C (unless otherwise noted)

| PARAMETER | SYMBOL | TEST CO | NDITIONS | TA | V. | MIN | TYP | MAX | UNIT |
|------------------------------|-----------------------|--|---------------------------------------|------|----------------|-----|------|-----|------|
| Dynamic | | | | | | | | | |
| Turn-on time | + | $V_{COM} = 3 V,$ | C _L = 35 pF, | 25°C | 5 V | 3.5 | 4.8 | 5.5 | 20 |
| rum-on time | t _{ON} | $R_L = 300 \Omega$, | See Figure 17 | Full | 4.5 V to 5.5 V | 3.5 | | 7.5 | ns |
| Turn-off time | | $V_{COM} = 3 V,$ | C _L = 35 pF, | 25°C | 5 V | 2 | 3 | 4.5 | |
| rum-on ume | t _{OFF} | $R_L = 300 \Omega$, | See Figure 17 | Full | 4.5 V to 5.5 V | 2 | | 5.5 | ns |
| Charge injection | Q _C | $V_{GEN} = 0,$ $C_L = 0.1 \text{ nF},$ | See Figure 20 | 25°C | 5 V | | 1 | | рС |
| NO OFF capacitance | C _{NO(OFF)} | $V_{NO} = V_{+}$ or GND, Switch OFF, | See Figure 16 | 25°C | 5 V | | 6.8 | | pF |
| COM OFF capacitance | C _{COM(OFF)} | $V_{COM} = V_+ \text{ or GND},$ Switch OFF, | See Figure 16 | 25°C | 5 V | | 6.8 | | pF |
| NO ON capacitance | C _{NO(ON)} | V _{NO} = V ₊ or GND, Switch ON, | See Figure 16 | 25°C | 5 V | | 14 | | pF |
| COM ON capacitance | C _{COM(ON)} | $V_{COM} = V_+ \text{ or GND},$ Switch ON, | See Figure 16 | 25°C | 5 V | | 14 | | pF |
| Digital input capacitance | Cı | $V_I = V_+ \text{ or GND},$ | See Figure 16 | 25°C | 5 V | | 2.2 | | pF |
| Bandwidth | BW | $R_L = 50 \Omega$, Switch ON, | See Figure 18 | 25°C | 5 V | | 400 | | MHz |
| OFF isolation | O _{ISO} | $\begin{array}{l} R_{L} = 50 \ \Omega, \\ f = 10 \ MHz, \end{array}$ | Switch OFF, See Figure 19 | 25°C | 5 V | | -68 | | dB |
| Total harmonic distortion | THD | $R_L = 600 \Omega,$ $C_L = 50 pF,$ | f = 20 Hz to 20 kHz, See Figure 21 | 25°C | 5 V | | 0.14 | | % |
| Supply | | | | | | | | | |
| Positive supply | 1 | $V_1 = V_+$ or GND, | Switch ON or OFF | 25°C | 5.5 V | | 0.05 | 1 | |
| current | I+ | $v_{l} = v_{+}$ or GivD, | Switch ON OFF | Full | 5.5 V | | | 5 | μA |

4



www.ti.com

SCDS185C – JANUARY 2005–REVISED SEPTEMBER 2012

Electrical Characteristics for 3.3-V Supply⁽¹⁾

 $V_{+} = 3 \text{ V}$ to 3.6 V, $T_{A} = -40^{\circ}\text{C}$ to 85°C (unless otherwise noted)

| PARAMETER | SYMBOL | TEST C | ONDITIONS | TA | V. | MIN | TYP | MAX | UNIT |
|-------------------------------|-----------------------------------|--|------------------------------|--------------|-------|----------------------|------|----------------------|------|
| Analog Switch | | · | | · | | | | | |
| Analog signal range | V_{COM}, V_{NO} | | | | | 0 | | V+ | V |
| ON-state | - | $0 \le V_{NO} \le V_+,$ | Switch ON, | 25°C | 3 V | | 11.5 | 14 | Ω |
| resistance | r _{on} | $I_{COM} = -24 \text{ mA},$ | See Figure 13 | Full | 3 V | | | 17 | 12 |
| ON-state | | $0 \le V_{NO} \le V_+,$ | Switch ON, | 25°C | | | 5 | 10 | |
| resistance flatness | r _{on(flat)} | $I_{COM} = -24 \text{ mA},$ | See Figure 13 | Full | 3 V | | | 12 | Ω |
| | | V _{NO} = 1 V, | | 25°C | | -0.2 | 0.1 | 0.2 | |
| NO OFF leakage current | I _{NO(OFF)} | $V_{COM} = 3 V,$ or $V_{NO} = 3 V,$ $V_{COM} = 1 V,$ | Switch OFF, See Figure 14 | Full | 3.6 V | -2 | | 2 | μA |
| | | $V_{COM} = 1 V,$ | | 25°C | | -0.1 | 0.05 | 0.1 | |
| COM OFF leakage current | I _{COM(OFF)} | $V_{NO} = 3 V,$ or $V_{COM} = 3 V,$ $V_{NO} = 1 V,$ | Switch OFF, See Figure 14 | ch OFF, | 3.6 V | -0.2 | | 0.2 | μΑ |
| | | $V_{NO} = 1 V,$ | | 25°C | | -0.2 | 0.1 | 0.2 | |
| NO ON leakage current | I _{NO(ON)} | $V_{COM} = Open,$ or $V_{NO} = 3 V,$ $V_{COM} = Open,$ | Switch ON, See Figure 15 | Full | 3.6 V | -2 | | 2 | μA |
| | | $V_{COM} = 1 V,$ | | 25°C | | -0.1 | 0.05 | 0.1 | |
| COM ON leakage current | I _{COM(ON)} | V_{NO}^{o} = Open, or V_{COM} = 3 V, V_{NO} = Open, | Switch ON, See Figure 15 | Full | 3.6 V | -0.2 | | 0.2 | μA |
| Digital Control I | nput (IN) | | | | | | | | |
| Input logic high | V _{IH} | | | Full | | V ₊ × 0.7 | | 5.5 | V |
| Input logic low | VIL | | | Full | | 0 | | V ₊ × 0.3 | V |
| Input leakage current | I _{IH} , I _{IL} | V _I = 5.5 V or 0 | | 25°C Full | 3.6 V | -0.1 | 0.05 | 0.1 | μA |

(1) The algebraic convention is used in this data sheet; the most negative value is shown in the minimum column.

SCDS185C – JANUARY 2005–REVISED SEPTEMBER 2012

www.ti.com

STRUMENTS

TEXAS

Electrical Characteristics for 3.3-V Supply⁽¹⁾ (continued)

 $V_{+} = 3 V$ to 3.6 V, $T_{A} = -40^{\circ}C$ to 85°C (unless otherwise noted)

| PARAMETER | SYMBOL | TEST CC | NDITIONS | T _A | V. | MIN | TYP | MAX | UNIT |
|------------------------------|-----------------------|---|--|----------------|-----------------|-----|------|-----|------|
| Dynamic | | | | | | | | | |
| | | N 0.V | 0 05 -5 | 25°C | 3.3 V | 4.5 | 5.5 | 8 | |
| Turn-on time | t _{ON} | $V_{COM} = 2 V,$ R _L = 300 Ω, | C _L = 35 pF, See Figure 17 | Full | 3 V to 3.6 V | 4.5 | | 8.5 | ns |
| | | V 2V | 0 25 55 | 25°C | 3.3 V | 2 | 3 | 4.5 | |
| Turn-off time | t _{OFF} | $V_{COM} = 2 V,$ R _L = 300 Ω, | C _L = 35 pF, See Figure 17 | Full | 3 V to 3.6 V | 2 | | 5.5 | ns |
| Charge injection | Q _C | $\begin{array}{l} V_{GEN}=0,\\ C_L=0.1 \text{ nF}, \end{array}$ | See Figure 20 | 25°C | 3.3 V | | 1 | | рС |
| NO OFF capacitance | C _{NO(OFF)} | $V_{NO} = V_{+} \text{ or GND},$ Switch OFF, | See Figure 16 | 25°C | 3.3 V | | 6.8 | | pF |
| COM OFF capacitance | C _{COM(OFF)} | $V_{COM} = V_+ \text{ or GND},$ Switch OFF, | See Figure 16 | 25°C | 3.3 V | | 6.8 | | pF |
| NO ON capacitance | C _{NO(ON)} | $V_{NO} = V_{+} \text{ or GND},$ Switch ON, | See Figure 16 | 25°C | 3.3 V | | 14 | | pF |
| COM ON capacitance | C _{COM(ON)} | $V_{COM} = V_+ \text{ or GND},$ Switch ON, | See Figure 16 | 25°C | 3.3 V | | 14 | | pF |
| Digital input capacitance | CI | $V_I = V_+ \text{ or } GND,$ | See Figure 16 | 25°C | 3.3 V | | 2.2 | | pF |
| Bandwidth | BW | $R_L = 50 \Omega$, Switch ON, | See Figure 18 | 25°C | 3.3 V | | 400 | | MHz |
| OFF isolation | O _{ISO} | $R_L = 50 \Omega,$ f = 10 MHz, | Switch OFF, See Figure 19 | 25°C | 3.3 V | | -68 | | dB |
| Total harmonic distortion | THD | $R_L = 600 \Omega,$ $C_L = 50 pF,$ | f = 20 Hz to 20 kHz, See Figure 21 | 25°C | 3.3 V | | 0.2 | | % |
| Supply | • | | | | · · · · | | | | |
| Positive supply current | I+ | $V_I = V_+ \text{ or } GND,$ | Switch ON or OFF | 25°C Full | 3.6 V | | 0.05 | 1 | μA |

6



www.ti.com

SCDS185C – JANUARY 2005–REVISED SEPTEMBER 2012

Electrical Characteristics for 2.5-V Supply⁽¹⁾

 V_{+} = 2.3 V to 2.7 V, T_{A} = –40°C to 85°C (unless otherwise noted)

| PARAMETER | SYMBOL | TEST | CONDITIONS | TA | V. | MIN | TYP | MAX | UNIT |
|-------------------------------|-----------------------------------|--|------------------------------|--------------|-------|----------------------|------|------------------|------|
| Analog Switch | | | | | | | | | |
| Analog signal range | V_{COM}, V_{NO} | | | | | 0 | | V+ | V |
| ON-state | r | $0 \le V_{NO} \le V_+,$ | Switch ON, | 25°C | 2.3 V | | 20 | 24 | Ω |
| resistance | r _{on} | $I_{COM} = -8 \text{ mA},$ | See Figure 13 | Full | 2.3 V | | | 27 | 12 |
| ON-state | | $0 \le V_{NO} \le V_+,$ | Switch ON, | 25°C | | | 7.5 | 15 | |
| resistance flatness | r _{on(flat)} | $I_{COM} = -8 \text{ mA},$ | See Figure 13 | Full | 2.3 V | | | 20 | Ω |
| | | V _{NO} = 0.5 V, | | 25°C | | -0.2 | 0.1 | 0.2 | |
| NO OFF leakage current | I _{NO(OFF)} | $V_{COM} = 2.2 V,$ or $V_{NO} = 2.2 V,$ $V_{COM} = 0.5 V,$ | Switch OFF, See Figure 14 | Full | 2.7 V | -2 | | 2 | μA |
| | | V _{COM} = 0.5 V, | | 25°C | | -0.1 | 0.05 | 0.1 | |
| COM OFF leakage current | I _{COM(OFF)} | $V_{NO} = 2.2 V,$ or $V_{COM} = 2.2 V,$ $V_{NO} = 0.5 V,$ | Switch OFF, See Figure 14 | Full | 2.7 V | -0.2 | | 0.2 | μA |
| | | V _{NO} = 0.5 V, | | 25°C | | -0.2 | 0.1 | 0.2 | |
| NO ON leakage current | I _{NO(ON)} | $\label{eq:COM} \begin{array}{l} V_{COM} = Open,\\ or\\ V_{NO} = 2.2 \ V,\\ V_{COM} = Open, \end{array}$ | Switch ON, See Figure 15 | Full | 2.7 V | -2 | | 2 | μA |
| | | V _{COM} = 0.5 V, | | 25°C | | -0.1 | 0.05 | 0.1 | |
| COM ON leakage current | I _{COM(ON)} | $V_{NO} = Open,$ or $V_{COM} = 2.2 V,$ $V_{NO} = Open,$ | Switch ON, See Figure 15 | Full | 2.7 V | -0.2 | | 0.2 | μA |
| Digital Control | Input (IN) | | | | | | | <u>.</u> | |
| Input logic high | V _{IH} | | | Full | | V ₊ × 0.7 | | 5.5 | V |
| Input logic low | V _{IL} | | | Full | | 0 | | $V_+ \times 0.3$ | V |
| Input leakage current | I _{IH} , I _{IL} | V _I = 5.5 V or 0 | | 25°C Full | 2.7 V | -0.1 -1 | 0.05 | 0.1 | μA |

(1) The algebraic convention is used in this data sheet; the most negative value is shown in the minimum column.

SCDS185C - JANUARY 2005-REVISED SEPTEMBER 2012

www.ti.com

STRUMENTS

TEXAS

Electrical Characteristics for 2.5-V Supply⁽¹⁾ (continued)

 $V_{+} = 2.3 \text{ V}$ to 2.7 V, $T_{A} = -40^{\circ}\text{C}$ to 85°C (unless otherwise noted)

| PARAMETER | SYMBOL | TEST C | ONDITIONS | TA | V. | MIN | TYP | MAX | UNIT |
|------------------------------|------------------------------|--|--|------|-------------------|-----|------|-----|------|
| Dynamic | | | | | | | | | |
| | | N 45N | 0 05 -5 | 25°C | 2.5 V | 4.5 | 5.5 | 8 | |
| Turn-on time | t _{ON} | $V_{COM} = 1.5 \text{ V},$ R _L = 300 Ω, | C _L = 35 pF, See Figure 17 | Full | 2.3 V to 2.7 V | 4.5 | | 8.5 | ns |
| | | N 45N | 0 05 -5 | 25°C | 2.5 V | 1.5 | 2.5 | 4 | |
| Turn-off time | t _{OFF} | $V_{COM} = 1.5 \text{ V},$ R _L = 300 Ω, | C _L = 35 pF, See Figure 17 | Full | 2.3 V to 2.7 V | 1.5 | | 5.5 | ns |
| Charge injection | Q _C | $\begin{array}{l} V_{GEN}=0,\\ C_L=0.1 \text{ nF}, \end{array}$ | See Figure 20 | 25°C | 2.5 V | | 1 | | рС |
| NO OFF capacitance | $C_{\text{NO}(\text{OFF})}$ | V _{NO} = V ₊ or GND, Switch OFF, | See Figure 16 | 25°C | 2.5 V | | 6.8 | | pF |
| COM OFF capacitance | $C_{\text{COM}(\text{OFF})}$ | $V_{COM} = V_+ \text{ or GND},$ Switch OFF, | See Figure 16 | 25°C | 2.5 V | | 6.8 | | pF |
| NO ON capacitance | C _{NO(ON)} | V _{NO} = V ₊ or GND, Switch ON, | See Figure 16 | 25°C | 2.5 V | | 14 | | pF |
| COM ON capacitance | C _{COM(ON)} | $V_{COM} = V_+ \text{ or GND},$ Switch ON, | See Figure 16 | 25°C | 2.5 V | | 14 | | pF |
| Digital input capacitance | CI | $V_1 = V_+ \text{ or } GND,$ | See Figure 16 | 25°C | 2.5 V | | 2.2 | | pF |
| Bandwidth | BW | $R_L = 50 \Omega$, Switch ON, | See Figure 18 | 25°C | 2.5 V | | 400 | | MHz |
| OFF isolation | O _{ISO} | $\begin{array}{l} R_L = 50 \ \Omega, \\ f = 10 \ MHz, \end{array}$ | Switch OFF, See Figure 19 | 25°C | 2.5 V | | -68 | | dB |
| Total harmonic distortion | THD | $R_L = 600 \Omega,$ $C_L = 50 pF,$ | f = 20 Hz to 20 kHz, See Figure 21 | 25°C | 2.5 V | | 0.32 | | % |
| Supply | | | | | ŀ | | | | |
| Positive supply | | $V_1 = V_+$ or GND, | Switch ON or OFF | 25°C | 2.7 V | | 0.05 | 1 | |
| current | I+ | $v_{\parallel} = v_{+}$ or GivD, | | Full | 2.1 V | | | 5 | μA |



SCDS185C - JANUARY 2005 - REVISED SEPTEMBER 2012

www.ti.com

Electrical Characteristics for 1.8-V Supply⁽¹⁾

 V_{+} = 1.65 V to 1.95 V, T_{A} = -40°C to 85°C (unless otherwise noted)

| PARAMETER | SYMBOL | TEST | CONDITIONS | T _A | V ₊ | MIN | TYP | MAX | UNIT |
|-------------------------------|------------------------------------|--|------------------------------|----------------|----------------|---------------------|------|-------------------|------|
| Analog Switch | | | | · | | | | | |
| Analog signal range | V _{COM} , V _{NO} | | | | | 0 | | V+ | V |
| ON-state | | $0 \leq V_{NO} \leq V_+,$ | Switch ON, | 25°C | 1.65 V | | 74.5 | 80 | Ω |
| resistance | r _{on} | $I_{COM} = -4 \text{ mA},$ | See Figure 13 | Full | V 60.1 | | | 100 | Ω |
| ON-state | | $0 \le V_{NO} \le V_+,$ | Switch ON, | 25°C | | | 64.5 | 70 | |
| resistance flatness | r _{on(flat)} | $I_{COM} = -4 \text{ mÅ},$ | See Figure 13 | Full | 1.65 V | | | 90 | Ω |
| | | V _{NO} = 0.3 V, | | 25°C | | -0.2 | 0.1 | 0.2 | |
| NO OFF leakage current | I _{NO(OFF)} | $V_{COM} = 1.65 V,$ or $V_{NO} = 1.65 V,$ $V_{COM} = 0.3 V,$ | Switch OFF, See Figure 14 | Full | 1.95 V | -2 | | 2 | μA |
| | | V _{COM} = 0.3 V, | | 25°C | | -0.1 | 0.05 | 0.1 | |
| COM OFF leakage current | I _{COM(OFF)} | $V_{NO} = 1.65 \text{ V},$ or $V_{COM} = 1.65 \text{ V},$ $V_{NO} = 0.3 \text{ V},$ | Switch OFF, See Figure 14 | | 1.95 V | -0.2 | | 0.2 | μA |
| | | V _{NO} = 0.3 V, | | 25°C | | -0.2 | 0.1 | 0.2 | |
| NO ON leakage current | I _{NO(ON)} | $V_{COM} = Open,$ or $V_{NO} = 1.65 V,$ $V_{COM} = Open,$ | Switch ON, See Figure 15 | Full | 1.95 V | -2 | | 2 | μA |
| | | V _{COM} = 0.3 V, | | 25°C | | -0.1 | 0.05 | 0.1 | |
| COM ON leakage current | I _{COM(ON)} | V_{NO} = Open, or V_{COM} = 1.65 V, V_{NO} = Open, | Switch ON, See Figure 15 | Full | 1.95 V | -0.2 | | 0.2 | μA |
| Digital Control I | nput (IN) | | | | | - | | | |
| Input logic high | V _{IH} | | | Full | | $V_{+} \times 0.65$ | | 5.5 | V |
| Input logic low | VIL | | | Full | | 0 | | $V_+ \times 0.35$ | V |
| Input leakage | lux lu | V ₁ = 5.5 V or 0 | | 25°C | 1.95 V | -0.1 | 0.05 | 0.1 | μA |
| current | I _{IH} , I _{IL} | vi = 5.5 v 0i 0 | | Full | 1.55 V | -1 | | 1 | μΑ |

(1) The algebraic convention is used in this data sheet; the most negative value is shown in the minimum column.

SCDS185C - JANUARY 2005-REVISED SEPTEMBER 2012

www.ti.com

STRUMENTS

EXAS

Electrical Characteristics for 1.8-V Supply⁽¹⁾ (continued)

 $V_{+} = 1.65$ V to 1.95 V, $T_{A} = -40^{\circ}$ C to 85°C (unless otherwise noted)


| PARAMETER | SYMBOL | TEST CO | NDITIONS | T _A | V. | MIN | TYP | MAX | UNIT |
|------------------------------|-----------------------|--|--|----------------|---------------------|-----|------|-----|------|
| Dynamic | • | | | | | | | | |
| | | N 40N | 0 05 -5 | 25°C | 1.8 V | 9.5 | 10 | 12 | |
| Turn-on time | t _{ON} | $V_{COM} = 1.3 \text{ V},$ R _L = 300 Ω, | C _L = 35 pF, See Figure 17 | Full | 1.65 V to 1.95 V | 8.5 | | 13 | ns |
| | | V 10V | 0 25 pF | 25°C | 1.8 V | 1.5 | 2 | 4 | |
| Turn-off time | t _{OFF} | $V_{COM} = 1.3 \text{ V},$ R _L = 300 Ω, | C _L = 35 pF, See Figure 17 | Full | 1.65 V to 1.95 V | 1.5 | | 5.5 | ns |
| Charge injection | Q _C | $V_{GEN} = 0,$ $C_L = 0.1 \text{ nF},$ | See Figure 20 | 25°C | 1.8 V | | 1 | | pC |
| NO OFF capacitance | C _{NO(OFF)} | $V_{NO} = V_+ \text{ or GND},$ Switch OFF, | See Figure 16 | 25°C | 1.8 V | | 6.8 | | pF |
| COM OFF capacitance | C _{COM(OFF)} | $V_{COM} = V_{+} \text{ or GND},$ Switch OFF, | See Figure 16 | 25°C | 1.8 V | | 6.8 | | pF |
| NO ON capacitance | C _{NO(ON)} | V _{NO} = V ₊ or GND, Switch ON, | See Figure 16 | 25°C | 1.8 V | | 14 | | pF |
| COM ON capacitance | C _{COM(ON)} | $V_{COM} = V_{+} \text{ or GND},$ Switch ON, | See Figure 16 | 25°C | 1.8 V | | 14 | | pF |
| Digital input capacitance | CI | $V_I = V_+ \text{ or GND},$ | See Figure 16 | 25°C | 1.8 V | | 2.2 | | pF |
| Bandwidth | BW | $R_L = 50 \Omega$, Switch ON, | See Figure 18 | 25°C | 1.8 V | | 400 | | MHz |
| OFF isolation | O _{ISO} | $R_L = 50 \Omega$, f = 10 MHz, | Switch OFF, See Figure 19 | 25°C | 1.8 V | | -68 | | dB |
| Total harmonic distortion | THD | $R_L = 600 \Omega,$ $C_L = 50 pF,$ | f = 20 Hz to 20 kHz, See Figure 21 | 25°C | 1.8 V | | 0.32 | | % |
| Supply | | | | | | | | | |
| Positive supply | 1 | V = V or CND | Switch ON or OFF | 25°C | 1.95 V | | 0.05 | 1 | |
| current | I ₊ | $V_{I} = V_{+}$ or GND, | Switch ON OF OFF | Full | 1.90 V | | | 5 | μA |

SCDS185C - JANUARY 2005 - REVISED SEPTEMBER 2012

TEXAS INSTRUMENTS

www.ti.com

TYPICAL PERFORMANCE



SCDS185C – JANUARY 2005 – REVISED SEPTEMBER 2012

TEXAS INSTRUMENTS

www.ti.com

TYPICAL PERFORMANCE




Figure 4. Leakage Current vs Temperature ($V_{+} = 5.5 V$)




Figure 6. t_{ON} and t_{OFF} vs Supply Voltage

TEXAS INSTRUMENTS

SCDS185C – JANUARY 2005–REVISED SEPTEMBER 2012

TYPICAL PERFORMANCE




Figure 9. Bandwidth (V₊ = 5 V)

| www.ti.com | |
|------------|--|

SCDS185C – JANUARY 2005–REVISED SEPTEMBER 2012

TEXAS INSTRUMENTS

www.ti.com






Figure 12. Power-Supply Current vs Temperature (V₊ = 5 V)

SCDS185C - JANUARY 2005 - REVISED SEPTEMBER 2012

www.ti.com

Table 3. PIN DESCRIPTION

| PIN | NAME | DESCRIPTION |
|-----|----------------|--------------------------------------|
| 1 | NO | Normally open |
| 2 | COM | Common |
| 3 | GND | Digital ground |
| 4 | IN | Digital control to connect COM to NO |
| 5 | V ₊ | Power supply |

Table 4. PARAMETER DESCRIPTION

| SYMBOL | DESCRIPTION |
|-----------------------------------|--|
| V _{COM} | Voltage at COM |
| V _{NO} | Voltage at NO |
| r on | Resistance between COM and NO ports when the channel is ON |
| r _{on(flat)} | Difference between the maximum and minimum value of ron in a channel over the specified range of conditions |
| I _{NO(OFF)} | Leakage current measured at the NO port, with the corresponding channel (NO to COM) in the OFF state |
| I _{NO(ON)} | Leakage current measured at the NO port, with the corresponding channel (NO to COM) in the ON state and the output (COM) open |
| I _{COM(OFF)} | Leakage current measured at the COM port, with the corresponding channel (COM to NO) in the OFF state |
| I _{COM(ON)} | Leakage current measured at the COM port, with the corresponding channel (COM to NO) in the ON state and the output (NO) open |
| VIH | Minimum input voltage for logic high for the control input (IN) |
| V _{IL} | Maximum input voltage for logic low for the control input (IN) |
| VI | Voltage at the control input (IN) |
| I _{IH} , I _{IL} | Leakage current measured at the control input (IN) |
| t _{ON} | Turn-on time for the switch. This parameter is measured under the specified range of conditions and by the propagation delay between the digital control (IN) signal and analog output (COM or NO) signal when the switch is turning ON. |
| t _{OFF} | Turn-off time for the switch. This parameter is measured under the specified range of conditions and by the propagation delay between the digital control (IN) signal and analog output (COM or NO) signal when the switch is turning OFF. |
| Q _C | Charge injection is a measurement of unwanted signal coupling from the control (IN) input to the analog (NO or COM) output. This is measured in coulomb (C) and measured by the total charge induced due to switching of the control input. Charge injection, $Q_C = C_L \times \Delta V_{COM}$, C_L is the load capacitance and ΔV_{COM} is the change in analog output voltage. |
| C _{NO(OFF)} | Capacitance at the NO port when the corresponding channel (NO to COM) is OFF |
| C _{NO(ON)} | Capacitance at the NO port when the corresponding channel (NO to COM) is ON |
| C _{COM(OFF)} | Capacitance at the COM port when the corresponding channel (COM to NO) is OFF |
| C _{COM(ON)} | Capacitance at the COM port when the corresponding channel (COM to NO) is ON |
| CI | Capacitance of IN |
| O _{ISO} | OFF isolation of the switch is a measurement of OFF-state switch impedance. This is measured in dB in a specific frequency, with the corresponding channel (NO to COM) in the OFF state. |
| BW | Bandwidth of the switch. This is the frequency in which the gain of an ON channel is -3 dB below the DC gain. |
| THD | Total harmonic distortion is defined as the ratio of the root mean square (RMS) value of the second, third, and higher harmonics to the magnitude of fundamental harmonic. |
| I+ | Static power-supply current with the control (IN) pin at V_+ or GND |
| ΔI_+ | This is the increase in I_+ for each control (IN) input that is at the specified voltage, rather than at V ₊ or GND. |



SCDS185C – JANUARY 2005 – REVISED SEPTEMBER 2012

www.ti.com

PARAMETER MEASUREMENT INFORMATION




Figure 13. ON-State Resistance (ron)






Figure 14. OFF-State Leakage Current (I_{COM(OFF)}, I_{NO(OFF)})







www.ti.com

SCDS185C – JANUARY 2005 – REVISED SEPTEMBER 2012







Figure 16. Capacitance (C_I, C_{COM(OFF)}, C_{COM(ON)}, C_{NO(OFF)}, C_{NO(ON)})



(1) All input pulses are supplied by generators having the following characteristics: PRR \leq 10 MHz, Z_O = 50 Ω , t_f < 5 ns, t_f < 5 ns.

(2) C_L includes probe and jig capacitance.

(3) See Electrical Characteristics for V_{COM}.

Figure 17. Turn-On (t_{ON}) and Turn-Off Time (t_{OFF})

SCDS185C - JANUARY 2005 - REVISED SEPTEMBER 2012



www.ti.com

PARAMETER MEASUREMENT INFORMATION (continued)




Figure 18. Bandwidth (BW)





Figure 19. OFF Isolation (O_{ISO})



www.ti.com

SCDS185C – JANUARY 2005 – REVISED SEPTEMBER 2012


PARAMETER MEASUREMENT INFORMATION (continued)



(1) All input pulses are supplied by generators having the following characteristics: PRR \leq 10 MHz, Z_O = 50 Ω , t_r < 5 ns, t_f < 5 ns.

(2) C_L includes probe and jig capacitance.





(1) C_L includes probe and jig capacitance.

Figure 21. Total Harmonic Distortion (THD)

SCDS185C – JANUARY 2005–REVISED SEPTEMBER 2012

REVISION HISTORY

| Changes from Revision B (April 2006) to Revision C | | | | | | |
|--|--------------------------------------|---|---|--|--|--|
| • | Updated package options information. | 2 | 2 | | | |

Copyright © 2005–2012, Texas Instruments Incorporated

www.ti.com





25-Oct-2016

PACKAGING INFORMATION

| Orderable Device | Status (1) | Package Type | Package Drawing | Pins | Package Qty | Eco Plan (2) | Lead/Ball Finish (6) | MSL Peak Temp (3) | Op Temp (°C) | Device Marking (4/5) | Samples |
|------------------|---------------|--------------|--------------------|------|----------------|----------------------------|-------------------------|----------------------|--------------|-------------------------|---------|
| TS5A1066DBVR | ACTIVE | SOT-23 | DBV | 5 | 3000 | Green (RoHS & no Sb/Br) | CU NIPDAU CU SN | Level-1-260C-UNLIM | -40 to 85 | (JADF ~ JADR) | Samples |
| TS5A1066DBVRG4 | ACTIVE | SOT-23 | DBV | 5 | 3000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM | -40 to 85 | JADF | Samples |
| TS5A1066DCKR | ACTIVE | SC70 | DCK | 5 | 3000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM | -40 to 85 | (JD5 ~ JDF ~ JDR) | Samples |
| TS5A1066DCKRG4 | ACTIVE | SC70 | DCK | 5 | 3000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM | -40 to 85 | (JD5 ~ JDF ~ JDR) | Samples |
| TS5A1066YZPR | ACTIVE | DSBGA | YZP | 5 | 3000 | Green (RoHS & no Sb/Br) | SNAGCU | Level-1-260C-UNLIM | -40 to 85 | (JD7 ~ JDN) | Samples |

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.

TBD: The Pb-Free/Green conversion plan has not been defined.

Pb-Free (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

Pb-Free (RoHS Exempt): This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.



www.ti.com

25-Oct-2016

⁽⁶⁾ Lead/Ball Finish - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer:The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

PACKAGE MATERIALS INFORMATION

www.ti.com


Texas Instruments

TAPE AND REEL INFORMATION





QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE




| *All dimensions are nominal | | | | | | | | | | | | |
|-----------------------------|-----------------|--------------------|---|------|--------------------------|--------------------------|------------|------------|------------|------------|-----------|------------------|
| Device | Package Type | Package Drawing | | SPQ | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
| TS5A1066DBVR | SOT-23 | DBV | 5 | 3000 | 178.0 | 9.0 | 3.23 | 3.17 | 1.37 | 4.0 | 8.0 | Q3 |
| TS5A1066DBVR | SOT-23 | DBV | 5 | 3000 | 180.0 | 8.4 | 3.23 | 3.17 | 1.37 | 4.0 | 8.0 | Q3 |
| TS5A1066DBVRG4 | SOT-23 | DBV | 5 | 3000 | 178.0 | 9.0 | 3.23 | 3.17 | 1.37 | 4.0 | 8.0 | Q3 |
| TS5A1066DCKR | SC70 | DCK | 5 | 3000 | 178.0 | 9.0 | 2.4 | 2.5 | 1.2 | 4.0 | 8.0 | Q3 |
| TS5A1066DCKR | SC70 | DCK | 5 | 3000 | 178.0 | 9.2 | 2.4 | 2.4 | 1.22 | 4.0 | 8.0 | Q3 |
| TS5A1066YZPR | DSBGA | YZP | 5 | 3000 | 178.0 | 9.2 | 1.02 | 1.52 | 0.63 | 4.0 | 8.0 | Q1 |

Texas Instruments

www.ti.com

PACKAGE MATERIALS INFORMATION

3-Aug-2017



*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Length (mm) | Width (mm) | Height (mm) |
|----------------|--------------|-----------------|------|------|-------------|------------|-------------|
| TS5A1066DBVR | SOT-23 | DBV | 5 | 3000 | 180.0 | 180.0 | 18.0 |
| TS5A1066DBVR | SOT-23 | DBV | 5 | 3000 | 202.0 | 201.0 | 28.0 |
| TS5A1066DBVRG4 | SOT-23 | DBV | 5 | 3000 | 180.0 | 180.0 | 18.0 |
| TS5A1066DCKR | SC70 | DCK | 5 | 3000 | 180.0 | 180.0 | 18.0 |
| TS5A1066DCKR | SC70 | DCK | 5 | 3000 | 180.0 | 180.0 | 18.0 |
| TS5A1066YZPR | DSBGA | YZP | 5 | 3000 | 220.0 | 220.0 | 35.0 |

DCK (R-PDSO-G5)

PLASTIC SMALL-OUTLINE PACKAGE



- NOTES: A. All linear dimensions are in millimeters.
 - B. This drawing is subject to change without notice.
 - C. Body dimensions do not include mold flash or protrusion. Mold flash and protrusion shall not exceed 0.15 per side.
 - D. Falls within JEDEC MO-203 variation AA.



LAND PATTERN DATA



NOTES:

- A. All linear dimensions are in millimeters.B. This drawing is subject to change without notice.
- C. Customers should place a note on the circuit board fabrication drawing not to alter the center solder mask defined pad.
- D. Publication IPC-7351 is recommended for alternate designs.
- E. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Example stencil design based on a 50% volumetric metal load solder paste. Refer to IPC-7525 for other stencil recommendations.



YZP0005



PACKAGE OUTLINE

DSBGA - 0.5 mm max height

DIE SIZE BALL GRID ARRAY



- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.



YZP0005

EXAMPLE BOARD LAYOUT

DSBGA - 0.5 mm max height

DIE SIZE BALL GRID ARRAY



NOTES: (continued)

3. Final dimensions may vary due to manufacturing tolerance considerations and also routing constraints. For more information, see Texas Instruments literature number SNVA009 (www.ti.com/lit/snva009).




YZP0005

EXAMPLE STENCIL DESIGN

DSBGA - 0.5 mm max height

DIE SIZE BALL GRID ARRAY



NOTES: (continued)

4. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release.



DBV (R-PDSO-G5)

PLASTIC SMALL-OUTLINE PACKAGE



- All linear dimensions are in millimeters. A.
 - This drawing is subject to change without notice. Β.
 - Body dimensions do not include mold flash or protrusion. Mold flash and protrusion shall not exceed 0.15 per side. C.
 - D. Falls within JEDEC MO-178 Variation AA.



DBV (R-PDSO-G5)

PLASTIC SMALL OUTLINE



NOTES:

A. All linear dimensions are in millimeters.B. This drawing is subject to change without notice.

- C. Customers should place a note on the circuit board fabrication drawing not to alter the center solder mask defined pad.
- D. Publication IPC-7351 is recommended for alternate designs.
- E. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Example stencil design based on a 50% volumetric metal load solder paste. Refer to IPC-7525 for other stencil recommendations.



IMPORTANT NOTICE

Texas Instruments Incorporated (TI) reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete.

TI's published terms of sale for semiconductor products (http://www.ti.com/sc/docs/stdterms.htm) apply to the sale of packaged integrated circuit products that TI has qualified and released to market. Additional terms may apply to the use or sale of other types of TI products and services.

Reproduction of significant portions of TI information in TI data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such reproduced documentation. Information of third parties may be subject to additional restrictions. Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyers and others who are developing systems that incorporate TI products (collectively, "Designers") understand and agree that Designers remain responsible for using their independent analysis, evaluation and judgment in designing their applications and that Designers have full and exclusive responsibility to assure the safety of Designers' applications and compliance of their applications (and of all TI products used in or for Designers' applications) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to their applications, Designer has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any applications that include TI products, Designer will thoroughly test such applications and the functionality of such TI products as used in such applications.

TI's provision of technical, application or other design advice, quality characterization, reliability data or other services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using TI Resources in any way, Designer (individually or, if Designer is acting on behalf of a company, Designer's company) agrees to use any particular TI Resource solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

Designer is authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNER AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

Unless TI has explicitly designated an individual product as meeting the requirements of a particular industry standard (e.g., ISO/TS 16949 and ISO 26262), TI is not responsible for any failure to meet such industry standard requirements.

Where TI specifically promotes products as facilitating functional safety or as compliant with industry functional safety standards, such products are intended to help enable customers to design and create their own applications that meet applicable functional safety standards and requirements. Using products in an application does not by itself establish any safety features in the application. Designers must ensure compliance with safety-related requirements and standards applicable to their applications. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equipment includes, without limitation, all medical devices identified by the U.S. Food and Drug Administration as Class III devices and equivalent classifications outside the U.S.

TI may expressly designate certain products as completing a particular qualification (e.g., Q100, Military Grade, or Enhanced Product). Designers agree that it has the necessary expertise to select the product with the appropriate qualification designation for their applications and that proper product selection is at Designers' own risk. Designers are solely responsible for compliance with all legal and regulatory requirements in connection with such selection.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's noncompliance with the terms and provisions of this Notice.

> Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated