ETR0303 005

Large Current Positive Voltage Regulators

■GENERAL DESCRIPTION

The XC6203 series are highly precise, low power consumption, 3 terminal positive voltage regulators manufactured using CMOS and laser trimming technologies.

The series provides large currents with a significantly small dropout voltage.

The XC6203P consists of a driver transistor, a current limiter, a precision reference voltage and an error amplifier. The XC6203E is also available but without the current limiter function. Output voltage is selectable in 0.1V increments between a voltage of 1.8V and 6.0V.

SOT-23, SOT-89, SOT-223 package are available.

■APPLICATIONS

- Magnetic disk drive
- Note PCs / Tabet PCs
- Digital still cameras /Camcorders
- Digital audio equipments
- Reference voltage sources
- Multi-function power supplies

■FEATURES

Maximum Output Current : 400mA (3.3V)

Maximum Operating Voltage : 8.0V

Output Voltage Range : 1.8V ~ 6.0V

(selectable in 0.1V increments)

Highly Accurate : $\pm 2\%$

: ± 100 ppm/°C (TYP.)

Dropout Voltage : 150mV @ 100mA,

300mV @ 200mA


Operating Ambient Temperature: -40°C ~ 85°C

Packages : SOT-23, SOT-89,


SOT-223

Environmentally Friendly : EU RoHS Compliant, Pb Free


■TYPICAL APPLICATION CIRCUIT





■TYPICAL PERFORMANCE CHARACTERISTICS



■PIN CONFIGURATION







■PIN ASSIGNMENT

PIN NU	MBER	PIN NAME	FUNCTIONS	
SOT-23	SOT-89/SOT-223	PIN NAIVIE	FUNCTIONS	
1	1	Vss	Ground	
3	2	VIN	Power Input	
2	3	Vout	Output	

■PRODUCT CLASSIFICATION


Ordering Information


XC6203 123456-7(*1)

DESIGNATOR	ITEM	SYMBOL	DESCRIPTION
1	Type of Regulator	Р	Current limiter circuit built-in
U	Type of Regulator	Е	No current limiter circuit built-in
23	Output Voltage	18~	e.g. 1.8V → ③=1, ④=8
	Output Assurance	2	$\pm 2\%$ Output voltage is $\{x.x0V\}$ (the 2 nd decimal place is "0")
4	Output Accuracy	Α	±2% Output voltage is {x.x5V} (the 2 nd decimal place is "5)
		MR	SOT-23 (3,000/Reel)
	Packages (Order Unit)	MR-G	SOT-23 (3,000/Reel)
5 6-7 ^(*1)		PR	SOT-89 (1,000/Reel)
30-0		PR-G	SOT-89 (1,000/Reel)
		FR	SOT-223 (1,000/Reel)
		FR-G	SOT-223 (1,000/Reel)

^(*1) The "-G" suffix denotes Halogen and Antimony free as well as being fully EU RoHS compliant.

■BLOCK DIAGRAMS





^{*} Diodes inside the circuits are ESD protection diodes and parasitic diodes.

■ ABSOLUTE MAXIMUM RATINGS

Ta = 25°C

PARAM	PARAMETER		RATINGS	UNITS	
Input V	oltage	VIN	-0.3~+12.0	V	
Output (Current	lout	600(*1)	mA	
Output \	√oltage	Vout	-0.3~V _{IN} +0.3	V	
	SOT-23		250		
	301-23		500(PCB mounted)(*2)		
Power	SOT-89	Pd	500	mW	
Dissipation		Pu Pu	1000(PCB mounted)(*2)	IIIVV	
			300		
	SOT-223		1500(PCB mounted)(*2)]	
Operating Ambie	Operating Ambient Temperature		-40~+85	°C	
Storage Te	mperature	Tstg	-55 ~ +125	°C	

^{*1:} $I_{OUT} \le Pd / (V_{IN}-V_{OUT})$

^{*2} These values are example data which is taken with the PCB mounted. Please refer to pages 20 to 22 for details.

■ELECTRICAL CHARACTERISTICS

Ta=25°C XC6203 Series Type E

PARAMETER	SYMBOL	CON	DITIONS	MIN.	TYP.	MAX.	UNITS	CIRCUIT
Output Voltage	V _{OUT(E)} (*2)	I _{OUT} =40mA	1.8V≦V _{OUT(T)}	×0.98	V _{OUT(T)} (*3)	×1.02	V	2
Maximum Output Current	I _{OUTMAX}	V _{OUT} ≧E-1 ^(*4))	E-2 ^(*4)	-	-	mA	2
Load Regulation	ΔV_{OUT}	1.8V≦V _{OUT(} 1mA≦I _{OUT} ≦	,	-	40	100	mV	2
Dropout Voltage 1	Vdif1 ^(*5)	I _{OUT} =100mA		-	E-3	3(*4)	mV	<u> </u>
Dropout Voltage 2	Vdif2 ^(*5)	I _{OUT} =200mA		-	E-4	4(*4)	mV	2
Supply Current	I _{DD}			-	E-	5(*4)	μA	①
Line Regulation	$\Delta V_{OUT}/$ $(\Delta V_{IN} \cdot V_{OUT})$	1.8V≦V _{OUT(T)} V _{OUT(T)} +1.0V I _{OUT} =40mA	r), ≦V _{IN} ≦8.0V,	-	0.2	0.3	%/V	2
Input Voltage	V _{IN}			-	-	8.0	V	2
Output Voltage Temperature Characteristics	ΔV _{OUT} / (ΔTopr•V _{OUT})	I _{OUT} =40mA -40°C≦Topr	-`≦85°C	-	±100	-	ppm/°C	2

*5: Vdif = {V_{IN1} - V_{OUT1}}
 V_{IN1}: The input voltage when V_{OUT1} appears as input voltage is gradually decreased.
 V_{OUT1}: A voltage equal to 98% of the output voltage when "V_{OUT (T)} + 1.0V" is input.

^{*1:} Unless overwise stated, V_{IN}=V_{OUT(T)}+1.0V
*2: V_{OUT(E)}: Effective output voltage
*3: V_{OUT(T)}: Nominal output voltage.
*4: Please refer to the table E-1, E-2, E-3, E-4, E-5.

■ ELECTRICAL CHARACTERISTICS (Continued)

XC6203 Series Type P Ta=25°C

PARAMETER	SYMBOL	CONE	DITIONS	MIN.	TYP.	MAX.	UNITS	CIRCUIT
Output Voltage	V _{OUT(E)} (*2)	I _{OUT} =40mA	1.8V≦V _{OUT(T)}	×0.98	V _{OUT(T)} (*3)	×1.02	V	2
Maximum Output Current	I _{OUTMAX}	V _{OUT} ≧E-1 ^{(*4})	E-2 ^(*4)	-	-	mA	2
Load Regulation	ΔV_{OUT}	1.8V≦V _{OUT(} 1mA≦I _{OUT} ≦	- /	-	40	100	mV	2
Dropout Voltage 1	Vdif1 ^(*5)	I _{OUT} =100mA		1	E-3	3(*4)	mV	2
Dropout Voltage 2	Vdif2 ^(*5)	I _{OUT} =200mA		ı	E-4	1(*4)	mV	۷
Supply Current	I _{DD}			-	E-\$	5(*4)	μA	1
Line Regulation	$\Delta V_{OUT}/$ $(\Delta V_{IN} \cdot V_{OUT})$	1.8V≦V _{OUT(1} V _{OUT(T)} +1.0V I _{OUT} =40mA	• /	-	0.2	0.3	%/V	2
Input Voltage	V _{IN}			-	-	8.0	V	2
Output Voltage Temperature Characteristics	ΔV _{OUT} / (ΔTopr•V _{OUT})	I _{OUT} =40mA -40°C≦Topr≦85°C		-	±100	-	ppm/°C	2
Short-Circuit Current	I _{SHORT}	V _{OUT} =V _{SS}		-	60	-	mA	2

^{*1:} Unless overwise stated, $V_{IN}=V_{OUT(T)}+1.0V$

5/24

^{*2:} V_{OUT(E)}: Effective output voltage
*3: V_{OUT(T)}: Nominal output voltage.
*4: Please refer to the table E-1, E-2, E-3, E-4, E-5.

^{*5:} Vdif = $\{V_{\text{IN1}} - V_{\text{OUT1}}\}$ V_{IN1} : The input voltage when V_{OUT1} appears as input voltage is gradually decreased. V_{OUT1} : A voltage equal to 98% of the output voltage when " $V_{\text{OUT}(T)} + 1.0V$ " is input.

■ELECTRICAL CHARACTERISTICS (Continued)

NOMINAL OUTPUT		E-1	E-2	E	:-3	E	-4	E	-5	
VOLTAGE VOL	NOMINAL									
Vouting Vout		VOLT	ΓAGE	VOLT	VOLTAGE1		VOLTAGE2		CURRENT	
1.8		V _{OUT2} (V)		V _{dif1}		V _{dif2}		I _{SS} (
1.9 Vouriei×0.9 2.0 2.1 2.2 2.3 2.4 2.5 2.8 2.8 2.9 3.0 3.1 3.2 3.3 3.4 3.5 3.6 3.7 3.8 3.9 4.0 4.1 4.1 4.2 4.3 4.4 4.5 4.5 4.6 4.7 4.8 4.9 5.0 5.1 5.2 5.3	$V_{OUT(T)}$	-	MIN.	TYP.	MAX.	TYP.	MAX.	TYP.	MAX.	
1.9 2.0 2.1 2.1 2.2 2.3 2.4 2.5 Vourse)×0.93 2.6 2.7 2.8 2.85 2.9 3.0 3.1 3.2 3.3 3.4 3.5 3.6 3.7 3.8 3.9 4.0 4.1 4.2 4.3 4.4 4.5 4.6 4.7 4.8 4.9 5.0 5.0 5.1 5.2 5.3		V _{OUT(E)} × 0.9								
2.1 2.2 2.3 2.4 2.5 2.6 2.7 2.8 2.85 2.9 3.0 3.1 3.2 3.3 3.4 3.5 3.6 3.7 3.8 3.9 4.0 4.1 4.2 4.3 4.4 4.5 4.6 4.6 4.7 4.8 4.9 5.0 5.1 5.2 5.3		001(L)								
2.2 2.3 2.4 2.5 2.6 2.7 2.8 2.85 2.9 3.0 3.1 3.2 3.3 3.4 3.5 3.6 3.7 3.8 3.9 4.0 4.0 4.1 4.2 4.3 4.4 4.5 4.6 4.7 4.8 4.9 5.0 5.1 5.2 5.3										
2.3 2.4 2.5 2.6 2.7 2.8 2.85 2.9 3.0 3.1 3.2 3.3 3.4 3.5 3.6 3.7 3.8 3.9 4.0 4.0 4.1 4.2 4.3 4.4 4.5 4.6 4.6 4.7 4.8 4.9 5.0 5.1 5.2 5.3				200	300	400	600			
2.4 2.5 2.6 2.7 2.8 2.85 2.9 3.0 3.1 3.2 3.3 3.4 3.5 3.6 3.7 3.8 3.9 4.0 4.1 4.2 4.3 4.5 4.6 4.7 4.8 4.9 5.0 5.1 5.2 5.3										
2.5										
2.6 2.7 2.8 2.85 2.9 3.0 3.1 3.2 3.3 3.4 3.5 3.6 3.7 3.8 3.9 4.0 4.1 4.2 4.3 4.4 4.5 4.6 4.7 4.8 4.9 5.0 5.1 5.2 5.3					ı	ı				
2.7 2.8 2.85 2.9 3.0 3.1 3.2 3.3 3.4 3.5 3.6 3.7 3.8 3.9 4.0 4.1 4.2 4.3 4.4 4.5 4.6 4.7 4.8 4.9 5.0 5.1 5.2 5.3		$V_{OUT(E)} \times 0.93$								
2.8 2.85 2.9 3.0 3.1 3.2 3.3 3.4 3.5 3.6 3.7 3.8 3.9 4.0 4.1 4.2 4.3 4.4 4.5 4.6 4.7 4.8 4.9 5.0 5.1 5.2 5.3								8.0	16.0	
2.85 2.9 3.0 3.1 3.2 3.3 3.4 3.5 3.6 3.7 3.8 3.9 4.0 4.1 4.2 4.3 4.4 4.5 4.6 4.7 4.8 4.9 5.0 5.1 5.2 5.3				170	250	320	500		.0.0	
2.9 3.0 3.1 3.2 3.3 3.4 3.5 3.6 3.7 3.8 3.9 4.0 4.1 4.2 4.3 4.4 4.5 4.6 4.7 4.8 4.9 5.0 5.1 5.2 5.3										
3.0 3.1 3.2 3.3 3.4 3.5 3.6 3.7 3.8 3.9 4.0 4.1 4.2 4.3 4.4 4.5 4.6 4.7 4.8 4.9 5.0 5.1 5.2 5.3										
3.1 3.2 3.3 3.4 3.5 3.6 3.7 3.8 3.9 4.0 4.1 4.2 4.3 4.4 4.5 4.6 4.7 4.8 4.9 5.0 5.1 5.2 5.3										
3.2 3.3 3.4 3.5 3.6 3.7 3.8 3.9 4.0 4.1 4.2 4.3 4.4 4.5 4.6 4.7 4.8 4.9 5.0 5.1 5.2 5.3										
3.3 3.4 3.5 3.6 3.7 3.8 3.9 4.0 4.1 4.2 4.3 4.4 4.5 4.6 4.7 4.8 4.9 5.0 5.1 5.2 5.3										
3.4 3.5 3.6 3.7 3.8 3.9 4.0 4.1 4.2 4.3 4.4 4.5 4.6 4.7 4.8 4.9 5.0 5.1 5.2 5.3										
3.5 3.6 3.7 3.8 3.9 4.0 4.1 4.2 4.3 4.4 4.5 4.6 4.7 4.8 4.9 5.0 5.1 5.2 5.3										
3.6 3.7 3.8 3.9 4.0 4.1 4.2 4.3 4.4 4.5 4.6 4.7 4.8 4.9 5.0 5.1 5.2 5.3				150	220	300	420			
3.7 3.8 3.9 4.0 4.1 4.2 4.3 4.4 4.5 4.6 4.7 4.8 4.9 5.0 5.1 5.2 5.3			400							
3.8 3.9 4.0 4.1 4.2 4.3 4.4 4.5 4.6 4.7 4.8 4.9 5.0 5.1 5.2 5.3			400							
3.9 4.0 4.1 4.2 4.3 4.4 4.5 4.6 4.7 4.8 4.9 5.0 5.1 5.2 5.3										
4.0 4.1 4.2 4.3 4.4 4.5 4.6 4.7 4.8 4.9 5.0 5.1 5.2 5.3										
4.1 4.2 4.3 4.4 4.5 4.6 4.7 4.8 4.9 5.0 5.1 5.2 5.3										
4.2 4.3 4.4 4.5 4.6 4.7 4.8 4.9 5.0 5.1 5.2 5.3										
4.3 4.4 4.5 4.6 4.7 4.8 4.9 5.0 5.1 5.2 5.3 100 180 200 320										
4.5 4.6 4.7 4.8 4.9 5.0 5.1 5.2 5.3 130 200 250 380 10.0 20.0 200 380 10.0 20.0	4.3	V _{OUT(E)} ×0.96								
4.5 4.6 4.7 4.8 4.9 5.0 5.1 5.2 5.3 10.0 20.0 20.0				405	655	0=5	225			
4.7 4.8 4.9 5.0 5.1 5.2 5.3 100 180 200 320	4.5			130	200	250	380	10.0	20.0	
4.8 4.9 5.0 5.1 5.2 5.3 100 180 200 320	4.6									
4.9 5.0 5.1 5.2 5.3 100 180 200 320	4.7									
5.0 5.1 5.2 5.3 100 180 200 320	4.8									
5.1 5.2 5.3 100 180 200 320	4.9									
5.2 5.3 100 180 200 320	5.0									
5.3	5.1									
5.3	5.2			100	400	200	220			
	5.3			100	180	200	320			
5.4	5.4									
5.5	5.5									

^{*)} The symbol is as same as that in the chart of electrical characteristics.


■ELECTRICAL CHARACTERISTICS (Continued)

NOMINAL	E-1	E-2	E	-3	E	-4	Е	-5
OUTPUT VOLTAGE	MAXIMUM OUTPUT VOLTAGE		DROPOUT VOLTAGE1		DROPOUT VOLTAGE2		SUPPLY CURRENT	
VOLTAGE	V _{OUT2} (V)	I _{OUTMAX} (mA)	V_{dif1}	(mV)	V _{dif2}	(mV)	I _{SS} ((<i>µ</i> A)
$V_{\text{OUT(T)}}$	-	MIN.	TYP.	MAX.	TYP.	MAX.	TYP.	MAX.
5.6								
5.7								
5.8	V _{OUT(E)} ×0.96	400	100	180	200	320	10.0	20.0
5.9								
6.0								


^{*)} The symbol is as same as that in the chart of electrical characteristics.

■TYPICAL APPLICATION CIRCUIT

1) CIRCUIT(1)



2) CIRCUIT 2




■NOTES ON USE

- For temporary, transitional voltage drop or voltage rising phenomenon, the IC is liable to malfunction should the ratings be exceeded.
- 2. Where wiring impedance is high, operations may become unstable due to noise and/or phase lag depending on output current. Please keep the resistance low for the V_{BIAS} , V_{IN} and V_{SS} wiring in particular.
- 3. Please wire the C_{IN} and C_L as close to the IC as possible.
- 4. Capacitances of these capacitors (C_{IN}, C_L) are decreased by the influences of bias voltage and ambient temperature. Care shall be taken for capacitor selection to ensure stability of phase compensation from the point of ESR influence.
- 5. When it is used in a quite small input / output dropout voltage, output may go into unstable operation. Please test it thoroughly before using it in production.
- 6. Torex places an importance on improving our products and their reliability. We request that users incorporate fail-safe designs and post-aging protection treatment when using Torex products in their systems.


■TYPICAL PERFORMANCE CHARACTERISTICS

●XC6203E182PR


(1) Output Voltage vs. Output Current




(2) Output Voltage vs. Input Voltage




(3) Dropout Voltage vs. Output Current




(4) Supply Current vs. Input Voltage



(5) Output Voltage vs. Ambient Temperature




(6) Supply Current vs. Ambient Temperature



●XC6203E182PR (Continued)


(7) Input Transient Response

XC6203E182PR (1.8V)




(8) Load Transient Response

XC6203E182PR (1.8V)




XC6203E182PR (1.8V)




(9) Ripple Rejection Rate

XC6203E182PR (1.8V)




XC6203E182PR (1.8V)



●XC6203E252PR


(1) Output Voltage vs. Output Current

XC6203E252PR (2.5V)




(3) Dropout Voltage vs. Output Current

XC6203E252PR (2.5V)




(5) Output Voltage vs. Ambient Temperature

XC6203E252PR (2.5V)




(2) Output Voltage vs. Input Voltage

XC6203E252PR (2.5V)




(4) Supply Current vs. Input Voltage

XC6203E252PR (2.5V)




(6) Supply Current vs. Ambient Temperature


XC6203E252PR (2.5V)




●XC6203E252PR (Continued)


(7) Input Transient Response






(8) Load Transient Response






XC6203E252PR (2.5V)




(9) Ripple Rejection Rate

XC6203E252PR (2.5V)




XC6203E252PR (2.5V)




●XC6203E332PR


(1) Output Voltage vs. Output Current




(2) Output Voltage vs. Input Voltage




(3) Dropout Voltage vs. Output Current




(4) Supply Current vs. Input Voltage



(5) Output Voltage vs. Ambient Temperature





(6) Supply Current vs. Ambient Temperature



●XC6203E332PR (Continued)


(7) Input Transient Response






(8) Load Transient Response

XC6203E332PR (3.3V)




XC6203E332PR (3.3V)




(9) Ripple Rejection Rate

XC6203E332PR (3.3V)




XC6203E332PR (3.3V)



●XC6203E502PR


(1) Output Voltage vs. Output Current

XC6203E502PR (5.0V)




(2) Output Voltage vs. Input Voltage

XC6203E502PR (5.0V)




(3) Dropout Voltage vs. Output Current

XC6203E502PR (5.0V)




(4) Supply Current vs. Input Voltage

XC6203E502PR (5.0V)




(5) Output Voltage vs. Ambient Temperature

XC6203E502PR (5.0V)




(6) Supply Current vs. Ambient Temperature


XC6203E502PR (5.0V)




●XC6203E502PR (Continued)


(7) Input Transient Response







(8) Load Transient Response






(9) Ripple Rejection Rate






(10) Output Voltage vs. Output Current


XC6203P182 (1.8V)




XC6203P252 (2.5V)



XC6203P332 (3.3V)





XC6203P502 (5.0V)




■PACKAGING INFORMATION













●SOT-23 (unit:mm)









•SOT-23 Power Dissipation

Power dissipation data for the SOT-23 is shown in this page.

The value of power dissipation varies with the mount board conditions.

Please use this data as the reference data taken in the following.

1. Measurement Condition

Condition : Mount on a board Ambient : Natural convection Soldering : Lead (Pb) free

Board : Dimensions 40×40mm (1600mm² in one side)

Copper (Cu) traces occupy 50% of the board area

In top and back faces


Package heat-sink is tied to the copper traces

(Board of SOT-26 is used)

Material: Glass Epoxy (FR-4)

Thickness: 1.6mm

Through-hole: 4 x 0.8 Diameter




Evaluation Board (Unit: mm)

2. Power Dissipation vs. Ambient Temperature

Board Mount (Tjmax=125°C)

Ambient Temperature (°C)	Power Dissipation Pd (mW)	Thermal Resistance (°C/W)	
25	500	200.00	
85	200	200.00	



•SOT-89 Power Dissipation

Power dissipation data for the SOT-89 is shown in this page. The value of power dissipation varies with the mount board conditions. Please use this data as the reference data taken in the following.

1. Measurement Condition

Condition: Mount on a board Ambient: Natural convection Soldering: Lead (Pb) free

Board: Dimensions 40×40mm (1600mm² in one side) Copper (Cu) traces occupy 50% of the board area


In top and back faces

Package heat-sink is tied to the copper traces

Material: Glass Epoxy (FR-4)

Thickness: 1.6mm

Through-hole: 5 x 0.8 Diameter




Evaluation Board (Unit: mm)

2. Power Dissipation vs. Ambient Temperature

Board Mount (Tjmax=125°C)

Ambient Temperature (°C)	Power Dissipation Pd (mW)	Thermal Resistance (°C/W)	
25	1000	100.00	
85	400		



●SOT-223 Power Dissipation

Power dissipation data for the SOT-223 is shown in this page. The value of power dissipation varies with the mount board conditions. Please use this data as the reference data taken in the following condition.

1. Measurement Condition

Condition: Mount on a board
Ambient: Natural convection
Soldering: Lead (Pb) free

Board: Dimensions 40 x 40 mm (1600 mm² in one side)

Copper (Cu) traces occupy 50% of the board area


In top and back faces

Package heat-sink is tied to the copper traces

Material: Glass Epoxy (FR-4)

Thickness: 1.6 mm

Through-hole: 4 x 0.8 Diameter




Evaluation Board (Unit: mm)

2. Power Dissipation vs. Ambient Temperature


Board Mount (Tj max = 125°C)


()		
Ambient Temperature (°C)	Power Dissipation Pd(mW)	Thermal Resistance (°C/W)
25	1500	66.67
85	600	00.07




■MARKING RULE

●SOT-23, SOT-89, SOT-223







① represents product series

MARK	PRODUCT SERIES
3	XC6203xxxxx

② represents type of regulator

	MARK	PRODUCT SERIES	
VOLTAGE=0.1~3.0V	VOLTAGE=3.1∼6.0V	VOLTAGE=2.85V	FRODUCT SERIES
5	6	7	XC6203Pxxxxx
2	3	4	XC6203Exxxxx

3 represents output voltage

MARK	OUTPUT VOLTAGE (V)			MARK	OUTPUT VOLTAGE (V)		
0	1	3.1	_	F	_	4.6	_
1	_	3.2	_	Н	_	4.7	_
2	1	3.3	1	K	1.8	4.8	_
3	-	3.4	_	L	1.9	4.9	_
4	_	3.5	_	M	2.0	5.0	_
5	1	3.6	1	N	2.1	5.1	_
6	1	3.7	ı	Р	2.2	5.2	_
7	1	3.8	l	R	2.3	5.3	_
8	1	3.9	1	S	2.4	5.4	_
9	1	4.0	ı	Т	2.5	5.5	_
Α	-	4.1	_	U	2.6	5.6	_
В	_	4.2	_	V	2.7	5.7	_
С		4.3		X	2.8	5.8	2.85
D	-	4.4	ı	Y	2.9	5.9	_
Е	_	4.5	_	Z	3.0	6.0	_

4 represents production lot number

 $0\sim9$, A to Z or inverted characters of 0 to 9 and A to Z repeated (G, I, J, O, Q, W excluded)

- 1. The product and product specifications contained herein are subject to change without notice to improve performance characteristics. Consult us, or our representatives before use, to confirm that the information in this datasheet is up to date.
- 2. The information in this datasheet is intended to illustrate the operation and characteristics of our products. We neither make warranties or representations with respect to the accuracy or completeness of the information contained in this datasheet nor grant any license to any intellectual property rights of ours or any third party concerning with the information in this datasheet.
- 3. Applicable export control laws and regulations should be complied and the procedures required by such laws and regulations should also be followed, when the product or any information contained in this datasheet is exported.
- 4. The product is neither intended nor warranted for use in equipment of systems which require extremely high levels of quality and/or reliability and/or a malfunction or failure which may cause loss of human life, bodily injury, serious property damage including but not limited to devices or equipment used in 1) nuclear facilities, 2) aerospace industry, 3) medical facilities, 4) automobile industry and other transportation industry and 5) safety devices and safety equipment to control combustions and explosions. Do not use the product for the above use unless agreed by us in writing in advance.
- 5. Although we make continuous efforts to improve the quality and reliability of our products; nevertheless Semiconductors are likely to fail with a certain probability. So in order to prevent personal injury and/or property damage resulting from such failure, customers are required to incorporate adequate safety measures in their designs, such as system fail safes, redundancy and fire prevention features.
- 6. Our products are not designed to be Radiation-resistant.
- 7. Please use the product listed in this datasheet within the specified ranges.
- 8. We assume no responsibility for damage or loss due to abnormal use.
- 9. All rights reserved. No part of this datasheet may be copied or reproduced unless agreed by Torex Semiconductor Ltd in writing in advance.

TOREX SEMICONDUCTOR LTD.