## 1, 2 and 4-Channel Low Capacitance ESD Protection Arrays

#### **Product Description**

The CM1213A family of diode arrays has been designed to provide ESD protection for electronic components or subsystems requiring minimal capacitive loading. These devices are ideal for protecting systems with high data and clock rates or for circuits requiring low capacitive loading. Each ESD channel consists of a pair of diodes in series which steer the positive or negative ESD current pulse to either the positive ( $V_P$ ) or negative ( $V_N$ ) supply rail. A Zener diode is embedded between  $V_P$  and  $V_N$ , offering two advantages. First, it protects the  $V_{CC}$  rail against ESD strikes, and second, it eliminates the need for a bypass capacitor that would otherwise be needed for absorbing positive ESD strikes to ground. The CM1213A will protect against ESD pulses up to 12 kV per the IEC 61000–4–2 standard.

#### **Features**

- One, Two, and Four Channels of ESD Protection
   Note: For 6 and 8-channel Devices, See the CM1213 Datasheet
- Provides ESD Protection to IEC61000-4-2 Level 4
  - ◆ ±12 kV Contact Discharge
- Low Channel Input Capacitance of 0.85 pF Typical
- Minimal Capacitance Change with Temperature and Voltage
- Channel Input Capacitance Matching of 0.02 pF Typical is Ideal for Differential Dignals
- Each I/O Pin Can Withstand Over 1000 ESD Strikes\*
- SZ Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant

#### **Applications**

- USB2.0 Ports at 480 Mbps in Desktop PCs, Notebooks and Peripherals
- IEEE1394 Firewire<sup>®</sup> Ports at 400 Mbps/800 Mbps
- DVI Ports, HDMI Ports in Notebooks, Set Top Boxes, Digital TVs, LCD Displays
- Serial ATA Ports in Desktop PCs and Hard Disk Drives
- PCI Express Ports
- General Purpose High-Speed Data Line ESD Protection



#### ON Semiconductor®

#### www.onsemi.com







SO SUFFIX CASE 318

SOT-143 SR SUFFIX CASE 318A

SC-74 SO SUFFIX CASE 318F








MSOP-10 MR SUFFIX CASE 846AE

#### **MARKING DIAGRAMS**





XXX = Specific Device Code
M = Date Code
Pb-Free Package



XXXX = Specific Device Code A = Assembly Location

Y = Year
W = Work Week
Pb-Free Package


(Note: Microdot may be in either location)

#### ORDERING INFORMATION

See detailed ordering, marking and shipping information in the package dimensions section on page 2 of this data sheet.

<sup>\*</sup>Standard test condition is IEC61000–4–2 level 4 test circuit with each pin subjected to ±8 kV contact discharge for 1000 pulses. Discharges are timed at 1 second intervals and all 1000 strikes are completed in one continuous test run. The part is then subjected to standard production test to verify that all of the tested parameters are within spec after the 1000 strikes.

#### **BLOCK DIAGRAM**



**Table 1. ORDERING INFORMATION** 

Device	Marking	Package	Shipping <sup>†</sup>	
CM1213A-01SO	231	SOT23–3 3,000 / Tape & Re		
SZCM1213A-01SO*		(Pb-Free)		
CM1213A-02SR	D232	SOT143-4	3,000 / Tape & Reel	
SZCM1213A-02SR*		(Pb-Free)		
CM1213A-02SO	233	SC-74 (Pb-Free)	3,000 / Tape & Reel	
CM1213A-04S7	D38	SC70-6 (Pb-Free)	3,000 / Tape & Reel	
CM1213A-04MR	D237	MSOP-10 (Pb-Free)	4,000 / Tape & Reel	

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.
\*SZ Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC–Q101 Qualified and PPAP

Capable.

#### **Table 2. PIN DESCRIPTIONS**

1-0	1-Channel, 3-Lead SOT23-3 Package (CM1213A-01SO)					
Pin	Name	Туре	Description			
1	CH1	I/O	ESD Channel			
2	V <sub>P</sub>	PWR	Positive Voltage Supply Rail			
3	V <sub>N</sub>	GND	Negative Voltage Supply Rail			


2-0	2-Channel, 4-Lead SOT143-4 Package (CM1213A-02SR)				
Pin Name Type Description					
1	V <sub>N</sub>	GND	Negative Voltage Supply Rail		
2	CH1	I/O	ESD Channel		
3	CH2	I/O	ESD Channel		
4	V <sub>P</sub>	PWR	Positive Voltage Supply Rail		


2-Channel, SC-74 Package (CM1213A-02SO)				
Pin	Name	Туре	Description	
1	NC	-	No Connect	
2	VN	GND	Negative Voltage Supply Rail	
3	CH1	I/O	ESD Channel	
4	CH2	I/O	ESD Channel	
5	NC	-	No Connect	
6	VP	PWR	Positive Voltage Supply Rail	


	4-Channel, 6-Lead SC70-6 (CM1213A-04S7)				
Pin	Name	Туре	Description		
1	CH1	I/O	ESD Channel		
2	V <sub>N</sub>	GND	Negative Voltage Supply Rail		
3	CH2	I/O	ESD Channel		
4	СНЗ	I/O	ESD Channel		
5	V <sub>P</sub>	PWR	Positive Voltage Supply Rail		
6	CH4	I/O	ESD Channel		


4-C	4-Channel, 10-Lead MSOP-10 Package (CM1213A04MR)				
Pin	Name	Туре	Description		
1	CH1	I/O	ESD Channel		
2	NC	_	No Connect		
3	V <sub>P</sub>	PWR	Positive Voltage Supply Rail		
4	CH2	I/O	ESD Channel		
5	NC	_	No Connect		
6	CH3	I/O	ESD Channel		
7	NC	-	No Connect		
8	V <sub>N</sub>	GND	Negative Voltage Supply Rail		
9	CH4	I/O	ESD Channel		
10	NC	_	No Connect		


#### **PACKAGE/PINOUT DIAGRAMS**











#### **SPECIFICATIONS**

**Table 3. ABSOLUTE MAXIMUM RATINGS** 

Parameter	Rating	Units
Operating Supply Voltage (V <sub>P</sub> – V <sub>N</sub> )	6.0	V
Operating Temperature Range	-40 to +150	°C
Storage Temperature Range	-65 to +150	°C
DC Voltage at any channel input	$(V_N - 0.5)$ to $(V_P + 0.5)$	V
Package Power Rating SOT23–3, SOT143–4, SC–74, and SC70–6 Packages MSOP–10 Package	225 400	mW
ESD IEC 61000–4–2 Contact IEC 61000–4–2 Air ISO 10605 330 pF / 330 $\Omega$ Contact ISO 10605 330 pF / 2 k $\Omega$ Contact ISO 10605 150 pF / 2 k $\Omega$ Contact ISO 10605 150 pF / 2 k $\Omega$ Contact	±12 ±12 ±9 ±22 ±25	kV

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

Table 4. ELECTRICAL OPERATING CHARACTERISTICS (Note1)

Symbol	Parameter	Conditions	Min	Тур	Max	Units
V <sub>P</sub>	Operating Supply Voltage (V <sub>P</sub> -V <sub>N</sub> )			3.3	5.5	V
l <sub>P</sub>	Operating Supply Current	$(V_P - V_N) = 3.3 \text{ V}$			8.0	μΑ
V <sub>F</sub>	Diode Forward Voltage Top Diode Bottom Diode	I <sub>F</sub> = 8 mA; T <sub>A</sub> = 25°C	0.60 0.60	0.80 0.80	0.95 0.95	V
I <sub>LEAK</sub>	Channel Leakage Current	$T_A = 25^{\circ}C; V_P = 5 V, V_N = 0 V$		0.1	1.0	μΑ
C <sub>IN</sub>	Channel Input Capacitance	At 1 MHz, V <sub>P</sub> = 3.3 V, V <sub>N</sub> = 0 V, V <sub>IN</sub> = 1.65 V (Note 2)		0.85	1.2	pF
ΔC <sub>IN</sub>	Channel Input Capacitance Matching	At 1 MHz, V <sub>P</sub> = 3.3 V, V <sub>N</sub> = 0 V, V <sub>IN</sub> = 1.65 V (Note 2)		0.02		pF
V <sub>CL</sub>	Channel Clamp Voltage Positive Transients Negative Transients	$T_A = 25^{\circ}C$ , $I_{PP} = 1A$ , $t_P = 8/20 \mu S$ (Note 2)		+10 -1.7		V
R <sub>DYN</sub>	Dynamic Resistance Positive Transients Negative Transients	I <sub>PP</sub> = 1A, t <sub>P</sub> = 8/20 μS Any I/O pin to Ground (Note 2)		0.9 0.5		Ω

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

- 1. All parameters specified at  $T_A$  = 25°C unless otherwise noted. 2. Standard IEC 61000–4–2 with  $C_{Discharge}$  = 150 pF,  $R_{Discharge}$  = 330  $\Omega$ ,  $V_P$  = 3.3 V,  $V_N$  grounded. 3. These measurements performed with no external capacitor on  $V_P$  ( $V_P$  floating).

#### PERFORMANCE INFORMATION

### **Input Channel Capacitance Performance Curves**




Figure 1. Typical Variation of C<sub>IN</sub> vs. V<sub>IN</sub> (f = 1 MHz, V<sub>P</sub> = 3.3 V, V<sub>N</sub> = 0 V, 0.1  $\mu$ F Chip Capacitor between V<sub>P</sub> and V<sub>N</sub>, 25°C)




Figure 2. Typical Variation of  $C_{IN}$  vs. Temp (f = 1 MHz,  $V_{IN}$  = 30 mV,  $V_P$  = 3.3 V,  $V_N$  = 0 V, 0.1  $\mu F$  Chip Capacitor between  $V_P$  and  $V_N$ )

## PERFORMANCE INFORMATION (Cont'd)

Typical Filter Performance (nominal conditions unless specified otherwise, 50 Ohm Environment)




Figure 3. Insertion Loss (S21) vs. Frequency (0 V DC Bias, V<sub>P</sub>=3.3 V)




Figure 4. Insertion Loss (S21) vs. Frequency (2.5 V DC Bias, V<sub>P</sub>=3.3 V)

### **APPLICATION INFORMATION**

#### **Design Considerations**

In order to realize the maximum protection against ESD pulses, care must be taken in the PCB layout to minimize parasitic series inductances on the Supply/Ground rails as well as the signal trace segment between the signal input (typically a connector) and the ESD protection device. Refer to Application of Positive ESD Pulse between Input Channel and Ground, which illustrates an example of a positive ESD pulse striking an input channel. The parasitic series inductance back to the power supply is represented by  $L_1$  and  $L_2$ . The voltage  $V_{CL}$  on the line being protected is:

### $V_{CL}$ = Fwd Voltage Drop of $D_1 + V_{SUPPLY} + L_1 \times d(I_{ESD}) / dt + L_2 \times d(I_{ESD}) / dt$

where I<sub>ESD</sub> is the ESD current pulse, and V<sub>SUPPLY</sub> is the positive supply voltage.

An ESD current pulse can rise from zero to its peak value in a very short time. As an example, a level 4 contact discharge per the IEC61000–4–2 standard results in a current pulse that rises from zero to 30 Amps in 1 ns. Here  $d(I_{ESD})/dt$  can be approximated by  $\Delta I_{ESD}/\Delta t$ , or  $30/(1x10^{-9})$ . So just 10 nH of series inductance (L<sub>1</sub> and L<sub>2</sub> combined) will lead to a 300 V increment in V<sub>CL</sub>!

Similarly for negative ESD pulses, parasitic series inductance from the  $V_N$  pin to the ground rail will lead to drastically increased negative voltage on the line being protected.

The CM1213A has an integrated Zener diode between  $V_P$  and  $V_N$ . This greatly reduces the effect of supply rail inductance  $L_2$  on  $V_{CL}$  by clamping  $V_P$  at the breakdown voltage of the Zener diode. However, for the lowest possible  $V_{CL}$ , especially when  $V_P$  is biased at a voltage significantly below the Zener breakdown voltage, it is recommended that a 0.22  $\mu F$  ceramic chip capacitor be connected between  $V_P$  and the ground plane.

As a general rule, the ESD Protection Array should be located as close as possible to the point of entry of expected electrostatic discharges. The power supply bypass capacitor mentioned above should be as close to the  $V_P$  pin of the Protection Array as possible, with minimum PCB trace lengths to the power supply, ground planes and between the signal input and the ESD device to minimize stray series inductance.

#### **Additional Information**

See also ON Semiconductor Application Note "Design Considerations for ESD Protection", in the Applications section.




Figure 5. Application of Positive ESD Pulse between Input Channel and Ground







SOT-23 (TO-236) CASE 318-08 **ISSUE AS** 

**DATE 30 JAN 2018** 

# SCALE 4:1 D Ε <-- 3X b


**TOP VIEW** 






STYLE 27: PIN 1. CATHODE 2. CATHODE

3. CATHODE



#### **RECOMMENDED SOLDERING FOOTPRINT**



DIMENSIONS: MILLIMETERS

STYLE 28: PIN 1. ANODE 2. ANODE


3. ANODE

- NOTES:
  1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
  2. CONTROLLING DIMENSION: MILLIMETERS.
  3. MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH.
  MINIMUM LEAD THICKNESS IS THE MINIMUM THICKNESS OF THE BASE MATERIAL
- 4. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH,

PROTE	RUSIONS, OR GATE BURRS.

	MILLIMETERS				INCHES	
DIM	MIN	NOM	MAX	MIN	NOM	MAX
Α	0.89	1.00	1.11	0.035	0.039	0.044
A1	0.01	0.06	0.10	0.000	0.002	0.004
b	0.37	0.44	0.50	0.015	0.017	0.020
С	0.08	0.14	0.20	0.003	0.006	0.008
D	2.80	2.90	3.04	0.110	0.114	0.120
E	1.20	1.30	1.40	0.047	0.051	0.055
е	1.78	1.90	2.04	0.070	0.075	0.080
L	0.30	0.43	0.55	0.012	0.017	0.022
L1	0.35	0.54	0.69	0.014	0.021	0.027
HE	2.10	2.40	2.64	0.083	0.094	0.104
Т	0°		10°	0°		10°

#### **GENERIC MARKING DIAGRAM\***



XXX = Specific Device Code

M = Date Code

= Pb-Free Package

(Note: Microdot may be in either location)

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot " ■", may or may not be present.

STYLE 1 THRU 5: CANCELLED	STYLE 6: PIN 1. BASE 2. EMITTER 3. COLLECTOR	STYLE 7: PIN 1. EMITTER 2. BASE 3. COLLECTOR	STYLE 8: PIN 1. ANODE 2. NO CONNECTION 3. CATHODE	N	
STYLE 9:	STYLE 10:	STYLE 11:	STYLE 12: PIN 1. CATHODE 2. CATHODE 3. ANODE	STYLE 13:	STYLE 14:
PIN 1. ANODE	PIN 1. DRAIN	PIN 1. ANODE		PIN 1. SOURCE	PIN 1. CATHODE
2. ANODE	2. SOURCE	2. CATHODE		2. DRAIN	2. GATE
3. CATHODE	3. GATE	3. CATHODE-ANODE		3. GATE	3. ANODE
STYLE 15:	STYLE 16:	STYLE 17:	STYLE 18:	STYLE 19:	STYLE 20:
PIN 1. GATE	PIN 1. ANODE	PIN 1. NO CONNECTION	PIN 1. NO CONNECTION	N PIN 1. CATHODE	PIN 1. CATHODE
2. CATHODE	2. CATHODE	2. ANODE	2. CATHODE	2. ANODE	2. ANODE
3. ANODE	3. CATHODE	3. CATHODE	3. ANODE	3. CATHODE–ANODE	3. GATE
STYLE 21:	STYLE 22:	STYLE 23:	STYLE 24:	STYLE 25:	STYLE 26:
PIN 1. GATE	PIN 1. RETURN	PIN 1. ANODE	PIN 1. GATE	PIN 1. ANODE	PIN 1. CATHODE
2. SOURCE	2. OUTPUT	2. ANODE	2. DRAIN	2. CATHODE	2. ANODE
3. DRAIN	3. INPUT	3. CATHODE	3. SOURCE	3. GATE	3. NO CONNECTION

DOCUMENT NUMBER:	98ASB42226B	Electronic versions are uncontrolle	
STATUS:	ON SEMICONDUCTOR STANDARD	accessed directly from the Document versions are uncontrolled except	'
NEW STANDARD:		"CONTROLLED COPY" in red.	•
DESCRIPTION:	SOT-23 (TO-236)		PAGE 1 OF 2



<b>DOCUMENT</b>	NUMBER:
98ASB42226	В

#### PAGE 2 OF 2


ISSUE	REVISION	DATE
AJ	ADDED STYLE 27. REQ. BY P. LEM.	07 JUL 2004
AK	OBSOLETED -09 VERSION. REQ. BY D. TRUHITTE.	14 SEP 2004
AL	ADDED NOMINAL VALUES AND UPDATED GENERIC MARKING DIAGRAM. REQ. BY HONG XIAO.	27 MAY 2005
AM	REDREW LEAD SIDE VIEW. REQ BY DARRELL TRUHITTE.	26 AUG 2005
AN	REINTRODUCED LABELS FOR DIMENSION C. REQ. BY D. TRUHITTE.	14 OCT 2005
AP	ADDED THETA DEGREE VALUES TO DIMENSION TABLE. REQ. BY D. TRUHITTE.	17 NOV 2009
AR	MODIFIED DIMENSIONS C AND L. REQ. BY M. YOU.	10 OCT 2016
AS	ADDED STYLE 28. REQ. BY E. ESTILLER.	30 JAN 2018


ON Semiconductor and are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.




SOT-143 CASE 318A-06 **ISSUE U** 

**DATE 07 SEP 2011** 








NOTES:

- 10 DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
  2. CONTROLLING DIMENSION: MILLIMETERS.
  3. MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH. MINIM-UM LEAD THICKNESS IS THE MINIMUM THICKNESS OF BASE MATERIAL.
- DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS. MOLD FLASH, PROTRUSIONS, AND GATE BURRS SHALL NOT EXCEED 0.25 PER SIDE.
  DIMENSION E1 DOES NOT INCLUDE INTERLEAD FLASH OR PROTRUSION. INTERLEAD FLASH AND PROTRUSION SHALL NOT EXCEED 0.25 PER SIDE.
- 5. DIMENSIONS D AND E1 ARE DETERMINED AT DATUM H.
  6. DATUMS A AND B ARE DETERMINED AT DATUM H.

	MILLIMETERS		
DIM	MIN	MAX	
Α	0.80	1.12	
A1	0.01	0.15	
b	0.30	0.51	
b1	0.76	0.94	
C	0.08	0.20	
D	2.80	3.05	
Е	2.10	2.64	
E1	1.20	1.40	
е	1.92 BSC		
e1	0.20 BSC		
L	0.35	0.70	
L2	0.25 BSC		

#### RECOMMENDED **SOLDERING FOOTPRINT**



0.20			3.	
0.96-	<b>← &gt;</b>	-	3X <b>⋖</b> − 0.54	
	DIM	ENSION:	S: MILLIMETERS	

STYLE 2: PIN 1. SOURCE

2. DRAIN

STYLE 1: PIN 1. COLLECTOR

#### **GENERIC MARKING DIAGRAM\***



XXX = Specific Device Code

M = Date Code

STYLE 5: PIN 1. SOURCE

2. DRAIN

= Pb-Free Package

(Note: Microdot may be in either location)

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot " ■", may or may not be present.

> STYLE 6: PIN 1. GND 2. RF IN 3. VREG 4. RF OUT

3. EMITTER 4. BASE	3. GATE 1 4. GATE 2	3. INPUT 4. OUTPUT	3. GROUND 4. INPUT	3. GATE 1 4. SOURCE	
STYLE 7: PIN 1. SOURCE	STYLE 8: PIN 1. SOURCE	STYLE 9: PIN 1. GND	STYLE 10: PIN 1. DRAIN	STYLE 11: PIN 1. SOURCE	
2. GATE	2. GATE	2. IOUT	2. N/C	2. GATE 1	
<ol><li>DRAIN</li></ol>	3. DRAIN	3. VCC	3. SOURCE	3. GATE 2	
4. SOURCE	4. N/C	4. VREF	4. GATE	4. DRAIN	

STYLE 3: PIN 1. GROUND

2. SOURCE

DOCUMENT NUMBER:	98ASB42227B	Electronic versions are uncontrolle		
STATUS:	ON SEMICONDUCTOR STANDARD	accessed directly from the Document versions are uncontrolled except	. ,	
NEW STANDARD:		"CONTROLLED COPY" in red.		
DESCRIPTION:	SOT-143		PAGE 1 OF 2	

STYLE 4: PIN 1. OUTPUT

2. GROUND

ON	Semiconductor®	0
ON	Semiconductor®	0

DOCUMENT NUMBER: 98ASB42227B

PAGE 2 OF 2


ISSUE	REVISION	DATE
U	REDREW TO JEDEC STANDARDS. ADDED SOLDER FOOTPRINT. REQ. BY D. TRUHITTE.	07 SEP 2011


ON Semiconductor and are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.




SC-74 CASE 318F-05 **ISSUE N** 


**DATE 08 JUN 2012** 







## **SOLDERING FOOTPRINT\***



\*For additional information on our Pb–Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

STYLE 3:

STYLE 2:

STYLE 1:

#### NOTES:

- NOTES:

  1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.

  2. CONTROLLING DIMENSION: INCH.

  3. MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH
  THICKNESS, MINIMUM LEAD THICKNESS IS THE MINIMUM THICKNESS OF BASE MATERIAL.
  4. 318F-01, -02, -03, -04 OBSOLETE. NEW STANDARD 318F-05.

	MILLIMETERS				INCHES	
DIM	MIN	NOM	MAX	MIN	NOM	MAX
Α	0.90	1.00	1.10	0.035	0.039	0.043
A1	0.01	0.06	0.10	0.001	0.002	0.004
b	0.25	0.37	0.50	0.010	0.015	0.020
С	0.10	0.18	0.26	0.004	0.007	0.010
D	2.90	3.00	3.10	0.114	0.118	0.122
E	1.30	1.50	1.70	0.051	0.059	0.067
е	0.85	0.95	1.05	0.034	0.037	0.041
L	0.20	0.40	0.60	0.008	0.016	0.024
HE	2.50	2.75	3.00	0.099	0.108	0.118
θ	0°	_	10°	0°	_	10°

#### **GENERIC MARKING DIAGRAM\***



XXX= Specific Device Code

= Date Code Μ = Pb-Free Package

(Note: Microdot may be in either location)

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot " ■", may or may not be present.

STYLE 6:

STYLE 5:

STILL I.	STILL Z.	STILL S.	STILL 4.		JIILL U.
PIN 1. CATHODE	PIN 1. NO CONNECTION	PIN 1. EMITTER 1	PIN 1. COLLECTOR 2	PIN 1. CHANNEL 1	PIN 1. CATHODE
2. ANODE	2. COLLECTOR	2. BASE 1	2. EMITTER 1/EMITTER 2	2. ANODE	<ol><li>ANODE</li></ol>
<ol><li>CATHODE</li></ol>	3. EMITTER	<ol><li>COLLECTOR 2</li></ol>	3. COLLECTOR 1	<ol><li>CHANNEL 2</li></ol>	<ol><li>CATHODE</li></ol>
<ol><li>CATHODE</li></ol>	4. NO CONNECTION	4. EMITTER 2	4. EMITTER 3	<ol><li>CHANNEL 3</li></ol>	<ol><li>CATHODE</li></ol>
5. ANODE	<ol><li>COLLECTOR</li></ol>	5. BASE 2	<ol><li>BASE 1/BASE 2/COLLECTOR 3</li></ol>	<ol><li>CATHODE</li></ol>	<ol><li>CATHODE</li></ol>
<ol><li>CATHODE</li></ol>	6. BASE	<ol><li>COLLECTOR 1</li></ol>	6. BASE 3	<ol><li>CHANNEL 4</li></ol>	<ol><li>CATHODE</li></ol>
STYLE 7: PIN 1. SOURCE 1 2. GATE 1 3. DRAIN 2 4. SOURCE 2 5. GATE 2 6. DRAIN 1	STYLE 8: PIN 1. EMITTER 1 2. BASE 2 3. COLLECTOR 2 4. EMITTER 2 5. BASE 1 6. COLLECTOR 1	STYLE 9: PIN 1. EMITTER 2 2. BASE 2 3. COLLECTOR 1 4. EMITTER 1 5. BASE 1 6. COLLECTOR 2	STYLE 10: PIN 1. ANODE/CATHODE 2. BASE 3. EMITTER 4. COLLECTOR 5. ANODE 6. CATHODE	STYLE 11: PIN 1. EMITTER 2. BASE 3. ANODE/CATHODE 4. ANODE 5. CATHODE 6. COLLECTOR	<b>:</b>

STYLE 4:

DOCUMENT NUMBER:	98ASB42973B	Electronic versions are uncontrolled	' '	
STATUS:	ON SEMICONDUCTOR STANDARD	accessed directly from the Document Rep versions are uncontrolled except whe		
NEW STANDARD:		"CONTROLLED COPY" in red.		
DESCRIPTION:	SC-74	P.	PAGE 1 OF 2	



DOCUMENT	NUMBER:
98ASB42973	В


PAGE 2 OF 2

ISSUE	REVISION	DATE
D	CHANGE OF OWNERSHIP FROM MOTOROLA TO ON SEMICONDUCTOR. DIM A WAS: 2.70–3.10 MM/0.1063–0.1220 IN. DIM C WAS: 1.000–1.30 MM/0.0394–0.0511IN DIM D WAS: 0.25–0.40 MM/0.0098–0.0157 IN. REQ. BY D. TRUHITTE	14 MAR 01
E	CHANGED "USED ON" WAS: SC-59, 6 LEAD. REQ.BY D. TRUHITTE.	27 MAR 01
F	ADDED STYLE 3. REQ. BY S. BACHMAN.	23 APR 01
G	ADDED STYLE 4. REQ. BY S. BACHMAN.	28 AUG 02
Н	ADDED STYLE 5. REQ. BY B. BLACKMON.	21 OCT 02
J	ADDED STYLE 6. REQ. BY B. BLACKMON.	09 JAN 03
K	ADDED STYLES 7 & 8. REQ. BY S. CHANG	03 JUN 03
L	ADDED NOMINAL VALUES AND UPDATED GENERIC MARKING DIAGRAM. REQ. BY HONG XIAO.	27 MAY 05
М	ADDED STYLE 9. REQ. BY W. MEADOWS.	11 APR 2006
N	ADDED STYLES 10 & 11. REQ. BY Y. KALDERON.	08 JUN 2012


ON Semiconductor and unarranged are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

#### SC-88 (SC-70 6 Lead), 1.25x2 CASE 419AD-01 ISSUE A


**DATE 07 JUL 2010** 




**TOP VIEW** 



SIDE VIEW





**END VIEW** 

### Notes:

- (1) All dimensions are in millimeters. Angles in degrees.
- (2) Complies with JEDEC MO-203.

DOCUMENT NUMBER:	98AON34266E	Electronic versions are uncontrolle	
STATUS:	ON SEMICONDUCTOR STANDARD	accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.	
REFERENCE:			
DESCRIPTION:	SC-88 (SC-70 6 LEAD), 1.25X2		PAGE 1 OF 2



DOCUMENT NUMBER: 98AON34266E

PAGE 2 OF 2


ISSUE	REVISION	DATE
0	RELEASED FOR PRODUCTION FROM POD #SC706-023-02 TO ON SEMICONDUCTOR. REQ. BY B. BERGMAN.	19 DEC 2008
Α	ADDED SC-88 TO DESCRIPTION AND TITLE. REQ. BY D. TRUHITTE.	07 JUL 2010


ON Semiconductor and are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights or the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.




MSOP10, 3x3 CASE 846AE **ISSUE A** 

**DATE 20 JUN 2017** 





#### RECOMMENDED **SOLDERING FOOTPRINT\***



DIMENSIONS: MILLIMETERS

#### NOTES:

- DIMENSIONS AND TOLERANCING PER ASME Y14.5M, 1994. CONTROLLING DIMENSIONS: MILLIMETERS. DIMENSION & DOES NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE DAMBAR PROTRUSION SHALL BE 0.10 MM IN
- ALLOWABLE DAMBAR PROTRUSION SHALL BE 0.10 MM IN EXCESS OF MAXIMUM MATERIAL CONDITION.
  DIMENSION D DOES NOT INCLUDE MOLD FLASH,
  PROTRUSIONS, OR GATE BURRS. MOLD FLASH,
  PROTRUSIONS, OR GATE BURRS SHALL NOT EXCEED 0.15
  MM PER SIDE. DIMENSION E DOES NOT INCLUDE INTERLEAD FLASH OR PROTRUSION. INTERLEAD FLASH OR
  PROTRUSION SHALL NOT EXCEED 0.25 MM PER SIDE.
  DIMENSIONS D AND E ARE DETERMINED AT DATUME. DIMENSIONS D AND E ARE DETERMINED AT DATUM F. DATUMS A AND B TO BE DETERMINED AT DATUM F.
- A1 IS DEFINED AS THE VERTICAL DISTANCE FROM THE SEATING PLANE TO THE LOWEST POINT ON THE PACKAGE

	MILLIMETERS		
DIM	MIN	NOM	MAX
Α			1.10
A1	0.00	0.05	0.15
A2	0.75	0.85	0.95
b	0.17		0.27
С	0.13		0.23
D	2.90	3.00	3.10
E	4.75	4.90	5.05
E1	2.90	3.00	3.10
е	0.50 BSC		
L	0.40	0.70	0.80
L1	0.95 REF		
L2	0.25 BSC		
θ	0°		8°

#### **GENERIC MARKING DIAGRAM\***



XXXX = Specific Device Code = Assembly Location Α

Υ = Year W = Work Week = Pb-Free Package

(Note: Microdot may be in either location)

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot " ■", may or may not be present and may be in either location. Some products may not follow the Generic Marking.

DOCUMENT NUMBER:	98AON34098E	Electronic versions are uncontrolle	
STATUS:	N SEMICONDUCTOR STANDARD accessed directly from the Docuversions are uncontrolled exceptions.		' '
REFERENCE:		"CONTROLLED COPY" in red.	
DESCRIPTION:	MSOP10, 3X3		PAGE 1 OF 2

<sup>\*</sup>For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.



<b>DOCUMENT</b>	NUMBER:
98AON34098	E

PAGE 2 OF 2

ISSUE	REVISION	DATE		
0	RELEASED FOR PRODUCTION FROM POD #MSOP10-013-01 TO ON SEMICONDUCTOR. REQ. BY B. BERGMAN.	19 DEC 2008		
А	MODIFIED DRAWING TO ON SEMICONDUCTOR JEDEC STANDARD AND ADDED SOLDERING FOOTPRINT. REQ. BY M. PREJZEK.	20 JUN 2017		

ON Semiconductor and are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <a href="https://www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor dates sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify a

#### **PUBLICATION ORDERING INFORMATION**

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303–675–2175 or 800–344–3860 Toll Free USA/Canada Fax: 303–675–2176 or 800–344–3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada

Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative