

SDIO PORT EXPANDER WITH VOLTAGE-LEVEL TRANSLATION

FEATURES

- 6-to-12 Demultiplexer/Multiplexer Allows SDIO Port Expansion
- Built-in Level Translator Eliminates Voltage Mismatch Between Baseband and SD Card or SDIO Peripheral
- V_{CCA}, V_{CCB0}, and V_{CCB1} Each Operate Over Full 1.1-V to 3.6-V Range
- Latch-Up Performance Exceeds 100 mA Per JESD 78, Class II
- ESD Performance A Port
 - 2000-V Human-Body Model (A114-B)
 - 100-V Machine Model (A115-A)
 - 1500-V Charged-Device Model (C101)
- ±8-kV Contact Discharge IEC 61000-4-2 ESD Performance (B Port)

DESCRIPTION/ORDERING INFORMATION

The TXS02612 is designed to interface the cell phone baseband with external SDIO peripherals. The device includes a 6-channel SPDT switch with voltage-level translation capability. This allows a single SDIO port to be interfaced with two SDIO peripherals. The TXS02612 has three separate supply rails that operate over the full range of 1.1 V to 3.6 V. This allows the baseband and SDIO peripherals to operate at different supply voltages if required.


The select (SEL) input is used to choose between the B0 port and B1 port. When SEL = Low, B0 port is selected; when SEL = High, B1 port is selected. SEL is referenced to V_{CCA} . For the unselected B port, the clock output is held low, whereas the data and command I/Os are pulled high to their respective V_{CCB} through a 70-k Ω resistor (±30% tolerance).


ORDERING INFORMATION(1)

T _A	PACKAGE	(2)	ORDERABLE PART NUMBER	TOP-SIDE MARKING
-40°C to 85°C	MicroStar Junior™ BGA (VFBGA) – ZQS	Reel of 3000	TXS02612ZQSR	YJ612
10 0 10 00 0	QFN – RTW	Reel of 3000	TXS02612RTWR	YJ612

⁽¹⁾ For the most current package and ordering information, see the Package Option Addendum at the end of this document, or see the TI web site at www.ti.com.

(2) Package drawings, thermal data, and symbolization are available at www.ti.com/packaging.





For RTW, if the exposed center pad is used, it must be connected to ground or electrically open.

Table 1. ZQS PACKAGE TERMINAL ASSIGNMENTS


	1	2	3	4	5
Α	DAT2A	SEL	DAT3 _{B0}	CMD _{B0}	CLK _{B0}
В	DAT3A		DAT2 _{B0}	V _{CCB0}	DAT0 _{B0}
С	CMDA	V_{CCA}	GND	V _{CC B1}	DAT1 _{B0}
D	DAT0A	CLKA	GND	DAT1 _{B1}	DAT0 _{B1}
E	DAT1A	DAT2 _{B1}	DAT3 _{B1}	CMD _{B1}	CLK _{B1}



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.



APPLICATION BLOCK DIAGRAM




PIN ASSIGNMENTS


RTW PACKAGE PIN NO.	ZQS PACKAGE BALL NO.	NAME	FUNCTION	TYPE
1	A1	DAT2A	Data bit 2. Referenced to V _{CCA} .	I/O
3	B1	DAT3A	Data bit 3. Referenced to V _{CCA} .	I/O
4	C1	CMDA	Command bit. Referenced to V _{CCA} .	I/O
6	D1	DAT0A	Data bit 0. Referenced to V _{CCA} .	I/O
7	E1	DAT1A	Data bit 1. Referenced to V _{CCA} .	I/O
24	A2	SEL	Select pin to choose between B0 and B1. Referenced to V _{CCA} .	Input
	B2		Depopulated	
5	C2	V_{CCA}	A-port supply voltage. 1.1 $V \le V_{CCA} \le 3.6 V$.	Power
9	D2	CLKA	Clock input A. Referenced to V _{CCA} .	Input
8	E2	DAT2 _{B1}	Data bit 2. Referenced to V _{CCB1} .	I/O
22	A3	DAT3 _{B0}	Data bit 3. Referenced to V _{CCB0} .	I/O
23	В3	DAT2 _{B0}	Data bit 2. Referenced to V _{CCB0} .	I/O
2	C3	GND	Ground	
11	D3	GND	Ground	
10	E3	DAT3 _{B1}	Data bit 3. Referenced to V _{CCB1} .	I/O
20	A4	CMD _{B0}	Command bit. Referenced to V _{CCB0} .	I/O
21	B4	V _{CCB0}	B0-port supply voltage. 1.1 V \leq V _{CCB0} \leq 3.6 V.	Power
17	C4	V _{CCB1}	B1-port supply voltage. 1.1 V \leq V _{CCB1} \leq 3.6 V.	Power
15	D4	DAT1 _{B1}	Data bit 1. Referenced to V _{CCB1} .	I/O
12	E4	CMD _{B1}	Command bit. Referenced to V _{CCB1} .	I/O
19	A5	CLK _{B0}	Clock output. Referenced to V _{CCB0} .	Output
18	B5	DAT0 _{B0}	Data bit 0. Referenced to V _{CCB0} .	I/O
16	C5	DAT1 _{B0}	Data bit 1. Referenced to V _{CCB0} .	I/O
14	D5	DAT0 _{B1}	Data bit 0. Referenced to V _{CCB1} .	I/O
13	E5	CLK _{B1}	Clock output. Referenced to V _{CCB1} .	Output



SIMPLIFIED INTERNAL STRUCTURE



Simplified Architecture of Command and Each Data Path



Simplified Architecture of the Clock Path

- A. R₁ and R₂ resistor values are determined based upon the logic level applied to the A port or B port, as follows:
 - R_1 and R_2 = 40 $k\Omega$ when a logic level low is applied to the A port or B port.
 - R_1 and R_2 = 4 $k\Omega$ when a logic level high is applied to the A port or B port.
 - R_1 and R_2 = 70 k Ω when the port is deselected.

FUNCTION TABLE

	Clock Channel											
SEL	CLKB0	CLKB1	OPERATION									
L	Active	Low	CLKA to CLKB0									
Н	Low	Active	CLKA to CLKB1									
	Da	ata and Command Channel										
SEL	DATxB0 or CMDxB0	DATxB1 or CMDxB1	OPERATION									
L	Active	Disabled, pulled to V_{CCB1} through 70 k Ω	DATxA to DATxB0, CMDA to CMDB0									
Н	Disabled, pulled to V_{CCB0} through 70 k Ω	Active	DATxA to DATxB1, CMDA to CMDB1									

ABSOLUTE MAXIMUM RATINGS(1) (2)

over operating free-air temperature range (unless otherwise noted)

			MIN	MAX	UNIT
V _{CCA} V _{CCB0} V _{CCB1}	Supply voltage range (2)		-0.5	4.6	٧
VI	Input voltage range	A port, B0 port, B1 port, control inputs	-0.5	V _{CCx} + 0.5	V
Vo	Voltage range applied to any output in the high-impedance or power-off state	A port, B0 port, B1 port	-0.5	V _{CCx} + 0.5	V
I_{IK}	Input clamp current	V _I < 0		-50	mA
lok	Output clamp current	V _O < 0		- 50	mA
I _{CC} /	Continuous current through V_{CCA} , V_{CCB0} , V_{CCB1} , or GND			±100	mA
T _{stg}	Storage temperature range	·	-65	150	°C

⁽¹⁾ Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

PACKAGE THERMAL IMPEDANCE

	PARAMETER		UNIT	
0	Dealine at the armed improduces	RTW package	66	90.44
θЈА	Package thermal impedance	ZQS package	171.6	°C/W

⁽²⁾ The input and output voltage ratings may be exceeded if the input and output clamp-current ratings are observed.



RECOMMENDED OPERATING CONDITIONS

			V _{CCA}	V _{CCBx} ⁽¹⁾	MIN	MAX	UNIT
V _{CCA} V _{CCB0} V _{CCB1}	Supply voltage				1.1	3.6	V
		A-port I/Os			V _{CCI} - 0.2	V_{CCI}	
V_{IH}	High-level input voltage	B-port I/Os	1.1 V to 3.6 V	1.1 V to 3.6 V	V _{CCI} - 0.2	V _{CCI}	V
		SEL, CLKA			$V_{CCA} \times 0.65 V$	3.6	
		A-port I/Os			0	0.15	
V_{IL}	Low-level input voltage	B-port I/Os	1.1 V to 3.6 V	1.1 V to 3.6 V	0	0.15	V
		SEL, CLKA			0	$V_{CCA} \times 0.35$	
Δt/Δν	Input transition rise or fall rate	CLK, SEL				10	ns/V
T _A	Operating free-air temperature				-40	85	°C

⁽¹⁾ V_{CCBx} refers to V_{CCB0} and V_{CCB1} .

ELECTRICAL CHARACTERISTICS

over recommended operating free-air temperature range (unless otherwise noted)

DADAMETER	TEST CONDITIONS	V	V	$T_A = 25^{\circ}C$	$T_A = -40^{\circ}C$ to	85°C	UNIT
PARAMETER	TEST CONDITIONS	V _{CCA}	V _{CCBx}	TYP	MIN	MAX	UNII
		1.1 V	1.1 V		0.74		
V_{OHA}		1.4 V	1.4 V		V _{CCA} × 0.67		
(DATA &	$I_{OH} = -20 \mu A,$ $V_{IBx} \ge V_{CCBx} - 0.2 V$	1.65 V	1.65 V		V _{CCA} × 0.67		V
CMD)	VIBX = VCCBX U.2 V	2.3 V	2.3 V		V _{CCA} × 0.67		
		3 V	3 V		V _{CCA} × 0.67		
	$I_{OL} = 135 \mu A, V_{IBx} \le 0.15 V$	1.1 V	1.1 V			0.35	
V_{OLA}	$I_{OL} = 180 \mu A, V_{IBx} \le 0.15 V$	1.4 V	1.4 V			0.35	
(DATA &	I _{OL} = 220 μA, V _{IBx} ≤ 0.15 V	1.65 V	1.65 V			0.45	V
CMD)	I _{OL} = 300 μA, V _{IBx} ≤ 0.15 V	2.3 V	2.3 V			0.55	
	$I_{OL} = 620 \mu A, V_{IBx} \le 0.15 V$	3 V	3 V			0.70	
		1.1 V	1.1 V		0.74		
V_{OHB}		1.4 V	1.4 V		V _{CCBx} × 0.67		
(DATA & $I_{OH} = -20 \mu A$, $V_{IAx} \ge V_{CCAx} - 0.2 V$	$I_{OH} = -20 \mu A,$ $V_{IAX} \ge V_{CCAX} - 0.2 V$	1.65 V	1.65 V		$V_{CCBx} \times 0.67$		V
		2.3 V	2.3 V		$V_{CCBx} \times 0.67$		
		3 V	3 V		$V_{CCBx} \times 0.67$		
	$I_{OH} = -0.5 \text{ mA}$	1.1 V	1.1 V		0.74		
	I _{OH} = - 1 mA	1.4 V	1.4 V		1.05		
V _{OHCLKB}	I _{OH} = -2 mA	1.65 V	1.65 V		1.2		V
	I _{OH} = - 4 mA	2.3 V	2.3 V		1.75		
	$I_{OH} = -8 \text{ mA}$	3 V	3 V		2.3		
	$I_{OL} = 135 \mu A, V_{IAx} \le 0.15 V$	1.1 V	1.1 V			0.35	
V_{OLB}	I _{OL} = 180 μA, V _{IAx} ≤ 0.15 V	1.4 V	1.4 V			0.35	
(DATA &	I _{OL} = 220 μA, V _{IAx} ≤ 0.15 V	1.65 V	1.65 V			0.45	V
CMD)	$I_{OL} = 300 \mu A, V_{IAX} \le 0.15 V$	2.3 V	2.3 V			0.55	
	$I_{OL} = 620 \mu A, V_{IAX} \le 0.15 V$	3 V	3 V			0.70	
	I _{OL} = 0.5 mA	1.1 V	1.1 V			0.35	
	I _{OL} = 1 mA	1.4 V	1.4 V			0.35	
/ _{OLCLKB}	I _{OL} = 2 mA	1.65 V 1.65 V 0.45			0.45		
	I _{OL} = 4 mA	2.3 V	2.3 V			0.55	
	I _{OL} = 8 mA	3 V	3 V			0.7	

ELECTRICAL CHARACTERISTICS (continued)

over recommended operating free-air temperature range (unless otherwise noted)

DADAMETED	TEST COMPITIONS	V	V	T _A = 25°C	$T_A = -40^{\circ}C$ to $85^{\circ}C$	LINUT
PARAMETER	TEST CONDITIONS	V _{CCA}	V _{CCBx}	TYP	MIN MAX	UNIT
	SEL, CLKA	1.1 V to 3.6 V	1.1 V to 3.6 V	±1	±2	^
11	DAT, CMD	1.1 V 10 3.6 V	1.1 V 10 3.6 V	±1	±2	μА
		1.1 V to 3.6 V	1.1 V to 3.6 V		12	
I _{CCA}	$V_I = V_O = Open, I_O = 0,$ SEL, CLK = High or Low	3.6 V	0 V		12	μΑ
	oce, ocive riight of Low	0 V	3.6 V		-1	
		1.1 V to 3.6 V	1.1 V to 3.6 V		24	
I _{CCB0} or I _{CCB1}	$V_I = V_O = Open, I_O = 0,$ SEL, CLK = High or Low	3.6 V	0 V		-12	μΑ
ICCB1	OLL, OLK = High of Low	0 V	3.6 V		24	
C _i	SEL, CLKA	3.3 V	3.3 V	2.5	3.5	pF
C	A port	221	221/	7	7.5	, r
C _{io}	B port	3.3 V	3.3 V	9.5	10	pF

TIMING REQUIREMENTS

 $T_A = 25^{\circ}C, V_{CCA} = 1.2 \text{ V}$

	/ COA			V _{CCB} = 1.2 V	V _{CCB} = 1.5 V	V _{CCB} = 1.8 V	V _{CCB} = 2.5 V	V _{CCB} = 3.3 V	LINIT	
				TYP	TYP	TYP	TYP	TYP	UNIT	
Data rate Clock		Push-pull dri	ving	60	80	120	120	120	N.41	
	Command	Open-drain driving		2	2	2	2	2	Mbps	
	Clock	Push-pull driving		30	40	60	60	60	MHz	
	Data	Push-pull driving		60	80	120	120	120	Mbps	
		Push-pull driving	CLK	17	13	8	8	8		
t _w	Pulse duration	Open-drain driving	CMD	500	500	500	500	500	ns	
		Push-pull	Data	17	13	8	8	8		
		driving	CMD	17	13	8	8	8		



TIMING REQUIREMENTS

over recommended operating free-air temperature range, $V_{CCA} = 1.5 \text{ V} \pm 0.1 \text{ V}$ (unless otherwise noted)

				V _{CCB} = 1.2 V	V _{CCB} = ± 0.7		V _{CCB} = 1.8 V ± 0.15 V		V _{CCB} = 2.5 V ± 0.2 V		V _{CCB} = 3.3 V ± 0.3 V		UNIT
				TYP	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
	Command	Push-pull dri	ving	60		80		120		120		120	Mhna
Data	Command	Open-drain o	Iriving	2		2		2		2		2	Mbps
rate	Clock	Push-pull dri	ving	30		40		60		60		60	MHz
	Data	Push-pull driving		60		80		120		120		120	Mbps
	1	Push-pull driving	CLK	17	13		8		8		8		
T T	Pulse duration	Open-drain driving	CMD	500	500		500		500		500		ns
		Push-pull	Data	17	13		8		8		8		
		driving	CMD	17	13		8		8		8		

TIMING REQUIREMENTS

over recommended operating free-air temperature range, V_{CCA} = 1.8 V ± 0.15 V (unless otherwise noted)

				V _{CCB} = 1.2 V	V _{CCB} = ± 0.7		V _{CCB} = 1.8 V ± 0.15 V		V _{CCB} = 2.5 V ± 0.2 V		V _{CCB} = 3.3 V ± 0.3 V		UNIT
				TYP	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
	0	Push-pull dri	ving	60		80		120		120		120	Maria
Data	Command	Open-drain driving		2		2		2		2		2	Mbps
rate	Clock	Push-pull driving		30		40		60		60		60	MHz
	Data	Push-pull driving		60		80		120		120		120	Mbps
		Push-pull driving	CLK	17	13		8		8		8		
t _w	Pulse duration	Open-drain driving	CMD	500	500		500		500		500		ns
		Push-pull	Data	17	13		8		8		8		
		driving	CMD	17	13		8		8		8		

TIMING REQUIREMENTS

over recommended operating free-air temperature range, $V_{CCA} = 2.5 \text{ V} \pm 0.2 \text{ V}$ (unless otherwise noted)

				V _{CCB} = 1.2 V	V _{CCB} = ± 0.1		V _{CCB} = ± 0.1		V _{CCB} = ± 0.2		V _{CCB} = ± 0.3		UNIT
				TYP	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
	Command	Push-pull dri	ving	60		80		120		120		120	Mbps
Data	Command	Open-drain o	driving	2		2		2		2		2	Minha
rate	Clock	Push-pull dri	ving	30		40		60		60		60	MHz
	Data	Push-pull dri	ving	60		80		120		120		120	Mbps
		Push-pull driving	CLK	17	13		8		8		8		
t _w	Pulse duration	Open-drain driving	CMD	500	500		500		500		500		ns
		Push-pull	Data	17	13		8		8		8		
		driving	CMD	17	13		8		8		8		

TIMING REQUIREMENTS

over recommended operating free-air temperature range, V_{CCA} = 3.3 V ± 0.3 V (unless otherwise noted)

				V _{CCB} = 1.2 V	V _{CCB} = ± 0.7		V _{CCB} = ± 0.1		V _{CCB} = ± 0.2		V _{CCB} = ± 0.3		UNIT
				TYP	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
	C	Push-pull dri	ving	60		80		120		120		120	Mha
Data	Command	Open-drain o	driving	2		2		2		2		2	Mbps
rate	Clock	Push-pull dri	ving	30		40		60		60		60	MHz
	Data	Push-pull dri	ving	60		80		120		120		120	Mbps
		Push-pull driving	CLK	17	13		8		8		8		
t _w	Pulse duration	Open-drain driving	CMD	500	500		500		500		500		ns
		Push-pull	Data	17	13		8		8		8		
		driving	CMD	17	13		8		8		8		



SWITCHING CHARACTERISTICS

 $T_A = 25^{\circ}C, V_{CCA} = 1.2 \text{ V}$

PARAMETER	FROM	то	TEST	V _{CCB} = 1.2 V	V _{CCB} = 1.5 V	V _{CCB} = 1.8 V	V _{CCB} = 2.5 V	V _{CCB} = 3.3 V	UNIT
PARAMETER	(INPUT)	(OUTPUT)	CONDITIONS	TYP	TYP	TYP	TYP	TYP	UNII
	CMDA	CMDB	Push-pull driving	5.9	4.8	4.4	4	4.46	
	CIVIDA	CIVIDB	Open-drain driving	238	214	192	159	140	
	CMDB	CMDA	Push-pull driving	5.6	4.8	4.4	4.1	4	
	CIVIDB	CIVIDA	Open-drain driving	227	201	176	137	114	no
t _{PD}	CLKA	CLKB	Push-pull driving	5.5	4.1	3.6	3.2	3	ns
	DATA	DATB	Push-pull driving	5.8	4.8	4.4	4.2	6.8	
	DATB	DATA	Push-pull driving	5.6	4.8	4.4	4.1	4	
	SEL	B-Port	Push-pull driving	13	11	10	9.4	9.1	
t _{rA}	A-port	rise time	Push-pull driving	4.8	5.1	5.1	5.3	5.7	
t _{rB}	B-port	rise time	Push-pull driving	6.1	3.8	2.9	1.9	1.5	
t _{rB}	CLKA	CLKB	Push-pull driving	5.2	3.4	2.6	1.7	1.3	
t _{fA}	A-port	fall time	Push-pull driving	3.4	2.8	2.6	2.6	2.6	ns
t _{fB}	B-port	fall time	Push-pull driving	4.2	3	2.3	1.7	1.5	
t _{fB}	CLKA	CLKB	Push-pull driving	3.1	2.1	1.6	1.2	1	
	ChA-to-	ChB skew	Push-pull driving	0.4	0.4	0.3	0.4	0.4	
tura	ChB-to-	ChA skew	Push-pull driving	0.3	0.3	0.3	0.3	0.4	ns
t _{sk(O)}		el-to-Clock kew	Push-pull driving	1.68	1.5	1.5	1.5	1.7	113
	Command		Push-pull driving	60	80	120	120	120	
Marrialata wata		Command	Open-drain driving	2	2	2	2	2	Mbps
Max data rate	С	lock	Push-pull driving	30	40	60	60	60	MHz
	Data	ata	Push-pull driving	60	80	120	120	120	Mbps

SWITCHING CHARACTERISTICS

over operating free-air temperature range, $V_{CCA} = 1.5 \text{ V} \pm 0.1 \text{ V}$ (unless otherwise noted)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	TEST CONDITIONS	V _{CCB} = 1.2 V	V _{CCB} = ± 0.1	1.5 V V	V _{CCB} = 1 ± 0.15		V _{CCB} = ± 0.2		V _{CCB} = ± 0.3		UNIT
	(INFUI)	(OUTPUT)	CONDITIONS	TYP	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
	CMDA	CMDB	Push-pull driving	5.1		13		9		8		7.5	
	CIVIDA	CIVIDB	Open-drain driving	210		777		756		684		758	
	CMDB	CMDA	Push-pull driving	4.5		10.6		9.2		8.5		8.2	
	CIVIDB	CIVIDA	Open-drain driving	200		616		560		433		375	ns
t _{PD}	CLKA	CLKB	Push-pull driving	4.7		13.1		9.8		6		5.2	115
	DATA	DATB	Push-pull driving	5.1		13		9		8		7.8	
	DATB	DATA	Push-pull driving	4.5		11		9.3		8.8		8.4	
	SEL	B-Port	Push-pull driving	9.5		26		21		19		18	
t _{rA}	A-port	rise time	Push-pull driving	2.7	1.5	5.8	1.7	5.9	1.7	6	1.8	6.1	
t _{rB}	B-port	rise time	Push-pull driving	3.3	1.7	8.2	1.3	6.6	1	4.3	0.8	2.9	ns
t _{rB}	CLKA	CLKB	Push-pull driving	5.2	1.7	6.4	1.3	4.9	0.9	3.2	0.8	2.5	
t _{fA}	A-port	fall time	Push-pull driving	2.4	1	3.9	0.9	3.4	0.9	3.2	1.3	3.3	
t _{fB}	B-port	fall time	Push-pull driving	3.7	1.1	6.3	0.9	5.2	0.6	3.9	0.6	3.2	ns
t _{fB}	CLKA	CLKB	Push-pull driving	3.1	0.9	4.1	0.8	3.2	0.5	2.2	0.5	1.9	
	ChA-to-	ChB skew	Push-pull driving	0.32		0.47		0.58		0.63		0.63	
t _{sk(O)}	ChB-to-	ChA skew	Push-pull driving	0.27		0.24		0.23		0.22		0.22	ns
*SK(O)		el-to-Clock kew	Push-pull driving	1.47		1.66		1.68		1.82		1.77	
	0		Push-pull driving	60		80		120		120		120	Maria
May data rat-	Con	nmand	Open-drain driving	2		2		2		2		2	Mbps
Max data rate	С	lock	Push-pull driving	30		40		60		60		60	MHz
	D	ata	Push-pull driving	60		80		120		120		120	Mbps



SWITCHING CHARACTERISTICS

over operating free-air temperature range, $V_{CCA} = 1.8 \text{ V} \pm 0.15 \text{ V}$ (unless otherwise noted)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	TEST CONDITIONS	V _{CCB} = 1.2 V	V _{CCB} = ± 0.1	1.5 V V	V _{CCB} = ± 0.15		V _{CCB} = : ± 0.2	2.5 V V	V _{CCB} = ± 0.3		UNIT
	(INPUT)	(001701)	CONDITIONS	TYP	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
	CMDA	CMDB	Push-pull driving	4.8		12		8		6		5.7	
	CIVIDA	CIVIDB	Open-drain driving	183		726		715		686		780	
	CMDB	CMDA	Push-pull driving	4		9		7		6.4		6	
	CIVIDB	CIVIDA	Open-drain driving	175		565		563		441		392	
t _{PD}	CLKA	CLKB	Push-pull driving	4.5		13		9		5.4		4.5	ns
	DATA	DATB	Decelor and definition	4.7		12		8.4		6		5.8	
	DATB	DATA	Push-pull driving	4.1		9		7.5		6.4		6.3	
	SEL	B-Port	Push-pull driving	8.2		22		17		14.8		14	
t _{rA}	A-port	rise time	Push-pull driving	2	1.1	4	1.1	4.3	1.2	4.5	1.3	4.6	
t _{rB}	B-port	rise time	Push-pull driving	6.2	1.7	7.9	1.2	6.2	1	4.3	8.0	3.1	ns
t _{rB}	CLKA	CLKB	Push-pull driving	5.2	1.7	6.4	1.3	4.9	0.9	3.2	8.0	2.5	
t _{fA}	A-port	fall time	Push-pull driving	1.8	0.8	3.2	0.7	2.8	0.7	1.7	0.7	2.6	
t_{fB}	B-port	fall time	Push-pull driving	3.5	1	5.6	0.9	3.5	0.6	1.9	0.6	3	ns
t_{fB}	CLKA	CLKB	Push-pull driving	3.1	0.9	4.1	0.8	3.2	0.5	2.2	0.5	1.9	
	ChA-to-	ChB skew	Push-pull driving	0.33		0.45		0.48		0.53		0.67	
t _{sk(O)}	ChB-to-	ChA skew	Push-pull driving	0.28		0.24		0.23		0.23		0.22	ns
*SK(O)		el-to-Clock kew	Push-pull driving	1.51		1.58		1.46		1.56		1.48	110
	0	d	Push-pull driving	60		80		120		120		120	Misses
NA	Con	nmand	Open-drain driving	2		2		2		2		2	Mbps
Max data rate	С	lock	Push-pull driving	30		40		60		60		60	MHz
		Data	Push-pull driving	60		80		120		120		120	Mbps

SWITCHING CHARACTERISTICS

over operating free-air temperature range, $V_{CCA} = 2.5 \text{ V} \pm 0.2 \text{ V}$ (unless otherwise noted)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	TEST CONDITIONS	V _{CCB} = 1.2 V	V _{CCB} = ± 0.1		V _{CCB} = ± 0.15		V _{CCB} = ± 0.2	2.5 V ! V	V _{CCB} = ± 0.3		UNIT
	(INPUT)	(OUTPUT)	CONDITIONS	TYP	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
	CMDA	CMDB	Push-pull driving	4.4		11		7.4		4.4		3.8	
	CIVIDA	CIVIDB	Open-drain driving	143		544		596		605		669	
	CMDB	CMDA	Push-pull driving	3.8		7.6		5.5		4.2		3.7	
	CIVIDB	CIVIDA	Open-drain driving	137		434		444		414		372	20
t _{PD}	CLKA	CLKB	Push-pull driving	4.1		12		8		4.8		3.8	ns
	DATA	DATB	Duck pull deising	4.4		11		7		4.5		3.8	
	DATB	DATA	Push-pull driving	4.4		8		5.5		4.1		3.7	
	SEL	B-Port	Push-pull driving	7		18		13		10.5		9	
t _{rA}	A-port	rise time	Push-pull driving	1.4	0.75	2.2	0.74	2.2	1.06	2.6	0.7	2.8	
t _{rB}	B-port	rise time	Push-pull driving	6.3	1.91	7.7	1.34	6.1	0.95	4.2	0.83	3.2	ns
t _{rB}	CLKA	CLKB	Push-pull driving	5.2	1.67	6.4	1.27	4.9	0.9	3.2	0.76	2.6	
t _{fA}	A-port	fall time	Push-pull driving	1.1	0.58	1.9	0.58	2	0.61	1.9	0.57	1.9	
t _{fB}	B-port	fall time	Push-pull driving	3.6	1.04	5.4	0.87	4.3	0.66	3.4	0.57	3	ns
t_{fB}	CLKA	CLKB	Push-pull driving	3.1	0.92	4.2	0.79	3.2	0.56	2.2	0.49	1.9	
	ChA-to-	ChB skew	Push-pull driving	0.41		0.43		0.39		0.59		0.68	
t _{sk(O)}	ChB-to-	ChA skew	Push-pull driving	0.41		0.24		0.2		0.19		0.18	ns
*SK(O)		el-to-Clock kew	Push-pull driving	2.11		1.47		1.3		1.25		1.21	110
	0		Push-pull driving	60		80		120		120		120	Misse
Man data as	Con	nmand	Open-drain driving	2		2		2		2		2	Mbps
Max data rate	С	lock	Push-pull driving	30		40		60		60		60	MHz
		ata	Push-pull driving	60		80		120		120		120	Mbps



SWITCHING CHARACTERISTICS

over operating free-air temperature range, V_{CCA} = 3.3 V \pm 0.3 V (unless otherwise noted)

PARAMETER	FROM	TO (OUTPUT)	TEST	V _{CCB} = 1.2 V	V _{CCB} = ± 0.1	1.5 V V	V _{CCB} = ± 0.15		V _{CCB} = ± 0.2		V _{CCB} = ± 0.3		UNIT
	(INPUT)	(OUTPUT)	CONDITIONS	TYP	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
	CMDA	CMDB	Push-pull driving	4.4		11		7		4.1		3.3	
	CIVIDA	CIVIDB	Open-drain driving	116		432		477		506		533	
	CMDB	CMDA	Push-pull driving	4.2		7.5		5.4		3.8		3	
•	CIVIDB	CIVIDA	Open-drain driving	112		349		363		347		324	ns
t _{PD}	CLKA	CLKB	Push-pull driving	4.1		12		7.8		4.4		3.5	115
	DATA	DATB	Push-pull driving	4.3		11		6.8		4		3.8	
	DATB	DATA	r usii-puii uiiviiig	7.9		7.8		5.4		3.4		3	
	SEL	B-Port	Push-pull driving	6.4		16		11.5		8.8		7.6	
t _{rA}	A-port	rise time	Push-pull driving	1.1	0.57	1.7	0.57	1.8	0.56	1.7	0.53	1.8	
t _{rB}	B-port	rise time	Push-pull driving	6.2	1.96	7.7	1.43	6.1	0.95	4.2	0.71	3.1	ns
t _{rB}	CLKA	CLKB	Push-pull driving	5.2	1.67	6.4	1.26	4.9	0.91	3.3	0.76	2.5	
t _{fA}	A-port	fall time	Push-pull driving	1	0.53	1.6	0.52	1.6	0.53	1.6	0.56	1.6	
t _{fB}	B-port	fall time	Push-pull driving	3.4	0.95	5.2	0.8	4.1	0.63	3.2	0.58	2.9	ns
t _{fB}	CLKA	CLKB	Push-pull driving	3.1	0.92	4.1	0.79	3.2	0.56	2.2	0.49	1.9	
	ChA-to-	ChB skew	Push-pull driving	0.39		0.36		0.39		0.57		0.65	
t _{sk(O)}	ChB-to-	ChA skew	Push-pull driving	0.45		0.3		0.19		0.19		0.18	ns
*SK(O)		el-to-Clock kew	Push-pull driving	1.7		1.61		1.34		1.22		1.14	
	0		Push-pull driving	60		80		120		120		120	Misses
May data rata	Con	nmand	Open-drain driving	2		2		2		2		2	Mbps
Max data rate	С	lock	Push-pull driving	30		40		60		60		60	MHz
	Data	Push-pull driving	60		80		120		120		120	Mbps	

OPERATING CHARACTERISTICS

over operating free-air temperature range (unless otherwise noted)

						V_{CCA}			
				1.2 V	1.5 V	1.8 V	2.5 V	3.3 V	
		PARAMETER	TEST CONDITIONS		•	V _{CCB}	•	•	UNIT
				1.2 V	1.5 V	1.8 V	2.5 V	3.3 V	
	A port inp			TYP	TYP	TYP	TYP	TYP	
		A-port input, B-port output		14.5	12.9	12.1	13.4	15	
Data	C _{pdA} R port input A port ou		$C_L = 0, f = 10 \text{ MHz},$	20.7	20.7	21	22	23.2	
and		A-port input, B-port output	$t_r = t_r = 1 \text{ ns},$ OE = outputs enabled	23.2	23.4	23.6	24.5	25.5	pF
CMD	C_{pdB}	B-port input, A-port output	·	14.1	12.2	11.5	12.9	14.4	
		A-port input, B-port output	OE = outputs disabled	0.1	0.1	0.1	0.1	0.1	
	C_{pdA}	A-port input, B-port output	$C_L = 0$, $f = 10 \text{ MHz}$,	0.4	0.4	0.4	0.5	0.7	
Clock	C _{pdB}	B-port input, A-port output	$t_r = t_r = 1 \text{ ns},$ OE = outputs enabled		13.9	13.8	13.8	13.7	pF


POWER-UP CONSIDERATIONS


The following power-up sequence for this TXS02612 SDIO port expander with voltage-level translator should be followed to ensure proper operation and to avoid any unnecessary excessive supply current, bus contention, oscillations, or other anomalies caused by improperly biased device pins. The following power-up sequence should be used to safe-guard against these problems:

- 1. Connect the ground pin of the device first before any power-supply voltage is applied.
- 2. Connect and power up V_{CCA}, which internally powers up the SEL control logic of the TXS02612.
- 3. Depending on the port to be chosen, the SEL pin can be high or low. If SEL high is needed (i.e., A port to B_1 port), ramp the SEL pin with the V_{CCA} power supply. Otherwise, keep SEL Low.
- 4. Apply V_{CCB0} and V_{CCB1} only after the V_{CCA} power supply is applied.



PARAMETER MEASUREMENT INFORMATION







DATA RATE, PULSE DURATION, PROPAGATION DELAY, ENABLE/DISABLE
OUTPUT RISE AND FALL TIME MEASUREMENT USING
A PUSH-PULL DRIVER

DATA RATE, PULSE DURATION, PROPAGATION DELAY,
OUTPUT RISE AND FALL TIME MEASUREMENT USING
AN OPEN-DRAIN DRIVER

VOLTAGE WAVEFORMS

ENABLE AND DISABLE TIMES





NOTES:

- : A. C_L includes probe and jig capacitance.
 - B. Waveform 1 is for an output with internal conditions such that the output is lowexcept when disabled by the output control. Waveform2 is for an output with internal conditions such that the output is high, except when disabled by the output control.
 - C. All input pulses are supplied by generators having the following characteristics: PRR 10 MHz, Z $_{\rm O}=50\Omega$, dv/dt \geq 1 V/ns.
 - D. The outputs are measured one at a time, with one transition per measurement.
 - E. t_{PLZ} and t_{HZ} are the same as t_{is} .
 - F. t_{PZL} and t_{PZH} are the same as t_{PZL} .
 - G. t_{PLH} and t_{HL} are the same as t_d.
 - H. V_{CCI} is the V_{CC} associated with the input port.
 - I. V_{CCO} is the V_{CC} associated with the output port.

VOLTAGE WAVEFORMS

PROPAGATION DELAY TIMES

J. All parameters and waveforms are not applicable to all devices.

Figure 1. Load Circuit and Voltage Waveforms



PACKAGE OPTION ADDENDUM

20-May-2013

PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package	Pins	Package	Eco Plan	Lead/Ball Finish	MSL Peak Temp	Op Temp (°C)	Device Marking	Samples
	(1)		Drawing		Qty	(2)		(3)		(4/5)	
TXS02612RTWR	ACTIVE	WQFN	RTW	24	3000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-2-260C-1 YEAR	-40 to 85	YJ612	Samples
TXS02612ZQSR	ACTIVE	BGA MICROSTAR JUNIOR	ZQS	24	2500	Green (RoHS & no Sb/Br)	SNAGCU	Level-1-260C-UNLIM	-40 to 85	YJ612	Samples

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.

TBD: The Pb-Free/Green conversion plan has not been defined.

Pb-Free (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes. **Pb-Free** (RoHS Exempt): This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

- (3) MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.





20-May-2013

PACKAGE MATERIALS INFORMATION

www.ti.com 2-Nov-2016

TAPE AND REEL INFORMATION





	Dimension designed to accommodate the component width
	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TXS02612RTWR	WQFN	RTW	24	3000	330.0	12.4	4.25	4.25	1.15	8.0	12.0	Q2
TXS02612ZQSR	BGA MI CROSTA R JUNI OR	ZQS	24	2500	330.0	12.4	3.3	3.3	1.6	8.0	12.0	Q1

www.ti.com 2-Nov-2016



*All dimensions are nominal


Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TXS02612RTWR	WQFN	RTW	24	3000	367.0	367.0	35.0
TXS02612ZQSR	BGA MICROSTAR JUNIOR	ZQS	24	2500	336.6	336.6	28.6



- NOTES: A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M-1994.
 - B. This drawing is subject to change without notice.
 - C. Quad Flatpack, No-Leads (QFN) package configuration.
 - D. The package thermal pad must be soldered to the board for thermal and mechanical performance.
 - E. See the additional figure in the Product Data Sheet for details regarding the exposed thermal pad features and dimensions.
 - F. Falls within JEDEC MO-220.



PLASTIC QUAD FLATPACK-NO LEAD




NOTES:

- All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.



PLASTIC QUAD FLATPACK-NO LEAD




NOTES: (continued)

3. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271) .



PLASTIC QUAD FLATPACK-NO LEAD




NOTES: (continued)

4. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



ZQS (S-PBGA-N24)

PLASTIC BALL GRID ARRAY



NOTES: All linear dimensions are in millimeters.

- This drawing is subject to change without notice.
- C. Falls within JEDEC MO-225
- D. This package is lead-free.



IMPORTANT NOTICE

Texas Instruments Incorporated (TI) reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete.

TI's published terms of sale for semiconductor products (http://www.ti.com/sc/docs/stdterms.htm) apply to the sale of packaged integrated circuit products that TI has qualified and released to market. Additional terms may apply to the use or sale of other types of TI products and services.

Reproduction of significant portions of TI information in TI data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such reproduced documentation. Information of third parties may be subject to additional restrictions. Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyers and others who are developing systems that incorporate TI products (collectively, "Designers") understand and agree that Designers remain responsible for using their independent analysis, evaluation and judgment in designing their applications and that Designers have full and exclusive responsibility to assure the safety of Designers' applications and compliance of their applications (and of all TI products used in or for Designers' applications) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to their applications, Designer has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any applications that include TI products, Designer will thoroughly test such applications and the functionality of such TI products as used in such applications.

TI's provision of technical, application or other design advice, quality characterization, reliability data or other services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using TI Resources in any way, Designer (individually or, if Designer is acting on behalf of a company, Designer's company) agrees to use any particular TI Resource solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

Designer is authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNER AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

Unless TI has explicitly designated an individual product as meeting the requirements of a particular industry standard (e.g., ISO/TS 16949 and ISO 26262), TI is not responsible for any failure to meet such industry standard requirements.

Where TI specifically promotes products as facilitating functional safety or as compliant with industry functional safety standards, such products are intended to help enable customers to design and create their own applications that meet applicable functional safety standards and requirements. Using products in an application does not by itself establish any safety features in the application. Designers must ensure compliance with safety-related requirements and standards applicable to their applications. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equipment includes, without limitation, all medical devices identified by the U.S. Food and Drug Administration as Class III devices and equivalent classifications outside the U.S.

TI may expressly designate certain products as completing a particular qualification (e.g., Q100, Military Grade, or Enhanced Product). Designers agree that it has the necessary expertise to select the product with the appropriate qualification designation for their applications and that proper product selection is at Designers' own risk. Designers are solely responsible for compliance with all legal and regulatory requirements in connection with such selection.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's non-compliance with the terms and provisions of this Notice.