











#### SN65HVD10, SN65HVD10Q, SN75HVD10, SN65HVD11 SN65HVD12, SN75HVD12, SN65HVD11Q, SN75HVD11

SLLS505O - FEBRUARY 2002-REVISED FEBRUARY 2017

# SNx5HVD1x 3.3-V RS-485 Transceivers

#### **Features**

- Operates With a 3.3-V Supply
- Bus-Pin ESD Protection Exceeds 16-kV HBM
- 1/8 Unit-Load Option Available (Up to 256 Nodes on the Bus)
- Optional Driver Output Transition Times for Signaling Rates (1) of 1 Mbps, 10 Mbps, and
- Meets or Exceeds the Requirements of ANSI TIA/EIA-485-A
- Bus-Pin Short-Circuit Protection From -7 V to 12 V
- Low-Current Standby Mode: 1 µA, Typical
- Open-Circuit, Idle-Bus, and Shorted-Bus Failsafe Receiver
- Thermal Shutdown Protection
- Glitch-Free Power-Up and Power-Down Protection for Hot-Plugging Applications
- SN75176 Footprint

# **Applications**

- **Digital Motor Control**
- **Utility Meters**
- Chassis-to-Chassis Interconnects
- **Electronic Security Stations**
- **Industrial Process Control**
- **Building Automation**
- Point-of-Sale (POS) Terminals and Networks
- (1) The signaling rate of a line is the number of voltage transitions that are made per second expressed in the units bps (bits per second).

## 3 Description

SN65HVD10. SN75HVD10. SN75HVD11, SN65HVD12, and SN75HVD12 bus transceivers combine a 3-state differential line driver and differential input line receiver that operate with a single 3.3-V power supply. They are designed for balanced transmission lines and meet or exceed ANSI standard TIA/EIA-485-A and ISO 8482:1993. These differential bus transceivers are monolithic integrated circuits designed for bidirectional data communication on multipoint bus-transmission lines. The drivers and receivers have active-high and active-low enables, respectively, that can be externally connected together to function as direction control. Very low device standby supply current can be achieved by disabling the driver and the receiver.


The driver differential outputs and receiver differential inputs connect internally to form a differential input/ output (I/O) bus port that is designed to offer minimum loading to the bus whenever the driver is disabled or  $V_{CC} = 0$ . These parts feature wide positive and negative common-mode voltage ranges making them suitable for party-line applications.

#### Device Information<sup>(1)</sup>

PART NUMBER	PACKAGE	BODY SIZE (NOM)
SN65HVD12	SOIC (8)	4.90 mm × 3.91 mm
SN75HVD12 SN65HVD11		
SN75HVD12	PDIP (8)	9.81 mm × 6.35 mm
SN65HVD10 SN75HVD10		

(1) For all available packages, see the orderable addendum at the end of the data sheet.

#### **Typical Application Diagram**



Copyright © 2016, Texas Instruments Incorporated



## **Table of Contents**

1	Features	1		9.2 Functional Block Diagram	17
2				9.3 Feature Description	17
3				9.4 Device Functional Modes	17
4			10	Application and Implementation	19
5				10.1 Application Information	19
6				10.2 Typical Application	20
7	_		11	Power Supply Recommendations	23
′	7.1 Absolute Maximum Ratings		12	Layout	23
	7.2 ESD Ratings			12.1 Layout Guidelines	23
	7.3 Recommended Operating Conditions			12.2 Layout Example	24
	7.4 Thermal Information			12.3 Thermal Considerations	24
	7.5 Driver Electrical Characteristics		13	Device and Documentation Support	26
	7.6 Receiver Electrical Characteristics			13.1 Device Support	26
	7.7 Power Dissipation Characteristics			13.2 Related Links	26
	7.8 Driver Switching Characteristics			13.3 Receiving Notification of Documentation Upd	ates 26
	7.9 Receiver Switching Characteristics			13.4 Community Resources	26
	7.10 Dissipation Ratings			13.5 Trademarks	26
	7.11 Typical Characteristics			13.6 Electrostatic Discharge Caution	26
8				13.7 Glossary	27
9			14	Mechanical, Packaging, and Orderable	
·	9.1 Overview			Information	27
Cha	nges from Revision N (July 2015) to Revision	n O			Page
• /	Added MIN value of -55°C to the Storage temper	erature in Ab	osolute N	laximum Ratings	4
Cha	nges from Revision M (July 2013) to Revisio	n N			Page
I	Added Pin Configuration and Functions section, Modes, Application and Implementation section, and Documentation Support section, and Mecha	Power Supp	ply Reco	mmendations section, Layout section, Device	1
Cha	nges from Revision L (July 2013) to Revisior	ı M			Page
• (	Changed the V <sub>IT+</sub> TYP value From: –0.65 V To:	–0.065 V			6
Cha	nges from Revision K (September 2011) to R	evision L			Page
• /	Added TYP = -0.65 V to V <sub>IT+</sub>				6
• /	Added TYP = $-0.1 \text{ V to V}_{\text{IT}}$				6
Cha	nges from Revision J (February 2009) to Rev	vision K			Page




# 5 Device Comparison Table

PART N	UMBER	SIGNALING RATE	UNIT LOADS	т	SOIC MARKING
SOIC <sup>(1)</sup>	PDIP	SIGNALING RATE	UNII LUADS	T <sub>A</sub>	SOIC MARKING
SN65HVD10D	SN65HVD10P	32 Mbps	1/2		VP10
SN65HVD11D	SN65HVD11P	10 Mbps	1/8	-40°C to 85°C	VP11
SN65HVD12D	SN65HVD12P	1 Mbps	1/8		VP12
SN75HVD10D	SN75HVD10P	32 Mbps	1/2		VN10
SN75HVD11D	SN75HVD11P	10 Mbps	1/8	−0°C to 70°C	VN11
SN75HVD12D	SN75HVD12P	1 Mbps	1/8		VN12
SN65HVD10QD	SN65HVD10QP	32 Mbps	1/2	40°C to 405°C	VP10Q
SN65HVD11QD	SN65HVD11QP	10 Mbps	1/8	-40°C to 125°C	VP11Q

<sup>(1)</sup> The D package is available as a tape and reel. Add an R suffix to the part number (that is, SN75HVD11DR) for this option.

# 6 Pin Configuration and Functions



## **Pin Functions**

P	IN				
NAME NO.		TYPE	DESCRIPTION		
Α	6	Bus input/output	Driver output or receiver input (complementary to B)		
В	7	Bus input/output	Driver output or receiver input (complementary to A)		
D	4	Digital input	Digital input Driver data input		
DE	3	Digital input	Active-high driver enable		
GND	5	Reference potential	Local device ground		
R	1	Digital output	Receive data output		
RE	2	Digital input	Active-low receiver enable		
V <sub>CC</sub>	8	Supply	3-V to 3.6-V supply		



## 7 Specifications

#### 7.1 Absolute Maximum Ratings

over operating free-air temperature range unless otherwise noted (1) (2)

		MIN	MAX	UNIT
$V_{CC}$	Supply voltage	-0.3	6	V
	Voltage at A or B	-9	14	V
	Input voltage at D, DE, R, or RE	-0.5	$V_{CC} + 0.5$	V
	Voltage input, transient pulse, A and B, through 100 $\Omega$ , see Figure 22	-50	50	V
Io	Receiver output current	-11	11	mA
	Continuous total power dissipation	See Dissi	pation Ratings	
$T_{J}$	Junction temperature		170	°C
T <sub>stg</sub>	Storage temperature	<b>–</b> 55	145	°C

Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

#### 7.2 ESD Ratings

				VALUE	UNIT
		Human body model (HBM), per ANSI/ESDA/JEDEC JS-001 <sup>(1)</sup>	Pins 5, 6, and 7	±16000	
		numan body model (nbivi), per ANSI/ESDA/JEDEC 35-001	All pins	±4000	
V <sub>(ESD)</sub>	Electrostatic discharge	Charged device model (CDM), per JEDEC specification JESD22-C101 (2)	All pins	±1000	V
		Electrical fast transient/burst <sup>(3)</sup>	Pins 5, 6, and 7	±4000	

<sup>(1)</sup> JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

#### 7.3 Recommended Operating Conditions

over operating free-air temperature range unless otherwise noted

			MIN	NOM	MAX	UNIT
V <sub>CC</sub>	Supply voltage		3		3.6	
V <sub>I</sub> or V <sub>IC</sub>	Voltage at any bus terminal (separ	rately or common mode)	-7 <sup>(1)</sup>		12	
V <sub>IH</sub>	High-level input voltage	D, DE, RE	2		V <sub>CC</sub>	V
V <sub>IL</sub>	Low-level input voltage	D, DE, RE	0		0.8	
V <sub>ID</sub>	Differential input voltage	See Figure 18	-12		12	
	High lavel systems arment	Driver	-60			A
I <sub>OH</sub>	High-level output current	Receiver	-8			mA
	Landard and a second	Driver			60	A
I <sub>OL</sub>	Low-level output current	Receiver			8	mA
R <sub>L</sub>	Differential load resistance		54	60		Ω
C <sub>L</sub>	Differential load capacitance			50		pF
		HVD10			32	
	Signaling rate	HVD11			10	Mbps
		HVD12			1	
T <sub>J</sub> <sup>(2)</sup>	Junction temperature				145	°C

<sup>(1)</sup> The algebraic convention, in which the least positive (most negative) limit is designated as minimum is used in this data sheet.

<sup>(2)</sup> All voltage values, except differential I/O bus voltages, are with respect to network ground terminal.

<sup>2)</sup> JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

<sup>(3)</sup> Tested in accordance with IEC 61000-4-4.

<sup>(2)</sup> See thermal characteristics table for information regarding this specification.



#### 7.4 Thermal Information

			SNx5F	IVD1xx	
	THERMA	AL METRIC	D (SOIC)	P (PDIP)	UNIT
		8 Pins	8 Pins		
0	$R_{\theta JA}$ Junction-to-ambient thermal resistance <sup>(1)</sup>	High-K board (2), No airflow	121		90044
$R_{\theta JA}$		No airflow <sup>(3)</sup>		93	°C/W
0	lunction to be and the moral marietanes	High-K board	67		90044
$R_{\theta JB}$	Junction-to-board thermal resistance	See <sup>(3)</sup>		57	°C/W
$R_{\theta JC}$	Junction-to-case thermal resistance		41	55	°C/W

<sup>(1)</sup> The intent of R<sub>0JA</sub> specification is solely for a thermal performance comparison of one package to another in a standardized environment. This methodology is not meant to and will not predict the performance of a package in an application-specific environment.

#### 7.5 Driver Electrical Characteristics

over recommended operating conditions unless otherwise noted

	PARAMETER		TEST CONDITIONS		MIN	TYP <sup>(1)</sup>	MAX	UNIT
V <sub>IK</sub>	Input clamp voltage		I <sub>I</sub> = -18 mA	$I_I = -18 \text{ mA}$				V
			I <sub>O</sub> = 0		2		$V_{CC}$	
V <sub>OD</sub>	Differential output voltage (2)		$R_L = 54 \Omega$ , See Figu	ire 11	1.5			V
			$V_{\text{test}} = -7 \text{ V to } 12 \text{ V},$	See Figure 12	1.5			
$\Delta  V_{OD} $	Change in magnitude of different voltage	tial output	See Figure 11 and F	Figure 12	-0.2		0.2	V
V <sub>OC(PP)</sub>	Peak-to-peak common-mode ou	tput voltage				400		mV
V <sub>OC(SS)</sub>	Steady-state common-mode out	put voltage	See Figure 13	See Figure 42			2.5	V
$\Delta V_{OC(SS)}$	Change in steady-state commor output voltage	n-mode	See Figure 13		-0.05		0.05	V
l <sub>OZ</sub>	High-impedance output current		See receiver input c	urrents				
	lanut ourrant	D			-100		0	^
l <sub>l</sub>	Input current	DE			0		100	μΑ
Ios	Short-circuit output current		$-7 \text{ V} \leq \text{V}_{\text{O}} \leq 12 \text{ V}$		-250		250	mA
C <sub>(OD)</sub>	Differential output capacitance		$V_{OD} = 0.4 \sin(4E6\pi t)$	) + 0.5 V, DE at 0 V		16		рF
			RE at V <sub>CC</sub> , D and DE at V <sub>CC</sub> , No load	Receiver disabled and driver enabled		9	15.5	mA
I <sub>cc</sub>	Supply current		RE at V <sub>CC</sub> , D at V <sub>CC</sub> , DE at 0 V, No load	Receiver disabled and driver disabled (standby)		1	5	μА
			RE at 0 V, D and DE at V <sub>CC</sub> , No load	Receiver enabled and driver enabled		9	15.5	mA

<sup>(1)</sup> All typical values are at 25°C and with a 3.3-V supply.

<sup>(2)</sup> JSD51-7, High Effective Thermal Conductivity Test Board for Leaded Surface Mount Packages.

<sup>(3)</sup> JESD51-10, Test Boards for Through-Hole Perimeter Leaded Package Thermal Measurements.

<sup>(2)</sup> For  $T_A > 85$ °C,  $V_{CC}$  is ±5%.



#### 7.6 Receiver Electrical Characteristics

over recommended operating conditions unless otherwise noted

	PARAMETER	TES	ST CONDIT	TONS	MIN	TYP <sup>(1)</sup>	MAX	UNIT
$V_{IT+}$	Positive-going input threshold voltage	$I_O = -8 \text{ mA}$				-0.065	-0.01	
V <sub>IT</sub>	Negative-going input threshold voltage	I <sub>O</sub> = 8 mA			-0.2	-0.1		V
V <sub>hys</sub>	Hysteresis voltage (V <sub>IT+</sub> – V <sub>IT-</sub> )				35		mV	
$V_{IK}$	Enable-input clamp voltage	$I_I = -18 \text{ mA}$			-1.5			V
$V_{OH}$	High-level output voltage	$V_{ID}$ = 200 mV, $I_{OH}$	= -8 mA, s	ee Figure 18	2.4			V
$V_{OL}$	Low-level output voltage	$V_{ID} = -200 \text{ mV}, I_{OL}$	= 8 mA, se	ee Figure 18			0.4	V
$I_{OZ}$	High-impedance-state output current	$V_O = 0$ or $V_{CC}$ , $\overline{RE}$	at V <sub>CC</sub>		-1		1	μΑ
		$V_A$ or $V_B = 12 V$				0.05	0.11	
		$V_A$ or $V_B = 12 V$ , $V_A$	<sub>CC</sub> = 0 V	HVD11, HVD12,		0.06	0.13	mΛ
		$V_A$ or $V_B = -7 \text{ V}$ Other inputs at 0 V		-0.1	-0.05		mA	
	Due input current	$V_A$ or $V_B = -7$ V, $V_{CC} = 0$ V			-0.05	-0.04		
I <sub>I</sub>	Bus input current	$V_A$ or $V_B = 12 V$				0.2	0.5	
		$V_A$ or $V_B = 12 \text{ V}$ , $V_{CC} = 0 \text{ V}$		HVD10,		0.25	0.5	mA
		$V_A$ or $V_B = -7 \text{ V}$		Other inputs at 0 V	-0.4	-0.2		mA
		$V_A$ or $V_B = -7 \text{ V}, \text{ V}$	<sub>CC</sub> = 0 V		-0.4	-0.15		
I <sub>IH</sub>	High-level input current, RE	V <sub>IH</sub> = 2 V			-30		0	μА
I <sub>IL</sub>	Low-level input current, RE	$V_{IL} = 0.8 \ V$			-30		0	μА
$C_{ID}$	Differential input capacitance	$V_{ID} = 0.4 \sin(4E6\pi t)$	) + 0.5 V, D	E at 0 V		15		pF
		RE at 0 V D and DE at 0 V No load	Receiver disabled	enabled and driver		4	8	mA
I <sub>CC</sub>	Supply current	RE at V <sub>CC</sub> D at V <sub>CC</sub> DE at 0 V No load	Receiver disabled and driver disabled (standby)			1	5	μА
		RE at 0 V D and DE at V <sub>CC</sub> No load	Receiver enabled	enabled and driver		9	15.5	mA

<sup>(1)</sup> All typical values are at 25°C and with a 3.3-V supply.

#### 7.7 Power Dissipation Characteristics

	i owei bissipation on	aracteristics					
	PARAMETER	TEST CONDITIONS		MIN	TYP	MAX	UNIT
		$R_L$ = 60 $\Omega$ , $C_L$ = 50 pF, DE at $V_{CC}$ , $RE$ at 0 V, Input to D is a 50% duty-cycle square wave at indicated signaling	HVD10 (32Mbps)		198	250	
P <sub>D</sub>	Device power dissipation		HVD11 (10Mbps)		141	176	mW
		rate	HVD12 (500 kbps)		133	161	
_	A	High-K board, no airflow	D pkg	-40		116	00
T <sub>A</sub>	Ambient air temperature <sup>(1)</sup>	No airflow <sup>(2)</sup>	P pkg	-40		123	°C
$T_{JSD}$	Thermal shutdown junction tem		165		°C		

<sup>(1)</sup> See Thermal Characteristics of IC Packages section for an explanation of these parameters.

<sup>(2)</sup> JESD51-10, Test Boards for Through-Hole Perimeter Leaded Package Thermal Measurements.



## 7.8 Driver Switching Characteristics

over recommended operating conditions unless otherwise noted

	PARAMETER		TEST CONDITIONS	MIN	TYP <sup>(1)</sup>	MAX	UNIT
		HVD10		5	8.5	16	
t <sub>PLH</sub>	Propagation delay time, low-to-high-level output	HVD11		18	25	40	ns
	low to riight level output	HVD12		135	200	300	
		HVD10		5	8.5	16	
t <sub>PHL</sub>	Propagation delay time, high-to-low-level output	HVD11		18	25	40	ns
	mgm to low lovel output	HVD12		135	200	300	
		HVD10		3	4.5	10	
t <sub>r</sub>	Differential output signal rise time	HVD11	$R_L = 54 \Omega$ , $C_L = 50 pF$ See Figure 14	10	20	30	ns
	noc time	HVD12	Occ rigulo 14	100	170	300	
		HVD10		3	4.5	10	
t <sub>f</sub>	Differential output signal fall time	HVD11		10	20	30	ns
	idii diilo	HVD12		100	170	300	
		HVD10				1.5	
t <sub>sk(p)</sub>	Pulse skew ( t <sub>PHL</sub> - t <sub>PLH</sub>  )	HVD11				2.5	ns
		HVD12				7	
		HVD10			6		
t <sub>sk(pp)</sub> (2)	Part-to-part skew	HVD11				11	ns
t <sub>sk(pp)</sub>		HVD12				100	
	Propagation delay time,	HVD10				31	
t <sub>PZH</sub>	high-impedance-to-high-	HVD11				55	ns
	level output	HVD12	$R_L = 110 \Omega$ , $\overline{RE}$ at 0 V			300	
	Propagation delay time,	HVD10	See Figure 15			25	
t <sub>PHZ</sub>	high-level-to-high-	HVD11				55	ns
	impedance output	HVD12				300	
	Propagation delay time,	HVD10				26	
$t_{PZL}$	high-impedance-to-low-	HVD11				55	ns
	level output	HVD12	$R_L = 110 \Omega$ , $\overline{RE}$ at 0 V			300	
	Propagation delay time,	HVD10	See Figure 16			26	
t <sub>PLZ</sub>	low-level-to-high-	HVD11				75	ns
	impedance output	HVD12				400	
t <sub>PZH</sub>	Propagation delay time, stalevel output	andby-to-high-	$R_L = 110 \Omega$ , $\overline{RE}$ at 3 V See Figure 15			6	μS
t <sub>PZL</sub>	Propagation delay time, stalevel output	andby-to-low-	$R_L = 110 \Omega$ , $\overline{RE}$ at 3 V See Figure 16			6	μS

<sup>(1)</sup> All typical values are at 25°C and with a 3.3-V supply.

<sup>(2)</sup> t<sub>sk(pp)</sub> is the magnitude of the difference in propagation delay times between any specified terminals of two devices when both devices operate with the same supply voltages, at the same temperature, and have identical packages and test circuits.



#### 7.9 Receiver Switching Characteristics

over recommended operating conditions unless otherwise noted

	PARAMETER		TEST CONDITIONS	MIN	TYP <sup>(1)</sup>	MAX	UNIT		
t <sub>PLH</sub>	Propagation delay time, low-to-high-level output	HVD10		12.5	20	25	ns		
t <sub>PHL</sub>	Propagation delay time, high-to-low-level output	HVD10		12.5	20	25	115		
t <sub>PLH</sub>	Propagation delay time, low-to-high-level output	HVD11 HVD12	$V_{ID} = -1.5 \text{ V to } 1.5 \text{ V}$ $C_L = 15 \text{ pF}$	30	55	70	ns		
t <sub>PHL</sub>	Propagation delay time, high-to-low-level output	HVD11 HVD12	See Figure 19	30	55	70	ns		
		HVD10				1.5			
t <sub>sk(p)</sub>	Pulse skew ( t <sub>PHL</sub> - t <sub>PLH</sub>  )	HVD11				4	ns		
		HVD12				4			
		HVD10				8			
t <sub>sk(pp)</sub> (2)	Part-to-part skew	HVD11				15	ns		
		HVD12				15			
t <sub>r</sub>	Output signal rise time		$C_1 = 15  pF$	1	2	5	-		
t <sub>f</sub>	Output signal fall time		See Figure 19	1	2	5	ns		
t <sub>PZH</sub> <sup>(1)</sup>	Output enable time to high	level				15			
t <sub>PZL</sub> <sup>(1)</sup>	Output enable time to low I	evel	$C_1 = 15  pF$ , DE at 3 V			15			
t <sub>PHZ</sub>	Output disable time from h	gh level	See Figure 20			20	ns		
t <sub>PLZ</sub>	Output disable time from lo	w level				15			
t <sub>PZH</sub> (2)	Propagation delay time, stalevel output	andby-to-high-	C <sub>L</sub> = 15 pF, DE at 0						
t <sub>PZL</sub> (2)	Propagation delay time, stallevel output	andby-to-low-	See Figure 21			6	μS		

<sup>(1)</sup> All typical values are at 25°C and with a 3.3-V supply

# 7.10 Dissipation Ratings

PACKAGE	T <sub>A</sub> ≤ 25°C POWER RATING	DERATING FACTOR <sup>(1)</sup> ABOVE T <sub>A</sub> = 25°C	T <sub>A</sub> = 70°C POWER RATING	T <sub>A</sub> = 85°C POWER RATING	T <sub>A</sub> = 125°C POWER RATING
D <sup>(2)</sup>	597 mW	4.97 mW/°C	373 mW	298 mW	100 mW
D <sup>(3)</sup>	990 mW	8.26 mW/°C	620 mW	496 mW	165 mW
Р	1290 mW	10.75 mW/°C	806 mW	645 mW	215 mW

<sup>1)</sup> This is the inverse of the junction-to-ambient thermal resistance when board-mounted and with no air flow.


 <sup>(2)</sup> t<sub>sk(pp)</sub> is the magnitude of the difference in propagation delay times between any specified terminals of two devices when both devices operate with the same supply voltages, at the same temperature, and have identical packages and test circuits.

<sup>(2)</sup> Tested in accordance with the Low-K thermal metric definitions of EIA/JESD51-3.

<sup>(3)</sup> Tested in accordance with the High-K thermal metric definitions of EIA/JESD51-7.




## 7.11 Typical Characteristics



 $V_{CC}$  – Supply Voltage – V Figure 9. Driver Output Current vs Supply Voltage



## **Typical Characteristics (continued)**




V<sub>(TEST)</sub> - Common-Mode Voltage - V

Figure 10. Enable Time vs Common-Mode Voltage



## 8 Parameter Measurement Information



Copyright © 2017, Texas Instruments Incorporated

Figure 11. Driver V<sub>OD</sub> Test Circuit and Voltage and Current Definitions





Figure 12. Driver V<sub>OD</sub> With Common-Mode Loading Test Circuit




Copyright © 2017, Texas Instruments Incorporated

Input: PRR = 500 kHz, 50% Duty Cycle,  $t_{\rm r}$  < 60 ns,  $t_{\rm f}$  < 6 ns  $\rm Z_{O}$  = 50  $\rm \Omega$ 

Figure 13. Test Circuit and Definitions for the Driver Common-Mode Output Voltage






Copyright © 2017, Texas Instruments Incorporated

Generator: PRR = 500 kHz, 50% Duty Cycle,  $t_{r}$  < 60 ns,  $t_{f}$  < 6 ns  $Z_{O}$  = 50  $\Omega$ 


Figure 14. Driver Switching Test Circuit and Voltage Waveforms



Copyright © 2017, Texas Instruments Incorporated

Generator: PRR = 500 kHz, 50% Duty Cycle,  $t_r$  < 60 ns,  $t_f$  < 6 ns  $Z_O$  = 50  $\Omega$ 

Figure 15. Driver High-Level Enable and Disable Time Test Circuit and Voltage Waveforms




Copyright © 2017, Texas Instruments Incorporated

Generator: PRR = 500 kHz, 50% Duty Cycle,  $t_{\rm r}$  < 60 ns,  $t_{\rm f}$  < 6 ns  $Z_{\rm O}$  = 50  $\Omega$ 


Figure 16. Driver Low-Level Output Enable and Disable Time Test Circuit and Voltage Waveforms





The time  $t_{PZL(x)}$  is the measure from DE to  $V_{OD}(x)$ .  $V_{OD}$  is valid when it is greater than 1.5 V.


Figure 17. Driver Enable Time from DE to VoD




Copyright © 2017, Texas Instruments Incorporated

Figure 18. Receiver Voltage and Current Definitions






Generator: PRR = 500 kHz, 50% Duty Cycle,  $t_r$  <6 ns,  $t_f$  <6 ns,  $Z_0$  = 50  $\Omega$ 



Copyright © 2017, Texas Instruments Incorporated

Figure 19. Receiver Switching Test Circuit and Voltage Waveforms



Generator: PRR = 500 kHz, 50% Duty Cycle,  $t_r$  <6 ns,  $t_f$  <6 ns,  $t_o$  = 50  $\Omega$ 





Figure 20. Receiver Enable and Disable Time Test Circuit and Voltage Waveforms With Drivers Enabled





Generator: PRR = 100 kHz, 50% Duty Cycle,  $t_r$  <6 ns,  $t_f$  <6 ns,  $Z_o$  = 50  $\Omega$ 





Figure 21. Receiver Enable Time From Standby (Driver Disabled)




Copyright © 2017, Texas Instruments Incorporated

NOTE: This test is conducted to test survivability only. Data stability at the R output is not specified.

Figure 22. Test Circuit, Transient Over Voltage Test





	R1/R2	R3
SN65HVD10	9 kW	45 kW
SN65HVD11	36 kW	180 kW
SN65HVD12	36 kW	180 kW

Copyright © 2017, Texas Instruments Incorporated

Figure 23. Equivalent Input and Output Schematic Diagrams




## 9 Detailed Description

#### 9.1 Overview

The SN65HVD10, SN65HVD11, and SN65HVD12 are 3.3 V, half-duplex, RS-485 transceivers available in 3 speed grades suitable for data transmission up to 32 Mbps, 10 Mbps, and 1 Mbps, respectively.

These devices have active-high driver enables and active-low receiver enables. A standby current of less than 5 µA can be achieved by disabling both driver and receiver.

#### 9.2 Functional Block Diagram



Copyright © 2016, Texas Instruments Incorporated

#### 9.3 Feature Description

Internal ESD protection circuits protect the transceiver bus terminals against ±16-kV Human Body Model (HBM) electrostatic discharges and ±4-kV electrical fast transients (EFT) according to IEC61000-4-4.

The SN65HVD1x half-duplex family provides internal biasing of the receiver input thresholds for open-circuit, bus-idle, or short-circuit failsafe conditions, and a typical receiver hysteresis of 35 mV.

#### 9.4 Device Functional Modes

When the driver enable pin, DE, is logic high, the differential outputs A and B follow the logic states at data input D. A logic high at D causes A to turn high and B to turn low. In this case the differential output voltage defined as  $V_{OD} = V_A - V_B$  is positive. When D is low, the output states reverse, B turns high, A becomes low, and  $V_{OD}$  is negative.

When DE is low, both outputs turn high-impedance. In this condition the logic state at D is irrelevant. The DE pin has an internal pulldown resistor to ground; thus, when left open, the driver is disabled (high-impedance) by default. The D pin has an internal pullup resistor to  $V_{CC}$ ; thus, when left open while the driver is enabled, output A turns high and B turns low.

Table 1. Driver Functions (1)

INPUT	ENABLE	OUT	PUTS	FUNCTION
D	DE	Α	В	FUNCTION
Н	Н	Н	L	Actively drive bus High
L	Н	L	Н	Actively drive bus Low
X	L	Z	Z	Driver disabled
X	OPEN	Z	Z	Driver disabled by default
OPEN	Н	Н	L	Actively drive bus High by default

(1) H = high level; L = low level; Z = high impedance; X = irrelevant; ? = indeterminate



When the receiver enable pin,  $\overline{RE}$ , is logic low, the receiver is enabled. When the differential input voltage defined as  $V_{ID} = V_A - V_B$  is positive and higher than the positive input threshold,  $V_{IT+}$ , the receiver output, R, turns high. When  $V_{ID}$  is negative and lower than the negative input threshold,  $V_{IT-}$ , the receiver output, R, turns low. If  $V_{ID}$  is between  $V_{IT+}$  and  $V_{IT-}$ , the output is indeterminate.

When  $\overline{RE}$  is logic high or left open, the receiver output is high-impedance and the magnitude and polarity of  $V_{ID}$  are irrelevant. Internal biasing of the receiver inputs causes the output to go failsafe-high when the transceiver is disconnected from the bus (open-circuit), the bus lines are shorted (short-circuit), or the bus is not actively driven (idle bus).

Table 2. Receiver Functions<sup>(1)</sup>

DIFFERENTIAL INPUT $V_{ID} = V_{A} - V_{B}$	ENABLE RE	OUTPUT R	FUNCTION
$V_{ID} > V_{IT+}$	L	Н	Receive valid bus High
$V_{IT-} < V_{ID} < V_{IT+}$	L	?	Indeterminate bus state
$V_{ID} < V_{IT-}$	L	L	Receive valid bus Low
X	Н	Z	Receiver disabled
X	OPEN	Z	Receiver disabled by default
Open-circuit bus	L	Н	Fail-safe high output
Short-circuit bus	L	Н	Fail-safe high output

<sup>(1)</sup> H = high level; L = low level; Z = high impedance; X = irrelevant; ? = indeterminate

#### 9.4.1 Low-Power Standby Mode

When both the driver and receiver are disabled (DE low and  $\overline{RE}$  high) the device is in standby mode. If the enable inputs are in this state for less than 60 ns, the device does not enter standby mode. This guards against inadvertently entering standby mode during driver or receiver enabling. Only when the enable inputs are held in this state for 300 ns or more, the device is assured to be in standby mode. In this low-power standby mode, most internal circuitry is powered down, and the supply current is typically less than 1  $\mu$ A. When either the driver or the receiver is re-enabled, the internal circuitry becomes active.




# 10 Application and Implementation


#### NOTE


Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

#### 10.1 Application Information

The SN65HVD10, 'HVD11, and 'HVD12 are half-duplex RS-485 transceivers commonly used for asynchronous data transmissions. The driver and receiver enable pins allow for the configuration of different operating modes.







- a) Independent driver and receiver enable signals
- b) Combined enable signals for use as directional control pin
- c) Receiver always on

Copyright © 2016, Texas Instruments Incorporated


Figure 24. Half-Duplex Transceiver Configurations

- a. Using independent enable lines provides the most flexible control as it allows for the driver and the receiver to be turned on and off individually. While this configuration requires two control lines, it allows for selective listening into the bus traffic, whether the driver is transmitting data or not.
- b. Combining the enable signals simplifies the interface to the controller by forming a single direction-control signal. In this configuration, the transceiver operates as a driver when the direction-control line is high, and as a receiver when the direction-control line is low.
- c. Only one line is required when connecting the receiver-enable input to ground and controlling only the driverenable input. In this configuration, a node not only receives the data from the bus, but also the data it sends and can verify that the correct data have been transmitted.



#### 10.2 Typical Application

An RS-485 bus consists of multiple transceivers connected in parallel to a bus cable. To eliminate line reflections, each cable end is terminated with a termination resistor,  $R_T$ , whose value matches the characteristic impedance,  $Z_0$ , of the cable. This method, known as parallel termination, allows for higher data rates over a longer cable length.



Copyright © 2016, Texas Instruments Incorporated

Figure 25. Typical RS-485 Network With Half-Duplex Transceivers

#### 10.2.1 Design Requirements

RS-485 is a robust electrical standard suitable for long-distance networking that may be used in a wide range of applications with varying requirements, such as distance, data rate, and number of nodes.

#### 10.2.1.1 Data Rate and Bus Length

There is an inverse relationship between data rate and bus length, meaning the higher the data rate, the shorter the cable length; and conversely, the lower the data rate, the longer the cable may be without introducing data errors. While most RS-485 systems use data rates between 10 kbps and 100 kbps, some applications require data rates up to 250 kbps at distances of 4000 feet and longer. Longer distances are possible by allowing for small signal jitter of up to 5 or 10%.




Figure 26. Cable Length vs Data Rate Characteristic

0.75

7.67



#### Typical Application (continued)

#### 10.2.1.2 Stub Length

When connecting a node to the bus, the distance between the transceiver inputs and the cable trunk, known as the stub, should be as short as possible. Stubs present a nonterminated piece of bus line which can introduce reflections as the length of the stub increases. As a general guideline, the electrical length, or round-trip delay, of a stub should be less than one-tenth of the rise time of the driver, thus giving a maximum physical stub length as shown in Equation 1.

 $L_{(STUB)} \le 0.1 \times t_r \times v \times c$ 

#### where

- t<sub>r</sub> is the 10/90 rise time of the driver
- v is the signal velocity of the cable or trace as a factor of c
- c is the speed of light (3 x 10<sup>8</sup> m/s)

**DEVICE** 

SN65HVD11

SN65HVD12

(1)

Per Equation 1, Table 3 lists the maximum cable-stub lengths for the minimum-driver output rise-times of the SN65HVD1x full-duplex family of transceivers for a signal velocity of 78%.

**MAXIMUM STUB LENGTH** MINIMUM DRIVER OUTPUT RISE TIME (ns) (m) (ft) 3 SN65HVD10 0.07 0.23

0.23

2.34

Table 3. Maximum Stub Length

10

100

#### 10.2.1.3 Bus Loading

The RS-485 standard specifies that a compliant driver must be able to driver 32 unit loads (UL), where 1 unit load represents a load impedance of approximately 12 kΩ. Because the SN65HVD11 and HVD12 are each 1/8 UL transceivers, it is possible to connect up to 256 receivers to the bus. The SN65HVD10 is a 1/4 UL transceiver, and up to 64 receivers may be connected to the bus.

#### 10.2.1.4 Receiver Failsafe

The differential receivers of the SN65HVD1x family are failsafe to invalid bus states caused by:

- Open bus conditions, such as a disconnected connector
- Shorted bus conditions, such as cable damage shorting the twisted-pair together
- Idle bus conditions that occur when no driver on the bus is actively driving.

In any of these cases, the differential receiver will output a failsafe logic High state so that the output of the receiver is not indeterminate.


Receiver failsafe is accomplished by offsetting the receiver thresholds such that the input indeterminate range does not include zero volts differential. To comply with the RS-422 and RS-485 standards, the receiver output must output a High when the differential input V<sub>ID</sub> is more positive than +200 mV, and must output a Low when V<sub>ID</sub> is more negative than -200 mV. The receiver parameters which determine the failsafe performance are V<sub>IT(+)</sub> and V<sub>IT(-)</sub>. As shown in Receiver Electrical Characteristics, differential signals more negative than -200 mV will always cause a Low receiver output, and differential signals more positive than +200 mV will always cause a High receiver output.

When the differential input signal is close to zero, it is still above the maximum  $V_{IT(+)}$  threshold of -10 mV, and the receiver output will be High.



#### 10.2.2 Detailed Design Procedure

To protect bus nodes against high-energy transients, the implementation of external transient protection devices is therefore necessary. Figure 27 shows a protection circuit against 10-kV ESD (IEC 61000-4-2), 4-kV EFT (IEC 61000-4-4), and 1-kV surge (IEC 61000-4-5) transients.



copyright of 2011, robust most among most portated

Figure 27. Transient Protection Against ESD, EFT, and Surge Transients

**DEVICE MANUFACTURER FUNCTION ORDER NUMBER XCVR** SN65HVD1xD 3.3-V, full-duplex RS-485 ΤI transceiver R1, R2 10-Ω, pulse-proof, thick-film CRCW0603010RJNEAHP Vishay resistor TVS Bidirectional 400-W CDSOT23-SM712 **Bourns** transient suppressor

Table 4. Bill of Materials

#### 10.2.3 Application Curve

Figure 28 demonstrates operation of the SN65HVD12 at a signaling rate of 250 kbps. Two SN65HVD12 transceivers are used to transmit data through a 2,000 foot (600 m) segment of Commscope 5524 category 5e+ twisted pair cable. The bus is terminated at each end by a  $100-\Omega$  resistor, matching the cable characteristic impedance.




Figure 28. SN65HVD12 Input and Output Through 2000 Feet of Cable



## 11 Power Supply Recommendations

To assure reliable operation at all data rates and supply voltages, each supply must be buffered with a 100-nF ceramic capacitor located as close to the supply pins as possible. The TPS76333 linear voltage regulator is suitable for the 3.3-V supply.

## 12 Layout

#### 12.1 Layout Guidelines

On-chip IEC-ESD protection is sufficient for laboratory and portable equipment but never sufficient for EFT and surge transients occurring in industrial environments. Therefore, robust and reliable bus node design requires the use of external transient protection devices.

Because ESD and EFT transients have a wide frequency bandwidth from approximately 3 MHz to 3 GHz, high-frequency layout techniques must be applied during PCB design.

- 1. Place the protection circuitry close to the bus connector to prevent noise transients from entering the board.
- 2. Use V<sub>CC</sub> and ground planes to provide low-inductance. Note that high-frequency currents follow the path of least inductance and not the path of least impedance.
- 3. Design the protection components into the direction of the signal path. Do not force the transient currents to divert from the signal path to reach the protection device.
- Apply 100-nF to 220-nF bypass capacitors as close as possible to the V<sub>CC</sub> pins of transceiver, UART, and controller ICs on the board.
- 5. Use at least two vias for V<sub>CC</sub> and ground connections of bypass capacitors and protection devices to minimize effective via-inductance.
- 6. Use  $1-k\Omega$  to  $10-k\Omega$  pull-up or pull-down resistors for enable lines to limit noise currents in these lines during transient events.
- 7. Insert pulse-proof series resistors into the A and B bus lines if the TVS clamping voltage is higher than the specified maximum voltage of the transceiver bus terminals. These resistors limit the residual clamping current into the transceiver and prevent it from latching up.
- 8. While pure TVS protection is sufficient for surge transients up to 1 kV, higher transients require metal-oxide varistors (MOVs) which reduce the transients to a few hundred volts of clamping voltage, and transient blocking units (TBUs) that limit transient current to less than 1 mA.



#### 12.2 Layout Example




Figure 29. SN65HVD1x Layout Example

#### 12.3 Thermal Considerations

#### 12.3.1 Thermal Characteristics of IC Packages

 $R_{\theta JA}$  (Junction-to-Ambient Thermal Resistance) is defined as the difference in junction temperature to ambient temperature divided by the operating power.

R<sub>BJA</sub> is not a constant and is a strong function of:

- the PCB design (50% variation)
- altitude (20% variation)
- device power (5% variation)

 $R_{\theta JA}$  can be used to compare the thermal performance of packages if the specific test conditions are defined and used. Standardized testing includes specification of PCB construction, test chamber volume, sensor locations, and the thermal characteristics of holding fixtures.  $R_{\theta JA}$  is often misused when it is used to calculate junction temperatures for other installations.

TI uses two test PCBs as defined by JEDEC specifications. The low-k board gives average in-use condition thermal performance, and it consists of a single copper trace layer 25 mm long and 2-oz thick. The high-k board gives best case in-use condition, and it consists of two 1-oz buried power planes with a single copper trace layer 25 mm long and 2-oz thick. A 4% to 50% difference in  $R_{0,IA}$  can be measured between these two test cards.

 $R_{\theta JC}$  (Junction-to-Case Thermal Resistance) is defined as difference in junction temperature to case divided by the operating power. It is measured by putting the mounted package up against a copper block cold plate to force heat to flow from die, through the mold compound into the copper block.

 $R_{\theta JC}$  is a useful thermal characteristic when a heatsink is applied to package. It is not a useful characteristic to predict junction temperature because it provides pessimistic numbers if the case temperature is measured in a nonstandard system and junction temperatures are backed out. It can be used with  $R_{\theta JB}$  in 1-dimensional thermal simulation of a package system.

 $R_{\theta JB}$  (Junction-to-Board Thermal Resistance) is defined as the difference in the junction temperature and the PCB temperature at the center of the package (closest to the die) when the PCB is clamped in a cold-plate structure.  $R_{\theta JB}$  is only defined for the high-k test card.

 $R_{\theta JB}$  provides an overall thermal resistance between the die and the PCB. It includes a bit of the PCB thermal resistance (especially for BGAs with thermal balls) and can be used for simple 1-dimensional network analysis of package system, see Figure 30.



# **Thermal Considerations (continued)**




Figure 30. PCB Thermal Resistances



## 13 Device and Documentation Support

#### 13.1 Device Support

#### 13.1.1 Third-Party Products Disclaimer

TI'S PUBLICATION OF INFORMATION REGARDING THIRD-PARTY PRODUCTS OR SERVICES DOES NOT CONSTITUTE AN ENDORSEMENT REGARDING THE SUITABILITY OF SUCH PRODUCTS OR SERVICES OR A WARRANTY, REPRESENTATION OR ENDORSEMENT OF SUCH PRODUCTS OR SERVICES, EITHER ALONE OR IN COMBINATION WITH ANY TI PRODUCT OR SERVICE.

#### 13.2 Related Links

The table below lists quick access links. Categories include technical documents, support and community resources, tools and software, and quick access to sample or buy.

**TECHNICAL SUPPORT & TOOLS & PARTS** PRODUCT FOLDER **ORDER NOW SOFTWARE DOCUMENTS** COMMUNITY SN65HVD12 Click here Click here Click here Click here Click here SN75HVD12 Click here Click here Click here Click here Click here SN65HVD11 Click here Click here Click here Click here Click here SN65HVD11Q Click here SN75HVD11 Click here Click here Click here SN65HVD10 Click here Click here Click here Click here Click here SN65HVD10Q Click here Click here Click here Click here Click here SN75HVD10 Click here Click here Click here Click here Click here

Table 5. Related Links

# 13.3 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. In the upper right corner, click on *Alert me* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

#### 13.4 Community Resources

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

TI E2E™ Online Community TI's Engineer-to-Engineer (E2E) Community. Created to foster collaboration among engineers. At e2e.ti.com, you can ask questions, share knowledge, explore ideas and help solve problems with fellow engineers.

**Design Support** *TI's Design Support* Quickly find helpful E2E forums along with design support tools and contact information for technical support.

#### 13.5 Trademarks

E2E is a trademark of Texas Instruments.

All other trademarks are the property of their respective owners.

#### 13.6 Electrostatic Discharge Caution



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.



www.ti.com

#### 13.7 Glossary

SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.

# 14 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.





15-Apr-2017

## **PACKAGING INFORMATION**

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead/Ball Finish (6)	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Sample
SN65HVD10D	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 85	VP10	Sample
SN65HVD10DG4	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 85	VP10	Sample
SN65HVD10DR	ACTIVE	SOIC	D	8	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 85	VP10	Sample
SN65HVD10DRG4	ACTIVE	SOIC	D	8	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 85	VP10	Sample
SN65HVD10P	ACTIVE	PDIP	Р	8	50	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type	-40 to 85	65HVD10	Sample
SN65HVD10QD	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 125	VP10Q	Sample
SN65HVD10QDG4	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 125	VP10Q	Sample
SN65HVD10QDR	ACTIVE	SOIC	D	8	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 125	VP10Q	Sample
SN65HVD10QDRG4	ACTIVE	SOIC	D	8	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 125	VP10Q	Sample
SN65HVD11D	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 85	VP11	Sample
SN65HVD11DG4	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 85	VP11	Sample
SN65HVD11DR	ACTIVE	SOIC	D	8	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 85	VP11	Sample
SN65HVD11DRG4	ACTIVE	SOIC	D	8	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 85	VP11	Sample
SN65HVD11P	ACTIVE	PDIP	Р	8	50	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type	-40 to 85	65HVD11	Sample
SN65HVD11PE4	ACTIVE	PDIP	Р	8	50	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type	-40 to 85	65HVD11	Sampl
SN65HVD11QD	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 125	VP11Q	Sample
SN65HVD11QDG4	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 125	VP11Q	Sample



www.ti.com

15-Apr-2017

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead/Ball Finish (6)	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
SN65HVD11QDR	ACTIVE	SOIC	D	8	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 125	VP11Q	Samples
SN65HVD12D	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 85	VP12	Samples
SN65HVD12DG4	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 85	VP12	Samples
SN65HVD12DR	ACTIVE	SOIC	D	8	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 85	VP12	Samples
SN65HVD12DRG4	ACTIVE	SOIC	D	8	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 85	VP12	Samples
SN65HVD12P	ACTIVE	PDIP	Р	8	50	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type	-40 to 85	65HVD12	Samples
SN65HVD12PE4	ACTIVE	PDIP	Р	8	50	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type	-40 to 85	65HVD12	Samples
SN75HVD10D	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	VN10	Samples
SN75HVD10DG4	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	VN10	Samples
SN75HVD10DR	ACTIVE	SOIC	D	8	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	VN10	Samples
SN75HVD10DRG4	ACTIVE	SOIC	D	8	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	VN10	Samples
SN75HVD10P	ACTIVE	PDIP	Р	8	50	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type	0 to 70	75HVD10	Samples
SN75HVD11D	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	VN11	Samples
SN75HVD11DG4	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	VN11	Samples
SN75HVD11DR	ACTIVE	SOIC	D	8	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	VN11	Samples
SN75HVD11DRG4	ACTIVE	SOIC	D	8	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	VN11	Samples
SN75HVD12D	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	VN12	Samples
SN75HVD12DG4	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	VN12	Samples



## PACKAGE OPTION ADDENDUM

15-Apr-2017

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead/Ball Finish	MSL Peak Temp	Op Temp (°C)	Device Marking	Samples
	(1)		Diawing		Qty	(2)	(6)	(3)		(4/5)	
SN75HVD12DR	ACTIVE	SOIC	D	8	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	VN12	Samples
SN75HVD12DRG4	ACTIVE	SOIC	D	8	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	VN12	Samples
SN75HVD12P	ACTIVE	PDIP	Р	8	50	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type	0 to 70	75HVD12	Samples
SN75HVD12PE4	ACTIVE	PDIP	Р	8	50	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type	0 to 70	75HVD12	Samples

(1) The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.

**TBD:** The Pb-Free/Green conversion plan has not been defined.

**Pb-Free** (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

**Pb-Free (RoHS Exempt):** This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead/Ball Finish Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and



# **PACKAGE OPTION ADDENDUM**

15-Apr-2017

continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

#### OTHER QUALIFIED VERSIONS OF SN65HVD10, SN65HVD11, SN65HVD12:

• Enhanced Product: SN65HVD10-EP, SN65HVD12-EP

NOTE: Qualified Version Definitions:

• Enhanced Product - Supports Defense, Aerospace and Medical Applications

# PACKAGE MATERIALS INFORMATION

www.ti.com 18-Jan-2017

## TAPE AND REEL INFORMATION





	Dimension designed to accommodate the component width
	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



#### \*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
SN65HVD10DR	SOIC	D	8	2500	330.0	12.4	6.4	5.2	2.1	8.0	12.0	Q1
SN65HVD10QDR	SOIC	D	8	2500	330.0	12.4	6.4	5.2	2.1	8.0	12.0	Q1
SN65HVD11DR	SOIC	D	8	2500	330.0	12.4	6.4	5.2	2.1	8.0	12.0	Q1
SN65HVD11QDR	SOIC	D	8	2500	330.0	12.4	6.4	5.2	2.1	8.0	12.0	Q1
SN65HVD12DR	SOIC	D	8	2500	330.0	12.4	6.4	5.2	2.1	8.0	12.0	Q1
SN75HVD10DR	SOIC	D	8	2500	330.0	12.4	6.4	5.2	2.1	8.0	12.0	Q1
SN75HVD11DR	SOIC	D	8	2500	330.0	12.4	6.4	5.2	2.1	8.0	12.0	Q1
SN75HVD12DR	SOIC	D	8	2500	330.0	12.4	6.4	5.2	2.1	8.0	12.0	Q1

www.ti.com 18-Jan-2017



\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
SN65HVD10DR	SOIC	D	8	2500	340.5	338.1	20.6
SN65HVD10QDR	SOIC	D	8	2500	340.5	338.1	20.6
SN65HVD11DR	SOIC	D	8	2500	340.5	338.1	20.6
SN65HVD11QDR	SOIC	D	8	2500	340.5	338.1	20.6
SN65HVD12DR	SOIC	D	8	2500	340.5	338.1	20.6
SN75HVD10DR	SOIC	D	8	2500	340.5	338.1	20.6
SN75HVD11DR	SOIC	D	8	2500	340.5	338.1	20.6
SN75HVD12DR	SOIC	D	8	2500	340.5	338.1	20.6

# D (R-PDSO-G8)

## PLASTIC SMALL OUTLINE



NOTES:

- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.006 (0,15) each side.
- Body width does not include interlead flash. Interlead flash shall not exceed 0.017 (0,43) each side.
- E. Reference JEDEC MS-012 variation AA.



# P (R-PDIP-T8)

# PLASTIC DUAL-IN-LINE PACKAGE



NOTES:

- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- C. Falls within JEDEC MS-001 variation BA.



#### **IMPORTANT NOTICE**

Texas Instruments Incorporated (TI) reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete.

TI's published terms of sale for semiconductor products (http://www.ti.com/sc/docs/stdterms.htm) apply to the sale of packaged integrated circuit products that TI has qualified and released to market. Additional terms may apply to the use or sale of other types of TI products and services.

Reproduction of significant portions of TI information in TI data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such reproduced documentation. Information of third parties may be subject to additional restrictions. Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyers and others who are developing systems that incorporate TI products (collectively, "Designers") understand and agree that Designers remain responsible for using their independent analysis, evaluation and judgment in designing their applications and that Designers have full and exclusive responsibility to assure the safety of Designers' applications and compliance of their applications (and of all TI products used in or for Designers' applications) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to their applications, Designer has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any applications that include TI products, Designer will thoroughly test such applications and the functionality of such TI products as used in such applications.

TI's provision of technical, application or other design advice, quality characterization, reliability data or other services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using TI Resources in any way, Designer (individually or, if Designer is acting on behalf of a company, Designer's company) agrees to use any particular TI Resource solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

Designer is authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNER AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

Unless TI has explicitly designated an individual product as meeting the requirements of a particular industry standard (e.g., ISO/TS 16949 and ISO 26262), TI is not responsible for any failure to meet such industry standard requirements.

Where TI specifically promotes products as facilitating functional safety or as compliant with industry functional safety standards, such products are intended to help enable customers to design and create their own applications that meet applicable functional safety standards and requirements. Using products in an application does not by itself establish any safety features in the application. Designers must ensure compliance with safety-related requirements and standards applicable to their applications. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equipment includes, without limitation, all medical devices identified by the U.S. Food and Drug Administration as Class III devices and equivalent classifications outside the U.S.

TI may expressly designate certain products as completing a particular qualification (e.g., Q100, Military Grade, or Enhanced Product). Designers agree that it has the necessary expertise to select the product with the appropriate qualification designation for their applications and that proper product selection is at Designers' own risk. Designers are solely responsible for compliance with all legal and regulatory requirements in connection with such selection.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's non-compliance with the terms and provisions of this Notice.