





Tools &

THVD1510, THVD1512 THVD1550, THVD1551, THVD1552

SLLSEV1A - SEPTEMBER 2017 - REVISED JANUARY 2018

# THVD15xx 5-V RS-485 Transceivers With ±18-kV IEC ESD Protection

#### Features 1

Texas

Instruments

- Meets or Exceeds the Requirements of the TIA/EIA-485A Standard
- 4.5 V to 5.5 V Supply Voltage
- Integrated Bus I/O Protection
  - ± 30 kV HBM ESD
  - ± 18 kV IEC 61000-4-2 ESD Contact Discharge
  - ± 25 kV IEC 61000-4-2 ESD Air-Gap Discharge
  - ± 4 kV IEC 61000-4-4 Electrical Fast Transient
- Extended Operational Common-mode: ± 15 V
- Low EMI 500 kbps and 50 Mbps Data Rates
- Extended Temperature Range: -40°C to 125°C
- Large Receiver Hysteresis for Noise Rejection
- Low Power Consumption
  - Low Standby Supply Current: < 1 µA</li>
  - Current During Operation: < 1 mA</li>
- Glitch-Free Power-Up/Down for Hot Plug-in • Capability
- Open, Short, and Idle Bus Failsafe
- 1/8 Unit Load Options (Up to 256 Bus Nodes)
- Small-Size VSSOP Packages Save Board Space or SOIC for Drop-in Compatibility

#### Applications 2

- Motor Drives
- Factory Automation and Control
- Grid Infrastructure
- **Building Automation**
- **HVAC Systems**
- Video Surveillance
- **Process Analytics**
- **Telecom Infrastructure**

#### Description 3

THVD15xx is a family of noise-immune RS-485/RS-422 transceivers designed to operate in rugged industrial environments. The bus pins of these devices are robust to high levels of IEC electrical fast transients (EFT) and IEC electrostatic discharge (ESD) events, eliminating the need for additional system-level protection components.

Each of these devices operates from a single 5-V supply. The devices in this family feature an extended common-mode voltage range which makes them suitable for multi-point applications over long cable runs.


THVD15xx family of devices is available in small VSSOP packages for space-constrained applications. These devices are characterized over ambient freeair temperatures from -40°C to 125°C.

Device	Informati	on <sup>(1)</sup>
--------	-----------	-------------------

PART NUMBER	PACKAGE	BODY SIZE (NOM)	
THVD1510	VSSOP (8)	3.00 mm × 3.00 mm	
THVD1550	SOIC (8)	4.90 mm × 3.91 mm	
THVD1551	VSSOP (8)	3.00 mm × 3.00 mm	
THVD1512	VSSOP (10)	3.00 mm × 3.00 mm	
THVD1552	VSSOP (10)	3.00 mm × 3.00 mm	
1001552	SOIC (14)	8.65 mm × 3.91 mm	


(1) For all available packages, see the orderable addendum at the end of the data sheet.

### **THVD1510 and THVD1550 Simplified Schematic**




Copyright © 2017, Texas Instruments Incorporated

#### **THVD1551 Simplified Schematic**



Copyright © 2017, Texas Instruments Incorporated

### THVD1512 and THVD1552 Simplified Schematic



Copyright © 2017, Texas Instruments Incorporated



# **Table of Contents**

1		tures 1
2	Арр	lications 1
3		cription 1
4	Rev	ision History 2
5	Dev	ice Comparison Table 3
6	Pin	Configuration and Functions 3
7	Spe	cifications6
	7.1	Absolute Maximum Ratings 6
	7.2	ESD Ratings6
	7.3	Recommended Operating Conditions
	7.4	Thermal Information7
	7.5	Power Dissipation7
	7.6	Electrical Characteristics
	7.7	Switching Characteristics
	7.8	Switching Characteristics
	7.9	Typical Characteristics 10
8	Para	ameter Measurement Information 11
9	Deta	ailed Description 14
	9.1	Overview 14
	9.2	Functional Block Diagrams 14

	9.3	Feature Description	15
	9.4	Device Functional Modes	15
10	Арр	lication and Implementation	18
	10.1	Application Information	18
	10.2	Typical Application	18
11	Pow	ver Supply Recommendations	24
12	Lay	out	25
	12.1		
	12.2	Layout Example	25
13	Dev	ice and Documentation Support	26
	13.1	Device Support	26
	13.2	Third-Party Products Disclaimer	26
	13.3	Related Links	26
	13.4	Receiving Notification of Documentation Updates	26
	13.5	Community Resources	26
	13.6	Trademarks	26
	13.7		
	13.8	Glossary	26
14		hanical, Packaging, and Orderable	
	Info	rmation	27

## 4 Revision History


2


Cł	nanges from Original (September 2017) to Revision A	Page
•	Changed the Machine model (MM) value From: ±400 To: ±200 in the ESD Ratings	6
•	Changed the V <sub>OH</sub> MIN value From: 2.4 V To: 4 V in the <i>Electrical Characteristics</i> table	8

### 5 Device Comparison Table

PART NUMBER	DUPLEX	ENABLES	SIGNALING RATE	NODES	
THVD1512	Full	DE, RE	up to 500 kbpp	256	
THVD1510	Half	DE, RE	up to 500 kbps		
THVD1552	Full	DE, RE		196	
THVD1551	Full	None	up to 50 Mbps		
THVD1550	Half	DE, RE			

## 6 Pin Configuration and Functions





#### **Pin Functions**


	PIN		1/2	DESCRIPTION	
NAME D DGK		DGK	I/O		
A	6	6	Bus input/output	Bus I/O port, A (complementary to B)	
В	7	7	Bus input/output	Bus I/O port, B (complementary to A)	
D	4	4	Digital input	Driver data input	
DE	3	3	Digital input	Driver enable, active high (2 M $\Omega$ internal pull-down)	
GND	5	5	Ground	Device ground	
R	1	1	Digital output	Receive data output	
V <sub>CC</sub>	8	8	Power	5-V supply	
RE	2	2	Digital input	Receiver enable, active low (2 M $\Omega$ internal pull-up)	

#### THVD1510, THVD1512 THVD1550, THVD1551, THVD1552 SLLSEV1A-SEPTEMBER 2017-REVISED JANUARY 2018



www.ti.com

#### THVD1551 Device 8-Pin DGK Package (VSSOP) Top View




#### **Pin Functions**


PIN		I/O	DESCRIPTION	
NAME	DGK	1/0	DESCRIPTION	
А	8	Bus input	Bus input, A (complementary to B)	
В	7	Bus input	Bus input, B (complementary to A)	
D	3	Digital input	Driver data input	
GND	4	Ground	Device ground	
R	2	Digital output	Receive data output	
V <sub>CC</sub>	1	Power	5-V supply	
Y	5	Bus output	Bus output, Y (complementary to Z)	
Z	6	Bus output	Bus output, Z (complementary to Y)	



5

#### www.ti.com





#### **Pin Functions**

PIN		1/0	DESCRIPTION		
NAME	D	DGS	I/O	DESCRIPTION	
А	12	9	Bus input	Bus input, A (complementary to B)	
В	11	8	Bus input	Bus input, B (complementary to A)	
D	5	4	Digital input	Driver data input	
DE	4	3	Digital input	Driver enable, active high (2 M $\Omega$ internal pull-down)	
GND	6, 7 <sup>(1)</sup>	5	Ground	Device ground	
NC	1, 8	—	—	Internally not connected	
R	2	1	Digital output	Receive data output	
V <sub>CC</sub>	13, 14 <sup>(1)</sup>	10	Power	5-V supply	
Υ	9	6	Bus output	Bus output, Y (Complementary to Z)	
Z	10	7	Bus output	Bus output, Z (Complementary to Y)	
RE	3	2	Digital input	Receiver enable, active low (2 M $\Omega$ internal pull-up)	

(1) These pins are internally connected

## 7 Specifications

### 7.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)<sup>(1)</sup>

		MIN	MAX	UNIT
Supply voltage	V <sub>cc</sub>	-0.5	7	V
Bus voltage	Range at any bus pin (A, B, Y, or Z) as differential or common-mode with respect to GND	-18	18	V
Input voltage	Range at any logic pin (D, DE, or $\overline{RE}$ )	-0.3	5.7	V
Receiver output current	Io	-24	24	mA
Storage temperature, T <sub>stg</sub>		-65	150	°C

(1) Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

### 7.2 ESD Ratings

6

				VALUE	UNIT
		Contact discharge, per IEC 61000-4-2	Bus terminals and GND	±18,000	
		Air-gap discharge, per IEC 61000-4-2	Bus terminals and GND	±25,000	
		Liuman hadu madal (LIDM), par	Bus terminals and GND	±30,000	
$V_{(ESD)}$	Electrostatic discharge	Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 <sup>(1)</sup>	All pins except Bus terminals and GND	±8,000	V
		Charged-device model (CDM), per JEDEC C101 $^{\left(2\right)}$	Specification JESD22-	±1,500	)
		Machine model (MM), per JEDEC JESD22	2-A115-A	±200	
V <sub>(EFT)</sub>	Electrical fast transient	Per IEC 61000-4-4	Bus terminals	±4,000	V

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.



### 7.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

			MIN	NOM MAX	UNIT
V <sub>CC</sub>	Supply voltage		4.5	5.5	V
VI	Input voltage at any bus termina	l <sup>(1)</sup>	-15	15	V
V <sub>IH</sub>	High-level input voltage (driver, inputs)	driver enable, and receiver enable	2	V <sub>CC</sub>	V
V <sub>IL</sub>	Low-level input voltage (driver, o inputs)	river enable, and receiver enable	0	0.8	V
V <sub>ID</sub>	Differential input voltage		-15	15	V
I <sub>O</sub>	Output current, driver	-60	60	mA	
I <sub>OR</sub>	Output current, receiver		-8	8	mA
R <sub>L</sub>	Differential load resistance		54		Ω
4 /4		THVD1510, THVD1512		500	kbps
1/t <sub>UI</sub>	Signaling rate	THVD1550, THVD1551, THVD1552		50	Mbps
T <sub>A</sub>	Operating ambient temperature	·	-40	125	°C
TJ	Junction temperature		-40	150	°C

(1) The algebraic convention, in which the least positive (most negative) limit is designated as minimum is used in this data sheet.

#### 7.4 Thermal Information

THERMAL METRIC <sup>(1)</sup>		THVD1510 THVD1550	THVD1552	THVD1510 THVD1550 THVD1551	THVD1512 THVD1552	UNIT
		D (SOIC)	D (SOIC)	DGK (VSSOP)	DGS (VSSOP)	0
		8 PINS	14 PINS	8 PINS	10 PINS	
$R_{\theta JA}$	Junction-to-ambient thermal resistance	112.4	88.0	151.7	151.4	°C/W
$R_{\theta JC(top)}$	Junction-to-case (top) thermal resistance	62.7	45.4	62.8	59.3	°C/W
$R_{\theta JB}$	Junction-to-board thermal resistance	62.0	44.1	81.3	81.6	°C/W
ΨJT	Junction-to-top characterization parameter	15.4	11.3	7.8	6.5	°C/W
ΨЈВ	Junction-to-board characterization parameter	61.3	43.7	79.8	79.9	°C/W
R <sub>0JC(bot)</sub>	Junction-to-case (bottom) thermal resistance	N/A	N/A	N/A	N/A	°C/W

(1) For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report.

### 7.5 Power Dissipation

PARAMETER		TEST CONDITIONS		VALUE	UNIT
		Unterminated	THVD151x 500 kbps	210	mW
Driver and receiver enabled, $V_{CC} = 5.5 \text{ V}, T_A = 125 ^{\circ}\text{C},$	$R_L = 300 \Omega$ , $C_L = 50 pF$ (driver)	THVD155x 50 Mbps	350	TTIVV	
	RS-422 load	THVD151x 500 kbps	220		
PD	50% duty cycle square wave at	$R_L$ = 100 $\Omega$ , $C_L$ = 50 pF (driver)	THVD155x 50 Mbps	330	mW
signaling rate	signaling rate	RS-485 load	THVD151x 500 kbps	250	
		$R_L = 54 \Omega$ , $C_L = 50 pF$ (driver)	THVD155x 50 Mbps	340	mW

Product Folder Links: THVD1510 THVD1512 THVD1550 THVD1551 THVD1552

SLLSEV1A-SEPTEMBER 2017-REVISED JANUARY 2018

INSTRUMENTS

EXAS

www.ti.com

### 7.6 Electrical Characteristics

over operating free-air temperature range (unless otherwise noted)

	PARAMETER	TES	T CONDITIONS		MIN	TYP	MAX	UNIT
Driver								
		$R_{L}$ = 60 $\Omega$ , -15 V ≤ V <sub>test</sub> ≤ 15 V	, (See Figure 11	)	1.5	2.7		V
V <sub>OD</sub>	Driver differential output voltage magnitude	$R_L = 100 \Omega$ (See Figure 12)			2	3		V
	i inago magimado	$R_L = 54 \Omega$ (See Figure 12)			1.5	2.7		V
$\Delta  V_{OD} $	Change in differential output voltage		$R_L = 54 \Omega$ (See Figure 12)				200	mV
V <sub>oc</sub>	Common-mode output voltage	$R_L = 54 \Omega$ (See Figure 12)				V <sub>CC</sub> /2	3	V
$\Delta V_{OC(SS)}$	Change in steady-state common-mode output voltage				-200		200	mV
l <sub>os</sub>	Short-circuit output current	$DE = V_CC,  \text{-15} \; V \leq V_O \leq 15 V$	$E = V_{CC}, -15 V \le V_0 \le 15V$				250	mA
Receiver								
				V <sub>I</sub> = 12 V		75	125	
				V <sub>I</sub> = 15 V		95	156	
			THVD151x	V <sub>I</sub> = -7 V	-100	-40		
				V <sub>I</sub> = -15 V	-215	-85		μА
I <sub>I</sub>	Bus input current	$DE = 0 V, V_{CC} = 0 V \text{ or } 5.5 V$		V <sub>I</sub> = 12 V		115	160	
			THVD155x	V <sub>I</sub> = 15 V		150	200	
				V <sub>1</sub> = -7 V	-130	-75		
				V <sub>I</sub> = -15 V	-280	-180		
Receiver								
V <sub>TH+</sub>	Positive-going input threshold voltage		Over common-mode range of - 7 V to +12 V			-85	-20	mV
V <sub>TH-</sub>	Negative-going input threshold voltage	Over common-mode range of				-135	See <sup>(1)</sup>	mV
V <sub>HYS</sub>	Input hysteresis	-				50		mV
V <sub>TH+</sub>	Positive-going input threshold voltage				See <sup>(1)</sup>	-85	-20	mV
V <sub>TH-</sub>	Negative-going input threshold voltage	Over common-mode range of	± 15 V	-	-220	-135	See <sup>(1)</sup>	mV
V <sub>HYS</sub>	Input hysteresis					50		mV
V <sub>OH</sub>	Output high voltage	I <sub>OH</sub> = -8 mA			4	V <sub>CC</sub> - 0.3		V
V <sub>OL</sub>	Output low voltage	I <sub>OL</sub> = 8 mA				0.2	0.4	V
I <sub>OZ</sub>	Output high-impedance current	$V_0 = 0 V \text{ or } V_{CC}, \overline{RE} = V_{CC}$			-1		1	μA
Logic				Ш				
I <sub>IN</sub>	Input current (D, DE, RE)	$4.5 \text{ V} \leq \text{V}_{\text{CC}} \leq 5.5 \text{ V}, 0 \text{ V} \leq \text{V}_{\text{IN}} \leq \text{V}_{\text{CC}}$			-5	0	5	μA
Supply				L				
		Driver and receiver enabled $\overline{RE} = 0 \text{ V}, \text{ DE} = \text{V}_{CC},$ No load			700	1000	μA	
	Supply surrent (suissessit)	Driver enabled, receiver disabled $\overline{RE} = V_{CC}$ , $DE = V_{CC}$ , No load				400	620	μA
I <sub>CC</sub>	Supply current (quiescent)	Driver disabled, receiver enab	led	$\overline{RE} = 0 V, DE = 0 V,$ No load		400	630	μA
		Driver and receiver disabled $\overline{RE} = V_{CC}$ , $DE = 0 V$ , D = open, No load			0.1	1	μA	

(1) Under any specific conditions,  $V_{TH+}$  is specified to be at least  $V_{HYS}$  higher than  $V_{TH-}$ .

8

Product Folder Links: THVD1510 THVD1512 THVD1550 THVD1551 THVD1552



### 7.7 Switching Characteristics

500-kbps devices (THVD1510, THVD1512) over recommended operating conditions

PARAMETER		TEST C	ONDITIONS	MIN TYP MAX		UNIT	
Driver						¥	
t <sub>r</sub> , t <sub>f</sub>	Differential output rise/fall time			300	400	600	ns
t <sub>PHL</sub> , t <sub>PLH</sub>	Propagation delay	$R_L = 54 \Omega, C_L = 50 pF$	See Figure 13		350	500	ns
t <sub>SK(P)</sub>	Pulse skew,  t <sub>PHL</sub> – t <sub>PLH</sub>					15	ns
t <sub>PHZ</sub> , t <sub>PLZ</sub>	Disable time (THVD1510, THVD1512)		See Figure 14 and		110	200	ns
	Enable time (THVD1510,	RE = 0 V	Figure 15		100	500	ns
t <sub>PZH</sub> , t <sub>PZL</sub> THVD1512)	$\overline{RE} = V_{CC}$			2	4	μs	
Receiver						·	
t <sub>r</sub> , t <sub>f</sub>	Differential output rise/fall time				15	25	ns
t <sub>PHL</sub> , t <sub>PLH</sub>	Propagation delay	C <sub>L</sub> = 15 pF	See Figure 16		50	60	ns
t <sub>SK(P)</sub>	Pulse skew,  t <sub>PHL</sub> – t <sub>PLH</sub>					10	ns
t <sub>PHZ</sub> , t <sub>PLZ</sub>	Disable time (THVD1510, THVD1512)				30	40	ns
t <sub>PZH(1)</sub> ,		$DE = V_{CC}$	See Figure 17		60	100	ns
t <sub>PZL(1)</sub> , t <sub>PZH(2)</sub> , t <sub>PZL(2)</sub>	Enable time (THVD1510, THVD1512)	DE = 0 V	See Figure 18		3	8	μS

### 7.8 Switching Characteristics

50-Mbps devices (THVD1550, THVD1551, THVD1552) over recommended operating conditions


	PARAMETER	TEST C	MIN	TYP	MAX	UNIT	
Driver							
t <sub>r</sub> , t <sub>f</sub>	Differential output rise/fall time			1	2	6	ns
t <sub>PHL</sub> , t <sub>PLH</sub>	Propagation delay	$R_L = 54 \Omega$ , $C_L = 50 pF$	See Figure 13	5	10	16	ns
t <sub>SK(P)</sub>	Pulse skew,  t <sub>PHL</sub> – t <sub>PLH</sub>	_				3.5	ns
t <sub>PHZ</sub> , t <sub>PLZ</sub>	Disable time (THVD1550, THVD1552)		See Figure 14 and		10	22	ns
	Enable time (THVD1550,	RE = 0 V Figure 15		10	22	ns	
t <sub>PZH</sub> , t <sub>PZL</sub> THVD1552)	$\overline{RE} = V_{CC}$			2	4	μS	
Receiver							
t <sub>r</sub> , t <sub>f</sub>	Differential output rise/fall time			1	3	6	ns
t <sub>PHL</sub> , t <sub>PLH</sub>	Propagation delay	C <sub>L</sub> = 15 pF	See Figure 16		30	45	ns
t <sub>SK(P)</sub>	Pulse skew,  t <sub>PHL</sub> – t <sub>PLH</sub>	_				2	ns
t <sub>PHZ</sub> , t <sub>PLZ</sub>	Disable time (THVD1550, THVD1552)				8	18	ns
t <sub>PZH(1)</sub> ,		DE = V <sub>CC</sub>	See Figure 17		55	90	ns
t <sub>PZL(1)</sub> , t <sub>PZH(2)</sub> , t <sub>PZL(2)</sub>	t <sub>PZL(1)</sub> , Enable time (THVD1550, t <sub>PZH(2)</sub> , THVD1552)	DE = 0 V	See Figure 18		3	8	μS

#### THVD1510, THVD1512 THVD1550, THVD1551, THVD1552 SLLSEV1A – SEPTEMBER 2017 – REVISED JANUARY 2018

TEXAS INSTRUMENTS

www.ti.com

### 7.9 Typical Characteristics




Copyright © 2017-2018, Texas Instruments Incorporated


Product Folder Links: THVD1510 THVD1512 THVD1550 THVD1551 THVD1552



#### **Typical Characteristics (continued)**



### 8 Parameter Measurement Information



Copyright © 2017, Texas Instruments Incorporated

Figure 11. Measurement of Driver Differential Output Voltage With Common-Mode Load



### Parameter Measurement Information (continued)




Figure 12. Measurement of Driver Differential and Common-Mode Output With RS-485 Load




Figure 13. Measurement of Driver Differential Output Rise and Fall Times and Propagation Delays




Figure 14. Measurement of Driver Enable and Disable Times With Active High Output and Pull-Down Load





Figure 15. Measurement of Driver Enable and Disable Times With Active Low Output and Pull-up Load






Product Folder Links: THVD1510 THVD1512 THVD1550 THVD1551 THVD1552




### Parameter Measurement Information (continued)



Copyright © 2017, Texas Instruments Incorporated

#### Figure 17. Measurement of Receiver Enable/Disable Times With Driver Enabled



Copyright © 2017, Texas Instruments Incorporated

Figure 18. Measurement of Receiver Enable Times With Driver Disabled




### 9 Detailed Description

#### 9.1 Overview

THVD1510 and THVD1550 are low-power, half-duplex RS-485 transceivers available in two speed grades suitable for data transmission up to 500 kbps and 50 Mbps respectively.


THVD1551 is fully enabled with no external enabling pins. THVD1512 and THVD1552 have active-high driver enables and active-low receiver enables. A standby current of less than 1  $\mu$ A can be achieved by disabling both driver and receiver.

#### 9.2 Functional Block Diagrams




Copyright © 2017, Texas Instruments Incorporated

#### Figure 19. THVD1510 and THVD1550




Copyright © 2017, Texas Instruments Incorporated

Figure 20. THVD1551



Copyright © 2017, Texas Instruments Incorporated





#### 9.3 Feature Description

Internal ESD protection circuits of the THVD15xx protect the transceivers against electrostatic discharges (ESD) according to IEC 61000-4-2 of up to  $\pm$ 18 kV and against electrical fast transients (EFT) according to IEC 61000-4-4 of up to  $\pm$ 4 kV. With careful system design, one could achieve  $\pm$ 4 kV EFT Criterion A (no data loss when transient noise is present).

The THVD15xx device family provides internal biasing of the receiver input thresholds in combination with large input-threshold hysteresis. The receiver output remains logic high under a bus-idle or bus-short conditions without the need for external failsafe biasing resistors. Device operation is specified over a wide ambient temperature range from -40°C to 125°C.

#### 9.4 Device Functional Modes

#### 9.4.1 Device Functional Modes for THVD1510 and THVD1550

When the driver enable pin, DE, is logic high, the differential outputs A and B follow the logic states at data input D. A logic high at D causes A to turn high and B to turn low. In this case the differential output voltage defined as  $V_{OD} = V_A - V_B$  is positive. When D is low, the output states reverse: B turns high, A becomes low, and  $V_{OD}$  is negative.

When DE is low, both outputs turn high-impedance. In this condition the logic state at D is irrelevant. The DE pin has an internal pull-down resistor to ground, thus when left open the driver is disabled (high-impedance) by default. The D pin has an internal pull-up resistor to  $V_{CC}$ , thus, when left open while the driver is enabled, output A turns high and B turns low.

INPUT	ENABLE	OUTPUTS		FUNCTION
D	DE	Α	В	FUNCTION
Н	Н	Н	L	Actively drive bus high
L	Н	L	н	Actively drive bus low
Х	L	Z	Z	Driver disabled
Х	OPEN	Z	Z	Driver disabled by default
OPEN	Н	Н	L	Actively drive bus high by default

Table 1. Driver Function Table for THVD1510 and THVD1550

When the receiver enable pin,  $\overline{RE}$ , is logic low, the receiver is enabled. When the differential input voltage defined as  $V_{ID} = V_A - V_B$  is higher than the positive input threshold,  $V_{TH+}$ , the receiver output, R, turns high. When  $V_{ID}$  is lower than the negative input threshold,  $V_{TH-}$ , the receiver output, R, turns low. If  $V_{ID}$  is between  $V_{TH+}$  and  $V_{TH-}$  the output is indeterminate.

When  $\overline{RE}$  is logic high or left open, the receiver output is high-impedance and the magnitude and polarity of V<sub>ID</sub> are irrelevant. Internal biasing of the receiver inputs causes the output to go failsafe-high when the transceiver is disconnected from the bus (open-circuit), the bus lines are shorted to one another (short-circuit), or the bus is not actively driven (idle bus).

DIFFERENTIAL INPUT	ENABLE	OUTPUT	FUNCTION
$V_{ID} = V_A - V_B$	RE	R	FUNCTION
$V_{TH+} < V_{ID}$	L	Н	Receive valid bus high
$V_{TH-} < V_{ID} < V_{TH+}$	L	?	Indeterminate bus state
$V_{ID} < V_{TH-}$	L	L	Receive valid bus low
х	н	Z	Receiver disabled
X	OPEN	Z	Receiver disabled by default
Open-circuit bus	L	Н	Fail-safe high output
Short-circuit bus	L	Н	Fail-safe high output
Idle (terminated) bus	L	Н	Fail-safe high output



#### 9.4.2 Device Functional Modes for THVD1551

For this device, the driver and receiver are fully enabled, thus the differential outputs Y and Z follow the logic states at data input D at all times. A logic high at D causes Y to turn high and Z to turn low. In this case, the differential output voltage defined as  $V_{OD} = V_Y - V_Z$  is positive. When D is low, the output states reverse: Z turns high, Y becomes low, and VOD is negative. The D pin has an internal pull-up resistor to  $V_{CC}$ , thus, when left open while the driver is enabled, output Y turns high and Z turns low.

INPUT	OUTI	PUTS	FUNCTIONS
D	Y	Z	FUNCTIONS
Н	Н	L	Actively drive bus high
L	L	Н	Actively drive bus low
OPEN	Н	L	Actively drive bus high by default

#### Table 3. Driver Function Table for THVD1551

When the differential input voltage defined as  $V_{ID} = V_A - V_B$  is higher than the positive input threshold,  $V_{TH+}$ , the receiver output, R, turns high. When  $V_{ID}$  is less than the negative input threshold,  $V_{TH-}$ , the receiver output, R, turns low. If  $V_{ID}$  is between  $V_{TH+}$  and  $V_{TH-}$  the output is indeterminate. Internal biasing of the receiver inputs causes the output to go failsafe-high when the transceiver is disconnected from the bus (open-circuit), the bus lines are shorted to one another (short-circuit), or the bus is not actively driven (idle bus).

DIFFERENTIAL INPUT	OUTPUT	FUNCTION				
$V_{ID} = V_A - V_B$	R	FONCTION				
$V_{TH+} < V_{ID}$	н	Receive valid bus high				
$V_{TH-} < V_{ID} < V_{TH+}$	?	Indeterminate bus state				
$V_{ID} < V_{TH-}$	L	Receive valid bus low				
Open-circuit bus	Н	Fail-safe high output				
Short-circuit bus	Н	Fail-safe high output				
Idle (terminated) bus	Н	Fail-safe high output				

#### Table 4. Receiver Function Table for THVD1551

#### 9.4.3 Device Functional Modes for THVD1512 and THVD1552

н

When the driver enable pin, DE, is logic high, the differential outputs Y and Z follow the logic states at data input D. A logic high at D causes Y to turn high and Z to turn low. In this case the differential output voltage defined as  $V_{OD} = V_Y - V_Z$  is positive. When D is low, the output states reverse: Z turns high, Y becomes low, and  $V_{OD}$  is negative.

When DE is low, both outputs turn high-impedance. In this condition the logic state at D is irrelevant. The DE pin has an internal pull-down resistor to ground, thus when left open the driver is disabled (high-impedance) by default. The D pin has an internal pull-up resistor to  $V_{CC}$ , thus, when left open while the driver is enabled, output Y turns high and Z turns low.

INPUT	ENABLE	OUTI	PUTS	FUNCTION
D	DE	Y	Z	FUNCTION
Н	Н	Н	L	Actively drive bus high
L	Н	L	Н	Actively drive bus low
Х	L	Z	Z	Driver disabled
Х	OPEN	Z	Z	Driver disabled by default

L.

н

 Table 5. Driver Function Table for THVD1512 and THVD1552

OPEN

Actively drive bus high by default



When the receiver enable pin,  $\overline{RE}$ , is logic low, the receiver is enabled. When the differential input voltage defined as  $V_{ID} = V_A - V_B$  is higher than the positive input threshold,  $V_{TH+}$ , the receiver output, R, turns high. When  $V_{ID}$  is lower than the negative input threshold,  $V_{TH-}$ , the receiver output, R, turns low. If  $V_{ID}$  is between  $V_{TH+}$  and  $V_{TH-}$  the output is indeterminate.

When  $\overline{\text{RE}}$  is logic high or left open, the receiver output is high-impedance and the magnitude and polarity of V<sub>ID</sub> are irrelevant. Internal biasing of the receiver inputs causes the output to go failsafe-high when the transceiver is disconnected from the bus (open-circuit), the bus lines are shorted to one another (short-circuit), or the bus is not actively driven (idle bus).

DIFFERENTIAL INPUT	ENABLE	OUTPUT	FUNCTION
$V_{ID} = V_A - V_B$	RE	R	FUNCTION
$V_{TH+} < V_{ID}$	L	н	Receive valid bus high
$V_{TH-} < V_{ID} < V_{TH+}$	L	?	Indeterminate bus state
V <sub>ID</sub> < V <sub>TH-</sub>	L	L	Receive valid bus low
Х	Н	Z	Receiver disabled
Х	OPEN	Z	Receiver disabled by default
Open-circuit bus	L	Н	Fail-safe high output
Short-circuit bus	L	Н	Fail-safe high output
Idle (terminated) bus	L	Н	Fail-safe high output

#### Table 6. Receiver Function Table for THVD1512 and THVD1552



### **10** Application and Implementation

#### NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

#### **10.1** Application Information

The THVD15xx family consists of half-duplex and full-duplex RS-485 transceivers commonly used for asynchronous data transmissions. For half-duplex devices, the driver and receiver enable pins allow for the configuration of different operating modes. Full-duplex implementation requires two signal pairs (four wires), and allows each node to transmit data on one pair while simultaneously receiving data on the other pair.

#### **10.2 Typical Application**

An RS-485 bus consists of multiple transceivers connecting in parallel to a bus cable. To eliminate line reflections, each cable end is terminated with a termination resistor,  $R_T$ , whose value matches the characteristic impedance,  $Z_0$ , of the cable. This method, known as parallel termination, generally allows for higher data rates over longer cable length.




Figure 22. Typical RS-485 Network With Half-Duplex Transceivers




Figure 23. Typical RS-485 Network With Full-Duplex Transceivers



#### **Typical Application (continued)**

#### 10.2.1 Design Requirements

RS-485 is a robust electrical standard suitable for long-distance networking that may be used in a wide range of applications with varying requirements, such as distance, data rate, and number of nodes.

#### 10.2.1.1 Data Rate and Bus Length

There is an inverse relationship between data rate and cable length, which means the higher the data rate, the shorter the cable length; and conversely, the lower the data rate, the longer the cable length. While most RS-485 systems use data rates between 10 kbps and 100 kbps, some applications require data rates up to 250 kbps at distances of 4000 feet and longer. Longer distances are possible by allowing for small signal jitter of up to 5 or 10%.




Figure 24. Cable Length vs Data Rate Characteristic

Even higher data rates are achievable (that is, 50 Mbps for the THVD1550, THVD1551 and THVD1552) in cases where the interconnect is short enough (or has suitably low attenuation at signal frequencies) to not degrade the data.

#### 10.2.1.2 Stub Length

When connecting a node to the bus, the distance between the transceiver inputs and the cable trunk, known as the stub, should be as short as possible. Stubs present a non-terminated piece of bus line which can introduce reflections of varying phase as the length of the stub increases. As a general guideline, the electrical length, or round-trip delay, of a stub should be less than one-tenth of the rise time of the driver, thus giving a maximum physical stub length as shown in Equation 1.

 $L_{(STUB)} \le 0.1 \times t_r \times v \times c$ 

where

- t<sub>r</sub> is the 10/90 rise time of the driver
- c is the speed of light  $(3 \times 10^8 \text{ m/s})$
- *v* is the signal velocity of the cable or trace as a factor of *c*

(1)

### 10.2.1.3 Bus Loading

The RS-485 standard specifies that a compliant driver must be able to drive 32 unit loads (UL), where 1 unit load represents a load impedance of approximately 12 k $\Omega$ . Because the THVD15xx family consists of 1/8 UL transceivers, connecting up to 256 receivers to the bus is possible.



### **Typical Application (continued)**

#### 10.2.1.4 Receiver Failsafe

The differential receivers of the THVD15xx family are failsafe to invalid bus states caused by the following:

- Open bus conditions, such as a disconnected connector
- Shorted bus conditions, such as cable damage shorting the twisted-pair together
- Idle bus conditions that occur when no driver on the bus is actively driving

In any of these cases, the differential receiver will output a failsafe logic high state so that the output of the receiver is not indeterminate.

Receiver failsafe is accomplished by offsetting the receiver thresholds such that the input indeterminate range does not include zero volts differential. In order to comply with the RS-422 and RS-485 standards, the receiver output must output a high when the differential input  $V_{ID}$  is more positive than 200 mV, and must output a low when  $V_{ID}$  is more negative than -200 mV. The receiver parameters which determine the failsafe performance are  $V_{TH+}$ ,  $V_{TH-}$ , and  $V_{HYS}$  (the separation between  $V_{TH+}$  and  $V_{TH-}$ ). As shown in the Electrical Characteristics table, differential signals more negative than -200 mV will always cause a low receiver output, and differential signals more positive than 200 mV will always cause a high receiver output.

When the differential input signal is close to zero, it is still above the  $V_{TH+}$  threshold, and the receiver output will be high. Only when the differential input is more than  $V_{HYS}$  below  $V_{TH+}$  will the receiver output transition to a low state. Therefore, the noise immunity of the receiver inputs during a bus fault conditions includes the receiver hysteresis value,  $V_{hys}$ , as well as the value of  $V_{TH+}$ .



#### **Typical Application (continued)**

#### 10.2.1.5 Transient Protection

The bus pins of the THVD15xx transceiver family include on-chip ESD protection against ±30-kV HBM and ±18-kV IEC 61000-4-2 contact discharge. The International Electrotechnical Commission (IEC) ESD test is far more severe than the HBM ESD test. The 50% higher charge capacitance,  $C_{(S)}$ , and 78% lower discharge resistance,  $R_{(D)}$ , of the IEC model produce significantly higher discharge currents than the HBM model. As stated in the IEC 61000-4-2 standard, contact discharge is the preferred transient protection test method.





Figure 25. HBM and IEC ESD Models and Currents in Comparison (HBM Values in Parenthesis)

The on-chip implementation of IEC ESD protection significantly increases the robustness of equipment. Common discharge events occur because of human contact with connectors and cables. Designers may choose to implement protection against longer duration transients, typically referred to as surge transients.

EFTs are generally caused by relay-contact bounce or the interruption of inductive loads. Surge transients often result from lightning strikes (direct strike or an indirect strike which induce voltages and currents), or the switching of power systems, including load changes and short circuit switching. These transients are often encountered in industrial environments, such as factory automation and power-grid systems.

Figure 26 compares the pulse power of the EFT and surge transients with the power caused by an IEC ESD transient. The left-hand diagram shows the relative pulse-power for a 0.5-kV surge transient and 4-kV EFT transient, both of which dwarf the 10-kV ESD transient visible in the lower-left corner. 500-V surge transients are representative of events that may occur in factory environments in industrial and process automation.

The right-hand diagram shows the pulse-power of a 6-kV surge transient, relative to the same 0.5-kV surge transient. 6-kV surge transients are most likely to occur in power generation and power-grid systems.





Copyright © 2017–2018, Texas Instruments Incorporated

Product Folder Links: THVD1510 THVD1512 THVD1550 THVD1551 THVD1552

#### THVD1510, THVD1512 THVD1550, THVD1551, THVD1552 SLLSEV1A – SEPTEMBER 2017 – REVISED JANUARY 2018

TEXAS INSTRUMENTS

www.ti.com

### **Typical Application (continued)**

In the case of surge transients, high-energy content is characterized by long pulse duration and slow decaying pulse power. The electrical energy of a transient that is dumped into the internal protection cells of a transceiver is converted into thermal energy, which heats and destroys the protection cells, thus destroying the transceiver. Figure 27 shows the large differences in transient energies for single ESD, EFT, surge transients, and an EFT pulse train that is commonly applied during compliance testing.





Figure 27. Comparison of Transient Energies

### 10.2.2 Detailed Design Procedure

Figure 28 and Figure 29 suggest a protection circuit against 1 kV surge (IEC 61000-4-5) transients. Table 7 shows the associated bill of materials.



Copyright © 2017, Texas instruments incorporated


Figure 28. Transient Protection Against Surge Transients for Half-Duplex Devices

Copyright © 2017-2018, Texas Instruments Incorporated

Product Folder Links: THVD1510 THVD1512 THVD1550 THVD1551 THVD1552



# Typical Application (continued)



Copyright © 2017, Texas Instruments Incorporated

#### Figure 29. Transient Protection Against Surge Transients for Full-Duplex Devices

### Table 7. Bill of Materials

DEVICE	FUNCTION	ORDER NUMBER	MANUFACTURER
XCVR	5-V, RS-485 transceiver	THVD15xx	TI
R1	10.0 pulse proof thick film register		Viebov
R2	10- $\Omega$ , pulse-proof thick-film resistor	CRCW0603010RJNEAHP	Vishay
TVS	Bidirectional 400-W transient suppressor	CDSOT23-SM712	Bourns


## THVD1510, THVD1512 THVD1550, THVD1551, THVD1552

SLLSEV1A-SEPTEMBER 2017-REVISED JANUARY 2018



www.ti.com

#### 10.2.3 Application Curves



#### **Power Supply Recommendations** 11

To ensure reliable operation at all data rates and supply voltages, each supply should be decoupled with a 100 nF ceramic capacitor located as close to the supply pins as possible. This helps to reduce supply voltage ripple present on the outputs of switched-mode power supplies and also helps to compensate for the resistance and inductance of the PCB power planes.




## 12 Layout

### 12.1 Layout Guidelines

Robust and reliable bus node design often requires the use of external transient protection devices in order to protect against surge transients that may occur in industrial environments. Since these transients have a wide frequency bandwidth (from approximately 3 MHz to 300 MHz), high-frequency layout techniques should be applied during PCB design.

- 1. Place the protection circuitry close to the bus connector to prevent noise transients from propagating across the board.
- 2. Use V<sub>CC</sub> and ground planes to provide low inductance. Note that high-frequency currents tend to follow the path of least impedance and not the path of least resistance.
- 3. Design the protection components into the direction of the signal path. Do not force the transient currents to divert from the signal path to reach the protection device.
- 4. Apply 100-nF to 220-nF decoupling capacitors as close as possible to the  $V_{CC}$  pins of transceiver, UART and/or controller ICs on the board.
- 5. Use at least two vias for V<sub>CC</sub> and ground connections of decoupling capacitors and protection devices to minimize effective via inductance.
- 6. Use  $1-k\Omega$  to  $10-k\Omega$  pullup and pulldown resistors for enable lines to limit noise currents in these lines during transient events.
- 7. Insert pulse-proof resistors into the A and B bus lines if the TVS clamping voltage is higher than the specified maximum voltage of the transceiver bus pins. These resistors limit the residual clamping current into the transceiver and prevent it from latching up.
- 8. While pure TVS protection is sufficient for surge transients up to 1 kV, higher transients require metal-oxide varistors (MOVs) which reduce the transients to a few hundred volts of clamping voltage, and transient blocking units (TBUs) that limit transient current to less than 1 mA.



### 12.2 Layout Example

Figure 32. Half-Duplex Layout Example

TEXAS INSTRUMENTS

www.ti.com

### **13** Device and Documentation Support

#### **13.1 Device Support**

#### 13.2 Third-Party Products Disclaimer

TI'S PUBLICATION OF INFORMATION REGARDING THIRD-PARTY PRODUCTS OR SERVICES DOES NOT CONSTITUTE AN ENDORSEMENT REGARDING THE SUITABILITY OF SUCH PRODUCTS OR SERVICES OR A WARRANTY, REPRESENTATION OR ENDORSEMENT OF SUCH PRODUCTS OR SERVICES, EITHER ALONE OR IN COMBINATION WITH ANY TI PRODUCT OR SERVICE.

#### 13.3 Related Links

The table below lists quick access links. Categories include technical documents, support and community resources, tools and software, and quick access to order now.

PARTS	PRODUCT FOLDER	ORDER NOW	TECHNICAL DOCUMENTS	TOOLS & SOFTWARE	SUPPORT & COMMUNITY
THVD1510	Click here	Click here	Click here	Click here	Click here
THVD1512	Click here	Click here	Click here	Click here	Click here
THVD1550	Click here	Click here	Click here	Click here	Click here
THVD1551	Click here	Click here	Click here	Click here	Click here
THVD1552	Click here	Click here	Click here	Click here	Click here

#### Table 8. Related Links

### 13.4 Receiving Notification of Documentation Updates

To receive notification of documentation updates — go to the product folder for your device on ti.com. In the upper right-hand corner, click the *Alert me* button to register and receive a weekly digest of product information that has changed (if any). For change details, check the revision history of any revised document.

### 13.5 Community Resources

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

TI E2E<sup>™</sup> Online Community *TI's Engineer-to-Engineer (E2E) Community.* Created to foster collaboration among engineers. At e2e.ti.com, you can ask questions, share knowledge, explore ideas and help solve problems with fellow engineers.

**Design Support TI's Design Support** Quickly find helpful E2E forums along with design support tools and contact information for technical support.

#### 13.6 Trademarks

E2E is a trademark of Texas Instruments.

#### 13.7 Electrostatic Discharge Caution



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

### 13.8 Glossary

SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.



27

### 14 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

#### THVD1510, THVD1512 THVD1550, THVD1551, THVD1552 SLLSEV1A – SEPTEMBER 2017 – REVISED JANUARY 2018

D0008B

Texas Instruments


www.ti.com



### PACKAGE OUTLINE

#### SOIC - 1.75 mm max height

SOIC



NOTES:

28

- 1. Linear dimensions are in inches [millimeters]. Dimensions in parenthesis are for reference only. Controlling dimensions are in inches. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.
- 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed .006 [0.15], per side.
- 4. This dimension does not include interlead flash.
- 5. Reference JEDEC registration MS-012, variation AA.

www.ti.com

Copyright © 2017-2018, Texas Instruments Incorporated




D0008B

#### www.ti.com

# **EXAMPLE BOARD LAYOUT**

### SOIC - 1.75 mm max height

SOIC



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

www.ti.com

#### THVD1510, THVD1512 THVD1550, THVD1551, THVD1552 SLLSEV1A-SEPTEMBER 2017-REVISED JANUARY 2018

D0008B


Texas Instruments

www.ti.com

### EXAMPLE STENCIL DESIGN

SOIC - 1.75 mm max height

SOIC



NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

9. Board assembly site may have different recommendations for stencil design.

www.ti.com

Copyright © 2017–2018, Texas Instruments Incorporated


Product Folder Links: THVD1510 THVD1512 THVD1550 THVD1551 THVD1552



### **MECHANICAL DATA**

DGK (S-PDSO-G8)

## PLASTIC SMALL-OUTLINE PACKAGE




- NOTES: A. All linear dimensions are in millimeters.
  - B. This drawing is subject to change without notice.
  - Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 per end.
  - D Body width does not include interlead flash. Interlead flash shall not exceed 0.50 per side.
  - E. Falls within JEDEC MO-187 variation AA, except interlead flash.



TEXAS INSTRUMENTS

www.ti.com

### LAND PATTERN DATA




NOTES: A. All linear dimensions are in millimeters.

- B. This drawing is subject to change without notice.
- C. Publication IPC-7351 is recommended for alternate designs.
- D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC-7525 for other stencil recommendations.
- E. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.





### LAND PATTERN DATA



NOTES: A. All linear dimensions are in millimeters.

- B. This drawing is subject to change without notice.
- C. Publication IPC-7351 is recommended for alternate designs.
- D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC-7525 for other stencil recommendations.
- E. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.



#### THVD1510, THVD1512 THVD1550, THVD1551, THVD1552 SLLSEV1A-SEPTEMBER 2017-REVISED JANUARY 2018

ÈXAS **NSTRUMENTS** 


www.ti.com

# **DGS0010A**

# **PACKAGE OUTLINE**

### VSSOP - 1.1 mm max height

SMALL OUTLINE PACKAGE



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M. 2. This drawing is subject to change without notice.
- 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
- This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
   Reference JEDEC registration MO-187, variation BA.


www.ti.com

# EXAMPLE BOARD LAYOUT

# VSSOP - 1.1 mm max height

SMALL OUTLINE PACKAGE





NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

www.ti.com

**DGS0010A** 




www.ti.com

### **EXAMPLE STENCIL DESIGN**

### VSSOP - 1.1 mm max height

SMALL OUTLINE PACKAGE



NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations. 9. Board assembly site may have different recommendations for stencil design.

www.ti.com

Copyright © 2017-2018, Texas Instruments Incorporated

Product Folder Links: THVD1510 THVD1512 THVD1550 THVD1551 THVD1552



24-Jan-2018

# PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead/Ball Finish	MSL Peak Temp	Op Temp (°C)	Device Marking	Samples
	(1)	0010		0		(2)	(6)	(3)	40 1 405	(4/5)	
THVD1510D	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 125	VD1510	Sample
THVD1510DGK	ACTIVE	VSSOP	DGK	8	80	Green (RoHS & no Sb/Br)	CU NIPDAUAG	Level-1-260C-UNLIM	-40 to 125	1510	Sample
THVD1510DGKR	ACTIVE	VSSOP	DGK	8	2500	Green (RoHS & no Sb/Br)	CU NIPDAUAG	Level-1-260C-UNLIM	-40 to 125	1510	Sample
THVD1510DR	ACTIVE	SOIC	D	8	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 125	VD1510	Sample
THVD1512D	PREVIEW	SOIC	D	14	75	TBD	Call TI	Call TI	-40 to 125		
THVD1512DGS	ACTIVE	VSSOP	DGS	10	80	Green (RoHS & no Sb/Br)	CU NIPDAUAG	Level-1-260C-UNLIM	-40 to 125	1512	Samples
THVD1512DGSR	ACTIVE	VSSOP	DGS	10	2500	Green (RoHS & no Sb/Br)	CU NIPDAUAG	Level-1-260C-UNLIM	-40 to 125	1512	Samples
THVD1512DR	PREVIEW	SOIC	D	14	2500	TBD	Call TI	Call TI	-40 to 125		
THVD1550D	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 125	VD1550	Samples
THVD1550DGK	ACTIVE	VSSOP	DGK	8	80	Green (RoHS & no Sb/Br)	CU NIPDAUAG	Level-1-260C-UNLIM	-40 to 125	1550	Samples
THVD1550DGKR	ACTIVE	VSSOP	DGK	8	2500	Green (RoHS & no Sb/Br)	CU NIPDAUAG	Level-1-260C-UNLIM	-40 to 125	1550	Samples
THVD1550DR	ACTIVE	SOIC	D	8	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-40 to 125	VD1550	Samples
THVD1551DGK	ACTIVE	VSSOP	DGK	8	80	Green (RoHS & no Sb/Br)	CU NIPDAUAG	Level-1-260C-UNLIM	-40 to 125	1551	Samples
THVD1551DGKR	ACTIVE	VSSOP	DGK	8	2500	Green (RoHS & no Sb/Br)	CU NIPDAUAG	Level-1-260C-UNLIM	-40 to 125	1551	Samples
THVD1552D	PREVIEW	SOIC	D	14	50	TBD	Call TI	Call TI	-40 to 125		
THVD1552DGS	ACTIVE	VSSOP	DGS	10	80	Green (RoHS & no Sb/Br)	CU NIPDAUAG	Level-1-260C-UNLIM	-40 to 125	1552	Samples
THVD1552DGSR	ACTIVE	VSSOP	DGS	10	2500	Green (RoHS & no Sb/Br)	CU NIPDAUAG	Level-1-260C-UNLIM	-40 to 125	1552	Samples
THVD1552DR	PREVIEW	SOIC	D	14	2500	TBD	Call TI	Call TI	-40 to 125		

<sup>(1)</sup> The marketing status values are defined as follows:



24-Jan-2018

ACTIVE: Product device recommended for new designs. LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect. NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

<sup>(2)</sup> RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

**RoHS Exempt:** TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption. **Green:** TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

<sup>(3)</sup> MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

<sup>(4)</sup> There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(<sup>5)</sup> Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

(6) Lead/Ball Finish - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:**The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

# PACKAGE MATERIALS INFORMATION

www.ti.com


Texas Instruments

### TAPE AND REEL INFORMATION





### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal												
Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
THVD1510DGKR	VSSOP	DGK	8	2500	330.0	12.4	5.3	3.4	1.4	8.0	12.0	Q1
THVD1510DR	SOIC	D	8	2500	330.0	12.4	6.4	5.2	2.1	8.0	12.0	Q1
THVD1512DGSR	VSSOP	DGS	10	2500	330.0	12.4	5.3	3.4	1.4	8.0	12.0	Q1
THVD1550DGKR	VSSOP	DGK	8	2500	330.0	12.4	5.3	3.4	1.4	8.0	12.0	Q1
THVD1550DR	SOIC	D	8	2500	330.0	12.4	6.4	5.2	2.1	8.0	12.0	Q1
THVD1551DGKR	VSSOP	DGK	8	2500	330.0	12.4	5.3	3.4	1.4	8.0	12.0	Q1
THVD1552DGSR	VSSOP	DGS	10	2500	330.0	12.4	5.3	3.4	1.4	8.0	12.0	Q1

Texas Instruments

www.ti.com

# PACKAGE MATERIALS INFORMATION

20-Dec-2017



\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
THVD1510DGKR	VSSOP	DGK	8	2500	364.0	364.0	27.0
THVD1510DR	SOIC	D	8	2500	340.5	338.1	20.6
THVD1512DGSR	VSSOP	DGS	10	2500	364.0	364.0	27.0
THVD1550DGKR	VSSOP	DGK	8	2500	364.0	364.0	27.0
THVD1550DR	SOIC	D	8	2500	340.5	338.1	20.6
THVD1551DGKR	VSSOP	DGK	8	2500	364.0	364.0	27.0
THVD1552DGSR	VSSOP	DGS	10	2500	364.0	364.0	27.0

#### **IMPORTANT NOTICE**

Texas Instruments Incorporated (TI) reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete.

TI's published terms of sale for semiconductor products (http://www.ti.com/sc/docs/stdterms.htm) apply to the sale of packaged integrated circuit products that TI has qualified and released to market. Additional terms may apply to the use or sale of other types of TI products and services.

Reproduction of significant portions of TI information in TI data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such reproduced documentation. Information of third parties may be subject to additional restrictions. Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyers and others who are developing systems that incorporate TI products (collectively, "Designers") understand and agree that Designers remain responsible for using their independent analysis, evaluation and judgment in designing their applications and that Designers have full and exclusive responsibility to assure the safety of Designers' applications and compliance of their applications (and of all TI products used in or for Designers' applications) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to their applications, Designer has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any applications that include TI products, Designer will thoroughly test such applications and the functionality of such TI products as used in such applications.

TI's provision of technical, application or other design advice, quality characterization, reliability data or other services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using TI Resources in any way, Designer (individually or, if Designer is acting on behalf of a company, Designer's company) agrees to use any particular TI Resource solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

Designer is authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNER AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

Unless TI has explicitly designated an individual product as meeting the requirements of a particular industry standard (e.g., ISO/TS 16949 and ISO 26262), TI is not responsible for any failure to meet such industry standard requirements.

Where TI specifically promotes products as facilitating functional safety or as compliant with industry functional safety standards, such products are intended to help enable customers to design and create their own applications that meet applicable functional safety standards and requirements. Using products in an application does not by itself establish any safety features in the application. Designers must ensure compliance with safety-related requirements and standards applicable to their applications. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equipment includes, without limitation, all medical devices identified by the U.S. Food and Drug Administration as Class III devices and equivalent classifications outside the U.S.

TI may expressly designate certain products as completing a particular qualification (e.g., Q100, Military Grade, or Enhanced Product). Designers agree that it has the necessary expertise to select the product with the appropriate qualification designation for their applications and that proper product selection is at Designers' own risk. Designers are solely responsible for compliance with all legal and regulatory requirements in connection with such selection.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's noncompliance with the terms and provisions of this Notice.

> Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2018, Texas Instruments Incorporated