

Order

Now



LMV358A SBOS923 – DECEMBER 2017

LMV3xxA Dual Low-Voltage Rail-to-Rail Output Operational Amplifier

Technical

Documents

1 Features

- Rail-to-Rail Output
- Low Input Offset Voltage: ±1 mV
- Unity-Gain Bandwidth: 1 MHz
- Low Broadband Noise: 30 nV/√Hz
- Low Input Bias Current: 10 pA
- Low Quiescent Current: 80 µA/Ch
- Unity-Gain Stable
- Internal RFI and EMI Filter
- Operational at Supply Voltages as Low as 2.5 V
- Easier to Stabilize With Higher Capacitive Load Due to Resistive Open-Loop Output Impedance
- Extended Temperature Range: –40°C to +125°C

2 Applications

- HVAC: Heating, Ventilating, and Air Conditioning
- Large and Small Appliances
- Power Modules
- Motor Control: AC Induction
- Smoke Detectors
- Motion Detectors
- Wearable Devices
- EPOS
- Barcode Scanners
- Personal Electronics
- Active Filters
- Sensor Signal Conditioning
- Low-Side Current Sensing

3 Description

Tools &

Software

The LMV3xxA family includes dual - (LMV358A) lowvoltage (2.5 V to 5.5 V) operational amplifiers (op amps) with rail-to-rail output swing capabilities. These op amps provide a cost-effective solution for spaceconstrained applications, such as large appliances, smoke detectors, and personal electronics, where low-voltage operation and high capacitive-load drive are required. The capacitive-load drive of the LMV3xxA family is 500 pF, and the resistive openloop output impedance makes it easy to stabilize with much higher capacitive loads. These op amps are designed specifically for low-voltage operation (2.5 V to 5.5 V) with performance specifications similar to the LMV3xx devices.

Support &

Community

20

The robust design of the LMV3xxA family simplifies circuit design. The op amps feature unity-gain stability, an integrated RFI and EMI rejection filter, and no-phase reversal in overdrive condition.

The LMV3xxA family is available in industry-standard packages, such as SOIC, MSOP, SOT-23 and TSSOP packages.

PART NUMBER	PACKAGE	BODY SIZE (NOM)			
	SOIC (8)	3.91 mm × 4.90 mm			
LMV358A	WSON (8)	2.00 mm × 2.00 mm			
	VSSOP (8)	3.00 mm × 3.00 mm			

Device Information⁽¹⁾

(1) For all available packages, see the orderable addendum at the end of the data sheet.

Single-Pole, Low-Pass Filter




Table of Contents

1	Feat	tures	1
2	Арр	lications	1
3	Des	cription	1
4		ision History	
5	Pin	Configuration and Functions	3
6	Spe	cifications	4
	6.1	Absolute Maximum Ratings	4
	6.2	ESD Ratings	4
	6.3	Recommended Operating Conditions	4
	6.4	Thermal Information: LMV358A	4
	6.5	Electrical Characteristics	5
	6.6	Typical Characteristics	7
7	Deta	ailed Description	13
	7.1	Overview	13
	7.2	Functional Block Diagram	13
	7.3	Feature Description	14
	7.4	Device Functional Modes	14

8	App	lication and Implementation	15
	8.1	Application Information	15
	8.2	Typical Application	15
9	Pow	er Supply Recommendations	20
	9.1	Input and ESD Protection	20
10	Lay	out	21
	10.1	Layout Guidelines	21
	10.2	Layout Example	21
11	Dev	ice and Documentation Support	22
	11.1	Documentation Support	22
	11.2	Related Links	22
	11.3	Receiving Notification of Documentation Updates	22
	11.4	Community Resources	22
	11.5	Trademarks	22
	11.6	Electrostatic Discharge Caution	22
	11.7	Glossary	22
12	Mec	hanical, Packaging, and Orderable	
	Info	rmation	22


4 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

DATE	REVISION	NOTES
December 2017	*	Initial release.



5 Pin Configuration and Functions



(1) Connect thermal pad to V-

Pin Functions: LMV358A

PIN		I/O	DESCRIPTION	
NAME	NO.	1/0	DESCRIPTION	
–IN A	2	I	Inverting input, channel A	
+IN A	3	I	Noninverting input, channel A	
–IN B	6	I	Inverting input, channel B	
+IN B	5	I	Noninverting input, channel B	
OUT A	1	0	Output, channel A	
OUT B	7	0	Output, channel B	
V–	4	_	Negative (lowest) supply or ground (for single-supply operation)	
V+	8	—	Positive (highest) supply	

6 Specifications

6.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)⁽¹⁾

			MIN	MAX	UNIT
Supply voltage ([V+] -	- [V–])		0	6	V
	Voltage ⁽²⁾	Common-mode	(V–) – 0.5	(V+) + 0.5	V
Signal input pins	voltage -/	Differential		(V+) – (V–) + 0.2	V
	Current ⁽²⁾		-10	10	mA
Output short-circuit ⁽³⁾			Con	tinuous	mA
Operating, T _A			-55	150	°C
Junction, T _J				150	°C
Storage, T _{stg}			-65	150	°C

(1) Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

(2) Input pins are diode-clamped to the power-supply rails. Input signals that may swing more than 0.5 V beyond the supply rails must be current limited to 10 mA or less.

(3) Short-circuit to ground, one amplifier per package.

6.2 ESD Ratings

			VALUE	UNIT
V	Electrostatia discharge	Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 ⁽¹⁾	±2000	M
V _(ESD)	Electrostatic discharge	Charged-device model (CDM), per JEDEC specification JESD22-C101 ⁽²⁾	±1000	V

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

6.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

		MIN	MAX	UNIT
Vs	Supply voltage	2.5	5.5	V
T _A	Specified temperature	-40	125	°C

6.4 Thermal Information: LMV358A

		LMV358A	
	THERMAL METRIC ⁽¹⁾	D (SOIC)	UNIT
		8 PINS	
$R_{ hetaJA}$	Junction-to-ambient thermal resistance	147.4	°C/W
R _{0JC(top)}	Junction-to-case (top) thermal resistance	94.3	°C/W
R_{\thetaJB}	Junction-to-board thermal resistance	89.5	°C/W
ΨJT	Junction-to-top characterization parameter	47.3	°C/W
Ψјв	Junction-to-board characterization parameter	89	°C/W

(1) For more information about traditional and new thermal metrics, see Semiconductor and IC Package Thermal Metrics application report.

6.5 Electrical Characteristics

For $V_S = (V+) - (V-) = 2.5 \text{ V}$ to 5.5 V (±0.9 V to ±2.75 V), $T_A = 25 \text{ °C}$, $R_L = 10 \text{ k}\Omega$ connected to $V_S / 2$, and $V_{CM} = V_{OUT} = V_S / 2$ (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
OFFSET V	/OLTAGE					
V _{os}	Input offset voltage	Vs = 5 V		±1	±4	mV
•OS	input onset voltage	$Vs = 5 V, T_A = -40^{\circ}C \text{ to } 125^{\circ}C$			±5	mV
dV _{OS} /dT	V _{OS} vs temperature	$T_A = -40^{\circ}C$ to $125^{\circ}C$		±1		μV/°C
PSRR	Power-supply rejection ratio	V_{S} = 2.5 to 5.5 V, V_{CM} = (V–)	78	100		dB
INPUT VO	LTAGE RANGE		- F			
V _{CM}	Common-mode voltage range	No phase reversal, rail-to-rail input	(V–) – 0.1		(V+) – 1	V
				86		dB
	Common-mode	$V_{S} = 5.5 \text{ V}, (V-) - 0.1 \text{ V} < V_{CM} < (V+) - 1.4 \text{ V}$ $T_{A} = -40^{\circ}\text{C} \text{ to } 125^{\circ}\text{C}$		95		dB
CMRR	rejection ratio	$V_{S} = 5.5 \text{ V}, (V-) - 0.1 \text{ V} < V_{CM} < (V+) + 0.1 \text{ V}$ $T_{A} = -40^{\circ}\text{C} \text{ to } 125^{\circ}\text{C}$	63	77		dB
		$V_{S} = 2.5 \text{ V}, (V-) - 0.1 \text{ V} < V_{CM} < (V+)+ 0.1 \text{ V}$ $T_{A} = -40^{\circ}\text{C} \text{ to } 125^{\circ}\text{C}$		68		dB
INPUT BIA	AS CURRENT					
I _B	Input bias current	Vs = 5 V		±10		pА
I _{OS}	Input offset current			±3		pA
NOISE						
	Input voltage noise					
En	(peak-to-peak)	f = 0.1 Hz to 10 Hz, Vs = 5 V		5.1		μV_{PP}
e _n	Input voltage noise density	f = 1 kHz, Vs = 5 V		33		nV/√Hz
o _n	input voltage holde density	f = 10 kHz, Vs = 5 V		30		nV/√Hz
i _n	Input current noise density	f = 1 kHz, Vs = 5 V		25		fA/√Hz
INPUT CA	PACITANCE		- F			
C _{ID}	Differential			1.5		pF
CIC	Common-mode			5		pF
OPEN-LO	OP GAIN					
		V_{S} = 5.5 V, (V–) + 0.05 V < V_{O} < (V+) – 0.05 V, R_{L} = 10 $k\Omega$	100	115		dB
A _{OL}	Open-loop voltage gain	V_{S} = 2.5 V, (V–) + 0.04 V < V_{O} < (V+) – 0.04 V, R_{L} = 10 k Ω		98		dB
, OL	opon toop tonago gant	$V_{S} = 2.5 \text{ V}, (V-) + 0.1 \text{ V} < V_{O} < (V+) - 0.1 \text{ V}, R_{L} = 2 \text{ k}\Omega$		112		dB
		$\rm V_S$ = 5.5 V, (V–) + 0.15 V < $\rm V_O$ < (V+) – 0.15 V, $\rm R_L$ = 2 k Ω		128		dB
FREQUEN	ICY RESPONSE					
GBW	Gain-bandwidth product	Vs = 5 V		1		MHz
φm	Phase margin	V _S = 5.5 V, G = 1		76		degrees
SR	Slew rate	Vs = 5 V		1.7		V/µs
ts	Settling time	To 0.1%, $V_S = 5 V$, 2-V Step , G = +1, $C_L = 100 \text{ pF}$		3		μS
•5		To 0.01%, V _S = 5 V, 2-V Step , G = +1, C _L = 100 pF		4		μS
t _{OR}	Overload recovery time	$V_{S} = 5 V, V_{IN} \times gain > V_{S}$		0.9		μS
THD+N	Total harmonic distortion + noise	V_S = 5.5 V, V_{CM} = 2.5 V, V_O = 1 V_{RMS},G = +1, f = 1 kHz, 80 kHz measurement BW		0.005		%
OUTPUT						
Vo	Voltage output swing	$V_{S} = 5.5 \text{ V}, \text{ R}_{L} = 10 \text{ k}\Omega$		20	50	mV
0	from supply rails	$V_{S} = 5.5 \text{ V}, \text{ R}_{L} = 2 \text{ k}\Omega$		40	75	mV
I _{SC}	Short-circuit current	Vs = 5.5 V		±40		mA
Zo	Open-loop output impedance	Vs = 5 V, f = 1 MHz		1200		Ω
POWER S	UPPLY					
Vs	Specified voltage range		2.5 (±1.25)	1	5.5 (±2.75)	V
l _Q	Quiescent current per	$I_0 = 0 \text{ mA}, V_S = 5.5 \text{ V}$		80	125	μA
·u	amplifier	$I_O = 0$ mA, $V_S = 5.5$ V, $T_A = -40^{\circ}$ C to 125° C			150	μA



Electrical Characteristics (continued)


For $V_S = (V+) - (V-) = 2.5$ V to 5.5 V (±0.9 V to ±2.75 V), $T_A = 25$ °C, $R_L = 10$ k Ω connected to V_S / 2, and $V_{CM} = V_{OUT} = V_S$ / 2 (unless otherwise noted)

PARAMETER	TEST CONDITIONS	MIN	ТҮР	MAX	UNIT
Power-on time	$V_{S} = 0 V$ to 5 V, to 90% I_{Q} level		50		μs



6.6 Typical Characteristics


at T_A = 25°C, V+ = 2.75 V, V- = -2.75 V, R_L = 10 k Ω connected to V_S / 2, V_{CM} = V_S / 2, and V_{OUT} = V_S / 2 (unless otherwise noted)



LMV358A SBOS923-DECEMBER 2017


www.ti.com

Typical Characteristics (continued)






Typical Characteristics (continued)




Typical Characteristics (continued)






Typical Characteristics (continued)



Typical Characteristics (continued)

at T_A = 25°C, V+ = 2.75 V, V- = -2.75 V, R_L = 10 k Ω connected to V_S / 2, V_{CM} = V_S / 2, and V_{OUT} = V_S / 2 (unless otherwise noted)






7 Detailed Description

7.1 Overview

The LMV3xxA series is a family of low-power, rail-to-rail output op amps. These devices operate from 2.5 V to 5.5 V, are unity-gain stable, and are designed for a wide range of general-purpose applications. The input common-mode voltage range includes the negative rail and allows the LMV3xxA series to be used in many single-supply applications. Rail-to-rail output swing significantly increases dynamic range, especially in low-supply applications, and makes them suitable for driving sampling analog-to-digital converters (ADCs).

7.2 Functional Block Diagram



Copyright © 2017, Texas Instruments Incorporated



7.3 Feature Description

7.3.1 Operating Voltage

The LMV3xxA series of op amps are ensured for operation from 2.5 V to 5.5 V. In addition, many specifications apply from –40°C to +125°C. Parameters that vary significantly with operating voltages or temperature are shown in the section.

7.3.2 Rail-to-Rail Input

The input common-mode voltage range of the LMV3xxA family extends 100 mV beyond the negative supply rail and within 1 V below the positive rail for the full supply voltage range of 2.5 V to 5.5 V. This performance is achieved with a P-channel differential pair, as shown in the *Functional Block Diagram*. Additionally, a complementary N-channel differential pair has been included in parallel to eliminate issues with phase reversal that are common with previous generations of op amps. However, the N-channel pair is not optimized for operation. TI recommends limiting any voltages applied at the inputs to less than V_{CC}- 1V to ensure that the op amp conforms to the specifications detailed in the *Electrical Characteristics* table.

7.3.3 Rail-to-Rail Output

Designed as a low-power, low-voltage operational amplifier, the LMV3xxA series delivers a robust output drive capability. A class-AB output stage with common-source transistors achieves full rail-to-rail output swing capability. For resistive loads of 10 k Ω , the output swings to within 20 mV of either supply rail, regardless of the applied power-supply voltage. Different load conditions change the ability of the amplifier to swing close to the rails.

7.3.4 Overload Recovery

Overload recovery is defined as the time required for the operational amplifier output to recover from a saturated state to a linear state. The output devices of the operational amplifier enter a saturation region when the output voltage exceeds the rated operating voltage, because of the high input voltage or the high gain. After the device enters the saturation region, the charge carriers in the output devices require time to return to the linear state. After the charge carriers return to the linear state, the device begins to slew at the specified slew rate. Therefore, the propagation delay (in case of an overload condition) is the sum of the overload recovery time and the slew time. The overload recovery time for the LMV3xxA series is approximately 850 ns.

7.4 Device Functional Modes

The LMV3xxA family has a single functional mode. The devices are powered on as long as the power-supply voltage is between and 5.5 V (\pm 2.75 V).



8 Application and Implementation

NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.


8.1 Application Information

The LMV3xxA is a family of low-power, rail-to-rail output operational amplifiers specifically designed for portable applications. The devices operate from 2.5 V to 5.5 V, are unity-gain stable, and are suitable for a wide range of general-purpose applications. The class AB output stage is capable of driving less than or equal to $10-k\Omega$ loads connected to any point between V+ and V–. The input common-mode voltage range includes the negative rail, and allows the LMV3xxA to be used in many single-supply applications.

8.2 Typical Application

8.2.1 LMV3xxA Low-Side, Current Sensing Application

Figure 32 shows the LMV3xxA configured in a low-side current sensing application.



Copyright © 2017, Texas Instruments Incorporated

Figure 32. LMV3xxA in a Low-Side, Current-Sensing Application

0.6

0.8

1

Copyright © 2017, Texas Instruments Incorporated

Typical Application (continued)

8.2.1.1 Design Requirements

The design requirements for this design are:

- Load current: 0 A to 1 A
- Output voltage: 4.9 V
- Maximum shunt voltage: 100 mV

8.2.1.2 Detailed Design Procedure

The transfer function of the circuit in is given in Equation 1:

5

4

Cutput (V) 5

1

0

0

0.2

$$V_{OUT} = I_{LOAD} \times R_{SHUNT} \times Gain$$

The load current ($_{ILOAD}$) produces a voltage drop across the shunt resistor (R_{SHUNT}). The load current is set from 0 A to 1 A. To keep the shunt voltage below 100 mV at maximum load current, the largest shunt resistor is shown using Equation 2:

$$R_{SHUNT} = \frac{V_{SHUNT} MAX}{I_{LOAD} MAX} = \frac{100 \text{mV}}{1\text{A}} = 100 \text{m}\Omega$$
(2)

Using Equation 2, R_{SHUNT} is calculated to be 100 m Ω . The voltage drop produced by I_{LOAD} and R_{SHUNT} is amplified by the LMV3xxA to produce an output voltage of approximately 0 V to 4.9 V. The gain needed by the LMV3xxA to produce the necessary output voltage is calculated using Equation 3:

$$Gain = \frac{\left(V_{OUT_MAX} - V_{OUT_MIN}\right)}{\left(V_{IN_MAX} - V_{IN_MIN}\right)}$$
(3)

Using Equation 3, the required gain is calculated to be 49 V/V, which is set with resistors RF and RG. Equation 4 sizes the resistors RF and RG, to set the gain of the LMV3xxA to 49 V/V.

$$Gain = 1 + \frac{(R_F)}{(R_G)}$$
(4)

Selecting RF as 57.6 k Ω and RG as 1.2 k Ω provides a combination that equals 49 V/V. Figure 33 shows the measured transfer function of the circuit shown in Figure 32.

8.2.1.3 Application Curve



I_{LOAD} (A)

0.4



(1)

NSTRUMENTS

EXAS



Typical Application (continued)

8.2.2 Single-Supply Photodiode Amplifier

Photodiodes are used in many applications to convert light signals to electrical signals. The current through the photodiode is proportional to the light energy applied to the current, and is commonly in the range of a few hundred picoamps to a few tens of microamps. An amplifier in a transimpedance configuration is typically used to convert the low-level photodiode current to a voltage signal for processing in an MCU. The circuit shown in Figure 34 is an example single-supply photodiode amplifier circuit using the LMV358A.




Figure 34. Single-Supply Photodiode Amplifier Circuit

8.2.2.1 Design Requirements

Supply Voltage: 3.3 V Input: 0 µA to 10 µA

8.2.2.2 Detailed Design Procedure

Typical Application (continued)

The design requirements for this design are:

The transfer function between the output voltage, V_{OUT} , the input current, I_{IN} , and the reference voltage, V_{REF} , is defined in Equation 5.

$$V_{OUT} = I_{IN} \times R_F + V_{REF}$$

Where

$$V_{\mathsf{REF}} = V_{+} \times \left(\frac{\mathsf{R}_{1} \times \mathsf{R}_{2}}{\mathsf{R}_{1} + \mathsf{R}_{2}}\right) \tag{6}$$

Set VREF to 100mV to meet the minimum output voltage level by setting R1 and R2 to meet the required ratio calculated in Equation 7.

$$\frac{V_{\mathsf{REF}}}{V_{+}} = \frac{0.1\,\mathrm{V}}{3.3\,\mathrm{V}} = 0.0303\tag{7}$$

The closest resistor ratio to meet this ratio sets R1 to 11.5 k Ω and R2 to 357 $\Omega.$

The required feedback resistance can be calculated based on the input current and desired output voltage.

$$R_{F} = \frac{V_{OUT} - V_{REF}}{I_{IN}} = \frac{3.2 \ V - 0.1 \ V}{10 \ \mu A} = 310 \frac{kV}{A} \approx 309 \ k\Omega$$
(8)

Calculate the value for the feedback capacitor based RF and the desired -3-dB bandwidth, (f-3dB) using Equation 9.

$$C_{\mathsf{F}} = \frac{1}{2 \times \pi \times \mathsf{R}_{\mathsf{F}} \times \mathsf{f}_{-3\mathsf{dB}}} = \frac{1}{2 \times \pi \times 309 \text{ k}\Omega \times 50 \text{ kHz}} = 10.3 \text{ pF} \approx 10 \text{ pF}$$
(9)

The minimum op amp bandwidth required for this application is based on the value of RF, CF and the capacitance on the IN– pin of the LMV358A which is equal to the sum of the photodiode shunt capacitance, CPD, the common-mode input capacitance CCM and the differential input capacitance CD as shown in Equation 10.

$$C_{IN} = C_{PD} + C_{CM} + C_{D} = 47 \text{ pF} + 5 \text{ pF} + 1 \text{ pF} = 53 \text{ pF}$$
(10)

The minimum op amp bandwidth is calculated in Equation 11.

$$f_{=BGW} \ge \frac{C_{IN} + C_F}{2 \times \pi \times R_F \times C_F^2} \ge 324 \text{ kHz}$$
(11)

The 1-MHz bandwidth of the LMV3xxA meets the minimum bandwidth requirement and remains stable in this application configuration.

(6)


(5)



Typical Application (continued)

8.2.2.3 Application Curves

The measured current-to-voltage transfer function for photodiode amplifier circuit is shown in Figure 35. The measured DC performance of the photodiode amplifier circuit is shown in Figure 36.





9 Power Supply Recommendations

The LMV3xxA series is specified for operation from 2.5 V to 5.5 V (\pm 1.25 V to \pm 2.75 V); many specifications apply from –40°C to +125°C. The section presents parameters that may exhibit significant variance with regard to operating voltage or temperature.

CAUTION Supply voltages larger than 6 V may permanently damage the device; see the table.

Place 0.1-µF bypass capacitors close to the power-supply pins to reduce coupling errors from noisy or highimpedance power supplies. For more detailed information on bypass capacitor placement, see the *Layout Guidelines* section.

9.1 Input and ESD Protection

The LMV3xxA series incorporates internal ESD protection circuits on all pins. For input and output pins, this protection primarily consists of current-steering diodes connected between the input and power-supply pins. These ESD protection diodes provide in-circuit, input overdrive protection, as long as the current is limited to 10-mA, as stated in the table. Figure 37 shows how a series input resistor can be added to the driven input to limit the input current. The added resistor contributes thermal noise at the amplifier input and the value must be kept to a minimum in noise-sensitive applications.




Figure 37. Input Current Protection



10 Layout

10.1 Layout Guidelines

For best operational performance of the device, use good printed circuit board (PCB) layout practices, including:

- Noise can propagate into analog circuitry through the power pins of the circuit as a whole and of op amp itself. Bypass capacitors are used to reduce the coupled noise by providing low-impedance power sources local to the analog circuitry.
 - Connect low-ESR, 0.1-µF ceramic bypass capacitors between each supply pin and ground, placed as close to the device as possible. A single bypass capacitor from V+ to ground is applicable for singlesupply applications.
- Separate grounding for analog and digital portions of circuitry is one of the simplest and most-effective methods of noise suppression. One or more layers on multilayer PCBs are usually devoted to ground planes. A ground plane helps distribute heat and reduces electromagnetic interference (EMI) noise pickup. Ensure to physically separate digital and analog grounds, paying attention to the flow of the ground current. For more detailed information, see *Circuit Board Layout Techniques*.
- In order to reduce parasitic coupling, run the input traces as far away from the supply or output traces as possible. If these traces cannot be kept separate, crossing the sensitive trace perpendicular is much better as opposed to in parallel with the noisy trace.
- Place the external components as close to the device as possible, as shown in Figure 39. Keeping R_F and R_G close to the inverting input minimizes parasitic capacitance.
- Keep the length of input traces as short as possible. Remember that the input traces are the most sensitive part of the circuit.
- Consider a driven, low-impedance guard ring around the critical traces. A guard ring may significantly reduce leakage currents from nearby traces that are at different potentials.
- Cleaning the PCB following board assembly is recommended for best performance.
- Any precision integrated circuit can experience performance shifts resulting from moisture ingress into the plastic package. Following any aqueous PCB cleaning process, baking the PCB assembly is recommended to remove moisture introduced into the device packaging during the cleaning process. A low-temperature, post-cleaning bake at 85°C for 30 minutes is sufficient for most circumstances.

10.2 Layout Example






Figure 38. Schematic Representation for Figure 39





TEXAS INSTRUMENTS

www.ti.com

11 Device and Documentation Support

11.1 Documentation Support

11.1.1 Related Documentation

For related documentation, see the following:

• Texas Instruments, EMI Rejection Ratio of Operational Amplifiers application report

11.2 Related Links

The table below lists quick access links. Categories include technical documents, support and community resources, tools and software, and quick access to order now.

Table 1. Related Links

PARTS	PRODUCT FOLDER	ORDER NOW	TECHNICAL DOCUMENTS	TOOLS & SOFTWARE	SUPPORT & COMMUNITY
LMV358A	Click here	Click here	Click here	Click here	Click here

11.3 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. In the upper right corner, click on *Alert me* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

11.4 Community Resources

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

TI E2E[™] Online Community *TI's Engineer-to-Engineer (E2E) Community.* Created to foster collaboration among engineers. At e2e.ti.com, you can ask questions, share knowledge, explore ideas and help solve problems with fellow engineers.

Design Support TI's Design Support Quickly find helpful E2E forums along with design support tools and contact information for technical support.

11.5 Trademarks

E2E is a trademark of Texas Instruments. All other trademarks are the property of their respective owners.

11.6 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

11.7 Glossary

SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.

12 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.



22-Dec-2017

PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package	Pins	Package	Eco Plan	Lead/Ball Finish	MSL Peak Temp	Op Temp (°C)	Device Marking	Samples
	(1)		Drawing		Qty	(2)	(6)	(3)		(4/5)	
LMV358AIDR	ACTIVE	SOIC	D	8	2500	Green (RoHS & no Sb/Br)	CU SN	Level-2-260C-1 YEAR	-40 to 125	MV358A	Samples

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

⁽²⁾ RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

(6) Lead/Ball Finish - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

PACKAGE MATERIALS INFORMATION

www.ti.com


Texas Instruments

TAPE AND REEL INFORMATION





QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
LMV358AIDR	SOIC	D	8	2500	330.0	15.4	6.4	5.2	2.1	8.0	12.0	Q1

TEXAS INSTRUMENTS

www.ti.com

PACKAGE MATERIALS INFORMATION

21-Dec-2017



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
LMV358AIDR	SOIC	D	8	2500	336.6	336.6	41.3

D (R-PDSO-G8)

PLASTIC SMALL OUTLINE



NOTES: A. All linear dimensions are in inches (millimeters).

- B. This drawing is subject to change without notice.
- Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.006 (0,15) each side.
- Body width does not include interlead flash. Interlead flash shall not exceed 0.017 (0,43) each side.
- E. Reference JEDEC MS-012 variation AA.



IMPORTANT NOTICE

Texas Instruments Incorporated (TI) reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete.

TI's published terms of sale for semiconductor products (http://www.ti.com/sc/docs/stdterms.htm) apply to the sale of packaged integrated circuit products that TI has qualified and released to market. Additional terms may apply to the use or sale of other types of TI products and services.

Reproduction of significant portions of TI information in TI data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such reproduced documentation. Information of third parties may be subject to additional restrictions. Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyers and others who are developing systems that incorporate TI products (collectively, "Designers") understand and agree that Designers remain responsible for using their independent analysis, evaluation and judgment in designing their applications and that Designers have full and exclusive responsibility to assure the safety of Designers' applications and compliance of their applications (and of all TI products used in or for Designers' applications) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to their applications, Designer has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any applications that include TI products, Designer will thoroughly test such applications and the functionality of such TI products as used in such applications.

TI's provision of technical, application or other design advice, quality characterization, reliability data or other services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using TI Resources in any way, Designer (individually or, if Designer is acting on behalf of a company, Designer's company) agrees to use any particular TI Resource solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

Designer is authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNER AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

Unless TI has explicitly designated an individual product as meeting the requirements of a particular industry standard (e.g., ISO/TS 16949 and ISO 26262), TI is not responsible for any failure to meet such industry standard requirements.

Where TI specifically promotes products as facilitating functional safety or as compliant with industry functional safety standards, such products are intended to help enable customers to design and create their own applications that meet applicable functional safety standards and requirements. Using products in an application does not by itself establish any safety features in the application. Designers must ensure compliance with safety-related requirements and standards applicable to their applications. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equipment includes, without limitation, all medical devices identified by the U.S. Food and Drug Administration as Class III devices and equivalent classifications outside the U.S.

TI may expressly designate certain products as completing a particular qualification (e.g., Q100, Military Grade, or Enhanced Product). Designers agree that it has the necessary expertise to select the product with the appropriate qualification designation for their applications and that proper product selection is at Designers' own risk. Designers are solely responsible for compliance with all legal and regulatory requirements in connection with such selection.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's noncompliance with the terms and provisions of this Notice.

> Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated