













TPS62065, TPS62067

SLVS833D - MARCH 2010-REVISED NOVEMBER 2016

# TPS6206x 3-MHz, 2-A, Step-Down Converter in 2-mm × 2-mm SON Package

#### 1 Features

- 3-MHz Switching Frequency
- V<sub>IN</sub> Range from 2.9 V to 6 V
- Up to 97% Efficiency
- Power Save Mode / 3-MHz Fixed PWM Mode
- Power Good Output
- Output Voltage Accuracy in PWM Mode ±1.5%
- Output Capacitor Discharge Function
- Typical 18 µA Quiescent Current
- 100% Duty Cycle for Lowest Dropout
- Voltage Positioning
- · Clock Dithering
- -40°C to 125°C Operating Junction Temperature
- · Supports Maximum 1-mm Height Solutions
- Available in a 2 mm x 2 mm x 0.75 mm WSON

# 2 Applications

- · Point of Load (POL)
- Notebooks, Pocket PCs
- · Portable Media Players
- DSP Supply

## 3 Description

The TPS6206x is a family of highly efficient synchronous step down DC/DC converters. They provide up to 2-A output current.

With an input voltage range of 2.9 V to 6 V, the device is a perfect fit for power conversion from a 5-V or 3.3-V system supply rail. The TPS6206x operates at 3-MHz fixed frequency and enters power save mode operation at light load currents to maintain high efficiency over the entire load current range. The power save mode is optimized for low output voltage ripple. For low noise applications, TPS62065 can be forced into fixed frequency PWM mode by pulling the MODE pin high. TPS62067 provides an open drain power good output.

In the shutdown mode, the current consumption is reduced to less than 1  $\mu A$  and an internal circuit discharges the output capacitor.

TPS6206x family is optimized for operation with a tiny 1  $\mu$ H inductor and a small 10- $\mu$ F output capacitor to achieve smallest solution size and high regulation performance.


It is available in a small 2-mm  $\times$  2-mm  $\times$  0.75-mm 8-pin WSON package.

## **Device Information**(1)


PART NUMBER	PACKAGE	BODY SIZE (NOM)
TPS62065 TPS62067	WSON (8)	2.00 mm × 2.00 mm

(1) For all available packages, see the orderable addendum at the end of the data sheet.

# **Typical Application Schematic**



#### **Efficiency vs Load Current**





# **Table of Contents**

1	Features 1	9 Application and Implementation	12
2	Applications 1	9.1 Application Information	12
3	Description 1	9.2 Typical Application	12
4	Revision History2	9.3 System Example	18
5	Device Comparison Table3	10 Power Supply Recommendations	19
6	Pin Configuration and Functions3	11 Layout	19
7	Specifications4	11.1 Layout Guidelines	19
•	7.1 Absolute Maximum Ratings	11.2 Layout Example	19
	7.2 ESD Ratings	12 Device and Documentation Support	20
	7.3 Recommended Operating Conditions	12.1 Device Support	20
	7.4 Thermal Information	12.2 Related Links	20
	7.5 Electrical Characteristics	12.3 Receiving Notification of Documentation L	Jpdates 20
	7.6 Typical Characteristics	12.4 Community Resources	20
8	Detailed Description 7	12.5 Trademarks	20
U	8.1 Overview	12.6 Electrostatic Discharge Caution	20
	8.2 Functional Block Diagram	12.7 Glossary	20
	8.3 Feature Description 8	13 Mechanical, Packaging, and Orderable Information	20
	8.4 Device Functional Modes9	In ormation	20

# 4 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

CI	nanges from Revision C (September 2015) to Revision D	age
•	Changed the conditions statement for the <i>Electrical Characteristics</i>	5
•	Added Note 1 to the Test conditions of I <sub>SD</sub> , I <sub>IN</sub> , and I <sub>LKG</sub> in the <i>Electrical Characteristics</i>	5
<u>•</u>	Changed temperature values From: T <sub>A</sub> To: T <sub>J</sub> in Figure 1 and Figure 3	6
CI	nanges from Revision B (November 2013) to Revision C	age
•	Added Pin Configuration and Functions section, ESD Ratings table, Feature Description section, Device Functional Modes, Application and Implementation section, Power Supply Recommendations section, Layout section, Device and Documentation Support section, and Mechanical, Packaging, and Orderable Information section	1
CI	nanges from Revision A (May 2010) to Revision B	age
•	Added Thermal Information table and deleted Dissipation Ratings table	5
CI	nanges from Original (March 2010) to Revision A Pa	age
•	Changed V <sub>IN</sub> Range from "3V to 6V" to "2.9V to 6V", throughout	1
•	Added equation to "Output Voltage Setting" section.	. 12
•	Changed equation for calculating f <sub>z.</sub>	12




# Device Comparison Table<sup>(1)</sup>

PART NUMBER	OUTPUT VOLTAGE <sup>(1)</sup>	FUN	CTION	MAXIMUM OUTPUT
PART NUMBER	OUTPUT VOLTAGE	MODE	POWER GOOD (PG)	CURRENT
TPS62065	Adjustable	Selectable	No	2 A
TPS62067	Adjustable	Auto PWM/PFM	Yes	2 A

- For the most current package and ordering information, see the Mechanical, Packaging, and Orderable Information at the end of this document, or see the TI website at www.ti.com. Contact TI for other fixed output voltage options

# 6 Pin Configuration and Functions



## **Pin Functions**

PIN		1/0	DESCRIPTION	
NAME	NO.	1/0	DESCRIPTION	
AGND	3	I	Analog GND supply pin for the control circuit.	
AVIN	7	I	Analog $V_{\text{IN}}$ power supply for the control circuit. Must be connected to PVIN and input capacitor.	
EN	5	I	This is the enable pin of the device. Pulling this pin to low forces the device into shutdown mode. Pulling this pin to high enables the device. This pin must be terminated	
FB	4	I	Feedback pin for the internal regulation loop. Connect the external resistor divider to this pin. In case of fixed output voltage option, connect this pin directly to the output capacitor	
MODE 6		I	<b>MODE</b> : MODE pin = High forces the device to operate in fixed frequency PWM mode. MODE pin = Low enables the power save mode with automatic transition from PFM mode to fixed frequency PWM mode. This pin must be terminated.	
PG		Open- Drain	<b>PG</b> : Power Good Open-Drain output. Connect an external pullup resistor to a rail which is below or equal AV <sub>IN</sub> .	
PGND	1	PWR	GND supply pin for the output stage.	
PowerPAD™	_	_	For good thermal performance, this PAD must be soldered to the land pattern on the PCB. This PAD should be used as device GND.	
PVIN	8	PWR	V <sub>IN</sub> power supply pin for the output stage.	
sw	2	0	This is the switch pin and is connected to the internal MOSFET switches. Connect the external inductor between this terminal and the output capacitor.	



## 7 Specifications

#### 7.1 Absolute Maximum Ratings

Over operating free-air temperature range (unless otherwise noted) (1)

		MIN	MAX	UNIT
	AVIN, PVIN	-0.3	7	
Voltage <sup>(2)</sup>	EN, MODE, PG, FB	-0.3	$V_{IN} + 0.3 < 7$	V
	SW	-0.3	7	
Current (sink)	into PG		1	mA
Current (source)	Peak output	Intern	ally limited	Α
Tomporeture	T <sub>J</sub>	-40	125	°C
Temperature	T <sub>stg</sub>	-65	150	°C

<sup>(1)</sup> Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

(2) All voltage values are with respect to network ground terminal.

## 7.2 ESD Ratings

			VALUE	UNIT
		Human body model (HBM), per ANSI/ESDA/JEDEC JS-001 (1)	±2000	
$V_{(ESD)}$	Electrostatic discharge	Charged-device model (CDM), per JEDEC specification JESD22-C101 (2)	±1000	V

<sup>(1)</sup> JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

## 7.3 Recommended Operating Conditions

	orimionary operaning community				
		MIN	NOM	MAX	UNIT
AV <sub>IN</sub> , PV <sub>IN</sub>	Supply voltage	2.9		6	V
	Output current capability			2000	mA
	Output voltage range for adjustable voltage	0.8		$V_{IN}$	V
L	Effective inductance	0.7	1	1.6	μΗ
C <sub>OUT</sub>	Effective output capacitance	4.5	10	22	μF
T <sub>J</sub>	Operating junction temperature	-40		125	°C

#### 7.4 Thermal Information

	40	TPS62065 TPS62067	
	THERMAL METRIC <sup>(1)</sup>	DSG (WSON)	UNIT
		8 PINS	
$R_{\theta JA}$	Junction-to-ambient thermal resistance	65.3	°C/W
$R_{\theta JC(top)}$	Junction-to-case (top) thermal resistance	74.2	°C/W
$R_{\theta JB}$	Junction-to-board thermal resistance	35.4	°C/W
ΨЈТ	Junction-to-top characterization parameter	2.2	°C/W
ΨЈВ	Junction-to-board characterization parameter	36	°C/W
$R_{\theta JC(bot)}$	Junction-to-case (bottom) thermal resistance	12.8	°C/W

 For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report.

<sup>(2)</sup> JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.



#### 7.5 Electrical Characteristics


 $T_J$  = -40°C to 125°C, typical values are at  $T_A$  = 25°C. Unless otherwise noted, specifications apply for condition  $V_{IN}$  = EN = 3.6 V. External components  $C_{IN}$  = 10  $\mu$ F 0603,  $C_{OUT}$  = 10  $\mu$ F 0603, L = 1  $\mu$ H, see the parameter measurement information.

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
SUPPLY					<u> </u>	
V <sub>IN</sub>	Input voltage range		2.9		6	V
I <sub>Q</sub>	Operating quiescent current	I <sub>OUT</sub> = 0 mA, device operating in PFM mode and device not switching		18		μА
I <sub>SD</sub>	Shutdown current	EN = GND, current into AVIN and PVIN <sup>(1)</sup>		0.1	1	μА
V	Lindon coltage leakeut threshold	Falling	1.73	1.78	1.83	V
$V_{UVLO}$	Undervoltage lockout threshold	Rising	1.9	1.95	1.99	V
ENABLE, M	ODE					
$V_{IH}$	High level input voltage	$2.9 \text{ V} \le \text{V}_{IN} \le 6 \text{ V}$	1		6	V
$V_{IL}$	Low level input voltage	2.9 V ≤ V <sub>IN</sub> ≤ 6 V	0		0.4	V
I <sub>IN</sub>	Input bias current	EN, mode tied to GND or AVIN <sup>(1)</sup>		0.01	1	μΑ
POWER GO	OD OPEN-DRAIN OUTPUT					
	Devices and the sale of values	Rising feedback voltage	93%	95%	98%	
$V_{THPG}$	Power good threshold voltage	Falling feedback voltage	87%	90%	92%	
V <sub>OL</sub>	Output low voltage	I <sub>OUT</sub> = -1mA; must be limited by external pullup resistor <sup>(1)</sup>			0.3	V
$V_{H}$	Output high voltage	Voltage applied to PG pin through external pullup resistor			$V_{\text{IN}}$	V
I <sub>LKG</sub>	Leakage current into PG pin	$V_{(PG)} = 3.6V^{(1)}$			100	nA
t <sub>PGDL</sub>	Internal power good delay time			5		μs
POWER SW	ITCH				, , , , , , , , , , , , , , , , , , ,	
<u></u>	High-side MOSFET on-resistance	$V_{IN} = 3.6 \text{ V}^{(1)}$		120	180	
R <sub>DS(on)</sub>		$V_{IN} = 5 V^{(1)}$		95	150	mΩ
_	Low-side MOSFET on-resistance	$V_{IN} = 3.6 V^{(1)}$		90	130	
R <sub>DS(on)</sub>		V <sub>IN</sub> = 5 V <sup>(1)</sup>		75	100	mΩ
I <sub>LIMF</sub>	Forward current limit MOSFET high-side and low-side	2.9 V ≤ V <sub>IN</sub> ≤ 6 V	2300	2750	3300	mA
_	Thermal shutdown	Increasing junction temperature		150		
T <sub>SD</sub>	Thermal shutdown hysteresis	Decreasing junction temperature		10		°C
OSCILLATO	DR .					
f <sub>SW</sub>	Oscillator frequency	2.9 V ≤ V <sub>IN</sub> ≤ 6 V	2.6	3	3.4	MHz
OUTPUT						
V <sub>ref</sub>	Reference voltage			600		mV
V <sub>FB(PWM)</sub>	Feedback voltage PWM mode	PWM operation, MODE = $V_{IN}$ , 2.9 V $\leq$ V <sub>IN</sub> $\leq$ 6 V, 0 mA load	-1.5%	0%	1.5%	
V <sub>FB(PFM)</sub>	Feedback voltage PFM mode, voltage positioning	device in PFM mode, voltage positioning active <sup>(2)</sup>		1%		
	Load regulation			-0.5		%/A
$V_{FB}$	Line regulation			0		%/V
R <sub>(Discharge)</sub>	Internal discharge resistor	Activated with EN = GND, 2.9 V $\leq$ V <sub>IN</sub> $\leq$ 6 V, 0.8 $\leq$ V <sub>OUT</sub> $\leq$ 3.6 V	75	200	1450	Ω
t <sub>START</sub>	Start-up time	Time from active EN to reach 95% of V <sub>OUT</sub>		500		μS

 <sup>(1)</sup> Maximum value applies for T<sub>J</sub> = 85°C
 (2) In PFM mode, the internal reference voltage is set to typ. 1.01 x V<sub>ref</sub>. See the parameter measurement information.

# TEXAS INSTRUMENTS

## 7.6 Typical Characteristics



Submit Documentation Feedback

Copyright © 2010–2016, Texas Instruments Incorporated



## 8 Detailed Description


#### 8.1 Overview

The TPS6206x step down converter operates with typically 3-MHz fixed frequency pulse width modulation (PWM) at moderate to heavy load currents. At light load currents the converter can automatically enter power save mode and operates then in pulse frequency modulation (PFM) mode.

During PWM operation the converter use a unique fast response voltage mode controller scheme with input voltage feed-forward to achieve good line and load regulation allowing the use of small ceramic input and output capacitors. At the beginning of each clock cycle initiated by the clock signal, the high-side MOSFET switch is turned on. The current flows now from the input capacitor through the high-side MOSFET switch through the inductor to the output capacitor and load. During this phase, the current ramps up until the PWM comparator trips and the control logic will turn off the switch. The current limit comparator will also turn off the switch in case the current limit of the high-side MOSFET switch is exceeded. After a dead time preventing shoot through current, the low-side MOSFET rectifier is turned on and the inductor current ramps down. The current flows now from the inductor to the output capacitor and to the load. It returns back to the inductor through the low-side MOSFET rectifier.

The next cycle will be initiated by the clock signal again turning off the low-side MOSFET rectifier and turning on the high-side MOSFET switch.

#### 8.2 Functional Block Diagram



<sup>\*</sup> Function depends on device option

Submit Documentation Feedback



#### 8.3 Feature Description

#### 8.3.1 Mode Selection (TPS62065)

The MODE pin allows mode selection between forced PWM mode and power save mode.

Connecting this pin to GND enables the power save mode with automatic transition between PWM and PFM mode. Pulling the MODE pin high forces the converter to operate in fixed frequency PWM mode even at light load currents. This allows simple filtering of the switching frequency for noise sensitive applications. In this mode, the efficiency is lower compared to the power save mode during light loads.

The condition of the MODE pin can be changed during operation and allows efficient power management by adjusting the operation mode of the converter to the specific system requirements.

In device options where the MODE pin is replaced with power good output, the power save mode is enabled per default.

#### 8.3.2 Power Good Output (TPS62067)

This function is available in the TPS62067. The power good output is an open-drain output and requires an external pullup resistor. The circuit is active once the device is enabled and AVIN is above the undervoltage lockout threshold  $V_{UVLO}$ . It is driven by an internal comparator connected to the FB voltage. The PG output provides a high level once the feedback voltage exceeds typically 95% of its nominal value. The PG output is driven to low level once the feedback voltage falls below typically 90% of its nominal value. The PG output is activated with an internal delay of 5  $\mu$ s.

The PG open-drain output transistor is turned on immediately with EN = Low level and pulls the output low. The external pullup resistor can be connected to any voltage rail lower or equal the voltage applied to AVIN of the device. The value of the pullup resistor must be carefully selected to limit the current into the PG pin to maximum 1 mA. The external pullup resistor can be connected to VOUT or another voltage rail which does not exceed the  $V_{IN}$  level. The current flowing through the pullup resistor impacts the current consumption of the application circuit in shutdown mode.

The shutdown current of the device does not include the current through the external pullup and internal opendrain stage. The PG signal can be used for sequencing various converters or to reset a microcontroller.




Figure 7. Power Good Output Pg

#### 8.3.3 **Enable**

The device is enabled by setting EN pin to high. At first, the internal reference is activated and the internal analog circuits are settled. Afterwards, the soft start is activated and the output voltage is ramped up. The output voltages reaches 95% of its nominal value within  $t_{START}$  of typically 500  $\mu$ s after the device has been enabled. The EN input can be used to control power sequencing in a system with various DC/DC converters. The EN pin can be connected to the output of another converter, to drive the EN pin high and getting a sequencing of supply rails. With EN = GND, the device enters shutdown mode. In this mode, all circuits are disabled and the SW pin is connected to PGND through an internal resistor to discharge the output.



#### Feature Description (continued)

#### 8.3.4 Clock Dithering

To reduce the noise level of switch frequency harmonics in the higher RF bands, the TPS6206x family has a built-in clock-dithering circuit. The oscillator frequency is slightly modulated with a sub clock causing a clock dither of typically 6 ns.

#### 8.3.5 Undervoltage Lockout

The undervoltage lockout circuit prevents the device from malfunctioning at low input voltages and from excessive discharge of the battery. It disables the output stage of the converter once the falling V<sub>IN</sub> trips the undervoltage lockout threshold  $V_{UVLO}$ . The undervoltage lockout threshold  $V_{UVLO}$  for falling  $V_{IN}$  is typically 1.78 V. The device starts operation once the rising V<sub>IN</sub> trips undervoltage lockout threshold V<sub>UVLO</sub> again at typically 1.95

#### 8.3.6 Thermal Shutdown

As soon as the junction temperature, T<sub>J</sub>, exceeds 150°C (typical) the device goes into thermal shutdown. In this mode, the high-side and low-side MOSFETs are turned off. The device continues its operation with a soft start once the junction temperature falls below the thermal shutdown hysteresis.

#### 8.4 Device Functional Modes

#### 8.4.1 Soft Start

The TPS6206x has an internal soft start circuit that controls the ramp up of the output voltage. Once the converter is enabled and the input voltage is above the undervoltage lockout threshold V<sub>UVI O</sub> the output voltage ramps up from 5% to 95% of its nominal value within  $t_{Ramp}$  of typically 250  $\mu s$ .

This limits the inrush current in the converter during start-up and prevents possible input voltage drops when a battery or high impedance power source is used.

During soft start, the switch current limit is reduced to 1/3 of its nominal value I<sub>LIMF</sub> until the output voltage reaches 1/3 of its nominal value. Once the output voltage trips this threshold, the device operates with its nominal current limit I<sub>LIMF</sub>.

#### 8.4.2 Power Save Mode

Copyright © 2010-2016, Texas Instruments Incorporated

At TPS62065 pulling the MODE pin low enables power save mode. In TPS62067 power save mode is enabled per default. If the load current decreases, the converter enters power save mode operation automatically. During power save mode the converter skips switching and operates with reduced frequency in PFM mode with a minimum guiescent current to maintain high efficiency. The converter positions the output voltage typically +1% above the nominal output voltage. This voltage positioning feature minimizes voltage drops caused by a sudden load step.

The transition from PWM mode to PFM mode occurs once the inductor current in the low-side MOSFET switch becomes zero, which indicates discontinuous conduction mode.

During the power save mode the output voltage is monitored with a PFM comparator. As the output voltage falls below the PFM comparator threshold of V<sub>OUTnominal</sub> +1%, the device starts a PFM current pulse. For this the highside MOSFET switch will turn on and the inductor current ramps up. After the on-time expires the switch will be turned off and the low-side MOSFET switch will be turned on until the inductor current becomes zero.

The converter effectively delivers a current to the output capacitor and the load. If the load is below the delivered current the output voltage will rise. If the output voltage is equal or higher than the PFM comparator threshold, the device stops switching and enters a sleep mode with typically 18 µA current consumption.

In case the output voltage is still below the PFM comparator threshold, further PFM current pulses will be generated until the PFM comparator threshold is reached. The converter starts switching again once the output voltage drops below the PFM comparator threshold due to the load current.

The PFM mode is exited and PWM mode entered in case the output current can no longer be supported in PFM mode.

(1)

#### **Device Functional Modes (continued)**

#### 8.4.3 Dynamic Voltage Positioning

This feature reduces the voltage undershoots and overshoots at load steps from light to heavy load and vice versa. It is active in power save mode and regulates the output voltage 1% higher than the nominal value. This provides more headroom for both the voltage drop at a load step, and the voltage increase at a load throw-off.




Figure 8. Power Save Mode Operation with Automatic Mode Transition

#### 8.4.4 100% Duty Cycle Low Dropout Operation

The device starts to enter 100% duty cycle mode as the input voltage comes close to the nominal output voltage. To maintain the output voltage, the high-side MOSFET switch is turned on 100% for one or more cycles.

With further decreasing  $V_{IN}$  the high-side MOSFET switch is turned on completely. In this case the converter offers a low input-to-output voltage difference. This is particularly useful in battery-powered applications to achieve longest operation time by taking full advantage of the whole battery voltage range.

The minimum input voltage to maintain regulation depends on the load current and output voltage, and can be calculated as:

 $V_{IN}min = V_{O}max + I_{O}max \times (R_{DS(on)}max + R_{L})$ 

#### where

- I<sub>O</sub>max = maximum output current
- R<sub>DS(on)</sub>max = maximum P-channel switch R<sub>DS(on)</sub>
- R<sub>L</sub> = DC resistance of the inductor
- V<sub>O</sub>max = nominal output voltage plus maximum output voltage tolerance

#### 8.4.5 Internal Current Limit and Fold-Back Current Limit for Short Circuit Protection

During normal operation the high-side and low-side MOSFET switches are protected by its current limits  $I_{LIMF}$ . Once the high-side MOSFET switch reaches its current limit, it is turned off and the low-side MOSFET switch is turned on. The high-side MOSFET switch can only turn on again, once the current in the low-side MOSFET switch decreases below its current limit  $I_{LIMF}$ . The device is capable to provide peak inductor currents up to its internal current limit  $I_{LIMF}$ .

As soon as the switch current limits are hit and the output voltage falls below 1/3 of the nominal output voltage due to overload or short circuit condition, the foldback current limit is enabled. In this case the switch current limit is reduced to 1/3 of the nominal value  $I_{LMF}$ .

Due to the short circuit protection is enabled during start-up, the device does not deliver more than 1/3 of its nominal current limit  $I_{LIMF}$  until the output voltage exceeds 1/3 of the nominal output voltage. This needs to be considered when a load is connected to the output of the converter, which acts as a current sink.

0 Submit Documentation Feedback

Copyright © 2010–2016, Texas Instruments Incorporated



## **Device Functional Modes (continued)**

## 8.4.6 Output Capacitor Discharge

With EN = GND, the device enters shutdown mode and all internal circuits are disabled. The SW pin is connected to PGND through an internal resistor to discharge the output capacitor. This feature ensures a startup in a discharged output capacitor once the converter is enabled again and prevents "floating" charge on the output capacitor. The output voltage ramps up monotonic starting from 0 V.

## 9 Application and Implementation


#### NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

## 9.1 Application Information

The TPS62065 and TPS62067 are highly efficient synchronous step down DC/DC converters providing up to 2-A output current.

## 9.2 Typical Application



Copyright © 2016, Texas Instruments Incorporated

Figure 9. TPS62065 1.8-V Adjustable Output Voltage Configuration

#### 9.2.1 Design Requirements

The device operates over an input voltage range from 2.9 V to 6 V. The output voltage is adjustable using an external feedback divider.

#### 9.2.2 Detailed Design Procedure

#### 9.2.2.1 Output Voltage Setting

The output voltage can be calculated to:

$$V_{OUT} = V_{REF} \times \left(1 + \frac{R_1}{R_2}\right)$$
  $R_1 = \left(\frac{V_{OUT}}{V_{REF}} - 1\right) \times R_2$ 

with an internal reference voltage V<sub>RFF</sub> typically 0.6 V.

To minimize the current through the feedback divider network,  $R_2$  should be within the range of 120 k $\Omega$  to 360 k $\Omega$ . The sum of  $R_1$  and  $R_2$  should not exceed approximately 1 M $\Omega$ , to keep the network robust against noise. An external feed-forward capacitor  $C_{\rm ff}$  is required for optimum regulation performance. Lower resistor values can be used.  $R_1$  and  $C_{\rm ff}$  places a zero in the loop. The right value for  $C_{\rm ff}$  can be calculated as:

$$f_{z} = \frac{1}{2 \times \pi \times R_{1} \times C_{ff}} = 25 \text{ kHz}$$

$$C_{ff} = \frac{1}{2 \times \pi \times R_{1} \times 25 \text{ kHz}}$$

#### 9.2.2.2 Output Filter Design (Inductor and Output Capacitor)

The internal compensation network of TPS6206x is optimized for a LC output filter with a corner frequency of:



#### **Typical Application (continued)**

$$f_{c} = \frac{1}{2 \times \pi \times \sqrt{(1 \mu H \times 10 \mu F)}} = 50 \text{kHz}$$
(2)

The device operates with nominal inductors of 1  $\mu$ H to 1.2  $\mu$ H and with 10  $\mu$ F to 22  $\mu$ F small X5R and X7R ceramic capacitors. Refer to the lists of inductors and capacitors. The device is optimized for a 1- $\mu$ H inductor and 10- $\mu$ F output capacitor.

#### 9.2.2.2.1 Inductor Selection

The inductor value has a direct effect on the ripple current. The selected inductor must be rated for its DC resistance and saturation current. The inductor ripple current ( $\Delta I_L$ ) decreases with higher linductance and increases with higher  $V_{IN}$  or  $V_{OUT}$ .

Equation 3 calculates the maximum inductor current in PWM mode under static load conditions. The saturation current of the inductor should be rated higher than the maximum inductor current as calculated with Equation 4. This is recommended because during heavy load transient the inductor current rises above the calculated value.

$$\Delta I_{L} = Vout \times \frac{1 - \frac{Vout}{Vin}}{L \times f}$$

$$I_{Lmax} = I_{outmax} + \frac{\Delta I_{L}}{2}$$
(3)

#### where

- f = Switching frequency (3 MHz typical)
- L = Inductor value
- $\Delta I_L$  = Peak-to-peak inductor ripple current

A more conservative approach is to select the inductor current rating just for the switch current limit I<sub>LIMF</sub> of the converter.

The total losses of the coil have a strong impact on the efficiency of the DC/DC conversion and consist of both the losses in the DC resistance  $R_{(DC)}$  and the following frequency-dependent components:

- The losses in the core material (magnetic hysteresis loss, especially at high switching frequencies)
- Additional losses in the conductor from the skin effect (current displacement at high frequencies)
- Magnetic field losses of the neighboring windings (proximity effect)
- Radiation losses

Table 1. List of Inductors

DIMENSIONS (mm <sup>3</sup> )	INDUCTANCE (μH)	INDUCTOR TYPE	SUPPLIER
3.2 x 2.5 x 1 maximum	1	LQM32PN (MLCC)	Murata
3.7 × 4 × 1.8 maximum	1	LQH44 (wire wound)	Murata
4 x 4 x 2.6 maximum	1.2	NRG4026T (wire wound)	Taiyo Yuden
$3.5 \times 3.7 \times 1.8$ maximum	1.2	DE3518 (wire wound)	ТОКО

#### 9.2.2.2.2 Output Capacitor Selection

The advanced fast-response voltage mode control scheme of the TPS6206x allows the use of tiny ceramic capacitors. TI recommends ceramic capacitors with low ESR values that have the lowest output voltage ripple. The output capacitor requires either an X7R or X5R dielectric. Y5V and Z5U dielectric capacitors, aside from their wide variation in capacitance over temperature, become resistive at high frequencies and may not be used. For most applications a nominal 10- $\mu$ F or 22- $\mu$ F capacitor is suitable. At small ceramic capacitors, the DC-bias effect decreases the effective capacitance. Therefore a 22- $\mu$ F capacitor can be used for output voltages higher than 2 V, see list of capacitors.



In case additional ceramic capacitors in the supplied system are connected to the output of the DC/DC converter, the output capacitor  $C_{\text{OUT}}$  must be decreased in order not to exceed the recommended effective capacitance range. In this case a loop stability analysis must be performed as described later.

At nominal load current, the device operates in PWM mode and the RMS ripple current is calculated as:

$$I_{\text{RMSCout}} = V_{\text{out}} \times \frac{1 - \frac{V_{\text{out}}}{V_{\text{in}}}}{L \times f} \times \frac{1}{2 \times \sqrt{3}}$$
(5)

#### 9.2.2.2.3 Input Capacitor Selection

Because of the nature of the buck converter having a pulsating input current, a low ESR input capacitor is required for best input voltage filtering and minimizing the interference with other circuits caused by high input voltage spikes. For most applications, TI recommends a 10-µF ceramic capacitor. The input capacitor can be increased without any limit for better input voltage filtering.

Take care when using only small ceramic input capacitors. When a ceramic capacitor is used at the input and the power is being supplied through long wires, such as from a wall adapter, a load step at the output or VIN step on the input can induce ringing at the VIN pin. This ringing can couple to the output and be mistaken as loop instability or could even damage the part by exceeding the maximum ratings.

**CAPACITANCE SUPPLIER TYPE** SIZE (mm<sup>3</sup>)  $10\mu F$ GRM188R60J106M 0603: 1.6 x 0.8 x 0.8 Murata 22μF GRM188R60G226M 0603: 1.6 x 0.8 x 0.8 Murata 22µF CL10A226MQ8NRNC 0603: 1.6 x 0.8 x 0.8 Samsung 10µF CL10A106MQ8NRNC 0603: 1.6 x 0.8 x 0.8 Samsung

Table 2. List of Capacitors

#### 9.2.2.3 Checking Loop Stability

The first step of circuit and stability evaluation is to look from a steady-state perspective at the following signal


- Switching node, SW
- Inductor current, I<sub>1</sub>
- Output ripple voltage, V<sub>OUT(AC)</sub>

These are the basic signals that must be measured when evaluating a switching converter. When the switching waveform shows large duty cycle jitter or the output voltage or inductor current shows oscillations, the regulation loop may be unstable. This is often a result of board layout and/or wrong L-C output filter combinations. As a next step in the evaluation of the regulation loop, the load transient response is tested. The time between the application of the load transient and the turnon of the P-channel MOSFET, the output capacitor must supply all of the current required by the load.  $V_{OUT}$  immediately shifts by an amount equal to  $\Delta_{I(LOAD)}$  x ESR, where ESR is the effective series resistance of  $C_{OUT}$ .  $\Delta_{I(LOAD)}$  begins to charge or discharge  $C_{OUT}$  generating a feedback error signal used by the regulator to return  $V_{OUT}$  to its steady-state value. The results are most easily interpreted when the device operates in PWM mode at medium to high load currents.


During this recovery time,  $V_{OUT}$  can be monitored for settling time, overshoot, or ringing; that helps evaluate stability of the converter. Without any ringing, the loop has usually more than 45 $^{\circ}$  of phase margin.



#### 9.2.3 Application Curves








Submit Documentation Feedback

Copyright © 2010–2016, Texas Instruments Incorporated





Copyright © 2010-2016, Texas Instruments Incorporated Submit Documentation Feedback



## 9.3 System Example

The TPS62067 provides an open-drain power good output, refer to *Power Good Output (TPS62067)*.

## 9.3.1 TPS62067 Adjustable 1.8-V Output




Figure 27. TPS62067 Adjustable 1.8-V Output

Submit Documentation Feedback



## 10 Power Supply Recommendations

The power supply to the TPS6206x must have a current rating according to the supply voltage, output voltage, and output current of the TPS6206x.

#### 11 Layout

#### 11.1 Layout Guidelines

Take care in board layout to get the specified performance. If the layout is not carefully done, the regulator could show poor line and/or load regulation, stability issues as well as EMI and thermal problems. It is critical to provide a low inductance, impedance ground path. Therefore, use wide and short traces for the main current paths. The input capacitor should be placed as close as possible to the IC pins as well as the inductor and output capacitor.

Connect the AGND and PGND pins of the device to the PowerPAD™ land of the PCB and use this pad as a star point. Use a common power PGND node and a different node for the signal AGND to minimize the effects of ground noise. The FB divider network should be connected right to the output capacitor and the FB line must be routed away from noisy components and traces (for example, SW line).

Due to the small package of this converter and the overall small solution size the thermal performance of the PCB layout is important. To get a good thermal performance, TI recommends a four or more Layer PCB design. The PowerPAD<sup>TM</sup> of the IC must be soldered on the power pad area on the PCB to get a proper thermal connection. For good thermal performance the PowerPAD<sup>TM</sup> on the PCB needs to be connected to an inner GND plane with sufficient via connections. Refer to the documentation of the evaluation kit.

#### 11.2 Layout Example




Figure 28. PCB Layout

Product Folder Links: TPS62065 TPS62067

corporated Submit Documentation Feedback



## 12 Device and Documentation Support

#### 12.1 Device Support

## 12.1.1 Third-Party Products Disclaimer

TI'S PUBLICATION OF INFORMATION REGARDING THIRD-PARTY PRODUCTS OR SERVICES DOES NOT CONSTITUTE AN ENDORSEMENT REGARDING THE SUITABILITY OF SUCH PRODUCTS OR SERVICES OR A WARRANTY, REPRESENTATION OR ENDORSEMENT OF SUCH PRODUCTS OR SERVICES, EITHER ALONE OR IN COMBINATION WITH ANY TI PRODUCT OR SERVICE.

#### 12.2 Related Links

The table below lists quick access links. Categories include technical documents, support and community resources, tools and software, and quick access to sample or buy.

Table 3. Related Links

PARTS	PRODUCT FOLDER	SAMPLE & BUY	TECHNICAL DOCUMENTS	TOOLS & SOFTWARE	SUPPORT & COMMUNITY
TPS62065	Click here	Click here	Click here	Click here	Click here
TPS62067	Click here	Click here	Click here	Click here	Click here

#### 12.3 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. In the upper right corner, click on *Alert me* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

## 12.4 Community Resources

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

TI E2E™ Online Community *TI's Engineer-to-Engineer (E2E) Community.* Created to foster collaboration among engineers. At e2e.ti.com, you can ask questions, share knowledge, explore ideas and help solve problems with fellow engineers.

**Design Support** *TI's Design Support* Quickly find helpful E2E forums along with design support tools and contact information for technical support.

#### 12.5 Trademarks

PowerPAD, E2E are trademarks of Texas Instruments.
All other trademarks are the property of their respective owners.

#### 12.6 Electrostatic Discharge Caution



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

#### 12.7 Glossary

SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.

## 13 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.




# **DSG0008A**



## PACKAGE OUTLINE

# WSON - 0.8 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



#### NOTES:

- All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
   This drawing is subject to change without notice.
   The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.

www.ti.com




## **EXAMPLE BOARD LAYOUT**

# **DSG0008A**

# WSON - 0.8 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



NOTES: (continued)

- 4. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).
- Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.

www.ti.com




## **EXAMPLE STENCIL DESIGN**

# **DSG0008A**

## WSON - 0.8 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

www.ti.com





6-Dec-2016

#### **PACKAGING INFORMATION**

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead/Ball Finish (6)	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
TPS62065DSGR	ACTIVE	WSON	DSG	8	3000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-2-260C-1 YEAR	-40 to 125	OFA	Samples
TPS62065DSGT	ACTIVE	WSON	DSG	8	250	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-2-260C-1 YEAR	-40 to 125	OFA	Samples
TPS62067DSGR	ACTIVE	WSON	DSG	8	3000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-2-260C-1 YEAR	-40 to 125	ODH	Samples
TPS62067DSGT	ACTIVE	WSON	DSG	8	250	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-2-260C-1 YEAR	-40 to 125	ODH	Samples

(1) The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.

TBD: The Pb-Free/Green conversion plan has not been defined.

**Pb-Free (RoHS):** TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

Pb-Free (RoHS Exempt): This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead/Ball Finish Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.



## **PACKAGE OPTION ADDENDUM**

6-Dec-2016

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

#### OTHER QUALIFIED VERSIONS OF TPS62065, TPS62067:

Automotive: TPS62065-Q1, TPS62067-Q1

NOTE: Qualified Version Definitions:

• Automotive - Q100 devices qualified for high-reliability automotive applications targeting zero defects

**PACKAGE MATERIALS INFORMATION** 

www.ti.com 3-Aug-2017

## TAPE AND REEL INFORMATION





_		
		Dimension designed to accommodate the component width
		Dimension designed to accommodate the component length
		Dimension designed to accommodate the component thickness
	W	Overall width of the carrier tape
ſ	P1	Pitch between successive cavity centers

## QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



#### \*All dimensions are nominal

Device		Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TPS62065DSGR	WSON	DSG	8	3000	180.0	8.4	2.3	2.3	1.15	4.0	8.0	Q2
TPS62065DSGT	WSON	DSG	8	250	180.0	8.4	2.3	2.3	1.15	4.0	8.0	Q2
TPS62067DSGR	WSON	DSG	8	3000	179.0	8.4	2.2	2.2	1.2	4.0	8.0	Q2
TPS62067DSGT	WSON	DSG	8	250	180.0	8.4	2.3	2.3	1.15	4.0	8.0	Q2
TPS62067DSGT	WSON	DSG	8	250	179.0	8.4	2.2	2.2	1.2	4.0	8.0	Q2

www.ti.com 3-Aug-2017



\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TPS62065DSGR	WSON	DSG	8	3000	210.0	185.0	35.0
TPS62065DSGT	WSON	DSG	8	250	210.0	185.0	35.0
TPS62067DSGR	WSON	DSG	8	3000	195.0	200.0	45.0
TPS62067DSGT	WSON	DSG	8	250	210.0	185.0	35.0
TPS62067DSGT	WSON	DSG	8	250	195.0	200.0	45.0

#### **IMPORTANT NOTICE**

Texas Instruments Incorporated (TI) reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete.

TI's published terms of sale for semiconductor products (http://www.ti.com/sc/docs/stdterms.htm) apply to the sale of packaged integrated circuit products that TI has qualified and released to market. Additional terms may apply to the use or sale of other types of TI products and services.

Reproduction of significant portions of TI information in TI data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such reproduced documentation. Information of third parties may be subject to additional restrictions. Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyers and others who are developing systems that incorporate TI products (collectively, "Designers") understand and agree that Designers remain responsible for using their independent analysis, evaluation and judgment in designing their applications and that Designers have full and exclusive responsibility to assure the safety of Designers' applications and compliance of their applications (and of all TI products used in or for Designers' applications) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to their applications, Designer has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any applications that include TI products, Designer will thoroughly test such applications and the functionality of such TI products as used in such applications.

TI's provision of technical, application or other design advice, quality characterization, reliability data or other services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using TI Resources in any way, Designer (individually or, if Designer is acting on behalf of a company, Designer's company) agrees to use any particular TI Resource solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

Designer is authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNER AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

Unless TI has explicitly designated an individual product as meeting the requirements of a particular industry standard (e.g., ISO/TS 16949 and ISO 26262), TI is not responsible for any failure to meet such industry standard requirements.

Where TI specifically promotes products as facilitating functional safety or as compliant with industry functional safety standards, such products are intended to help enable customers to design and create their own applications that meet applicable functional safety standards and requirements. Using products in an application does not by itself establish any safety features in the application. Designers must ensure compliance with safety-related requirements and standards applicable to their applications. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equipment includes, without limitation, all medical devices identified by the U.S. Food and Drug Administration as Class III devices and equivalent classifications outside the U.S.

TI may expressly designate certain products as completing a particular qualification (e.g., Q100, Military Grade, or Enhanced Product). Designers agree that it has the necessary expertise to select the product with the appropriate qualification designation for their applications and that proper product selection is at Designers' own risk. Designers are solely responsible for compliance with all legal and regulatory requirements in connection with such selection.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's non-compliance with the terms and provisions of this Notice.