

# 18-Bit, 100-kSPS, Serial Interface, microPower, Miniature, True-Differential Input, SAR Analog-to-Digital Converter

Check for Samples: ADS8887

#### **FEATURES**

- Sample Rate: 100 kHzNo Latency Output
- Unipolar, True-Differential Input Range:
   -V<sub>RFF</sub> to +V<sub>RFF</sub>
- Wide Common-Mode Voltage Range:
   0 V to V<sub>REF</sub> with 90-dB CMRR (min)
- SPI<sup>™</sup>-Compatible Serial Interface with Daisy-Chain Option
- Excellent AC and DC Performance:
  - SNR: 100 dB, THD: -115 dB
  - INL: ±1.5 LSB (typ), ±3.0 LSB (max)
  - DNL: +1.5 and -1 LSB (max), 18-Bit NMC
- Wide Operating Range:
  - AVDD: 2.7 V to 3.6 V
  - DVDD: 1.65 V to 3.6 V (Independent of AVDD)
  - REF: 2.5 V to 5 V (Independent of AVDD)
  - Operating Temperature: -40°C to +85°C
- Low-Power Dissipation:
  - 0.7 mW at 100 kSPS
  - 70 µW at 10 kSPS
- Power-Down Current (AVDD): 50 nA
- Full-Scale Step Settling to 18 Bits: 1200 ns
- Packages: MSOP-10 and SON-10

#### **APPLICATIONS**

- Automatic Test Equipment (ATE)
- Instrumentation and Process Controls
- Precision Medical Equipment
- · Low-Power, Battery-Operated Instruments


#### DESCRIPTION

The ADS8887 is an 18-bit, 100-kSPS, true-differential input, analog-to-digital converter (ADC). The device operates with a 2.5-V to 5-V external reference, offering a wide selection of signal ranges without additional input signal scaling. The reference voltage setting is independent of, and can exceed, the analog supply voltage (AVDD).

The device offers an SPI-compatible serial interface that also supports daisy-chain operation for cascading multiple devices.

The device supports unipolar, true-differential analog input signals with a differential input swing of  $-V_{REF}$  to  $+V_{REF}$ . This true-differential analog input structure allows for a common-mode voltage of any value in the range of 0 V to  $+V_{REF}$  (when both inputs are within the operating input range of -0.1 V to  $V_{REF}$  +0.1 V).

Device operation is optimized for very low-power operation. Power consumption directly scales with speed. This feature makes the ADS8887 excellent for lower-speed applications.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

TINA is a trademark of Texas Instruments Inc..

SPI is a trademark of Motorola Inc.

All other trademarks are the property of their respective owners.





This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

#### FAMILY INFORMATION<sup>(1)</sup>

| THROUGHPUT | 18-BIT, TRUE-DIFFERENTIAL | 16-BIT, SINGLE-ENDED   | 16-BIT, TRUE-DIFFERENTIAL |
|------------|---------------------------|------------------------|---------------------------|
| 100 kSPS   | ADS8887                   | ADS8866                | ADS8867                   |
| 250 kSPS   | _                         | _                      | _                         |
| 400 kSPS   | ADS8885                   | ADS8864                | ADS8865                   |
| 500 kSPS   | _                         | ADS8319 <sup>(2)</sup> | ADS8318 <sup>(2)</sup>    |
| 680 kSPS   | ADS8883                   | ADS8862                | ADS8863                   |
| 1 MSPS     | ADS8881                   | ADS8860                | ADS8861                   |

For the most current package and ordering information, see the Package Option Addendum at the end of this document, or visit the device product folder at www.ti.com.

# **ABSOLUTE MAXIMUM RATINGS**(1)

Over operating free-air temperature range, unless otherwise noted.

|   | VALUE | VALUE      |      |  |
|---|-------|------------|------|--|
|   | MIN   | MAX        | UNIT |  |
| AINP to GND or AINN to GND                  | -0.3  | REF + 0.3  | V    |  |
| AVDD to GND or DVDD to GND                  | -0.3  | 4          | V    |  |
| REF to GND                                  | -0.3  | 5.7        | V    |  |
| Digital input voltage to GND                | -0.3  | DVDD + 0.3 | V    |  |
| Digital output to GND                       | -0.3  | DVDD + 0.3 | V    |  |
| Operating temperature range, T <sub>A</sub> | -40   | +85        | °C   |  |
| Storage temperature range, T <sub>stg</sub> | -65   | +150       | °C   |  |

<sup>(1)</sup> Stresses beyond those listed under *absolute maximum ratings* may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under *electrical characteristics* is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

#### THERMAL INFORMATION

|                  |  | ADS     |         |        |
|------------------|--|---------|---------|--------|
|                  | THERMAL METRIC <sup>(1)</sup>                | DGS     | DRC     | UNITS  |
|                  |  | 10 PINS | 10 PINS |        |
| $\theta_{JA}$    | Junction-to-ambient thermal resistance       | 151.9   | 111.1   |        |
| $\theta_{JCtop}$ | Junction-to-case (top) thermal resistance    | 45.4    | 46.4    |        |
| $\theta_{JB}$    | Junction-to-board thermal resistance         | 72.2    | 45.9    | 90.444 |
| ΨЈТ              | Junction-to-top characterization parameter   | 3.3     | 3.5     | °C/W   |
| ΨЈВ              | Junction-to-board characterization parameter | 70.9    | 45.5    |        |
| $\theta_{JCbot}$ | Junction-to-case (bottom) thermal resistance | N/A     | N/A     |        |

(1) For more information about traditional and new thermal metrics, see the IC Package Thermal Metrics application report, SPRA953.

<sup>(2)</sup> Pin-to-pin compatible device with AVDD = 5 V.

www.ti.com

#### **ELECTRICAL CHARACTERISTICS**

All minimum and maximum specifications are at  $T_A = -40^{\circ}\text{C}$  to +85°C, AVDD = 3 V, DVDD = 3 V,  $V_{REF} = 5$  V,  $V_{CM} = V_{REF} / 2$  V, and  $f_{SAMPLE} = 100$  kSPS, unless otherwise noted. Typical specifications are at  $T_A = +25^{\circ}\text{C}$ , AVDD = 3 V, and DVDD = 3 V.

|                   | PARAMETER                                       | TEST CONDITIONS   | MIN               | TYP                  | MAX                    | UNIT               |
|-------------------|---|---|-------------------|----------------------|------------------------|--------------------|
| ANALO             | G INPUT   | -   |                   |                      | Į.                     |                    |
|                   | Full-scale input span <sup>(1)(2)</sup>         | AINP – AINN   | -V <sub>REF</sub> |                      | $V_{REF}$              | V                  |
|                   | (1)/2)  | AINP  | -0.1              |                      | V <sub>REF</sub> + 0.1 | V                  |
|                   | Operating input range (1)(2)                    | AINN  | -0.1              |                      | V <sub>REF</sub> + 0.1 | V                  |
| $V_{CM}$          | Input common-mode range                         |   | 0                 | V <sub>REF</sub> / 2 | $V_{REF}$              | V                  |
| Cı                | Input capacitance                               | AINP and AINN terminal to GND                           |                   | 59                   |                        | pF                 |
|                   | Input leakage current                           | During acquisition for dc input                         |                   | 5                    |                        | nA                 |
| SYSTE             | M PERFORMANCE                                   |   |                   |                      |                        |                    |
|                   | Resolution                                      |   |                   | 18                   |                        | Bits               |
| NMC               | No missing codes                                |   | 18                |                      |                        | Bits               |
| DNL               | Differential linearity                          |   | -0.99             | ±0.7                 | 1.5                    | LSB <sup>(3)</sup> |
| INL               | Integral linearity (4)                          |   | -3                | ±1.5                 | 3                      | LSB <sup>(3)</sup> |
| Eo                | Offset error <sup>(5)</sup>                     |   | -4                | ±1                   | 4                      | mV                 |
|                   | Offset error drift with temperature             |   |                   | ±1.5                 |                        | μV/°C              |
| E <sub>G</sub>    | Gain error                                      |   | -0.01             | ±0.005               | 0.01                   | %FSR               |
|                   | Gain error drift with temperature               |   |                   | ±0.15                |                        | ppm/°C             |
| CMRR              | Common-mode rejection ratio                     | With common-mode input signal = 5 V <sub>PP</sub> at dc | 90                | 100                  |                        | dB                 |
| PSRR              | Power-supply rejection ratio                    | At mid-code   |                   | 80                   |                        | dB                 |
|                   | Transition noise                                |   |                   | 0.7                  |                        | LSB                |
| SAMPL             | ING DYNAMICS                                    |   |                   |                      |                        |                    |
| t <sub>conv</sub> | Conversion time                                 |   | 500               |                      | 8800                   | ns                 |
| t <sub>ACQ</sub>  | Acquisition time                                |   | 1200              |                      |                        | ns                 |
|                   | Maximum throughput rate with or without latency |   |                   |                      | 100                    | kHz                |
|                   | Aperture delay                                  |   |                   | 4                    |                        | ns                 |
|                   | Aperture jitter, RMS                            |   |                   | 5                    |                        | ps                 |
|                   | Step response                                   | Settling to 18-bit accuracy                             |                   | 1200                 |                        | ns                 |
|                   | Overvoltage recovery                            | Settling to 18-bit accuracy                             |                   | 1200                 |                        | ns                 |

Ideal input span, does not include gain or offset error. Specified for  $V_{CM} = V_{REF} / 2$ . Refer to the *Analog Input* section for the effect of  $V_{CM}$  on the full-scale input range. LSB = least significant bit.

This parameter is the endpoint INL, not best-fit.

Measured relative to actual measured reference.



All minimum and maximum specifications are at  $T_A = -40^{\circ}C$  to +85°C, AVDD = 3 V, DVDD = 3 V,  $V_{REF} = 5$  V,  $V_{CM} = V_{REF}$  / 2 V, and  $f_{SAMPLE} = 100$  kSPS, unless otherwise noted.

Typical specifications are at  $T_A = +25$ °C, AVDD = 3 V, and DVDD = 3 V.

|                       | PARAMETER                                |                          | TEST CONDITIONS  | MIN        | TYP  | MAX        | UNIT |
|-----------------------|--|--------------------------|--|------------|------|------------|------|
| DYNAM                 | IC CHARACTERISTI                         | cs                       |  | 1          |      | <u></u>    |      |
|                       |  |                          | At 1 kHz, V <sub>REF</sub> = 5 V                         | 98         | 99.9 |            | dB   |
| SINAD                 | NAD Signal-to-noise + distortion (6)     |                          | At 10 kHz, V <sub>REF</sub> = 5 V                        |            | 98.7 |            | dB   |
|                       |  |                          | At 49 kHz, V <sub>REF</sub> = 5 V                        |            | 93.3 |            | dB   |
|                       |  |                          | At 1 kHz, V <sub>REF</sub> = 5 V                         | 98.5       | 100  |            | dB   |
| SNR                   | SNR Signal-to-noise ratio <sup>(6)</sup> |                          | At 10 kHz, V <sub>REF</sub> = 5 V                        |            | 99.5 |            | dB   |
| Signal-to-noise ratio |  |                          | At 49 kHz, V <sub>REF</sub> = 5 V                        |            | 93.5 |            | dB   |
|                       |  |                          | At 1 kHz, V <sub>REF</sub> = 5 V                         |            | -115 |            | dB   |
| THD                   | Total harmonic disto                     | ortion (6) (7)           | At 10 kHz, V <sub>REF</sub> = 5 V                        |            | -112 |            | dB   |
|                       |  |                          | At 49 kHz, V <sub>REF</sub> = 5 V                        |            | -102 |            | dB   |
|                       |  |                          | At 1 kHz, V <sub>REF</sub> = 5 V                         |            | 115  |            | dB   |
| SFDR                  | Spurious-free dynar                      | nic range <sup>(6)</sup> | At 10 kHz, V <sub>REF</sub> = 5 V                        |            | 112  |            | dB   |
|                       |  |                          | At 49 kHz, V <sub>REF</sub> = 5 V                        |            | 102  |            | dB   |
| BW <sub>-3dB</sub>    | -3-dB small-signal b                     | andwidth                 |  |            | 30   |            | MHz  |
| EXTER                 | NAL REFERENCE IN                         | PUT                      |  | 1          |      |            |      |
| $V_{REF}$             | Input range                              |                          |  | 2.5        |      | 5          | V    |
|                       | Reference input cur                      | rent                     | During conversion, 100-kHz sample rate, mid-code         |            | 35   |            | μA   |
|                       | Reference leakage current                |                          |  |            | 250  |            | nA   |
| $C_{REF}$             | Decoupling capacitor at the REF input    |                          |  | 10 22      |      |            | μF   |
| POWER                 | -SUPPLY REQUIRE                          | MENTS                    |  |            |      |            |      |
|                       | Power-supply                             | AVDD                     | Analog supply  | 2.7        | 3    | 3.6        | V    |
|                       | voltage                                  | DVDD                     | Digital supply range                                     | 1.65       | 1.8  | 3.6        | V    |
|                       | Supply current                           | AVDD                     | 100-kHz sample rate, AVDD = 3 V                          |            | 0.23 | 0.4        | mA   |
| _                     | Danier dia sia atia a                    |                          | 100-kHz sample rate, AVDD = 3 V                          |            | 0.7  | 1.2        | mW   |
| $P_{VA}$              | Power dissipation                        |                          | 10-kHz sample rate, AVDD = 3 V                           |            | 70   |            | μW   |
| IA <sub>PD</sub>      | Device power-down                        | current <sup>(8)</sup>   |  |            | 50   |            | nA   |
| DIGITAL               | INPUTS: LOGIC FA                         | MILY (CMOS)              |  |            |      | <u> </u>   |      |
| V                     | High lavel inner to the                  |                          | 1.65 V < DVDD < 2.3 V                                    | 0.8 × DVDD |      | DVDD + 0.3 | V    |
| $V_{IH}$              | High-level input volt                    | age                      | 2.3 V < DVDD < 3.6 V                                     | 0.7 × DVDD |      | DVDD + 0.3 | V    |
| .,                    | 1 1 1 1 1 1 1                            |                          | 1.65 V < DVDD < 2.3 V                                    | -0.3       |      | 0.2 × DVDD | V    |
| $V_{IL}$              | Low-level input voltage                  |                          | 2.3 V < DVDD < 3.6 V                                     | -0.3 0.3 × |      | 0.3 × DVDD | V    |
| I <sub>LK</sub>       | Digital input leakage                    | current                  |  |            | ±10  | ±100       | nA   |
| DIGITAL               | OUTPUTS: LOGIC                           | FAMILY (CMC              | OS)  | *          |      |            |      |
| V <sub>OH</sub>       | High-level output vo                     | ltage                    | $I_O = 500$ - $\mu$ A source, $C_{LOAD} = 20 \text{ pF}$ | 0.8 × DVDD |      | DVDD       | V    |
| $V_{OL}$              | Low-level output vol                     | tage                     | $I_O = 500$ - $\mu$ A sink, $C_{LOAD} = 20 \text{ pF}$   | 0          |      | 0.2 × DVDD | V    |
| TEMPE                 | RATURE RANGE                             |                          |  |            |      | ,          |      |
| T <sub>A</sub>        | Operating free-air te                    | emperature               |  | -40        |      | +85        | °C   |

All specifications expressed in decibels (dB) refer to the full-scale input (FSR) and are tested with an input signal 0.5 dB below full-scale, unless otherwise specified.

Calculated on the first nine harmonics of the input frequency.

The device automatically enters a power-down state at the end of every conversion, and remains in power-down during the acquisition phase.



#### **TIMING CHARACTERISTICS**

#### **3-WIRE OPERATION**




Figure 1. 3-Wire Operation: CONVST Functions as Chip Select

# Table 1. TIMING REQUIREMENTS: 3-Wire Operation<sup>(1)</sup>

|                         | PARAMETER   | MIN   | TYP | MAX  | UNIT              |
|-------------------------|---|-------|-----|------|-------------------|
| t <sub>ACQ</sub>        | Acquisition time  | 1200  |     |      | ns                |
| t <sub>conv</sub>       | Conversion time   | 500   |     | 8800 | ns                |
| 1/f <sub>sample</sub>   | Time between conversions  | 10000 |     |      | ns                |
| t <sub>wh-CNV</sub>     | Pulse duration: CONVST high   | 10    |     |      | ns                |
| f <sub>SCLK</sub>       | SCLK frequency  |       |     | 16   | MHz               |
| t <sub>SCLK</sub>       | SCLK period   | 62.5  |     |      | ns                |
| t <sub>clkl</sub>       | SCLK low time   | 0.45  |     | 0.55 | t <sub>SCLK</sub> |
| t <sub>clkh</sub>       | SCLK high time  | 0.45  |     | 0.55 | t <sub>SCLK</sub> |
| t <sub>h-CK-DO</sub>    | SCLK falling edge to current data invalid                                     | 3     |     |      | ns                |
| t <sub>d-CK-DO</sub>    | SCLK falling edge to next data valid delay                                    |       |     | 13.4 | ns                |
| t <sub>d-CNV-DO</sub>   | Enable time: CONVST low to MSB valid  |       |     | 12.3 | ns                |
| t <sub>d-CNV-DOhz</sub> | Disable time: CONVST high or last SCLK falling edge to DOUT 3-state (CS mode) |       |     | 13.2 | ns                |
| t <sub>quiet</sub>      | Quiet time  | 20    |     |      | ns                |

<sup>(1)</sup> All specifications are at  $T_A = -40$  °C to +85 °C, AVDD = 3 V, and DVDD = 3 V, unless otherwise noted.



#### **4-WIRE OPERATION**




Figure 2. 4-Wire Operation: DIN Functions as Chip Select

Table 2. TIMING REQUIREMENTS: 4-Wire Operation<sup>(1)</sup>

|                        | PARAMETER  | MIN   | TYP | MAX  | UNIT |
|------------------------|--|-------|-----|------|------|
| t <sub>ACQ</sub>       | Acquisition time   | 1200  |     |      | ns   |
| t <sub>conv</sub>      | Conversion time  | 500   |     | 8800 | ns   |
| 1/f <sub>sample</sub>  | Time between conversions                                       | 10000 |     |      | ns   |
| t <sub>wh-DI</sub>     | Pulse duration: DIN high                                       | 10    |     |      | ns   |
| $t_{\text{wl-CNV}}$    | Pulse width: CONVST low  | 20    |     |      | ns   |
| t <sub>d-DI-DO</sub>   | Delay time: DIN low to MSB valid                               |       |     | 12.3 | ns   |
| t <sub>d-DI-DOhz</sub> | Delay time: DIN high or last SCLK falling edge to DOUT 3-state |       |     | 13.2 | ns   |
| t <sub>su-DI-CNV</sub> | Setup time: DIN high to CONVST rising edge                     | 7.5   |     |      | ns   |
| t <sub>h-DI-CNV</sub>  | Hold time: DIN high from CONVST rising edge                    | 0     |     |      | ns   |

<sup>(1)</sup> All specifications are at  $T_A = -40$ °C to +85°C, AVDD = 3 V, and DVDD = 3 V, unless otherwise noted.



#### **DAISY-CHAIN OPERATION**




Figure 3. Daisy-Chain Operation: Two Devices

Table 3. TIMING REQUIREMENTS: Daisy-Chain<sup>(1)</sup>

| PARAMETER  | MIN  | TYP   | MAX   | UNIT   |
|--|--|---|---|--|
| Acquisition time   | 1200   |   |   | ns   |
| Conversion time  | 500  |   | 8800  | ns   |
| Time between conversions                                 | 10000  |   |   | ns   |
| Setup time: SCLK valid to CONVST rising edge             | 5  |   |   | ns   |
| Hold time: SCLK valid from CONVST rising edge            | 5  |   |   | ns   |
| Setup time: DIN low to CONVST rising edge (see Figure 2) | 7.5  |   |   | ns   |
| Hold time: DIN low from CONVST rising edge               | 0  |   |   | ns   |
| Setup time: DIN valid to SCLK falling edge               | 1.5  |   |   | ns   |
|  | Acquisition time  Conversion time  Time between conversions  Setup time: SCLK valid to CONVST rising edge  Hold time: SCLK valid from CONVST rising edge  Setup time: DIN low to CONVST rising edge (see Figure 2)  Hold time: DIN low from CONVST rising edge | Acquisition time         1200           Conversion time         500           Time between conversions         10000           Setup time: SCLK valid to CONVST rising edge         5           Hold time: SCLK valid from CONVST rising edge         5           Setup time: DIN low to CONVST rising edge (see Figure 2)         7.5           Hold time: DIN low from CONVST rising edge         0 | Acquisition time         1200           Conversion time         500           Time between conversions         10000           Setup time: SCLK valid to CONVST rising edge         5           Hold time: SCLK valid from CONVST rising edge         5           Setup time: DIN low to CONVST rising edge (see Figure 2)         7.5           Hold time: DIN low from CONVST rising edge         0 | Acquisition time         1200           Conversion time         500         8800           Time between conversions         10000           Setup time: SCLK valid to CONVST rising edge         5           Hold time: SCLK valid from CONVST rising edge         5           Setup time: DIN low to CONVST rising edge (see Figure 2)         7.5           Hold time: DIN low from CONVST rising edge         0 |

<sup>(1)</sup> All specifications are at  $T_A = -40$ °C to +85°C, AVDD = 3 V, and DVDD = 3 V, unless otherwise noted.



#### **EQUIVALENT CIRCUITS**






Figure 4. Load Circuit for Digital Interface Timing



Submit Documentation Feedback



#### **PIN CONFIGURATIONS**



#### **PIN ASSIGNMENTS**

| PIN NAME            | PIN<br>NUMBER | FUNCTION        | DESCRIPTION  |
|---------------------|---------------|-----------------|--|
| AINN                | 4             | Analog input    | Inverting analog signal input  |
| AINP                | 3             | Analog input    | Noninverting analog signal input   |
| AVDD                | 2             | Analog          | Analog power supply. This pin must be decoupled to GND with a 1-µF capacitor.  |
| CONVST              | 6             | Digital input   | Convert input.  This pin also functions as the $\overline{\text{CS}}$ input in 3-wire interface mode. Refer to the   Description and Timing Characteristics sections for more details.   |
| DIN 9 Digital input |               | Digital input   | Serial data input.  The DIN level at the start of a conversion selects the mode of operation (such as $\overline{\text{CS}}$ or daisy-chain mode). This pin also serves as the $\overline{\text{CS}}$ input in 4-wire interface mode. Refer to the <i>Description</i> and <i>Timing Characteristics</i> sections for more details. |
| DOUT                | 7             | Digital output  | Serial data output   |
| DVDD                | 10            | Power supply    | Digital interface power supply.  This pin must be decoupled to GND with a 1-µF capacitor.  |
| GND                 | 5             | Analog, digital | Device ground.  Note that this pin is a common ground pin for both the analog power supply (AVDD) and digital I/O supply (DVDD). The reference return line is also internally connected to this pin.   |
| REF                 | 1             | Analog          | Positive reference input. This pin must be decoupled with a 10-µF or larger capacitor.   |
| SCLK                | 8             | Digital input   | Clock input for serial interface. Data output (on DOUT) are synchronized with this clock.  |
| Thermal pad         | _             | Thermal pad     | Exposed thermal pad. Texas Instruments recommends connecting the thermal pad to the printed circuit board (PCB) ground.  |



#### TYPICAL CHARACTERISTICS

At  $T_A = +25$ °C, AVDD = 3 V, DVDD = 3 V,  $V_{REF} = 5$  V, and  $f_{SAMPLE} = 100$  kSPS, unless otherwise noted.




Figure 6. TYPICAL INL (V<sub>REF</sub> = 2.5 V)




Figure 7. TYPICAL DNL (V<sub>REF</sub> = 2.5 V)




Figure 8. TYPICAL INL (V<sub>REF</sub> = 5 V)




Figure 9. TYPICAL DNL (V<sub>REF</sub> = 5 V)




Figure 10. INL vs TEMPERATURE




Figure 11. DNL vs TEMPERATURE

Submit Documentation Feedback



At  $T_A = +25$ °C, AVDD = 3 V, DVDD = 3 V,  $V_{REF} = 5$  V, and  $f_{SAMPLE} = 100$  kSPS, unless otherwise noted.




Figure 12. INL vs REFERENCE VOLTAGE




Figure 13. DNL vs REFERENCE VOLTAGE




Figure 14. DC INPUT HISTOGRAM ( $V_{REF} = 2.5 \text{ V}$ )




Figure 15. DC INPUT HISTOGRAM (V<sub>REF</sub> = 5 V)




Figure 16. TYPICAL FFT ( $V_{REF} = 2.5 \text{ V}$ )




Figure 17. TYPICAL FFT ( $V_{REF} = 5 \text{ V}$ )

Copyright © 2013, Texas Instruments Incorporated



At  $T_A = +25$ °C, AVDD = 3 V, DVDD = 3 V,  $V_{REF} = 5$  V, and  $f_{SAMPLE} = 100$  kSPS, unless otherwise noted.




Figure 18. SNR vs REFERENCE VOLTAGE




Figure 19. SINAD vs REFERENCE VOLTAGE




Figure 20. ENOB vs REFERENCE VOLTAGE




Figure 21. THD vs REFERENCE VOLTAGE




Figure 22. SFDR vs REFERENCE VOLTAGE




Figure 23. SNR vs TEMPERATURE

Submit Documentation Feedback



At  $T_A = +25$ °C, AVDD = 3 V, DVDD = 3 V,  $V_{REF} = 5$  V, and  $f_{SAMPLE} = 100$  kSPS, unless otherwise noted.




Figure 24. SINAD vs TEMPERATURE




Figure 25. ENOB vs TEMPERATURE




Figure 26. THD vs TEMPERATURE




Figure 27. SFDR vs TEMPERATURE




Figure 28. SUPPLY CURRENT vs TEMPERATURE




Figure 29. POWER CONSUMPTION vs TEMPERATURE



At  $T_A = +25$ °C, AVDD = 3 V, DVDD = 3 V,  $V_{REF} = 5$  V, and  $f_{SAMPLE} = 100$  kSPS, unless otherwise noted.





Figure 30. SUPPLY CURRENT vs THROUGHPUT






Figure 32. POWER-DOWN CURRENT vs TEMPERATURE




Figure 33. OFFSET vs TEMPERATURE




Figure 34. GAIN ERROR vs TEMPERATURE





Figure 35. TYPICAL DISTRIBUTION OF GAIN ERROR

Submit Documentation Feedback



At  $T_A = +25$ °C, AVDD = 3 V, DVDD = 3 V,  $V_{REF} = 5$  V, and  $f_{SAMPLE} = 100$  kSPS, unless otherwise noted.






Figure 36. TYPICAL DISTRIBUTION OF OFFSET ERROR

Figure 37. TYPICAL DISTRIBUTION OF DIFFERENTIAL NONLINEARITY (Minimum and Maximum)




Figure 38. TYPICAL DISTRIBUTION OF INTEGRAL NONLINEARITY (Minimum and Maximum)



#### **OVERVIEW**

The ADS8887 is a high-speed, successive approximation register (SAR), analog-to-digital converter (ADC) from a 16- and 18-bit product family. This compact device features high performance. Power consumption is inherently low and scales linearly with sampling speed. The architecture is based on charge redistribution, which inherently includes a sample-and-hold (S/H) function.

The ADS8887 supports a true-differential analog input across two pins (INP and INN). When a conversion is initiated, the differential input on these pins is sampled on the internal capacitor array. While a conversion is in progress, both the INP and INN inputs are disconnected from the internal circuit.

The ADS8887 uses an internal clock to perform conversions. The device reconnects the sampling capacitors to the INP and INN pins after conversion and then enters an acquisition phase. During the acquisition phase, the device is powered down and the conversion result can be read.

The device digital output is available in SPI-compatible format, which makes interfacing with microprocessors, digital signal processors (DSPs), or field-programmable gate arrays (FPGAs) easy.

#### **ANALOG INPUT**

As shown in Figure 39, the device features a differential analog input. Both positive and negative inputs are individually sampled on 55-pF sampling capacitors and the device converts for the voltage difference between the two sampled values:  $V_{INP} - V_{INN}$ .




Figure 39. Detailed Block Diagram



Most differential input SAR ADCs prohibit the input common-mode voltage,  $V_{CM}$  (that is, the average voltage between the inputs), at AINP or AINM from varying more than approximately 10% beyond the mid-scale input value. As shown in Figure 40, the device has a unique common-mode voltage detection and rejection block that does not have this restriction and thus allows  $V_{CM}$  to be set to any value between 0 V and  $V_{REF}$  without degrading device performance.




Figure 40. Conceptual Diagram: True Differential Input Structure

Table 4 shows the full-scale input range of the device as a function of input common-mode voltage. The device offers a maximum dynamic range for  $V_{CM} = V_{REF} / 2$ . The differential input with wide common-mode range allows connecting differential signals from sensors without any signal conditioning.

Table 4. Full-Scale Input Range

| V                      | ABSOLUTE II                                | NPUT RANGE                                 | FILL SCALE INDUT DANCE (V. )  |  |  |  |
|------------------------|--|--|---|--|--|--|
| V <sub>CM</sub>        | V <sub>AINP</sub>                          | V <sub>AINN</sub>                          | FULL SCALE INPUT RANGE (V <sub>FS</sub> )                           |  |  |  |
| $V_{CM} < V_{REF} / 2$ | 0 to 2 × V <sub>CM</sub>                   | 0 to 2 x V <sub>CM</sub>                   | $(-2 \times V_{CM})$ to $(2 \times V_{CM})$                         |  |  |  |
| $V_{CM} = V_{REF} / 2$ | 0 to V <sub>REF</sub>                      | 0 to V <sub>REF</sub>                      | (-V <sub>REF</sub> ) to (V <sub>REF</sub> )                         |  |  |  |
| $V_{CM} > V_{REF} / 2$ | $(2 \times V_{CM} - V_{REF})$ to $V_{REF}$ | $(2 \times V_{CM} - V_{REF})$ to $V_{REF}$ | $(-2 \times (V_{CM} - V_{REF}))$ to $(2 \times (V_{CM} - V_{REF}))$ |  |  |  |

Figure 41 shows an equivalent circuit of the input sampling stage. The sampling switch is represented by a 96- $\Omega$  resistance in series with the ideal switch. Refer to the *ADC Input Driver* section for more details on the recommended driving circuits.




Figure 41. Input Sampling Stage Equivalent Circuit

Figure 39 and Figure 41 illustrate electrostatic discharge (ESD) protection diodes to REF and GND from both analog inputs. Make sure that these diodes do not turn on by keeping the analog inputs within the specified range.



#### REFERENCE

The device operates with an external reference voltage and switches binary-weighted capacitors onto the reference terminal (REF pin) during the conversion process. The switching frequency is proportional to the internal conversion clock frequency but the dynamic charge requirements are a function of the absolute value of the input voltage and reference voltage. This dynamic load must be supported by a reference driver circuit without degrading the noise and linearity performance of the device. During the acquisition process, the device automatically powers down and does not take any dynamic current from the external reference source. The basic circuit diagram for such a reference driver circuit for precision ADCs is shown in Figure 42. Refer to the ADC Reference Driver section for more details on the application circuits.




Figure 42. Reference Driver Schematic

#### **CLOCK**

The device uses an internal clock for conversion. Conversion duration may vary but is bounded by the minimum and maximum value of  $t_{conv}$ , as specified in the Timing Characteristics section. An external SCLK is only used for a serial data read operation. Data are read after a conversion completes and when the device is in acquisition phase for the next sample.



#### **ADC TRANSFER FUNCTION**

The ADS8887 is a unipolar, differential input device. The device output is in twos compliment format.

Figure 43 shows ideal characteristics for the device. The full-scale range for the ADC input (AINP – AINN) is equal to twice the reference input voltage to the ADC ( $2 \times V_{REF}$ ). The LSB for the ADC is given by Equation 1.




Figure 43. Differential Transfer Characteristics

#### **DIGITAL INTERFACE**

The ADS8887 is a low pin-count device. However, the device offers three different options for interfacing with the digital host.

These options can be broadly classified as being either  $\overline{CS}$  mode (in either a 3- or 4-wire interface) or daisy-chain mode. The device operates in  $\overline{CS}$  mode if DIN is high at the CONVST rising edge. If DIN is low at the CONVST rising edge, or if DIN and CONVST are connected together, the device operates in daisy-chain mode.

The 3-wire interface in  $\overline{\text{CS}}$  mode is useful for applications that need galvanic isolation on-board. The 4-wire interface in  $\overline{\text{CS}}$  mode allows the user to sample the analog input independent of the serial interface timing and, therefore, allows easier control of an individual device while having multiple, similar devices on-board. The daisy-chain mode is provided to hook multiple devices in a chain similar to a shift register and is useful in reducing component count and the number of signal traces on the board.

#### **CS** Mode

CS mode is selected if DIN is high at the CONVST rising edge. There are two different interface options available in this mode: 3-wire CS mode, and 4-wire CS mode. The following sections discuss these interface options in detail.



#### 3-Wire CS Mode

This interface option is most useful when a single ADC is connected to an SPI-compatible digital host. In this interface option, DIN can be connected to DVDD and CONVST functions as  $\overline{CS}$  (as shown in Figure 44). As shown in Figure 45, a CONVST rising edge forces DOUT to 3-state, samples the input signal, and causes the device to enter a conversion phase. Conversion is done with the internal clock and continues regardless of the state of CONVST. As a result, CONVST (functioning as  $\overline{CS}$ ) can be pulled low after the start of the conversion to select other devices on the board. However, CONVST must return high before the minimum conversion time ( $t_{conv-min}$ ) elapses and is held high until the maximum possible conversion time ( $t_{conv-max}$ ) elapses.




Figure 44. Connection Diagram: 3-Wire CS Mode (DIN = 1)




Figure 45. Interface Timing Diagram: 3-Wire CS Mode (DIN = 1)

When conversion is complete, the device enters an acquisition phase and powers down. CONVST (functioning as  $\overline{\text{CS}}$ ) can be brought low after the maximum conversion time ( $t_{\text{conv-max}}$ ) elapses. On the CONVST falling edge, DOUT comes out of 3-state and the device outputs the MSB of the data. The lower data bits are output on subsequent SCLK falling edges. Data are valid on both SCLK edges. Data are valid on both edges of SCLK and can be captured on either edge. However, a digital host capturing data on the SCLK falling edge can achieve a faster reading rate (provided  $t_{h\_CK\_DO}$  is acceptable). DOUT goes to 3-state after the 18th SCLK falling edge or when CONVST goes high, whichever occurs first.

www.ti.com

#### 4-Wire CS Mode

This interface option is useful when one or more ADCs are connected to an SPI-compatible digital host. Figure 46 shows the connection diagram for single ADC, Figure 48 shows the connection diagram for two ADCs.




Figure 46. Connection Diagram: Single ADC with 4-Wire CS Mode

In this interface option, DIN is controlled by the digital host and functions as  $\overline{CS}$ . As shown in Figure 47, with DIN high, a CONVST rising edge selects  $\overline{CS}$  mode, forces DOUT to 3-state, samples the input signal, and causes the device to enter a conversion phase. In this interface option, CONVST must be held at a high level from the start of the conversion until all data bits are read. Conversion is done with the internal clock and continues regardless of the state of DIN. As a result, DIN (functioning as  $\overline{CS}$ ) can be pulled low to select other devices on the board. However, DIN must be pulled high before the minimum conversion time ( $t_{conv-min}$ ) elapses and remains high until the maximum possible conversion time ( $t_{conv-max}$ ) elapses.




Figure 47. Interface Timing Diagram: Single ADC with 4-Wire CS Mode



When conversion is complete, the device enters acquisition phase and powers down. DIN (functioning as  $\overline{\text{CS}}$ ) can be brought low after the maximum conversion time ( $t_{\text{conv-max}}$ ) elapses. On the DIN falling edge, DOUT comes out of 3-state and the device outputs the MSB of the data. The lower data bits are output on subsequent SCLK falling edges. Data are valid on both SCLK edges. Data are valid on both edges of SCLK and can be captured on either edge. However, a digital host capturing data on the SCLK falling edge can achieve a faster reading rate (provided  $t_{h_{\text{CK}},\text{DO}}$  is acceptable). DOUT goes to 3-state after the 18th SCLK falling edge or when DIN goes high, whichever occurs first.

As shown in Figure 48, multiple devices can be hooked together on the same data bus. In this case, as shown in Figure 49, the DIN of the second device (functioning as CS for the second device) can go low after the first device data are read and the DOUT of the first device is in 3-state.

Care must be taken so that CONVST and DIN are not both low together at any time during the cycle.




Figure 48. Connection Diagram: Two ADCs with 4-Wire CS Mode




Figure 49. Interface Timing Diagram: Two ADCs with 4-Wire CS Mode



#### **DAISY-CHAIN MODE**

Daisy-chain mode is selected if DIN is low at the time of a CONVST rising edge or if DIN and CONVST are connected together. The following section discusses this interface option in detail.

#### **Daisy-Chain Mode**

This interface option is most useful in applications where multiple ADC devices are used but the digital host has limited interfacing capability. Figure 50 shows a connection diagram with *N* ADCs connected in the daisy-chain. The CONVST pins of all ADCs in the chain are connected together and are controlled by a single pin of the digital host. Similarly, the SCLK pins of all ADCs in the chain are connected together and are controlled by a single pin of the digital host. The DIN pin for ADC 1 is connected to GND. The DOUT pin of ADC 1 is connected to the DIN pin of ADC 2, and so on. The DOUT pin of the last ADC in the chain (ADC N) is connected to the SDI pin of the digital host.




Figure 50. Connection Diagram: Daisy-Chain Mode (DIN = 0)

As shown in Figure 51, the device DOUT pin is driven low when DIN and CONVST are low together. With DIN low, a CONVST rising edge selects daisy-chain mode, samples the analog input, and causes the device to enter a conversion phase. In this interface option, CONVST must remain high from the start of the conversion until all data bits are read. When started, the conversion continues regardless of the state of SCLK, however SCLK must be low at the CONVST rising edge.




Figure 51. Interface Timing Diagram: For Two devices in Daisy-Chain Mode



At the end of conversion, every ADC in the chain loads its own conversion result into the internal, 18-bit, shift register and also outputs the MSB bit of this conversion result on its own DOUT pin. All ADCs enter an acquisition phase and power-down. On every subsequent SCLK falling edge, the internal shift register of each ADC latches the data available on its DIN pin and shifts out the next bit of data on its DOUT pin. Therefore, the digital host receives the data of ADC N, followed by the data of ADC N–1, and so on (in MSB-first fashion). A total of 18 x N SCLK falling edges are required to capture the outputs of all N devices in the chain. Data are valid on both SCLK edges. Data are valid on both edges of SCLK and can be captured on either edge. However, a digital host capturing data on the SCLK falling edge can achieve a faster reading rate (provided  $t_{h\_CK\_DO}$  is acceptable).

#### **POWER SUPPLY**

The device has two separate power supplies: AVDD and DVDD. The internal circuits of the device operate on AVDD; DVDD is used for the digital interface. AVDD and DVDD can be independently set to any value within the permissible range.

Decouple the AVDD and DVDD pins with GND, using individual 1- $\mu$ F decoupling capacitors placed in close proximity to the pin, as shown in Figure 52.




Figure 52. Supply Decoupling

#### **POWER SAVING**

The device has an auto power-down feature that powers down the internal circuitry at the end of every conversion. Referring to Figure 53, the input signal is acquired on the sampling capacitors when the device is in a power-down state  $(t_{acq})$ ; at the same time, the result for the previous conversion is available for reading. The device powers up on the start of the next conversion. During conversion phase  $(t_{conv})$ , the device also consumes current from the reference source (connected to pin REF).

Product Folder Links: ADS8887

Copyright © 2013, Texas Instruments Incorporated






Figure 53. Power Scaling with Throughput

The conversion time,  $t_{conv}$ , is independent of the SCLK frequency. When operating the device at speeds lower than the maximum rated throughput, the conversion time,  $t_{conv}$ , does not change; the device spends more time in power-down state. Therefore, as shown in Figure 54, the device power consumption from the AVDD supply and the external reference source is directly proportional to the speed of operation. Extremely low AVDD power-down current (50 nA, typical) and extremely low external reference leakage current (250 nA, typical), make this device ideal for very low throughput applications (such as pulsed measurements).




Figure 54. Power Scaling with Throughput



#### **APPLICATION INFORMATION**

The two primary circuits required to maximize the performance of a high-precision, successive approximation register (SAR), analog-to-digital converter (ADC) are the input driver and the reference driver circuits. This section details some general principles for designing these circuits, followed by some application circuits designed using the ADS8887.

#### **ADC REFERENCE DRIVER**

The external reference source to the ADS8887 must provide low-drift and very accurate voltage for the ADC reference input and support the dynamic charge requirements without affecting the noise and linearity performance of the device. The output broadband noise of most references can be in the order of a few 100  $\mu$ V<sub>RMS</sub>. Therefore, to prevent any degradation in the noise performance of the ADC, the output of the voltage reference must be appropriately filtered by using a low-pass filter with a cutoff frequency of a few hundred Hertz.

After band-limiting the noise of the reference circuit, the next important step is to design a reference buffer that can drive the dynamic load posed by the reference input of the ADC. The reference buffer must regulate the voltage at the reference pin such that the value of  $V_{REF}$  stays within the 1-LSB error at the start of each conversion. This condition necessitates the use of a large capacitor,  $C_{BUF\_FLT}$  (refer to Figure 42) for regulating the voltage at the reference input of the ADC. The amplifier selected to drive the reference pin should have an extremely low offset and temperature drift with a low output impedance to drive the capacitor at the ADC reference pin without any stability issues.

#### Reference Driver Circuit for V<sub>REF</sub> = 4.5 V

The application circuit in Figure 55 shows the schematic of a complete reference driver circuit that generates a voltage of 4.5 V dc using a single 5-V supply. This circuit is suitable to drive the reference of the ADS8887 at higher sampling rates up to 100 kSPS. The 4.5-V reference voltage in this design is generated by the high-precision, low-noise REF5045 circuit. The output broadband noise of the reference is heavily filtered by a low-pass filter with a 3-dB cutoff frequency of 160 Hz.




Figure 55. Schematic of Reference Driver Circuit with  $V_{REF} = 4.5 \text{ V}$ 

The reference buffer is designed with the THS4281 and OPA333 in a composite architecture to achieve superior dc and ac performance at a reduced power consumption, compared to using a single high-performance amplifier. The THS4281 is a high-bandwidth amplifier with a very low output impedance of 1  $\Omega$  at a frequency of 1 MHz. The low output impedance makes the THS4281 a good choice for driving a high capacitive load to regulate the voltage at the reference input of the ADC. The high offset and drift specifications of the THS4281 are corrected by using a dc-correcting amplifier (OPA333) inside the feedback loop. The composite scheme inherits the extremely low offset and temperature drift specifications of the OPA333.



For step-by-step design procedure, circuit schematics, bill of materials, PCB files, simulation results, and test results, using a similar device, refer to 18-Bit Data Acquisition (DAQ) Block Optimized for 1-µs Full-Scale Step Response (SLAU512).

www.ti.com

# Reference Driver Circuit for V<sub>REF</sub> = 2.5 V in Ultralow Power, Lower Throughput Applications

The application circuit in shows the schematic of a complete reference driver circuit that generates a voltage of 2.5 V dc using a single 3.3-V supply. This ultralow power reference block is suitable to drive the ADS8887 for power-sensitive applications at a relatively lower throughput. This design uses the high-precision REF3325 circuit that provides an accurate 2.5-V reference voltage at an extremely low quiescent current of 5  $\mu$ A. The output broadband noise of the reference is heavily filtered by a low-pass filter with a 3-dB cutoff frequency of 16 Hz.

The reference buffer is designed using the low-power OPA333 that can operate from a 3.3-V supply at an extremely low quiescent current of 28  $\mu$ A. The wideband noise contribution from the amplifier is limited by a low-pass filter of a cutoff frequency equal to 1.5 kHz, formed by a 4.7- $\Omega$  resistor in combination with a 22- $\mu$ F capacitor. The 4.7- $\Omega$  series resistor creates an additional drop in the reference voltage, which is corrected by a dual-feedback configuration.



For step-by-step design procedure, circuit schematics, bill of materials, PCB files, simulation results, and test results, using a similar device, refer to 18-Bit, 10kSPS Data Acquisition (DAQ) Block Optimized for Ultra Low Power < 1mW (SLAU514).

(3)



#### **ADC INPUT DRIVER**

The input driver circuit for a high-precision ADC mainly consists of two parts: a driving amplifier and a fly-wheel RC filter. The amplifier is used for signal conditioning of the input voltage and its low output impedance provides a buffer between the signal source and the switched capacitor inputs of the ADC. The RC filter helps attenuate the sampling charge injection from the switched-capacitor input stage of the ADC and functions as an antialiasing filter to band-limit the wideband noise contributed by the front-end circuit. Careful design of the front-end circuit is critical to meet the linearity and noise performance of a high-precision, 18-bit ADC such as the ADS8887.

#### Input Amplifier Selection

Selection criteria for the input amplifiers is highly dependent on the input signal type as well as the performance goals of the data acquisition system. Some key amplifier specifications to consider while selecting an appropriate amplifier to drive the inputs of the ADC are:

• Small-signal bandwidth. Select the small-signal bandwidth of the input amplifiers to be as high as possible after meeting the power budget of the system. Higher bandwidth reduces the closed-loop output impedance of the amplifier, thus allowing the amplifier to more easily drive the low cutoff frequency RC filter (refer to the Antialiasing Filter section) at the inputs of the ADC. Higher bandwidth also minimizes the harmonic distortion at higher input frequencies. In order to maintain the overall stability of the input driver circuit, the amplifier bandwidth should be selected as described in Equation 2:

Unity – Gain Bandwidth 
$$\geq 4 \times \left(\frac{1}{2\pi \times R_{FLT} \times C_{FLT}}\right)$$
 (2)

Noise. Noise contribution of the front-end amplifiers should be as low as possible to prevent any degradation
in SNR performance of the system. As a rule of thumb, to ensure that the noise performance of the data
acquisition system is not limited by the front-end circuit, the total noise contribution from the front-end circuit
should be kept below 20% of the input-referred noise of the ADC. Noise from the input driver circuit is bandlimited by designing a low cutoff frequency RC filter, as explained in Equation 3.

$$N_G \times \sqrt{2} \times \sqrt{\left(\frac{V_{1_f-AMP\_PP}}{6.6}\right)^2 + e_{n\_RMS}^2 \times \frac{\pi}{2} \times f_{-3dB}} \quad \leq \quad \frac{1}{5} \times \frac{V_{REF}}{\sqrt{2}} \times 10^{-\left(\frac{SNR(dB)}{20}\right)}$$

where:

- V<sub>1 / f AMP PP</sub> is the peak-to-peak flicker noise in μV<sub>RMS</sub>,
- e<sub>n RMS</sub> is the amplifier broadband noise density in nV/√Hz,
- f<sub>-3dB</sub> is the 3-dB bandwidth of the RC filter, and
- N<sub>G</sub> is the noise gain of the front-end circuit, which is equal to '1' in a buffer configuration.
- Distortion. Both the ADC and the input driver introduce nonlinearity in a data acquisition block. As a rule of thumb, to ensure that the distortion performance of the data acquisition system is not limited by the front-end circuit, the distortion of the input driver should be at least 10 dB lower than the distortion of the ADC, as shown in Equation 4.

$$THD_{AMP} \leq THD_{ADC} - 10 (dB)$$
(4)

Settling Time. For dc signals with fast transients that are common in a multiplexed application, the input signal
must settle within an 18-bit accuracy at the device inputs during the acquisition time window. This condition is
critical to maintain the overall linearity performance of the ADC. Typically, the amplifier data sheets specify
the output settling performance only up to 0.1% to 0.001%, which may not be sufficient for the desired 18-bit
accuracy. Therefore, the settling behavior of the input driver should always be verified by TINA™-SPICE
simulations before selecting the amplifier.

www.ti.com

#### Antialiasing Filter

Converting analog-to-digital signals requires sampling an input signal at a constant rate. Any higher frequency content in the input signal beyond half the sampling frequency is digitized and folded back into the low-frequency spectrum. This process is called *aliasing*. Therefore, an analog, antialiasing filter must be used to remove the harmonic content from the input signal before being sampled by the ADC. An antialiasing filter is designed as a low-pass, RC filter, for which the 3-dB bandwidth is optimized based on specific application requirements. For dc signals with fast transients (including multiplexed input signals), a high-bandwidth filter is designed to allow accurately settling the signal at the inputs of the ADC during the small acquisition time window. For ac signals, the filter bandwidth should be kept low to band-limit the noise fed into the input of the ADC, thereby increasing the signal-to-noise ratio (SNR) of the system.

Besides filtering the noise from the front-end drive circuitry, the RC filter also helps attenuate the sampling charge injection from the switched-capacitor input stage of the ADC. A differential capacitor,  $C_{FLT}$ , is connected across the inputs of the ADC (as shown in Figure 56). This capacitor helps reduce the sampling charge injection and provides a charge bucket to quickly charge the internal sample-and-hold capacitors during the acquisition process. As a rule of thumb, the value of this capacitor should be at least 10 times the specified value of the ADC sampling capacitance. For the ADS8887, the input sampling capacitance is equal to 59 pF, thus the value of  $C_{FLT}$  should be greater than 590 pF. The capacitor should be a COG- or NPO-type because these capacitor types have a high-Q, low-temperature coefficient, and stable electrical characteristics under varying voltages, frequency, and time.




Figure 56. Antialiasing Filter

Note that driving capacitive loads can degrade the phase margin of the input amplifiers, thus making the amplifier marginally unstable. To avoid amplifier stability issues, series isolation resistors ( $R_{FLT}$ ) are used at the output of the amplifiers. A higher value of  $R_{FLT}$  is helpful from the amplifier stability perspective, but adds distortion as a result of interactions with the nonlinear input impedance of the ADC. Distortion increases with source impedance, input signal frequency, and input signal amplitude. Therefore, the selection of  $R_{FLT}$  requires balancing the stability and distortion of the design. For the ADS8887, TI recommends limiting the value of  $R_{FLT}$  to a maximum of 22  $\Omega$  in order to avoid any significant degradation in linearity performance. The tolerance of the selected resistors can be chosen as 1% because the use of a differential capacitor at the input balances the effects resulting from any resistor mismatch.

The input amplifier bandwidth should be much higher than the cutoff frequency of the antialiasing filter. TI strongly recommends performing a SPICE simulation to confirm that the amplifier has more than 40° phase margin with the selected filter. Simulation is critical because even with high-bandwidth amplifiers, some amplifiers might require more bandwidth than others to drive similar filters. If an amplifier has less than a 40° phase margin with  $22-\Omega$  resistors, using a different amplifier with higher bandwidth or reducing the filter cutoff frequency with a larger differential capacitor is advisable.



#### **APPLICATION CIRCUIT EXAMPLES**

This section describes some common application circuits using the ADS8887. These data acquisition (DAQ) blocks are optimized for specific input types and performance requirements of the system. For simplicity, power-supply decoupling capacitors are not shown in these circuit diagrams; refer to the *Power Supply* section for suggested guidelines.

#### DAQ Circuit for a 10-µs, Full-Scale Step Response

The application circuit shown in Figure 57 is optimized for using the ADS8887 at the maximum-specified throughput of 100 kSPS for a full-scale step input voltage. Such step input signals are common in multiplexed applications when switching between different channels. In a worst-case scenario, one channel is at the negative full-scale (NFS) and the other channel is at the positive full-scale (PFS) voltage, in which case the step size is the full-scale range (FSR) of the ADC when the MUX channel is switched.

In such applications, the primary design requirement is to ensure that the full-scale step input signal settles to 18-bit accuracy at the ADC inputs. This condition is critical to achieve the excellent linearity specifications of the ADC. Therefore, the bandwidth of the antialiasing RC filter should be large enough to allow optimal settling of the input signal during the ADC acquisition time. The filter capacitor helps reduce the sampling charge injection at the ADC inputs, but degrades the phase margin of the driving amplifier, thereby leading to stability issues. Amplifier stability is maintained by the series isolation resistor. Therefore, the component values of the antialiasing filter should be carefully selected to meet the settling requirements of the system as well as to maintain the stability of the input driving amplifiers.




Figure 57. DAQ Circuit for 10-µs, Full-Scale Step Response



For step-by-step design procedure, circuit schematics, bill of materials, PCB files, simulation results, and test results, using a similar device, refer to 18-Bit Data Acquisition (DAQ) Block Optimized for 1-µs Full-Scale Step Response (SLAU512).

Submit Documentation Feedback

www.ti.com

#### Low-Power DAQ Circuit for Excellent Dynamic Performance at 100 kSPS

The application circuit shown in Figure 58 is optimized for using the ADS8887 at the maximum specified throughput of 100 kSPS for a full-scale sinusoidal signal of 1-kHz frequency. This circuit achieves excellent dynamic performance for the lowest power consumption. The differential ac input signal is processed through low-noise and low-power amplifiers configured as unity-gain buffers and a low-pass, RC filter before being fed into the ADC.

In such applications, the input driver must be low in power and noise as well as able to support rail-to-rail input and output swing with a single supply. A high amplifier bandwidth is also preferred to help attenuate high-frequency distortion. However, oftentimes bandwidth and noise are traded off with the power consumption of the amplifier. This circuit uses the OPA313 as the front-end driving amplifier because this device offers relatively low noise density at ultra-low quiescent currents of 50  $\mu$ A per channel.

The noise contribution from the front-end amplifier is band-limited by the 3-dB bandwidth of the RC filter, which is designed to be 30 kHz in this application. To maintain good phase margin,  $R_{FLT}$  is selected as 47  $\Omega$  instead of the 22- $\Omega$  recommended maximum. The result is a slight degradation in linearity, which is a common tradeoff for very low-power applications.




Figure 58. DAQ Circuit for Lowest Power and Excellent Dynamic Performance at 100 kSPS



For step-by-step design procedure, circuit schematics, bill of materials, PCB files, simulation results, and test results, using a similar device, refer to 18-Bit, 1-MSPS Data Acquisition (DAQ) Block Optimized for Lowest Power (SLAU513).



#### DAQ Circuit for Lowest Distortion and Noise Performance at 100 kSPS

This section describes two application circuits (Figure 59 and Figure 60) that are optimized for using the ADS8887 with lowest distortion and noise performance at a throughput of 100 kSPS. In both applications, the input signal is processed through a high-bandwidth, low-distortion, fully-differential amplifier (FDA) designed in an inverting gain configuration and a low-pass RC filter before being fed into the ADC.

As a rule of thumb, the distortion from the input driver should be at least 10 dB less than the ADC distortion. The distortion resulting from variation in the common-mode signal is eliminated by using the FDA in an inverting gain configuration that establishes a fixed common-mode level for the circuit. This configuration also eliminates the requirement of a rail-to-rail swing at the amplifier input. Therefore, these circuits use the low-power THS4521 as an input driver, which provides exceptional ac performance because of its extremely low-distortion and high-bandwidth specifications.

In addition, the components of the antialiasing filter are such that the noise from the front-end circuit is kept low without adding distortion to the input signal.

#### **Differential Input Configuration**

The circuit in Figure 59 shows a fully-differential DAQ block optimized for low distortion and noise using the THS4521 and ADS8887. This front-end circuit configuration requires a differential signal at the input of the FDA and provides a differential output to drive the ADC inputs. The common-mode voltage of the input signal provided to the ADC is set by the  $V_{\rm OCM}$  pin of the THS4521 (not shown in Figure 59). To use the complete dynamic range of the ADC,  $V_{\rm OCM}$  can be set to  $V_{\rm REF}$  / 2 by using a simple resistive divider. However, note that the ADS8887 allows the common-mode input voltage ( $V_{\rm CM}$ ) to be set to any value in the range of 0 V to  $V_{\rm REF}$ .




Figure 59. Differential Input DAQ Circuit for Lowest Distortion and Noise at 100 kSPS



For step-by-step design procedure, circuit schematics, bill of materials, PCB files, simulation results, and test results, using a similar device, refer to 18-Bit, 1-MSPS Data Acquisition (DAQ) Block Optimized for Lowest Distortion and Noise (SLAU515).

Submit Documentation Feedback



#### Single-Ended to Differential Configuration

The circuit in Figure 60 shows a single-ended to differential DAQ block optimized for low distortion and noise using the THS4521 and the ADS8887. This front-end circuit configuration requires a single-ended ac signal at the input of the FDA and provides a fully-differential output to drive the ADC inputs. The common-mode voltage of the input signal provided to the ADC is set by the  $V_{OCM}$  pin of the THS4521 (not shown in Figure 60). To use the complete dynamic range of the ADC,  $V_{OCM}$  can be set to  $V_{REF}$  / 2 by using a simple resistive divider. However, note that the ADS8887 allows the common-mode input voltage ( $V_{CM}$ ) to be set to any value in the range of 0 V to  $V_{REF}$ .




Figure 60. Single-Ended to Differential DAQ Circuit for Lowest Distortion and Noise at 100 kSPS



#### Ultralow-Power DAQ Circuit at 10 kSPS

The data acquisition circuit shown in Figure 61 is optimized for using the ADS8887 at a reduced throughput of 10 kSPS with ultralow-power consumption (< 1 mW) targeted at portable and battery-powered applications.

In order to save power, this circuit is operated on a single 3.3-V supply. The circuit uses extremely low-power, dual amplifiers (such as the OPA2333) with a maximum quiescent current of 28  $\mu$ A per channel to drive the ADC inputs. The input amplifiers are configured in a modified unity-gain buffer configuration. The filter capacitor at the ADC inputs attenuates the sampling charge-injection noise from the ADC but effects the stability of the input amplifiers by degrading the phase margin. This attenuation requires a series isolation resistor to maintain amplifier stability. The value of the series resistor is directly proportional to the open-loop output impedance of the driving amplifier to maintain stability, which is high (in the order of k $\Omega$ ) in the case of low-power amplifiers such as the OPA333. Therefore, a high value of 1 k $\Omega$  is selected for the series resistor at the ADC inputs. However, this series resistor creates an additional voltage drop in the signal path, thereby leading to linearity and distortion issues. The dual-feedback configuration used in Figure 61 corrects for this additional voltage drop and maintains system performance at ultralow-power consumption.




Figure 61. Ultralow-Power DAQ Circuit at 10 kSPS



For step-by-step design procedure, circuit schematics, bill of materials, PCB files, simulation results, and test results, using a similar device, refer to 18-Bit, 10kSPS Data Acquisition (DAQ) Block Optimized for Ultra Low Power < 1mW (SLAU514).

Submit Documentation Feedback

#### www.ti.com

# **REVISION HISTORY**

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

| CI | hanges from Original (May 2013) to Revision A                                      | Page |
|----|--|------|
| •  | Changed Wide Common-Mode Voltage Range Features bullet                             | 1    |
| •  | Changed sub-bullets of AC and DC Performance Features bullet                       | 1    |
| •  | Changed Full-Scale Step Settling Features bullet                                   | 1    |
| •  | Deleted last two Applications bullets  | 1    |
| •  | Changed Description section  | 1    |
| •  | Changed front page graphic   | 1    |
|    | Added Family Information, Absolute Maximum Ratings, and Thermal Information tables |      |
| •  | Added Electrical Characteristics table   | 3    |
| •  | Added Timing Characteristics section   | 5    |
| •  | Added Pin Configurations section   | 9    |
| •  | Added Typical Characteristics section  | 10   |
| •  | Added Overview section   | 16   |
| •  | Added Application Information section  | 26   |





30-Sep-2014

#### **PACKAGING INFORMATION**

| Orderable Device | Status | Package Type | Package<br>Drawing | Pins | Package<br>Qty | Eco Plan                   | Lead/Ball Finish | MSL Peak Temp       | Op Temp (°C) | Device Marking<br>(4/5) | Samples |
|------------------|--------|--------------|--------------------|------|----------------|----------------------------|------------------|---------------------|--------------|-------------------------|---------|
| ADS8887IDGS      | ACTIVE | VSSOP        | DGS                | 10   | 80             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU        | Level-2-260C-1 YEAR | -40 to 85    | 8887                    | Samples |
| ADS8887IDGSR     | ACTIVE | VSSOP        | DGS                | 10   | 2500           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU        | Level-2-260C-1 YEAR | -40 to 85    | 8887                    | Samples |
| ADS8887IDRCR     | ACTIVE | VSON         | DRC                | 10   | 3000           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU        | Level-2-260C-1 YEAR | -40 to 85    | 8887                    | Samples |
| ADS8887IDRCT     | ACTIVE | VSON         | DRC                | 10   | 250            | Green (RoHS<br>& no Sb/Br) | CU NIPDAU        | Level-2-260C-1 YEAR | -40 to 85    | 8887                    | Samples |

(1) The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.

TBD: The Pb-Free/Green conversion plan has not been defined.

**Pb-Free (RoHS):** TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

Pb-Free (RoHS Exempt): This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead/Ball Finish Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.



# PACKAGE OPTION ADDENDUM

30-Sep-2014

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

# PACKAGE MATERIALS INFORMATION

www.ti.com 3-Aug-2017

# TAPE AND REEL INFORMATION



# TAPE DIMENSIONS KO P1 BO Cavity A0

|    | Dimension designed to accommodate the component width     |
|----|---|
|    | Dimension designed to accommodate the component length    |
| K0 | Dimension designed to accommodate the component thickness |
| W  | Overall width of the carrier tape                         |
| P1 | Pitch between successive cavity centers                   |

#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



#### \*All dimensions are nominal

| All difficulties are norminal |                 |                    |    |      |                          |                          |            |            |            |            |           |                  |
|-------------------------------|-----------------|--------------------|----|------|--------------------------|--------------------------|------------|------------|------------|------------|-----------|------------------|
| Device                        | Package<br>Type | Package<br>Drawing |    | SPQ  | Reel<br>Diameter<br>(mm) | Reel<br>Width<br>W1 (mm) | A0<br>(mm) | B0<br>(mm) | K0<br>(mm) | P1<br>(mm) | W<br>(mm) | Pin1<br>Quadrant |
| ADS8887IDGSR                  | VSSOP           | DGS                | 10 | 2500 | 330.0                    | 12.4                     | 5.3        | 3.4        | 1.4        | 8.0        | 12.0      | Q1               |
| ADS8887IDRCR                  | VSON            | DRC                | 10 | 3000 | 330.0                    | 12.4                     | 3.3        | 3.3        | 1.1        | 8.0        | 12.0      | Q2               |
| ADS8887IDRCT                  | VSON            | DRC                | 10 | 250  | 180.0                    | 12.4                     | 3.3        | 3.3        | 1.1        | 8.0        | 12.0      | Q2               |

**PACKAGE MATERIALS INFORMATION** 

www.ti.com 3-Aug-2017



\*All dimensions are nominal

| 7 till dillitorionomo di o mominidi |              |                 |      |      |             |            |             |  |
|-------------------------------------|--------------|-----------------|------|------|-------------|------------|-------------|--|
| Device                              | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |  |
| ADS8887IDGSR                        | VSSOP        | DGS             | 10   | 2500 | 367.0       | 367.0      | 35.0        |  |
| ADS8887IDRCR                        | VSON         | DRC             | 10   | 3000 | 367.0       | 367.0      | 35.0        |  |
| ADS8887IDRCT                        | VSON         | DRC             | 10   | 250  | 210.0       | 185.0      | 35.0        |  |



- NOTES: A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M-1994.
  - B. This drawing is subject to change without notice.
  - C. Small Outline No-Lead (SON) package configuration.
  - D. The package thermal pad must be soldered to the board for thermal and mechanical performance, if present.
  - E. See the additional figure in the Product Data Sheet for details regarding the exposed thermal pad features and dimensions, if present



# DRC (S-PVSON-N10)


# PLASTIC SMALL OUTLINE NO-LEAD

#### THERMAL INFORMATION

This package incorporates an exposed thermal pad that is designed to be attached directly to an external heatsink. The thermal pad must be soldered directly to the printed circuit board (PCB). After soldering, the PCB can be used as a heatsink. In addition, through the use of thermal vias, the thermal pad can be attached directly to the appropriate copper plane shown in the electrical schematic for the device, or alternatively, can be attached to a special heatsink structure designed into the PCB. This design optimizes the heat transfer from the integrated circuit (IC).

For information on the Quad Flatpack No—Lead (QFN) package and its advantages, refer to Application Report, QFN/SON PCB Attachment, Texas Instruments Literature No. SLUA271. This document is available at www.ti.com.

The exposed thermal pad dimensions for this package are shown in the following illustration.



NOTE: A. All linear dimensions are in millimeters

# DGS (S-PDSO-G10)

# PLASTIC SMALL-OUTLINE PACKAGE



NOTES:

- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion.
- D. Falls within JEDEC MO-187 variation BA.



# DGS (S-PDSO-G10)

# PLASTIC SMALL OUTLINE PACKAGE



#### NOTES:

- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Publication IPC-7351 is recommended for alternate designs.
- D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC-7525 for other stencil recommendations.
- E. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.



#### **IMPORTANT NOTICE**

Texas Instruments Incorporated (TI) reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete.

TI's published terms of sale for semiconductor products (http://www.ti.com/sc/docs/stdterms.htm) apply to the sale of packaged integrated circuit products that TI has qualified and released to market. Additional terms may apply to the use or sale of other types of TI products and services.

Reproduction of significant portions of TI information in TI data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such reproduced documentation. Information of third parties may be subject to additional restrictions. Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyers and others who are developing systems that incorporate TI products (collectively, "Designers") understand and agree that Designers remain responsible for using their independent analysis, evaluation and judgment in designing their applications and that Designers have full and exclusive responsibility to assure the safety of Designers' applications and compliance of their applications (and of all TI products used in or for Designers' applications) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to their applications, Designer has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any applications that include TI products, Designer will thoroughly test such applications and the functionality of such TI products as used in such applications.

TI's provision of technical, application or other design advice, quality characterization, reliability data or other services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using TI Resources in any way, Designer (individually or, if Designer is acting on behalf of a company, Designer's company) agrees to use any particular TI Resource solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

Designer is authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNER AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

Unless TI has explicitly designated an individual product as meeting the requirements of a particular industry standard (e.g., ISO/TS 16949 and ISO 26262), TI is not responsible for any failure to meet such industry standard requirements.

Where TI specifically promotes products as facilitating functional safety or as compliant with industry functional safety standards, such products are intended to help enable customers to design and create their own applications that meet applicable functional safety standards and requirements. Using products in an application does not by itself establish any safety features in the application. Designers must ensure compliance with safety-related requirements and standards applicable to their applications. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equipment includes, without limitation, all medical devices identified by the U.S. Food and Drug Administration as Class III devices and equivalent classifications outside the U.S.

TI may expressly designate certain products as completing a particular qualification (e.g., Q100, Military Grade, or Enhanced Product). Designers agree that it has the necessary expertise to select the product with the appropriate qualification designation for their applications and that proper product selection is at Designers' own risk. Designers are solely responsible for compliance with all legal and regulatory requirements in connection with such selection.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's non-compliance with the terms and provisions of this Notice.