

NISSEI

SPECIFICATION

METALLIZED POLYPROPYLENE FILM CAPACITOR

TYPE MPX, MPXF, MPXC, MPXV - 450, 630V. DC

DRAWING PSC320000

PLEASE RETURN 1 COPY WITH RECEIVED STAMP.

DATE March 21, 2012

DESIGNED Y. Ootashiro

CHECKED M. Sasaki

APPROVED H. Kawagoe

NISSEI ELECTRIC CO., LTD.

120067



安全に関する注意

コンデンサを使用するに当たり、使用環境、及び取り付け環境を確認の上、納入仕様書に規定した定格性能の範囲内でご使用下さい。

納入仕様書、添付注意事項の範囲を越えて使用しますと、ショート、オープン、発煙、発火に至る場合がありますので、定格性能の範囲内であることを確認願います。

尚、納入仕様書に記載のない項目、不明な内容については、必ずお問い合わせ下さい。

又、生命に影響を与える可能性がある装置、機器（生命維持装置、航空機用制御装置、自動車用制御装置等）に使用される場合にも必ずお問い合わせ下さい。

※本仕様書は、発行日より 6 ヶ月を経過して返却されなかった場合は、受領いただけなかったものと判断し、無効とさせていただきます事ご了承願います。



Cautions About Safety In Use of Capacitors

When using a capacitor, please use one within the range of values specified in the specification after checking the environments of using and mounting.

If used beyond the range specified in the specification or the attached cautions, it may lead to short circuit, open, smoking and firing.

Be sure to inquire of us as to the items which are not specified in the specification or are unclear to you.

Also, in case of using capacitors for such equipment or apparatus as may possibly affect human lives like life-support system, aircraft and automotive control systems, etc., please never fail to inquire of us as to further details.

If this specification is not returned within six months, we consider it not to be accepted by you and will make it null and void.

Change Record


SPECIFICATION	METALLIZED POLYPROPYLENE FILM CAPACITOR	SPEC PSC320000																							
1. SCOPE																									
This specification defines general requirements for metallized POLYPROPYLENE film capacitor MPX type (hereinafter called capacitor).																									
2. PARTS NUMBER CODE SYSTEM																									
<table border="1"> <tr> <td>M</td><td>P</td><td>X</td><td></td><td>*</td><td>0</td><td>4</td><td>5</td><td>0</td><td>K</td><td>1</td><td>0</td><td>5</td><td>0</td><td>0</td><td>0</td><td>0</td><td>0</td><td>0</td><td>0</td><td>0</td><td>0</td><td>0</td> </tr> </table>			M	P	X		*	0	4	5	0	K	1	0	5	0	0	0	0	0	0	0	0	0	0
M	P	X		*	0	4	5	0	K	1	0	5	0	0	0	0	0	0	0	0	0	0			
Designation																									
MP X : Straight lead type																									
MP XF : Single-formed lead type																									
MP XC : Cut lead type																									
MP XV : Automatic vertical insertion type (Formed lead type)																									
Internal use																									
Rated DC voltage																									
450, 630 V. DC																									
Tolerance on capacitance																									
J : ± 5 %, K : ± 10 %																									
Capacitance Code																									
Capacitance value shall be given by 3-digit figure of which unit used is expressed in pF.																									
The first 2 digits are significant figures of the capacitance value, the third digit to indicate the number of additional zeros to follow the significant figure.																									
⑥ Model code (Internal use)																									
REVISIONS																									
	SIGNATURE	DATE																							
	DESIGNED <i>Y. Ootashiro</i>	<i>March 1, 2012</i>																							
	CHECKED <i>M. Sasaki</i>	<i>March 1, 2012</i>																							
	APPROVED <i>H. Kawagoe</i>	<i>March 1, 2012</i>																							



SPECIFICATION	METALLIZED POLYPROPYLENE FILM CAPACITOR	SPEC PSC320000																																														
Lead dimension / Packing mode																																																
<table border="1"> <thead> <tr> <th>Designation</th> <th colspan="4">Code</th> </tr> </thead> <tbody> <tr> <td>MPX</td> <td colspan="4">0000</td> </tr> <tr> <td rowspan="3">MPXF</td> <td>Code</td> <td>Lead spacing</td> <td>Code</td> <td>Lead spacing</td> </tr> <tr> <td>0050</td> <td>5.0 mm</td> <td>0150</td> <td>15.0 mm</td> </tr> <tr> <td>0075</td> <td>7.5 mm</td> <td>0175</td> <td>17.5 mm</td> </tr> <tr> <td>—</td> <td>—</td> <td>0225</td> <td>22.5 mm</td> </tr> <tr> <td>MPXC</td> <td colspan="4">0050</td> </tr> <tr> <td rowspan="2">MPXV</td> <td>Code</td> <td colspan="3">Style</td> </tr> <tr> <td>D210</td> <td colspan="3">3</td> </tr> <tr> <td></td> <td>0200</td> <td colspan="3">6</td> </tr> </tbody> </table>			Designation	Code				MPX	0000				MPXF	Code	Lead spacing	Code	Lead spacing	0050	5.0 mm	0150	15.0 mm	0075	7.5 mm	0175	17.5 mm	—	—	0225	22.5 mm	MPXC	0050				MPXV	Code	Style			D210	3				0200	6		
Designation	Code																																															
MPX	0000																																															
MPXF	Code	Lead spacing	Code	Lead spacing																																												
	0050	5.0 mm	0150	15.0 mm																																												
	0075	7.5 mm	0175	17.5 mm																																												
—	—	0225	22.5 mm																																													
MPXC	0050																																															
MPXV	Code	Style																																														
	D210	3																																														
	0200	6																																														
<p>3. RATING</p> <p>3.1 Operating Temperature Range : Operating temperature range to capacitors shall be $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$ (Voltage derating in case of over 85).</p> <p>3.1.1 Maximum Operating Temperature : Maximum value of capacitor's surface temperature (ambient temperature+self heating temperature rise+radiation and conduction heat from other electric supply sources) at which capacitors shall be capable of applying continuously.</p> <p>3.1.2 Minimum Operating Temperature : Minimum temperature range at which capacitors shall be capable of applying continuously.</p> <p>3.2 Rated voltage : The rated voltage shall be the voltage which can be continuously applied to a capacitor within the range of the working temperature and shall be 450 and 630V.DC. However, rated voltage shall be derated 1.5% at each 1 in the range of $+85^{\circ}\text{C} \sim +105^{\circ}\text{C}$ as shown in the Fig. below.</p>																																																
<table border="1"> <caption>Data points estimated from the graph</caption> <thead> <tr> <th>Temperature (°C)</th> <th>Rated Voltage Derating Ratio (%)</th> </tr> </thead> <tbody> <tr><td>85</td><td>100</td></tr> <tr><td>90</td><td>90</td></tr> <tr><td>95</td><td>82</td></tr> <tr><td>100</td><td>75</td></tr> <tr><td>105</td><td>70</td></tr> </tbody> </table>			Temperature (°C)	Rated Voltage Derating Ratio (%)	85	100	90	90	95	82	100	75	105	70																																		
Temperature (°C)	Rated Voltage Derating Ratio (%)																																															
85	100																																															
90	90																																															
95	82																																															
100	75																																															
105	70																																															
<p>3.3 Capacitance range</p> <p>450V. DC : $0.10 \sim 2.2 \mu\text{F}$ (E-12)</p> <p>630V. DC : $0.10 \sim 2.2 \mu\text{F}$ (E-12)</p> <p>3.4 Tolerance on capacitance</p> <p>$\pm 5\%$, $\pm 10\%$</p>																																																

SPECIFICATION	METALLIZED POLYPROPYLENE FILM CAPACITOR	SPEC PSC320000
<p>4. CONSTRUCTION OF CAPACITOR</p> <p>Capacitor shall be non-inductive wound construction with dielectric of metallized Polypropylene film, and wire lead shall be connected to capacitor element.</p> <p>An exterior coating shall be given damp-proofing and insulation treatments by using a flame-retardant epoxy resin (Recognized UL94V-0).</p> <p>Capacitor element (Metallized Polypropylene film)</p> <p>Metal Spray (Sn base alloy)</p> <p>Lead wire (Tinned copper-covered wire)</p> <p>Epoxy resin</p> <p>Flame retardant epoxy resin</p>		

5. DIMENSIONS

Dimensions are specified in the attached sheet.

SPECIFICATION	METALLIZED POLYPROPYLENE FILM CAPACITOR	SPEC PSC320000																								
6. MARKING																										
6.1 Marking item																										
The capacitors shall be marked clearly by an indelible way.																										
1) Nominal capacitance Shall be marked with 3-digit code. Exp) 474, 105																										
2) Tolerance on capacitance J, K																										
3) Production date code																										
Marking(Year) : It shall be indicated by the alphabet except G, I, O, Q, Y, Z.																										
<table border="1"> <thead> <tr> <th>Year</th><th>2010</th><th>2011</th><th>2012</th><th>2013</th><th>2014</th><th>2015</th><th>2016</th><th>2017</th><th>2018</th><th>2019</th><th>2020</th></tr> <tr> <th>Code</th><td>A</td><td>B</td><td>C</td><td>D</td><td>E</td><td>F</td><td>H</td><td>J</td><td>K</td><td>L</td><td>M</td></tr> </thead> </table>	Year	2010	2011	2012	2013	2014	2015	2016	2017	2018	2019	2020	Code	A	B	C	D	E	F	H	J	K	L	M		
Year	2010	2011	2012	2013	2014	2015	2016	2017	2018	2019	2020															
Code	A	B	C	D	E	F	H	J	K	L	M															
Marking(Month)																										
<table border="1"> <thead> <tr> <th>Month</th><th>1</th><th>2</th><th>3</th><th>4</th><th>5</th><th>6</th><th>7</th><th>8</th><th>9</th><th>10</th><th>11</th><th>12</th></tr> <tr> <th>Code</th><td>1</td><td>2</td><td>3</td><td>4</td><td>5</td><td>6</td><td>7</td><td>8</td><td>9</td><td>O</td><td>N</td><td>D</td></tr> </thead> </table>	Month	1	2	3	4	5	6	7	8	9	10	11	12	Code	1	2	3	4	5	6	7	8	9	O	N	D
Month	1	2	3	4	5	6	7	8	9	10	11	12														
Code	1	2	3	4	5	6	7	8	9	O	N	D														
Marking(Week)																										
<table border="1"> <thead> <tr> <th>Week</th><th>1</th><th>2</th><th>3</th><th>4</th><th>5</th><th>6</th></tr> <tr> <th>Code</th><td>1</td><td>2</td><td>3</td><td>4</td><td>5</td><td>6</td></tr> </thead> </table>	Week	1	2	3	4	5	6	Code	1	2	3	4	5	6												
Week	1	2	3	4	5	6																				
Code	1	2	3	4	5	6																				
4) Rated DC voltage Unit code V is omitted.																										
5) Manufacturer's Identification NIS																										
6.2 Marking position																										
(Example)																										
	105K450	NIS B92																								

SPECIFICATION	METALLIZED POLYPROPYLENE FILM CAPACITOR	SPEC PSC320000																																								
7. PACKING																																										
1) Straight leads and formed leads type. The capacitors shall be put in poly-bag and packed in box marked with necessary information.																																										
Inside packing case																																										
																																										
<table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr> <th colspan="3">Dimension (mm)</th> </tr> <tr> <th>W</th> <th>L</th> <th>H</th> </tr> </thead> <tbody> <tr> <td>198</td> <td>176</td> <td>74</td> </tr> </tbody> </table>			Dimension (mm)			W	L	H	198	176	74																															
Dimension (mm)																																										
W	L	H																																								
198	176	74																																								
External packing case																																										
																																										
<table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr> <th colspan="3">Dimension (mm)</th> </tr> <tr> <th>Inside packing case quantity</th> <th>W</th> <th>L</th> </tr> </thead> <tbody> <tr> <td>2</td> <td>165</td> <td>210</td> </tr> <tr> <td>4</td> <td>210</td> <td>310</td> </tr> <tr> <td>6</td> <td>235</td> <td>410</td> </tr> <tr> <td>8</td> <td>310</td> <td>410</td> </tr> <tr> <td>12</td> <td>410</td> <td>450</td> </tr> <tr> <td></td> <td></td> <td>"</td> </tr> </tbody> </table>			Dimension (mm)			Inside packing case quantity	W	L	2	165	210	4	210	310	6	235	410	8	310	410	12	410	450			"																
Dimension (mm)																																										
Inside packing case quantity	W	L																																								
2	165	210																																								
4	210	310																																								
6	235	410																																								
8	310	410																																								
12	410	450																																								
		"																																								
Example)																																										
<table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <td colspan="6" style="padding: 2px;">CODE CUSTOMER</td> <td colspan="2" style="padding: 2px;">INSP DATE</td> <td colspan="2" style="padding: 2px;">PKG NO</td> </tr> <tr> <td colspan="6" style="padding: 2px;">PARTS NO</td> <td colspan="2" style="padding: 2px;">MACH NO</td> <td colspan="2" style="padding: 2px;">QTY/PKG</td> </tr> <tr> <td colspan="3" style="padding: 2px;">ORDER NO</td> <td colspan="3" style="padding: 2px;">LOT NO</td> <td colspan="2" style="padding: 2px;">ROHS</td> <td colspan="2" style="padding: 2px;">⑦</td> </tr> <tr> <td style="padding: 2px;">TYPE</td> <td style="padding: 2px;">⑤</td> <td style="padding: 2px;">WV</td> <td style="padding: 2px;">TOL</td> <td style="padding: 2px;">CAP</td> <td style="padding: 2px;">EDP CODE</td> <td colspan="2" style="padding: 2px;">QT (PCS)</td> <td colspan="2"></td> </tr> </table>			CODE CUSTOMER						INSP DATE		PKG NO		PARTS NO						MACH NO		QTY/PKG		ORDER NO			LOT NO			ROHS		⑦		TYPE	⑤	WV	TOL	CAP	EDP CODE	QT (PCS)			
CODE CUSTOMER						INSP DATE		PKG NO																																		
PARTS NO						MACH NO		QTY/PKG																																		
ORDER NO			LOT NO			ROHS		⑦																																		
TYPE	⑤	WV	TOL	CAP	EDP CODE	QT (PCS)																																				
CODE CUSTOMER			MACH NO			PRODUCTION COUNTRY			TOL(%)																																	
INSP DATE			ORDER NO			TYPE			CAP																																	
PARTS NO			LOT NO			W V			EDP CODE																																	
									QT(PCS)																																	
2) Automatic vertical insertion type.																																										
This is specified by the specification of automatic vertical insertion type.																																										

SPECIFICATION	METALLIZED POLYPROPYLENE FILM CAPACITOR	SPEC PSC320000

8. APPLICABLE STANDARD

Unless otherwise specified, performance and a testing method shall comply with JIS C 5101-1:2010.

9. DISUSE OF O.D.C.

No ozone depleting chemicals are used at any stage of the manufacturing process.

10. DISUSE OF PBBO, PBDPO, PBDPE, PBBs

This products does not contain PBBO, PBDPO, PBDPE, PBBs.

11. CERTAIN HAZARDOUS SUBSTANCES RESTRICTED BY RoHS DIRECTIVE

In the product, materials to which certain hazardous substances restricted by RoHS Directive (2002/95/EC) (cadmium, hexavalent chromium, mercury, lead, PBB and PBDE) are added on purpose aren't used.


12. PRODUCTION COUNTRY

- JAPAN
- CHINA

Production country shall be distinguished in the column .

Example) JP : JAPAN
 blank : CHINA

SPECIFICATION	METALLIZED POLYPROPYLENE FILM CAPACITOR	SPEC PSC320000
13. CHARACTERISTICS AND TEST CONDITIONS		
13.1 TEST CONDITIONS		
The test and measurement, unless otherwise specified, the standard range of atmospheric conditions of marking measurements and test is as follows		
Dielectric strength	Ambient temperature : 5 to 35°C	
	Relative humidity : 45 to 85%	
If there may be anydoubt on the results, measurements shall be made within the following limits.		
13.2 Electrical characteristics test	Ambient temperature : $20 \pm 2^\circ\text{C}$	
	Relative humidity : 60 to 70%	
Item	Characteristics	Test conditions
Dielectric strength	Between terminations No breakdown. However momentary breakdown is permissible.	Capacitors shall withstand 150% of rated DC voltage for 1 minute or 175% of rated DC voltage for 1~5 seconds. (Charge or discharge current : 1A max)
	Between terminations and case No breakdown.	Capacitors shall withstand 200% of rated DC voltage for 1~5 seconds.
Insulation resistance (Between terminations)	$C \leq 0.33 \mu\text{F}$ 30,000M or more ----- $C > 0.33 \mu\text{F}$ 7,500 F or more	DC voltage specified below shall be applied for 1 minute, after which measurement shall be made. Test voltage : 100V. DC
Capacitance		Capacitance shall be measured with 1kHz $\pm 20\%$, 5Vrms max.
Tangent of loss angle	0.001 or less	

SPECIFICATION	METALLIZED POLYPROPYLENE FILM CAPACITOR	SPEC PSC320000
Item	Characteristics	Test conditions
Connection of element		
	<p>There shall be no intermittent contacts or open circuiting which would result in any needle deflection on the voltage detector.</p>	<p>As in the diagramed circuit measure the variation of terminal voltage for the series resistor(R) while a weak impact is made on the test capacitor to check the bonding strength of the terminals to the capacitor.</p>  <p>C : Capacitor R : Series resistor $R() = 150/C(\mu F)$ C=Nominal capacitance μF ④ : Detector Internal impedance shall be large enough as compared with c. E : 100mV (peak value) or less</p>
13.3 Mechanical characteristics test		
Item	Characteristics	Test conditions
Tensile strength		Test capacitors shall be fixed, and unless otherwise specified, a tensile force of 10N shall be gradually applied to the axial of the leads, and then maintained for 30 ± 5 seconds.
Termination strength	<p>Tensile strength</p> <p>Without mechanical damage, such as break of terminal damage.</p> <p>Bending strength</p>	<p>The bend test shall consist of hanging a weight of 5N to the end of the leads and then rotating the capacitors 90 degrees in one direction, then to the starting point. This test shall be applied for 2.5 seconds per each time. At the same test speed, the capacitors shall be rotated 90 degrees in alternating direction, then return to the starting point.</p>

SPECIFICATION	METALLIZED POLYPROPYLENE FILM CAPACITOR		SPEC P S C 3 2 0 0 0 0
Item	Characteristics		Test conditions
Vibration resistance	There shall be no short-circuits or open-circuits in the element and state of the connection shall be stable. Moreover, There shall be no anomalies in appearance after test.		The frequency shall be varied uniformly from 10Hz to 55Hz at 0.75mm amplitude and back to 10Hz in approximately 1 minute intervals. This test shall be applied 2 hours per each direction, total 6 hours.
Solderability	At least 95% of the circumferential face of termination up to immersed level shall be covered with new solder.		Capacitor's leads shall be immersed into Flux (25% rosin) using sheltering board (Thickness : 1.5 ± 0.5 mm) from radial test, then immersed into soldering bath at 245 ± 3 for 3 ± 0.3 seconds up to the depth of 2~2.5mm from the bottom of the body. (Composition of solder : Sn96.5 Ag3 Cu0.5) Immersed and removing speed shall be 25 ± 2.5 mm/sec.
Resistance to soldering heat	Appearance	No visible damage.	
	Dielectric strength (Between terminations)	No breakdown.	
	Insulation resistance	C $\leq 0.33 \mu F$ 30,000M or more C $> 0.33 \mu F$ 7,500 F or more	Using sheltering board from the radial heat, capacitor's leads shall be immersed into soldering bath at 260 ± 5 for 10 ± 1 seconds up to the depth of 1.5~2mm from the bottom of the body.
	Tangent of loss angle	0.001 以下	
	Capacitance change	Within $\pm 3\%$ of the initial value.	
Resistance to solvent	Marking	Markings shall be legible with ease.	After immersed in isopropyl-alcohol for 30 ± 5 seconds, the condition of markings on a capacitor shall be checked.



SPECIFICATION	METALLIZED POLYPROPYLENE FILM CAPACITOR	SPEC P S C 3 2 0 0 0 0
13.4 Climatic test		
Item	Characteristics	Test conditions
Cold	Appearance	No visible damage.
	Capacitance change	Within +3, -0% of the initial value at +20°C.
Dry heat	Appearance	No visible damage.
	Insulation resistance	C \leq 0.33 μ F 50M or more C > 0.33 μ F 10 F or more
	Capacitance change	Within +0, -4% of the initial value at +20°C.
Humidity resistance (steady state)	Appearance	No visible damage.
	Dielectric strength (Between terminations)	No breakdown.
	Insulation resistance	C \leq 0.33 μ F 3,500M or more C > 0.33 μ F 1,000 F or more
	Tangent of loss angle	0.003 or less
	Capacitance change	Within $\pm 5\%$ of the initial value.
Endurance test for humidity	Appearance	No visible damage.
	Dielectric strength (Between terminations)	No breakdown.
	Insulation resistance	C \leq 0.33 μ F 3,500M or more C > 0.33 μ F 1,000 F or more
	Tangent of loss angle	0.003 or less
	Capacitance change	Within $\pm 10\%$ of the initial value.

SPECIFICATION	METALLIZED POLYPROPYLENE FILM CAPACITOR	SPEC P S C 3 2 0 0 0 0															
Endurance test for high temperature	Item	Characteristics															
	Appearance	No visible damage.															
	Dielectric strength (Between terminations)	No breakdown.															
	Insulation resistance	$C \leq 0.33 \mu F$ 3,500M or more $C > 0.33 \mu F$ 1,000 F or more															
	Tangent of loss angle	0.003 or less															
Rapid change of temperature	Capacitance change	Within $\pm 10\%$ of the initial value.															
	Appearance	No visible damage.															
	Dielectric strength (Between terminations)	No breakdown.															
	Insulation resistance	$C \leq 0.33 \mu F$ 7,000M or more $C > 0.33 \mu F$ 2,000 F or more															
	Tangent of loss angle	0.003 or less															
	Capacitance change	Within $\pm 5\%$ of the initial value.															
	The voltage of 125% of rated voltage shall be continuously applied to the capacitor through a series of 20~1,000 per 1 voltage in the test chamber at 85 ± 3 for $1,000^{+4}_{-6}$ hours. (However, for 450V.DC, 500V.DC shall be applied.)																
	After the test, the capacitor shall be left under the ordinarily condition for 1~2 hours.																
	The capacitors shall withstand 150% of rated DC voltage for 1 minute																
	The capacitor put into the test chamber and continuously left for the specified duration at each temperature of the step 1 to 4 given in Table 1. This operation is considered as 1 cycle and 5 cycles shall be continuously repeated. After the test, the capacitor shall be left under the ordinarily condition for 1~2 hours.																
Table 1																	
<table border="1"> <thead> <tr> <th>Step</th><th>Temperature</th><th>Maintaind time</th></tr> </thead> <tbody> <tr> <td>1</td><td>$-40^{+0}_{-3}^{\circ}\text{C}$</td><td>$30 \pm 3$ minuites</td></tr> <tr> <td>2</td><td>Normal temperature</td><td>3 minutes max</td></tr> <tr> <td>3</td><td>$+85^{+3}_{-0}^{\circ}\text{C}$</td><td>$30 \pm 3$ minuites</td></tr> <tr> <td>4</td><td>Normal temperature</td><td>3 minutes max</td></tr> </tbody> </table>			Step	Temperature	Maintaind time	1	$-40^{+0}_{-3}^{\circ}\text{C}$	30 ± 3 minuites	2	Normal temperature	3 minutes max	3	$+85^{+3}_{-0}^{\circ}\text{C}$	30 ± 3 minuites	4	Normal temperature	3 minutes max
Step	Temperature	Maintaind time															
1	$-40^{+0}_{-3}^{\circ}\text{C}$	30 ± 3 minuites															
2	Normal temperature	3 minutes max															
3	$+85^{+3}_{-0}^{\circ}\text{C}$	30 ± 3 minuites															
4	Normal temperature	3 minutes max															

SPECIFICATION	METALLIZED POLYPROPYLENE FILM CAPACITOR	SPEC PSC320000			
14. REGULATION IN USAGE					
14.1 Permissible voltage					
When containing a portion of D.C.Bias, the crasy value (peak voltage V_{o-p}) waveform shall not exceed the rated voltage.					
14.2 Permissible current to frequency					
A permissible current is regilated by both a root-mean-square value current and a peak current. A root-mean-square value current is to be a permissible current value to frequency attached. A permissible peak current is determined by a permissible peak current value attached.					
The values of continuous peak current in the allowable peak current shall be those of continuous current, and the values of single peak current shall be those of discontinuous current such as rush current in switching on or off. The highest number of times of single peak current shall be limited to 10,000 times. (In case of exceeding 10,000 times, please contact us.)					
Permissible Peak Current (Pulse Current)					
Capacitance Symbol	Capacitance (μF)	450V.DC		630V.DC	
		Single (A_{o-p})	Continual (A_{o-p})	Single (A_{o-p})	Continual (A_{o-p})
104	0.10	10.08	1.43	19.20	2.70
124	0.12	12.96	1.72	23.04	3.23
154	0.15	16.20	2.15	28.80	4.04
184	0.18	19.44	2.58	34.56	4.85
224	0.22	23.76	3.15	42.24	5.93
274	0.27	29.16	3.87	27.27	3.81
334	0.33	35.64	4.73	33.33	4.66
394	0.39	42.12	5.59	39.39	5.51
474	0.47	28.91	3.81	47.47	6.64
564	0.56	34.44	4.54	56.56	7.91
684	0.68	41.82	5.51	68.68	9.60
824	0.82	50.43	6.64	48.38	6.95
105	1.0	61.50	8.10	59.00	8.47
125	1.2	73.80	9.72	70.80	10.17
155	1.5	55.50	7.56	88.50	12.71
185	1.8	66.60	9.07	106.20	15.25
225	2.2	81.40	11.08	129.80	18.64


Furtermore, when used beyond 85~105°C at temperature of capacitor surface, derate the permissible current rated as shown below.

Temperature (°C)	Percentage (%)
85	100
90	90
95	82
100	75
105	71

SPECIFICATION	METALLIZED POLYPROPYLENE FILM CAPACITOR	SPEC PSC320000												
<p>14.3 Soldering</p> <p>When soldering a capacitor, heat in soldering is conducted to the elements of the capacitor from lead wire and an enclosure, and hence it should be noted that soldering under high temperature and a long period may cause deterioration of characteristic or breakdown of capacitors.</p> <p>When mounting a capacitor together with chip components, it shall be carried out after curing an adhesive for chip components.</p> <p>(1) When subjecting a capacitor to flow soldering</p> <p>Using a capacitor with formed leads is recommended when subjecting a capacitor to flow soldering.</p> <p>When using a capacitor with straight leads or using a capacitor under the following circumstances for reasons of mounting, the temperature of the capacitor's innards in soldering (temperature of the point of measurement shown below) shall be 140°C or less.</p> <ul style="list-style-type: none"> • When using a double-sided through-hole substrate. • Where other components are installed around a capacitor and heat is trapped. • When mounting a capacitor in a place near the edge of a substrate.  <p>※Temperature measurements shall be made by inserting by about 2mm the tip of a thermo couple having a diameter of 0.2mm or less into a hole made in an outer covering.</p> <p>Preheating condition : 120°C, for one minute</p>  <table border="1"> <caption>Data points estimated from the graph</caption> <thead> <tr> <th>Soldering time (sec.)</th> <th>Solder temperature (°C)</th> </tr> </thead> <tbody> <tr><td>0</td><td>260</td></tr> <tr><td>5</td><td>260</td></tr> <tr><td>6</td><td>255</td></tr> <tr><td>7</td><td>245</td></tr> <tr><td>8</td><td>230</td></tr> <tr><td>8.2</td><td>220</td></tr> </tbody> </table> <p>(2) When using soldering iron</p> <p>Iron tip temperature less than 350°C Soldering time (sec.) within 3 seconds</p> <p>(3) When soldering a capacitor mounted on the board with chip-type components</p> <p>Please avoid mounting a capacitor with chip-type components on a printed circuit board because the application of hardening heat for bonding chip components shall cause deterioration of the dielectric film.</p>	Soldering time (sec.)	Solder temperature (°C)	0	260	5	260	6	255	7	245	8	230	8.2	220
Soldering time (sec.)	Solder temperature (°C)													
0	260													
5	260													
6	255													
7	245													
8	230													
8.2	220													


周波数に対する許容電流特性

CHARACTERISTICS OF PERMISSIBLE CURRENT TO FREQUENCY



周波数に対する許容電流特性

CHARACTERISTICS OF PERMISSIBLE CURRENT TO FREQUENCY



SPECIFICATION


METALLIZED POLYPROPYLENE FILM CAPACITOR

SPEC


P S C 3 2 0 0 0 0

Drawing direction

- MP X : Straight lead type




- MP XC : Cut lead type





- MP XF : Single-formed lead type


«Type A »



«Type B »



SPECIFICATION	METALLIZED POLYPROPYLENE FILM CAPACITOR							SPEC									
										P S C 3 2 0 0 0 0							
MPX, MPXF, MPXC-450V.DC																	
Parts No.																	
Capacitance (μ F)	Dimensions (mm)									d							
	W	H	T	P	F	B	A	F	A								
MPX 0450 1040000	0.10	13.0	8.3	5.0	10.0	5.0	7.5	10.0	10.0	0.6							
MPX 0450 1240000	0.12	"	8.5	5.3	"	"	"	"	"	"							
MPX 0450 1540000	0.15	"	9.0	5.6	"	"	"	"	"	"							
MPX 0450 1840000	0.18	"	9.5	6.0	"	"	"	"	"	"							
MPX 0450 2240000	0.22	"	9.9	6.4	"	"	"	"	"	"							
MPX 0450 2740000	0.27	"	10.4	6.9	"	"	"	"	"	"							
MPX 0450 3340000	0.33	"	11.1	7.5	"	"	"	"	"	"							
MPX 0450 3940000	0.39	"	11.5	8.0	"	"	"	"	"	"							
MPX 0450 4740000	0.47	18.0	10.0	6.8	15.0	"	"	B	15.0	"							
MPX 0450 5640000	0.56	"	10.6	7.5	"	"	"	"	"	"							
MPX 0450 6840000	0.68	"	11.2	8.0	"	"	"	"	"	0.8							
MPX 0450 8240000	0.82	"	11.9	8.6	"	"	"	"	"	"							
MPX 0450 1050000	1.0	"	12.5	9.1	"	"	"	"	"	"							
MPX 0450 1250000	1.2	18.3	14.6	9.5	"	"	"	"	"	"							
MPX 0450 1550000	1.5	"	15.7	10.6	"	"	"	"	"	"							
MPX 0450 1850000	1.8	"	16.5	11.5	"	"	"	"	"	"							
MPX 0450 2250000	2.2	"	17.8	12.6	"	"	"	"	"	"							

SPECIFICATION	METALLIZED POLYPROPYLENE FILM CAPACITOR	SPEC PSC320010				
Drawing direction						
<ul style="list-style-type: none"> • MPX : Straight lead type 						
MPX-450V.DC						
Parts	Capacitance (μ F)	Dimensions (mm)				
		W	H	T	P	d
MPX 0450J47401Z90000	0.47	13.0	12.2	8.6	10.0	0.6

SPECIFICATION	METALLIZED POLYPROPYLENE FILM CAPACITOR	SPEC No. PSC320017
<p>Drawing direction</p> <p>• MPX : Straight lead type</p>		

MPX-450V. DC



Parts No.	Capacitance (μ F)	Dimensions (mm)				
		W	H	T	P	ϕ d
MPX□□0450K4740A030000	0.47	13.0	15.3	7.0	10.0	0.6
MPX□□0450K6840A030000	0.68	"	19.0	"	"	"



SPECIFICATION	METALLIZED POLYPROPYLENE FILM CAPACITOR	SPEC No. PSC320011				
Drawing direction						
• MPX : Straight lead type						
MPX-450V. DC						
Parts No.	Capacitance (μ F)	Dimensions (mm)				
		W	H	T	P	ϕ d
MPX□□0450J105010E0000	1.0	17.8	16.0	7.0	15.0	0.8


SPECIFICATION	METALLIZED POLYPROPYLENE FILM CAPACITOR	SPEC No. PSC320013						
Drawing direction								
• MPXC : Cut lead type								
MPXC-450V. DC								
Parts No.	Capacitance (μ F)	Dimensions (mm)					Volume (mm ³)	Note
		W	H	T	P	ϕ d		
MPXC-0450J1050000P035	1.0	18.0	12.5	9.1	15.0	0.8	1500	※

※Capacitors with a volume less than 1750mm³ need not meet requirement for passive flammability.

SPECIFICATION	METALLIZED POLYPROPYLENE FILM CAPACITOR							SPEC								
									P S C 3 2 0 0 0 0							
MPX, MPXF, MPXC-630V.DC																
Parts No.	Capacitance (μ F)	Dimensions (mm)							d							
		W	H	T	P	F	F	F								
MPX 0630 1040000	0.10	18.3	9.0	5.8	15.0	5.0	B	7.5	B	15.0	A	0.6				
MPX 0630 1240000	0.12	"	9.3	6.1	"	"	"	"	"	"	"	"				
MPX 0630 1540000	0.15	"	9.9	6.8	"	"	"	"	"	"	"	"				
MPX 0630 1840000	0.18	"	10.6	7.4	"	"	"	"	"	"	"	"				
MPX 0630 2240000	0.22	"	11.6	7.6	"	"	"	"	"	"	"	"				
MPX 0630 2740000	0.27	"	12.1	8.1	"	"	"	"	"	"	"	"				
MPX 0630 3340000	0.33	"	12.7	8.8	"	"	"	"	"	"	"	0.8				
MPX 0630 3940000	0.39	"	13.4	9.3	"	"	"	"	"	"	"	"				
MPX 0630 4740000	0.47	"	14.7	9.8	"	"	"	"	"	"	"	"				
MPX 0630 5640000	0.56	"	15.5	10.8	"	"	"	"	"	"	"	"				
MPX 0630 6840000	0.68	"	16.7	11.7	"	"	"	"	"	"	"	"				
MPX 0630 8240000	0.82	"	17.7	12.6	"	"	"	"	"	"	"	"				
MPX 0630 1050000	1.0	"	19.8	13.1	"	"	"	"	"	"	"	"				
MPX 0630 1250000	1.2	25.5	18.0	11.5	22.5	17.5	B	22.5	A			"				
MPX 0630 1550000	1.5	"	19.3	12.8	"	"	"	"	"			"				
MPX 0630 1850000	1.8	"	20.7	14.0	"	"	"	"	"			"				
MPX 0630 2250000	2.2	"	22.0	15.5	"	"	"	"	"			"				

SPECIFICATION	METALLIZED POLYPROPYLENE FILM CAPACITOR	SPEC PSC320000											
SPECIFICATION OF TAPING FOR AUTOMATIC INSERTION (Type MPXV)													
<p>1. SCOPE</p> <p>This specification applies to the taping dimensions and performance required for film capacitors used in the automatic radial insertion system.</p> <p>Style of packing : Ammo pack</p>													
<p>2. TAPING DIMENSIONS</p> <table border="1"> <thead> <tr> <th>Type</th> <th>Taping style Rated voltage</th> <th>STYLE-3 (D210)</th> <th>STYLE-6 (0200)</th> </tr> </thead> <tbody> <tr> <td rowspan="2">MP X V</td> <td>450V. DC</td> <td>104~105</td> <td>104~185</td> </tr> <tr> <td>630V. DC</td> <td>104~334</td> <td>104~564</td> </tr> </tbody> </table>			Type	Taping style Rated voltage	STYLE-3 (D210)	STYLE-6 (0200)	MP X V	450V. DC	104~105	104~185	630V. DC	104~334	104~564
Type	Taping style Rated voltage	STYLE-3 (D210)	STYLE-6 (0200)										
MP X V	450V. DC	104~105	104~185										
	630V. DC	104~334	104~564										
<p>3. TAPING PERFORMANCE (to be satisfied with the following point)</p> <p>3-1. Appearance : To be no damages or cracks on components and the tape.</p> <p>3-2. Missing components : A maximum of 3 consecutive components may be missing.</p> <p>3-3. Tip of the tape : To leave the blank tape more than 4.5 feed hole pitch from the start, and the end of the tape.</p> 													
<p>3-4. Tape splicing : Tape splicing may be done with (1) or (2).</p> <p>(1) The carrier tape (include hold-down tape) shall be cut at the center of hole and hole, and spliced with tape.</p> <p>(2) The carrier tape (include hold down tape) shall be cut at the center of hole, and spliced with splicing tape.</p> 													

SPECIFICATION	METALLIZED POLYPROPYLENE FILM CAPACITOR	SPEC PSC320000								
3-5. Adhesive strength : When pulling an adhesive tape in W direction (upward) using a push-and-pull scale, adhesive strength shall be 3N or more										
										
3-6. Tensile test : When pulling a test sample by the force 10N, there shall be no gaps or breakdowns.										
										
3-7. Moisture resistance : A taped test sample shall be left in a chamber with a temperature of 40°C and RH95% for 96 hours. Then after being left for one hour at room temperature the test sample shall be submitted to a tensile test of item 3.6.										
3-8. Temperature cycling test : A test sample shall be submitted to 5 cycles of temperature cycling test. One cycle consists of : 2 hours at -40°C 2 hours at +85°C Then after being left for one hour at room temperature, the test sample shall be submitted to a tensile test of item 3.6.										
4. BOX DIMENSIONS										
(Unit : mm)										
<table border="1"> <thead> <tr> <th>Type</th> <th>A</th> <th>B</th> <th>T</th> </tr> </thead> <tbody> <tr> <td>e</td> <td>330 ± 7</td> <td>330 ± 7</td> <td>55 ± 5</td> </tr> </tbody> </table>			Type	A	B	T	e	330 ± 7	330 ± 7	55 ± 5
Type	A	B	T							
e	330 ± 7	330 ± 7	55 ± 5							

SPECIFICATION	METALLIZED POLYPROPYLENE FILM CAPACITOR	SPEC PSC320000																												
5. STYLE OF PACKING (Ammo pack)																														
5-1. Packaging																														
<ul style="list-style-type: none"> * Fold the tape in the cardboard box, with hold-down tape turning up against an outlet opening. * Thread the feed hole with a axle and fix the tape. 																														
																														
5-2. Marking																														
The following particulars shall be labelled on the surface of a box.																														
Example)																														
<table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <td colspan="5" style="padding: 2px;">CODE CUSTOMER</td> <td style="padding: 2px;">INSP DATE</td> <td style="padding: 2px;">PKG NO</td> </tr> <tr> <td colspan="5" style="padding: 2px;">PARTS NO</td> <td style="padding: 2px;">MACH NO</td> <td style="padding: 2px;">QTY/PKG</td> </tr> <tr> <td colspan="2" style="padding: 2px;">ORDER NO</td> <td style="padding: 2px;">LOT NO</td> <td style="padding: 2px;">(5)</td> <td style="padding: 2px;">(6)</td> <td style="padding: 2px;">ROHS</td> <td style="padding: 2px;">(7)</td> </tr> <tr> <td style="padding: 2px;">TYPE</td> <td style="padding: 2px;">WV</td> <td style="padding: 2px;">TOL</td> <td style="padding: 2px;">CAP</td> <td style="padding: 2px;">EDP CODE</td> <td colspan="2" style="padding: 2px;">QT (PCS)</td> </tr> </table>			CODE CUSTOMER					INSP DATE	PKG NO	PARTS NO					MACH NO	QTY/PKG	ORDER NO		LOT NO	(5)	(6)	ROHS	(7)	TYPE	WV	TOL	CAP	EDP CODE	QT (PCS)	
CODE CUSTOMER					INSP DATE	PKG NO																								
PARTS NO					MACH NO	QTY/PKG																								
ORDER NO		LOT NO	(5)	(6)	ROHS	(7)																								
TYPE	WV	TOL	CAP	EDP CODE	QT (PCS)																									
CODE CUSTOMER	MACH NO	PRODUCTION COUNTRY	TOL(%)																											
INSP DATE	ORDER NO	TYPE	CAP																											
PARTS NO	LOT NO	W V	EDP CODE																											
			QT(PCS)																											

SPECIFICATION	METALLIZED POLYPROPYLENE FILM CAPACITOR	SPEC												
		P S C 3 2 0 0 0 0												
Type M P X V														
S T Y L E - 3 (D 2 1 0)		104 ~ 105 450V. DC 104 ~ 334 630V. DC												
<p style="text-align: center;">Drawing direction</p>														
(Unit : mm)														
P	P ₀	(1) P ₁	(1) P ₂	d	(1) F	(2) h	W	W ₀	W ₁	(3) W ₂	H	(1) H ₀	D ₀	t
25.4	12.7	3.85	6.35	0.8	5.0	0	18.0	5.0	9.0	3.0 Max	22.0 Max	16.0	4.0	0.7
±1.0	±0.3	±0.7	±1.3	±0.05	±0.8 -0.2	±2.0	±1.0 -0.5	—	±0.5	—	—	±0.5	±0.2	±0.2

(1) To be measured under the clinch-position.
 (2) To be measured the top of component.
 (3) Hold-down tape is not to exceed over the carrier tape.

SPECIFICATION	METALLIZED POLYPROPYLENE FILM CAPACITOR		SPEC											
Type MPXV STYLE - 6 (0200)	104 ~ 185	450V. DC 104 ~ 564	PSC320000											
Drawing direction →														
(Unit : mm)														
P	P _o	(1) P ₁	P ₂	d	(1) F	(2) h	W	W _o	W _i	(3) W _z	H	(1) H _o	D _o	t
30.0	15.0	3.75	7.5	0.8	7.5	0	18.0	5.0	9.0	3.0 Max	22.0 Max	16.0	4.0	0.7
±1.0	±0.3	±0.7	±1.3	±0.05	+0.8 -0.2	±2.0	+1.0 -0.5	—	±0.5	—	—	±0.5	±0.2	±0.2

- (1) To be measured under the clinch-position.
- (2) To be measured the top of component.
- (3) Hold-down tape is not to exceed over the carrier tape.

SPECIFICATION	METALLIZED POLYPROPYLENE FILM CAPACITOR	SPEC PSC320000
---------------	---	-------------------

Packing quantity

MPXV-450V. DC (Unit : pcs)

Capacitance (μ F)	STYLE-3 (D210)	STYLE-6 (0200)
0.10	500	500
0.12	"	"
0.15	"	"
0.18	"	400
0.22	"	"
0.27	"	"
0.33	400	300
0.39	"	"
0.47	500	400
0.56	400	300
0.68	"	"
0.82	"	"
1.0	300	"
1.2		"
1.5		200
1.8		"

MPXV-630V. DC (Unit : pcs)

Capacitance (μ F)	STYLE-3 (D210)	STYLE-6 (0200)
0.10	500	500
0.12	"	"
0.15	"	400
0.18	400	"
0.22	"	"
0.27	"	300
0.33	"	"
0.39		"
0.47		"
0.56		200



Cautions about safety In use of Capacitors

(MPX type)

Registry

HWC 3 2 0 0 0 0

Rev.

0 1

Sheet

1 / 2

When using a capacitor, please use one within the range of the specified values in the specification after checking the environments of using and mounting.

If used beyond the range specified in the specification or the attached cautions, it may lead to short circuit, open, smoking and firing.

Be sure to inquire of us as to the items which are not specified in the specification or are unclear to you.

Also, in case of using capacitors for such equipment or apparatus as may possibly affect human lives like life-support systems, aircraft and automotive control system, etc., please never fail to inquire of us as to further details.

1. Operating temperature and humidity

- (1) In actual use, make sure that the operating temperature is within the range specified in the specification.
- (2) Even if the operating temperature is within the specified range, sudden change in the operating temperature may lead to cracks on the enclosure and result in deterioration of the insulation resistance or the increase in tangent of loss angle by absorbing moisture through cracks on the enclosure. Please take good care of the operating temperature.
- (3) Please avoid using a capacitor in high humidity which may lead to the condensation as much as possible.

Even if there are no cracks or damage on an enclosure, deterioration of the insulation resistance or the increase in tangent of loss angle, etc. may be caused by absorbing moisture. Therefore, please be careful when using a capacitor.

2. When using a capacitor in a circuit except a d.c. one

When using a capacitor in a circuit except a d.c. one, a capacitor shall be used below the permissible current to frequency.

When used beyond the specified values, the capacitor surface temperature may rise due to the occurrence of corona charge or self heat generation of a capacitor and it may result in a short life, the destruction of the dielectric or the lowering of the insulation resistance.

At worst smoking or firing may be led.

3. Soldering

When soldering a capacitor, heat in soldering is conducted to the inside of the capacitor through lead wires and an enclosure.

Therefore soldering at high temperature and for hours may cause deterioration of characteristics or breakdown of a capacitor.

Be sure to solder a capacitor within the range specified in the specification when soldering.

In case of soldering beyond the range recommended by us, please inquire of us as to the details in advance.

- (1) Avoid soldering over again in a short time.

When dipping again in order to correct, dipping must be applied after the temperature of a capacitor comes down to a room temperature and within twice.

- (2) Avoid any work that puts the stress on lead wires of a capacitor such as correction of the position right after soldering.

- (3) When soldering with a soldering iron, please see to it lest a soldering iron should touch the body of a capacitor directly.



Cautions about safety In use of Capacitors

(MPX type)

Registry

HWC 3 2 0 0 0 0

Rev.

0 1

Sheet

2 / 2

4. Mounting

- (1) When inserting a lead wire into the printed circuit board, the stress put on a lead wire shall be within the following range.

Bending of lead wire

When bending a lead wire vertically and then restoring straight, bending of a lead wire in the same place shall be less than two cycles. (One cycle -- bending at 90° and restoring straight)

Twisting of lead wire

Twisting of a lead wire should be carried out within a turn (a 360° turn) in total.

Pulling of lead wire

The load in pulling of a lead wire shall be less than 20N.

In case that the above stress is combined together, the value in application should be set less than half of each value.

- (2) When mounting a capacitor by force owing to the difference of the space between lead wires of a capacitor from the space between the holes on the printed circuit board, be careful.

It may cause breakage of a lead wire or cracks on coating resin.

- (3) When mounting a capacitor of large size or a capacitor on the equipment affected by vibrations, fix the body of a capacitor with resin etc. which has no effect on a capacitor.

However, resin used for fixing shall be a flame retardant and minimum.

- (4) Mount a capacitor lest it should touch other parts.

Especially in case of touching a part with self heat generation, a capacitor may deteriorate due to heat and short circuit may be easily caused owing to lowering of dielectric strength or deterioration of the insulation resistance, etc..

5. Cleaning

- (1) When using the solvents for cleaning, use alcohol derivative cleaning solvents (isopropyl alcohol, etc.).

- (2) Since a small amount of ingredient contained in flux may lead to corrosion of terminations of the capacitor or chemical change of the capacitor element, be sure to clean a printed circuit board right after soldering.

- (3) The temperature for drying after cleaning shall be less than the maximum operating temperature.

- (4) When cleaning with solvents but alcohol derivatives, please inquire of us in advance.

6. Storing and waste

- (1) Store under the conditions not exceeding -10 °C ~ +40 °C, 75%RH in the room and avoid storing in the place filled with a sudden change in the temperature, the direct sunlight or corrosive gases (hydrogen sulfide, sulfuric acid, chlorine and ammonia, etc.).

- (2) A long-term storage may cause deterioration of characteristics of a capacitor due to absorbing moisture little by little.

Therefore, be sure to use after checking its characteristics and solderability if stored for over one year.

- (3) As capacitors are classified into industrial waste, please ask experts to dispose of them.

7. The others

Please refer to "Guideline of notabilia for fixed plastic film capacitors for use in electronic equipment" published by Electronic Industries Association of Japan (EIAJ RCR-2350) unless specified in the specification.