

Sample &

Buy





SLVS640F-OCTOBER 2007-REVISED FEBRUARY 2015

# **TPD12S520 Single-Chip HDMI Receiver Port Protection and Interface Device**

Technical

Documents

### 1 Features

- IEC 61000-4-2 Level 4 ESD Protection
  - ±8-kV Contact Discharge on External Lines
- Single-Chip ESD Solution for HDMI Driver
- 12 Channel ESD Protection Diodes
- Supports All HDMI 1.3 and HDMI 1.4b Data Rates (-3 dB Frequency > 3 GHz)
- 0.8-pF Capacitance for the High Speed TMDS Lines
- 0.05-pF Matching Capacitance Between the Differential Signal Pair
- 38-Pin TSSOP Provides Seamless Layout Option with HDMI Connector
- 24-Pin WQFN Package for Space Constrained Applications
- Backdrive Protection
- Lead-Free Package

## 2 Applications

- Video Interface
- Consumer Electronics
- Displays and Digital Televisions
- Handheld Displays

## 3 Description

Tools &

Software

The TPD12S520 is a single-chip electro-static discharge (ESD) circuit protection device for the highdefinition multimedia interface (HDMI) receiver port. While providing ESD protection with transient voltage suppression (TVS) diodes, the TVS protection adds little or no additional glitch in the high-speed differential signals. The high-speed transition minimized differential signaling (TMDS) ESD protection lines add only 0.8-pF capacitance.

Support &

Community

**.**...

The low-speed control lines offer voltage-level shifting to eliminate the need for an external voltage levelshifter IC. The control line TVS diodes add 3.5-pF capacitance to the control lines. The 38-pin DBT package offers a seamless layout routing option to eliminate the routing glitch for the differential signal pairs. The DBT package pitch (0.5 mm) matches with the HDMI connector pitch. In addition, the pin mapping follows the same order as the HDMI connector pin mapping. This HDMI receiver port and interface protection device is designed specifically for HDMI receiver-interface protection. The 24-pin RMN package offers flow through routing using only two layers for highly integrated, spaceefficient full HDMI protection.

#### **Device Information**<sup>(1)</sup>

DEVICE NAME	PACKAGE	BODY SIZE (NOM)
TDD126520	TSSOP (38)	6.40 mm × 9.70 mm
1PD125520	WQFN (24)	4.50 mm × 1.50 mm

(1) For all available packages, see the orderable addendum at the end of the datasheet.



#### **Circuit Protection Scheme**

An IMPORTANT NOTICE at the end of this data sheet addresses availability, warranty, changes, use in safety-critical applications, intellectual property matters and other important disclaimers. PRODUCTION DATA.

## **Table of Contents**

Feat	ures 1							
Арр	lications 1							
Description 1								
Revision History 2								
Pin	Configuration and Functions 3							
Spe	cifications 4							
6.1	Absolute Maximum Ratings 4							
6.2	ESD Ratings 4							
6.3	Recommended Operating Conditions 4							
6.4	Thermal Information 5							
6.5	Electrical Characteristics5							
6.6	Typical Characteristics 6							
Deta	ailed Description7							
7.1	Overview							
7.2	Functional Block Diagram 7							
	Feat App Des Rev 6.1 6.2 6.3 6.4 6.5 6.6 Deta 7.1 7.2							

	7.3	Feature Description	8
	7.4	Device Functional Modes	8
8	App	ication and Implementation	9
	8.1	Application Information	9
	8.2	Typical Application	9
9	Pow	er Supply Recommendations	10
10	Lay	out	<b>1</b> 1
	10.1	Layout Guidelines	<mark>1</mark> 1
	10.2	Layout Example	<b>1</b> 1
11	Dev	ice and Documentation Support	12
	11.1	Trademarks	12
	11.2	Electrostatic Discharge Caution	12
	11.3	Glossary	12
12	Mec Infor	hanical, Packaging, and Orderable mation	12

## **4** Revision History

CI	nanges from Revision E (September 2014) to Revision F Page					
•	Added clarification to HDMI data rates	······ ·	1			
•	Added clarification to HDMI data rates	8	8			

#### Changes from Revision D (December 2013) to Revision E

Added Pin Configuration and Functions section, Handling Rating table, Feature Description section, Device Functional Modes, Application and Implementation section, Power Supply Recommendations section, Layout section, Device and Documentation Support section, and Mechanical, Packaging, and Orderable Information section ......1

#### Changes from Revision C (April 2009) to Revision D

•	Added new application to Applications section.	1
•	Added RMN Package to Datasheet.	1
•	Updated RMN Package.	1
•	Updated Pin Description Table.	4
•	Added additonal graphs to Typical Performance section.	6

8

**STRUMENTS** 

EXAS

## Page

Page



#### **TPD12S520** SLVS640F-OCTOBER 2007-REVISED FEBRUARY 2015

(TOP VIEW)

#### Pin Configuration and Functions 5





#### **Pin Functions**

NAME	PIN NO.		TYPE E	ESD	DESCRIPTION
NAME	DBT	RMN	ITPE	LEVEL	DESCRIPTION
5V_SUPPLY	1	12	PWR	2 kV <sup>(1)</sup>	Bias for TMDS protection
LV_SUPPLY	2	13	PWR	2 kV <sup>(1)</sup>	Bias for CE/DDC/HOTPLUG level shifters
GND, TMDS_GND	3, 5, 8, 11,14, 25, 28, 31, 34, 36	6, 9, 10, 14, 17	GND	NA	TMDS ESD and parasitic GND return <sup>(2)</sup>
TMDS_D2+	4, 35	18	ю	8 kV (3)	TMDS 0.8-pF ESD protection <sup>(4)</sup>
TMDS_D2-	6, 33	19	ю	8 kV <sup>(3)</sup>	TMDS 0.8-pF ESD protection <sup>(4)</sup>
TMDS_D1+	7, 32	15	ю	8 kV <sup>(3)</sup>	TMDS 0.8-pF ESD protection <sup>(4)</sup>
TMDS_D1-	9, 30	16	ю	8 kV <sup>(3)</sup>	TMDS 0.8-pF ESD protection <sup>(4)</sup>
TMDS_D0+	10, 29	8	ю	8 kV <sup>(3)</sup>	TMDS 0.8-pF ESD protection <sup>(4)</sup>
TMDS_D0-	12, 27	7	ю	8 kV <sup>(3)</sup>	TMDS 0.8-pF ESD protection <sup>(4)</sup>
TMDS_CK+	13, 26	5	ю	8 kV <sup>(3)</sup>	TMDS 0.8-pF ESD protection <sup>(4)</sup>
TMDS_CK-	15, 24	4	ю	8 kV <sup>(3)</sup>	TMDS 0.8-pF ESD protection <sup>(4)</sup>
CE_REMOTE_IN	16	20	ю	2 kV <sup>(1)</sup>	LV_SUPPLY referenced logic level into ASIC
DDC_CLK_IN	17	21	IO	2 kV <sup>(1)</sup>	LV_SUPPLY referenced logic level into ASIC
DDC_DAT_IN	18	22	ю	2 kV <sup>(1)</sup>	LV_SUPPLY referenced logic level into ASIC
HOTPLUG_DET_IN	19	23	ю	2 kV <sup>(1)</sup>	LV_SUPPLY referenced logic level into ASIC
HOTPLUG_DET_OUT	20	24	ю	8 kV <sup>(3)</sup>	5 V_SUPPLY referenced logic level out, plus 3.5-pF $ESD^{(5)}$ to connector

(1) Human body model (HBM) per MIL-STD-883, Method 3015, C<sub>DISCHARGE</sub> = 100 pF, R<sub>DISCHARGE</sub> = 1.5 kΩ, 5V\_SUPPLY and LV\_SUPPLY within recommended operating conditions, GND = 0 V, and ESD\_BYP (pin 37) and HOTPLUG\_DET\_OUT (pin 20) each bypassed with a 0.1-µF ceramic capacitor connected to GND.

These pins should be routed directly to the associated GND pins on the HDMI connector, with single-point ground vias at the connector. (2)

Standard IEC 61000-4-2, C<sub>DISCHARGE</sub> = 150 pF, R<sub>DISCHARGE</sub> = 330 Ω, 5V\_SUPPLY and LV\_SUPPLY within recommended operating (3) conditions, GND = 0 V, and ESD\_BYP (pin 37) and HOTPLUG\_DET\_OUT (pin 20) each bypassed with a 0.1-µF ceramic capacitor connected to GND.

- These two pins must be connected together inline on the PCB. (4)
- This output can be connected to an external 0.1-µF ceramic capacitor, resulting in an increased ESD withstand voltage rating. (5)

Copyright © 2007–2015, Texas Instruments Incorporated

STRUMENTS

**XAS** 

#### **Pin Functions (continued)**

	PIN NO.		TYDE	ESD	DESCRIPTION		
NAWE	DBT	RMN	TTPE	LEVEL	DESCRIPTION		
DDC_DAT_OUT	21	1	ю	8 kV <sup>(3)</sup>	5 V_SUPPLY referenced logic level out, plus 3.5-pF ESD to connector		
DDC_CLK_OUT	22	2	ю	8 kV <sup>(3)</sup>	5 V_SUPPLY referenced logic level out, plus 3.5-pF ESD to connector		
CE_REMOTE_OUT	23	3	ю	8 kV <sup>(3)</sup>	5 V_SUPPLY referenced logic level out, plus 3.5-pF ESD to connector		
ESD_BYP	37	11	Ю	2 kV <sup>(1)</sup>	ESD bypass. This pin must be connected to a 0.1- $\mu$ F ceramic capacitor.		
NC	38			NA	No connection		

## 6 Specifications

### 6.1 Absolute Maximum Ratings<sup>(1)</sup>

over operating free-air temperature range (unless otherwise noted)

		MIN	MAX	UNIT
V <sub>5V_SUPPLY</sub> V <sub>LV_SUPPLY</sub>	Supply voltage	-0.3	6	V
V <sub>I/O</sub>	DC voltage at any channel input	-0.5	6	V
T <sub>A</sub>	Operating Free Air Temperature	-40	85	°C
T <sub>stg</sub>	Storage temperature range	-65	150	°C

(1) Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions* is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

### 6.2 ESD Ratings

				VALUE	UNIT	
V <sub>(ESD)</sub>	Electrostatic discharge	Human body model (HBM), per MIL-STD- 883, Method 3015, C <sub>DISCHARGE</sub> = 100 pF, $R_{DISCHARGE} = 1.5 k\Omega^{(1)}$	See Pin Configuration and Functions	±2000	V	
		IEC 61000-4-2 Contact Discharge <sup>(2)</sup>	See Pin Configuration and Functions	±8000		

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process. Manufacturing with less than 500-V HBM is possible with the necessary precautions.

(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process. Manufacturing with less than 250-V CDM is possible with the necessary precautions.

### 6.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

		MIN	TYP	MAX	UNIT
T <sub>A</sub>	Operating free-air temperature	-40		85	°C
5V_SUPPLY	Operating supply voltage	GND	5	5.5	V
LV_SUPPLY	Bias supply voltage	1	3.3	5.5	V

4

### 6.4 Thermal Information

		TPD1	TPD12S520			
	THERMAL METRIC <sup>(1)</sup>	DBT	RMN	UNIT		
		38 PINS	24 PINS			
$R_{\thetaJA}$	Junction-to-ambient thermal resistance	83.6	80.8			
R <sub>0JC(top)</sub>	Junction-to-case (top) thermal resistance	29.8	36.4			
$R_{\theta JB}$	Junction-to-board thermal resistance	44.7	27.1	°C/W		
Ψ <sub>JT</sub>	Junction-to-top characterization parameter	2.9	1.4			
$\Psi_{JB}$	Junction-to-board characterization parameter	44.1	27.0			

(1) For more information about traditional and new thermal metrics, see the IC Package Thermal Metrics application report, SPRA953.

## 6.5 Electrical Characteristics

over operating free-air temperature range (unless otherwise noted)

	PARAMETER	TEST CONDITIONS			MIN	ТҮР	MAX	UNIT
I <sub>5V</sub>	Operating supply current	5V_SUPPLY = 5 V	5V_SUPPLY = 5 V			1	5	μA
I <sub>LV</sub>	Bias supply current	LV_SUPPLY = 3.3 V	LV_SUPPLY = 3.3 V			1	2	mA
I <sub>OFF</sub>	OFF-state leakage current, level-shifting NFET	LV_SUPPLY = 0 V	LV_SUPPLY = 0 V			0.1	1	μA
I <sub>BACK</sub> drive	Current conducted from output pins to V_SUPPLY rails when powered down	5V_SUPPLY < V <sub>CH_OUT</sub>	TMDS_D[2:0]+/-, TMDS_CK+/-, CE_REMOTE_OUT, DDC_DAT_OUT, DDC_CLK_OUT, HOTPLUG_DET_OUT			0.1	5	μΑ
V <sub>ON</sub>	Voltage drop across level-shifting NFET when ON	$LV_SUPPLY = 2.5 V, V_S = G$	LV_SUPPLY = 2.5 V, V <sub>S</sub> = GND, I <sub>DS</sub> = 3 mA			95	140	mV
V	Diado forward voltago	I <sub>F</sub> = 8 mA, Top diode			1		V	
٧F	T <sub>A</sub> = $25^{\circ}C^{(1)}$		Bottom diode			1		v
V.	Channel clamp voltage at	$TA = 25^{\circ}C^{(1)(2)}$	Positive transients			9		V
*CL	±8 kV HBM ESD	1/1 = 20 0	Negative transients			-9		v
Row	Dynamic resistance	$I = 1 A T_{1} = 25^{\circ}C^{(3)}$	Positive transients			0.6		0
INDYN	Bynamie resistance	1 = 1 / , 1 <sub>A</sub> = 25 0	Negative transients			0.5		32
I <sub>LEAK</sub>	TMDS channel leakage current	$T_{A} = 25^{\circ}C^{(1)}$				0.01	1	μA
C <sub>IN</sub> , TMDS	TMDS channel input capacitance	5V_SUPPLY= 5 V, Measured V <sub>BIAS</sub> = 2.5 V <sup>(1)</sup>	l at 1 MHz,			0.8	1.0	pF
ΔC <sub>IN</sub> , TMDS	TMDS channel input capacitance matching	$5V_SUPPLY=5 V$ , Measured $V_{BIAS} = 2.5 V^{(1)(4)}$	5V_SUPPLY= 5 V, Measured at 1 MHz, $V_{BIAS} = 2.5 V^{(1)(4)}$			0.05		pF
C <sub>MUTUAL</sub>	Mutual capacitance between signal pin and adjacent signal pin	5V_SUPPLY= 0 V, Measured at 1 MHz, $V_{BIAS} = 2.5 V^{(1)}$			0.07		pF	
	Level-shifting input	5V SLIPPLY- 0.V Moosuroo	at 100 KHz	DDC		3.5	4	
C <sub>IN</sub>	capacitance, capacitance	$V_{\text{DMO}} = 2.5 V^{(1)}$	ומנ זעט תווב,	CEC		3.5	4	pF
	to GND	V <sub>BIAS</sub> = 2.5 V V		HP		3.5	4	

(1)

This parameter is specified by design and verified by device characterization Human-Body Model (HBM) per MIL-STD-883, Method 3015,  $C_{DISCHARGE} = 100 \text{ pF}$ ,  $R_{DISCHARGE} = 1.5 \text{ k}\Omega$ These measurements performed with no external capacitor on ESD\_BYP. (2)

(3) (4)

Intrapair matching, each TMDS pair (i.e., D+, D-)

TEXAS INSTRUMENTS

**TPD12S520** SLVS640F – OCTOBER 2007 – REVISED FEBRUARY 2015

www.ti.com

## 6.6 Typical Characteristics





## 7 Detailed Description

#### 7.1 Overview

The TPD12S520 is a single-chip ESD solution for the HDMI receiver port. In many cases the core ICs, such as the scalar chipset, may not have robust ESD cells to sustain system-level ESD strikes. In these cases, the TPD12S520 provides the desired system-level ESD protection, such as the IEC61000-4-2 (Level 4) ESD, by absorbing the energy associated with the ESD strike.

While providing the ESD protection, the TPD12S520 adds little or no additional glitch in the high-speed differential signals (see Figure 7 and Figure 8). The high-speed TMDS lines add only 0.8-pF capacitance to the lines. In addition, the monolithic integrated circuit technology ensures that there is excellent matching between the two-signal pair of the differential line. This is a direct advantage over discrete ESD clamp solutions where variations between two different ESD clamps may significantly degrade the differential signal quality.

The low-speed control lines offer voltage-level shifting to eliminate the need for an external voltage level-shifter IC. The control line ESD clamps add 3.5-pF capacitance to the control lines. The 38-pin DBT package offers a seamless layout routing option to eliminate the routing glitch for the differential signal pairs. DBT package pitch (0.5 mm) matches with HDMI connector pitch. In addition, pin mapping follows the same order as the HDMI connector pin mapping. The 24-pin RMN package offers flow through routing using only two layers for highly integrated, space-efficient full HDMI protection.

#### 7.2 Functional Block Diagram





#### 7.3 Feature Description

#### 7.3.1 ±8-kV Contact ESD Protection on External Lines

In many cases, the core ICs, such as the scalar chipset, may not have robust ESD cells to sustain system-level ESD strikes. In these cases, the TPD12S520 provides the desired system-level ESD protection, such as the IEC61000-4-2 (Level 4) ESD, by absorbing the energy associated with the ESD strike.

#### 7.3.2 Single-Chip ESD Solution for HDMI Driver

TPD12S520 provides a complete ESD protection scheme for an HDMI 1.4 compliant port. The monolithic integrated circuit technology ensures that there is excellent matching between the two-signal pair of the differential line. This is a direct advantage over discrete ESD clamp solutions where variations between two different ESD clamps may significantly degrade the differential signal quality. The 38-pin DBT package offers a seamless layout routing option to eliminate the routing glitch for the differential signal pair.

#### 7.3.3 Supports All HDMI 1.3 and HDMI 1.4b Data Rates

The high-speed TMDS pins of the TPD12S520 add only 0.8 pF of capacitance to the TMDS lines. Excellent intrapair capacitance matching of 0.05 pF provides ultra low intra-pair skew. Insertion loss -3 dB point > 3 GHz provides enough bandwidth to pass all HDMI 1.4*b* TMDS data rates.

#### 7.3.4 38-Pin TSSOP Provides Seamless Layout Option With HDMI Connector

The 38-pin DBT package offers seamless layout routing option to eliminate the routing glitch for the differential signal pair. DBT package pitch (0.5 mm) matches with HDMI connector pitch. In addition, pin mapping follows the same order as the HDMI connector pin mapping. This HDMI receiver port protection and interface device is specifically designed for next-generation HDMI receiver protection.

#### 7.3.5 24-Pin WQFNPackage for Space Constrained Applications

The 24-pin RMN package offers flow through routing using only two layers for highly integrated, space-efficient full HDMI protection.

#### 7.3.6 Integrated Level Shifting for the Control Lines

The low-speed control lines offer voltage-level shifting to eliminate the need for an external voltage level-shifter IC. The control line ESD clamps add 3.5-pF capacitance to the control lines.

#### 7.3.7 Backdrive Protection

Backdrive protection is offered on the connector side pins.

#### 7.3.8 Lead-Free Package

Lead-Free Package for RoHS Compliance.

#### 7.4 Device Functional Modes

TPD12S520 is active with the conditions in the *Recommended Operating Conditions* met. The bi-directional voltage-level translators provide non-inverting level shifting from either 5V (for SDA, SCL, HPD), or 3.3 V (for CEC) on the connector side to  $V_{LV}$  on the system side. Each connector side pin has an ESD clamp that triggers when voltages are above  $V_{BR}$  or below the lower diode's  $V_f$ . During ESD events, voltages as high as ±8-kV (contact ESD) can be directed to ground via the internal diode network. Once the voltages on the protected line fall below these trigger levels (usually within 10's of nano-seconds), these pins revert to a non-conductive state.



### 8 Application and Implementation

#### NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

#### 8.1 Application Information

TPD12S520 provides IEC61000-4-2 Level 4 Contact ESD rating to the HDMI 1.4 receiver port. Integrated voltage-level shifting reduces the board space needed to implement the control lines.

#### 8.2 Typical Application

TPD12S520 is designed to protect a typical HDMI 1.4 receiver port. Refer to Figure 6 for a typical schematic. The eight TMDS data lines (D2+/-, D1+/-, D0+/-, CLK+/-) each have two pins on TPD12S520 to connect to. The TMDS data lines flow through their respective pin pairs, attaching to the passive ESD protection circuitry.



Figure 6. TPD12S520 Configured with an HDMI 1.4 Receiver Port

#### 8.2.1 Design Requirements

For this example, use the following table as input parameters:

DESIGN PARAMETERS	EXAMPLE VALUE
Voltage on 5V_SUPPLY	4.5 V - 5.5 V
Voltage on LV_SUPPLY	1.7 V - 1.9 V

#### **TPD12S520**

SLVS640F-OCTOBER 2007-REVISED FEBRUARY 2015



#### 8.2.2 Detailed Design Procedure

To begin the design process the designer needs to know the 5V\_SUPPLY voltage range and the logic level, LV\_SUPPLY, voltage range.

#### 8.2.3 Application Curves



### 9 Power Supply Recommendations

This device is designed to operate from an input voltage range of between 1.0 V and 5.5 V. This input supply should be well regulated. If the input supply is more than a few inches from TPD12S520 additional bulk capacitance may be required in addition to the ceramic bypass capacitors. Otherwise, the device is a passive ESD protection device and there is no need to power it. Care should be taken to not violate the maximum voltage specifications to ensure that the device functions properly. The 5V\_SUPPLY TVS diode can tolerate up to 6 V.



### 10 Layout

#### **10.1 Layout Guidelines**

- The optimum placement is as close to the connector as possible.
  - EMI during an ESD event can couple from the trace being struck to other nearby unprotected traces, resulting in early system failures.
  - The PCB designer needs to minimize the possibility of EMI coupling by keeping any unprotected traces away from the protected traces which are between the TVS and the connector.
- Route the protected traces as straight as possible.
- Eliminate any sharp corners on the protected traces between the TVS and the connector by using rounded corners with the largest radii possible.
  - Electric fields tend to build up on corners, increasing EMI coupling.

#### 10.2 Layout Example





Use external and internal ground planes and stitch them together with VIAs as close to the GND pins of TPD12S520 as possible. This allows for a low impedance path to ground so that the device can properly dissipate an ESD event.

## **11** Device and Documentation Support

### 11.1 Trademarks

All trademarks are the property of their respective owners.

#### **11.2 Electrostatic Discharge Caution**



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

#### 11.3 Glossary

#### SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.

### 12 Mechanical, Packaging, and Orderable Information

The following pages include mechanical packaging and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.



18-Feb-2015

## PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package	Pins	Package	Eco Plan	Lead/Ball Finish	MSL Peak Temp	Op Temp (°C)	Device Marking	Samples
	(1)		Drawing		Qty	(2)	(6)	(3)		(4/5)	
TPD12S520DBTR	ACTIVE	TSSOP	DBT	38	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-2-260C-1 YEAR	-40 to 85	PN520	Samples
TPD12S520RMNR	ACTIVE	WQFN	RMN	24	3000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-3-260C-168 HR	-40 to 85	P520S	Samples

<sup>(1)</sup> The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

**NRND:** Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW**: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.

**TBD:** The Pb-Free/Green conversion plan has not been defined.

**Pb-Free (RoHS):** TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes. **Pb-Free (RoHS Exempt):** This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between

the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

<sup>(3)</sup> MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

<sup>(4)</sup> There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

<sup>(5)</sup> Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

(6) Lead/Ball Finish - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.



## PACKAGE OPTION ADDENDUM

18-Feb-2015

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

## PACKAGE MATERIALS INFORMATION

www.ti.com

Texas Instruments

### TAPE AND REEL INFORMATION





## QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal												
Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TPD12S520DBTR	TSSOP	DBT	38	2000	330.0	16.4	6.9	10.2	1.8	12.0	16.0	Q1
TPD12S520RMNR	WQFN	RMN	24	3000	330.0	12.4	1.8	4.8	0.95	8.0	12.0	Q1

TEXAS INSTRUMENTS

www.ti.com

## PACKAGE MATERIALS INFORMATION

22-Feb-2016



\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TPD12S520DBTR	TSSOP	DBT	38	2000	367.0	367.0	38.0
TPD12S520RMNR	WQFN	RMN	24	3000	338.0	355.0	50.0

DBT (R-PDSO-G38)

PLASTIC SMALL OUTLINE



B. This drawing is subject to change without notice.

- C. Body dimensions do not include mold flash or protrusion.
- D. Falls within JEDEC MO-153.





- NOTES: A. All linear dimensions are in millimeters.
  - B. This drawing is subject to change without notice.
  - C. Publication IPC-7351 is recommended for alternate designs
  - D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC-7525.
  - E. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.



# **RMN0024A**



## **PACKAGE OUTLINE**

## WQFN - 0.8 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M. 2. This drawing is subject to change without notice.



## **RMN0024A**

# **EXAMPLE BOARD LAYOUT**

## WQFN - 0.8 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



3. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).



## **RMN0024A**

## **EXAMPLE STENCIL DESIGN**

## WQFN - 0.8 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



4. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



#### **IMPORTANT NOTICE**

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have *not* been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products		Applications	
Audio	www.ti.com/audio	Automotive and Transportation	www.ti.com/automotive
Amplifiers	amplifier.ti.com	Communications and Telecom	www.ti.com/communications
Data Converters	dataconverter.ti.com	Computers and Peripherals	www.ti.com/computers
DLP® Products	www.dlp.com	Consumer Electronics	www.ti.com/consumer-apps
DSP	dsp.ti.com	Energy and Lighting	www.ti.com/energy
Clocks and Timers	www.ti.com/clocks	Industrial	www.ti.com/industrial
Interface	interface.ti.com	Medical	www.ti.com/medical
Logic	logic.ti.com	Security	www.ti.com/security
Power Mgmt	power.ti.com	Space, Avionics and Defense	www.ti.com/space-avionics-defense
Microcontrollers	microcontroller.ti.com	Video and Imaging	www.ti.com/video
RFID	www.ti-rfid.com		
OMAP Applications Processors	www.ti.com/omap	TI E2E Community	e2e.ti.com
Wireless Connectivity	www.ti.com/wirelessconn	ectivity	

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2016, Texas Instruments Incorporated