



PC56H19 V1

Product Specification

Approval Sheet

PC56H19 V1

Product Specification

RoHS

Product	White SMD LED
Part Number	PC56H19 V1
Issue Date	2015/03/17



■ Feature




- ✓ White SMD LED (L x W x H) of 5.6 x 3.0 x 0.6 mm
- ✓ ASNI hybrid binning
- ✓ Dice Technology : InGaN
- ✓ Qualified according to JEDEC moisture sensitivity Level 3
- ✓ Environmental friendly ; RoHS compliance
- ✓ Packing : 1,000 or 2,000 pcs/reel

■ Applications

- ✓ Portable flashlight
- ✓ Reading lights
- ✓ Security / garden lighting
- ✓ General lighting
- ✓ Indoor and outdoor commercial lighting


Outline Dimension

PC56H19 V1
Product Specification



Unit: mm, Tolerance: $\pm 0.1\text{mm}$

Recommended Soldering Pad



Performance

PC56H19 V1

Product Specification

■ Electro-Optical Characteristics (Ta=25°C)

Parameter	Symbol	Condition	Min.	Typ.	Max.	Unit
Forward Voltage ⁽¹⁾	V _F	I _F = 65 mA	2.6	-	3.1	V
Color Rendering Index ⁽²⁾	R _a		80	-	-	-
View Angle	θ		-	120	-	deg
Thermal Resistance ⁽³⁾	R _{th}		-	16	-	°C/W

(1) The Forward Voltage tolerance is ±0.1V

(2) The Color Rendering Index tolerance is ±2

(3) Thermal resistance is calculated from junction to solder

■ Luminous Flux (Ta=25°C)

CCT	Condition	Rank
2600K~3700K	I _F = 65 mA	VG, H1, H2
3700K~7000K		H1, H2, I1, I2

* The luminous flux tolerance is ± 7%

■ Absolute Maximum Ratings

Parameter	Symbol	value	Unit
DC Forward Current ⁽¹⁾	I _F	180	mA
Power Dissipation	P _d	0.58	W
Pulse Forward Current ⁽²⁾	I _{FP}	300	mA
Storage Temperature	T _S	-40 ~ 100	°C
Operating Temperature	T _{opr}	-40 ~ 85	°C
Junction Temperature	T _J	120	°C
Assembly Temperature	-	260 (max. 5sec)	°C

(1) Proper current rating must be observed to maintain junction temperature below maximum at all time

(2) IFP Condition: Duty 1/10, Pulse within 10msec

Ordering Code

P C 5 6 H 1 9 1 - A 2 7 0 C 0 V G H 2 8 2 - 0 0 0

1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23
---	---	---	---	---	---	---	---	---	----	----	----	----	----	----	----	----	----	----	----	----	----	----

Item	Pos.	Code	Spec	
Model Name	1-8	PC56H191	PC56H19 V1	
CIE Center Point	9	A	ANSI 1931 on B.B.L	
CCT	10,11	27	27 = 2700K	
		30	30 = 3000K	
		35	35 = 3500K	
		40	40 = 4000K	
		50	50 = 5000K	
		57	57 = 5700K	
		65	65 = 6500K	
R9	12	0	No requirements	
CIE Bin Group ⁽¹⁾	13,14	A0	27A	
		B0	27A,27B,27C,27D,27E	
		C0	27A,27B,27C,27D,27E,27F,27G,27H,27I	
IV Bin Group	15,16,	VGH2	Bin code : VG,H1,H2	
	17,18	H1I2	Bin code : H1,H2,I1,I2	
Vf Bin Group	19,20	82	Bin code : 8,9,0,1,2	
Kitting Rules	CIE ⁽¹⁾	21	0	No requirements.
			1 ⁽²⁾	Single Bin : 27A,27B,27C,27D,27E Mixing Bin : 27F+27H,27G+27I
			2 ⁽²⁾	Single Bin : 27A Mixing Bin : 27C+27E,27B+27D,27F+27H,27G+27I
			3 ⁽²⁾	Single Bin : 27A Mixing Bin : 27C+27E,27B+27D
	IV	22	0	No requirements.
	Vf	23	0	No requirements.

(1) The first two digits 27 means CCT in 2700K, can be replaced to 30, 35, 40, 50, 57, 65 for different CCT requirements.

(2) Only under an agreement between customer and Lextar Electronics, kitting rules besides "0" can be supplied.

■ **Standard Ordering Code:**

CCT	Ordering Code ⁽¹⁾	CIE Bin Group	IV Bin Group	Vf Bin Group
2700K	PC56H191-A270A0VGH282-000	A0		
	PC56H191-A270B0VGH282-000	B0	VG,H1,H2	8,9,0,1,2
	PC56H191-A270C0VGH282-000	C0		
3000K	PC56H191-A300A0VGH282-000	A0		
	PC56H191-A300B0VGH282-000	B0	VG,H1,H2	8,9,0,1,2
	PC56H191-A300C0VGH282-000	C0		
3500K	PC56H191-A350A0VGH282-000	A0		
	PC56H191-A350B0VGH282-000	B0	VG,H1,H2	8,9,0,1,2
	PC56H191-A350C0VGH282-000	C0		
4000K	PC56H191-A400A0H1I282-000	A0		
	PC56H191-A400B0H1I282-000	B0	H1,H2,I1,I2	8,9,0,1,2
	PC56H191-A400C0H1I282-000	C0		
5000K	PC56H191-A500A0H1I282-000	A0		
	PC56H191-A500B0H1I282-000	B0	H1,H2,I1,I2	8,9,0,1,2
	PC56H191-A500C0H1I282-000	C0		
5700K	PC56H191-A570A0H1I282-000	A0		
	PC56H191-A570B0H1I282-000	B0	H1,H2,I1,I2	8,9,0,1,2
	PC56H191-A570C0H1I282-000	C0		
6500K	PC56H191-A650A0H1I282-000	A0		
	PC56H191-A650B0H1I282-000	B0	H1,H2,I1,I2	8,9,0,1,2
	PC56H191-A650C0H1I282-000	C0		

(1) Only under an agreement between customer and Lextar Electronics, Ordering codes not in "Standard Ordering Code Definitions" can be supplied.

Binning

PC56H19 V1
 Product Specification


Bin code definition

V _F Rank	Luminous Flux Rank	CIE Rank
0	H1	27A

V _F Rank	Condition	Min.	Max.
8	I _F = 65 mA	2.6	2.7
9		2.7	2.8
0		2.8	2.9
1		2.9	3.0
2		3.0	3.1

Luminous Flux Rank	Condition	Min	Max.
VG	I _F = 65 mA	28	31.5
H1		31.5	33.5
H2		33.5	35.5
I1		35.5	37.5
I2		37.5	39.5

■ Chromaticity Coordinates




Note:


- (1) Correlated color Temperature is derived from the CIE 1931 Chromaticity diagram
- (2) CIE measurement tolerance is ± 0.005
- (3) The luminous flux tolerance is $\pm 7\%$
- (4) The Forward Voltage tolerance is $\pm 0.1V$

■ **Bin code definition**

2700K




Nominal ANSI CCT	Color Space	Target Center Point (cx, cy)	Major Axis, a	Minor Axis, b	Ellipse Rotation Angle
2700K	Single 3-step MacAdam ellipse	(0.4578, 0.4101)	0.00810	0.00420	53.70°
2700K	Single 5-step MacAdam ellipse	(0.4578, 0.4101)	0.01350	0.00700	53.70°




Nominal ANSI CCT	Color Space	Target Center Point (cx, cy)	Major Axis, a	Minor Axis, b	Ellipse Rotation Angle
3000K	Single 3-step MacAdam ellipse	(0.4338, 0.403)	0.00834	0.00408	53.22°
3000K	Single 5-step MacAdam ellipse	(0.4338, 0.403)	0.01390	0.00680	53.22°

3500K




Nominal ANSI CCT	Color Space	Target Center Point (cx, cy)	Major Axis, a	Minor Axis, b	Ellipse Rotation Angle
3500K	Single 3-step MacAdam ellipse	(0.4073, 0.3917)	0.00927	0.00414	53.22°
3500K	Single 5-step MacAdam ellipse	(0.4073, 0.3917)	0.01545	0.00690	53.22°

4000K




Nominal ANSI CCT	Color Space	Target Center Point (cx, cy)	Major Axis, a	Minor Axis, b	Ellipse Rotation Angle
4000K	Single 3-step MacAdam ellipse	(0.3818, 0.3797)	0.00939	0.00402	53.72°
4000K	Single 5-step MacAdam ellipse	(0.3818, 0.3797)	0.01565	0.00670	53.72°

5000K




Nominal ANSI CCT	Color Space	Target Center Point (cx, cy)	Major Axis, a	Minor Axis, b	Ellipse Rotation Angle
5000K	Single 3-step MacAdam ellipse	(0.3447, 0.3553)	0.00822	0.00354	59.62°
5000K	Single 5-step MacAdam ellipse	(0.3447, 0.3553)	0.01370	0.00590	59.62°

5700K




Nominal ANSI CCT	Color Space	Target Center Point (cx, cy)	Major Axis, a	Minor Axis, b	Ellipse Rotation Angle
5700K	Single 3-step MacAdam ellipse	(0.3287, 0.3417)	0.00746	0.00320	59.09°
5700K	Single 5-step MacAdam ellipse	(0.3287, 0.3417)	0.01243	0.00533	59.09°

6500K




Nominal ANSI CCT	Color Space	Target Center Point (cx, cy)	Major Axis, a	Minor Axis, b	Ellipse Rotation Angle
6500K	Single 3-step MacAdam ellipse	(0.3123, 0.3282)	0.00669	0.00285	58.57°
6500K	Single 5-step MacAdam ellipse	(0.3123, 0.3282)	0.01115	0.00475	58.57°


■ Spectrum




■ Radiation Pattern





■ **Forward Voltage vs. Forward Current**




■ **Forward Current vs. Relative Luminosity**




■ Forward Current vs. Chromaticity Coordinate





■ Relative Forward Voltage vs. Ambient Temperature



■ **Relative Luminous Intensity vs. Ambient Temperature**



■ **Chromaticity vs. Ambient Temperature**



Reliability

PC56H19 V1
 Product Specification

Reliability test

Item	Condition	Current	Time/Cycle
Steady State Operating Life of Low Temperature -40°C	-40°C Operating	180mA	1000 Hrs
Steady State Operating Life of High Temperature 60°C	60°C Operating	180mA	1000 Hrs
Steady State Operating Life of High Temperature 85°C	85°C Operating	180mA	1000 Hrs
Low temperature storage -40°C	-40°C Storage	NA	1000 Hrs
High temperature storage 100°C	100°C Storage	NA	1000 Hrs
Steady State Operating Life of High Humidity Heat 60°C 90%	60°C/90% Operating	180mA	1000 Hrs
Resistance to soldering heat on PCB (JEDEC MSL3)	pre-store@60°C, 60%RH for 52hrs Tsld max.=260°C 10sec	NA	3 Times
Thermal shock	-40°C/20minr ~5minr ~ 100°C/20min	NA	300 Cycles

Judgment Criteria

Item	Symbol	Test Condition	Judgment Criteria
Forward Voltage	Vf	180mA	$\Delta Vf < 10 \%$
Luminous Flux	Iv	180mA	$\Delta Iv < 30 \%$

Packing


PC56H19 V1


Product Specification

Label



Carrier Taping






Unit: mm

Item	Spec	To1. (+/-)	Item	Spec	To1. (+/-)
W	12.00	±0.10	P2	2.00	±0.05
E	1.75	±0.10	P0 x 10	40.00	±0.20
F	5.50	±0.05	t1	0.25	±0.05
D	1.50	+0.10, -0.00	A0	3.25	±0.10
D1	1.50	±0.10	B0	5.90	±0.10
P0、P1	4.00	±0.20	K0	0.95	±0.10


■ Shield Bag Taping




■ **Packing Box**

Type	Large Box		Medium Box		Small Box	
Dimension	541X511X276mm		385X303X260mm		283X235x70mm	
Maximum Reels	7"X12mm Reel	64/R	7"X12mm Reel	21/R	7"X12mm Reel	4/R
Minimum Reels	7"X12mm Reel	32/R	7"X12mm Reel	9/R	7"X12mm Reel	1/R


■ **Small Box**



■ **Medium Box**



■ **Large Box**



Precautions

PC56H19 V1

Product Specification

■ Safety Precautions


- The LED light output is too strong for human eyes without shield. Prevent eye contact directly more than seconds.
- Ensure operating under maximum rating.

■ Storage

- Before opening the package, the LEDs should storage under 30°C, 60% RH.
- After opening the package bag, the LEDs should be keep under 30°C, 60% RH. Recommend to use within 168 hrs. If unused LEDs remain, suggest to store into moisture proof bag or original package bag with moisture absorbent material such as silica gel. Reseal well is necessary.
- If the product exceeded the storage period or the moisture absorbent material faded away, baking treatment should be done by following conditions.
Bake condition: 60°C, 12hours (One time only).

■ Soldering Notice and Conditions

- When soldering LEDs,
- Do not solder/reflow the same LED over two times.
- Recommend soldering conditions:
Hand soldering: 350 °C max , 3 sec. max.
Reflow soldering: Pre-heat 180 °C max , 180 sec. max.
Peak 260 °C max , 5 sec. max.
- Reflow temperature profile as below: (lead-free solder)



- When soldering, don't put stress on the LEDs
- After LEDs have been soldered, strongly recommend not to repair to keep the LEDs performance.

■ Static Electricity

- LED package is extremely sensitive to static electricity. It's recommended that anti-electrostatic glove and wrist band is necessary when handling the LEDs. All devices are also be grounded properly as well.
- Protection devices design should be considered in the LED driving circuit.

■ Cleaning

- If washing is required, recommend to use alcohol as a solvent.
- Recommend to avoid cleaning the LEDs by ultrasonic. If necessary, pre-test the LED is necessary to confirm whether any damage occur after the process.

Revision History

PC56H19 V1

Product Specification

Date	Contents	Writer	Approved
2015.03.17	New version	Louis Chou	Berris Huang
2015.06.05	Revise dimension and binning	Louis Chou	Berris Huang
2015.10.02	Revise drawing and max rating	Louis Chou	Berris Huang
2015.10.26	R9 value and RA current update	Louis Chou	Berris Huang
2016.03.15	CIE binning temperature update	Louis Chou	Berris Huang
2016.07.1	Add ordering code & fine binning	Louis Chou	Berris Huang
2018.05.30	Revise IV Rank	Anita Chen	Berris Huang

Smart Lighting *Amazing Life*

Lextar Electronics Corp. is the leading LED (Light Emitting Diode) maker integrating upper stream epitaxial, middle stream chip, and downstream package, SMT and LED lighting applications.

Founded in May, 2008, Lextar is a subsidiary of AU Optronics, the leading TFT-LCD and solar PV manufacturer.

Lextar's product applications include lighting and LCD backlight. Lextar's manufacturing sites include Hsinchu and Chunan in Taiwan, and Suzhou in China. The company turnover in 2012 is 340 million USD.

Copyright ©2010 Lextar Electronics Corporation. All rights reserved. Lextar.com