



JCS4N70C

主要参数 MAIN CHARACTERISTICS

ID	4.0 A
V _{DSS}	700 V
R _{dson-max} (@V _{GS} =10V)	2.8 Ω
Q _{G-typ}	16nC

用途

- 高频开关电源
- 电子镇流器
- UPS 电源

APPLICATIONS

- High frequency switching mode power supply
- Electronic ballast
- UPS


产品特性

- 低栅极电荷
- 低 C_{rss} (典型值 14pF)
- 开关速度快
- 产品全部经过雪崩测试
- 高抗 dv/dt 能力
- RoHS 产品

FEATURES

- Low gate charge
- Low C_{rss} (typical 14pF)
- Fast switching
- 100% avalanche tested
- Improved dv/dt capability
- RoHS product

封装 Package





订货信息 ORDER MESSAGE

订货型号 Order codes	印 记 Marking	封 装 Package	无卤素 Halogen Free	包 装 Packaging	器件重量 Device Weight
JCS4N70VC-O-V-N-B	JCS4N70V	IPIAK	否 NO	条管 Tube	0.35 g(typ)
JCS4N70VC-R-V-N-B	JCS4N70V	IPIAK	是 YES	条管 Tube	0.35 g(typ)
JCS4N70VC-R-VN2-N-B	JCS4N70V	TO-251N-S2	是 YES	条管 Tube	0.35 g(typ)
JCS4N70RC-O-R-N-B	JCS4N70R	DPAK	否 NO	条管 Tube	0.30 g(typ)
JCS4N70RC-O-R-N-A	JCS4N70R	DPAK	否 NO	编带 Reel	0.30 g(typ)
JCS4N70MFC-O-MF-N-B	JCS4N70MF	TO-126F	否 NO	条管 Tube	1.50 g(typ)
JCS4N70SC-O-S-N-B	JCS4N70S	TO-263	否 NO	条管 Tube	1.37 g(typ)
JCS4N70SC-O-S-N-A	JCS4N70S	TO-263	否 NO	编带 Reel	1.37 g(typ)
JCS4N70BC-O-B-N-B	JCS4N70B	TO-262	否 NO	条管 Tube	1.71 g(typ)
JCS4N70CC-O-C-N-B	JCS4N70C	TO-220C	否 NO	条管 Tube	2.15 g(typ)
JCS4N70FC-O-F-N-B	JCS4N70F	TO-220MF	否 NO	条管 Tube	2.20 g(typ)
JCS4N70FC-O-F1-N-B	JCS4N70F	TO-220MF-K1	否 NO	条管 Tube	1.78 g(typ)
JCS4N70FC-O-F2-N-B	JCS4N70F	TO-220MF-K2	否 NO	条管 Tube	1.78 g(typ)





JCS4N70C

绝对最大额定值 ABSOLUTE RATINGS (T_c=25°C)

项 目 Parameter	符 号 Symbol	数 值 Value				单 位 Unit
		JCS4N70MFC	JCS4N70V C/RC	JCS4N70S C/BC/CC	JCS4N70FC	
最高漏极—源极直流电压 Drain-Source Voltage	V _{DSS}	700				V
连续漏极电流 Drain Current -continuous	I _D T=25°C	4.0		4.0*	A	
	T=100°C	2.5		2.5*	A	
最大脉冲漏极电流 (注 1) Drain Current - pulse (note 1)	I _{DM}	16		16*	A	
最高栅源电压 Gate-Source Voltage	V _{GSS}	±30				V
单脉冲雪崩能量 (注 2) Single Pulsed Avalanche Energy(note 2)	E _{AS}	265				mJ
雪崩电流 (注 1) Avalanche Current (note 1)	I _{AR}	4.0				A
重复雪崩能量 (注 1) Repetitive Avalanche Current (note 1)	E _{AR}	11.0				mJ
二极管反向恢复最大电压 变化速率 (注 3) Peak Diode Recovery dv/dt (note 3)	dv/dt	5.0				V/n s
耗散功率 Power Dissipation	P _D T _c =25°C -Derate above25°C	26	51	100	33	W
		0.21	0.39	0.80	0.26	W/ °C
最高结温及存储温度 Operating and Storage Temperature Range	T _J , T _{STG}	-55~+150				°C
引线最高焊接温度 Maximum Lead Temperature for Soldering Purposes	T _L	300				°C

*漏极电流由最高结温限制

*Drain current limited by maximum junction temperature



吉林华微电子股份有限公司

JILIN SINO-MICROELECTRONICS CO., LTD.



JCS4N70C

电特性 ELECTRICAL CHARACTERISTICS

项 目 Parameter	符 号 Symbol	测试条件 Tests conditions	最 小 Min	典 型 Typ	最 大 Max	单 位 Units
关态特性 Off -Characteristics						
漏—源击穿电压 Drain-Source Voltage	BV_{DSS}	$I_D=250\mu A, V_{GS}=0V$	700	-	-	V
击穿电压温度特性 Breakdown Voltage Temperature Coefficient	$\Delta BV_{DSS}/\Delta T_J$	$I_D=250\mu A$, referenced to $25^\circ C$	-	0.66	-	V/ $^\circ C$
零栅压下漏极漏电流 Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS}=700V, V_{GS}=0V, T_C=25^\circ C$	-	-	10	μA
		$V_{DS}=560V, T_C=125^\circ C$	-	-	100	μA
正向栅极体漏电流 Gate-body leakage current, forward	I_{GSSF}	$V_{DS}=0V, V_{GS}=30V$	-	-	100	nA
反向栅极体漏电流 Gate-body leakage current, reverse	I_{GSSR}	$V_{DS}=0V, V_{GS}=-30V$	-	-	-100	nA
通态特性 On-Characteristics						
阈值电压 Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}, I_D=250\mu A$	2.0	-	4.0	V
静态导通电阻 Static Drain-Source On-Resistance	$R_{DS(ON)}$	$V_{GS}=10V, I_D=2A$	-	2.6	2.8	Ω
正向跨导 Forward Transconductance	g_{fs}	$V_{DS}=40V, I_D=2A$ (note 4)	-	3.6	-	S
动态特性 Dynamic Characteristics						
输入电容 Input capacitance	C_{iss}	$V_{DS}=25V, V_{GS}=0V, f=1.0MHz$	-	790	950	pF
输出电容 Output capacitance	C_{oss}		-	67	92	pF
反向传输电容 Reverse transfer capacitance	C_{rss}		-	14	17	pF



电特性 ELECTRICAL CHARACTERISTICS

开关特性 Switching Characteristics							
延迟时间 Turn-On delay time	$t_{d(on)}$	$V_{DD}=350V, I_D=4A, R_G=25\Omega$ (note 4, 5)	-	30	50	ns	
上升时间 Turn-On rise time	t_r		-	65	110	ns	
延迟时间 Turn-Off delay time	$t_{d(off)}$		-	50	130	ns	
下降时间 Turn-Off Fall time	t_f		-	45	90	ns	
栅极电荷总量 Total Gate Charge	Q_g	$V_{DS}=560V, I_D=4A$ $V_{GS}=10V$ (note 4, 5)	-	16	20	nC	
栅—源电荷 Gate-Source charge	Q_{gs}		-	2.0	-	nC	
栅—漏电荷 Gate-Drain charge	Q_{gd}		-	7.0	-	nC	
漏—源二极管特性及最大额定值 Drain-Source Diode Characteristics and Maximum Ratings							
正向最大连续电流 Maximum Continuous Drain -Source Diode Forward Current	I_S			-	-	4 A	
正向最大脉冲电流 Maximum Pulsed Drain-Source Diode Forward Current	I_{SM}			-	-	16 A	
正向压降 Drain-Source Diode Forward Voltage	V_{SD}	$V_{GS}=0V, I_S=4.0A$	-	-	1.4	V	
反向恢复时间 Reverse recovery time	t_{rr}	$V_{GS}=0V, I_S=4.0A$ $dI_F/dt=100A/\mu s$ (note 4)	-	340	-	ns	
反向恢复电荷 Reverse recovery charge	Q_{rr}		-	2.65	-	μC	

热特性 THERMAL CHARACTERISTIC

项 目 Parameter	符 号 Symbol	I	最大 Max				单 位 Unit
			JCS4N7 0MFC	JCS4N7 0VC/RC	JCS4N70 SC/BC/CC	JCS4N70 FC	
结到管壳的热阻 Thermal Resistance, Junction to Case	$R_{th(j-c)}$		4.8	2.50	1.25	3.79	°C/W
结到环境的热阻 Thermal Resistance, Junction to Ambient	$R_{th(j-A)}$		110	83	62.5	62.5	°C/W

Notes:

注释:


- 1: 脉冲宽度由最高结温限制
- 2: $L=31mH, I_{AS}=4.0A, V_{DD}=50V, R_G=25\Omega$,起始结温 $T_J=25^\circ C$
- 3: $I_{SD} \leq 4.0A, di/dt \leq 200A/\mu s, VDD \leq BV_{DSS}$,起始结温 $T_J=25^\circ C$
- 4: 脉冲测试: 脉冲宽度 $\leq 300\mu s$, 占空比 $\leq 2\%$
- 5: 基本与工作温度无关
- 1: Pulse width limited by maximum junction temperature
- 2: $L=31mH, I_{AS}=4.0A, V_{DD}=50V, R_G=25\Omega$, Starting $T_J=25^\circ C$
- 3: $I_{SD} \leq 4.0A, di/dt \leq 200A/\mu s, VDD \leq BV_{DSS}$, Starting $T_J=25^\circ C$
- 4: Pulse Test: Pulse Width $\leq 300\mu s$, Duty Cycle $\leq 2\%$
- 5: Essentially independent of operating temperature






特征曲线 ELECTRICAL CHARACTERISTICS (curves)


On-Region Characteristics




Transfer Characteristics




On-Resistance Variation vs. Drain Current and Gate Voltage




Body Diode Forward Voltage Variation vs. Source Current and Temperature








Capacitance Characteristics



Gate Charge Characteristics



特征曲线 ELECTRICAL CHARACTERISTICS (curves)




Breakdown Voltage Variation
vs. TemperatureOn-Resistance Variation
vs. TemperatureMaximum Safe Operating Area
For JCS4N70VC/RC/SC/BC/CCMaximum Safe Operating Area
For JCS4N70FCMaximum Drain Current
vs. Case Temperature

吉林华微电子股份有限公司

JILIN SINO-MICROELECTRONICS CO., LTD.



特征曲线 ELECTRICAL CHARACTERISTICS (curves)

Transient Thermal Response Curve
For JCS4N70VC/RCTransient Thermal Response Curve
For JCS4N70SC/BC/CCTransient Thermal Response Curve
For JCS4N70FC

吉林华微电子股份有限公司


JILIN SINO-MICROELECTRONICS CO., LTD.




外形尺寸 PACKAGE MECHANICAL DATA

TO-126F

单位 Unit: mm



符号 Symbol	MIN	MAX
A	3.10	3.30
B	1.22	1.47
b	0.60	0.90
c	0.45	0.70
D	10.50	11.20
E	7.50	8.50
e	2.29 TYP	
L	15.00	16.00
L2	2.10	2.30
Q	3.60	4.00
Q1	1.80	2.20
P	2.95	3.15







JCS4N70C


外形尺寸 PACKAGE MECHANICAL DATA

IPAK

单位 Unit: mm




SYMBOL	MM	
	MIN	MAX
A	2.1	2.5
A1	0.87	1.27
b	0.63	0.93
b1	5.13	5.53
c	0.40	0.60
D	5.80	6.40
E	6.30	6.90
L	9.10	9.70
e	2.286BSC	
L1	0.82	1.22



外形尺寸 PACKAGE MECHANICAL DATA

TO-251N-S2

单位 Unit: mm






SYMBOL	MM	
	MIN	MAX
A	2.050	2.550
A1	1.050	1.350
b1	0.680	0.920
b2	5.150	5.450
b3	0.530	0.770
b4	0.480	0.720
b5	0.280	0.520
b6	0.180	0.420
c	0.400	0.600
c1	0.400	0.600
c2	0.180	0.420
D	5.350	5.850
E	6.350	6.850
e	2.3 (TYP)	
L	2.550	3.050
L1	1.4	1.8
L2	1.25	1.55



外形尺寸 PACKAGE MECHANICAL DATA



DPAK

单位 Unit: mm



符号 symbol	MIN	MAX
A	2.2	2.4
A1	0.0	0.2
b	0.7	0.9
c	0.45	0.55
D	6.0	6.3
D1	0.8	1.2
E	6.5	6.8
E1	5.2	5.5
e	2.28TYP	
F	0.45	0.55
H	9.65	10.45
L	1.4	1.7
L2	0.6	1.0

编带 REEL




吉林华微电子股份有限公司

JILIN SINO-MICROELECTRONICS CO., LTD.


外形尺寸 PACKAGE MECHANICAL DATA

TO-262

单位 Unit: mm




符号 symbol	MIN	MAX
A	4.40	4.90
B	1.10	1.40
b	0.70	0.95
c	0.30	0.60
c1	0.33	0.63
D2	8.20	9.20
E	9.60	10.50
e	2.39	2.69
F	1.20	1.35
L	13.11	14.61
L2	3.55	4.05
Q	1.10	1.40
Q1	2.65	2.85



外形尺寸 PACKAGE MECHANICAL DATA


TO-263

单位 Unit: mm



符合 symbol	MIN	MAX
A	4.3	4.8
B	1.2	1.4
D	8.5	8.8
E	9.5	10.5
F	1.2	1.4
F1	2.5	2.9
G	4.7	5.5
L1	1.4	1.7
Q	1.2	1.5
b	0.75	0.95
c	0.35	0.5
e	2.49	2.59
g	1.9	2.7
h	2.3	3.3

编带 REEL



NOTES


1. 10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE 0.2mm;
任意10个传输孔间距累积误差0.2mm;
2. MATERIAL: BLACK CONDUCTIVE POLYSTYRENE;
材料: 黑色防静电聚苯乙烯;
3. DEMENSIONS ARE IN mm (UNLESS OTHERWISE SPECIFIED);
除非特别标注, 尺寸单位为毫米;
4. K0 MEASURED FROM A PLANE ON THE INSIDE BOTTOM OF
THE POCKET TO THE TOP SURFACE ON THE CARRIER;
K0是从凹槽底部上表面到载带正面的测量尺寸;
5. A0 AND B0 MEASURED ON A PLANE 0.30mm ABOVE THE BOTTOM OF THE POCKET;
从凹槽底部上方测量A0和B0的平面度是0.30mm;
6. SURFACE RESISTIVITY IS BETWEEN 1×10^6 TO 1×10^{10} OHMS/SQUARE;
表面阻抗 1×10^6 ~ 1×10^{10} Ω/□;
7. Allowable Camber to be 1 mm/100 mm
载带100mm以内, 弯曲度不可超过1mm。

外观	尺寸	外观	尺寸
P0	4.0 ± 0.1	W	24.0 ± 0.3
P2	2.0 ± 0.1	A0	10.8 ± 0.2
P	16.0 ± 0.1	E	1.75 ± 0.1
T	0.35 ± 0.05	F	11.5 ± 0.1
K0	4.85 ± 0.1	D	1.55 ± 0.05
B0	16.3 ± 0.1	D1	1.5 ± 0.1
W1	規格1	規格1	16.9 ± 0.1
	規格2	規格2	17.2 ± 0.1

外形尺寸 PACKAGE MECHANICAL DATA

TO-220C

单位 Unit: mm




符号 symbol	MIN	MAX
A	4.30	4.70
B	1.10	1.40
b	0.70	0.95
c	0.40	0.65
D	15.20	16.20
D2	9.00	9.40
E	9.70	10.10
e	2.39	2.69
F	1.25	1.40
L	12.60	13.60
L2	2.80	3.20
Q	2.60	3.00
Q1	2.20	2.60
P	3.50	3.80



外形尺寸 PACKAGE MECHANICAL DATA

TO-220MF

单位 Unit: mm




SYMBOL	mm	
	MIN	MAX
A	4.5	4.9
B		1.47
b	0.7	0.9
c	0.45	0.60
D	15.67	16.07
D1	9.04	9.20
e	2.54TYPE	
E	9.96	10.36
F	2.34	2.74
L	12.58	13.38
L1	3.13	3.33
Q	3.2	3.4
Q1	2.56	2.96
ΦP	3.08	3.28



外形尺寸 PACKAGE MECHANICAL DATA

TO-220MF-K1

单位 Unit: mm




SYMBOL	mm	
	MIN	MAX
A	4.5	4.9
B	1.22	1.47
b	0.7	0.9
c	0.45	0.60
D	15.6	16.1
D1	9.0	9.3
e	2.54TYPE	
E	9.9	10.4
F	2.3	2.8
L	12.6	13.3
L1	3.1	3.4
Q	3.2	3.4
Q1	2.6	2.9
ΦP	3.0	3.5



外形尺寸 PACKAGE MECHANICAL DATA

TO-220MF-K2

单位 Unit: mm



SYMBOL	mm	
	MIN	MAX
A	4.5	4.9
B		1.27
b	0.59	0.79
c	0.45	0.60
D	15.67	16.07
D1	8.97	9.37
e	2.54TYPE	
E	9.96	10.36
F	2.34	2.74
L	12.65	13.35
L1	1.80	2.20
Q	3.2	3.4
Q1	2.56	2.96
ΦP	3.08	3.28



**注意事项**

1. 吉林华微电子股份有限公司的产品销售分为直销和销售代理，无论哪种方式，订货时请与公司核实。
2. 购买时请认清公司商标，如有疑问请与公司本部联系。
3. 在电路设计时请不要超过器件的绝对最大额定值，否则会影响整机的可靠性。
4. 本说明书如有版本变更不另外告知

NOTE

1. Jilin Sino-microelectronics co., Ltd sales its product either through direct sales or sales agent , thus, for customers, when ordering , please check with our company.
2. We strongly recommend customers check carefully on the trademark when buying our product, if there is any question, please don't be hesitate to contact us.
3. Please do not exceed the absolute maximum ratings of the device when circuit designing.
4. Jilin Sino-microelectronics co., Ltd reserves the right to make changes in this specification sheet and is subject to change without prior notice.

联系方式**吉林华微电子股份有限公司**

公司地址：吉林省吉林市深圳街 99 号

邮编：132013

总机：86-432-64678411

传真：86-432-64665812

网址：www.hwdz.com.cn

市场营销部

地址：吉林省吉林市深圳街 99 号

邮编：132013

电话： 86-432-64675588

64675688

64678411

传真：86-432-64671533

CONTACT**JILIN SINO-MICROELECTRONICS CO., LTD.**

ADD: No.99 Shenzhen Street, Jilin City, Jilin Province, China.

Post Code: 132013

Tel: 86-432-64678411

Fax: 86-432-64665812

Web Site: www.hwdz.com.cn

MARKET DEPARTMENT

ADD: No.99 Shenzhen Street, Jilin City, Jilin Province, China.

Post Code: 132013

Tel: 86-432-64675588

64675688

64678411

Fax: 86-432-64671533

