

SN54AHC32 SN74AHC32

SCLS247I -OCTOBER 1995-REVISED JUNE 2013

QUADRUPLE 2-INPUT POSITIVE-OR GATES

Check for Samples: SN54AHC32, SN74AHC32

FEATURES

www.ti.com

- Operating Range 2-V to 5.5-V V_{CC}
- Latch-Up Performance Exceeds 250 mA Per JESD 17
- ESD Protection Exceeds JESD 22
 - 2000-V Human-Body Model (A114-A)
 - 200-V Machine Model (A115-A)
 - 1000-V Charged-Device Model (C101)



DESCRIPTION

The 'AHC32 devices are quadruple 2-input positive-OR gates. These devices perform the Boolean function $Y = \overline{A \cdot B}$ or Y = A + B in positive logic.

FUNCTION TABLE

| (EACH GATE) | | | | | | | | | | |
|-------------|------------------------------------|--|--|--|--|--|--|--|--|--|
| INPUTS | | | | | | | | | | |
| В | Y | | | | | | | | | |
| Х | Н | | | | | | | | | |
| н | Н | | | | | | | | | |
| L | L | | | | | | | | | |
| | ACH GAT UTS B X H L | | | | | | | | | |

LOGIC DIAGRAM (POSITIVE LOGIC)





Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

SN54AHC32 SN74AHC32

SCLS247I-OCTOBER 1995-REVISED JUNE 2013



www.ti.com

ABSOLUTE MAXIMUM RATINGS

over operating free-air temperature range (unless otherwise noted)⁽¹⁾

| | | VALUE | UNIT | | | | |
|--|---|-------------------------------|------|--|--|--|--|
| Supply voltage range, V _{CC} | | -0.5 to 7 | V | | | | |
| Input voltage range, V _I ⁽²⁾ | | –0.5 to 7 | V | | | | |
| Output voltage range, V _O ⁽²⁾ | | -0.5 to V _{CC} + 0.5 | V | | | | |
| Input clamp current, I_{IK} (V _I < 0) | | -20 | mA | | | | |
| Output clamp current, I_{OK} (V _O < 0 or V _O : | Dutput clamp current, I _{OK} (V _O < 0 or V _O > V _{CC}) | | | | | | |
| Continuous output current, I_O (V _O = 0 to | ±25 | mA | | | | | |
| Continuous current through V_{CC} or GND | ±50 | mA | | | | | |
| | D package ⁽³⁾ | 86 | | | | | |
| | DB package ⁽³⁾ | 96 | | | | | |
| | DGV package ⁽³⁾ | 127 | | | | | |
| Package thermal impedance, θ_{JA} | N package ⁽³⁾ | 80 | °C/W | | | | |
| | NS package ⁽³⁾ | 76 | | | | | |
| | PW package ⁽³⁾ | 113 | | | | | |
| | RGY package ⁽⁴⁾ | 47 | | | | | |
| Storage temperature range, T _{sta} | | -65 to 150 | °C | | | | |

(1) Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

(2) The input and output voltage ratings may be exceeded if the input and output current ratings are observed.

(3) The package thermal impedance is calculated in accordance with JESD 51-7.

(4) The package thermal impedance is calculated in accordance with JESD 51-5

RECOMMENDED OPERATING CONDITIONS⁽¹⁾

| | | | SN54AH | IC32 | SN74AH | C32 | |
|-----------------|------------------------------------|--------------------------|--------|-----------------|--------|----------|--------------|
| | | | MIN | MAX | MIN | MAX | UNIT |
| V _{CC} | Supply voltage | | 2 | 5.5 | 2 | 5.5 | V |
| | | V _{CC} = 2 V | 1.5 | | 1.5 | | |
| VIH | High-level input voltage | V _{CC} = 3V | 2.1 | | 2.1 | | V |
| | | V _{CC} = 5.5 V | 3.85 | | 3.85 | | |
| | | V _{CC} = 2 V | | 0.5 | | 0.5 | |
| VIL | Low-level Input voltage | V _{CC} = 3 V | | 0.9 | | 0.9 | V |
| | | V _{CC} = 5.5 V | | 1.65 | | 1.65 | |
| VI | Input voltage | | 0 | 5.5 | 0 | 5.5 | V |
| Vo | Output voltage | | 0 | V _{CC} | 0 | V_{CC} | V |
| | | $V_{CC}=2 V$ | | -50 | | -50 | |
| I _{OH} | High-level output current | V_{CC} = 3.3 V ± 0.3 V | | -4 | | -4 | mA |
| | | V_{CC} = 5 V ± 0.5 V | | -8 | | -8 | |
| | | V _{CC} = 2 V | | 50 | | 50 | |
| I _{OL} | Low-level output current | V_{CC} = 3.3 V ± 0.3 V | | 4 | | 4 | mA |
| 02 | | V_{CC} = 5 V ± 0.5 V | | 8 | | 8 | |
| A+/A | Input Transition rise or fall rate | V_{CC} = 3.3 V ± 0.3 V | | 100 | | 100 | n o// |
| ΔυΔν | input transition use of fail fate | V_{CC} = 5 V ± 0.5 V | | 20 | | 20 | 115/ V |
| T _A | Operating free-air temperature | -55 | 125 | -40 | 125 | °C | |

 All unused inputs of the device must be held at V_{CC} or GND to ensure proper device operation. Refer to the TI application report, Implications of Slow or Floating CMOS Inputs, literature number SCBA004.



www.ti.com

ELECTRICAL CHARACTERISTICS

over operating free-air temperature range (unless otherwise noted)

| | | | | | | $T_{A} = -55^{\circ}$ | сто | T _A = -40° | сто | T _A = -40° 125°(| сто С | |
|-----------------|-------------------------------|-----------------|------|-----------------------|------|-----------------------|-------------------|-----------------------|------|--------------------------------|----------|------|
| PARAMETER | TEST CONDITIONS | Vcc | - | T _A = 25°C | ; | SN54AHC32 | | 65 C | • | Recommended | | UNIT |
| | | | | | | | | SN74AHC32 | | SN74AHC32 | | |
| | | | MIN | TYP | MAX | MIN | MAX | MIN | MAX | MIN | MAX | |
| | | 2 V | 1.9 | 2 | | 1.9 | | 1.9 | | 1.9 | | |
| | I _{OH} = -50 μA | 3 V | 2.9 | 3 | | 2.9 | | 2.9 | | 2.9 | | |
| V _{OH} | | 4.5 V | 4.4 | 4.5 | | 4.4 | | 4.4 | | 4.4 | | V |
| | I _{OH} = -4 mA | 3 V | 2.58 | | | 2.48 | | 2.48 | | 2.48 | | |
| 1 | I _{OH} = -8 mA | 4.5 V | 3.94 | | | 3.8 | | 3.8 | | 3.8 | | |
| | | 2 V | | | 0.1 | | 0.1 | | 0.1 | | 0.1 | |
| | I _{OL} = 50 μA | 3 V | | | 0.1 | | 0.1 | | 0.1 | | 0.1 | |
| V _{OL} | | 4.5 V | | | 0.1 | | 0.1 | | 0.1 | | 0.1 | V |
| | I _{OH} = 4 mA | 3 V | | | 0.36 | | 0.5 | | 0.44 | | 0.5 | |
| | I _{OH} = 8 mA | 4.5 V | | | 0.36 | | 0.5 | | 0.44 | | 0.5 | |
| l _i | V ₁ = 5.5 V or GND | 0 V to 5.5 V | | | ±0.1 | | ±1 ⁽¹⁾ | | ±1 | | ±1 | μA |
| I _{cc} | | 5.5 V | | | 2 | | 20 | | 20 | | 20 | μA |
| C _i | $V_{I} = V_{CC}$ or GND | 5 V | | 2 | 10 | | | | 10 | | | pF |

(1) On products compliant to MIL-PRF-38535, this parameter is not production tested at VCC = 0 V.

SWITCHING CHARACTERISTICS

over recommended operating free-air temperature range, V_{CC} = 3.3 V ± 0.3 V (unless otherwise noted) (see Figure 1)

| | | | | | | T _A = -5 | 5°C TO | $T_A = -4$ | ос то | T _A = -4 125 | 0°С ТО 5°С | | | | | | | | | | | | | | |
|------------------|----------|----------|------------------------|--|------------------------|------------------------|------------------------|------------------------|------------------------|----------------------------|------------------------|------------------------|------------------------|------------------------|------------------------|------------------------|---|------|---|----|---|----|---|----|-----|
| PARAMETER | FROM | TO | | LOAD $T_A = 25^{\circ}C$ 125 CPACITANCESN54AHC32 | | | 85 | ι. | Recom | nended | UNIT | | | | | | | | | | | | | | |
| | (141 01) | (001201) | CALACITATICE | | | SN54AHC32 | | SN74AHC32 | | SN74AHC32 | | | | | | | | | | | | | | | |
| | | | | TYP | MAX | MIN | MAX | MIN | MAX | MIN | MAX | | | | | | | | | | | | | | |
| t _{PLH} | A or P | v | 0 – 15 pF | 5.5 ⁽¹⁾ | 7.9 ⁽¹⁾ | 1 ⁽¹⁾ | 9.5 ⁽¹⁾ | 1 | 9.5 | 1 | 9.5 | | | | | | | | | | | | | | |
| t _{PHL} | AOIB | ř | C _L = 15 pF | 5.5 ⁽¹⁾ | 7.9 ⁽¹⁾ | 1 ⁽¹⁾ | 9.5 ⁽¹⁾ | 1 | 9.5 | 1 | 9.5 | ns | | | | | | | | | | | | | |
| t _{PLH} | A or B | ~ | C = 50 pF | 8 | 11.4 | 1 | 13 | 1 | 13 | 1 | 13 | | | | | | | | | | | | | | |
| t _{PHL} | AUB | Y | $C_L = 50 \text{ pF}$ | C _L = 50 pF | C _L = 50 pF | C _L = 50 pF | C _L = 50 pF | C _L = 50 pF | C _L = 50 pF | C _L = 50 pF | C _L = 50 pF | C _L = 50 pF | C _L = 50 pF | C _L = 50 pF | C _L = 50 pF | C _L = 50 pF | 8 | 11.4 | 1 | 13 | 1 | 13 | 1 | 13 | 115 |

(1) On products compliant to MIL-PRF-38535, this parameter is not production tested.

SWITCHING CHARACTERISTICS

over recommended operating free-air temperature range, V_{CC} = 5 V ± 0.5 V (unless otherwise noted) (see Figure 1)

| PARAMETER | FROM | то | LOAD | T _A = 2 | 25°C | T _A = -5 125 | 5°C TO 5°C | T _A = -4 85 | 0°С ТО °С | T _A = -40 125 Recomm | D°C TO PC nended | UNIT |
|------------------|---------|----------|-----------------------|--------------------|--------------------|----------------------------|--------------------|---------------------------|--------------|---------------------------------------|------------------------|------|
| | (INPUT) | (OUTPUT) | CAPACITANCE | _ | | SN54AHC32 | | SN74AHC32 | | SN74A | ••••• | |
| | | | | ТҮР | MAX | MIN | MAX | MIN | MAX | MIN | MAX | |
| t _{PLH} | A or P | V | C = 15 pF | 3.8 ⁽¹⁾ | 5.5 ⁽¹⁾ | 1 ⁽¹⁾ | 6.5 ⁽¹⁾ | 1 | 6.5 | 1 | 6.5 | |
| t _{PHL} | AUB | Т | CL = 15 pF | 3.8 ⁽¹⁾ | 5.5 ⁽¹⁾ | 1 ⁽¹⁾ | 6.5 ⁽¹⁾ | 1 | 6.5 | 1 | 6.5 | 115 |
| t _{PLH} | A or B | ~ | C = 50 pE | 5.3 | 7.5 | 1 | 8.5 | 1 | 8.5 | 1 | 8.5 | nc |
| t _{PHL} | AUB | T | $O_L = 50 \text{ pr}$ | 5.3 | 7.5 | 1 | 8.5 | 1 | 8.5 | 1 | 8.5 | 115 |

(1) On products compliant to MIL-PRF-38535, this parameter is not production tested.

SCLS247I-OCTOBER 1995-REVISED JUNE 2013



www.ti.com

NOISE CHARACTERISTICS

 $V_{CC} = 5 \ V, \ C_L = 50 \ pF, \ T_A = 25^{\circ}C^{(1)}$

| | DADAMETER | SN | 74AHC3 | 2 | UNIT |
|--------------------|---|-----|--------|------|------|
| | PARAMETER | MIN | TYP | MAX | |
| V _{OL(P)} | Quiet output, maximum dynamic V _{OL} | | 0.3 | 0.8 | V |
| V _{OL(V)} | Quiet output, minimum dynamic V _{OL} | | -0.3 | -0.8 | V |
| V _{OH(V)} | Quiet output, minimum dynamic V _{OH} | | 4.7 | | V |
| V _{IH(D)} | High-level dynamic input voltage | 3.5 | | | V |
| V _{IL(D)} | Low-level dynamic input voltage | | | 1.5 | V |

(1) Characteristics are for surface-mount packages only.

OPERATING CHARACTERISTICS

 $V_{CC} = 5 \text{ V}, \text{ } \text{T}_{A} = 25^{\circ}\text{C}$

| | PARAMETER | TEST (| CONDITIONS | TYP | UNIT |
|-----------------|-------------------------------|----------|------------|-----|------|
| C _{pd} | Power dissipation capacitance | No load, | f = 1 MHz | 14 | pF |

Copyright © 1995–2013, Texas Instruments Incorporated



SCLS247I – OCTOBER 1995 – REVISED JUNE 2013

PARAMETER MEASUREMENT INFORMATION



- A. C_L includes probe and jig capacitance.
- B. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control.

Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.

- C. All input pulses are supplied by generators having the following characteristics: PRR ≤ 1 MHz, Z_0 = 50 Ω , t_r ≤ 3 ns, t_f ≤ 3 ns.
- D. The outputs are measured one at a time with one input transition per measurement.
- E. All parameters and waveforms are not applicable to all devices.

Figure 1. Load Circuit and Voltage Waveforms

www.ti.com

REVISION HISTORY

| Cł | nanges from Revision H (July 2003) to Revision I Pa | ge |
|----|--|-----|
| • | Changed document format from Quicksilver to DocZone. | . 1 |
| • | Extended operating temperature range to 125°C | . 2 |



17-Mar-2017

PACKAGING INFORMATION

| Orderable Device | Status | Package Type | Package | Pins | Package | Eco Plan | Lead/Ball Finish | MSL Peak Temp | Op Temp (°C) | Device Marking | Samples |
|------------------|--------|--------------|---------|------|---------|----------------------------|------------------|--------------------|--------------|---|---------|
| | (1) | | Drawing | | Qty | (2) | (6) | (3) | | (4/5) | |
| 5962-9682501Q2A | ACTIVE | LCCC | FK | 20 | 1 | TBD | POST-PLATE | N / A for Pkg Type | -55 to 125 | 5962- 9682501Q2A SNJ54AHC 32FK | Samples |
| 5962-9682501QCA | ACTIVE | CDIP | J | 14 | 1 | TBD | A42 | N / A for Pkg Type | -55 to 125 | 5962-9682501QC A SNJ54AHC32J | Samples |
| 5962-9682501QDA | ACTIVE | CFP | W | 14 | 1 | TBD | A42 | N / A for Pkg Type | -55 to 125 | 5962-9682501QD A SNJ54AHC32W | Samples |
| SN74AHC32D | ACTIVE | SOIC | D | 14 | 50 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM | -40 to 125 | AHC32 | Samples |
| SN74AHC32DBR | ACTIVE | SSOP | DB | 14 | 2000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM | -40 to 125 | HA32 | Samples |
| SN74AHC32DE4 | ACTIVE | SOIC | D | 14 | 50 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM | -40 to 125 | AHC32 | Samples |
| SN74AHC32DG4 | ACTIVE | SOIC | D | 14 | 50 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM | -40 to 125 | AHC32 | Samples |
| SN74AHC32DGVR | ACTIVE | TVSOP | DGV | 14 | 2000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM | -40 to 125 | HA32 | Samples |
| SN74AHC32DR | ACTIVE | SOIC | D | 14 | 2500 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM | -40 to 125 | AHC32 | Samples |
| SN74AHC32DRG4 | ACTIVE | SOIC | D | 14 | 2500 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM | -40 to 125 | AHC32 | Samples |
| SN74AHC32N | ACTIVE | PDIP | Ν | 14 | 25 | Pb-Free (RoHS) | CU NIPDAU | N / A for Pkg Type | -40 to 125 | SN74AHC32N | Samples |
| SN74AHC32NSR | ACTIVE | SO | NS | 14 | 2000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM | -40 to 125 | AHC32 | Samples |
| SN74AHC32PW | ACTIVE | TSSOP | PW | 14 | 90 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM | -40 to 125 | HA32 | Samples |
| SN74AHC32PWR | ACTIVE | TSSOP | PW | 14 | 2000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM | -40 to 125 | HA32 | Samples |
| SN74AHC32PWRE4 | ACTIVE | TSSOP | PW | 14 | 2000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM | -40 to 125 | HA32 | Samples |



17-Mar-2017

| Orderable Device | Status | Package Type | Package | Pins | Package | Eco Plan | Lead/Ball Finish | MSL Peak Temp | Op Temp (°C) | Device Marking | Samples |
|------------------|--------|--------------|---------|------|---------|----------------------------|------------------|---------------------|--------------|---|---------|
| | (1) | | Drawing | | Qty | (2) | (6) | (3) | | (4/5) | |
| SN74AHC32PWRG4 | ACTIVE | TSSOP | PW | 14 | 2000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM | -40 to 125 | HA32 | Samples |
| SN74AHC32RGYR | ACTIVE | VQFN | RGY | 14 | 3000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-2-260C-1 YEAR | -40 to 125 | HA32 | Samples |
| SNJ54AHC32FK | ACTIVE | LCCC | FK | 20 | 1 | TBD | POST-PLATE | N / A for Pkg Type | -55 to 125 | 5962- 9682501Q2A SNJ54AHC 32FK | Samples |
| SNJ54AHC32J | ACTIVE | CDIP | J | 14 | 1 | TBD | A42 | N / A for Pkg Type | -55 to 125 | 5962-9682501QC A SNJ54AHC32J | Samples |
| SNJ54AHC32W | ACTIVE | CFP | W | 14 | 1 | TBD | A42 | N / A for Pkg Type | -55 to 125 | 5962-9682501QD A SNJ54AHC32W | Samples |

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

⁽²⁾ Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.

TBD: The Pb-Free/Green conversion plan has not been defined.

Pb-Free (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes. **Pb-Free (RoHS Exempt):** This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.



PACKAGE OPTION ADDENDUM

17-Mar-2017

(6) Lead/Ball Finish - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF SN54AHC32, SN74AHC32 :

- Catalog: SN74AHC32
- Enhanced Product: SN74AHC32-EP, SN74AHC32-EP
- Military: SN54AHC32

NOTE: Qualified Version Definitions:

- Catalog TI's standard catalog product
- Enhanced Product Supports Defense, Aerospace and Medical Applications
- Military QML certified for Military and Defense Applications

PACKAGE MATERIALS INFORMATION

www.ti.com

Texas Instruments

TAPE AND REEL INFORMATION





QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



| *All dimensions are nominal | | | | | | | | | | | | |
|-----------------------------|-----------------|--------------------|------|------|--------------------------|--------------------------|------------|------------|------------|------------|-----------|------------------|
| Device | Package Type | Package Drawing | Pins | SPQ | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
| SN74AHC32DBR | SSOP | DB | 14 | 2000 | 330.0 | 16.4 | 8.2 | 6.6 | 2.5 | 12.0 | 16.0 | Q1 |
| SN74AHC32DGVR | TVSOP | DGV | 14 | 2000 | 330.0 | 12.4 | 6.8 | 4.0 | 1.6 | 8.0 | 12.0 | Q1 |
| SN74AHC32DR | SOIC | D | 14 | 2500 | 330.0 | 16.4 | 6.5 | 9.0 | 2.1 | 8.0 | 16.0 | Q1 |
| SN74AHC32NSR | SO | NS | 14 | 2000 | 330.0 | 16.4 | 8.2 | 10.5 | 2.5 | 12.0 | 16.0 | Q1 |
| SN74AHC32PWR | TSSOP | PW | 14 | 2000 | 330.0 | 12.4 | 6.9 | 5.6 | 1.6 | 8.0 | 12.0 | Q1 |
| SN74AHC32RGYR | VQFN | RGY | 14 | 3000 | 330.0 | 12.4 | 3.75 | 3.75 | 1.15 | 8.0 | 12.0 | Q1 |

TEXAS INSTRUMENTS

www.ti.com

PACKAGE MATERIALS INFORMATION

17-Jun-2013



*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Length (mm) | Width (mm) | Height (mm) |
|---------------|--------------|-----------------|------|------|-------------|------------|-------------|
| SN74AHC32DBR | SSOP | DB | 14 | 2000 | 367.0 | 367.0 | 38.0 |
| SN74AHC32DGVR | TVSOP | DGV | 14 | 2000 | 367.0 | 367.0 | 35.0 |
| SN74AHC32DR | SOIC | D | 14 | 2500 | 367.0 | 367.0 | 38.0 |
| SN74AHC32NSR | SO | NS | 14 | 2000 | 367.0 | 367.0 | 38.0 |
| SN74AHC32PWR | TSSOP | PW | 14 | 2000 | 367.0 | 367.0 | 35.0 |
| SN74AHC32RGYR | VQFN | RGY | 14 | 3000 | 367.0 | 367.0 | 35.0 |

LEADLESS CERAMIC CHIP CARRIER

FK (S-CQCC-N**) 28 TERMINAL SHOWN



NOTES: A. All linear dimensions are in inches (millimeters).

B. This drawing is subject to change without notice.

- C. This package can be hermetically sealed with a metal lid.
- D. Falls within JEDEC MS-004



MECHANICAL DATA



- D. The package thermal pad must be soldered to the board for thermal and mechanical performance.
- E. See the additional figure in the Product Data Sheet for details regarding the exposed thermal pad features and dimensions.
- earrow Pin 1 identifiers are located on both top and bottom of the package and within the zone indicated.
- The Pin 1 identifiers are either a molded, marked, or metal feature.
- G. Package complies to JEDEC MO-241 variation BA.



RGY (S-PVQFN-N14)

PLASTIC QUAD FLATPACK NO-LEAD

THERMAL INFORMATION

This package incorporates an exposed thermal pad that is designed to be attached directly to an external heatsink. The thermal pad must be soldered directly to the printed circuit board (PCB). After soldering, the PCB can be used as a heatsink. In addition, through the use of thermal vias, the thermal pad can be attached directly to the appropriate copper plane shown in the electrical schematic for the device, or alternatively, can be attached to a special heatsink structure designed into the PCB. This design optimizes the heat transfer from the integrated circuit (IC).

For information on the Quad Flatpack No-Lead (QFN) package and its advantages, refer to Application Report, QFN/SON PCB Attachment, Texas Instruments Literature No. SLUA271. This document is available at www.ti.com.

The exposed thermal pad dimensions for this package are shown in the following illustration.



NOTE: All linear dimensions are in millimeters





NOTES: A. All linear dimensions are in millimeters.

- B. This drawing is subject to change without notice.
- C. Publication IPC-7351 is recommended for alternate designs.
- D. This package is designed to be soldered to a thermal pad on the board. Refer to Application Note, Quad Flat-Pack QFN/SON PCB Attachment, Texas Instruments Literature No. SLUA271, and also the Product Data Sheets for specific thermal information, via requirements, and recommended board layout. These documents are available at www.ti.com http://www.ti.com.
- E. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC 7525 for stencil design considerations.
- F. Customers should contact their board fabrication site for minimum solder mask web tolerances between signal pads.



MECHANICAL DATA

PLASTIC SMALL-OUTLINE PACKAGE

0,51 0,35 ⊕0,25⊛ 1,27 8 14 0,15 NOM 5,60 8,20 5,00 7,40 \bigcirc Gage Plane ₽ 0,25 7 1 1,05 0,55 0-10 Δ 0,15 0,05 Seating Plane — 2,00 MAX 0,10PINS ** 14 16 20 24 DIM 10,50 10,50 12,90 15,30 A MAX A MIN 9,90 9,90 12,30 14,70 4040062/C 03/03

NOTES: A. All linear dimensions are in millimeters.

NS (R-PDSO-G**)

14-PINS SHOWN

- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.



W (R-GDFP-F14)

CERAMIC DUAL FLATPACK



- A. All linear dimensions are in inches (millimeters).
 - B. This drawing is subject to change without notice.
 - C. This package can be hermetically sealed with a ceramic lid using glass frit.
 - D. Index point is provided on cap for terminal identification only.
 - E. Falls within MIL STD 1835 GDFP1-F14



MECHANICAL DATA

PLASTIC SMALL-OUTLINE

MPDS006C - FEBRUARY 1996 - REVISED AUGUST 2000

DGV (R-PDSO-G**)

24 PINS SHOWN



NOTES: A. All linear dimensions are in millimeters.

B. This drawing is subject to change without notice.

- C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15 per side.
- D. Falls within JEDEC: 24/48 Pins MO-153

14/16/20/56 Pins – MO-194



GENERIC PACKAGE VIEW

CDIP - 5.08 mm max height

CERAMIC DUAL IN LINE PACKAGE



Images above are just a representation of the package family, actual package may vary. Refer to the product data sheet for package details.



J0014A



PACKAGE OUTLINE

CDIP - 5.08 mm max height

CERAMIC DUAL IN LINE PACKAGE



NOTES:

- 1. All controlling linear dimensions are in inches. Dimensions in brackets are in millimeters. Any dimension in brackets or parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.
- 3. This package is hermitically sealed with a ceramic lid using glass frit.
- Index point is provided on cap for terminal identification only and on press ceramic glass frit seal only.
 Falls within MIL-STD-1835 and GDIP1-T14.



J0014A

EXAMPLE BOARD LAYOUT

CDIP - 5.08 mm max height

CERAMIC DUAL IN LINE PACKAGE





D (R-PDSO-G14)

PLASTIC SMALL OUTLINE



NOTES: A. All linear dimensions are in inches (millimeters).

- B. This drawing is subject to change without notice.
- Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.006 (0,15) each side.
- Body width does not include interlead flash. Interlead flash shall not exceed 0.017 (0,43) each side.
- E. Reference JEDEC MS-012 variation AB.





NOTES: A. All linear dimensions are in millimeters.

- B. This drawing is subject to change without notice.
- C. Publication IPC-7351 is recommended for alternate designs.
- D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC-7525 for other stencil recommendations.
 E. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.



PW (R-PDSO-G14)

PLASTIC SMALL OUTLINE



A. An integration of the information o

Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0,15 each side.

Body width does not include interlead flash. Interlead flash shall not exceed 0,25 each side.

E. Falls within JEDEC MO-153



N (R-PDIP-T**)

PLASTIC DUAL-IN-LINE PACKAGE

16 PINS SHOWN



NOTES:

- A. All linear dimensions are in inches (millimeters).B. This drawing is subject to change without notice.
- Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
- \triangle The 20 pin end lead shoulder width is a vendor option, either half or full width.



MECHANICAL DATA

MSSO002E - JANUARY 1995 - REVISED DECEMBER 2001

DB (R-PDSO-G**)

PLASTIC SMALL-OUTLINE

28 PINS SHOWN



NOTES: A. All linear dimensions are in millimeters.

- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion not to exceed 0,15.
- D. Falls within JEDEC MO-150



IMPORTANT NOTICE

Texas Instruments Incorporated (TI) reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete.

TI's published terms of sale for semiconductor products (http://www.ti.com/sc/docs/stdterms.htm) apply to the sale of packaged integrated circuit products that TI has qualified and released to market. Additional terms may apply to the use or sale of other types of TI products and services.

Reproduction of significant portions of TI information in TI data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such reproduced documentation. Information of third parties may be subject to additional restrictions. Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyers and others who are developing systems that incorporate TI products (collectively, "Designers") understand and agree that Designers remain responsible for using their independent analysis, evaluation and judgment in designing their applications and that Designers have full and exclusive responsibility to assure the safety of Designers' applications and compliance of their applications (and of all TI products used in or for Designers' applications) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to their applications, Designer has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any applications that include TI products, Designer will thoroughly test such applications and the functionality of such TI products as used in such applications.

TI's provision of technical, application or other design advice, quality characterization, reliability data or other services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using TI Resources in any way, Designer (individually or, if Designer is acting on behalf of a company, Designer's company) agrees to use any particular TI Resource solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

Designer is authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNER AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

Unless TI has explicitly designated an individual product as meeting the requirements of a particular industry standard (e.g., ISO/TS 16949 and ISO 26262), TI is not responsible for any failure to meet such industry standard requirements.

Where TI specifically promotes products as facilitating functional safety or as compliant with industry functional safety standards, such products are intended to help enable customers to design and create their own applications that meet applicable functional safety standards and requirements. Using products in an application does not by itself establish any safety features in the application. Designers must ensure compliance with safety-related requirements and standards applicable to their applications. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equipment includes, without limitation, all medical devices identified by the U.S. Food and Drug Administration as Class III devices and equivalent classifications outside the U.S.

TI may expressly designate certain products as completing a particular qualification (e.g., Q100, Military Grade, or Enhanced Product). Designers agree that it has the necessary expertise to select the product with the appropriate qualification designation for their applications and that proper product selection is at Designers' own risk. Designers are solely responsible for compliance with all legal and regulatory requirements in connection with such selection.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's noncompliance with the terms and provisions of this Notice.

> Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated