



AP9214L

#### SINGLE CHIP SOLUTION FOR 1-CELL Li+ BATTERY PACK

### **Description**

The AP9214L is a single chip protection solution specially designed for 1-cell Li+ rechargeable battery pack application.

The AP9214L includes a 1-cell Lion battery protection chip and dual N-CH, ultra low  $R_{SS(ON)}$  MOSFET with common drain.


The AP9214L provides rich battery protection features and can turnoff the N-CH MOSFET by detecting overcharge voltage/current, over discharge voltage/current, or load short circuit. The AP9214L has built-in fixed delay time to save external components.

The AP9214L is available in U-DFN2535-6 package with two kinds of pin options.


#### **Features**

- High Voltage CMOS Process, up to 30V (V<sub>DD</sub> to V<sub>M</sub>)
- Low Quiescent Current (+25°C)
  - In Normal Mode, 3.0µA (Typ.), 4.5µA (Max.), V<sub>DD</sub> = 3.5V
  - In Power-Down Mode, 0.1µA (Max.)
- High-Accuracy Voltage Detection Circuit (+25°C)
  - Overcharge Detection Voltage: 3.5V to 4.5V (5mV Steps)
     Accuracy ±25mV
  - Overcharge Hysteresis Voltage Range: 0.1V to 0.4V (50mV Steps) Accuracy ±50mV
  - Overdischarge Detection Voltage: 2.0V to 3.4V (10mV Steps) Accuracy ±35mV
  - Overdischarge Hysteresis Voltage Range: 0V to 0.7V (40mV Steps) Accuracy ±65mV
  - Discharge Overcurrent Detection Voltage: 0.05V to 0.32V (10mV Steps) Accuracy ±15mV
  - Short Current Detection Voltage: 0.45V to 0.7V (50mV Steps) Accuracy ±100mV
  - Charge Overcurrent Detection Voltage: -0.2V to -0.05V (10mV Steps) Accuracy ±15mV
  - Overcharger Detection Voltage: 8.0V (Fixed) Accuracy ±2V
  - Overcharger Release Voltage: 7.3V (Fixed) Accuracy ±2V
- Built-in Fixed Detection Delay Time (+25°C), Accuracy ±20%
- Power-Down Mode Selectable (Yes or No)
- 0V Battery Charge Selectable (Permission or Inhibition)
- Overcharge Protection Mode Selectable (Auto Release or Latch)
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)

### **Pin Assignments**



U-DFN2535-6 (Option 1)



U-DFN2535-6 (Option 2)

### **Applications**


Li+ Rechargeable Battery Pack

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.



### **Typical Applications Circuit** (Note 4)



A (B) A for Pin-out Option 1 B for Pin-out Option 2

Note:

4. R1 and C1 are used to stabilize the supply voltage of the AP9214L. The recommended range of R1 value is 330Ω to 470Ω and C1 value is 10nF to 1000nF, typical value is 100nF. R2 should be connected between P- to V<sub>M</sub> sense terminal to monitor the status of charger and the charge/discharge current. The R2 should be between 300Ω and 4kΩ, typical value is 2.7kΩ. R1 and R2 are also used as current limit resistors if the battery or charger is connected reversely. Polarity reversing may cause the power consumption of R1 and R2 to go over their power dissipation rating, therefore R1 and R2 values should be selected appropriately for the actual application. If R2 is more than 4kΩ resistor, charge may not be off due to the voltage drop on R2.

For power-down mode, when first connecting AP9214L system board to the battery, it is necessary to use charger or to short P- to the battery negative polarity. Once the AP9214L is activated, the charger or connection can be removed, otherwise the battery cannot discharge current through system board.


The values selected should follow the recommended typical range mentioned above. It has not been confirmed whether the operation is normal or not in circuits other than the above example of connection. In addition, the example of connection shown above and the typical value do not exactly guarantee proper operation. Please perform the actual application to set the suitable value through your complete evaluation.

# **Pin Descriptions**

Pin Number Option 1	Pin Number Option 2	Pin Name	Function
1	1	S1	Source pin of discharging MOSFET, connecting this pin to battery negative pole.
2	2	VSS	Negative power supply pin.
3	3	VDD	Positive power supply pin, connecting this pin to battery positive pole through R1.
4	5	VM	Charger negative input pin, short this pin to S2 pin through R2.
5	4	NC	Not connected, leave this pin floating.
6	6	S2	Source pin of charging MOSFET, connecting this pin to charge negative input.
EP	EP	Drain	Thermal PAD is common drain of charge and discharge MOSFET, so in PCB layout, prefer to use large copper area to cover this pad for better thermal dissipation, then leave it open.



# **Functional Block Diagram**



A (B) A for Pin-out Option 1 B for Pin-out Option 2



### Absolute Maximum Ratings (Notes 5 & 6)

Symbol	Parameter	Ratings	Unit
V <sub>DS</sub>	Supply Voltage (Between V <sub>DD</sub> and V <sub>SS</sub> )	-0.3 to 12	V
$V_{DM}$	Charge Input Voltage (Between $V_{DD}$ and $V_{M}$ for Protection Chip)	-0.3 to 24	V
V <sub>DSS</sub>	MOSFET Drain-to-Source Voltage	24	V
$V_{GSS}$	MOSFET Gate-to-Source Voltage	±12	V
	Continuous Drain Current, V <sub>GS</sub> = 4.5V, T <sub>A</sub> = +25°C	9.0	А
ID	Continuous Drain Current, V <sub>GS</sub> = 4.5V, T <sub>A</sub> = +70°C	7.1	А
PD	Power Dissipation	1000	mW
TJ	Maximum Junction Temperature	+150	°C
T <sub>STG</sub> Storage Temperature Range		-65 to +150	°C

Notes: 5. Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these conditions is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

# **Recommended Operating Conditions**

Symbol	Parameter	Min	Мах	Unit
$V_{DS}$	V <sub>DS</sub> Supply Voltage (Between V <sub>DD</sub> and V <sub>SS</sub> )		5.5	V
$V_{DM}$	V <sub>DM</sub> Charge Input Voltage (Between V <sub>DD</sub> and V <sub>M</sub> )		5.5	V
T <sub>A</sub>	T <sub>A</sub> Operating Ambient Temperature		+85	°C

<sup>6.</sup> Ratings apply to ambient temperature at +25°C. The JEDEC High-K board design used to derive this data was a 2 inch x 2 inch multilayer board with 2-ounce internal power and ground planes and 2-ounce copper traces on the top and bottom of the board.



# $\hline \textbf{Electrical Characteristics} \ (T_A = +25^{\circ}\text{C}, \ V_{DD} = 3.5\text{V}, \ V_{SS} = 0\text{V}, \ R1 = 220\Omega, \ R2 = 1.0\text{k}\Omega, \ C1 = 100\text{nF}, \ unless \ otherwise \ specified.} )$

Symbol	Parameter		Conditions	Min	Тур	Max	Units
Vcu	Overcharge Detection Voltage	_	_		V <sub>CU</sub>	V <sub>CU</sub> + 0.025	V
$V_{CL}$	Overcharge Release Voltage	V <sub>CL</sub> ≠V <sub>CU</sub>		V <sub>CL</sub> - 0.050	$V_{CL}$	V <sub>CL</sub> + 0.050	V
V CL	Overcharge Release voltage	$V_{CL} = V_{CU}$		V <sub>CL</sub> - 0.025	$V_{CL}$	V <sub>CL</sub> + 0.025	V
$V_{DL}$	Overdischarge Detection Voltage	_		V <sub>DL</sub> - 0.035	$V_{DL}$	V <sub>DL</sub> + 0.035	V
Vou	Overdischarge Poleage Voltage	V <sub>DU</sub> ≠ V <sub>DL</sub>		V <sub>DU</sub> - 0.100	$V_{DU}$	V <sub>DU</sub> + 0.100	V
V <sub>DU</sub>	Overdischarge Release Voltage	$V_{DU} = V_{DL}$		V <sub>DU</sub> - 0.035	$V_{DU}$	V <sub>DU</sub> + 0.035	V
$V_{DOC}$	Discharge Overcurrent Detection Voltage	_		V <sub>DOC</sub> -0.015	$V_{DOC}$	V <sub>DOC</sub> +0.015	V
V <sub>SHORT</sub>	Load Short-Circuiting Detection Voltage	_	_		V <sub>SHORT</sub>	V <sub>SHORT</sub> +0.10	V
V <sub>coc</sub>	Charge Overcurrent Detection Voltage	_		V <sub>COC</sub> -0.015	$V_{COC}$	V <sub>COC</sub> +0.015	V
Icc	Current Consumption During Operation	$V_{DD} = 3.5V$	, $V_M = 0V$	1.5	3.0	4.5	μΑ
		$V_{DD} = 1.8V$	Power Down Mode	_	_	0.1	μΑ
I <sub>STB</sub>	Current Consumption at Power Down	VM Pin Floating	Without Power Down Mode (Auto Wake up)	_	_	5.5	μΑ
$R_{VMD}$	Resistance Between VM Pin and VDD Pin	$V_{DD} = 1.8V$	$V_{M} = 0V$	150	300	500	kΩ
R <sub>VMS</sub>	Resistance Between VM Pin and VSS Pin	$V_{DD} = 3.5V$	, V <sub>M</sub> = 1.0V	10	30	50	kΩ
V <sub>0CHA</sub>	0V Battery Charge Starting Charge Voltage	0V Battery	Charging "Available"	1.2	-	_	V
V <sub>0INH</sub>	0V Battery Charge Inhibition Battery Voltage	0V Battery	Charging "Unavailable"	_	_	0.45	V
Vovchg	Overvoltage Charge Detection Voltage	$V_{DD} = 3.5V$		6.0	8.0	10.0	V
Vovchgr	Overvoltage Charge Release Voltage	$V_{DD} = 3.5V$		5.3	7.3	9.3	V
t <sub>CU</sub>	Overcharge Detection Delay Time	_		t <sub>CU</sub> * 0.8	t <sub>CU</sub>	t <sub>CU</sub> * 1.2	ms
t <sub>CUR</sub>	Overcharge Release Delay Time	_		t <sub>CUR</sub> * 0.8	t <sub>CUR</sub>	t <sub>CUR</sub> * 1.2	ms
t <sub>DL</sub>	Overdischarge Detection Delay Time	_		t <sub>DL</sub> * 0.8	t <sub>DL</sub>	t <sub>DL</sub> * 1.2	ms
t <sub>DLR</sub>	Overdischarge Release Delay Time	_	_		t <sub>DLR</sub>	t <sub>DLR</sub> * 1.2	ms
t <sub>DOC</sub>	Discharge Overcurrent Detection Delay Time	_		t <sub>DOC</sub> * 0.8	tDOC	t <sub>DOC</sub> * 1.2	ms
tDOCR	Discharge Overcurrent Release Delay Time			t <sub>DOCR</sub> * 0.8	tDOCR	t <sub>DOCR</sub> * 1.2	ms
tshort	Load Short Detection Delay Time			t <sub>SHORT</sub> * 0.8	tshort	t <sub>SHORT</sub> * 1.2	μs
t <sub>COC</sub>	Charge Overcurrent Detection Delay Time	_		t <sub>COC</sub> * 0.8	tcoc	t <sub>COC</sub> * 1.2	ms
tcocr	Charge Overcurrent Release Delay Time		_		t <sub>COCR</sub>	t <sub>COCR</sub> * 1.2	ms



# **Electrical Characteristics (Cont.)**

 $(T_A = -40^{\circ}C \text{ to } +85^{\circ}C, V_{DD} = 3.5V, V_{SS} = 0V, R1 = 220\Omega, R2 = 1.0k\Omega, C1 = 100nF, unless otherwise specified.)$ 

Symbol	Parameter	(	Conditions	Min	Тур	Max	Units
Vcu	Overcharge Detection Voltage	_		V <sub>CU</sub> - 0.060	V <sub>CU</sub>	V <sub>CU</sub> + 0.040	V
Va	V <sub>CL</sub> Overcharge Release Voltage			V <sub>CL</sub> - 0.080	$V_{CL}$	V <sub>CL</sub> + 0.065	V
VCL	Overcharge Release voltage	V <sub>CL</sub> = V <sub>CU</sub>		V <sub>CL</sub> - 0.060	$V_{CL}$	V <sub>CL</sub> + 0.040	V
V <sub>DL</sub>	Overdischarge Detection Voltage	_		V <sub>DL</sub> - 0.080	$V_{DL}$	V <sub>DL</sub> + 0.080	V
V <sub>DU</sub>	Overdischarge Release Voltage	V <sub>DU</sub> ≠ V <sub>DL</sub>		V <sub>DU</sub> - 0.150	$V_{DU}$	V <sub>DU</sub> + 0.190	V
<b>V</b> D0	Overdischarge Nelease voltage	$V_{DU} = V_{DL}$		V <sub>DU</sub> - 0.080	$V_{DU}$	V <sub>DU</sub> + 0.080	V
V <sub>DOC</sub>	Discharge Overcurrent Detection Voltage	_		V <sub>DOC</sub> -0.021	$V_{DOC}$	V <sub>DOC</sub> +0.024	V
V <sub>SHORT</sub>	Load Short Detection Voltage	_		V <sub>SHORT</sub> -0.34	V <sub>SHORT</sub>	V <sub>SHORT</sub> +0.34	V
Vcoc	Charge Overcurrent Detection Voltage	_		V <sub>COC</sub> -0.040	Vcoc	V <sub>COC</sub> +0.040	V
Icc	Current Consumption During Operation	$V_{DD} = 3.5V$	$V_{M} = 0V$	1.0	3.0	7.0	μΑ
	!	V <sub>DD</sub> =1.8V	Power Down Mode	_	Ī	1.0	μΑ
I <sub>STB</sub>	Current Consumption at Power Down	VM Pin Floating	Without Power Down Mode (Auto Wake up)	_	_	8	μΑ
R <sub>VMD</sub>	Resistance Between VM Pin and VDD Pin	$V_{DD} = 1.8V$		100	300	650	kΩ
R <sub>VMS</sub>	Resistance Between VM Pin and VSS Pin	$V_{DD} = 3.5V$	, V <sub>M</sub> = 1.0V	5	30	65	kΩ
V <sub>0CHA</sub>	0V Battery Charge Starting Charge Voltage	0V Battery "Available"	Charging	1.2	_	_	٧
Voinh	0V Battery Charge Inhibition Battery Voltage	0V Battery "Unavailabl		_	_	0.3	٧
V <sub>OVCHG</sub>	Overvoltage Charge Detection Voltage	$V_{DD} = 3.5V$		5.5	8.0	10.5	V
V <sub>OVCHGR</sub>	Overvoltage Charge Release Voltage	$V_{DD} = 3.5V$		5.0	7.3	9.5	٧
tcu	Overcharge Detection Delay Time	1		t <sub>CU</sub> * 0.6	tcu	t <sub>CU</sub> * 1.4	ms
t <sub>CUR</sub>	Overcharge Release Delay Time	_		t <sub>CUR</sub> * 0.6	tcur	t <sub>CUR</sub> * 1.4	ms
t <sub>DL</sub>	Overdischarge Detection Delay Time	_		t <sub>DL</sub> * 0.6	t <sub>DL</sub>	t <sub>DL</sub> * 1.4	ms
t <sub>DLR</sub>	Overdischarge Release Delay Time	_		t <sub>DLR</sub> * 0.6	t <sub>DLR</sub>	t <sub>DLR</sub> * 1.4	ms
t <sub>DOC</sub>	Discharge Overcurrent Detection Delay Time	_		t <sub>DOC</sub> * 0.6	t <sub>DOC</sub>	t <sub>DOC</sub> * 1.4	ms
t <sub>DOCR</sub>	Discharge Overcurrent Release Delay Time	_		t <sub>DOCR</sub> * 0.6	t <sub>DOCR</sub>	t <sub>DOCR</sub> * 1.4	ms
t <sub>SHORT</sub>	Load Short Detection Delay Time	_		t <sub>SHORT</sub> * 0.6	t <sub>SHORT</sub>	t <sub>SHORT</sub> * 1.4	μs
t <sub>COC</sub>	Charge Overcurrent Detection Delay Time	1		t <sub>COC</sub> * 0.6	t <sub>COC</sub>	t <sub>COC</sub> * 1.4	ms
tcocr	Charge Overcurrent Release Delay Time	_		t <sub>COCR</sub> * 0.6	tcocr	t <sub>COCR</sub> * 1.4	ms



# Electrical Characteristics (Cont., Notes 7, 8)

 $(T_{A}=+25^{\circ}C,\,V_{DD}=3.5V,\,V_{SS}=0V,\,R1=220\Omega,\,R2=1.0k\Omega,\,C1=100nF,\,unless\,otherwise\,specified.)$ 

Symbol	Parameter	Conditions	Min	Тур	Max	Units
I <sub>DSS</sub>	Zero Gate Voltage Drain Current	V <sub>DS</sub> = 20V, V <sub>GS</sub> = 0	_	_	1.0	μΑ
R <sub>SS(ON)1</sub>	Static Source-Source On-Resistance 1	V <sub>DD</sub> = 4.0V, I <sub>D</sub> = 1.0A	10	13	16	mΩ
R <sub>SS(ON)2</sub>	Static Source-Source On-Resistance 2	V <sub>DD</sub> = 3.9V, I <sub>D</sub> = 1.0A	10	13.5	16.5	mΩ
Rss(ON)3	Static Source-Source On-Resistance 3	V <sub>DD</sub> = 3.0V, I <sub>D</sub> = 1.0A	11	14	17	mΩ
V <sub>SD</sub>	Diode Forward Voltage	V <sub>GS</sub> = 0V, I <sub>S</sub> = 1A	_	0.75	1.0	V

Notes:

- 7. In case of Gate-Source voltage of charging MOSFET is 0V. In case of Gate-Source voltage of discharging MOSFET is 0V.
- 8. These specifications are guaranteed by design will not be tested in production.



### **Application Information**

#### **Operation Mode**

#### 1. Normal Status

The AP9214L monitors the battery voltage between the VDD pin and VSS pin as well as the voltage difference between the VM pin and VSS pin to control battery charging and discharging. When the battery voltage is between overdischarge detection voltage ( $V_{DL}$ ) and overcharge detection voltage ( $V_{CU}$ ) as well as the VM pin voltage is between the charge overcurrent detection voltage ( $V_{COC}$ ) and discharge overcurrent detection voltage ( $V_{DOC}$ ), the AP9214L will turn on discharging and charging MOSFET. In these conditions, the battery can charge and discharge freely. Also,  $R_{VMD}$  does not connect to VDD pin and  $R_{VMS}$  does not connect to VSS pin in this status.

#### 2. Overcharge Status

If the battery voltage is more than  $V_{CU}$  during charging status for the overcharge detection delay time ( $t_{CU}$ ) or longer, the AP9214L turns off the charging MOSFET to stop charging.  $R_{VMD}$  and  $R_{VMS}$  are not connected in overcharge status.

When VM pin voltage is lower than V<sub>DOC</sub> and battery voltage falls below V<sub>CL</sub>, the AP9214L will release from overcharge status.

When VM pin voltage is equal or more than V<sub>DOC</sub> and battery voltage falls below V<sub>CU</sub>, the AP9214L will release from overcharge status.

#### 3. Overdischarge Status

If the battery voltage is less than  $V_{DL}$  during discharging status for the overdischarge detection delay time ( $t_{DL}$ ) or longer, the AP9214L turns off the discharging MOSFET to stop discharging. In overdischarge status,  $R_{VMD}$  is connected to VDD and VM pin voltage is pulled up to VDD by  $R_{VMD}$ , but  $R_{VMS}$  is not connected.

For power-down mode version, the AP9214L recovers normal status from overdischarge status only by charging the battery through the charger.

When VM pin voltage to VSS pin voltage is less than typical -0.7V and the battery voltage rises over  $V_{DL}$ , the AP9214L will release from overdischarge status. If VM pin voltage to VSS pin voltage is higher than typical -0.7V, the AP9214L will release from overdischarge status until the battery voltage rises over  $V_{DU}$ .

For auto-wake-up version AP9214LA, the device recovers to normal status from overdischarge status if either of these two conditions are satisfied:

If charger is connected: the AP9214LA overdischarge status is released in the same way as described above in AP9214L overdischarge Status section.

If no charger is connected:

- 1) The battery voltage reaches the overdischarge release voltage (V<sub>DU</sub>) or higher;
- 2) Maintains continuous time more than overdischarge release delay time t<sub>DLR</sub>.

#### 4. Discharge Overcurrent and Short Current Status

When battery is in discharge overcurrent status, if the voltage of the VM pin to VSS pin is equal or more than  $V_{DOC}$  to  $V_{SHORT}$  and detection lasts for the discharge overcurrent detection delay time ( $t_{DOC}$ ) or longer, the AP9214L turns off the discharging MOSFET to stop discharging.

When the battery is in short current status, if the voltage of the VM pin to VSS pin is equal to or more than V<sub>SHORT</sub>, and the detection lasts for the short current detection delay time or longer, the AP9214L turns off the discharge MOSFET to stop discharging.

In discharge overcurrent or short current status,  $R_{VMS}$  is connected to VSS but  $R_{VMD}$  is not connected. The voltage of VM pin is almost equal to  $V_{DD}$  as long as the load is connected. When the load is disconnected, the voltage of VM pin will become almost equal to VSS (due to  $R_{VMS}$  being connected) and then the AP9214L will release from discharge overcurrent or short current status.

#### 5. Charge Overcurrent Status

When the battery is in charge overcurrent status, if the voltage of the VM pin to VSS pin is equal to or less than V<sub>COC</sub> and the detection continues for the charge overcurrent detection delay time (t<sub>COC</sub>) or longer, the AP9214L turns off the charging MOSFET to stop charging.

#### 6. 0V Battery Charging Function (Optional)

This function is available as an option and can be factory set internally. The AP9214L has this function built in.

0V charging function permits charger to recharge the battery whose voltage is 0V due to self-discharge. If 0V charging function is not present, the device will prevent charger to recharge the battery whose voltage is 0V due to self-discharge. (If a device without 0V charging function is needed, please contact Diodes sales team.)



# **Application Information (Cont.)**

#### 7. Overvoltage Charger Detection Circuit

This function is used to monitor the charger voltage between the VDD pin and VM pin, and when this voltage exceeds overvoltage charger detection voltage (8.0V Typ.), the AP9214L will turn off charging MOSFET, when this voltage drops below overvoltage charger release voltage (7.3V Typ.), it then turns on charging MOSFET. There is no delay time setting for detection and release.

#### 8. Power-Down Mode or Auto-Wake-Up Function (Optional)


In device with power-down function, during power-down mode, device enters the overdischarge status. The IC enters sleep mode and the current consumption becomes very low, typically 0.1µA. To release from power-down status to the normal status, charger connection is required.

In device with auto-wakeup mode, the IC remains active in the overdischarge state. The IC is released into the normal state by the operation that increases the battery voltage more than overdischarge release voltage.



# **Application Information (Timing Chart)**

#### 1. Overcharge and Overdischarge Detection




- 1: t<sub>DL</sub>
- 2: t<sub>CU</sub>
- $3: t_{CUR}$
- 4: t<sub>DLR</sub>

- S1: Charger connection
- S2: Load connection
- P1: R<sub>VMD</sub> pull-up connection



# Application Information (Timing Chart) (Cont.)

#### 2. Discharge Overcurrent Detection




- 1: t<sub>DOC</sub>
- 2: t<sub>SHORT</sub>
- 3: t<sub>DOCR</sub>

- S1: Connect over current load
- S2: Connect short current load
- P1: R<sub>VMS</sub> pull-down connection



# **Application Information (Timing Chart) (Cont.)**

### 3. Charge Overcurrent Detection




1: t<sub>COC</sub> 2: t<sub>COCR</sub>

S1: Connect over current charger



### **Ordering Information** (Note 9)



HSBR: U-DFN2535-6 (Pin-out Option 2)

Davisa	Pastrana Cada	Deelsesine	Din Out	7" Tape	and Reel
Device	vice Package Code Packaging		Pin Out	Quantity	Part Number Suffix
AP9214L(X)-X-HSB-7	HSB	U-DFN2535-6	Option 1	3000/Tape & Reel	-7
AP9214L(X)-X-HSBR-7	HSBR	U-DFN2535-6	Option 2	3000/Tape & Reel	-7

### **Voltage Combination**

Part Number	Overcharge Detection Voltage V <sub>CU</sub>	Overcharge Release Voltage V <sub>CL</sub>	Overdischarge Detection Voltage V <sub>DL</sub>	Overdischarge Release Voltage V <sub>DU</sub>	Discharge Overcurrent Detection Voltage V <sub>DOC</sub>	Load Short Detection Voltage V <sub>SHORT</sub>	Charge Overurrent Detection Voltage V <sub>COC</sub>	Over Voltage Charger Detection Voltage V <sub>OVCHG</sub>	Over Voltage Charger Release Voltage V <sub>OVCHGR</sub>	Powr-down Function	Overcharge Protection Mode	Delay Time	0V Battery Charge Function
AP9214L(X)- AA-HSB(X)-7	4.375V	4.175V	2.500V	2.900V	0.150V	0.700V	-0.150V	8.0V	7.3V	Selectable	Auto Release	Option 1	Permission
AP9214L(X)- AB-HSB(X)-7	4.425V	4.225V	2.500V	2.900V	0.150V	0.700V	-0.150V	8.0V	7.3V	Selectable	Auto Release	Option 1	Permission
AP9214L(X)- AC-HSB(X)-7	4.375V	4.175V	2.500V	2.900V	0.095V	0.700V	-0.095V	8.0V	7.3V	Selectable	Auto Release	Option 1	Permission
AP9214L(X)- AD-HSB(X)-7	4.375V	4.175V	2.500V	2.900V	0.120V	0.700V	-0.120V	8.0V	7.3V	Selectable	Auto Release	Option 1	Permission
AP9214L(X)- AE-HSB(X)-7	4.200V	4.100V	2.500V	3.000V	0.300V	0.550V	-0.100V	8.0V	7.3V	Selectable	Auto Release	Option 1	Permission
AP9214L(X)- AF-HSB(X)-7	4.375V	4.175V	2.500V	2.900V	0.180V	0.700V	-0.180V	8.0V	7.3V	Selectable	Auto Release	Option 1	Permission
AP9214L(X)- AG-HSB(X)-7	4.375V	4.175V	2.500V	2.900V	0.075V	0.700V	-0.075V	8.0V	7.3V	Selectable	Auto Release	Option 1	Permission
AP9214L(X)- AH-HSB(X)-7	4.425V	4.225V	2.500V	2.900V	0.075V	0.700V	-0.075V	8.0V	7.3V	Selectable	Auto Release	Option 1	Permission
AP9214L(X)- AI-HSB(X)-7	4.500V	4.300V	2.400V	2.800V	0.150V	0.700V	-0.075V	8.0V	7.3V	Selectable	Auto Release	Option 1	Permission
AP9214L(X)- AJ-HSB(X)-7	4.375V	4.175V	2.400V	2.800V	0.125V	0.700V	-0.125V	8.0V	7.3V	Selectable	Auto Release	Option 1	Permission
AP9214L(X)- AK-HSB(X)-7	4.250V	4.050V	2.400V	3.000V	0.150V	0.700V	-0.150V	8.0V	7.3V	Selectable	Auto Release	Option 1	Permission
AP9214L(X)- AL-HSB(X)-7	4.275V	4.175V	2.300V	2.400V	0.180V	0.700V	-0.180V	8.0V	7.3V	Selectable	Auto Release	Option 1	Permission
AP9214L(X)- AM-HSB(X)-7	4.375V	4.175V	2.300V	2.400V	0.180V	0.700V	-0.180V	8.0V	7.3V	Selectable	Auto Release	Option 1	Permission
AP9214L(X)- AN-HSB(X)-7	4.225V	4.025V	3.200V	3.400V	0.060V	0.450V	-0.060V	8.0V	7.3V	Selectable	Auto Release	Option 1	Permission
AP9214L(X)- BA-HSB(X)-7	4.240V	4.140V	3.000V	3.100V	0.081V	0.700V	-0.081V	8.0V	7.3V	Selectable	Auto Release	Option 1	Permission



### Ordering Information (Cont.) (Note 9)

### **Delay Time Combination**

Part Number	Overcharge Detection Delay Time t <sub>cu</sub>	Overcharge Release Delay Time t <sub>CUR</sub>	Overdischarge Detection Delay Time t <sub>DL</sub>	Overdischarge Release Delay Time t <sub>DLR</sub>	Discharge Overcurrent Detection Delay Time t <sub>DOC</sub>	Discharge Overcurrent Release Delay Time t <sub>DOCR</sub>	Charge Overcurrent Detection Delay Time t <sub>COC</sub>	Charge Overcurrent Release Delay Time t <sub>COCR</sub>	Load Short Detection Delay Time t <sub>SHORT</sub>
AP9214L(X)-XX- HSB(X)-7	1.0s	2.0ms	115ms	2.0ms	10.0ms	2.0ms	10.0ms	2.0ms	320µs

Note: 9. If products of any other voltage versions are needed, please contact with the local sales' office.

# **Marking Information**

(Top View)

\*XX(XXX)

 $\underline{Y} \underline{W} \underline{X}$ 

 $\frac{XX(XXX)}{Y}$ : Identification Code (2~5 Codes)  $\frac{X}{Y}$ : Year: 0 to 9

W : Week : A to Z : 1 to 26 week;

a to z: 27 to 52 week; z represents

52 and 53 week X : Internal Code



# **Marking Information** (Cont.)


Part Number	Package	Identification Code
AP9214LA-AA-HSB-7	U-DFN2535-6	14AA
AP9214LA-AB-HSB-7	U-DFN2535-6	14AB
AP9214LA-AC-HSB-7	U-DFN2535-6	14AC
AP9214LA-AD-HSB-7	U-DFN2535-6	14AD
AP9214LA-AE-HSB-7	U-DFN2535-6	14AE
AP9214LA-AF-HSB-7	U-DFN2535-6	14AF
AP9214LA-AG-HSB-7	U-DFN2535-6	\$6
AP9214LA-AH-HSB-7	U-DFN2535-6	S8
AP9214LA-AII-II-SB-7 AP9214LA-AI-HSB-7		
	U-DFN2535-6	14AI
AP9214LA-AJ-HSB-7	U-DFN2535-6	14AJ
AP9214LA-AK-HSB-7	U-DFN2535-6	14AK
AP9214LA-AL-HSB-7	U-DFN2535-6	14AL
AP9214LA-AM-HSB-7	U-DFN2535-6	14AM
AP9214LA-AN-HSB-7	U-DFN2535-6	14AN
AP9214LA-BA-HSB-7	U-DFN2535-6	14BA
AP9214LA-AA-HSBR-7	U-DFN2535-6	14AAR
AP9214LA-AB-HSBR-7	U-DFN2535-6	14ABR
AP9214LA-AC-HSBR-7	U-DFN2535-6	14ACR
AP9214LA-AD-HSBR-7	U-DFN2535-6	14ADR
AP9214LA-AE-HSBR-7	U-DFN2535-6	14AER
AP9214LA-AF-HSBR-7	U-DFN2535-6	14AFR
AP9214LA-AG-HSBR-7	U-DFN2535-6	R7
AP9214LA-AH-HSBR-7	U-DFN2535-6	RH
AP9214LA-AI-HSBR-7	U-DFN2535-6	14AIR
AP9214LA-AJ-HSBR-7	U-DFN2535-6	14AJR
AP9214LA-AK-HSBR-7	U-DFN2535-6	14AKR
AP9214LA-AL-HSBR-7	U-DFN2535-6	14ARR
AP9214LA-AM-HSBR-7	U-DFN2535-6	14AMR
AP9214LA-AN-HSBR-7	U-DFN2535-6	14ANR
AP9214LA-BA-HSBR-7	U-DFN2535-6	14BAR
AP9214L-AA-HSB-7	U-DFN2535-6	14A
AP9214L-AB-HSB-7	U-DFN2535-6	14B
AP9214L-AC-HSB-7	U-DFN2535-6	14C
AP9214L-AD-HSB-7	U-DFN2535-6	14D
AP9214L-AE-HSB-7	U-DFN2535-6	14E
AP9214L-AF-HSB-7	U-DFN2535-6	14F
AP9214L-AG-HSB-7	U-DFN2535-6	X8
AP9214L-AH-HSB-7	U-DFN2535-6	X9
AP9214L-AI-HSB-7	U-DFN2535-6	141
AP9214L-AJ-HSB-7	U-DFN2535-6	14J
AP9214L-AK-HSB-7	U-DFN2535-6	14K
AP9214L-AL-HSB-7	U-DFN2535-6	14L
AP9214L-AM-HSB-7	U-DFN2535-6	14M
AP9214L-AN-HSB-7	U-DFN2535-6	14N
AP9214L-AA-HSBR-7	U-DFN2535-6	14AR
AP9214L-AA-13BR-7 AP9214L-AB-HSBR-7	U-DFN2535-6	14BR
AP9214L-AD-HSBR-7	U-DFN2535-6	14CR
AP9214L-AC-HSBR-7 AP9214L-AD-HSBR-7	U-DFN2535-6	14DR
AP9214L-AE-HSBR-7	U-DFN2535-6	14ER
AP9214L-AF-HSBR-7	U-DFN2535-6	14FR
AP9214L-AG-HSBR-7	U-DFN2535-6	14GR
AP9214L-AH-HSBR-7	U-DFN2535-6	14HR
AP9214L-AI-HSBR-7	U-DFN2535-6	14IR
AP9214L-AJ-HSBR-7	U-DFN2535-6	14JR
AP9214L-AK-HSBR-7	U-DFN2535-6	14KR
AP9214L-AL-HSBR-7	U-DFN2535-6	14LR
AP9214L-AM-HSBR-7	U-DFN2535-6	14MR
AP9214L-AN-HSBR-7	U-DFN2535-6	14NR



# **Package Outline Dimensions**

Please see http://www.diodes.com/package-outlines.html for the latest version.

#### U-DFN2535-6 (Type B)




	U-DFN2535-6 (Type B)					
Dim	Min Max Typ					
Α	0.50	0.60	-			
A1	0.00	0.05	0.02			
A3	-	-	0.127			
b	0.25	0.35	0.30			
b2	1.05	1.15	1.10			
D	2.45	2.55	2.50			
D2	2.01	2.21	2.11			
Е	3.45	3.55	3.50			
E2	2.20	2.40	2.30			
е	-	-	0.55			
e1	-	-	0.95			
L	0.25	0.35	0.30			
Z	-	-	0.15			
All	All Dimensions in mm					

# Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

### U-DFN2535-6 (Type B)



Dimensions	Value
Dilliensions	(in mm)
С	0.550
C1	0.950
Х	0.400
X1	1.200
X2	2.210
Υ	0.500
Y1	2.400



#### **IMPORTANT NOTICE**

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

#### **LIFE SUPPORT**

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
  - 1. are intended to implant into the body, or
  - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2018, Diodes Incorporated

www.diodes.com