

TO:

Halogen Free Part

SPECIFICATION FOR APPROVAL

DESCRIPTION: MINI PCI-E 0.8PITCH 52P 5.2H

CUSTOMER P/N:

LOTES P/N: AAA-PCI-092-P07

CUSTOMER APPROVAL SIGN:

SEND BY	QA CONFIRM	R&D CONFIRM	PREPARE BY
		Barney	Xi huang Li








Lotes SZ Lotes GZ

Lotes TW

www.lotes.cc

CopyRight©2003 LOTES CO., LTD All right reserved



LOTES CO., LTD

INDEX

PAGE 1 INDEX

PAGE 2 ~ 5 PRODUCT SPECIFICATION

PAGE 6 ~ 12 PRODUCT DRAWING AND PACKAGE

PAGE 13 ~ 24 PRODUCT TEST REPORT

PAGE 25 ~ 65 PRODUCT MATERIAL REPORT &SGS

PRODUCT SPECIFICATION

REV	ECR No.
4C	SN14***

DIMENSION

- 1. This specification covers 0.8mm pitch MINI PCI EXPRESS(AAA-PCI-073/092/093-***) connector series.
- 2. The physical dimensions and the 0.8mm pitch MINI PCI EXPRESS connector are shown in drawing.

MATERIAL AND FINISH

- 1. Housing: High temperature thermoplastic.
- 2. Contact: Copper Alloy, Nickel-plating over all, Gold Plating on contact area, Matte Tin plated on solder area.
- 3.PEG: Copper Alloy, Matte Tin plated on solder area.

OPERATING PERFORMANCE

1.Operation Temperature: -40°C to 80°C 2.Voltage Rating: 25 V AC per contact

3.Current Rating: 0.5 A

ELECTRICAL PERFORMANCE

Test item	Test condition	Requirements
Examination of product	Visual inspectionEIA-364-18	No physical damage
Low Level Contact Resistance	Mate connectors: apply a current of 10mA(max) at open circuit voltage of 20mV (max) EIA-364-23	 55mΩ MAX. per contact (Initial) ∴LLCR=20mΩ Max.(Final)
Insulation resistance	Applying 500VDC between adjacent contacts of unmated and unmount connectors EIA-364-21	• 500MΩ MIN
Dielectric withstanding voltage	 Measured by applying 300VAC for one minute between adjacent contacts of unmated connector assemblies. EIA-364-20 	No breakdown or flashCurrent leakage:1mA

	0.8mm PITCH MINI PCI EXPRESS CONNECTOR					
	DOCUMENT No:	REV: 4C		PAGE:		
LOTES CO., LTD	APPROVED BY: CHECKED BY: Barney 01/09'14 Vito 01/09'14			1 OF 4		
			ED BY: WR		ITTEN BY:	
			Lxh 01/09'14			

PRODUCT NAME:

PRODUCT SPECIFICATION

REV	ECR No.
4C	SN14***

MECHANICAL PERFORMANCE

Test item	Test condition	Requirements
Vibration test (Random)	Subject mated connectors and vibrate per EIA 364-28 test Condition.VII test condition letter D(15 minutes in each of 3 mutually perpendicular directions)	 No electrical discontinuity greater than 1 microsecond. △LLCR =20mΩ Max.(Final)
Mechanical shock	Subject mated connector to 50Gs,half-sine shock pulses of 11 millisecond duration,3drops in each direction applied along the 3 mutually perpendicular planes total 18 shock. EIA-364-27 test condition A	 No electrical discontinuity greater than 1 microsecond △LLCR =20mΩ Max.(Final) No physical damage
Durability (repeated mate/un-mate)	Repeat insertion the card to the connector and extraction card from the connector for 50 cycles. EIA-364-09	• △LLCR =20mΩ Max.(Final)
Mating and Unmating force	Insert the card at the specified angle Rotate the card into position Reverse the installation sequence to unmating EIA-364-13	• 2.3 Kgf MAX

ΊT	LE:			

0.8mm PITCH MINI PCI EXPRESS CONNECTOR

DOCUMENT No: REV: PAGE: 2 OF 4

APPROVED BY: CHECKED BY: WRITTEN BY: Barney 01/09'14 Vito 01/09'14 Lxh 01/09'14

ENVIRONMENTAL PERFORMANCE

DD O DI	REV	ECR No.		
PRODU	JCT SPECIFICATION	4C	SN14***	
Test item	Test condition	Requirements		
		• △LLCR =20mΩ	! Max.(Final)	
Humidity	• Expose the mates connectors to 40±2℃,relative	 Insulation resist 	ance:500MΩMin.	
(steady state)	humidity 90~95%RH for 96 hours.EIA-364-31	No physical damage.		
The word sheet	• Expose the connectors to -55°C/30min. and 85°C	• △LLCR =20mΩ	Max.(Final)	
Thermal shock	/30min.(Repeat 10 cycles)EIA-364-32 condition I	No physical dan	nage.	
0.11	Solder temperature:245+5°C		2-2/14	
Solder ability	Immersion Duration:3+0.5sec.	Wet solder coverage: 95%M		
	Subject the connector to 5%salt-solution			
Salt spray	concentration at 35° for 24 hours.	• △LLCR =20mΩMax .(Final)		
	• EIA-364-26			
	• EIA -364-56C			
Resistance to Solder	IR Reflow:	. No ovidence of	nhyoigal damaga	
Heat	The peak temperature on the board shall be	No evidence of physical damag		
	maintained for 10 second 250 <u>+</u> 10°ℂ			
	Soldering iron method			
Bowerk temperature	Soldering Time : 5 sec.	No evidence of physical damage		
Rework temperature	Solder Temperature : 370-400°C	· No evidence of	priysical damage	
	0.5 mm from terminal tip			
	Mate PCB module and subject to 85±3℃ for 96 hours	Contact resistar	nce: △LLCR	
Temperature life	EIA-364-17 condition A	=20mΩ Max.(Final)		

TEST CONDITIONS

The tests shall be carried out under the conditions as the referring.

- (1).Temperature:15~35°C.
- (2). Humidity: 45~75%.

PACKAGE

All parts shall be packaged and packed to protect against physical damage, corrosion and deterioration during shipment and storage.

	TITLE:				
LOTES CO., LTD	0.8mm PITCH MINI PCI EXPRESS CONNECTOR				
	DOCUMENT No:	REV:		PAGE:	
	SP-AAA-PCI-073		4C	;	3 OF 4
	APPROVED BY:	PPROVED BY: CHECK		(ED BY: WRITTEN B	
	Barney 01/09'14 Vito 01/		09'14	L	xh 01/09'14

PRODUCT SPECIFICATION


REV	ECR No.
4C	SN14***

TEST SEQUENCE:

Test or Examination				Test	Group			
	Α	В	С	D	E	F	G	Н
Examination of Product	1,5	1,9	1,5	1,8	1,3	1,5	1,5	1,3
Contact Resistance	2,4	2,6	2,4			2,4	2,4	
Insulation Resistance				2,6				
Dielectric Withstanding Voltage				3,7				
Vibration	3							
Durability (Repeated)		5						
Mating force		3,7						
Unmating force		4,8						
Solder ability					2			
Humidity (Steady State)				5				
Thermal Shock				4				
Mechanical shock			3					
Temperature life						3		
Salt spray							3	
Resistance to Soldering Heat								2

RECOMMENDED INFORARED REFLOW CONDITION

Suggestion: In SMT process, the thickness of solder paste is 0.13mm minimum



LOTES CO., LTD


NODUC	
0.8m	m PITCH MINI PCI EXPRESS CONNECTOR


DOCUMENT No: REV: PAGE:


SP-AAA-PCI-073 4C 4 OF 4


 APPROVED BY:
 CHECKED BY:
 WRITTEN BY:


 Barney 01/09'14
 Vito 01/09'14
 Lxh 01/09'14



















Report No. GL-RD090107 GL-P-027-005

Product: MINI PCI-E 5.2H **Part NO.:** AAA-PCI-092-***

Test Object: Product Reliability Test

Sample Quantity: 40PCS

Test Environment: 20-24°C , 50-62%RH

Date of Test: Jan.08,09~ Mar.02,09

Test Result Summary:

Qualification Group	Pass / Fail	Comments
Test Group A	Pass	
Test Group B	Pass	
Test Group C	Pass	
Test Group D	Pass	
Test Group E	Pass	
Test Group F	Pass	
Test Group G	Pass	
Test Group H	Pass	



Report No. GL-RD090107

GL-P-027-005

1. Testing Sequence:

	Test or examination			7	Γest gro	oup step)		
	Test of examination	A	В	С	D	Е	F	G	Н
1	Examination of product	1,5	1,9	1,5	1,8	1,3	1,5	1,5	1,3
2	Contact Resistance	2,4	2,6	2,4			2,4	2,4	
3	Insulation Resistance				2,6				
4	4 Dielectric withstanding voltage				3,7				
5	Vibration	3							
6	Durability		5						
7	Mating force		3,7						
8	Unmating Force		4,8						
9	Solder ability					2			
10	Humidity				5				
11	Thermal Shock				4				
12	Mechanical shock			3					
13	Temperature life						3		
14	Salt spray							3	
15	Resistance to Solder Heat								2
	Specimen quantity (pcs)	5	5	5	5	5	5	5	5



Report No. GL-RD090107

GL-P-027-005

2. Test Item & Condition & Requirements:

	Test item	Test condition	Requirements
1	Examination of product	EIA-364-18. Meets requirements of product drawing	No physical damage
2	Contact Resistance	EIA 364-23 Subject mated contacts assembled in housing to closed circuit current of 10mA max. at open circuit voltage of 20mV max.	55 milliohms max.(initial). △R=20 milliohms max.(Final)
3	Dielectric Withstanding Voltage	EIA 364-20 Subject mated connector with a voltage of 300VAC for 1.0minute between adjacent contacts.	No disruptive discharge or leakage greater than 1.0 mA(max)
4	Insulation Resistance	EIA 364-21 Impressed voltage 500V DC. Test between adjacent contacts of unmated connectors.	500 MΩmin
5	Durability	EIA 364-9 Repeated insertion and Removal of P.C.B from the connector for 50 cycles	Show no physical damage △R=20 milliohms max.(Final)
6	Vibration	EIA 364-28 Subject mated connectors to 10-55-10Hz traversed in 1 minute at 1.52 mm amplitude 2hours each of 3 mutually perpendicular planes.100mA applied.	No electrical discontinuity greater Than 1.0microsecond shall occur. ΔR=20 mΩ max.(Final)
7	Mechanical Shock	EIA 364-27 Subject mated specimens to 50G's half- sine shock pulses of 11 milliseconds duration three shocks in each direction applied along three mutually perpendicular planes (18 shocks)	No electrical discontinuity greater than 1.0 microsencond shall occur. ΔR=20 mΩ max.(Final)



Report No. GL-RD090107

GL-P-027-005

8	Mating and Unmating force	EIA 364-13 Insert the card at the specified angle Rotate the card into position Reverse the installtion sequence to unmating	2.3kgfmax.
9	Temperature Life	EIA 364-17 Expose mated connectors to a temperature of 85+/-3°C for 96hours.	Show no physical damage. $\triangle R=20 \text{ m}\Omega \text{ max.(Final)}$
10	Thermal Shock	EIA 364-32 Mated connector -55°C/30 min., +85°C/30min. Making this a cycle, repeat 10 cycles	Show no physical damage. $\triangle R$ =20 m Ω max.(Final)
11	Humidity temperature cycling	EIA 364-31 Subject specimens to 96 hours at 40+/- 2°C, with RH of 90~95%	Show no physical damage. $\triangle R$ =20 m Ω max.(Final) Insulationresistance:500M Ω min
12	Solder ability	EIA 364-52 Solder Temperature(Tin): 245±5°C Immersion Durating::3+0.5 sec.	Wet solder coverage 95% min.
13	Salt Spray	EIA 364-26 Mated connector expose to 24 hours at 35±2°C and 5% salt-solution concentration. After the test, specimens shall be washed with running water and dried naturally before the measurement of contact resistance.	Show no physical damage
14	Resistance to solder heat	EIA-364-56 Max.peak temperature of 260+/-5°C 300°C with 10second(sohdering iron)	Show no physical damage.



Report No. GL-RD090107

GL-P-027-005

3. Testing Equipment:

Name	Model
Microscope	MITUTOYO-TM
Milliohmmeter	KEITHLEY-580
Withstanding voltage & insulation auto tester	ZENTECH-9052
Load cell auto tester	ALGOL-1220s
Thermal shock test chamber	CHANGHONG-SH-T-601
Temperature & humidity cycling chamber	WT-RF-5EE
Mechanical shock tester	King Design-DP-1200-ST-250
Vibration tester	King Design-9363EM-600F2K-40N120
High temperature oven	SMO-4
Salt Spray tester	SSF-060
PCB soldering machine	JIAZE-PS-2000

4. Testing Result:

Group A:

	Examination step/ item	Sample 1	Sample 2	Sample 3	Sample 4	Sample 5	Unit	Pass/fail
1	Examination of product	Normal	Normal	Normal	Normal	Normal	/	Pass
2	LLCR	40.37	37.84	36.93	39.41	42.76	mΩ	Pass
3	Vibration	Normal	Normal	Normal	Normal	Normal	/	Pass
4	LLCR	42.86	44.77	37.97	40.54	46.23	mΩ	Pass
5	Examination of product	Normal	Normal	Normal	Normal	Normal	/	Pass

Group B:

	Examination step/ item	Sample 1	Sample 2	Sample 3	Sample 4	Sample 5	Unit	Pass/fail
1	Examination of Product	Normal	Normal	Normal	Normal	Normal	/	Pass
2	LLCR	39.79	42.14	41.44	42.04	41.77	$m\Omega$	Pass
3	Mating force	0.15	0.32	0.10	0.13	0.19	kgf	Pass
4	Unmating force	0.09	0.20	0.06	0.01	0.07	kgf	Pass
5	Durability	Normal	Normal	Normal	Normal	Normal	/	Pass
6	LLCR	53.10	52.87	51.18	51.06	52.75	$m\Omega$	Pass
7	Mating force	0.31	0.21	0.24	0.15	0.25	kgf	Pass
8	Unmating force	0.02	0.05	0.05	0.03	0.09	kgf	Pass
9	Examination of Product	Normal	Normal	Normal	Normal	Normal	/	Pass



Report No. GL-RD090107

GL-P-027-005

Group C:

	Examination step/ item	Sample 1	Sample 2	Sample 3	Sample 4	Sample 5	Unit	Pass/fail
1	Examination of Product	Normal	Normal	Normal	Normal	Normal	/	Pass
2	LLCR	42.34	39.48	37.21	38.49	41.42	mΩ	Pass
3	Mechanical shock	Normal	Normal	Normal	Normal	Normal	/	Pass
4	LLCR	38.94	38.49	37.17	37.36	38.18	mΩ	Pass
5	Examination of Product	Normal	Normal	Normal	Normal	Normal	/	Pass

Group D:

	ար ու							
	Examination step/ item	Sample 1	Sample 2	Sample 3	Sample 4	Sample 5	Unit	Pass/fail
1	Examination of Product	Normal	Normal	Normal	Normal	Normal	/	Pass
2	IR	>500	>500	>500	>500	>500	ΜΩ	Pass
3	DWV	300	300	300	300	300	V	Pass
4	Thermal shock	Normal	Normal	Normal	Normal	Normal	/	Pass
5	Humidity	Normal	Normal	Normal	Normal	Normal	/	Pass
6	IR	>500	>500	>500	>500	>500	ΜΩ	Pass
7	DWV	300	300	300	300	300	V	Pass
8	Examination of Product	Normal	Normal	Normal	Normal	Normal	/	Pass

Group E:

	Examination Step/ Item	Sample 1	Sample 2	Sample 3	Sample 4	Sample 5	Unit	Pass/fail
1	Examination of product	Normal	Normal	Normal	Normal	Normal	/	Pass
2	Solder ability	Normal	Normal	Normal	Normal	Normal	/	Pass
3	Examination of product	Normal	Normal	Normal	Normal	Normal	/	Pass

Group F:

_									
]	Examination step/ item	Sample 1	Sample 2	Sample 3	Sample 4	Sample 5	Unit	Pass/fail
	1	Examination of Product	Normal	Normal	Normal	Normal	Normal	/	Pass
	2	LLCR	35.95	37.55	35.70	35.00	35.55	mΩ	Pass
	3	Temperature life	Normal	Normal	Normal	Normal	Normal	/	Pass
	4	LLCR	40.13	42.42	40.46	39.27	41.48	mΩ	Pass
	5	Examination of Product	Normal	Normal	Normal	Normal	Normal	/	Pass



Report No. GL-RD090107

GL-P-027-005

Group G:

	Examination step/ item	Sample 1	Sample 2	Sample 3	Sample 4	Sample 5	Unit	Pass/fail
1	Examination of Product	Normal	Normal	Normal	Normal	Normal	/	Pass
2	LLCR	40.89	39.85	42.73	44.50	40.01	mΩ	Pass
3	Salt spray	Normal	Normal	Normal	Normal	Normal	/	Pass
4	LLCR	44.45	41.60	36.95	35.20	35.60	mΩ	Pass
5	Examination of Product	Normal	Normal	Normal	Normal	Normal	/	Pass

Group H:

	Examination step/ item	Sample 1	Sample 2	Sample 3	Sample 4	Sample 5	Unit	Pass/fail
1	Examination of Product	Normal	Normal	Normal	Normal	Normal	/	Pass
2	Resistance to solder heat	Normal	Normal	Normal	Normal	Normal	/	Pass
3	Examination of Product	Normal	Normal	Normal	Normal	Normal	/	Pass



Report No. GL-RD090107

GL-P-027-005

5. The LLCR as follow:

Group A

					A-Vib	ration				
NO			Initial				Afte	er Vibrat	ion	
	A1	A2	A3	A4	A5	A1	A2	A3	A4	A5
1-3	38.55	37.03	36.93	37.30	38.03	42.86	37.08	37.97	38.18	38.52
5-7	36.97	36.94	36.70	37.26	35.96	39.38	44.77	37.45	37.68	39.17
9-11	37.57	36.85	36.54	37.79	37.75	39.86	39.57	36.63	38.52	38.40
13-15	37.28	37.07	36.71	36.65	36.52	39.88	37.59	37.22	37.09	38.03
17-19	36.81	37.15	36.31	37.53	38.30	37.66	37.00	36.58	37.72	39.08
21-23	36.81	36.84	36.37	37.52	38.07	37.76	36.45	36.24	38.06	38.88
25-27	37.07	37.24	36.09	39.41	38.76	38.11	36.90	36.18	40.54	40.41
29-31	38.31	36.85	36.37	38.12	37.50	40.18	36.48	36.67	38.71	38.44
33-35	37.83	37.14	36.24	39.17	42.76	39.04	37.04	36.98	38.71	46.23
37-39	37.49	36.60	36.08	37.07	38.53	38.88	36.42	36.09	37.56	39.10
41-43	40.37	37.84	36.03	37.33	37.04	42.84	37.06	36.13	38.26	37.78
45-47	37.14	37.57	36.56	36.65	37.75	39.32	36.75	36.61	37.13	38.70
49-51	37.33	37.03	36.63	37.16	37.88	40.08	37.17	37.06	36.85	38.93
2-4	25.64	27.06	26.78	25.86	27.44	26.83	25.39	26.21	25.16	26.41
6-8	27.35	27.16	29.71	26.09	25.93	26.90	25.85	25.42	25.67	26.23
10-12	26.46	27.99	26.75	28.55	25.77	26.53	25.88	25.69	26.00	26.44
14-16	26.40	28.61	26.47	25.95	26.47	26.10	26.23	25.77	25.78	26.40
18-20	26.90	26.94	26.40	26.37	27.57	27.04	25.71	25.61	25.98	26.67
22-24	26.53	27.01	25.94	26.33	26.40	26.30	27.02	25.30	25.64	27.38
26-28	26.31	26.85	28.84	26.32	26.06	27.26	26.44	26.42	25.67	27.95
30-32	26.62	27.54	26.30	26.77	27.39	26.24	26.34	26.01	26.64	26.70
34-36	26.65	26.32	26.09	26.68	25.75	27.49	26.63	26.52	25.99	28.09
38-40	25.99	26.63	25.81	26.81	26.34	26.80	26.52	26.21	25.95	26.65
42-44	25.56	26.30	27.45	26.56	25.86	27.23	26.54	25.76	25.66	26.91
46-48	25.68	26.96	25.92	26.75	25.77	27.06	26.90	28.65	25.66	27.35
50-52	25.06	25.97	25.51	25.93	26.22	26.88	26.06	27.45	25.68	27.23
Max	40.37	37.84	36.93	39.41	42.76	42.86	44.77	37.97	40.54	46.23
Min	25.06	25.97	25.51	25.86	25.75	26.10	25.39	25.30	25.16	26.23
Avg	31.95	32.06	31.59	32.07	32.22	33.25	31.99	31.49	31.94	33.15
Stdev	5.88	5.16	5.00	5.70	6.08	6.66	6.05	5.42	6.30	6.51



Report No. GL-RD090107

GL-P-027-005

Group B

Toup D					B-Dura	ability				
NO			Initial				After	r Durabi	litye	
	B1	B2	В3	B4	B5	B1	B2	В3	B4	B5
1-3	37.87	40.93	41.44	42.04	37.71	49.98	52.87	51.18	51.06	51.81
5-7	38.22	39.65	37.93	40.44	37.17	52.63	52.50	45.46	47.54	52.67
9-11	38.15	42.14	38.49	38.13	41.24	52.05	52.16	48.05	48.63	51.88
13-15	38.46	40.12	35.95	37.24	40.65	51.19	52.02	48.53	47.17	50.69
17-19	36.90	38.75	37.65	37.08	37.88	53.10	46.52	47.06	47.21	48.32
21-23	37.67	39.12	38.18	40.56	38.38	48.99	46.53	47.44	46.27	46.14
25-27	37.51	38.01	38.54	39.23	38.18	52.09	47.03	49.29	49.01	49.31
29-31	37.89	38.18	36.52	38.54	38.80	48.68	47.93	47.15	46.94	48.86
33-35	38.27	39.16	37.74	38.07	38.57	49.83	52.87	48.64	46.53	51.14
37-39	38.73	38.34	36.35	37.88	38.93	51.47	48.86	47.82	46.94	51.44
41-43	38.38	37.87	37.26	37.88	39.73	52.63	49.74	48.30	47.74	52.75
45-47	39.79	37.96	36.41	38.38	41.77	51.95	51.43	48.47	47.65	51.18
49-51	38.75	38.76	36.60	36.93	40.05	52.71	51.89	49.21	49.96	51.23
2-4	25.93	27.65	26.23	26.56	26.49	37.50	40.23	41.03	38.75	39.40
6-8	25.70	28.58	26.88	26.31	27.24	37.51	40.54	40.63	38.59	39.73
10-12	26.31	27.67	26.90	27.32	26.98	39.14	40.24	40.38	39.62	39.74
14-16	26.49	28.00	26.13	26.94	26.70	39.03	41.03	41.88	38.69	42.08
18-20	25.56	27.01	26.15	27.58	27.10	39.45	39.48	40.81	39.01	39.88
22-24	26.18	27.41	26.09	27.16	26.95	38.71	38.80	40.70	38.44	39.09
26-28	25.59	27.07	26.08	27.03	26.98	39.70	39.02	39.59	38.58	39.14
30-32	26.55	27.55	25.88	26.75	27.45	38.59	39.49	40.10	38.51	39.19
34-36	26.57	28.28	26.05	26.88	27.54	39.87	39.60	41.26	39.27	38.28
38-40	26.74	27.74	26.27	27.11	27.90	38.56	41.89	39.27	38.07	38.82
42-44	26.55	27.69	26.08	26.97	27.75	39.37	39.69	41.59	38.39	38.63
46-48	27.14	27.10	26.92	26.92	28.06	39.22	38.88	39.20	38.80	39.75
50-52	26.64	26.97	26.30	26.94	27.68	39.14	39.91	40.68	37.79	39.09
Max	39.79	42.14	41.44	42.04	41.77	53.10	52.87	51.18	51.06	52.75
Min	25.56	26.97	25.88	26.31	26.49	37.50	38.80	39.20	37.79	38.28
Avg	32.25	33.37	31.96	32.80	33.22	45.12	45.04	44.37	43.27	45.01
Stdev	6.09	5.97	5.86	6.06	6.14	6.44	5.55	4.06	4.82	5.86



Report No. GL-RD090107

GL-P-027-005

Group C

Group C										
				C	-Mechan	ical shoc	k			
NO			Initial					echanica		
	C1	C2	C3	C4	C5	C1	C2	C3	C4	C5
1-3	40.09	39.36	36.78	37.45	38.25	37.57	37.91	36.09	36.61	36.59
5-7	39.34	38.10	36.41	38.30	39.44	37.56	37.43	36.23	37.12	37.78
9-11	39.34	38.37	36.83	38.20	38.19	37.12	37.94	36.29	37.06	37.05
13-15	40.83	39.48	36.97	38.49	36.14	37.18	38.19	36.83	37.36	36.64
17-19	39.50	36.89	36.41	36.14	37.99	36.92	37.16	36.15	36.59	37.25
21-23	42.34	37.25	37.07	37.54	39.16	38.94	37.19	36.71	36.81	38.18
25-27	40.48	38.28	36.28	37.05	41.42	38.22	38.49	36.45	36.53	36.95
29-31	38.65	36.51	36.55	37.04	37.51	38.28	37.61	37.07	36.71	37.08
33-35	38.60	37.82	36.08	36.71	37.96	37.40	37.78	36.07	36.57	36.85
37-39	37.19	36.68	36.25	37.01	37.33	37.85	36.42	37.04	36.73	36.84
41-43	38.23	37.55	36.28	37.07	36.78	37.15	37.28	36.78	36.66	36.18
45-47	39.57	37.17	36.99	37.17	36.90	37.76	37.05	37.17	37.02	36.88
49-51	38.07	38.15	37.21	37.29	37.43	36.91	36.86	36.74	36.11	36.63
2-4	26.37	28.02	25.06	26.00	26.50	26.08	26.41	25.70	26.67	25.25
6-8	27.30	25.78	25.86	26.44	27.94	25.24	25.77	26.00	26.88	25.98
10-12	26.65	27.78	26.29	26.83	29.60	25.22	26.28	26.10	26.83	25.86
14-16	26.67	26.02	26.69	28.14	28.06	25.55	27.10	26.01	26.97	25.89
18-20	26.88	29.70	25.94	27.36	27.47	26.73	27.64	25.79	26.49	26.30
22-24	26.16	26.02	27.95	27.55	25.81	26.47	25.89	26.02	26.52	26.28
26-28	26.42	27.01	26.34	27.93	27.18	26.20	26.08	25.94	26.58	26.14
30-32	26.69	26.39	26.45	27.47	27.32	26.48	25.73	26.23	26.80	26.53
34-36	26.39	28.84	26.44	27.61	26.56	26.45	26.83	25.85	26.16	26.32
38-40	26.35	28.23	26.60	28.73	27.03	26.58	25.66	25.95	26.39	27.98
42-44	25.82	26.75	26.62	28.96	27.57	25.75	27.12	25.60	26.42	26.80
46-48	26.07	26.10	26.68	28.23	27.19	26.18	25.47	25.47	25.81	26.87
50-52	28.04	26.57	26.63	28.25	27.25	25.50	30.68	25.08	25.69	25.78
Max	42.34	39.48	37.21	38.49	41.42	38.94	38.49	37.17	37.36	38.18
Min	25.82	25.78	25.06	26.00	25.81	25.22	25.47	25.08	25.69	25.25
Avg	33.00	32.49	31.52	32.50	32.69	31.82	32.07	31.20	31.62	31.65
Stdev	6.61	5.53	5.23	5.00	5.57	5.93	5.61	5.50	5.25	5.48



Report No. GL-RD090107

GL-P-027-005

Group F

roup r		F- Temperature life											
210				F	- Tempei	rature life			11.0				
NO			Initial					emperati					
1.0	F1	F2	F3	F4	F5	F1	F2	F3	F4	F5			
1-3	35.95	36.15	34.40	33.70	35.55	40.13	41.17	40.46	38.20	40.73			
5-7	34.00	36.35	33.30	32.45	34.35	39.11	39.30	38.16	36.75	39.95			
9-11	33.85	37.20	34.05	35.00	33.20	38.55	40.70	38.89	39.27	38.65			
13-15	32.35	37.55	33.45	34.40	32.80	36.53	40.84	35.87	38.18	37.90			
17-19	33.65	35.30	33.45	32.95	33.60	38.63	39.47	38.04	37.17	38.81			
21-23	34.95	35.75	33.70	32.90	35.25	40.07	39.83	36.25	36.86	39.19			
25-27	34.90	36.60	34.00	33.80	34.70	40.07	39.68	37.89	37.80	39.19			
29-31	34.35	35.25	33.70	32.90	33.80	39.62	42.42	38.17	37.25	41.48			
33-35	34.30	33.65	34.55	34.30	33.35	38.33	39.67	38.12	37.91	39.94			
37-39	33.35	34.20	33.90	33.55	32.90	37.92	39.85	38.03	37.62	40.75			
41-43	33.05	34.95	35.70	34.00	32.90	36.31	39.83	38.52	37.14	39.57			
45-47	33.55	36.25	35.00	33.00	33.70	37.61	41.95	38.63	37.93	40.87			
49-51	33.90	33.00	35.70	33.95	33.15	37.12	37.61	39.29	38.64	40.11			
2-4	23.50	22.15	22.70	22.55	22.10	28.07	27.10	27.20	27.64	27.65			
6-8	23.45	23.05	23.55	23.05	22.05	28.45	27.52	27.38	28.32	27.93			
10-12	23.50	22.95	23.15	22.90	22.15	27.79	27.68	27.36	28.36	27.85			
14-16	23.45	23.00	23.30	23.15	22.20	27.87	27.47	27.38	28.22	27.71			
18-20	25.10	23.00	23.45	22.95	22.45	27.90	27.81	27.23	27.01	27.71			
22-24	23.25	23.25	23.55	22.80	22.50	27.97	27.90	27.40	27.83	28.03			
26-28	24.30	22.80	24.05	22.90	22.20	28.75	27.75	27.57	27.48	28.27			
30-32	24.10	22.55	23.90	22.80	22.35	28.21	27.67	27.67	27.16	28.56			
34-36	25.05	22.75	24.00	22.85	22.20	28.10	27.35	27.68	27.40	28.73			
38-40	24.30	22.80	23.75	27.80	22.55	27.89	27.42	27.52	27.59	28.98			
42-44	24.45	23.30	23.80	22.65	22.40	27.51	27.92	27.39	28.81	29.64			
46-48	23.50	22.45	23.90	22.65	22.80	26.74	26.83	27.53	28.16	29.80			
50-52	22.60	22.15	23.50	22.15	22.20	26.36	26.54	28.16	26.57	30.16			
Max	35.95	37.55	35.70	35.00	35.55	40.13	42.42	40.46	39.27	41.48			
Min	22.60	22.15	22.70	22.15	22.05	26.36	26.54	27.20	26.57	27.65			
Avg	28.95	29.17	28.90	28.39	28.05	33.14	33.82	32.84	32.74	34.16			
Stdev	5.23	6.58	5.46	5.44	5.88	5.52	6.55	5.51	5.15	5.81			



Report No. GL-RD090107

GL-P-027-005

Group G

Toup G					G-Salt	lt Spray						
NO			Initial				Afte	r Salt Sp	ray			
	G1	G2	G3	G4	G5	G1	G2	G3	G4	G5		
1-3	39.15	39.20	42.73	43.14	39.18	35.00	37.35	35.35	35.20	34.45		
5-7	39.06	38.45	39.71	43.19	38.55	36.50	35.60	34.05	34.65	33.80		
9-11	40.89	39.85	39.77	39.33	40.01	43.80	41.60	33.45	34.05	35.45		
13-15	38.76	38.15	36.88	37.52	38.54	44.45	37.10	32.55	33.20	34.10		
17-19	37.60	38.40	39.62	38.01	37.84	33.75	34.00	33.60	33.25	33.90		
21-23	38.66	37.64	41.01	44.50	37.21	33.65	33.55	34.80	33.95	33.55		
25-27	39.12	38.97	41.69	41.68	37.53	33.50	34.05	36.95	33.70	35.60		
29-31	26.11	38.48	39.03	39.01	37.61	34.35	34.05	34.20	34.00	33.90		
33-35	40.27	38.77	38.80	38.14	38.00	33.75	34.40	33.95	33.05	34.50		
37-39	39.91	37.74	37.90	39.37	37.49	33.85	34.05	34.15	33.80	33.60		
41-43	39.35	38.67	37.61	38.37	38.59	34.30	35.00	33.55	32.95	34.80		
45-47	39.82	38.79	37.64	38.60	37.87	34.45	34.35	34.30	33.35	34.75		
49-51	38.53	38.79	37.48	38.01	38.09	33.40	34.45	34.10	33.00	34.50		
2-4	26.54	27.41	27.54	31.56	26.25	22.90	23.50	22.60	23.35	22.80		
6-8	27.42	27.27	27.15	28.42	27.34	22.90	23.35	22.55	23.00	23.50		
10-12	26.92	28.02	27.80	27.56	26.92	23.00	23.35	23.15	23.55	24.10		
14-16	27.39	27.61	29.43	28.07	27.32	24.30	23.40	22.75	23.50	24.25		
18-20	27.51	27.97	31.14	27.74	26.42	23.30	23.35	23.20	24.00	23.10		
22-24	27.52	28.61	28.97	27.37	26.86	23.25	22.65	23.05	24.70	23.60		
26-28	27.37	28.82	29.93	27.68	26.71	22.20	23.10	23.25	27.50	23.30		
30-32	27.17	28.55	28.44	27.88	26.22	22.30	23.20	23.35	31.65	23.20		
34-36	26.87	28.99	28.04	27.88	26.45	22.10	23.75	23.50	27.15	23.55		
38-40	27.21	28.36	27.61	28.90	26.64	22.60	23.10	23.90	30.25	23.55		
42-44	27.37	28.48	27.56	28.99	26.12	22.30	23.50	23.55	26.25	23.30		
46-48	27.08	28.38	28.45	28.17	26.68	22.50	23.40	24.35	34.85	23.95		
50-52	26.52	27.82	26.92	27.16	26.03	22.55	23.35	22.50	28.75	22.65		
Max	40.89	39.85	42.73	44.50	40.01	44.45	41.60	36.95	35.20	35.60		
Min	26.11	27.27	26.92	27.16	26.03	22.10	22.65	22.50	23.00	22.65		
Avg	32.69	33.39	33.80	34.08	32.40	29.27	29.33	28.72	30.26	28.91		
Stdev	6.21	5.33	5.81	6.33	5.91	7.44	6.54	5.71	4.46	5.57		

TYPICAL PROPERTIES OF XYDAR® MG-350BPRL

Properties	Method	Unit	MG-850BPRL
Specific gravity 比重	ASTM D792	-	1.78
Tensile strength 引展被刺激さ	ASTM Deas	МРа	116
Elongation 引要被案件び	ASTM D688	%	8,0
Plexural strength 曲行独度	ASTM D790	MPa	160
Floreral modulus 曲げ弾性率	ASTM D790	GPa	13.3
Izod impact strength (unnotehed) アイソッド資章	ASTM D256	KJ/m*	42
DTUL 18.5 kgf/cm²	ASTM D648	r	275
Oven Blister Test ⁽⁾ 1mm dambbell 60min	NPCC original	τ	810
Weld strength st	NPCC original	MPa	85

¹⁾ Minimum oven temperature of blister breaking out on the specimen.

The data shown in this paper are based on our laboratory data, and not always directly applicable to your products used under different conditions.

²⁾ Flexural strength of the center weld specimen Gength 50mm, width 12.8mm, thickness 1mm)

Need more information? **Click Here** to go to the UL iQ[™] for Plastics database

Component - Plastics E91944

JX NIPPON OIL & ENERGY CORP

3-1 YAKO 2-CHOME, KAWASAKI-KU, KAWASAKI-SHI KANAGAWA 210-8545 JP

MG-350(r3), LCP MG-350(r3)

Liquid Crystal Aromatic Polymer (LCAP), "Xydar", furnished as pellets

	Min Thk	Flame			RTI	RTI	RTI
Color	(mm)	Class	HWI	HAI	Elec	lmp	Str
BK	0.17	V-0	-	-	130	130	130
NC, BK	0.30	V-0	-	-	130	130	130
	0.50	V-0	4	4	130	130	130
	0.75	V-0	4	4	130	130	130
	0.89	V-0	3	1	240	220	240
	1.5	V-0	1	1	240	240	240
	3.0	V-0	1	0	240	240	240

Comparative Tracking Index (CTI): 3

Dielectric Strength (kV/mm): 45

High-Voltage Arc Tracking Rate (HVTR): 0

Dimensional Stability (%): 0

Inclined Plane Tracking (IPT): -

Volume Resistivity (10x ohm-cm): 12

High Volt, Low Current Arc Resis (D495): 4

r3 - Virgin and Regrind from 26-50% by weight inclusive have the same Flame at 0.5mm and Tensile Impact characteristics at 3.0mm.

ANSI/UL 94 small-scale test data does not pertain to building materials, furnishings and related contents. ANSI/UL 94 small-scale test data is intended solely for determining the flammability of plastic materials used in the components and parts of end-product devices and appliances, where the acceptability of the combination is determined by UL.

Report Date: 1990-01-05 Last Revised: 2011-02-24

© 2012 UL LLC



IEC and ISO Test Methods

			Thickness	
Test Name	Test Method	Units	Tested (mm)	Value
Flammability	IEC 60695-11-10	Class (color)	0.17	V-0 (BK)
			0.30	V-0 (NC, BK)
			0.50	V-0 (NC, BK)
			0.75	V-0 (NC, BK)
			0.89	V-0 (NC, BK)
			1.5	V-0 (NC, BK)
			3.0	V-0 (NC, BK)
Glow-Wire Flammability (GWFI)	IEC 60695-2-12	С	-	-
Glow-Wire Ignition (GWIT)	IEC 60695-2-13	С	-	-
IEC Comparative Tracking Index	IEC 60112	Volts (Max)	-	-
IEC Ball Pressure	IEC 60695-10-2	С	-	-
ISO Heat Deflection (1.80 MPa)	ISO 75-2	С	-	-
ISO Tensile Strength	ISO 527-2	MPa	-	-
ISO Flexural Strength	ISO 178	MPa	-	-
ISO Tensile Impact	ISO 8256	kJ/m ²	-	-
ISO Izod Impact	ISO 180	kJ/m ²	-	-
ISO Charpy Impact	ISO 179-2	kJ/m ²	-	-

© 2012 UL LLC

The materials covered in this database are incomplete in certain constructional features or restricted in performance capabilities and are intended for use as components of complete equipment submitted for investigation rather than for direct separate installation in the field. THE FINAL ACCEPTANCE OF THE COMPONENT IS DEPENDENT UPON ITS INSTALLATION AND USE IN COMPLETE PRODUCTS SUBMITTED TO UNDERWRITERS LABORATORIES.

Notice of Disclaimer



號碼(No.) : CE/2014/24076 日期(Date) : 2014/03/05 頁數(Page) : 1 of 15

Test Report

JX NIPPON OIL & ENERGY CORPORATION
SPECIALTY CHEMICALS & MATERIALS DIVISION
ADVANCED MATERIALS DEPT.

3-1, YAKO 2-CHOME, KAWASAKI — KU, KAWASAKI CITY 210-8545 JAPAN

以下測試樣品係由申請廠商所提供及確認 (The following sample(s) was/were submitted and identified by/on behalf of the applicant as):

送樣廠商(Sample Submitted By) : JX NIPPON OIL & ENERGY CORPORATION

SPECIALTY CHEMICALS & MATERIALS DIVISION

ADVANCED MATERIALS DEPT.

樣品名稱(Sample Description) : LIQUID CRYSTAL POLYMER

樣品型號(Style/Item No.) : XYDAR MG-350BPRL

收件日期(Sample Receiving Date) : 2014/02/20

測試期間(Testing Period) : 2014/02/20 TO 2014/03/05

測試結果(Test Results) : 請見下一頁 (Please refer to next pages).

結論(Conclusion) : 根據客户所提供的樣品,其鎬、鉛、汞、六價鉻、多溴聯苯及多溴聯苯醚的測試結果符合

RoHS指令2002/95/EC的更新指令2011/65/EU之要求 (Based on the performed tests on submitted samples, the test results of Cadmium, Lead, Mercury, Hexavalent Chromium Cr(VI), PBBs and PBDEs comply with the limits as set by RoHS Directive

2011/65/EU Annex II; recasting 2002/95/EC.)



This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at http://www.sgs.com/en/Terms-and-Conditions.aspx and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at http://www.sgs.com/en/Terms-and-Conditions/Terms-Document.aspx. Attention of advant to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document one one appearance of this document cannot be reproduced, except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.

33, Wu Chuan Rd., New Taipei Industrial Park, New Taipei City, Taiwan / 新北市新北產業園區五權路33號 t+886 (02)2299 3279 f+886 (02)2299 3237 www.sgs.tw



號碼(No.): CE/2014/24076 日期(Date): 2014/03/05 頁數(Page): 2 of 15

Test Report

JX NIPPON OIL & ENERGY CORPORATION
SPECIALTY CHEMICALS & MATERIALS DIVISION
ADVANCED MATERIALS DEPT.

3-1, YAKO 2-CHOME, KAWASAKI — KU, KAWASAKI CITY 210-8545 JAPAN

測試結果(Test Results)

測試部位(PART NAME)No.1 : 黑色塑膠粒 (BLACK PLASTIC PELLETS)

測試項目 (Test Items)	單位 (Unit)	測試方法 (Method)	方法偵測 極限値 (MDL)	結果 (Result) No.1	法規 限値 (Limit)
鎬 / Cadmium (Cd)	mg/kg	參考IEC 62321-5: 2013方法, 以感應耦合電漿 原子發射光譜儀檢測. / With reference to	2	n.d.	100
鉛 / Lead (Pb)	mg/kg	IEC 62321-5: 2013 and performed by ICP-AES.	2	n.d.	1000
汞 / Mercury (Hg)	mg/kg	參考IEC 62321-4: 2013方法,以感應耦合電漿原子發射光譜儀檢測./With reference to IEC 62321-4: 2013 and performed by ICP-AES.	2	n.d.	1000
六價鉻 / Hexavalent Chromium Cr(VI)	mg/kg	參考IEC 62321: 2008方法,以UV-VIS檢測./ With reference to IEC 62321: 2008 and performed by UV-VIS.	2	n.d.	1000
绨 / Antimony (Sb)	mg/kg	参考US EPA 3052方法,以感應耦合電漿原子發射光譜儀檢測. / With reference to US EPA Method 3052. Analysis was performed by ICP-AES.	2	n.d.	-
三氧化二錦 / Antimony trioxide (Sb ₂ O ₃)*** (CAS No.: 1309-64-4)	mg/kg	參考US EPA 3052方法,以感應耦合電漿原子發射光譜儀檢測. / With reference to US EPA Method 3052. Analysis was performed by ICP-AES.***	-	n.d.	-
鈹 / Beryllium (Be)	mg/kg	參考US EPA 3052方法,以感應耦合電漿原子發射光譜儀檢測. / With reference to US EPA Method 3052. Analysis was performed by ICP-AES.	2	n.d.	-
聚氯乙烯 / PVC	**	以紅外光譜分析及焰色法檢測. / Analysis was performed by FTIR and FLAME Test.	-	Negative	-
五氣酚 / Pentachlorophenol (PCP) (CAS No.: 87-86-5)	mg/kg	參考US EPA 8041A方法,以氣相層析/質譜儀檢測./ With reference to US EPA 8041A method. Analysis was performed by GC/MS.	1	n.d.	-

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at http://www.sgs.com/en/Terms-and-Conditions.aspx and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at http://www.sgs.com/en/Terms-Document.aspx. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document on the company of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.



號碼(No.): CE/2014/24076 日期(Date): 2014/03/05 頁數(Page): 3 of 15

Test Report

JX NIPPON OIL & ENERGY CORPORATION
SPECIALTY CHEMICALS & MATERIALS DIVISION
ADVANCED MATERIALS DEPT.

3-1, YAKO 2-CHOME, KAWASAKI - KU, KAWASAKI CITY 210-8545 JAPAN

測試項目 (Test Items)	單位 (Unit)	測試方法 (Method)	方法偵測 極限値 (MDL)	結果 (Result) No.1	法規 限値 (Limit)
中鏈氯化石蠟 / Medium-Chained Chlorinated Paraffins (C14-C17) (MCCP) (CAS No.: 85535-85-9)	mg/kg	参考US EPA 3540C: 1996方法,以氣相層析/質 譜儀檢測. / With reference to US EPA 3540C: 1996 method. Analysis was performed by GC/MS.	50	n.d.	-
全氟辛烷磺酸 / Perfluorooctane sulfonates (PFOS-Acid, Metal Salt, Amide)	mg/kg	參考US EPA 3550C: 2007方法,以液相層析/質 譜儀檢測./With reference to US EPA	10	n.d.	-
全氟辛酸 / PFOA (CAS No.: 335-67- 1)	mg/kg	3550C: 2007. Analysis was performed by LC/MS.	10	n.d.	-
六溴環十二烷及所有主要被辨别出的 異構物 / Hexabromocyclododecane (HBCDD) and all major diastereoisomers identified (α -HBCDD, β -HBCDD, γ -HBCDD) (CAS No.: 25637-99-4 and 3194-55-6 (134237-51-7, 134237-50-6, 134237-52-8))	mg/kg	参考IEC 62321: 2008方法,以氣相層析/質譜 儀檢測. / With reference to IEC 62321: 2008 method. Analysis was performed by GC/MS.	5	n.d.	-
鄰苯二甲酸甲苯基丁酯 / BBP (Benzyl butyl phthalate) (CAS No.: 85-68-7)	%	参考EN 14372, 以氣相層析/質譜儀檢測./ With reference to EN 14372. Analysis was performed by GC/MS.	0.003	n.d.	-
鄰苯二甲酸二 (2-乙基己基)酯 / DEHP (Di- (2-ethylhexyl) phthalate) (CAS No.: 117-81-7)	%	参考EN 14372, 以氣相層析/質譜儀檢測./ With reference to EN 14372. Analysis was performed by GC/MS.	0.003	n.d.	-
鄰苯二甲酸二異癸酯 / DIDP (Di- isodecyl phthalate) (CAS No.: 26761-40-0; 68515-49-1)	%	參考EN 14372, 以氣相層析/質譜儀檢測./ With reference to EN 14372. Analysis was performed by GC/MS.	0.01	n.d.	-
鄰苯二甲酸二異壬酯 / DINP (Di- isononyl phthalate) (CAS No.: 28553-12-0; 68515-48-0)	%	參考EN 14372, 以氣相層析/質譜儀檢測./ With reference to EN 14372. Analysis was performed by GC/MS.	0.01	n.d.	-

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at http://www.sgs.com/en/Terms-and-Conditions.aspx and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at http://www.sgs.com/en/Terms-Document.aspx. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document on the company of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.



Test Report

號碼(No.): CE/2014/24076 日期(Date): 2014/03/05 頁數(Page): 4 of 15

JX NIPPON OIL & ENERGY CORPORATION
SPECIALTY CHEMICALS & MATERIALS DIVISION
ADVANCED MATERIALS DEPT.

3-1, YAKO 2-CHOME, KAWASAKI — KU, KAWASAKI CITY 210-8545 JAPAN

測試項目 (Test Items)	單位 (Unit)	測試方法 (Method)	方法偵測 極限値 (MDL)	結果 (Result) No.1	法規 限値 (Limit)
鄰苯二甲酸二正辛酯 / DNOP (Di-n-	%	參考EN 14372, 以氣相層析/質譜儀檢測./	0.003	n.d.	-
octyl phthalate) (CAS No.: 117-		With reference to EN 14372. Analysis was			
84-0)		performed by GC/MS.			
鄰苯二甲酸二丁酯 / DBP (Dibutyl	%	參考EN 14372, 以氣相層析/質譜儀檢測./	0.003	n.d.	-
phthalate) (CAS No.: 84-74-2)		With reference to EN 14372. Analysis was			
		performed by GC/MS.			
鄰苯二甲酸二異丁酯 / DIBP (Di-	%	參考EN 14372,以氣相層析/質譜儀檢測./	0.003	n.d.	-
isobutyl phthalate) (CAS No.: 84-		With reference to EN 14372. Analysis was			
69-5)		performed by GC/MS.			
多溴聯苯總和 / Sum of PBBs	mg/kg		-	n.d.	1000
一溴聯苯 / Monobromobiphenyl	mg/kg		5	n.d.	-
二溴聯苯 / Dibromobiphenyl	mg/kg		5	n.d.	-
三溴聯苯 / Tribromobiphenyl	mg/kg		5	n.d.	-
四溴聯苯 / Tetrabromobiphenyl	mg/kg		5	n.d.	-
五溴聯苯 / Pentabromobiphenyl	mg/kg		5	n.d.	-
六溴聯苯 / Hexabromobiphenyl	mg/kg	参考IEC 62321: 2008方法,以氣相層析/質譜 儀檢測. / With reference to IEC 62321: 2008 and performed by GC/MS.	5	n.d.	-
七溴聯苯 / Heptabromobiphenyl	mg/kg		5	n.d.	-
八溴聯苯 / Octabromobiphenyl	mg/kg		5	n.d.	-
九溴聯苯 / Nonabromobiphenyl	mg/kg		5	n.d.	-
十溴聯苯 / Decabromobiphenyl	mg/kg		5	n.d.	-
多溴聯苯醚總和 / Sum of PBDEs	mg/kg		-	n.d.	1000
一溴聯苯醚 / Monobromodiphenyl ether	mg/kg		5	n.d.	-
二溴聯苯醚 / Dibromodiphenyl ether	mg/kg		5	n.d.	-
三溴聯苯醚 / Tribromodiphenyl ether	mg/kg		5	n.d.	-
四溴聯苯醚 / Tetrabromodiphenyl ether	mg/kg		5	n.d.	-
五溴聯苯醚 / Pentabromodiphenyl ether	mg/kg		5	n.d.	-
六溴聯苯醚 / Hexabromodiphenyl ether	mg/kg		5	n.d.	-
七溴聯苯醚 / Heptabromodiphenyl ether	mg/kg		5	n.d.	-
八溴聯苯醚 / Octabromodiphenyl ether	mg/kg		5	n.d.	-
九溴聯苯醚 / Nonabromodiphenyl ether	mg/kg		5	n.d.	-
十溴聯苯醚 / Decabromodiphenyl ether	mg/kg		5	n.d.	-

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at http://www.sgs.com/en/Terms-and-Conditions.aspx and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at http://www.sgs.com/en/Terms-Document.aspx. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document on the company of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.



號碼(No.): CE/2014/24076 日期(Date): 2014/03/05 頁數(Page): 5 of 15

Test Report

JX NIPPON OIL & ENERGY CORPORATION

SPECIALTY CHEMICALS & MATERIALS DIVISION

ADVANCED MATERIALS DEPT.

3-1, YAKO 2-CHOME, KAWASAKI - KU, KAWASAKI CITY 210-8545 JAPAN

測試項目 (Test Items)	單位 (Unit)	測試方法 (Method)	方法偵測 極限値 (MDL)	結果 (Result) No.1	法規 限値 (Limit)
鹵素 / Halogen					
鹵素 (氟) / Halogen-Fluorine (F) (CAS No.: 14762-94-8)	mg/kg	参考BS EN 14582:2007,以離子層析儀分析./ With reference to BS EN 14582:2007. Analysis was performed by IC.	50	805	-
鹵素 (氣) / Halogen-Chlorine (Cl) (CAS No.: 22537-15-1)	mg/kg		50	n.d.	-
鹵素 (溴) / Halogen-Bromine (Br) (CAS No.: 10097-32-2)	mg/kg		50	n.d.	-
鹵素(碘)/ Halogen-Iodine (I) (CAS No.: 14362-44-8)	mg/kg		50	n.d.	-

備註(Note):

- 1. mg/kg = ppm ; 0.1wt% = 1000ppm
- 2. n.d. = Not Detected (未檢出)
- 3. MDL = Method Detection Limit (方法偵測極限值)
- 4. "-" = Not Regulated (無規格值)
- 5. **= Qualitative analysis (No Unit) 定性分析(無單位)
- 6. Negative = Undetectable 陰性(未偵測到); Positive = Detectable 陽性(已偵測到)
- 7. ***: 該物質是由錦之測試結果計算得知. 其MDL是針對錦之評估. (The substance was calculated by the test result of Antimony. The MDL was evaluated for Antimony.)

 $AX = A \times F$

AX	A	F
三氧化二銻 / Antimony trioxide (Sb ₂ O ₃)	绨 / Antimony	1.1971

PFOS参考資訊(Reference Information): 持久性有機污染物 POPs - (EU) 757/2010

PFOS濃度在物質或製備中不得超過0.001%(10ppm),在半成品、成品或零部件中不得超過0.1%(1000ppm),在紡織品或塗層材料中不得超過 $1\mu g/m^2$ 。

(Outlawing PFOS as substances or preparations in concentrations above 0.001% (10ppm), in semi-finished products or articles or parts at a level above 0.1%(1000ppm), in textiles or other coated materials above $1\mu g/m^2$.)

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at http://www.sgs.com/en/Terms-and-Conditions.aspx and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at http://www.sgs.com/en/Terms-Document.aspx. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document on the company of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.



號碼(No.): CE/2014/24076 日期(Date): 2014/03/05 頁數(Page): 6 of 15

Test Report


JX NIPPON OIL & ENERGY CORPORATION

SPECIALTY CHEMICALS & MATERIALS DIVISION

ADVANCED MATERIALS DEPT.

3-1, YAKO 2-CHOME, KAWASAKI - KU, KAWASAKI CITY 210-8545 JAPAN

- 1) 根據以下的流程圖之條件,樣品已完全溶解。(六價鉻測試方法除外) / These samples were dissolved totally by pre-conditioning method according to below flow chart. (Cr⁶⁺ test method excluded)
- 2) 測試人員:楊登偉 / Name of the person who made measurement: Climbgreat Yang
- 3) 測試負責人:張啓興 / Name of the person in charge of measurement: Troy Chang



Note** (For IEC 62321)

- (1) 針對非金屬材料加入鹼性消化液,加熱至 90~95℃萃取. / For non-metallic material, add alkaline digestion reagent and heat to 90~95℃.
- (2) 針對金屬材料加入純水,加熱至沸騰萃取. / For metallic material, add pure water and heat to boiling.

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at http://www.sgs.com/en/Terms-and-Conditions.aspx and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at http://www.sgs.com/en/Terms-Document.aspx. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document on the company of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.



號碼(No.): CE/2014/24076 日期(Date): 2014/03/05 頁數(Page): 7 of 15

Test Report

JX NIPPON OIL & ENERGY CORPORATION

SPECIALTY CHEMICALS & MATERIALS DIVISION


ADVANCED MATERIALS DEPT.

3-1, YAKO 2-CHOME, KAWASAKI - KU, KAWASAKI CITY 210-8545 JAPAN

- 1) 根據以下的流程圖之條件,樣品已完全溶解。 / These samples were dissolved totally by pre-conditioning method according to below flow chart.
- 2) 測試人員:楊登偉 / Name of the person who made measurement: Climbgreat Yang
- 3) 測試負責人:張啓興 / Name of the person in charge of measurement: Troy Chang

元素以 ICP-AES 分析的消化流程圖

(Flow Chart of digestion for the elements analysis performed by ICP-AES)



鋼,銅,鋁,焊錫 / Steel, copper, aluminum, solder	王水,硝酸,鹽酸,氫氟酸,雙氧水 /
	Aqua regia, HNO3, HC1, HF, H2O2
玻璃 / Glass	硝酸,氫氟酸 / HNO₃/HF
金,鉑,鈀,陶瓷 / Gold, platinum, palladium, ceramic	王水 / Aqua regia
銀 / Silver	硝酸 / HNO3
塑膠 / Plastic	硫酸,雙氧水,硝酸,鹽酸 / H2SO4, H2O2, HNO3, HC1
其他 / Others	加入適當的試劑至完全溶解 / Added appropriate
	reagent to total digestion

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at http://www.sgs.com/en/Terms-and-Conditions.aspx and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at http://www.sgs.com/en/Terms-Document.aspx. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document on the company of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.



號碼(No.): CE/2014/24076 日期(Date): 2014/03/05 頁數(Page): 8 of 15


Test Report

JX NIPPON OIL & ENERGY CORPORATION
SPECIALTY CHEMICALS & MATERIALS DIVISION
ADVANCED MATERIALS DEPT.

3-1, YAKO 2-CHOME, KAWASAKI - KU, KAWASAKI CITY 210-8545 JAPAN

六溴環十二烷分析流程圖 / HBCDD analytical flow chart

- 測試人員:翁賜彬 / Name of the person who made measurement: Roman Wong
- 測試負責人:張啓興 / Name of the person in charge of measurement: Troy Chang



This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at http://www.sgs.com/en/Terms-and-Conditions.aspx and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at http://www.sgs.com/en/Terms-Document.aspx. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document on the company of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.



號碼(No.): CE/2014/24076 日期(Date): 2014/03/05 頁數(Page): 9 of 15


Test Report

JX NIPPON OIL & ENERGY CORPORATION SPECIALTY CHEMICALS & MATERIALS DIVISION ADVANCED MATERIALS DEPT.

3-1, YAKO 2-CHOME, KAWASAKI - KU, KAWASAKI CITY 210-8545 JAPAN

氯化石蠟分析流程圖 / Chlorinated Paraffins analytical flow chart

- 測試人員: 曾勃鈞 / Name of the person who made measurement: Barry Tseng
- 測試負責人:張啓興 / Name of the person in charge of measurement: Troy Chang



This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at http://www.sgs.com/en/Terms-and-Conditions.aspx and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at http://www.sgs.com/en/Terms-Document.aspx. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document on the company of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.



號碼(No.): CE/2014/24076 日期(Date): 2014/03/05 頁數(Page): 10 of 15

Test Report

JX NIPPON OIL & ENERGY CORPORATION

SPECIALTY CHEMICALS & MATERIALS DIVISION


ADVANCED MATERIALS DEPT.

3-1, YAKO 2-CHOME, KAWASAKI — KU, KAWASAKI CITY 210-8545 JAPAN

聚氯乙烯物質判定分析流程圖 /

Analysis flow chart for determination of PVC in material

- 測試人員:陳君涵 / Name of the person who made measurement: Ginny Chen
- 測試負責人:張啓興 / Name of the person in charge of measurement: Troy Chang



This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at http://www.sgs.com/en/Terms-and-Conditions.aspx and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at http://www.sgs.com/en/Terms-Document.aspx. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document on the company of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.



號碼(No.): CE/2014/24076 日期(Date): 2014/03/05 頁數(Page): 11 of 15


Test Report

JX NIPPON OIL & ENERGY CORPORATION
SPECIALTY CHEMICALS & MATERIALS DIVISION
ADVANCED MATERIALS DEPT.

3-1, YAKO 2-CHOME, KAWASAKI — KU, KAWASAKI CITY 210-8545 JAPAN

全氟辛酸/全氟辛烷磺酸分析流程圖 / PFOA/PFOS analytical flow chart

- 測試人員: 翁賜彬 / Name of the person who made measurement: Roman Wong
- 測試負責人:張啓興 / Name of the person in charge of measurement: Troy Chang



This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at http://www.sgs.com/en/Terms-and-Conditions.aspx and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at http://www.sgs.com/en/Terms-Document.aspx. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document on the company of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.



Test Report

號碼(No.): CE/2014/24076 日期(Date): 2014/03/05 頁數(Page): 12 of 15

JX NIPPON OIL & ENERGY CORPORATION


SPECIALTY CHEMICALS & MATERIALS DIVISION

ADVANCED MATERIALS DEPT.

3-1, YAKO 2-CHOME, KAWASAKI — KU, KAWASAKI CITY 210-8545 JAPAN

可塑劑分析流程圖 / Analytical flow chart of phthalate content

- 測試人員: 翁賜彬 / Name of the person who made measurement: Roman Wong
- 測試負責人:張啓興 / Name of the person in charge of measurement: Troy Chang



This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at http://www.sgs.com/en/Terms-and-Conditions.aspx and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at http://www.sgs.com/en/Terms-Document.aspx. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document on the company of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.



Test Report

號碼(No.): CE/2014/24076 日期(Date): 2014/03/05 頁數(Page): 13 of 15


JX NIPPON OIL & ENERGY CORPORATION
SPECIALTY CHEMICALS & MATERIALS DIVISION
ADVANCED MATERIALS DEPT.

3-1, YAKO 2-CHOME, KAWASAKI — KU, KAWASAKI CITY 210-8545 JAPAN

多溴聯苯/多溴聯苯醚分析流程圖 / PBB/PBDE analytical FLOW CHART

- 測試人員: 翁賜彬 / Name of the person who made measurement: Roman Wong
- 測試負責人:張啓興 / Name of the person in charge of measurement: Troy Chang

確認程序 / Confirmation process - - - - ▶



This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at http://www.sgs.com/en/Terms-and-Conditions.aspx and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at http://www.sgs.com/en/Terms-Document.aspx. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document on the company of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.



Test Report


號碼(No.) : CE/2014/24076 日期(Date) : 2014/03/05 頁數(Page) : 14 of 15

JX NIPPON OIL & ENERGY CORPORATION
SPECIALTY CHEMICALS & MATERIALS DIVISION
ADVANCED MATERIALS DEPT.

3-1, YAKO 2-CHOME, KAWASAKI - KU, KAWASAKI CITY 210-8545 JAPAN

鹵素分析流程圖 / Analytical flow chart of halogen content

- 測試人員:陳恩臻 / Name of the person who made measurement: Rita Chen
- 測試負責人:張啓興 / Name of the person in charge of measurement: Troy Chang



This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at http://www.sgs.com/en/Terms-and-Conditions.aspx and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at http://www.sgs.com/en/Terms-Document.aspx. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document on the company of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.



號碼(No.): CE/2014/24076 日期(Date): 2014/03/05 頁數(Page): 15 of 15

Test Report

JX NIPPON OIL & ENERGY CORPORATION
SPECIALTY CHEMICALS & MATERIALS DIVISION
ADVANCED MATERIALS DEPT.

3-1, YAKO 2-CHOME, KAWASAKI — KU, KAWASAKI CITY 210-8545 JAPAN

* 照片中如有箭頭標示,則表示為實際檢測之樣品/部位. *
(The tested sample / part is marked by an arrow if it's shown on the photo.)

CE/2014/24076



** 報告結尾 (End of Report) **

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at http://www.sgs.com/en/Terms-and-Conditions.aspx and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at http://www.sgs.com/en/Terms-and-Conditions/Terms-Document.aspx. Attention of advant to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document on the company and the report of the company and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document and this document on the company and the co

昆山市天申铜业五金机电有限公司



产品质量证明书

天中 御业

	8户名称		产品名称	规格	状态	() 緑症	(g)	执行标准
- '	子(苏州)有限	公司	C2680	0.15*20.	5 EH	36,5	J	ISH3100
			化	学 成 2	分			
元 素	Cu	Fe	Pb	Sb	Bi	P	Zn	杂质总和
规范	64.0-68.0	< 0.05	< 0.03	< 0.005	< 0.002	<0.01	金田	< 0.3
实测	64.52	0,0083	0,0064	0,0014	0.0013	0.0016	20余	
	<u> </u>	1,	机	横性	能			
项目	[]	E度 Hv		and the second second	∰ MPa		伸长拳	%
规范		70-190		520)-620			
实 测		171			73		65	机也有点
			尺	寸 公	差		EL S	· · · // @? \
项目	厚 度		宽 歧	K B	E	侧弯		A =
规范	±0.01		+0/-0.1	1		/	The state of the s	海天双 书。
实 測	0,145		20.43	1				All All som
签证部门	质检部			日期	2009-10-15			1.5





Report No. RHS05G011858001

Page 1 of 4

Applicant KUNSHAN TIANSHEN COPPER HARDWARE ELECTRICAL AND

MECHANICAL CO., LTD.

Address NO. 328-3 DONGCHANG ROAD BACHENG TOWN KUNSHAN CITY

The following sample(s) and sample information was/were submitted and identified by/on the behalf of the client

Sample Name Brass
Part No. C2680
Material Cu, Zn

Sample Received Date Apr. 11, 2014

Testing Period Apr. 11, 2014 to Apr. 15, 2014

Test Requested As specified by client, to test Lead(Pb), Cadmium(Cd), Mercury(Hg),

Hexavalent Chromium (Cr(VI)) in the submitted sample(s).

Test Method

Test Item(s)	Test Method	Measured Equipment(s)	
Lead(Pb)	IEC 62321-5:2013 Ed.1.0	ICP-OES	
Cadmium(Cd)	IEC 62321-5:2013 Ed.1.0	ICP-OES	
Mercury(Hg)	IEC 62321-4:2013 Ed.1.0	ICP-OES	
Hexavalent Chromium (Cr(VI))	IEC 62321:2008 Ed.1 Annex B	UV-Vis	

Test Result(s)

Please refer to the following page(s).

Tested by Chen Liju

Reviewed by

Date

Apr. 15, 2014

Su Hongwei

Senior Laboratory Manager ternational Co.,Ltd. Shanghai Branch No. 1087211671

No.1996, New Jinqiao Road, Pudong District, Shanghai, China



Report No. RHS05G011858001

Page 2 of 4

Test Result(s)

Tested Item(s)	Result	MDL
Lead(Pb)	9 mg/kg	2 mg/kg
Cadmium (Cd)	N.D.	2 mg/kg
Mercury(Hg)	N.D.	2 mg/kg
Hexavalent Chromium (Cr(VI))	Negative	/

Tested Sample/Part Description

Golden metal

Note:

The sample(s) had been dissolved totally tested for Lead, Cadmium, Mercury.

-MDL = Method Detection Limit

-N.D. = Not Detected (<MDL)

-mg/kg = ppm = parts per million

-Negative = Absence of Cr(VI), the detected Cr(VI) concentration in the boiling water

extraction solution is less than 0.02 mg/kg with 50cm² sample surface area used.








Report No. RHS05G011858001


Page 3 of 4

Test Process


1. Lead(Pb), Cadmium(Cd)



2. Mercury(Hg)



3. Hexavalent Chromium (Cr(VI))






www.cti-cert.com



Report No. RHS05G011858001

Page 4 of 4

Photo(s) of the sample(s)



*** End of report ***

The test report is effective only with both signature and specialized stamp. The result(s) shown in this report refer only to the sample(s) tested. Without written approval of CTI, this report can't be reproduced except in full.





报告编号 ECL01G022173001E ECL01G022173001E Report No.

第1页 共 6 页 Page 1 of 6

申请单位 得意精密電子(蘇州)有限公司 LOTES(SUZHOU) CO.,LTD **Applicant**

地 江蘇省蘇州市相城經濟開發區漕湖大道26號 址

NO.26 CAOHU ROAD XIANGCHENG ECONOMIC DEVELOPMENT ZONE, SUZHOU Address

CHINA

以下测试之样品及样品信息由申请者提供并确认

The following sample(s) and sample information was/were submitted and identified by/on the behalf of the client

样品名称 鍍層Au Ni Sn

Sample Name Coating material Au Ni Sn

材料名称 C2680 Material

样品接收日期 2014.10.28

Oct. 28, 2014 Sample Received Date

样品检测日期 2014.10.28-2014.10.31

Testing Period Oct. 28, 2014 to Oct. 31, 2014

检测要求 根据客户要求,对所提交样品中的铅(Pb)、镉(Cd)、汞(Hg)、六价铬(Cr(VI))、

全氟辛烷磺酸盐(PFOS)进行测试。

As specified by client, to test Lead (Pb), Cadmium (Cd), Mercury (Hg), **Test Requested**

Hexavalent Chromium(Cr(VI)), Perfluorooctane Sulfonates(PFOS) in the

submitted sample(s).

检测依据/检测结果

Test Method/Test Result(s)

请参见下页。

Please refer to the following page(s).

主 Tested by

Su Hongwei

enior Laboratory Manager

检测技术股份有限公司上海分公司

ng International Co., Ltd. Shanghai Branch

Reviewed by

H

Date

2014.10.31

No. R187778204

上海市浦东新区新金桥路1996号

No.1996, New Jinqiao Road, Pudong District, Shanghai, China

400-6788-333 www.cti-cert.com





报告编号 ECL01G022173001E Report No. ECL01G022173001E

第 2 页 共 6 页 Page 2 of 6

检测依据 Test Method

测试项目 Test Item(s)	测试方法 Test Method	测试仪器 Measured Equipment(s)
铅 (Pb) Lead (Pb)	参考 IEC 62321-5:2013 Ed.1.0 Refer to IEC 62321-5:2013 Ed.1.0	ICP-OES
镉 (Cd) Cadmium (Cd)	参考 IEC 62321-5:2013 Ed.1.0 Refer to IEC 62321-5:2013 Ed.1.0	ICP-OES
汞 (Hg) Mercury (Hg)	参考 IEC 62321-4:2013 Ed.1.0 Refer to IEC 62321-4:2013 Ed.1.0	ICP-OES
六价铬 (Cr(VI)) Hexavalent Chromium(Cr(VI))	IEC 62321:2008 Ed.1 Annex B	UV-Vis
全氟辛烷磺酸盐 (PFOS) Perfluorooctane Sulfonates(PFOS)	参考 US EPA 3550C:2007 & US EPA 8321B:2007 Refer to US EPA 3550C:2007 & US EPA 8321B:2007	LC-MS-MS

检测结果 Test Result(s)

测试项目 Test Item(s)	结果 Result	方法检测限 MDL
铅 (Pb) Lead (Pb)	18 mg/kg	2 mg/kg
镉 (Cd) Cadmium (Cd)	N.D.	2 mg/kg
汞 (Hg) Mercury (Hg)	N.D.	2 mg/kg
六价铬 (Cr(VI)) Hexavalent Chromium(Cr(VI))	阴性 Negative	1

测试项目 Test Item(s)	结果 Result	方法检测限 MDL
全氟辛烷磺酸盐(PFOS) Perfluorooctane	N.D.	5 mg/kg
Sulfonates(PFOS)		

测试样品/部位描述

金色/银白色镀层

Tested Sample/Part Description

Golden/silver-white plating





















报告编号 ECL01G022173001E Report No. ECL01G022173001E 第**3**页 共**6**页 Page 3 of 6

注释: -N.D. = 未检出 (小于方法检测限).

-mg/kg=ppm=百万分之几.

-阴性表示不含有六价铬,即由表面积为 50cm²的样品所萃取出来的溶液中,测得六

价铬的浓度小于 0.02mg/kg。

Note: -MDL = Method Detection Limit

-N.D. = Not Detected (<MDL)


-mg/kg= ppm =parts per million

-Negative = Absence of Cr (VI). The Cr (VI) concentration detected in the boiling water

extraction solution is less than 0.02 mg/kg with 50cm² sample surface area used.

备注: 报告编号中"E"表示此报告为中英文对照版本。

Remark: The end sign of report number E represents the bilingual version.






报告编号 ECL01G022173001E Report No. ECL01G022173001E


第 **4** 页 共 **6** 页 Page 4 of 6

检测流程 Test Process

1. 铅**(Pb)**, 镉**(Cd)** Lead (Pb), Cadmium (Cd)



2. 汞**(Hg)**Mercury (Hg)









ECL01G022173001E 报告编号 ECL01G022173001E Report No.

第5页 共 6 页 Page 5 of 6

3. 全氟辛烷磺酸盐(PF0S) Perfluorooctane Sulfonates(PFOS)











报告编号 ECL01G022173001E Report No. ECL01G022173001E 第 6 页 共 6 页 Page 6 of 6

样品图片 Photo(s) of the sample(s)



报告结束 *** End of report ***

检测报告无批准人签字及"报告专用章"无效,本报告检测结果仅对受测样品负责。未经CTI书面同意,不得部分复制本报告。

The test report is effective only with both signature and specialized stamp. The result(s) shown in this report refer only to the sample(s) tested. Without written approval of CTI, this report can't be reproduced except in full.





报告编号 ECL01G022173002E ECL01G022173002E Report No.

第1页 共 6 页

Page 1 of 6

申请单位 得意精密電子(蘇州)有限公司 LOTES(SUZHOU) CO.,LTD **Applicant**

地 江蘇省蘇州市相城經濟開發區漕湖大道26號 址

NO.26 CAOHU ROAD XIANGCHENG ECONOMIC DEVELOPMENT ZONE, SUZHOU Address

CHINA

以下测试之样品及样品信息由申请者提供并确认

The following sample(s) and sample information was/were submitted and identified by/on the behalf of the client

样品名称 鍍層 Ni Sn

Sample Name Coating material Ni Sn

材料名称 C2680

Material

样品接收日期 2014.10.28 Oct. 28, 2014 Sample Received Date

样品检测日期 2014.10.28-2014.10.31

Testing Period Oct. 28, 2014 to Oct. 31, 2014

检测要求 根据客户要求,对所提交样品中的铅(Pb)、镉(Cd)、汞(Hg)、六价铬(Cr(VI))、

全氟辛烷磺酸盐(PFOS)进行测试。

As specified by client, to test Lead (Pb), Cadmium (Cd), Mercury (Hg), **Test Requested**

Hexavalent Chromium(Cr(VI)), Perfluorooctane Sulfonates(PFOS) in the

submitted sample(s).

检测依据/检测结果

Test Method/Test Result(s)

请参见下页。

Please refer to the following page(s).

主 Tested by

Su Hongwei

nior Laboratory Manager

这测技术股份有限公司上海分公司

g International Co., Ltd. Shanghai Branch

Reviewed by

H

Date

2014.10.31

No. R187778204

上海市浦东新区新金桥路1996号

No.1996, New Jinqiao Road, Pudong District, Shanghai, China

400-6788-333 www.cti-cert.com



报告编号 ECL01G022173002E Report No. ECL01G022173002E

第 2 页 共 6 页 Page 2 of 6

检测依据 Test Method

测试项目 Test Item(s)	测试方法 Test Method	测试仪器 Measured Equipment(s)
铅 (Pb) Lead (Pb)	参考 IEC 62321-5:2013 Ed.1.0 Refer to IEC 62321-5:2013 Ed.1.0	ICP-OES
镉 (Cd) Cadmium (Cd)	参考 IEC 62321-5:2013 Ed.1.0 Refer to IEC 62321-5:2013 Ed.1.0	ICP-OES
汞 (Hg) Mercury (Hg)	参考 IEC 62321-4:2013 Ed.1.0 Refer to IEC 62321-4:2013 Ed.1.0	ICP-OES
六价铬 (Cr(VI)) Hexavalent Chromium(Cr(VI))	IEC 62321:2008 Ed.1 Annex B	UV-Vis
全氟辛烷磺酸盐 (PF0S) Perfluorooctane Sulfonates(PFOS)	参考US EPA 3550C:2007 & US EPA 8321B:2007 Refer to US EPA 3550C:2007 & US EPA 8321B:2007	LC-MS-MS

检测结果 Test Result(s)

测试项目 Test Item(s)	结果 Result	方法检测限 MDL
铅 (Pb) Lead (Pb)	26 mg/kg	2 mg/kg
镉 (Cd) Cadmium (Cd)	N.D.	2 mg/kg
汞 (Hg) Mercury (Hg)	N.D.	2 mg/kg
六价铬(Cr(VI)) Hexavalent Chromium(Cr(VI))	阴性 Negative	1

测试项目 Test Item(s)	结果 Result	方法检测限 MDL
全氟辛烷磺酸盐 (PFOS) Perfluorooctane	N.D.	5 mg/kg
Sulfonates(PFOS)		

测试样品/部位描述 **Tested Sample/Part Description** 银色镀层 Silvery plating





















报告编号 ECL01G022173002E Report No. ECL01G022173002E 第**3**页 共**6**页 Page 3 of 6

注释: -N.D. = 未检出 (小于方法检测限).

-mg/kg=ppm=百万分之几.

-阴性表示不含有六价铬,即由表面积为 50cm² 的样品所萃取出来的溶液中,测得六

价铬的浓度小于 0.02mg/kg。

Note: -MDL = Method Detection Limit

-N.D. = Not Detected (< MDL)


-mg/kg= ppm =parts per million

-Negative = Absence of Cr (VI). The Cr (VI) concentration detected in the boiling water

extraction solution is less than 0.02 mg/kg with 50cm² sample surface area used.

备注: 报告编号中"E"表示此报告为中英文对照版本。

Remark: The end sign of report number E represents the bilingual version.






报告编号 ECL01G022173002E Report No. ECL01G022173002E


第 **4** 页 共 **6** 页 Page 4 of 6

检测流程 Test Process

1. 铅**(Pb)**, 镉**(Cd)** Lead (Pb), Cadmium (Cd)



2. 汞**(Hg)**Mercury (Hg)









报告编号 ECL01G022173002E Report No. ECL01G022173002E

第 **5** 页 共 **6** 页 Page 5 of 6

3. 全氟辛烷磺酸盐 (PFOS) Perfluorooctane Sulfonates (PFOS)










报告编号 ECL01G022173002E Report No. ECL01G022173002E 第 6 页 共 6 页 Page 6 of 6

样品图片 Photo(s) of the sample(s)



报告结束 *** End of report ***

检测报告无批准人签字及"报告专用章"无效,本报告检测结果仅对受测样品负责。未经**CT**Ⅰ书面同意,不得部分复制本报告。

The test report is effective only with both signature and specialized stamp. The result(s) shown in this report refer only to the sample(s) tested. Without written approval of CTI, this report can't be reproduced except in full.





Test Report NO.: 109042023504D Date: 2014.09.11 Page 1 of 7

Applicant: Shanghai Hua Ken Electronics Technology Co.,Ltd.

Address: Room 802, No.99, Feng Pu Avenue, Fengxian District, Shanghai China

The following sample(s) was/were submitted and identified on behalf of the client as:

Sample Name: Industrial Print ink

Sample Model: HI-68K

Sample Received Date: 2014.09.04

Test Period: 2014.09.04 To 2014.09.11

Reference Methods: IEC62321 Edition 1.0: 2008 method: Regulated Substances Content of test

process with Electrical & Electronic Products

(1) Lead Analysis is performed by AAS

(2) Cadmium Analysis is performed by AAS

(3) Mercury Analysis is performed by ICP-OES

(4) Hexavalent Chromium Analysis is performed by UV-Vis

(5) PBBs and PBDEs Analysis is performed by GC-MS

EN 14582: 2007 method, F, Cl, Br, I Analysis is performed by IC

EPA8061A:1996 method, Phthalate Analysis is performed by GC-MS EPA8270D: 2007 method, HBCDD Analysis is performed by GC-MS

Test Result: Please refer to next page(s)

Approved by: 2 hang Dargin

Code: r7fq503z

The page below is blank.



(020)89224310

Dun He Road, Hai Zhu District, Guangzhou




Test Report Page 2 of 7 NO.: I09042023504D Date: 2014.09.11


Test Result (Unit: ma/ka)

lest Result (Unit: mg/kg)			
Test Item	MDL	Test Result	RoHS Limit
Lead (Pb)	1/2)	N.D.	1000
Cadmium (Cd)	1	N.D.	100
Mercury (Hg)	1	N.D.	1000
Hexavalent Chromium (Cr ⁶⁺)	1	N.D.	1000
PBBs	_	_	1000
Bromobiphenyl	5	N.D.	A -
Dibromobiphenyl	5	N.D.	- <
Tribromobiphenyl	5	N.D.	- /^
Tetrabromobiphenyl	5	N.D.	- ~
Pentabromobiphenyl	5	N.D.	- /</td
Hexabromobiphenyl	5	N.D.	_ ~
Heptabromobiphenyl	5	N.D.	_
Octabromobiphenyl	5	N.D.	_
Nonabromobiphenyl	5	N.D.	_
Decabromobiphenyl	5	N.D.	-
PBDEs	- /		1000
Bromodiphenyl ether	5	N.D.	-
Dibromodiphenyl ether	5	N.D.	- <%
Tribromodiphenyl ether	5	N.D.	
Tetrabromodiphenyl ether	5	N.D.	_
Pentabromodiphenyl ether	5	N.D.	_
Hexabromodiphenyl ether	5	N.D.	A -
Heptabromodiphenyl ether	5	N.D.	3 - 1
Octabromodiphenyl ether	5	N.D.	
Nonabromodiphenyl ether	5	N.D.	- //
Decabromodiphenyl ether	5	N.D.	-

The page below is blank.







Add: Yingzhi Building,No.49-3,Suzhou Road,Haidian District, Beijing Tel: (010) 82618116

Building 35, No.680, Guiping Road, Building 6, Zhongxing Industry City, Xuhui District, Shanghai (021) 64851999 (0755) 26050909 Industry City, Shenzhen

6th Floor, No.190, Zhuzhou Road, Laoshan District, Qingdao (0532) 88706866

Add: Ying huan Building, HongqiRoad, Nan kai district, Tianjin Tel: (022)27360730

Phase 2 Building 4, No 150 Xinhui Rd, Gaoxin Dist, Ningbo City (0574)87736499

Building 3, No 189 Hai Zhu Techno park, Dun He Road, Hai Zhu District, Guangzhou (020)89224310



NO.: I09042023504D

Date: 2014.09.11

Page 3 of 7

Test Result (Unit: ma/ka)

Toot recount (Orne: Trig/reg)			
Test Iter	n 🕢	Test Result	(0)
HBCDI		Not Detected(<5)	
DBP	V	Not Detected(<50)	
BBP		Not Detected(<50)	
DEHP	4	Not Detected(<50)	
DIBP	3	Not Detected(<50)	_

Test Result (Unit: mg/kg)

` 5 6/				
Test Item	MDL	(0)	Test Result	(0)
(F)	50	1	N.D.	1
Cl	50		N.D.	
Br	50		N.D.	
	50		N.D.	

Note: (1) mg/kg = ppm


- (2) "-- " = Does not stipulate
- (3) N.D. = Not Detected (<MDL)
- (4) MDL = Method Detection Limit
- (5) The most allowable limit value reference to RoHS Directive 2011/65/EU Annex II

Photo:



Pony authenticate the photo on original report only The page below is blank.







Nan kai district, Tianjin Tel: (022)27360730

www. ponytest. com



NO.: 109042023504D

Date: 2014.09.11

Page 4 of 7


Measurement Flow-chart

Tested by: Zhao Ting Checked by: Cao Jia

Person in charge of the lab: Zhang Daiqin

These Samples Were Dissolved Totally By Pre-conditioning Method According To Below Flow Chart. (Cr⁶⁺

And PBBs/PBDEs Test Method Excluded)



The page below is blank.



© Hotline 400-819-5688

Add: Yingzhi Building,No.49-3,Suzhou Road,Haidian District, Beijing Tel: (010) 82618116

Building 35, No.680, Guiping Road, Xuhui District, Shanghai (021) 64851999

Chuangye Road, Nanshan District, Shenzhen (0755) 26050909

6th Floor, No.190, Zhuzhou Road Laoshan District, Qingdao (0532) 88706866

Add: Ying huan Building, HongqiRoad, Nan kai district, Tianjin Tel: (022)27360730 Phase 2 Building 4, No 150 Xinhui Rd, Gaoxin Dist, Ningbo City (0574)87736499 Building 3, No 189 Hai Zhu Techno park, Dun He Road, Hai Zhu District, Guangzhou (020)89224310



NO.: I09042023504D


Date: 2014.09.11

Page 5 of 7

Halogen measurement flow-chart

Tested by: Zhang Tianyu Checked by: Cao Jia

Person in charge of the lab: Zhang Daiqin



www. ponytest. com

© Hotline 400-819-5688







Tel: (022)27360730

Building 35, No.680, Guiping Road, Xuhui District, Shanghai (021) 64851999



NO.: 109042023504D


Date: 2014.09.11

Page 6 of 7

Phthalate Measurement Flow-chart

Tested by: Fan Suping Checked by: Cao Jia

Person in charge of the lab: Zhang Daiqin



The page below is blank.

Ad

www. ponytest. com

© Hotline 400-819-5688

Add: Yingzhi Building,No.49-3,Suzhou Road,Haidian District, Beijing Tel: (010) 82618116

ijing Xuhu (021)

Building 35, No.680, Guiping Road, Xuhui District, Shanghai (021) 64851999

chuangye Road, Nanshan District, Shenzhen (0755) 26050909

6th Floor, No.190, Zhuzhou Road Laoshan District, Qingdao (0532) 88706866

Add: Ying huan Building, HongqiRoad, Nan kai district, Tianjin Tel: (022)27360730 Phase 2 Building 4, No 150 Xinhui Rd, Gaoxin Dist, Ningbo City (0574)87736499 Building 3, No 189 Hai Zhu Techno park, Dun He Road, Hai Zhu District, Guangzhou (020)89224310



NO.: I09042023504D


Date: 2014.09.11

Page 7 of 7

HBCDD Flow Chart

Tested by: Ji Erjie Checked by: Cao Jia

Person in charge of the lab: Zhang Daiqin



End of Report

www. ponytest. com

© Hotline 400-819-5688

DNY谱 尼



Add: Yingzhi Building,No.49-3,Suzhou Road,Haidian District, Beijing Tel: (010) 82618116

Add: Ying huan Building, HongqiRoad, Nan kai district, Tianjin Tel: (022)27360730

Building 35, No.680, Guiping Road, Xuhui District, Shanghai (021) 64851999

Phase 2 Building 4, No 150 Xinhui Rd, Gaoxin Dist, Ningbo City (0574)87736499

Chuangye Road, Nanshan District, Shenzhen (0755) 26050909

6th Floor, No.190, Zhuzhou Road Laoshan District, Qingdao (0532) 88706866