




CIRCUIT
PROTECTION
SOLUTIONS FOR
AUTOMOTIVE
APPLICATIONS





# 

**Passenger Car Solutions** 



### Our offering of automotive circuit protection solutions encompasses a wide range of applications:

Powertrain Engine Management

Transmission Control

Cooling Fan Water Pump

Safety ABS

EPAS

Air Bag Chassis Control

**Comfort** Window Lift

Sun Roof Door Lock Power Seat

HVAC

**Infotainment** Dashboard Navigation

In-Car Entertainment

Fuse Box Power Supply Lighting Wire Harness Generator HID Headlight Headlight Leveling Directional Lighting



# portfolio of Littelfuse automotive technologies, products & services

### Passenger Automobiles | Aftermarket

### **SERVICES**

### Product Technologies Plus Application Design Evaluation Services

Littelfuse is the world leader in circuit protection. We offer an extensive selection of circuit protection technologies for Automotive applications. Littelfuse circuit protection expert staff can assist you in designing circuit protection for your most demanding applications. Solutions for over-current applications as well as over-voltage applications are available from Littelfuse.



### **CIRCUIT PROTECTION TECHNOLOGIES (1-8)**

### 1. Fuses/Footprint Reduction

MICRO2<sup>™</sup>, MICRO3<sup>™</sup> fuses

### 2. Medium Current Cartridge Fuses

MCASE+<sup>™</sup> cartridge fuses; considerably smaller than JCASE<sup>®</sup> and Low Profile JCASE<sup>®</sup> fuses

### 3. Discrete High Current Fuses

High Current Bolt Down fuses and fuse arrays

### 4. ZCase Masterfuse

Smallest high current distribution product in the industry

### 5. Masterfuse

High current distribution array

### 6. ZCase Single MEGA


Minimal Footprint Bolt Down fuse

### 7. High Voltage Fuses

Low-current fuses for Electric and Hybrid Electric Vehicles

### 8. Battery Cable Protection

CABLE PRO® protectors for mounting directly inline as part of a high power cable assembly

















# Table of Contents



Blade Fuses	1	
Cartridge Fuses	10	
High Current Fuses	16	
Cable & PAL Fuses	39	
High Voltage Fuses	43	
Specialty Products	48	
Fuseology	50	

### Helping to make the World a Cleaner Place to Live

### Littelfuse and the Environment

As members of the global community, we at Littelfuse have always strived to understand the impact of what we do, and of what we create, on the world around us. Because of this, our concern for the environment has always been an integral and fundamental part of our business. We continually work to balance our business objectives with the need to protect and improve the local and global environment.

### Our Strategy for the Design of Eco-friendly Products

Littelfuse has established a focused program committed to developing high-performance eco-friendly products along with a comprehensive set of processing/reliability data and technical process expertise. This includes processes for eliminating, detecting and documenting the presence of hazardous materials such as

- Lead
- Cadmium
- Hexavalent Chromium
- Mercury
- Brominated flame-retardants (PBBs and PBDEs)

The Littelfuse strategy for eco-friendly products is specifically designed to help support our worldwide customers in their transition to Lead-Free processing.



All products considered to be lead-free are marked with this symbol.

Littelfuse defines lead-free as products which contain less than 1000ppm (0.1%) Lead, measured by weight of the entire product.



All RoHS compliant products are marked with this symbol.


Littelfuse follows the requirement set by the European Union for all RoHS compliant products. The European Union Directive 2002/95/EC RoHS restricts the use of Lead, Mercury, Hexavalent Chromium, Cadmium and Brominated flame-retardants (PBBs and PBDEs)

Visit www.littelfuse.com/lead-free for further information.



# Blade Fuses

MICRO2™ Blade Fuse 32V	2
MICRO3™ Blade Fuse 32V	3
Low Profile MINI® Fuses Rated 58V	4
MINI® Blade Fuse Rated 32V	5
MINI® Blade Fuse Rated 58V	6
ATOF® Blade Fuse Rated 32V	7
MAXI® Blade Fuse Rated 32V	8
MAXI® Blade Fuse Rated 58V	9



## Blade Fuses







(Tin plated) Blade Fuses

### MICRO2™ Blade Fuses Rated 32V

105°C and 85°C are typical system level temperature requirements.

The MICRO2™ Fuse is the new standard for vehicle circuit protection. Its sub-miniature design meets the need for more circuits to be protected while utilizing less space and its ability to cope with high temperatures in adverse environments makes the MICRO2™ Fuse of recommended choice for protection.

Black amperage stamps are used on the 20A & 25A / light colored housings to improve contrast for vision system inspection.

Specifications	MICR02	MICRO2 Sn
	(Silver Plated)	(Tin Plated)
Voltage Rating:	32 VDC	32 VDC
Interrupting Ratings:	1000A @ 32 VDC	1000A @ 32 VDC
*Component Level Temperature Range:	-40°C to +125°C	-40°C to +105°C
**System Level Temperature Range:	-40°C to +105°C	-40°C to +85°C

Terminals: Ag plated zinc alloy Sn plated zinc alloy

Housing Material: PA66 PA66

500

50

Conforms to: SAE 2741 and ISO 8820-3 in reference to electrical, mechanical

and environmental performance requirements

### RoHS

### **Ordering Information**

# Part Number Package Size 0327xxx.YX2S 4000

0327xxx.LXS

0327xxx.UXS


VIICRU2 Sn Fuse	
0327xxx.YX2T	4000

### **Time-Current Characteristics**

% of Rating	Opening Time Min / Max
110	100 h / —
135	0.75 sec / 120 sec
160	0.30 sec / 50 sec
200	0.15 sec / 5 sec
350	0.04 sec / 0.50 sec
600	0.02 sec / 0.100 sec

# Dimensions Dimensions in mm







### Ratings

Part Number	Current Rating (A)	Housing Material Color	Typ. Voltage Drop (mV)	Cold Resistance $(m\Omega)$	l²t (A²s)
0327005	5		116	17.4	17
032707.5_	7.5		106	10.8	47
0327010	10		102	7.7	89
0327015	15		94	4.9	189
0327020	20		91	3.5	397
0327025	25		90	2.6	585
0327030	30		88	2.1	1028

### Temperature Rerating Curve



### Time-Current Characteristic Curves



\*Component Level Temperature = the maximum ambient temperature that a single fuse will survive. This does not factor-in the heat from a populated fuse box, but does include the heat from the current load with the proper rerating. \*\*System Level Temperature represents the ambient temperature of the fuse box at a location within the vehicle. The temperature within a populated fuse box (in a given location) will be higher. The limiting factor is the plating. Sn-plating's temperature limit is =130°C, and Ag-plating allows up to 150°C at the terminal

interface.

Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for a damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.





### MICRO3™ Blade Fuses Rated 32V

The MICRO3™ Fuse has 3 terminals and 2 fuse elements with a common center terminal. Its sub-miniature design meets the need for more circuits to be protected while utilizing less space and its ability to cope with high temperatures in adverse environments makes the MICRO3™ Fuse of recommended choice for protection.

### **Specifications**

Voltage Rating: 32 VDC

1000A @ 32 VDC Interrupting Ratings: -40°C to +125°C \*Component Level Temperature Range: \*\*System Level Temperature Range: -40°C to +105°C

105°C is a typical system level temperature requirement.

Terminals: Ag plated zinc alloy

**Package Size** 

2000

50

Housing Material: PA66

Conforms to: SAE 2741 and ISO 8820-3 in reference to electrical, mechanical


and environmental performance requirements

### RoHS

### **Dimensions**

Dimensions in mm

(<u>□</u>300 □



### **Part Number** 0337xxx.PX2S

0337xxx.LXS

**Ordering Information** 


### Time-Current Characteristics

% of Rating	Opening Time (Min / Max)
110	100 h / –
135	0.75 sec / 120 sec
160	0.30 sec / 50 sec
200	0.15 sec / 5 sec
350	0.04 sec / 0.50 sec
600	0.02 sec / 0.100 sec

### Ratings


Part Number	Current Rating (A)	Housing Material Color	Typ. Voltage Drop (mV)	Cold Resistance (mΩ)	l²t (A²s)
0337005	5		116	17.4	17
033707.5_	7.5		106	10.8	47
0337010	10		102	7.8	89
0337015	15		94	4.9	189

### Temperature Rerating Curve



\*Component Level Temperature = the maximum ambient temperature that a single fuse will survive. This does not factor-in the heat from a populated fuse box, but does include the heat from the current load with the proper rerating. \*\*System Level Temperature represents the ambient temperature of the fuse box at a location within the vehicle. The temperature within a populated fuse box (in a given location) will be higher. The limiting factor is the plating. Sn-plating's temperature limit is ≈130°C, and Ag-plating allows up to 150°C at the terminal interface.

### Time-Current Characteristic Curves



Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse

# Blade Fuses






Low Profile MINI® Blade Fuses




Low Profile MINI® 10.9mm Blade Fuses

### **Dimensions**

Dimensions in mm



### Low Profile MINI® 10.9mm



### Low Profile MINI® Blade Fuses Rated 58V

The Low Profile MINI® fuse has similar performance characteristics as the standard MINI® fuse. The lower overall height allows for more space and weight savings. The Low Profile MINI® fuse is designed to mate with tuning-fork terminals, which provides additional weight and material savings in fuse box designs by eliminating the need for female box terminals.

### **Specifications**

Voltage Rating: 58 VDC
Interrupting Rating: 1000A @ 58 VDC
\*Component Level Temperature Range: -40°C to +125°C

\*\*System Level Temperature Range: -40°C to +125°C

 105°C is a typical system level temperature requirement.

 Terminals:
 Ag plated zinc

 Housing Material:
 PA66

 Complies with:
 ISO 8820-9

### Low Profile MINI® 10.9mm

**RoHS** 

### **Ordering Information**

Part Number	Package Size	Plating	
0891xxx.NXS	5000	Ag	
0891xxx.U	500	Ag	
0891xxx.H	100	Ag	
Low Profile MINI® 10.9mm Fuse			
0891xxx.NXWS	5000	Ag	

### **Time-Current Characteristics**


% of Rating	Opening Time Min / Max (s)
110	360,000 s / -
135	0.750 s / 120 s
200	0.150 s / 5 s
350	0.080 s / 0.250 s
600	0.030 s / 0.100 s

### Ratings


Part Number	Current Rating (A)	Housing Material Color	Cold Resistance $(m\Omega)$	l²t (A²s)
0891002 <sup>†</sup>	2		54.2	3
0891005	5		17.21	22
089107.5_	7.5		10.65	53
0891010	10		7.59	102
0891015	15		4.70	198
0891020	20		3.35	420
0891025	25		2.56	613
0891030	30		2.06	1110

† Only offered for the 10.0mm series.

### Time-Current Characteristic



### Temperature Rerating Curve



\*Component Level Temperature = the maximum ambient temperature that a single fuse will survive. This does not factor-in the heat from a populated fuse box, but does include the heat from the current load with the proper rerating. \*\*System Level Temperature represents the ambient temperature of the fuse box at a location within the vehicle. The temperature within a populated fuse box (in a given location) will be higher. The limiting factor is the plating. Sn-plating's temperature limit is ≈130°C, and Ag-plating allows up to 150°C at the terminal interface.

Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-saving, life-saving or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall not be liable for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.








MINI® Sn (Tin plated) Blade Fuses

### Time-Current Characteristic Curves



\*Component Level Temperature = the maximum ambient temperature that a single fuse will survive. This does not factor-in the heat from a populated fuse box, but does include the heat from the current load with the proper rerating. \*\*System Level Temperature represents the ambient temperature of the fuse box at a location within the vehicle. The temperature within a populated fuse box (in a given location) will be higher. The limiting factor is the plating. Sn-plating's temperature limit is ~130°C, and Ag-plating allows up to 150°C at the terminal interface.

### MINI® Blade Fuses Rated 32V

The MINI® Fuse is the standard for vehicle circuit protection. Its miniature design meets the need for more circuits to be protected while utilizing less space, and its ability to cope with high temperatures in adverse environments makes the MINI® Fuse of recommended choice for protection.

Specification	MINI	MINI Sn
	(Silver Plated)	(Tin Plated)
Interrupting Rating:	1000A @ 32 VDC	1000A @ 32 VDC
Voltage Rating:	32 VDC	32 VDC
*Component Level Temperature Range:	-40°C to +125°C	-40°C to +105°C
**System Level Temperature Range:	-40°C to +105°C	-40°C to +85°C
105°C and 85°C are typical system level tem	perature requirements.	
Terminals:	Ag plated zinc alloy	Sn plated zinc alloy
Housing Material:	PA66	PA66
Complies with:	SAE J2077, ISO 8820-3,	SAE J2077, ISO 8820-3
	UL 248 Special Purpose Fuses	not UL recognized





### **Ordering Information**

Part Number	Package Size
0297xxx.WXNV	3000
0297xxx.U	500
0297xxx.H	100
0297xxx.L	50
MINI® Sn Fuse	
0297xxx.WXT	3000


### **Time-Current Characteristics**


% of Rating	Opening Time Min / Max (s)
110	360,000 s / -
135	0.75 s / 600 s
200	0.15 s / 5 s
350	0.080 s / 0.500 s
600	0.030 s / 0.100 s

### Ratings


Part Number	Current Rating (A)	Housing Material Color	Typ. Voltage Drop (mV)		l²t (A²s)
0297002	2		171	55.60	2.8
0297003	3		153	33.75	9.4
0297004	4		121	23.48	17
0297005	5		129	17.75	25
029707.5_	7.5		135	10.85	68
0297010	10		108	7.42	93
0297015	15		98	4.58	270
0297020	20		96	3.21	380
0297025	25		86	2.36	625
0297030	30		87	1.85	1130

### **Dimensions**





### Temperature Rerating Curve



Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-saving life-saving or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse





### MINI® Blade Fuses Rated 58V

MINI® style fuse for use in 42V Systems. Same Time-Current characteristic as the 32V MINI® fuse. Fits into standard MINI® fuse sockets. Has a rejection feature to prevent fuses with lower voltage rating from being wrongfully inserted into the circuit. Current rating 2A - 30A @58 VDC max.

### **Specifications**

Interrupting Rating: 1000A @ 58 VDC

Voltage Rating: 58 VDC

\*Component Level Temperature Range: -40°C to +125°C

\*\*System Level Temperature Range: -40°C to +105°C

105°C is a typical system level temperature requirement.

Terminals: Ag plated zinc alloy

Housing Materials: PA66


**RoHS** 

Complies with: SAE J2077, SAE 2576

ISO 8820

UL 248 Special Purpose Fuses

# Time-Current



\*Component Level Temperature = the maximum ambient temperature that a single fuse will survive. This does not factor-in the heat from a populated fuse box, but does include the heat from the current load with the proper rerating. \*\*System Level Temperature represents the ambient temperature of the fuse box at a location within the vehicle. The temperature within a populated fuse box (in a given location) will be higher. The limiting factor is the plating. Sn-plating's temperature limit is ~130°C, and Ag-plating allows up to 150°C at the terminal interface.

### **Ordering Information**

Part Number	Package Size
0997xxx.WXN	3000


### **Time-Current Characteristics**

% of Rating	Opening Time Min / Max (s)
110	360,000 s / -
135	0.75 s / 600 s
200	0.15 s / 5 s
350	0.080 s / 0.500 s
600	0.030 s / 0.100 s

### Ratings


Part Number	Current Rating (A)	Housing Material Color	Typ. Voltage Drop (mV)	$\begin{array}{c} \text{Cold Resistance} \\ \text{(m}\Omega) \end{array}$	l²t (A²s)
0997002_	2		171	55.60	2.8
0997003_	3		153	33.75	9.4
0997004_	4		121	23.48	17
0997005_	5		129	17.75	25
099707.5_	7.5		135	10.85	68
0997010_	10		108	7.42	93
0997015_	15		98	4.58	270
0997020_	20		96	3.21	380
0997025_	25		86	2.36	625
0997030_	30		87	1.85	1130

### Dimensions



# 0.825→|-

### Temperature Rerating Curve



Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.

# Blade Fuses






ATOF® Blade Fuses




ATO® Ag (Silver plated) Blade Fuses

### Time-Current Characteristic Curves



### Temperature Rerating Curve



### ATOF® Blade Fuses Rated 32V

Developed by Littelfuse for the automotive industry, the ATOF® fuse has become the original equipment circuit protection standard for foreign and domestic automobiles and trucks. Readily identifiable and easily replaced, this fuse can be specified for a variety of low voltage electronic applications.

Specification	AT0F®	ATO Ag
•	(Tin Plated)	(Silver Plated)
Voltage Rating:	32 VDC	32 VDC
Interrupting Rating:	1000A @ 32 VDC	1000A @ 32 VDC
*Component Level Temperature Range:	-40°C to +105°C	-40°C to +125°C
**System Level Temperature Range:	-40°C to +85°C	-40°C to +105°C
105°C and 85°C are typical system level te	mperature requirements.	
Terminals:	Sn plated zinc alloy	Ag plated zinc alloy
Housing Material:	PA66	PA66
Complies with:	SAE J1284,ISO 8820-3	SAE J1284,ISO 8820-3
Ul Listed:	File AU1410	File AU1410

File No. 29862



### Ordering Information

Part Number	Package Size
0287xxx.PXCN	2000
0287xxx.U	500
0287xxx.H	100
0287xxx.L	50
ATO® Ag Fuse	
0287xxx.PXS	2000

### **Time-Current Characteristics**

% of Rating	Current Rating	Opening Time Min / Max (s)
100	35A & 40A	360,000 s / -
110	1A-30A	360,000 s / -
135	1A & 2A 3A-40A	350 ms / 600 s 0.750 s / 600 s
160	1A-40A	250 ms / 50 s
200	1A & 2A 3A-40A	100 ms / 5.0 s 0.150 s / 5.0 s
350	1A & 2A 3A-40A	20 ms / 500 ms 80 ms / 500 ms
600	1A-30A 35A & 40A	- / 100 ms - / 150 ms


File No. 29862

### Ratings

Part Number	Current Rating (A)	Housing Material Color	Typ. Voltage Drop (mV)	Cold Resistance (mΩ)	l²t (A²s)
0287001	1		176	123	0.4
0287002	2		141	53.5	1.4
0287003	3		137	31.1	7.4
0287004	4		136	22.8	14
0287005	5		128	17.85	26
028707.5_	7.5		116	10.91	60
0287010	10		109	7.70	115
0287015	15		102	4.80	340
0287020	20		98	3.38	520
0287025	25		92	2.52	1080
0287030	30		84	1.97	1510
0287035	35		87	1.61	2280
0287040	40		96	1.44	3310
0287900	SHUNT				

### **Dimensions**

Dimensions in mm



\*Component Level Temperature = the maximum ambient temperature that a single fuse will survive. This does not factor-in the heat from a populated fuse box, but does include the heat from the current load with the proper rerating. \*\*System Level Temperature represents the ambient temperature of the fuse box at a location within the vehicle. The temperature within a populated fuse box (in a given location) will be higher. The limiting factor is the plating. Sn-plating's temperature limit is =130°C, and Ag-plating allows up to 150°C at the terminal interface.

Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-saving, life-saving or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any purpose arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.








MAXI Sn Fuse (tin plated)

### Time-Current Characteristic Curves



\*Component Level Temperature = the maximum ambient temperature that a single fuse will survive. This does not factor-in the heat from a populated fuse box, but does include the heat from the current load with the proper rerating. \*\*System Level Temperature represents the ambient temperature of the fuse box at a location within the vehicle. The temperature within a populated fuse box (in a given location) will be higher. The limiting factor is the plating. Sn-plating's temperature limit is ~130°C, and Ag-plating allows up to 150°C at the terminal interface.

### MAXI Blade Fuses Rated 32V

The MAXI® fuse uses "Diffusion Pill Technology" to provide predictable time delay characteristics and low heat dissipation.

Specification	MAXI	MAXI Sn
	(Silver Plated)	(Tin Plated)
Voltage Rating:	32 VDC32 VDC	
Interrupting Ratings:	1000A @ 32 VDC	1000A @ 32 VDC
*Component Level Temperature Range:	-40°C to +125°C	-40°C to +105°C
**System Level Temperature Range:	-40°C to +105°C	-40°C to +85°C
105°C and 85°C are typical system level	temperature requirements.	
Terminals:	Ag plated zinc alloy	Sn plated zinc alloy
Housing Material:	PA66 PA66	
Complies with:	SAE J 1888, SAE 2576,	SAE J 1888, SAE 2576,
Balle Palle	ISO 8820-3:2002(E)	ISO 8820-3:2002(E)



### **Ordering Information**

Part Number	Package Size
0299xxx.ZXNV	1200
0299xxx.L	50
0299xxx TXN	10

# MAXI Sn Fuse 0299xxx.ZXT 1200

### Time-Current Characteristics

% of Rating	Opening Time Min / Max (s)
100	360,000 s / -
135	60 s / 1,800 s
200	2 s / 60 s
350	0.20 s / 7 s
600	0.040 s / 1 s


### Ratings


Part Number	Current Rating (A)	Housing Material Color	Typ. Voltage Drop (mV)	Cold Resistance (mΩ)	l²t (A²s)
0299020	20		76	3.10	1100
0299025	25		75	2.39	2087
0299030	30		77	1.95	4070
0299035	35		75	1.71	6032
0299040	40		75	1.42	8450
0299050	50		73	1.10	11300
0299060	60		77	0.89	15300
0299070	70		61	0.64	21200
0299080	80		62	0.54	43600

### **Dimensions**

Dimensions in mm

### Temperature Rerating Curve





**MAXI Fuse Temperature Rerating Curve** 

Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.

# Blade Fuses





### MAXI Blade Fuses Rated 58V

The MAXI® style fuse for use in 42V Systems. Same Time-Current characteristic as the 32V MAXI fuse using "Diffusion Pill Technology" to provide predictable time delay characteristics and low heat dissipation. Fits into standard MAXI® fuse sockets. Has a rejection feature to prevent fuses with lower voltage rating from being wrongfully inserted into the circuit. Current rating 20A - 80A @58 VDC max.

### **Specifications**

Voltage Rating: 58 VDC
Interrupting Ratings: 1000A @ 58 VDC
\*Component Level Temperature Range: -40°C to +125°C
\*\*System Level Temperature Range: -40°C to +105°C
\*\*System Level Temperature Range: -40°C to +105°C

Terminals: Ag plated zinc alloy

Housing Material: PA66

Complies with: SAE J 1888, SAE 2576
ISO 8820-3:2002(E)



**Ordering Information** 

### Time-Current Characteristics

# Part Number Package Size 0999xxx.ZXN 1200

% of Rating	Opening Time Min / Max (s)
100	360,000 s / -
135	60 s / 1,800 s
200	2 s / 60 s
350	0.20 s / 7 s
600	0.040 s / 1 s


### Ratings

Part Number	Current Rating (A)	Housing Material Color	Typ. Voltage Drop (mV)	Cold Resistance (mΩ)	l²t (A²s)
0999020	20		76	3.10	1100
0999025	25		75	2.39	2087
0999030	30		77	1.95	4070
0999035	35		75	1.71	6032
0999040	40		75	1.42	8450
0999050	50		73	1.10	11300
0999060	60		77	0.89	15300
0999070	70		61	0.64	21200
0999080	80		62	0.54	43600

### **Dimensions**

Dimensions in mm

Temperature Rerating Curve




Time-Current


1000

Characteristic Curves

2224 2254 224 204 204 204 304

\*Component Level Temperature = the maximum ambient temperature that a single fuse will survive. This does not factor-in the heat from a populated fuse box, but does include the heat from the current load with the proper rerating.
\*\*System Level Temperature represents the ambient temperature of the fuse box at a location within the vehicle. The temperature within a populated fuse box (in a given location) will be higher. The limiting factor is the plating.
Sn-plating's temperature limit is = 130°C, and Ag-plating allows up to 150°C at the terminal interface.






Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-saving, life-saving or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall not be liable for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.



MCASE+ Cartridge Fuses Rated 32V	1
MCASE™ Cartridge Fuses Rated 32V	13
Low Profile JCASE® Fuse Rated 58V	1
JCASE® Fuse Rated 32V	1!







MCASE+™ Cartridge Fuses

### MCASE+™ Cartridge Fuses Rated 32V

The Unslotted MCASE+™ Fuse is a cartridge style fuse up to 40A with female terminals for 2.8 mm male terminals. The Slotted MCASE+™ Fuse is available in amperages up to 60A and can mate with larger male terminals (e.g., 6.3mm) or even mount directly to onto a busbar. It has a miniaturized footprint for optimal usage of space. It is a time delayed fuse and can handle inrush currents.

### **Specifications**

Voltage Rating: 32 VDC Interrupting Ratings: 1000A @ 32 VDC Operating Temperature Range: -40°C to +125°C PPA-GF33 Housing Material: PA66 Cover Material:

Fuse Insertion Force: 50N (11.2lbf) Typical

**Extraction Force:** 4N Min. (0.9 lb). I 24.5N Max. (5.5 lb)

Conforms to: SAE 2741 and ISO 8820-4 in reference to electrical, mechanical

and environmental performance requirements

### **Ordering Information**

Part Number	Package Size
0695xxx.PXPS Slotted	2000
0695xxx.PXP Unslotted	2000

### **Time-Current Characteristics**


% of Rating	Opening Time Min / Max
110	100hrs / –
135	60s / 1800s
200	2s / 60s
350	0.2s / 7s
600	N N4s / 1s

### Ratings


Part Number	Туре	Current Rating* (A)	Housing Material Color	Max. Voltage Drop (mV)	Cold Resistance $(\mathbf{m}\Omega)$	I²t (A²s)
0695015.PXP	Unslotted	15		125	5.1	310
0695020.PXP	Unslotted	20		125	3.4	750
0695025.PXP	Unslotted	25		125	2.5	1300
0695030.PXP	Unslotted	30		120	1.8	970
0695040.PXP	Unslotted	40		120	1	1550
0695015.PXPS	Slotted	15		125	5.1	310
0695020.PXPS	Slotted	20		125	3.4	750
0695025.PXPS	Slotted	25		125	2.5	1300
0695030.PXPS	Slotted	30		120	1.8	970
0695040.PXPS	Slotted	40		120	1.1	1550
0695050.PXPS	Slotted	50		120	0.8	4000
0695060.PXPS	Slotted	60		120	0.6	8500

<sup>\*</sup> The performance of the male terminal is critical to ensuring the fuse will function as designed. The current-carrying capability of the mating terminal must be verified to ensure proper system operation.

### Temperature Rerating Curve



### Time-Current Characteristic Curves



Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse





### MCASE+™ Cartridge Fuses Rated 32V

### **Dimensions**

Dimensions in mm

### Slotted












### Unslotted





6.6 (0.1 -







MCASE™ Cartridge Fuses

### MCASE™ Cartridge Fuses Rated 32V

The MCASE™ is a cartridge style fuse with female terminals for 2.8 mm male terminals. It has a miniaturized footprint for optimal usage of space. It is a time delayed fuse and can handle in rush currents.

### **Specifications**

Voltage Rating: 32 VDC

Interrupting Ratings: 1000A @ 32 VDC
Operating Temperature Range: -40°C to +125°C
Housing Material: PPA-GF33
Cover Material: PA66

Insertion Force: 50N (11.2lbf) Typical

Extraction Force: 4N Min. (0.9 lb). I 24.5N Max. (5.5 lb)

Conforms to: SAE 2741 and ISO 8820-4 in reference to electrical, mechanical

and environmental performance requirements



### **Ordering Information**


Part Number	Package Size
0695xxx.PX4	2000
0695xxx.U	500
0695xxx.L	50

### Time-Current Characteristics

% of Rating	Opening Time Min / Max (s)
110	100 hrs / –
135	60 s / 1800 s
200	2 s / 60 s
350	0.2 s / 7 s
600	0.04 s / 1 s

### Dimensions


Dimensions in mm




### Ratings

Part Number	Current Rating (A)	Housing Material Color	Max. Voltage Drop (mV)	Cold Resistance $(m\Omega)$	l²t (A²s)
0695015	15		125	4.9	160
0695020	20		125	3.5	530
0695025	25		125	2.3	1140
0695030	30		120	1.8	970
0695040	40		120	1.3	2950

### Time-Current Characteristic Curves



### Temperature Rerating Curve




Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-saving, life-saving or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.





Low Profile JCASE® Cartridge Fuses

### Time-Current Characteristic Curves



### Low Profile JCASE® Cartridge Fuses Rated 58V

The Low Profile JCASE® fuse has similar performance characteristics as the standard JCASE® fuse. The lower overall height reduction allows for more space and weight savings and also allows for a shorter male blade terminal, saving additional weight and material savings in fuse box designs.

### **Specifications**

Voltage Rating: 58 VDC
Interrupting Rating: 1000A @ 58 VDC
Operating Temperature Range: -40°C to + 125°C
Housing Material: PPA-GF13
Cover Material: PA66

Insertion Force: 53N Max. (12 lb.) Extraction Force: 9N Min (2 lb.)

Conforms to: SAE 2741 and ISO 8820-4 except for the life test – LF specification is 100-hours at 100% of rated current

### **Ordering Information**

Part Number	Package Size
0895xxx.Z	2000
0895xxx.U	500
0895xxx.T	10

### **Time-Current Characteristics**

	% of Rating	Opening Time Min / Max (s)
	100	360,000 s / —
	135	60 s / 1800 s
	200	4 s / 60 s
	350	0.200 s / 7 s
	600	0.040 s / 1 s


### Ratings

Current Rating (A)	Housing Material Color	Max. Voltage Drop (mV)	Cold Resistance $(m\Omega)$	l²t (A²s)
20		125	4.48	400
25		125	3.39	680
30		125	2.68	1780
40		125	1.89	5470
50		125	1.08	4880
60		125	0.83	9600
	(A) 20 25 30 40 50	(A) Material Color 20	(A) Material Color (mV)  20 125 25 125 30 125 40 125 50 125	(A)     Material Color     (mV)     (mΩ)       20     125     4.48       25     125     3.39       30     125     2.68       40     125     1.89       50     125     1.08


Corresponding holder see Section "Fuse Holders."

### **Dimensions**

Dimensions in mm



### Temperature Rerating Curve



Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-saving, life-saving or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any purpose arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.





JCASE® Cartridge Fuses

### JCASE® Cartridge Fuses Rated 32V

The JCASE® is a cartridge style fuse with female terminal design. JCASE® provides both increased time delay and low voltage drop to protect high current circuits. JCASE® has the ability to handle inrush currents.

### **Specifications**


Voltage Rating: 32 VDC Interrupting Rating: 1000A @ 32 VDC Operating Temperature Range: -40°C to + 125°C PA-GF13HS Housing Material: PA-GF13 Housing Material (60A): Cover Material: PC

Insertion Force: 53N max. (12 lb.) **Extraction Force:** 9N min. (2 lb.) SAE 2741, ISO 8820-4 Complies with:



### RoHS

### Time-Current Characteristic Curves



### **Ordering Information**

### **Time-Current Characteristics**


Part Number	Package Size	% of Rating	Opening Time Min / Max (s)
0495xxx.ZXA	2200	110	360,000 s / -
0495xxx.UXA	500	135	60 s / 1800 s
0495xxx.TXA	10	200	4 s / 60 s
		350	0.200 s / 7 s
atings		600	0.040 s / 1 s


### Ratings

Part Number	Current Rating (A)	Housing Material Color	Typ. Voltage Drop (mV)	Cold Resistance $(m\Omega)$	l²t (A²s)
0495020_	20		106	4.29	1750
0495025_	25		101	3.28	3220
0495030_	30		91	2.12	1480
0495040_	40		87	1.30	3650
0495050_	50		88	0.99	8750
0495060_	60		87	0.76	19500

### **Dimensions**

Dimensions in mm






Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse



ZCase Masterfuse	17
Masterfuse	18
ZCase Single Starter	19
MEGA® High Performance Fuse Rated 70V	21
MEGA® Fuse Rated 32V	22
MEGA® Low Temperature Fuse Rated 32V	24
UL Recognized Mega® Fuse Rated 32V	25
MIDI® Style Bolt-down Fuse Rated 32V	26
BF1 Fuse Rated 32V	28
BF1 Fuse Rated 58V	30
BF2 Fuse Rated 32V	31
BF2 Fuse Rated 58V	32
CF Fuse Rated 58V	33
Fuse Strips	34







### **ZCASE** Masterfuse

The ZCASE Masterfuse product is the smallest high current distribution product in the industry. It utilizes the Z-Axis effectively to create a compact design which takes one third the footprint of a traditional solution. This package allows the user to replace multiple discrete fuses in a power distribution box with a single component, thus eliminating additional bolts, bus bars and interconnects. The output bolt is integrated into the fuse creating a reliable interface to the mating terminal due to its high torque withstandablity. Keying features are available on each bolt position to ensure the correct mating ring terminal is used during assembly. The solution can also be connectorized to mate to high current terminals. This compact design enables the integration of the high current distribution into the main junction box due to its small footprint. This eliminates the need for a separate fuse box for high current distribution. By reducing the number of components required, overall system costs are reduced.

The ZCASE Masterfuse product is available as a standard design with customized fuse ratings. The modular manufacturing approach enables a wide range of configurations within a product family. In addition, the form factor can be fully customized for specific applications to further optimize the system. Contact Littelfuse to review your application needs.

### Features and Benefits:

Miniaturization: Compact design enables a 2/3 footprint reduction when compared to a traditional solution.

Integration: Enables the integration of the prefuse function into the main junction box due to its small footprint.

### **Specifications**

Mating Terminal Options: M10, M8, M6, M5 bolt-down connections or female terminals

Operating Temperature Range: -40°C to 125°C
Housing Material: PPA-GF33HS
Fuse Ratings Available: 30-500A
Voltage Rating: 32Vdc

Materials: Copper terminals (silver or tin plating options available)

Complies with: ISO 8820-5



### **Ordering Information**

Part Number	Description	Package Size
05980015Z-CN	MFUSE ZCASE 32V 2-Way 125A - 200A	200
05980016Z-CN	MFUSE ZCASE 32V 2-Way 125A - 125A	200
05980017Z-CN	MFUSE ZCASE 32V 2-Way 275A - 200A	200
05980019Z	MFUSE ZCASE 32V 1-MEGA + 4-MIDI	100
05980020Z	MFUSE ZCASE 32V 2-MEGA + 2-MIDI	50

17





#### Masterfuses

### **MASTERFUSE**

The MASTERFUSE product is a configurable fuse solution combining several different fuse types (i.e. MEGA and MIDI) and ratings in one compact package. This fuse package allows the user to replace multiple discrete fuses in a power distribution box with a single component, thus eliminating additional bolts, bus bars, and interconnects that are currently used. By reducing the number of connections required, overall system reliability is increased while cost is decreased.

Each MASTERFUSE is customized to the user's application creating an optimized circuit protection package. Contact Littelfuse to review your application needs.

### Features and Benefits:

Increased Reliability: due to reduced number of terminal interfaces

System Cost Savings: Material savings due to reduced number of components

required. Assembly cost savings due to reduced number of

operations required for installation.

Fuse Array Customization: Ability to mix different fuse types (i.e. MEGA, MIDI, etc.)

in one compact package

Termination Options: Ability to mate to female terminals to enable "bolt-less" design

Marking: Custom marking options available



### **Specifications**

Mating Terminal Options: M10, M8, M6, M5 bolt-down connections or female terminals


Operating Temperature Range: -40°C to 125°C
Housing Material: PPA-GF33HS
Fuse Ratings Available: 30A-250A Full Range
300A-600A Short Circuit

oltage Rating: 32Vdc

Materials: Copper terminals (silver or tin plating options available)

omplies with: ISO 8820-5

Note: Short circuit protected fuses have a limited continious current.



Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-saving, life-saving or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.





ZCASE Single Mega/Starter Fuse

### **ZCASE Single MEGA/Starter Fuse**

The Single ZCASE is a Minimal Footprint Bolt Down Fuse with a wide rating range up to 600A in the same packaging size. The Time Current characteristic is similar to the well known MEGA Design and can used as full wire protection until 250A. Higher ratings mostly used for typically Starter Fuse application as a protector fuse. The fuse design is optimized for a one bolt connection M6 (40A - 250A) or M8 (300A - 600A) and can used directly on a battery post or busbar connection. Littelfuse is offering a complete solution for the necessary stud and different busbar connections including some battery clamps.

### **Specifications**

Operating temperature: -40 to 125°C
Housing Material: PPA-GF33HS
Insulating Tube: Out of ceramic
Terminal: Tin plated Copper
Voltage Rating: 32V DC

Interrupting Rating: 2000A @ 32V VDC
Mounting Torque M6: 9.8Nm±1.4Nm
Mounting Torque M8: 14Nm±2Nm

### **Ordering Information**

Part Number	Package Size
3298XXX.ZXSTA	480
3298XXX.Z	480
3298XXX.H	100

### **Time-Current Characteristics**

% of Rating	Opening Tim	e Min / Max (s)	
	40A - 250A	300A - 500A	600A
50	-/-	14,400 /-	14,400 /-
100	14,400 /-	-/-	-/-
135	120 / 1800	-/-	-/-
200	1 / 15	1 / 40	1 / 40
350	0.300 / 5	0.300 / 5	0.300 / 5
500	-/-	-/-	0.100 / 1
600	0.100 / 1	0.100 / 1	-/-


### Ratings

Part number	Current Rating (A)	Wire size (mm²)	Max. Voltage Drop (mV)	Average Cold Resistance (m $\Omega$ )	l²t (A²s)
3298040	40	4	110	1.53	5000
3298060	60	6	110	0.98	18000
3298080	80	10	110	0.715	15500
3298100	100	16	110	0.57	31000
3298125	125	16	110	0.39	45000
3298150	150	25	110	0.32	75000
3298175	175	25	110	0.26	140000
3298200	200	35	110	0.231	235000
3298225	225	35	110	0.175	95000
3298250	250	50	110	0.167	160000
3298300.ZXSTA	300	35	70	0.128	310000
3298350.ZXSTA	350	35	70	0.103	570000
3298400.ZXSTA	400	50	70	0.084	870000
3298500.ZXSTA	500	50	70	0.065	1550000
3298600.ZXSTA	600	50	70	0.049	3000000
3298900	SHUNT	50	-	-	-

Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-saving, life-saving or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any purpose arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.



### ZCASE Single Mega/Starter Fuse




### Assembly Components (sold separately)

Part No.	Description
882-853	3-Way Bus Bar with M8 Insulating Bolts Assembly*
882-854	2-Way Bus Bar with M8 Insulating Bolts Assembly* *M8 Nuts not inlcuded
876-199	Battery Terminal Mount
32980001ZXM8	M8 Insulating Bolt



Please contact your Littelfuse representative for application support and information on mating hardware.


### Time-Current Characteristic Curves




All ZCASE Starters T/C curves were performed on the left or right side of the metal bar as shown in pictures above. A 50mm² Cu wire was mounted at the mid hole (M8) of the metal bar as current feed.


Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.





### Time-Current Characteristic Curves





### MEGA® High Performance Fuse Rated 70V

The MEGA® 70V High Performance (HP) Fuse is designed for high current circuit protection up to 500A with "Diffusion Pill Technology." The MEGA 70V HP features 1MOhm Open State Resistance after fuse opening to guarantee safe interruption at any voltage up to 70V. The MEGA® 70V HP Fuse is ideal for battery and alternator protection application and other heavy gauge cables requiring ultra-high current protection.

### **Specifications**

Interrupting Rating: 2500A @ 70 VDC

Voltage Rating: 70 VDC

Operating Temperature Range: -40°C to + 125°C

Housing Material: PPA-GF33

Terminals: ETP Copper (Tin plated)
Mounting Torque M6: 9Nm+/-1Nm
Mounting Torque M8: 20Nm+/-1Nm

Open State Resistance (after fuse opening) >1MOhm


Reference to: ISO 20934 - Type SF51 (draft), LV 230

### RoHS

### **Ordering Information**

•					
	Part Number	Package Size	Rating	Bolt Size	Bolt Hole Qty
	0998xxx.U-2M8		60 - 500	M8	2
	0998xxx.U-1M8		60 - 500	M8	1
	0998xxx.U-2M6		60 - 500	M6	2
	0998xxx.U-1M6		60 - 500	M6	1
	0998xxx.U-NH		60 - 500	N/A	0

### **Dimensions**



### **Time-Current Characteristics**

% of	Opening Time	Min / Max (s)
nating	60-300	350-500
75		14,400 s / -
100	14,400 s / -	
135	120 s / 1800 s	-/-
150	20 s / 450 s	-/-
200	1 s / 15 s	1 s / 15 s
350	0.500 s / 5 s	0.500 s / 5 s
600	0.100 s / 1 s	-/-

### Ratings

Part Number	Current Rating (A)	Font Color	Rated Voltage (V)	Voltage Drop (mV) max.	Wire (mm²)	I²t (A²s)
0998060	60		70	110	6	25000
0998080	80		70	110	10	46000
0998100	100		70	110	10	23000
0998125	125		70	110	16	43000
0998150	150		70	110	25	72000
0998175	175		70	110	25	112000
0998200	200		70	110	35	193000
0998225	225		70	110	35	250000
0998250	250		70	110	50	240000
0998300	300		70	80	50	300000
0998350	350		70	80	50	590000
0998400	400		70	80	70	950000
0998450	450		70	80	70	1250000
0998500	500		70	80	70	1750000

Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-saving, life-saving or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall not be liable for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.





### MEGA® and MEGA® Clear Top Fuse Rated 32V

The MEGA® Fuse is designed for high current circuit protection up to 500A with "Diffusion Pill Technology." The MEGA® Fuse also provides time delay characteristics. Designed and patented by Littelfuse, the MEGA® Fuse is ideal for battery and alternator protection application and other heavy gauge cables requiring ultra-high current protection.

### **Specifications**

Interrupting Rating: 2000A @ 32 VDC
Voltage Rating: 32 VDC
Operating Temperature Range: -40°C to + 125°C
Housing Material: PPA-GF33HS

Clear Top Housing Material: PES (top) PPA-GF33HS (bottom)
Terminals: Copper (Silver plated copper available)

M6 or M8 bolts available

Mounting Torque: 8-14 Nm M6 12-18 Nm M8

Complies with: ISO 8820-5





MEGA® Clear Top Housing Fuse

### RoHS

### **Ordering Information**

Part Number	Rating	Package Size	Plating	Bolt Size	Bolt Hole Qty	
0298xxx.ZXEH	80 - 250	500	None	M8	2	
0298xxx.ZXH	300 - 500	500	None	M8	2	
0298xxx.UX1M8	80 - 500	500	None	M8	1	
0298xxx.ZXB	40 - 250	500	Ag	M8	2	
0298xxx.ZXA	80 - 500	500	None	M6	2	
MEGA Clear Top Housing Material Fuse						
0298xxx.UXT	40 - 250	500	None	M8	2	

### **Time-Current Characteristics**

% of	Opening Time Min / Max (s)				
Rating	40-250	300-500			
75	-/-	14,400 s / -			
100	14,400 s / -	-/-			
135	120 s / 1800 s	-/-			
200	1 s / 15 s	1 s / 15 s			
350	0.300 s / 5 s	0.500 s / 5 s			
600	0.100 s / 1 s	0.100 s / 1 s			

### Ratings

Part Number	Current Rating (A)	Font Color* Typ. Voltage Drop (mV)		$\begin{array}{c} \text{Cold Resistance} \\ \text{(m}\Omega) \end{array}$	l²t (A²s)
02980401	40	-	132	2.510	8700
02980601	60	-	119	1.504	21000
0298080	80		87	0.720	21500
0298100	100		87	0.562	31100
0298125	125		80	0.423	57800
0298150	150		92	0.352	100000
0298175	175		86	0.294	168000
0298200	200		83	0.257	204000
0298225	225		82	0.222	257000
0298250	250		82	0.201	389000
02983002	300		74 **	0.167	315000
02983502	350		68 **	0.138	500000
02984002	400		64 **	0.126	610000
02984502	450		60 **	0.112	1050000
02985002	500		58 **	0.092	2050000

Note 1: Not mentioned in ISO standards Note 2: Short Circuit Protector only

Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for a damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.

<sup>\* 0298</sup>xxx.ZXB has white font color on all ratings.


<sup>\*\*</sup> Voltage Drop measurements for short circuit protectors taken at 75% of rated current.




### MEGA® Fuse Rated 32V

### **Dimensions**


Dimensions in mm



### Temperature Rerating Curve



### Time-Current Characteristic Curves



Notes

- 1: 60A, 80A Not mentioned in ISO Standards.
- 2: 300A to 500A Short Circuit Protector Only





MEGA® Low Temperature Fuses

### MEGA® Low Temperature Fuse Rated 32V

The MEGA® Fuse is designed for high current circuit protection up to 275A with "Diffusion Pill Technology." The MEGA® Fuse also provides time delay characteristics. Designed and patented by Littelfuse, the MEGA® Fuse is ideal for battery and alternator protection application and other heavy gauge cables requiring ultra-high current protection.

### **Specifications**

Interrupting Rating: 2000A @ 32 VDC
Voltage Rating: 32 VDC
Operating Temperature Range: -40°C to + 125°C
Housing Material: PPA-GF33HS

Terminals: Copper (Silver plated copper available)

M8 bolts 12-18 Nm M8

RoHS

Mounting Torque:

### **Ordering Information**

Part Number	Rating	Package Size	Plating	Bolt Hole Qty
0298125.ZXBLT	125	500	Ag	2
0298xxx.ZXEH-LT	150-275	500	None	2
0298xxx.UX1M8LT	150-275	500	None	1


### **Time-Current Characteristics**

% of Rating		Opening Time Min / Max (s)			
		125	150-275		
	100	4 hrs / –	4 hrs / –		
	135	120 s / 1800 s	120 s / 1800 s		
	200	1 s / 50 s	1 s / 150 s		
	350	0.300 s / 5 s	0.300 s / 5 s		
	600	0.100 s / 1 s	0.100 s / 1 s		

### Ratings


Part Number	Current Rating (A)	Font Color	Typ. Voltage Drop (mV)	Cold Resistance $(\mathbf{m}\Omega)$	l²t (A²s)
0298125.ZXBLT	125		67	0.330	57000 A
0298150.ZXEH-LT	150		62	0.258	59000 A
0298175.ZXEH-LT	175		65	0.232	123000 A
0298200.ZXEH-LT	200		61	0.214	140000 A
0298225.ZXEH-LT	225		57	0.177	317000 A
0298250.ZXEH-LT	250		54	0.144	637000 A
0298275.ZXEH-LT	275		53	0.122	800000 A

### Time-Current Characteristic Curves




Last figure of article no. = packaging code

### **Dimensions**



### Temperature Rerating Curve



Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.







UL Recognized MEGA® Fuses

### UL Recognized MEGA® Fuses Rated 32V

The MEGA® Fuse is designed for high current circuit protection with "Diffusion Pill Technology." The MEGA® Fuse also provides time delay characteristics. Designed and patented by Littelfuse, the MEGA® Fuse is ideal for battery and alternator protection application and other heavy gauge cables requiring ultra-high current protection.

### **Specifications**

Interrupting Rating: 2000A @ 32 VDC
Voltage Rating: 32 VDC
Operating Temperature Range: -40°C to + 125°C
Housing Material: PPA-GF30FR
Terminals: Copper
M8 bolts holes


Mounting Torque: 12-18 Nm M8

Complies with: ISO 8820-5 ,UL 248 Special Purpose Fuses





### Time-Current Characteristic Curves



### **Ordering Information**

Part Number	Package Size
0298xxx.ZXEH-UL	500

### **Time-Current Characteristics**


0/ - <b>f.D</b> - <b>f:</b>	Opening Time Min / Max (s)			
% of Rating	80A-175A			
75	-/-			
100	14,400 s / –			
135	120 s / 1800 s			
200	1 s / 15 s			
350	0.300 s / 5 s			
500	-/-			
600	0.100 s / 1 s			

### Ratings


Part Number	Current Rating (A)	Font Color	Typ. Voltage Drop (mV)	l²t (A²s)
0298080.ZXEH-UL	80		87	21500
0298100.ZXEH-UL	100		87	31100
0298125.ZXEH-UL	125		80	57800
0298150.ZXEH-UL	150		92	100000
0298175.ZXEH-UL	175		62	168000

### **Dimensions**

Dimensions in mm




### Temperature Rerating Curve



Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-saving, life-saving or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.





MIDI® Fuses





Clear MIDI® Fuses (transparent nylon composite cover)

One Hole MIDI® Fuses

### Time-Current Characteristics

% of Rating	Opening Time Min / Max (s)				
70 Of Hatting	23-125A	150-200A			
75	-/-	360,000 s / -			
100	360,000 s / –	-/-			
110	14,400 s / -	-/-			
150	90 s / 3,600 s	-/-			
200	3 s / 100 s	1 s / 15 s			
300 350	0.3 s / 3 s -/-	-/- 0.3 s / 5 s			
500	0.1 s / 1 s	-/-			
600	-/-	0.1 s / 1 s			

# $\text{MIDI}^{\$},$ Clear $\text{MIDI}^{\$},$ and One Hole $\text{MIDI}^{\$}$ Style Bolt-down Fuse Rated 32V

This MIDI® style fuse offers a bolt-on space saving fuse for high current wiring protection and provides time delay characteristics with "Diffusion Pill Technology". The MIDI® was designed and patented by Littelfuse.

### **Specifications**

Interrupting Rating: 1000A @ 32 VDC

Voltage Rating: 32 VDC

Operating Temperature Range: -40°C to + 125°C

Black Housing Material: PA-GF25FR

Clear Housing Material: PA-6/66

Terminal: Tin plated Copper

Mounting Torque M5: 4.5 Nm +/- 1Nm

Mounting Torque M6: 6.0 Nm +/- 1Nm

Complies with: ISO 8820-5:2003, UL 248 Special Purpose Fuses





### **Ordering Information**

Part Number	Package Size	Housing Color	Bolt Size	Bolt Hole Oty	Mfg Location
0498xxx.M	1000	Black	M5	2	Mexico
0498xxx.M-CN	1000	Black	M5	2	China
0498xxx.H	100	Black	M5	2	Mexico
0498xxx.MXM6	1000	Black	M6	2	Mexico
0498xxx.MXM6-CN	1000	Black	M6	2	China
0498xxx.MX1M5	1000	Black	M5	1	Mexico
0498xxx.MX1M5-CN	1000	Black	M5	1	China
0498xxx.MX1M6	1000	Black	M6	1	China
0498xxx.MX1M6-CN	1000	Black	M6	1	China
0498xxx.MXT	1000	Clear	M5	2	Mexico
0498xxx.MXT-CN	1000	Clear	M5	2	China
0498xxx.MXTM6	1000	Clear	M6	2	Mexico
0498xxx.MXTM6-CN	1000	Clear	M6	2	China

<sup>\*</sup> Materials manufactured in Asia are produced to the same specifications as materials manufactured in North America, and meets the same test requirements. Multiple production locations are for capacity expanison only.

### Ratings

Part Number	Current Rating (A)	Font Color	Typ. Voltage Drop max. (mV)	Cold Resistance (mΩ)	l²t (A²s)
0498023.M <sup>2</sup>	23		90	3.43	1,800
04980302	30		65	2.06	4,200
0498040	40		65	1.398	10,000
0498050	50		65	1.025	13,000
0498060	60		68	0.865	21,700
0498070	70		70	0.72	24,000
0498080	80		58	0.541	24,600
0498100	100		60	0.457	51,300
04981252	125		71	0.394	73,200
04981501,2	150		77	0.323	81,900
04981751,2	175		77	0.285	100,000
04982001,2	200		77	0.261	125,000


Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-saving, life-saving or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.



### MIDI®, Clear MIDI®, and One Hole MIDI® Style Bolt-down Fuse Rated 32V

### **Dimensions**

Dimensions in mm




15 T							MIDI R								
10															
ns _															
05															
00															
95											_				
90															
85 ∔ 40-	-30	-20	-1	0 (	 0 2	-	30 4	0 5	_	0 7	-	0 9	0 10	00 1	10

#### "A" "B" "C" Part Number mm (inch) mm (inch) mm (inch) 0498023. 0.41 (0.016) 4.0 (0.157) 8.0 (0.315) 0498030.\_ 0.41 (0.016) 4.0 (0.157) 8.0 (0.315) 0498040.\_ 0.41 (0.016) 4.0 (0.157) 8.0 (0.315) 0498050.\_ 0.41 (0.016) 4.0 (0.157) 8.0 (0.315) 0498060.\_ 0.41 (0.016) 4.0 (0.157) 8.0 (0.315) 0498070.\_ 0.41 (0.016) 4.0 (0.157) 8.0 (0.315) 0498080.\_ 0.41 (0.016) 4.0 (0.157) 8.0 (0.315) 0498100.\_ 0.63 (0.025) 4.3 (0.169) 8.3 (0.327) 0498125.\_ 0.63 (0.025) 4.3 (0.169) 8.3 (0.327) 8.3 (0.327) 0498150.\_ 0.63 (0.025) 4.3 (0.169) 4.3 (0.169) 0498175.\_ 0.63 (0.025) 8.3 (0.327) 0498200.\_ 0.63 (0.025) 4.3 (0.169) 8.3 (0.327)

### Time-Current Characteristic Curves

Temperature Rerating Curve



Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for admages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.





**BF1 Fuses** 



One Hole BF1 Fuses

### BF1 and One-Hole BF1 Fuse Rated 32V

This BF1 fuse is rated at 32V and offers a bolt-on fuse for high current wiring protection. Current rating 23A - 200A; with transparent housing material for easy detection of blown fuses. One-Hole BF1 fuses have a current rating 60-125A.

### **Specifications**

Operating Temperature: -40 to 125 degrees C

Housing Material: PET-GF30 Clear Housing Material: PES

Terminals: Copper alloy, gal. Sn

2 x M5 or M6 bolts, distance 30 mm

Mounting Torque M5: 4.5 Nm +/- 1NmMounting Torque M6: 6.0 Nm +/- 1Nm

Interrupting Rating: 23A & 30A: 1000A @32 VDC 40A - 150A: 2000A @32 VDC

200A: 1500A @32 VDC

ISO 8820-5, UL 248 Special Purpose Fuses





### **Ordering Information**

### Time-Current Characteristics

Part Number	Package	Bolt	Bolt Hole	Ratings	% of	% of Opening Time Min /		
150 50012	Size	Size	<b>Qty</b>	20.4.200.4	Rating	23-150A Fuses	200A Short Circuit	
153.5631.xxx2	1000	M5		30A-200A			Protectors	
153.5631.xxx1	10	M5	2	30A-200A	75	-/-	360,000 s / -	
153.7010.xxx2	1000	M6	2	30A-150A	100	360,000 s / -	-/-	
153.7000.xxx2	500	M6	2	200A	110	14,400 s / -	-/-	
153.0010.xxx2	1000	M6	1	60A-125A	150	90 s / 3,600 s	-/-	
153.0020.xxx2	500		0	30A-200A	200	3 s / 100 s	1 s / 15 s	
					300	0.300 s / 3 s	-/-	
					350	-/-	0.300 s / 5 s	
					500	0.100 s / 1 s	-/-	
					600	-/-	0.100 s / 1 s	

### Ratings

Part Ni	Part Number		Housing Material Color	Typ. Voltage Drop	Cold Resistance (mΩ)	I²t (A²s)
M5	M6	(A)	Material Color	(mV)	(11152)	(A-5)
153.5631.523_1,2	-	23		105	3.50	1,400
153.5631.530_	153.7010.530_	30		105	2.70	5,100
153.5631.540_	153.7010.540_	40		90	1.56	6,800
153.5631.550_	153.7010.550_	50		80	1.03	6,900
153.5631.560_	153.7010.560_	60		75	0.75	16,200
153.5631.570_	153.7010.570_	70		70	0.64	22,000
153.5631.580_	153.7010.580_	80		70	0.55	25,600
153.5631.610_	153.7010.610_	100		70	0.44	42,500
153.5631.612_	153.7010.612_	125		70	0.34	62,500
153.5631.615_1	153.7010.615_1	150		70	0.29	83,400
153.5631.620³	153.7000.6203	200		70	0.24	126,000

Corresponding holder see Section "Fuse Holders."


Note 1: not mentioned in ISO standard Note 2: Not UL rated Note 3: Short Circuit Protector only Note 4: For 1-Hole and No-Hole values, refer to 2-Hole version values



### BF1 and One-Hole BF1 Fuse Rated 32V

### **Dimensions**


Dimensions in mm



### Derating

Individual derating curves by rating can be ordered through your Littelfuse contact person.

### **Pre-Arcing Time-Limits**



23 A - 150 A: FI = 1.25 (max. operating current:  $0.8 \times I_{rat}$  at 23°C)

200 A: FI = 2.00 (max. operating current:  $0.5 \times I_{rat}$  at  $23^{\circ}$ C)





This BF1 fuse is rated at 58V and offers a bolt-on fuse for high current wiring protection. Current rating 30A - 200A; with transparent housing material for easy detection of blown fuses.

### **Specifications**

Operating temperature: -40 to 125 degrees C

Housing Material: PET-GF30 Clear Housing Material:

BF1 Fuses Rated 58V

Terminals: Copper alloy, gal. Sn

2 x M5 or M6 bolts, distance 30 mm

Mounting Torque M5: 4.5 Nm +/- 1Nm Mounting Torque M6: 6.0 Nm +/- 1Nm Interrupting Rating: 1000A @ 58 VDC


Complies with: ISO 8820-5, UL 248 Special Purpose Fuses






### **Dimensions**

Dimensions in mm






### **Ordering Information**

Part Number	Package Size	Bolt Size	Bolt Hole Qty
142.5631.xxx2	500	M5	2
142.7010.xxx2	500	M6	2
142.7020.xxx2	500	N/A	0

### **Time-Current Characteristics**

% of	Openin	g Time Min / Max (s)
Rating	30-150A Fuses	200A Short Circuit Protectors
75	-/-	360,000 s / –
100	360,000 s / -	-/-
110	14,400 s / -	-/-
150	90 s / 3,600 s	-/-
200	3 s / 100 s	1 s / 15 s
300	0.300 s / 3 s	-/-
350	-/-	0.300 s / 5 s
500	0.100 s / 1 s	-/-
600	-/-	0.100 s / 1 s

### **Pre-Arcing Time-Limits**



30 A - 150 A: FI = 1.25 (max. operating current:0.8 x I<sub>rat</sub> at 23°C) 200 A: FI = 2.00 (max.operating current: 0.5 x I<sub>rat</sub> at 23°C)

### Ratings

Part Number M5	Part Number M6	Current Rating (A)	Housing Material Color	Typ. Voltage Drop (mV)	Cold Resistance (mΩ)	l²t (A²s)
142.5631.5302 <sup>1</sup>	142.70xx.5302 <sup>1</sup>	30		105	2.70	5,100
142.5631.5402	142.70xx.5402	40		90	1.56	6,800
142.5631.5502	142.70xx.5502	50		80	1.03	6,900
142.5631.5602	142.70xx.5602	60		75	0.75	16,200
142.5631.5702	142.70xx.5702	70		70	0.64	22,000
142.5631.5802	142.70xx.5802	80		70	0.55	25,600
142.5631.6102	142.70xx.6002	100		70	0.44	42,500
142.5631.6122	142.70xx.6122	125		70	0.34	62,500
142.5631.6152	142.70xx.6152	150		70	0.29	83,400
142.5631.6202 <sup>2</sup>	142.70xx.6202	200		70	0.24	126,000


Note 1: Not UL rated Note 2: Short Circuit Protector only

### Derating

Individual derating curves by rating can be ordered through your Littelfuse contact person.

Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse





### BF2 Fuses Rated 32V

This BF2 fuse is rated at 32V and offers a bolt-on fuse for high current wiring protection. Current rating 100A - 500A; with transparent housing material for easy detection of blown fuses.

### **Specifications**

Housing Material: PET-GF30 Clear Housing Material: PES

Terminal: Copper alloy, gal. Sn

2 x M8 bolts, Distance 51 mm

Mounting Torque: 12.0 Nm +/- 1Nm

Breaking Capacity: 100 A - 300 A: 2.000 A, 32V, DC 400 A - 500 A: 1.500 A, 32V, DC

ISO 8820-5, UL 248 Special Purpose Fuses

Complies with:

RoHS


### c**FU**®us

### Ordering Information Time Current Characteristics

Part Number	Package Size
Standard M8 Holes	
153.5395.xxxx	200
M6 Holes	
153.7011.xxxx	200

% of Rating	Opening Time Min / Max (s)					
% Of natility	100A - 250A	300A - 500A				
75	-/-	4 h / –				
100	4 h / –	-/-				
135	120 s / 1,800 s	-/-				
200	1 s / 15 s	1 s / 15 s				
350	0.300 s / 5 s	0.500 s / 5 s				
600	0.100 s / 1 s	0.100 s / 1 s				

### Time-Current Characteristic Curves




400A-500A:  $F_L$ =2,00 (max. operating current: 0,5 x  $I_{rat}$  at 23°C)

### Ratings

Part Number M8 Holes	Part Number M6 Holes	Current Rating (A)	Housing Color	Typ. Voltage Drop (mV)	Cold Resistance (m $\Omega$ )	l²t (A²s)
153.5395.610_	153.7011.610_	100		110	0.70	46,800
153.5395.612_	153.7011.612_	125		110	0.52	118,100
153.5395.615_	153.7011.615_	150		110	0.42	113,400
153.5395.617_	153.7011.617_	175		110	0.36	154,400
153.5395.620_	153.7011.620_	200		110	0.34	288,000
153.5395.622_	153.7011.622_	225		110	0.29	236,000
153.5395.625_	153.7011.625_	250		110	0.25	292,500
153.5395.630_*	153.7011.630_*	300		110	0.21	486,000
153.5395.640_*	153.7011.640_*	400		110	0.13	964,000
153.5395.650_*	153.7011.650_*	500		110	0.12	1,449,000


Last figure of article no. = packaging code
Corresponding holder see Section "Fuse Holders."
\* Parts with asterisk are short circuit protectors only.

## Dimensions Dimensions in mm



Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-saving, life-saving or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.





### **BF2 Fuses Rated 58V**

This BF2 fuse is rated at 58V and offers a bolt-on fuse for high current wiring protection. Current rating 100A - 300A; with transparent housing material for easy detection of blown fuses.

### **Specifications**

PET-GF30 Housing Material: Clear Housing Material: PES

Terminal: Copper alloy, gal. Sn

2 x M8 bolts, Distance 51 mm

12.0 Nm +/- 1Nm Mounting Torque: 1000A, 58V DC Breaking Capacity:

Complies with: ISO 8820-5, UL 248 Special Purpose Fuses






### **Ordering Information**

Part Number	Package Size
142.5395.xxxx	200

### Time Current Characteristics

% of Rating	Opening Time Min / Max (s)					
% of nating	100A - 250A	300A				
75	-/-	-/-				
100	4 h / –	4 h / –				
135	120 s / 1,800 s	-/-				
200	1 s / 15 s	1 s / 15 s				
350	0.300 s / 5 s	0.500 s / 5 s				
600	0.100 s / 1 s	0.100 s / 1 s				

### Time-Current Characteristic Curves




100A-300A: F<sub>L</sub>=1,25 (max. operating current: 0,8 x I<sub>rat</sub> at 23°C) 400A-500A: F<sub>L</sub>=2,00 (max. operating current: 0,5 x I<sub>rat</sub> at 23°C)

### Ratings

Part Number	Current Rating (A)	Housing Color	Typ. Voltage Drop (mV)	Cold Resistance (m $\Omega$ )	l²t (A²s)
142.5395.6102	100		110	0.70	46,800
142.5395.6122	125		110	0.52	118,100
142.5395.6152	150		110	0.42	113,400
142.5395.6172	175		110	0.36	154,400
142.5395.6202	200		110	0.34	288,000
142.5395.6222	225		110	0.29	236,000
142.5395.6252	250		110	0.25	292,500
142.5395.6302 <sup>1</sup>	300		110	0.21	486,000

### **Dimensions**

Dimensions in mm



Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse





**CF Fuses** 

#### CF Fuses Rated 58V from 50A-300A

Main Fuse for mounting with battery clamp on the battery pole with transparent cover material for visual inspection of melting element.

#### **Specifications**

Ratings up to 125A

Operating Temperature Range: -40°C to +105°C Terminals: Sn plated zinc alloy

Ratings higher than 125A

Operating Temperature Range: -40°C to +125°C Terminals: Sn plated copper alloy

Insulating Body Material: Ceramic Cover Material:

Visible melting-element

Interrupting Rating: 2,000A @58VDC

Complies with: ISO 8820-6, DIN 72581-5, UL 248 Special Purpose Fuses

cULus Recognized: File No. E211637

c RoHS

#### **Ordering Information**

#### **Time-Current Characteristics**


Part Number	Package Size	% of Rating	Opening Time Min / Max (s)
155.0892.xxx1	100	100	360,000 s / -
·		135	− / 3,600 s
		150	1 s / 600 s
		200	0.200 s / 60 s
		300	0.050 s / 1.5 s
		400	0.020 s / 0.50 s
Ratings		600	- / 0.20 s


Part Number	Current Rating (A)	Typ. Voltage Drop (mV)	Cold Resistance (m $\Omega$ )	l²t (A²s)
155.0892.5501	50	100	1.20	1,900
155.0892.5751	75	90	0.60	12,000
155.0892.6101	100	80	0.60	14,000
155.0892.6121	125	75	0.45	51,000
155.0892.6151	150	70	0.35	63,800
155.0892.6171	175	70	0.25	120,000
155.0892.6201	200	65	0.25	172,800
155.0892.6251	250	70	0.20	330,000
155.0892.6301	300	70	0.15	372,000

Insert CF8-Fuse links only in conjunction with the insulating nuts, see Section "Fuse Holders." Corresponding battery clamp see Section "Fuse Holders."


#### **Dimensions**

Dimensions in mm





### **Pre-Arcing Time-Limits**



FI = 1.25 (max. operating current: 0.8 x Irat at 23°C)

Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse





# Fuse Strips with Housing Rated 36V - SPECIAL PURPOSE FUSES (NOT INTENDED FOR AUTOMOTIVE or TRUCK APPLICATIONS)

Housed fuse strips with window for visual inspection of melting element. Current rating 30A - 150A, 36 VDC. 90° fork type lugs.

#### **Specifications**

Voltage Rating: 36 VDC
Interrupt Ratings: up to 375A
Operating Temperature Range: -40° to 125°C
Insulating Body: Out of ceramic
Metal Parts: Zinc-alloy
Complies with: DIN 72581/2

### RoHS

#### **Ordering Information**

Part Number	Package Size
156.5611.xxx1	50

#### **Time-Current Characteristics**

% of Rating	Opening Time Min / Max (s)
130	3,600 s / -
250	-/60 s


#### Ratings

Part Number	Current Rating (A)*	Typ. Voltage Drop (mV)	Material Thickness "S" (mm)
156.5611.5301	30	70	0.25
156.5611.5401	40	70	0.20
156.5611.5501	50	70	0.25
156.5611.5601	60	70	0.40
156.5611.5701	70	70	0.45
156.5611.5801	80	70	0.50
156.5611.6101	100	70	0.70
156.5611.6111	120	70	0.70
156.5611.6121	125	70	0.70
156.5611.6151	150	70	1.00


Corresponding holder see Section "Fuse Holders."

#### **Dimensions**

Dimensions in mm



#### **Pre-Arcing Time-Limits**



FI = 1.00 (max. operating current : 1.0 x I<sub>rat</sub> at 23°C)

Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.

<sup>\*</sup>Metal parts in compliance with DIN 72581/2. Fuses with housings not mentioned in the standards.





# Fuse Strips Rated 48V - SPECIAL PURPOSE FUSES (NOT INTENDED FOR AUTOMOTIVE OR TRUCK APPLICATIONS)

Non-housed fuse strips for battery powered fuses rated at 48VDC.  $90^{\circ}$  and straight fork type lugs.

#### **Specifications**

Voltage Rating: 48 VDC
Interrupt Ratings: up to 3000A
Operating Temperature Range: - 40° to 125°C
Metal Parts: 35 A - 80 A: Zinc-alloy

100A - 500 A: Copper Cu, gal. Sn

Complies with: DIN 43560-1

### RoHS


#### **Ordering Information**

# Part Number Package Size 157.5700.xxx1 50 157.5916.xxx1 50


#### Time-Current Characteristics

% of Rating	Opening Time N	/lin / Max (s)	
	35-200	225 - 500	
150	3,600 s / -	-/-	
160	-/-	60 s / –	
220	-/60 s		
250	0.8 s / 10 s		
400	0.20 /	2 s	

### **Dimensions**Dimensions in mm



#### **Pre-Arcing Time-Limits**



FI = 1.00 (max. operating current:1.0 x  $I_{rat}$  at 23°C)

#### Ratings

Part Number		Current Rating	Typ. Voltage Drop	Breaking Capacity (VDC/A)	Material Thickness "S"
a = 11 mm	a = 9 mm*	(A)	(mV)	(,,	(mm)
157.5700.5351	157.5916.5351	35	125	48/210	0.6
157.5700.5401	-	40	125	48/240	0.6
157.5700.5501	157.5916.5501	50	125	48/300	0.6
157.5700.5631	157.5916.5631	63	125	48/378	0.6
157.5700.5801	157.5916.5801	80	125	48/480	0.6
157.5700.6101	157.5916.6101	100	125	48/600	0.5
157.5700.6121	157.5916.6121	125	125	48/750	0.8
157.5700.6131	157.5916.6131	130	125	48/780	0.8
157.5700.6141	_	135	125	48/810	0.8
157.5700.6151	-	150	125	48/900	0.8
157.5700.6161	157.5916.6161	160	125	48/960	1.0
157.5700.6171	-	175	125	48/1050	1.0
157.5700.6201	157.5916.6201	200	125	48/1200	0.8
157.5700.6231	-	225	125	48/1350	0.5
157.5700.6251	157.5916.6251	250	125	48/1500	0.5
157.5700.6271	-	275	125	48/1650	0.8
157.5700.6301	_	300	125	48/1800	0.8
157.5700.6331	-	325	125	48/1950	0.8
157.5700.6351	_	355	125	48/2130	0.8
157.5700.6401	-	400	125	48/2400	0.8
157.5700.6421	_	425	125	48/2550	1.0
157.5700.6501	-	500	125	48/3000	1.0

Corresponding holders = 177.5701.0001 and 177.5702.0001."

Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-saving, life-saving or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.





#### Fuse Strips with Housing Rated 48V - SPECIAL PURPOSE FUSES (NOT INTENDED FOR AUTOMOTIVE OR TRUCK APPLICATIONS)

Housed fuse strips for battery-powered vehicles. Current rating 35A - 500A, 48 VDC. 90° and straight fork type lugs. With window for visual inspection of melting element.

#### **Specifications**

Voltage Rating: 48 VDC Interrupt Ratings: up to 3000A Operating Temperature Range: -40° to 125°C Metal Parts: 35A - 80A: Zinc-alloy

100A - 500A: Copper Cu, gal. Sn Complies with: UL 248 Special Purpose Fuses

cULus Recognized: File No. E211637





#### **Ordering Information**

Part Number	Package Size
157.5701.xxx1	50
157.5917.xxx1	50

#### **Time-Current Characteristics**

% of Rating	Opening Time Min / Max (s)			
	35-200	225 - 500		
150	3,600 s/-	-/-		
160	-/-	60 s / –		
220	- / 60 s			
250	0.8 s / 10 s			
400	0.	.20 / 2 s		

### Glass Cover **Pre-Arcing Time-Limits**

**Dimensions** Dimensions in mm

1000	*****		
)W-		445 444 454	
18 - III			
1	//		
8.5	200	5000	Ш,

FI = 1.00 (max. operating current: 1.0 x I<sub>rat</sub> at 23°C)

#### Ratings

Part Number		Current Rating	Typ. Voltage Drop	Breaking Capacity	Material Thickness "S"
a = 11 mm	a = 9 mm*	(A)	(mV)	(VDC/A)	(mm)
157.5701.5351	157.5917.5351	35	125	48/210	0.6
157.5701.5401	-	40	125	48/240	0.6
157.5701.5501	157.5917.5501	50	125	48/300	0.6
157.5701.5631	157.5917.5631	63	125	48/378	0.6
157.5701.5801	157.5917.5801	80	125	48/480	0.6
157.5701.6101	157.5917.6101	100	125	48/600	0.5
157.5701.6121	157.5917.6121	125	125	48/750	0.8
157.5701.6131	-	130	125	48/780	0.8
157.5701.6141	_	135	125	48/810	0.8
157.5701.6151	157.5917.6151	150	125	48/900	0.8
157.5701.6161	157.5917.6161	160	125	48/960	1.0
157.5701.6171	157.5917.6171	175	125	48/1050	1.0
157.5701.6201	157.5917.6201	200	125	48/1200	0.8
157.5701.6231	157.5917.6231	225	125	48/1350	0.5
157.5701.6251	157.5917.6251	250	125	48/1500	0.5
157.5701.6271	157.5917.6281	275	125	48/1650	0.8
157.5701.6301	_	300	125	48/1800	0.8
157.5701.6331	157.5917.6331	325	125	48/1950	0.8
157.5701.6351	157.5917.6351	355	125	48/2130	0.8
157.5701.6401		400	125	48/2400	0.8
157.5701.6421	157.5917.6421	425	125	48/2550	1.0
157.5701.6501	157.5917.6501	500	125	48/3000	1.0

Corresponding holder see Section "Fuse Holders."

Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse





#### **HSB Fuses Rated 32V**

Non-housed fuse strips for rated voltage up to 32 VDC. Current rating 30 A -175 A. Ring type lugs.

#### **Specifications**

Voltage Rating: 32 VDC
Interrupt Ratings: 1000A
Operating Temperature Range: -40° to 125°C
Material: Zinc-alloy
Connections: Zinc-alloy

2 x M6 bolts, distance 30 mm

Torque: 4 Nm +/- 1 Nm

#### RoHS

#### **Ordering Information**

Part Number	Package Size
156.5677.xxx1	100
156.5677.xxx2	10000

#### Time-Current Characteristics


% of Rating	Opening Time Min / Max (s)
100	∞ / –
125	360,000 s / -
300	0.100 s / 10 s
600	0.020 s / 1 s
1000	0.010 s / 0.300 s

#### Ratings


Part Number	Current Rating (A)	Typ. Voltage Drop (mV)	Cold Resistance (mΩ)	l²t (A²s)	Material Thickness "S" (mm)
156.5677.530_	30	44	1.33	3800	0.4
156.5677.540_	40	40	0.89	11200	0.4
156.5677.550_	50	44	0.72	21300	0.4
156.5677.560_	60	38	0.58	41400	0.4
156.5677.580_	80	40	0.43	44800	0.8
156.5677.611_	110	40	0.31	139000	0.8
156.5677.615_	150	52	0.23	465000	0.8
156.5677.617_	175	46	0.22	560000	0.8

#### **Dimensions**

Dimensions in mm



### Pre-Arcing Time-Limits



FI = 1.00 (max. operating current: 1.0 x  $I_{rat}$  at 23°C)

Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-saving, life-saving or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.





# Fuse Strips with Rated 36V - SPECIAL PURPOSE FUSES (NOT INTENDED FOR AUTOMOTIVE OR TRUCK APPLICATIONS)

Non-housed fuse strips for Diesel vehicles. Current rating 25A - 150A, 36 VDC. 90° fork type lugs.

#### **Specifications**

Voltage Rating: 36 VDC
Interrupt Ratings up to 625A
Operating Temperature Range: -40° to 125°C
Material: Zinc-alloy
Complies with: DIN 72581/2

### RoHS

#### **Ordering Information**

#### **Time-Current Characteristics**

Part Number	Package Size	% of Rating	Opening Time Min / Max (s)
156.5610.xxx1	100	130	3,600 s / -
156.5610.xxx2	2000	250	-/60 s


#### Ratings

Part Number	Current Rating (A)	Typ. Voltage Drop (mV)	Material Thickness "S" (mm)
156.5610.525_	25*	70	0.20
156.5610.530_	30	70	0.25
156.5610.540_	40*	70	0.20
156.5610.550_	50	70	0.25
156.5610.560_	60*	70	0.40
156.5610.570_	70*	70	0.45
156.5610.580_	80	70	0.50
156.5610.610_	100	70	0.70
156.5610.611_	120*	70	0.70
156.5610.612_	125*	70	0.70
156.5610.615_	150*	70	1.00
156.5610.625_	250*	70	2.00


<sup>\*</sup>Not mentioned in the standards Corresponding holder see Section "Fuse Holders."

#### **Dimensions**

Dimensions in mm



### Pre-arcing Time-limits




FI = 1.00 (max. operating current:  $1.0 \times I_{rat}$  at 23°C)

Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-saving, life-saving or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.



# Cable/PAL Fuses

BF-Inline Fuses Rated 32V	40
CABLEPRO® Cable Protector Fuses Rated 32V	41
PAL Fuses	42







#### **BF-Inline Fuse Rated 32V**

Inline fuse to protect specific cable cross-sections and insulations; Cross-section 10mm² to 35mm². For rated voltage up to 32 VDC.

Assembly notes: The wire integrated fuse has to be insulated by using a self-adhesive shrinking tube. The wire has to be fixed on both sides of the fuse to minimize the wire forces. Recommended shrinking tube: DERAY(R)-IAKT 4:1, 24mm

#### **Specifications**

Voltage Rating: 32 VDC
Housing Material: PETGF30
Insulating Housing Matierial: PAGF30

Terminals: Crimp, Copper alloy, tinned

Interrupting Rating: 2000A @32VDC

#### **Ordering Information**

Part Number	Package Size
153.0000	300

#### Time-Current Characteristics 100A-190A


#### Time-Current Characteristics 300A


% of Rating	Opening Time Min / Max (s)		% of Rating	Opening Time M	lin / Max (s)
100	360,000 s	_	75	360,000 s	_
150	90 s	1800 s	165	10 s	100 s
200	3 s	240 s	200	1 s	15 s
300	0.3 s	60 s	350	0.3 s	5 s
500	0.1 s	10 s	500	0.1 s	1 s

#### Ratings

Part Number	Current Rating (A)	Wire Size/Type/ Marking	Typ. Voltage Drop (mV)	Cold Resistance $(m\Omega)$	l²t (A²s)
153.1002	100	10mm <sup>2</sup> /FLY/P	60	0.42	27,000
153.1012	125	10mm <sup>2</sup> /FL2G/S	70	0.32	87,500
153.1602	125	16mm <sup>2</sup> /FLY/P	75	0.41	29,600
153.1612	170	16mm²/FL2G/S	60	0.22	248,000
153.2502	170	25mm <sup>2</sup> /FLY/P	70	0.29	78,500
153.2512	190	25mm <sup>2</sup> /FL2G/S	52	0.22	248,000
153.3502	300	35mm <sup>2</sup> /FLY/P	70	0.20	373.000







Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-saving, life-saving or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.

### Cable Fuses





#### CABLEPRO® Cable Protector Fuses Rated 32V

#### Available in AWG and metric cables

The CABLEPRO® fuse is designed to replace conventional wire fusible links in high current automotive applications. The slim package of the CABLEPRO® and the predictable and reliable performance characteristics (similar to MEGA® fuse) make this far superior over wire fusible links. Interrupting rating 2000A @ 32 VDC.CablePro is not a sealed product. To seal it a shrink tube should be used.

#### **Specifications**

Voltage Rating: 32V

Interrupting rating: 2000A @ 32 VDC Housing Material: PPAGF33HS Operating Temperature Range:  $-40^{\circ}$ C to  $+125^{\circ}$ C

Cable Types Available: SAE J1127 SXT, SAE J1128 TXL, ISO 6722: Type FL2G
Operating Temperature Range: -40°C to +150°C - Optional for 150A, 175A and 200A ratings

Cable Type: Thin wall irradiated XLPE (SAE 4GA)

Available with UL recognized in 60, 100, 150 & 200 at 32V (UL not available with the thin wall irradiated XLPE SAE 4GA cable)








293 Series Auto Link PAL 293 Series Fuse Amps (A): 20, 30, 40, 50, 60, 70, 80, 100




2935 Series Auto Link PAL 2935 Series Fuse Amps (A): 25, 30, 45, 65, 75




2938 Series Auto Link PAL 2938 Series Fuse Amps (A): 20, 30, 40, 50, 60, 70, 80



294 Series Auto Link PAL 294 Series Fuse Amps (A): 30, 40, 50, 60, 70, 80, 100, 120




294C Series Auto Link PAL 294C Series Fuse Amps (A): 20, 30, 40, 50, 60, 70, 80, 100, 120



295 Series Auto Link PAL 295 Series Fuse Amps (A): 20, 30, 40, 50, 60, 70, 80, 100, 120,



283B Series Auto Link PAL 283B Series Fuse Amps (A): 20, 30, 40, 50, 60, 70, 80, 100, 120, 140




283 Series Auto Link PAL 283 Series Fuse Amps (A): 20, 30, 40, 50, 60, 70, 80, 100, 120, 140



LC High Voltage Fuse	44









Low Current HEV Fuses



0HEV040.ZXBD

#### Low Current HEV Fuse

The LC HEV fuse is designed for protection of high-voltage accessory circuits in electric and hybrid electric vehicles.

#### **Specifications**

Voltage Rating (10A, 15A, 20A, 30A): 450 VDC Voltage Rating (40A): 425 VDC

Note: The OHEV040.ZXBD is rated at 450 VDC

#### **Ordering Information**

#### **Time-Current Characteristics**


			Timo darront dilatadente locale				
Part Number Termination		Package Size	% of Rating Opening Time Min / Max (s)		Opening Time Min / Max (s)	Opening Time Min / Max (s	
0HEVxxx.ZXC	Cartridge	240	10A		15A, 20A, 30A	40A	
0HEVxxx.ZXIS0	Bolt Down (ISO)	240	100	100 hrs / -	100 hrs / -	100 hrs / -	
OHEVxxx.ZXPY	Blade	240	110	4 hrs / -	4 hrs / -	-	
0HEVxxx.ZXBD	Bolt Down (Axial)	240	135	100 / 3600	150 / 3600	150 / 3600	
			150	10 / 1000	10 / 1000	10 / 1000	
OHEVxxx.ZXPCB	PCB Mount	240	200	0.5 / 100	0.5 / 100	0.5 / 100	
OHEVxxx.ZXPCBL	PCB Mount (Long)	240	300	0.1 / 15	0.1 / 15	0.1 / 15	
			500	0.05 / 1	0.05 / 1	0.05 / 1	

#### Ratings


Part Number	Current Rating (A)	Color Code	Typical Voltage Drop at 70% I <sub>R</sub> (mV)	Maximum Voltage Drop Spec at 100% IR (mV)	Typical Cold Resistance $(m\Omega)$	Minimum Melting l²t (A²s)
0HEV010.xxx	10		114	300	12.8	255
0HEV015.xxx	15		96	200	7.9	133
0HEV020.xxx	20		79	200	5.0	268
0HEV030.xxx	30		67	200	2.7	993
0HEV040.xxx	40		69	200	2.0	1495

(Average Initial Measurements)

#### Time-Current Characteristic Curves



#### Temperature Rerating Curve



Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-saving, life-saving or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.



#### Low Current HEV Fuse

#### **Dimensions**

Dimensions in mm


#### **ZXC** Cartridge









#### ZXISO Bolt Down (ISO)




#### **ZXPY Blade**




#### ZXBD Bolt Down (Axial)



#### ZXPCB PCB Mount



#### **ZXPCBL PCB Mount (Long)**



Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.





Low Current High Voltage 50A Fuses

#### Low Current High Voltage 50A Fuse

The LC HEV fuse is designed for protection of high-voltage accessory circuits in electric and hybrid electric vehicles.

#### **Specifications**

Voltage Rating (50A): 275 VAC

 $\label{eq:continuity} \begin{array}{ll} \text{Interrupting Rating (50A):} & 10,000A @ 275 \text{ VAC} \\ \text{Operating Temperature Range:} & -40^{\circ}\text{C to } +125^{\circ}\text{C} \end{array}$ 

#### **Ordering Information**

	•		
	Part Number	Termination	Package Size
	0HEVxxx.ZXC2	Cartridge	240
	0HEVxxx.ZXIS02	Bolt Down (ISO)	240
	0HEVxxx.ZXP2Y	Blade	240
	0HEVxxx.ZXPCB2	PCB Mount	240
	0HEVxxx.ZXPCBL2	PCB Mount (Long)	240
	0HEVxxx.ZXBD2	Bolt Down (Axial)	240


#### **Time-Current Characteristics**

% of Rating	Opening Time Min / Max (s)
100	100 hrs / -
110	4 hrs / -
135	-
150	-
200	0.5 / 100
300	0.1 / 15
500	0.05 / 1


#### Ratings

Part Number	Current Rating (A)	Voltage Rating (VAC)	Color Code	Typical Voltage Drop at 70% I <sub>R</sub> (mV)	Maximum Voltage Drop Spec at 100% I <sub>R</sub> (mV)	Typical Cold Resistance $(m\Omega)$	Minimum Melting I²t (A²s)
OHEV050.XXX	50	275		57	200	1.2	1495

#### Time-Current Characteristic Curves



#### Temperature Rerating Curve



Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.



### Low Current High Voltage 50A Fuse


#### **Dimensions**

Dimensions in mm


#### ZXC2 Cartridge




#### ZXIS02 Bolt Down (IS0)




#### ZXP2Y Blade




#### ZXPCB2 PCB Mount



#### ZXPCBL2 PCB Mount (Long)



#### ZXBD2 Bolt Down (Axial)



Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.


7



# **Specialty Products**

Shunts

49



### **Specialty Products**



#### SHUNTS

#### ATO® Shunt



Operating Temp.: -40°C to +125°C
Maximum Continuous Load Rating: 35A\*
Housing Material: Thermoplastic
(UL 94V0 Rated)

Terminal Material: Brass Tin Plated

#### MINI® Shunt



Operating Temp.:  $-40^{\circ}\text{C}$  to  $+125^{\circ}\text{C}$  Maximum Continuous Load Rating:  $20A^{*}$  Housing Material: Thermoplastic

(UL 94V0 Rated)
Terminal Material: Zinc Silver Plated

#### MICRO2® Shunt



Operating Temp.: -40°C to +125°C Maximum Continuous Load Rating: 20A\*

Housing Material: PA66

Terminal Material: Ag plated zinc alloy

#### MICRO3® Shunt



Operating Temp.: -40°C to +125°C Maximum Continuous Load Rating: 15A\*

Housing Material: PA66

Terminal Material: Ag plated zinc alloy

#### JCASE® Shunt



Operating Temp.:  $-40^{\circ}\text{C}$  to  $+125^{\circ}\text{C}$  Maximum Continuous Load Rating:  $50\text{A}^*$ 

Housing Material: PA66
Terminal Material: Copper

#### MCASE+® Shunt



Operating Temp.: -40°C to +125°C

Maximum Continuous Load Rating Unslotted: 30A\*
Maximum Continuous Load Rating Slotted: 50A\*
Housing Material: PPA (33% / 35% GF)

Terminal Material: Copper

Part Number	Туре	Max Continuous Load Rating* (A)	Housing Material	Terminal Material	Part Quantity
02400094P	AT0	35	Thermoplastic (UL 94V0)	Brass Tin Plated	2000
0297900.WXNV	MINI	20	Thermoplastic (UL 94V0)	Zinc Silver Plated	3000
0327900.YX2S	MICRO2	20	PA66	Zinc Silver Plated	4000
0337900.PX2S	MICR03	15	PA66	Zinc Silver Plated	2000
0495900_	JCASE	50	PA66	Copper	Z=2200 pcs/X=1 pc
0695900.PXP	MCASE+ Unslotted	30	PPA (33%/35% GF)	Copper	2000
0695900.PXPS	MCASE+ Slotted	50	PPA (33%/35% GF)	Copper	2000

\*Rating varies based on mating terminal performance



#### I. Introduction

The purpose of this Fuseology section is to promote a better understanding of fuses and some of the more common application details. The fuses to be considered are current-sensitive devices which are designed as the intentional weak link in the electrical circuit. The function of a fuse is to provide discrete component or complete circuit protection by reliably melting under overcurrent conditions and thus safely interrupting the flow of current.

#### **II. Types of Overcurrents**

An overcurrent is any current which exceeds the ampere rating of wiring, equipment or devices under conditions of use. The term "overcurrent" includes both overloads and short circuits.

#### A. Overloads

An overload is an overcurrent which is confined to normal current paths. An overload occurs when the current exceeds the value for which the wires or equipment are rated. This can happen when too many devices are connected to the circuit, or when a device connected to the circuit malfunctions in a way that causes it to draw higher than normal current, usually in the range of one to six times normal current. Sustained overloads eventually overheat circuit components. Therefore, fuses must open circuits experiencing sustained overloads before damage occurs.

#### **B. Short Circuits**

A short circuit is current out of its normal path. It occurs when accident or malfunction creates an unintended path for the electricity to flow from the battery or alternator to ground. This shorter, more direct path to ground bypasses the resistance normally offered by the wiring and devices connected to the circuit. With virtually no resistance left to impede current flow, the voltage forces higher and higher current to flow through the wires to the point of the short. Under such a condition, the current will quickly build to such a high level that the heat generated can cause insulation to burn and equipment to be damaged unless the circuit is opened through the use of a fuse.

#### **III. Fuse Selection Parameters**

Since overcurrent protection is crucial to reliable electrical system operation and safety, fuse selection and application should be carefully considered. When selecting fuses, the following parameters should be evaluated:

#### A. Voltage Rating

The voltage rating, as marked on a fuse, indicates the maximum voltage of the circuit for which the fuse is designed to operate safely in the event of an overcurrent. Therefore, the fuse's voltage rating must equal or exceed the available circuit voltage where the fuse will be installed. System voltage exceeding the fuse's rated voltage may result in fuse damage. The voltage rating is 32 volts DC for the MINI®, MAXI®, ATO®, MIDI®, MEGA®, and CABLEPRO® Fuses.

#### **B. Interrupting Rating**

The interrupting rating (also known as breaking capacity or short circuit rating) is the maximum current, as stated by the manufacturer, which the fuse can safely interrupt at rated voltage. During a fault or short circuit condition, a fuse may receive an instantaneous current many times greater than its normal operating current. Safe operation requires that the fuse remain intact (no body rupture) and clear the circuit. The interrupting rating is 1000A @ 32 volts DC for the MINI®, MAXI®, ATO®, JCASE®, and MIDI® Fuses, and 2000A @ 32 volts DC for the MEGA® and CABLEPRO® Fuses.

#### C. Time-Current Characteristics

A fuse's time-current characteristics determine how fast it responds to different overcurrents. All fuses have inverse time-current characteristics, so opening time decreases as overcurrents increase. Time-current characteristics are presented graphically on standardized "log-log" paper. Figure 1 is a sample time-current curve for the MAXI Fuse series for fuses rated 20-60A. Current values increase from left to right, and time increases from bottom to top. The average melting time for any current can be determined from the curve. For example, from Figure 1 it can be determined that a 20A MAXI Fuse experiencing an overload of 100A will open in about 0.5 seconds. At 40A, the same 20A MAXI Fuse would open in about 9 seconds.

Time-current curves are also used to compare fuses of the same series but of different current ratings. Suppose it was desired to compare the opening times of 20A and 60A MAXI Fuses at an overload of 100A. From the curve in Figure 1, one can see that the 20A fuse opens in about 0.5 seconds at 100 amps, whereas the 60A fuse does not open until about 50 seconds.






Figure 1: Average Melting-Current Curve for the MAXI Fuse Series (20-60A)

Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-saving, life-saving or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.

50



It is important to note that time-current curves give only average melting times and are presented as a design aid but are not considered as part of the fuse specifications.

The term used in fuse design that describes how rapidly a fuse responds to various overcurrents is the fuse's "characteristics." Automotive fuse characteristics are determined by the fuse's degree of time delay. Initial or start-up pulses are normal for many automotive applications and require fuses to have a time delay designed in to enable them to survive these pulses and still provide protection against prolonged overloads. Fuses such as the MINI® Fuse and ATO® Fuse have a moderate degree of time delay, whereas fuses like the MAXI® Fuse and MEGA® Fuse have a high degree of time delay which enables them to handle high inrush currents like those caused by motor start-ups. Figure 2 compares sample time-current curves of a 30A MINI Fuse to a 30A MAXI Fuse. To see that the MAXI Fuse has more time delay than the MINI Fuse, compare their opening times at an overload of 100A. Despite the fact that the fuses are the same rating, the MINI Fuse opens in about 0.1 seconds while the MAXI Fuse opens in about 2.2 seconds.

When selecting a fuse, the start-up pulse should be defined and then compared to the time-current curve for the fuse.




Figure 2: Average Melting-Current Curve Comparing 30A MINI Fuse to 30A MAXI Fuse

#### D. Current Rating

The current rating is the maximum current which the fuse can continuously carry under specified conditions.

#### 1. Normal Operating Current

The current rating of a fuse is typically derated 25% for operation at 25°C to avoid nuisance blowing. For example, a fuse with a current rating of 10A is not

usually recommended for operation at more than 7.5A in a 25°C ambient.

#### 2. Rerating for Ambient Temperature

The current carrying capacity tests of fuses are performed

at 25°C & will be affected by changes in ambient temperature.

At higher ambient temperatures, a fuse will respond faster to a given overload. Conversely, at lower ambient temperatures, a fuse will respond slower to a given overload. In addition, the temperature of the fuse increases as the normal operating current approaches or exceeds the rating of the fuse.

A MINI Fuse operating at 25°C and 110% of rated current has a minimum life of 100 hours. However, if that same fuse were operated at a very high ambient temperature, rerating would be necessary. Figure 3 is a sample temperature rerating curve for the MINI Fuse. The following example shows how to use such a curve.

Suppose there is a normal operating current of 15 amperes in a particular circuit, and the ambient temperature will be 105°C instead of 25°C. Which MINI Fuse rating should be used? From Figure 3, the percent of rated current to be used at an ambient temperature of 105°C is 88%, so:

Ideal fuse rating =  $\frac{\text{Normal operating current}}{\text{Temp rerating factor x 0.75}}$ 

<u>15A</u> 0.88 x 0.75

= 22.73A

Therefore, a 25A or larger MINI Fuse should be used.

#### **E. Transient Overcurrent Considerations**




Figure 3: MINI Auto Fuse 297 Series Temperature Rerating Curve

Transient pulses of inrush current are commonplace in vehicle electrical systems. The transient overcurrent pulses affect the life of automotive fuses.

Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-saving, life-saving or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.

51

### Fuseology



#### 1. I2t

I2t is an expression of the available thermal energy resulting from current flow. With regard to fuses, the term is usually expressed as melting, arcing, and total clearing I2t. The units for I2t are expressed in ampere-squared-seconds [A2s].

Melting 12t: the thermal energy required to melt a specific fuse element.

Arcing l2t: the thermal energy passed by a fuse during the arcing time. The magnitude of arcing  $l^2t$  is a function of the available voltage and stored energy in the circuit.

Total Clearing 12t: the thermal energy through the fuse from overcurrent inception until current is completely interrupted. Total clearing  $I^2t = (\text{melting } I^2t) + (\text{arcing } I^2t)$ .

I<sup>2</sup>t has two important applications to fuse selection. The first is pulse cycle withstand capability and the second is selective coordination.

#### 2. Pulse Cycle Withstand Capability

Electrical pulses produce thermal cycling and possible mechanical fatigue that could affect the life of the fuse.

For this reason, it is important to know the pulse cycle withstand capability of the fuse, which is defined as the number of pulses of a given I2t value that can be withstood by the fuse without opening, assuming that there is sufficient cool down time between pulses.


**FUNCTION AND VALUE WAVESHAPE** 

Square



i = k $1^{2}t = i_{c}^{2}t$ 

Trapezoidal



Sine

 $i = i_C \sin t$  $I^2t = (1/2)i_C^2t$ 

Triangular



i = + kt $I^2t = (1/3)i_C^2t$ 

Second order power



 $i = kt^2$  $I^2t = (1/5)i_0^2t$ 

Natural decay to zero



 $i = i_C e - t/\tau$  $I^2t = (1/2)i_{C^2}$ 

Natural decay to non-zero value




Figure 4: Evaluating the I2t of a Variety of Current Wave Shapes

Figure 4 shows how I2t of the pulse can be calculated from the graph of the pulse current as a function of time.

Figure 5 is a graph of the pulse cycle withstand capability of blade fuses. Because electrical pulse conditions can vary considerably from one application to another, application testing is recommended to establish the ability of the fuse design to withstand the pulse condition.




Figure 5: Pulse Cycle Withstand Capability for Blade Fuses

#### 3. Selective Coordination

In a selectively coordinated system, only the fuse immediately on the line side of an overcurrent opens. Upstream fuses remain closed and undamaged. All other equipment remains in service, which simplifies locating overloaded equipment or short circuits. In Figure 6, if a short circuit arises behind fuse #1, fuse #1 should open and fuse #2 should stay closed and undamaged. The condition necessary to assure this result is that the minimum melting I<sup>2</sup>t of the supply side fuse (fuse #2) must be greater than the total clearing I<sup>2</sup>t of the load side fuse (fuse #1). This condition results in the load side fuse opening before the supply side fuse begins to melt. Minimum melting and total clearing I2t data are given in this catalog.




Figure 6: Selective Coordination for Fuses in Series

Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse

52



#### IV. Voltage Drop Across Terminals

A fuse is only as good as the system in which it is used. One aspect of the electrical system that has considerable effects on the performance of the fuse is the quality of the connection between the fuse and the cable it protects. High voltage drop across the fuse/terminal interface creates additional thermal loading, which in turn causes shifts in the time-current characteristics of the fuse. Table 1 below gives the maximum recommended voltage drop per terminal for automotive fuses. Figure 7 indicates the measurement locations used to determine the voltage drop across the terminal. The voltage drop across the left terminal would be  $\rm V_{2-4}$  and the voltage drop across the right terminal would be  $\rm V_{1-3-4}$ 

Туре	Maximum Recommended Voltage Drop Per Terminal [MV] (between points 1-3 or 2-4)
ATO® FUSE	30
MINI® FUSE	30
MAXI® FUSE	30
MEGA® FUSE	15

Table 1: Maximum Recommended Voltage Drop per Terminal




Figure 7: Measurement Locations along the Fuse/Terminal/Cable System Used to Determaine the Voltage Drop across the Terminal

#### V. Diffusion

Diffusion Pill Technology is a mixing of molecules, atoms or crystals in the solid, liquid or gaseous state. Diffusion Pill Technology is often used in the design of fuses for automotive, electronic and industrial fuse applications.

"M-effect" is the method of diffusing one metal into another to form a new alloy with a lower melting point. Littelfuse uses the "M-effect" to produce three very desirable characteristics in fuse designs: lower melting temperature, time delay, and lower voltage drop.

By affixing a diffusion pill tin to the element, the melting temperature is decreased. This decrease in melting temperature reduces the fuse rating. In order to reestablish its original rating the fuse elements' cross section needs to increase. An increase in cross section increases the blow time at higher overload condition. A higher degree of time delay enables a fuse to withstand higher current inrush pulses. This increase in cross section reduces the overall fuse resistance and voltage drop.

#### VI. Match Wire Gauge to Fuse

In order to protect wiring under all overload and short circuit conditions, it is necessary to standardize the fuse and wire selection process.

Fuses have controlled opening characteristics, and each wire gauge has its respective current carrying capacity. Fuses need to be selected to always protect the wire insulation from damage.

In the selection of wire gauge at various ambient temperatures, it is important to consider the worst case or highest ambient temperature for the application. Wires derate to a much higher degree than fuses, because wire insulation temperature capability is affected much more severely.

#### **Maximum Recommended Continuous Current**

Wire Size		Max Continuous Current (A)				
VVIIC	VVII & SIZE		At 25°C		At 80°C	
mm²	Gage No.	GXL (1)	GPT (2)	GXL (1)	GPT (2)	GXL (1)
0.3		15	10	11	4	9
0.5	20	21	15	16	6	13
0.75		27	21	20	7	17
0.8	18	31	22	23	7	19
1	16	33	23	25	9	20
1.5		43	30	33	12	27
2	14	50	36	37	14	32
2.5		60	42	45	15	38
3	12	68	47	51	18	42
4		80	56	61	22	50
5	10	90	65	68	23	58
6		103	73	78	28	64
8	8	125	87	96	30	79
10		146	103	111	40	90
13	6	170	120	129	47	105
19	4	221	156	166	61	137

<sup>(1) =</sup> General purpose cross link polyethylene insulation wire with a maximum insulation temperature of 155°C.

Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-saving, life-saving or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.

53

<sup>(2) =</sup> General purpose thermoplastic insulation wire with a maximum insulation temperature of  $90^{\circ}\text{C}$ .

Notes:	Expertise Applied   Answers Delivered

Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-saving, life-savinging or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.



#### To assist you with your design and selection processes, Littlefuse also offers:

#### Comprehensive Online Product Specs on Littelfuse.com—

Featuring easy-to-use navigation, search and selection tools, as well as additional product details. You can rely on **Littelfuse.com** for instant answers and continuously up-to-date information.

Printed Product Catalogs—For offline and off-the-shelf convenience, our printed product catalogs include data sheets, selection tables and tutorials covering all of our core technologies. Contact your Littelfuse product representative or visit www.littelfuse.com/about-us/product-catalogs to check availability.

Circuit Protection Design Guides—Our application-design center website, www.littelfuse.com/technical-resources/application-designs offers a wealth of circuit protection guidance to help you select and apply the best circuit protection solution for your application.

As the world's #1 brand in circuit protection Littelfuse offers the broadest and deepest portfolio of circuit protection products and a global network of technical support, backed by more than 85 years of application design expertise. For all of your circuit protection needs visit our Technical Resources center at www.littelfuse.com/technical-resources

- Application Notes
- **■** Application Testing
- SPICE Models
- Local Technical Support
- **■** Reference Designs
- Product Samples
- Technical Articles
- **■** Certification Documents
- Data Sheets



Littelfuse is the world leader in circuit protection. We offer an extensive selection of circuit protection technologies for Automotive applications. Littelfuse circuit protection expert staff can assist you in designing circuit protection for your most demanding applications. Solutions for over-current applications as well as over-voltage applications are available from Littelfuse.

Low Current Distribution (LCD) MICRO2, MICRO3, LP MINI, MINI, ATOF, MAXI, MCASE, LP JCASE, JCASE

High Current Distribution (HCD) ZCASE MASTERFUSE, MASTERFUSE, ZCASE MEGA, MIDI, BF1, MEGA, CF

High Voltage Fuses (HEV) OHEV

**Battery Cable Protection (BCP)** CABLE PRO and BF-Inline products for mounting directly inline as part of a high-power cable assembly

For more information, please contact your authorized Littelfuse product representative or visit our website at www.littelfuse.com