SiT8924B

Automotive AEC-Q100 Oscillator



Features

- AEC-Q100 with extended temperature range (-55°C to 125°C)
- Frequencies between 1 MHz and 110 MHz accurate to 6 decimal places
- Supply voltage of 1.8V or 2.25V to 3.63V
- Excellent total frequency stability as low as ±20 ppm
- Industry best G-sensitivity of 0.1 PPB/G
- Low power consumption of 3.8 mA typical at 1.8V
- Standby mode for longer battery life
- LVCMOS/LVTTL compatible output
- Industry-standard packages: 2.0 x 1.6, 2.5 x 2.0, 3.2 x 2.5, 5.0 x 3.2, 7.0 x 5.0 mm x mm
- RoHS and REACH compliant, Pb-free, Halogen-free and Antimony-free

Applications

- Automotive, extreme temperature and other high-rel electronics
- Infotainment systems, collision detection devices, and in-vehicle networking
- Powertrain control









Electrical Characteristics

Table 1. Electrical Characteristics^[1,2]

All Min and Max limits are specified over temperature and rated operating voltage with 15 pF output load unless otherwise stated. Typical values are at 25°C and nominal supply voltage.

| Parameters | Symbol | Min. | Тур. | Max. | Unit | Condition |
|------------------------|--------|------|------------|-------------|-------------|---|
| | | | | Frequency | Range | |
| Output Frequency Range | f | 1 | - | 110 | MHz | Refer to Table 13 to 15 for a list supported frequencies |
| | | | Frequ | uency Stabi | lity and Ag | ing |
| Frequency Stability | F_stab | -20 | _ | +20 | ppm | Inclusive of Initial tolerance at 25°C, 1st year aging at 25°C, |
| | | -25 | _ | +25 | ppm | and variations over operating temperature, rated power supply voltage and load (15 pF ± 10%). |
| | | -30 | _ | +30 | ppm | Supply voltage and load (15 pr ± 10%). |
| | | -50 | _ | +50 | ppm | |
| | | | Oper | ating Temp | erature Rar | nge |
| Operating Temperature | T_use | -40 | _ | +85 | °C | AEC-Q100 Grade 3 |
| Range (ambient) | | -40 | - | +105 | °C | AEC-Q100 Grade 2 |
| | | -40 | - | +125 | °C | AEC-Q100 Grade 1 |
| | | -55 | _ | +125 | °C | Extended cold AEC-Q100 Grade1 |
| | | | Supply Vol | tage and Cι | rrent Cons | sumption |
| Supply Voltage | Vdd | 1.62 | 1.8 | 1.98 | V | All voltages between 2.25V and 3.63V including 2.5V, 2.8V, 3.0V |
| | | 2.25 | _ | 3.63 | V | and 3.3V are supported. |
| Current Consumption | ldd | - | 4.0 | 4.8 | mA | No load condition, f = 20 MHz, Vdd = 2.25V to 3.63V |
| | | - | 3.8 | 4.5 | mA | No load condition, f = 20 MHz, Vdd = 1.8V |
| OE Disable Current | l_od | - | - | 4.5 | mA | Vdd = 2.5V to 3.3V, OE = Low, Output in high Z state. |
| | | ı | _ | 4.3 | mA | Vdd = 1.8V, OE = Low, Output in high Zstate. |
| Standby Current | I_std | - | 2.6 | - | μΑ | Vdd = 2.8V to 3.3V, ST = Low, Output is weakly pulled down |
| | | - | 1.4 | - | μΑ | Vdd = 2.5V, ST = Low, Output is weakly pulled down |
| | | 1 | 0.6 | - | μΑ | Vdd = 1.8V, ST = Low, Output is weakly pulled down |
| | | | LVCM | OS Output | Characteris | stics |
| Duty Cycle | DC | 45 | - | 55 | % | All Vdd levels |
| Rise/Fall Time | | - | 1.5 | 3 | ns | Vdd = 2.25V - 3.63V, 20% - 80% |
| | Tr, Tf | - | 1.3 | 2.5 | ns | Vdd = 1.8V, 20% - 80% |
| Output High Voltage | VOH | 90% | | | Vdd | IOH = -4 mA (Vdd = 3.0V or 3.3V) IOH = -3 mA (Vdd = 2.8V and Vdd = 2.5V) IOH = -2 mA (Vdd = 1.8V) |
| Output Low Voltage | VOL | ı | - | 10% | Vdd | IOL = 4 mA (Vdd = 3.0V or 3.3V) IOL = 3 mA (Vdd = 2.8V and Vdd = 2.5V) IOL = 2 mA (Vdd = 1.8V) |



Table 1. Electrical Characteristics^[1,2] (continued)

| Parameters | Symbol | Min. | Тур. | Max. | Unit | Condition | | |
|---------------------------|----------|------|------|-------------|------------|--|--|--|
| | | | | nput Chara | cteristics | | | |
| Input High Voltage | VIH | 70% | - | - | Vdd | Pin 1, OE or ST | | |
| Input Low Voltage | VIL | - | - | 30% | Vdd | Pin 1, OE or ST | | |
| Input Pull-up Impedance | Z_in | - | 100 | - | kΩ | Pin 1, OE logic high or logic low, or \overline{ST} logic high | | |
| | | 2 | - | - | MΩ | Pin 1, ST logic low | | |
| | | | Star | tup and Res | ume Timing | 1 | | |
| Startup Time | T_start | - | - | 10 | ms | Measured from the time Vdd reaches its rated minimum value | | |
| Enable/Disable Time | T_oe | - | - | 130 | ns | f = 110 MHz. For other frequencies, T_oe = 100 ns + 3 * cycles | | |
| Resume Time | T_resume | - | - | 5 | ms | Measured from the time $\overline{\text{ST}}$ pin crosses 50%threshold | | |
| | | | | Jitte | r | | | |
| RMS Period Jitter | T_jitt | - | 1.6 | 2.5 | ps | f = 75 MHz, 2.25V to 3.63V | | |
| | | _ | 1.9 | 3.0 | ps | f = 75 MHz, 1.8V | | |
| RMS Phase Jitter (random) | T_phj | - | 0.5 | - | ps | f = 75 MHz, Integration bandwidth = 900 kHz to 7.5 MHz | | |
| | | - | 1.3 | - | ps | f = 75 MHz, Integration bandwidth = 12 kHz to 20 MHz | | |

Notes:

- 1. All electrical specifications in the above table are specified with 15 pF output load and for all Vdd(s) unless otherwise stated.
- 2. The typical value of any parameter in the Electrical Characteristic table is specified for the nominal value of the highest voltage option for that parameter and at 25°C temperature.

Table 2. Pin Description

| Pin | Symbol | Functionality | | | | | |
|-----|------------|---------------|--|--|--|--|--|
| | | Output Enable | H ^[3] : specified frequency output L: output is high impedance. Only output driver is disabled. | | | | |
| 1 | OE/ST/NC | Standby | H ^[3] : specified frequency output L: output is low (weak pull down). Device goes to sleep mode. Supply current reduces to I_std. | | | | |
| | No Connect | | Any voltage between 0 and Vdd or Open ^[3] : Specified frequency output. Pin 1 has no function. | | | | |
| 2 | GND | Power | Electrical ground ^[4] | | | | |
| 3 | OUT | Output | Oscillator output | | | | |
| 4 | VDD | Power | Power supply voltage ^[4] | | | | |




Figure 1. Pin Assignments

- 3. In OE or \overline{ST} mode, a pull-up resistor of 10 k Ω or less is recommended if pin 1 is not externally driven. If pin 1 needs to be left floating, use the NC option.
- 4. A capacitor of value 0.1 μF or higher between Vdd and GND is required.



Table 3. Absolute Maximum Limits

Attempted operation outside the absolute maximum ratings may cause permanent damage to the part. Actual performance of the IC is only guaranteed within the operational specifications, not at absolute maximum ratings.

| Parameter | Min. | Max. | Unit |
|--|------|------|------|
| Storage Temperature | -65 | 150 | °C |
| Vdd | -0.5 | 4 | V |
| Electrostatic Discharge | - | 2000 | V |
| Soldering Temperature (follow standard Pb free soldering guidelines) | - | 260 | °C |
| Junction Temperature ^[5] | - | 150 | °C |

Note

Table 4. Thermal Consideration^[6]

| Package | θJA, 4 Layer Board (°C/W) | θJA, 2 Layer Board (°C/W) | θJC, Bottom (°C/W) |
|---------|------------------------------|------------------------------|-----------------------|
| 7050 | 142 | 273 | 30 |
| 5032 | 97 | 199 | 24 |
| 3225 | 109 | 212 | 27 |
| 2520 | 117 | 222 | 26 |
| 2016 | 152 | 252 | 36 |

Note

Table 5. Maximum Operating Junction Temperature^[7]

| Max Operating Temperature (ambient) | Maximum Operating Junction Temperature |
|-------------------------------------|--|
| 85°C | 95°C |
| 105°C | 115°C |
| 125°C | 135°C |

Note:

7. Datasheet specifications are not guaranteed if junction temperature exceeds the maximum operating junction temperature.

Table 6. Environmental Compliance

| Parameter | Condition/Test Method | | |
|----------------------------|---------------------------|--|--|
| Mechanical Shock | MIL-STD-883F, Method 2002 | | |
| Mechanical Vibration | MIL-STD-883F, Method 2007 | | |
| Temperature Cycle | JESD22, Method A104 | | |
| Solderability | MIL-STD-883F, Method 2003 | | |
| Moisture Sensitivity Level | MSL1 @ 260°C | | |

^{5.} Exceeding this temperature for extended period of time may damage the device.

^{6.} Refer to JESD51 for θ JA and θ JC definitions, and reference layout used to determine the θ JA and θ JC values in the above table.



Test Circuit and Waveform





Figure 2. Test Circuit^[8]

Note:


8. Duty Cycle is computed as Duty Cycle = TH/Period.

Timing Diagrams



T_start: Time to start from power-off

Figure 4. Startup Timing (OE/ST Mode)[9]



T_oe: Time to re-enable the clock output

Figure 6. OE Enable Timing (OE Mode Only)

Note:

9. SiT8924 has "no runt" pulses and "no glitch" output during startup or resume.






Figure 3. Waveform^[8]



T_resume: Time to resume from ST

Figure 5. Standby Resume Timing (ST Mode Only)




T_oe: Time to put the output in High Z mode

Figure 7. OE Disable Timing (OE Mode Only)



Performance Plots[10]







Figure 8. Idd vs Frequency

Figure 9. Frequency vs Temperature







Figure 10. RMS Period Jitter vs Frequency

Figure 11. Duty Cycle vs Frequency







Figure 12. 20%-80% Rise Time vs Temperature

Figure 13. 20%-80% Fall Time vs Temperature



Performance Plots[10]






Figure 14. RMS Integrated Phase Jitter Random (12 kHz to 20 MHz) vs Frequency^[11]

Figure 15. RMS Integrated Phase Jitter Random (900 kHz to 20 MHz) vs Frequency^[11]

- 10. All plots are measured with 15 pF load at room temperature, unless otherwise stated.
 11. Phase noise plots are measured with Agilent E5052B signal source analyzer. Integration range is up to 5 MHz for carrier frequencies up to 40 MHz.



Programmable Drive Strength

The SiT8924 includes a programmable drive strength feature to provide a simple, flexible tool to optimize the clock rise/fall time for specific applications. Benefits from the programmable drive strength feature are:

- Improves system radiated electromagnetic interference (EMI) by slowing down the clock rise/fall time.
- Improves the downstream clock receiver's (RX) jitter by decreasing (speeding up) the clock rise/fall time.
- Ability to drive large capacitive loads while maintaining full swing with sharp edge rates.

For more detailed information about rise/fall time control and drive strength selection, see the SiTime Application Notes section.

EMI Reduction by Slowing Rise/Fall Time

Figure 16 shows the harmonic power reduction as the rise/fall times are increased (slowed down). The rise/fall times are expressed as a ratio of the clock period. For the ratio of 0.05, the signal is very close to a square wave. For the ratio of 0.45, the rise/fall times are very close to near-triangular waveform. These results, for example, show that the 11th clock harmonic can be reduced by 35 dB if the rise/fall edge is increased from 5% of the period to 45% of the period.




Figure 16. Harmonic EMI reduction as a Function of Slower Rise/Fall Time

Jitter Reduction with Faster Rise/Fall Time

Power supply noise can be a source of jitter for the downstream chipset. One way to reduce this jitter is to speed up the rise/fall time of the input clock. Some chipsets may also require faster rise/fall time in order to reduce their sensitivity to this type of jitter. Refer to the Rise/Fall Time Tables (Table 7 to Table 11) to determine the proper drive strength.

High Output Load Capability

The rise/fall time of the input clock varies as a function of the actual capacitive load the clock drives. At any given drive strength, the rise/fall time becomes slower as the output load increases. As an example, for a 3.3V SiT8924 device with default drive strength setting, the typical rise/fall time is 1 ns for 15 pF output load. The typical rise/fall time slows down to 2.6 ns when the output load increases to 45 pF. One can choose to speed up the rise/fall time to 1.83 ns by then increasing the drive strength setting on the SiT8924.

The SiT8924 can support up to 60 pF in maximum capacitive loads with drive strength settings. Refer to the Rise/Tall Time Tables (Table 7 to Table 11) to determine the proper drive strength for the desired combination of output load vs. rise/fall time.

SiT8924 Drive Strength Selection

Tables 7 through 11 define the rise/fall time for a given capacitive load and supply voltage.

- 1. Select the table that matches the SiT8924 nominal supply voltage (1.8V, 2.5V, 2.8V, 3.0V, 3.3V).
- Select the capacitive load column that matches the application requirement (5 pF to 60 pF)
- Under the capacitive load column, select the desired rise/fall times.
- The left-most column represents the part number code for the corresponding drive strength.
- Add the drive strength code to the part number for ordering purposes.

Calculating Maximum Frequency

Based on the rise and fall time data given in Tables 7 through 11, the maximum frequency the oscillator can operate with guaranteed full swing of the output voltage over temperature can be calculated as follows:

Max Frequency =
$$\frac{1}{5 \times Trf}$$
 20/80

where Trf_20/80 is the typical value for 20%-80% rise/fall time.

Example 1

Calculate f_{MAX} for the following condition:

- Vdd = 1.8V (Table 7)
- Capacitive Load: 30 pF
- Desired Tr/f time = 3 ns
 (rise/fall time part number code = E)

Part number for the above example:

SiT8924BIE12-18E-66.66660



Drive strength code is inserted here. Default setting is "-"



Rise/Fall Time (20% to 80%) vs C_{LOAD} Tables

Table 7. Vdd = 1.8V Rise/Fall Times for Specific C_{LOAD}

| Rise/Fall Time Typ (ns) | | | | | | | |
|-----------------------------------|------|-------|-------|-------|-------|--|--|
| Drive Strength \C _{LOAD} | 5 pF | 15 pF | 30 pF | 45 pF | 60 pF | | |
| L | 6.16 | 11.61 | 22.00 | 31.27 | 39.91 | | |
| Α | 3.19 | 6.35 | 11.00 | 16.01 | 21.52 | | |
| R | 2.11 | 4.31 | 7.65 | 10.77 | 14.47 | | |
| В | 1.65 | 3.23 | 5.79 | 8.18 | 11.08 | | |
| Т | 0.93 | 1.91 | 3.32 | 4.66 | 6.48 | | |
| E | 0.78 | 1.66 | 2.94 | 4.09 | 5.74 | | |
| U | 0.70 | 1.48 | 2.64 | 3.68 | 5.09 | | |
| F or "-": default | 0.65 | 1.30 | 2.40 | 3.35 | 4.56 | | |

Table 9. Vdd = 2.8V Rise/Fall Times for Specific C_{LOAD}

| Rise/Fall Time Typ (ns) | | | | | | | |
|------------------------------------|------|-------|-------|-------|-------|--|--|
| Drive Strength \ C _{LOAD} | 5 pF | 15 pF | 30 pF | 45 pF | 60 pF | | |
| L | 3.77 | 7.54 | 12.28 | 19.57 | 25.27 | | |
| А | 1.94 | 3.90 | 7.03 | 10.24 | 13.34 | | |
| R | 1.29 | 2.57 | 4.72 | 7.01 | 9.06 | | |
| В | 0.97 | 2.00 | 3.54 | 5.43 | 6.93 | | |
| Т | 0.55 | 1.12 | 2.08 | 3.22 | 4.08 | | |
| E or "-": default | 0.44 | 1.00 | 1.83 | 2.82 | 3.67 | | |
| U | 0.34 | 0.88 | 1.64 | 2.52 | 3.30 | | |
| F | 0.29 | 0.81 | 1.48 | 2.29 | 2.99 | | |

Table 11. Vdd = 3.3V Rise/Fall Times for Specific CLOAD

| Rise/Fall Time Typ (ns) | | | | | | | |
|------------------------------------|------|-------|-------|-------|-------|--|--|
| Drive Strength \ C _{LOAD} | 5 pF | 15 pF | 30 pF | 45 pF | 60 pF | | |
| L | 3.39 | 6.88 | 11.63 | 17.56 | 23.59 | | |
| Α | 1.74 | 3.50 | 6.38 | 8.98 | 12.19 | | |
| R | 1.16 | 2.33 | 4.29 | 6.04 | 8.34 | | |
| В | 0.81 | 1.82 | 3.22 | 4.52 | 6.33 | | |
| T or "-": default | 0.46 | 1.00 | 1.86 | 2.60 | 3.84 | | |
| E | 0.33 | 0.87 | 1.64 | 2.30 | 3.35 | | |
| U | 0.28 | 0.79 | 1.46 | 2.05 | 2.93 | | |
| F | 0.25 | 0.72 | 1.31 | 1.83 | 2.61 | | |

Table 8. Vdd = 2.5V Rise/Fall Times for Specific C_{LOAD}

| Rise/Fall Time Typ (ns) | | | | | | | |
|-----------------------------------|------|-------|-------|-------|-------|--|--|
| Drive Strength \C _{LOAD} | 5 pF | 15 pF | 30 pF | 45 pF | 60 pF | | |
| L | 4.13 | 8.25 | 12.82 | 21.45 | 27.79 | | |
| Α | 2.11 | 4.27 | 7.64 | 11.20 | 14.49 | | |
| R | 1.45 | 2.81 | 5.16 | 7.65 | 9.88 | | |
| В | 1.09 | 2.20 | 3.88 | 5.86 | 7.57 | | |
| T | 0.62 | 1.28 | 2.27 | 3.51 | 4.45 | | |
| E or "-": default | 0.54 | 1.00 | 2.01 | 3.10 | 4.01 | | |
| U | 0.43 | 0.96 | 1.81 | 2.79 | 3.65 | | |
| F | 0.34 | 0.88 | 1.64 | 2.54 | 3.32 | | |

Table 10. Vdd = 3.0V Rise/Fall Times for Specific C_{LOAD}

| Rise/Fall Time Typ (ns) | | | | | | | |
|------------------------------------|------|-------|-------|-------|-------|--|--|
| Drive Strength \ C _{LOAD} | 5 pF | 15 pF | 30 pF | 45 pF | 60 pF | | |
| L | 3.60 | 7.21 | 11.97 | 18.74 | 24.30 | | |
| Α | 1.84 | 3.71 | 6.72 | 9.86 | 12.68 | | |
| R | 1.22 | 2.46 | 4.54 | 6.76 | 8.62 | | |
| В | 0.89 | 1.92 | 3.39 | 5.20 | 6.64 | | |
| T or "-": default | 0.51 | 1.00 | 1.97 | 3.07 | 3.90 | | |
| E | 0.38 | 0.92 | 1.72 | 2.71 | 3.51 | | |
| U | 0.30 | 0.83 | 1.55 | 2.40 | 3.13 | | |
| F | 0.27 | 0.76 | 1.39 | 2.16 | 2.85 | | |



Pin 1 Configuration Options (OE, \overline{ST} , or NC)

Pin 1 of the SiT8924 can be factory-programmed to support three modes: Output enable (OE), standby ST or No Connect (NC). These modes can also be programmed with the Time Machine II using Field Programmable Oscillators.

Output Enable (OE) Mode

In the OE mode, applying logic Low to the OE pin only disables the output driver and puts it in Hi-Z mode. The core of the device continues to operate normally. Power consumption is reduced due to the inactivity of the output. When the OE pin is pulled High, the output is typically enabled in<1µs.

Standby (ST) Mode

In the \overline{ST} mode, a device enters into the standby mode when Pin 1 pulled Low. All internal circuits of the device are turned off. The current is reduced to a standby current, typically in the range of a few μA . When \overline{ST} is pulled High, the device goes through the "resume" process, which can take up to 5 ms.

No Connect (NC) Mode

In the NC mode, the device always operates in its normal mode and output the specified frequency regardless of the logic level on pin 1.

Table 12 below summarizes the key relevant parameters in the operation of the device in OE, \overline{ST} , or NC mode.

Table 12. OE vs. ST vs. NC

| | OE | ST | NC |
|---|--------|-------------------|--------|
| Active current 20 MHz (max, 1.8V) | 4.5 mA | 4.5 mA | 4.5 mA |
| OE disable current (max. 1.8V) | 4.3 mA | N/A | N/A |
| Standby current (typical 1.8V) | N/A | 0.6 uA | N/A |
| OE enable time at 110 MHz (max) | 130 ns | N/A | N/A |
| Resume time from standby (max, all frequency) | N/A | 5 ms | N/A |
| Output driver in OE disable/standby mode | High Z | Weak pull-down | N/A |

Output on Startup and OE Enable

The SiT8924 comes with gated output. Its clock output is accurate to the rated frequency stability within the first pulse from initial device startup or when the output driver is enabled.

In addition, the SiT8924 supports "no runt" pulses and "no glitch" output during startup or when the device output driver is enabled as shown in the waveform captures in Figure 17 and Figure 18.




Figure 17. Startup Waveform vs. Vdd





Figure 18. Startup Waveform vs. Vdd (Zoomed-in View of Figure 17)




Dimensions and Patterns





Dimensions and Patterns




- 12. Top marking: Y denotes manufacturing origin and XXXX denotes manufacturing lot number. The value of "Y" will depend on the assembly location of the device.
- 13. A capacitor of value 0.1 μF or higher between Vdd and GND is required.



Ordering Information

The following part number guide is for reference only. To customize and build an exact part number, use the SiTime Part Number Generator.



Note:

Table 13. Supported Frequencies (-40°C to +85°C)^[15]

| Frequency Range | | |
|-----------------|----------------|--|
| Min. | Max. | |
| 1.000000 MHz | 110.000000 MHz | |

Table 14. Supported Frequencies (-40°C to +105°C or -40°C to +125°C)^[15, 16]

| Frequency Range | | | | |
|-----------------|----------------|--|--|--|
| Min. | Max. | | | |
| 1.000000 MHz | 61.222999 MHz | | | |
| 61.974001 MHz | 69.795999 MHz | | | |
| 70.485001 MHz | 79.062999 MHz | | | |
| 79.162001 MHz | 81.427999 MHz | | | |
| 82.232001 MHz | 91.833999 MHz | | | |
| 92.155001 MHz | 94.248999 MHz | | | |
| 94.430001 MHz | 94.874999 MHz | | | |
| 94.994001 MHz | 97.713999 MHz | | | |
| 98.679001 MHz | 110.000000 MHz | | | |

Table 15. Supported Frequencies (-55°C to +125°C)^[15, 16]

| Frequency Range | | | |
|-----------------|----------------|--|--|
| Min. | Max. | | |
| 1.000000 MHz | 61.222999 MHz | | |
| 61.974001 MHz | 69.239999 MHz | | |
| 70.827001 MHz | 78.714999 MHz | | |
| 79.561001 MHz | 80.159999 MHz | | |
| 80.174001 MHz | 80.779999 MHz | | |
| 82.632001 MHz | 91.833999 MHz | | |
| 95.474001 MHz | 96.191999 MHz | | |
| 96.209001 MHz | 96.935999 MHz | | |
| 99.158001 MHz | 110.000000 MHz | | |

- 15. Any frequency within the min and max values in the above tables are supported with 6 decimal places of accuracy.
- 16. Please contact SiTime for frequencies that are not listed in the tables above.

^{14.} The voltage portion of the SiT8924 part number consists of two characters that denote the specific supply voltage of the device. The SiT8924 supports either 1.8V ±10% or any voltage between 2.25V and 3.62V. In the 1.8V mode, one can simply insert 18 in the part number. In the 2.5V to 3.3V mode, two digits such as 18, 25 or 33 can be used in the part number to reflect the desired voltage. Alternatively, "XX" can be used to indicate the entire operating voltage range from 2.25V to 3.63V.



Table 16. Ordering Codes for Supported Tape & Reel Packing Method

| Device Size (mm x mm) | 16 mm T&R (3ku) | 16 mm T&R (1ku) | 12 mm T&R (3ku) | 12 mm T&R (1ku) | 8 mm T&R (3ku) | 8 mm T&R (1ku) |
|-----------------------|-----------------|-----------------|-----------------|-----------------|----------------|----------------|
| 2.0 x 1.6 | - | ı | - | - | D | E |
| 2.5 x 2.0 | - | ı | - | - | D | E |
| 3.2 x 2.5 | - | - | _ | - | D | E |
| 5.0 x 3.2 | - | - | Т | Y | - | _ |
| 7.0 x 5.0 | Т | Υ | - | - | - | - |



Table 17. Additional Information

| Document | Description Download Link | | |
|-----------------------------------|--|--|--|
| Time Machine II | MEMS oscillator programmer | http://www.sitime.com/support/time-machine-oscillator-programmer | |
| Field Programmable Oscillators | Devices that can be programmable in the field by Time Machine II | http://www.sitime.com/products/field-programmable-oscillators | |
| Manufacturing Notes | Tape & Reel dimension, reflow profile and other manufacturing related info | http://www.sitime.com/manufacturing-notes | |
| Qualification Reports | RoHS report, reliability reports, composition reports | http://www.sitime.com/support/quality-and-reliability | |
| Performance Reports | Additional performance data such as phase noise, current consumption and jitter for selected frequencies | http://www.sitime.com/support/performance-measurement-report | |
| Termination Techniques | Termination design recommendations | http://www.sitime.com/support/application-notes | |
| Layout Techniques | Layout recommendations | http://www.sitime.com/support/application-notes | |

Table 18. Revision History

| Revision | Release Date | Change Summary |
|----------|--------------|---|
| 0.1 | 05/19/2015 | Final production release |
| 1.3 | 03/18/2016 | Added the industrial temperature "-40°C to ±85°C" option Added support for ±20 ppm frequency stability Added 12 and 16 mm T&R information to Table 16 |
| 1.5 | 12/14/2016 | Changed Clock Generator to SOT23 Oscillator |
| 1.6 | 07/18/2018 | Added Standby mode option Removed center lines from the package drawings Revised description of temperature range options Updated logo and company address, links and other page layout changes |

SiTime Corporation, 5451 Patrick Henry Drive, Santa Clara, CA 95054, USA | Phone: +1-408-328-4400 | Fax: +1-408-328-4439

© SiTime Corporation 2015-2018. The information contained herein is subject to change at any time without notice. SiTime assumes no responsibility or liability for any loss, damage or defect of a Product which is caused in whole or in part by (i) use of any circuitry other than circuitry embodied in a SiTime product, (ii) misuse or abuse including static discharge, neglect or accident, (iii) unauthorized modification or repairs which have been soldered or altered during assembly and are not capable of being tested by SiTime under its normal test conditions, or (iv) improper installation, storage, handling, warehousing or transportation, or (v) being subjected to unusual physical, thermal, or electrical stress.

Disclaimer: SiTime makes no warranty of any kind, express or implied, with regard to this material, and specifically disclaims any and all express or implied warranties, either in fact or by operation of law, statutory or otherwise, including the implied warranties of merchantability and fitness for use or a particular purpose, and any implied warranty arising from course of dealing or usage of trade, as well as any common-law duties relating to accuracy or lack of negligence, with respect to this material, any SiTime product and any product documentation. Products sold by SiTime are not suitable or intended to be used in a life support application or component, to operate nuclear facilities, or in other mission critical applications where human life may be involved or at stake. All sales are made conditioned upon compliance with the critical uses policy set forth below.

CRITICAL USE EXCLUSION POLICY

BUYER AGREES NOT TO USE SITIME'S PRODUCTS FOR ANY APPLICATION OR IN ANY COMPONENTS USED IN LIFE SUPPORT DEVICES OR TO OPERATE NUCLEAR FACILITIES OR FOR USE IN OTHER MISSION-CRITICAL APPLICATIONS OR COMPONENTS WHERE HUMAN LIFE OR PROPERTY MAY BE AT STAKE.

SiTime owns all rights, title and interest to the intellectual property related to SiTime's products, including any software, firmware, copyright, patent, or trademark. The sale of SiTime products does not convey or imply any license under patent or other rights. SiTime retains the copyright and trademark rights in all documents, catalogs and plans supplied pursuant to or ancillary to the sale of products or services by SiTime. Unless otherwise agreed to in writing by SiTime, any reproduction, modification, translation, compilation, or representation of this material shall be strictly prohibited.



Supplemental Information



Best Reliability

Silicon is inherently more reliable than quartz. Unlike quartz suppliers, SiTime has in-house MEMS and analog CMOS expertise, which allows SiTime to develop the most reliable products. Figure 1 shows a comparison with quartz technology.

Why is SiTime Best in Class:

- SiTime's MEMS resonators are vacuum sealed using an advanced EpiSeal[™] process, which eliminates foreign particles and improves long term aging and reliability
- World-class MEMS and CMOS design expertise




Figure 1. Reliability Comparison^[1]

Best Aging

Unlike quartz, MEMS oscillators have excellent long term aging performance which is why every new SiTime product specifies 10-year aging. A comparison is shown in Figure 2.

Why is SiTime Best in Class:

- SiTime's MEMS resonators are vacuum sealed using an advanced EpiSeal™ process, which eliminates foreign particles and improves long term aging and reliability
- Inherently better immunity of electrostatically driven MEMS resonator




Figure 2. Aging Comparison^[2]

Best Electro Magnetic Susceptibility (EMS)

SiTime's oscillators in plastic packages are up to 54 times more immune to external electromagnetic fields than quartz oscillators as shown in Figure 3.

Why is SiTime Best in Class:

- Internal differential architecture for best common mode noise rejection
- Electrostatically driven MEMS resonator is more immune to EMS




Figure 3. Electro Magnetic Susceptibility (EMS)[3]

Best Power Supply Noise Rejection

SiTime's MEMS oscillators are more resilient against noise on the power supply. A comparison is shown in Figure 4.

Why is SiTime Best in Class:

- On-chip regulators and internal differential architecture for common mode noise rejection
- MEMS resonator is paired with advanced analog CMOS IC




Figure 4. Power Supply Noise Rejection^[4]



Best Vibration Robustness

High-vibration environments are all around us. All electronics, from handheld devices to enterprise servers and storage systems are subject to vibration. Figure 5 shows a comparison of vibration robustness.

Why is SiTime Best in Class:

- The moving mass of SiTime's MEMS resonators is up to 3000 times smaller than quartz
- Center-anchored MEMS resonator is the most robust design




Figure 5. Vibration Robustness^[5]

Figure labels:

- TXC = TXC
- Epson = EPSN
- Connor Winfield = CW
- Kyocera = KYCA
- SiLabs = SLAB
- SiTime = EpiSeal MEMS

Best Shock Robustness

SiTime's oscillators can withstand at least 50,000 g shock. They all maintain their electrical performance in operation during shock events. A comparison with quartz devices is shown in Figure 6.

Why is SiTime Best in Class:

- The moving mass of SiTime's MEMS resonators is up to 3000 times smaller than quartz
- Center-anchored MEMS resonator is the most robust design




Figure 6. Shock Robustness^[6]

Silicon MEMS Outperforms Quartz



Notes:

- 1. Data source: Reliability documents of named companies.
- 2. Data source: SiTime and quartz oscillator devices datasheets.
- 3. Test conditions for Electro Magnetic Susceptibility (EMS):
 - According to IEC EN61000-4.3 (Electromagnetic compatibility standard)
 - Field strength: 3V/m
 - Radiated signal modulation: AM 1 kHz at 80% depth
 - Carrier frequency scan: 80 MHz 1 GHz in 1% steps
 - Antenna polarization: Vertical
 - DUT position: Center aligned to antenna

Devices used in this test:

| Label | Manufacturer | Part Number | Technology |
|--------------|-----------------|-----------------------------|--|
| EpiSeal MEMS | SiTime | SiT9120AC-1D2-33E156.250000 | MEMS + PLL |
| EPSN | Epson | EG-2102CA156.2500M-PHPAL3 | Quartz, SAW |
| TXC | TXC | BB-156.250MBE-T | Quartz, 3 rd Overtone |
| CW | Conner Winfield | P123-156.25M | Quartz, 3 rd Overtone |
| KYCA | AVX Kyocera | KC7050T156.250P30E00 | Quartz, SAW |
| SLAB | SiLab | 590AB-BDG | Quartz, 3 rd Overtone + PLL |

4. 50 mV pk-pk Sinusoidal voltage.

Devices used in this test:

| Label | Manufacturer | Part Number | Technology |
|--------------|--------------|----------------------------|------------|
| EpiSeal MEMS | SiTime | SiT8208AI-33-33E-25.000000 | MEMS + PLL |
| NDK | NDK | NZ2523SB-25.6M | Quartz |
| KYCA | AVX Kyocera | KC2016B25M0C1GE00 | Quartz |
| EPSN | Epson | SG-310SCF-25M0-MB3 | Quartz |

5. Devices used in this test:

same as EMS test stated in Note 3.

- 6. Test conditions for shock test:
 - MIL-STD-883F Method 2002
 - Condition A: half sine wave shock pulse, 500-g, 1ms
 - Continuous frequency measurement in 100 μs gate time for 10 seconds

Devices used in this test:

same as EMS test stated in Note 3.

7. Additional data, including setup and detailed results, is available upon request to qualified customer. Please contact productsupport@sitime.com.