




# Compact - IPM ID30FFX60U1S\_A


### **Features**

- UL 1557 Certified.
- Adopt the latest trench IGBT technology to get a good overall loss trade-off.
- Open Emitter on N terminal for low cost current sensing application.
- Matched propagation delay and arm shooting through prevention.
- Built-in bootstrap diodes with current limiting resistor.
- Provided a fault signal (FO pin) and shut-off internal IGBT when suffer S.C. and under-voltage faulty event.
- RoHS compatible.









#### Ε


TERMIN	AL CODE
1 NC	16 COM
$2\;V_{B(U)}$	$17 \ V_{OT}$
$3\ V_{B(V)}$	$18~\text{N}_{\text{W}}$
$4\ V_{B(W)}$	$19\;\text{N}_\text{V}$
$5 IN_{(UH)}$	$20\;\text{N}_\text{U}$
6 IN <sub>(VH)</sub>	21 W
$7 \ IN_{(WH)}$	22 V
8 Vcc	23 U
9 COM	24 P
10 IN <sub>(UL</sub> )	25 NC
11 IN(VL)	

12 IN(WL)

 $13\;V_{CC}$ 

14 V<sub>FO</sub>

15 Csc






# **Table1: Pin Descriptions**

No.	Symbol	Pin Description
1	NC	No connection
2	V <sub>B(U)</sub>	High - side Bias Voltage for U Phase IGBT Driving
3	$V_{B(V)}$	High - side Bias Voltage for V Phase IGBT Driving
4	$V_{B(W)}$	High - side Bias Voltage for W Phase IGBT Driving
5	IN <sub>(UH)</sub>	Signal Input Terminal for High-side U Phase
6	IN <sub>(VH)</sub>	Signal Input Terminal for High-side V Phase
7	IN <sub>(WH)</sub>	Signal Input Terminal for High-side W Phase
8	Vcc	Supply Voltage Terminal for Driver IC
9	СОМ	Reference Voltage Terminal for Driver IC
10	IN <sub>(UL</sub> )	Signal Input Terminal for Low-side U Phase
11	IN <sub>(VL)</sub>	Signal Input Terminal for Low-side V Phase
12	IN <sub>(WL)</sub>	Signal Input Terminal for Low-side W Phase
13	Vcc	Supply Voltage Terminal for Driver IC
14	V <sub>FO</sub>	Fault Output Terminal
15	Csc	Short-Current Detection Input
16	СОМ	Reference Voltage Terminal for Driver IC
17	V <sub>OT</sub>	Temperature output
18	Nw	Negative DC-Link Input Terminal for W Phase
19	N∨	Negative DC-Link Input Terminal for V Phase
20	Nu	Negative DC-Link Input Terminal for U Phase
21	W	Output Terminal for W Phase
22	V	Output Terminal for V Phase
23	U	Output Terminal for U Phase
24	Р	Positive DC – Link Input
25	NC	No connection

(see figure 2, next page)






Figure 3. IPM Internal Block Diagram

#### Application:

- Short-circuit current protection AC 100~240Vrms class 3 phase output for low power motor control.
- Household electric appliances such as air conditioners, washing machines, refrigerators, etc...
- Low power industrial servo drives applications such as sewing machine, treadmill, etc...

# **MAXIMUM RATINGS** $(T_j = 25^{\circ}C)$

### **INVERTER PART**

Item	Symbol	Min.	Max.	Unit
Between collector to emitter voltage	V <sub>CES</sub> (IGBT)	•	600	V
Supply voltage P-N	V <sub>PN</sub>	•	450	V
Supply voltage (surge) P-N	VPN (surge)	ı	500	V
Each IGBT collector current	± Ic (Tc = 25°C)	•	30	Α
Each IGBT collector current (peak)	± I <sub>CP</sub> ( Tc = 25℃, pulse )	•	90	Α
Collector dissipation	Pc (Tc = $25^{\circ}$ C, per one chip)	ı	96	W
Junction temperature	Tj (Note 1)		+150	$^{\circ}\mathbb{C}$

Note 1: Power chip in IPM is qualified for 175°C operation. But overall junction temperature should be limited by  $T_j \le 125$ °C (@  $T_c \le 100$ °C) to fit long term reliability requirement.


### **CONTROL PART**


Item	Symbol	Min.	Max.	Unit
Driver IC supply voltage	Vcc	-0.3	20	V
P - side floating supply voltage	$V_{B(u)S(u),\ B(V)S(V),\ B(W)S(W)}$	-0.3	20	V
Current sensing input voltage	V <sub>SC</sub>	-0.3	Vcc+0.3	V
Logic input voltage	$\begin{split} &IN_{(UH)}, IN_{(VH)}, IN_{(WH)}, \\ &IN_{(UL)}, IN_{(VL)}, IN_{(WL)} \end{split}$	-0.3	Vcc+0.3	V
Fault output voltage	VFO	-0.3	Vcc+0.3	V
Fault output current	IFO	-	1	mA

### **TOTAL SYSTEM**

Item	Sym	bol	Min.	Max.	Unit
Module case operating temperature	Tc	(Note 2)	-20	+100	$^{\circ}\mathbb{C}$
Storage temperature	T <sub>stg</sub>		-40	+125	$^{\circ}\mathbb{C}$
Isolation voltage (60Hz Sinusoidal, AC 1 minute, pins to heat-sink plate)	V <sub>iso</sub>		-	1500	Vrms

### Control terminal





Power terminal

Figure 4. Tc Measurement Point

### THERMAL RESISTANCE

Item	Symbol	Condition	Min.	Тур.	Max.	Unit
Junction to case thermal	R <sub>th(j-c)Q</sub>	IGBT part (1/6)	-	1.3		°C 111
resistance	R <sub>th(j-c)</sub> F	FWD part (1/6)	-	1.7		°C/W

**ELECTRICAL CHARACTERISTICS** (T<sub>j</sub> = 25°C)

### **INVERTER PART**

Item	Symbol	Condition	Min.	Тур.	Max.	Unit
Collector-emitter saturation voltage	V <sub>CE</sub> (sat)	$V_{CC} = V_{B(U)S(U), B(V)S(V), B(W)S(W)} = 15V, I_{C} = 30A, V_{SC} = 0V$ $T_{j}=25^{\circ}C$		1.50		>
FWD forward voltage drop	VF	$T_j = 25^{\circ}C$ , - $I_C = 30A$		2.10		V
	$T_{on}$			1.40		
	Tr	$V_D = 300V$ ,		0.20		
Switching times	$T_{c(on)}$	$V_{CC} = V_{B(U), B(V), B(W)} = 15V,$		0.40		
(Fig. 5)	$T_{off}$	$I_C = 30A, T_j = 25^{\circ}C,$		1.60		μS
(i ig. 3)	T <sub>f</sub>	$V_{IN} = 5V <> 0V,$		0.35		
	$T_{c(off)}$	$V_{SC} = 0V$ , Inductive Load		0.30		
	$T_{rr}$			0.30		
Collector-emitter cut-off current	I <sub>CES</sub>	V <sub>CE</sub> =V <sub>CES</sub>			500	μA




Figure 5. Switching Time Definition

# **CONTROL PART** $(T_j = 25^{\circ}C)$

Item	Symbol	Condition	Min.	Тур.	Max.	Unit
IN(uh. vh. wh), IN(ul. vl. wl) ON threshold voltage	$V_{th(on)}$		1.4	1.7	2.0	V
IN <sub>(UH, VH, WH)</sub> ,IN <sub>(UL, VL, WL)</sub> OFF threshold voltage	$V_{\text{th(off)}}$		2.2	2.5	2.8	V
IN <sub>(UH, VH, WH)</sub> input bias current	IIN(UH, VH, WH)(HI)	VIN(UH. VH. WH) = 5V	0.7	1.0	1.5	mA
IN(UH, VH, WH) INPUT bias current	IN(UH, VH, WH) (LO)	V IN(UH, VH, WH) = $0V$	•	0	-	IIIA
IN an an anaign put bigg ourrent	In(UL, VL, WL) (HI)	$V_{IN(UL, VL, WL)} = 5V$	0.7-	1.0	1.3	mA
IN <sub>(UL</sub> , VL, WL) input bias current	IN(UL, VL, WL) (LO)	V IN(UL, VL, WL) = 0V	-	0	-	IIIA
Driver IC supply voltage	Vcc		13.5	15.0	16.5	V
P - side floating supply voltage	$V_{B(U),\;B(V),\;B(W)}$		13.5	15.0	16.5	V
Vcc terminal input current	lc		•	•	2.3	mA
Coult output voltage	V <sub>FOH</sub>	V <sub>SC</sub> =0V (Note 2)	4.9	1	-	V
Fault output voltage	$V_{FOL}$	V <sub>SC</sub> =1V	ı	1	950	mV
Short circuit trip level	V <sub>SC(ref)</sub>	V <sub>CC</sub> =15V, T <sub>j</sub> = 25 °C	0.455	0.480	0.505	V
Fault output pulse width	t <sub>FOD</sub>	(Note 3)	20	65	-	us
Cumply sireuit under veltage	UVT <sub>VCC</sub>	Trip level	9.5	10.4	11.0	V
Supply circuit under voltage protection	UVR <sub>VCC</sub>	Reset level	11.0	12.0	12.8	V
protection	UVH	Hysteresis	•	1.0	-	V
IN <sub>(UL、VL、WL)</sub> Input filter time	tin,fil	VIN = 0 & 5V (Note 4)	100	200	-	ns
Tomporatura Output	V	LVIC temperature=90°C		2.77		V
Temperature Output	V <sub>OT</sub>	LVIC temperature=25°C		1.13		V
VF	Bootstrap diode forward voltage	If=10mA, T <sub>j</sub> = 25℃	0.8	-	1.1	V
R	Limiting resistance	Individual resistor		25	-	Ohm

Note 2:  $V_{FO}$  output is open collector type, so this signal line should be pulled up to the +5V power supply with approximately 4.7K $\Omega$ 

Note 3: Fault output pulse width is filter capacitor of S.C. depended.

**Note 4:** For high side PWM, IN(UH, VH, WH) pulse width must be  $\geq 1$  us.

# **Input Filter Function**




Figure 6. Input Filter Function




Figure 7. VoT output characteristics

### **RECOMMENDED OPERATION CONDITIONS**

Item	Symbol	Condition	Min.	Тур.	Max.	Unit
DC – Link Supply voltage	$V_D$	Applied between P-N	0	400	450	V
Driver IC supply voltage	Vcc	Applied between Vcc - COM	13.5	15.0	16.5	V
P - side floating supply voltage	V <sub>BS</sub>	Applied between $V_{B(u, v, w)} - V_{S(u, v, w)}$	13.5	15.0	16.5	V
Input ON threshold voltage	V <sub>sc(ON)</sub>	Applied between IN(UH, VH, WH) - COM		0 ~ 0.65		V
Input OFF threshold voltage	V <sub>sc(OFF)</sub>	and IN(UL, VL, WL) - COM		4.0 ~ 5.5		V
Supply voltage ripple	$\Delta V_D$ , $\Delta V_{DB}$		-1	-	1	V/µs
Arm shoot-through blocking time	t dead		1	-	-	μs
PWM input frequency	f <sub>РWМ</sub>	Tc≦ 100°C, Tj≦ 125°C	-	15	-	kHz

# **MECHANICAL CHARACTERISTICS AND RATINGS**

Item	Condition		Min.	Тур.	Max.	Unit
Mounting torque	Mounting screw: M3	Recommended 0.65N•m	0.60	0.65	0.70	N•m
Weight			-	11.5	-	g
Heat-sink flatness			-50	•	100	μm





Figure 8. Measurement Location of Heat-sink Flatness



www.powersemi.cc




Figure 11. Timing Chart of SC Operation

- S1. The IGBT's are controlled by input PWM signal.(Normal operation)
- S2. Short circuit event occur and reach the limited level. (SC protection is trigger).
- S3. IGBT gate driving signal is disabled.
- S4. Current is cut off caused by IGBT turns OFF.
- S5. Disabled state
- S6. Fault level is kept on low level during the fault output activation
- S7. IGBT returns for normal operation when fault state is reset
- S8. Fault output starting once SC protection is trigger.




Figure 12. Timing Chart of Under-Voltage Operation

- S1. The IGBT's are controlled by input PWM signal.(Normal operation)
- S2. Under-voltage protection is trigger
- S3. IGBT driving signals are disabled when fault condition occur
- S4. Fault state and the period will be able to control by external capacitor value.
- S5. Under-voltage event is recovered
- S6. IGBT returns for normal operation when fault state is reset

## **Direct Input (without Photo Coupler) Interface Example**




Figure 13. Typical Application Circuit Interface Example without Photo-Coupler

#### Design reference:

- 1.  $R1:100\Omega$
- 2. R2 :  $4.7K\Omega$  ( VFO output is open collector so to have a pull high resistor is needed. )
- 3. R3: 5k-200k pull down resistor for getting linear output characteristics at low temperature below room temperature.
  - 4. C1:  $10 \sim 100 \mu F$  (Electrolytic, low impendence)
  - 5. C2: 100 ~ 1000pF (Ceramic) (The capacitor could filter the noise, but should be careful to the dead time)
  - 6.  $C8:220\mu F$  (Electrolytic, low impendence)
  - 7. D1: Zener diode (It is recommended to insert a Zener diode to prevent gate lifting and surge destruction)
  - 8. Only connect either pin 9 or pin 16 to ground, do not connect both together to form the ground loop internally.

## **Current Sense Shceme**




Figure 14. Current Sense Scheme

#### Description:

- 1. Half-bridge current sensing
- 2. Voltage shifting of the  $\ensuremath{V_{\text{sense}}}$
- 3. Voltage gain and filtering
- 4. Capacitor required by the ADC for sampling purpose

 $R_{\text{OUT}}$  resistor is usually required in order to make the  $OP_{\text{AMP}}$  stable when the  $C_{\text{OUT}}$  capacitance increases

## Design Reference :

 $1.\;R1:1.0\;K\Omega$ 

2. R2 : 5.6  $\mbox{K}\Omega$ 

3. R3 : 4.7 K $\Omega$ 

4. R4: 910  $\Omega$ 

5. R5 : 910  $\Omega$  6.ROUT : 1.0 K $\Omega$ 

7. C2:10pF ( Ceramic )

### **Precautions on Electrostatic Electricity**

- (1) Operators must wear anti-static clothing and conductive shoes (or a leg or heel strap).
- (2) Operators must wear a wrist strap grounded to earth via a resistor of about 1  $M\Omega$ .
- (3) Soldering irons must be grounded from iron tip to earth, and must be used only at low voltages.
- (4) If the tweezers you use are likely to touch the device terminals, use anti-static tweezers and in particular avoid metallic tweezers. If a charged device touches a low-resistance tool, rapid discharge can occur. When using vacuum tweezers, attach a conductive chucking pat to the tip, and connect it to a dedicated ground used especially for anti-static purposes (suggested resistance value:  $10^4$  to  $10^8\Omega$ ).
- (5) Do not place devices or their containers near sources of strong electrical fields (such as above a CRT).
- (6) When storing printed circuit boards which have devices mounted on them, use a board container or bag that's protected against static charge. To avoid the occurrence of static charge or discharge due to friction, keep the boards separate from one other and do not stack them directly on top of one another.
- (7) Ensure, if possible, that any articles (such as clipboards) which are brought to any location where the level of static electricity must be closely controlled are constructed of anti-static materials.
- (8) In cases where the human body comes into direct contact with a device, be sure to wear anti-static finger covers or gloves (suggested resistance value:  $10^8\Omega$  or less).
- (9) Equipment safety covers installed near devices should have resistance ratings of  $10^9\Omega$  or less.
- (10) If a wrist strap cannot be used for some reason, and there is a possibility of imparting friction to devices, use an ionizer.

#### **CONFIDENTIALITY OBLIGATIONS:**

This document contains sensitive information and classified "CONFIDENTIAL".

Please make sure you should comply with the following security rules at all times

Do not copy or reproduce all or part of this document and further copies can be provided on a "need to know basis", please contact your local Starpower sales office.

#### PLEASE READ CAREFULLY:

Starpower reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at anytime, without notice. Starpower assumes no liability whatsoever relating to the choice, selection or use of the Starpower products and services described herein.

And purchasers are solely responsible for the choice, selection and use of the Starpower products and services described herein, No license, express or implied, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by Starpower for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein. Unless otherwise set forth in Starpower terms and conditions of sale Starpower disclaims any express or implied warranty with respect to the use and/or sale of Starpower products including without limitation implied warranties of merchantability, fitness for a particular purpose (and their equivalents under the laws of any jurisdiction), or infringement of any patent, copyright or other intellectual property right. Unless expressly approved in writing by an authorized Starpower representative, Starpower products are not recommended, authorized or warranted for use in military, air craft, space, life saving, or life sustaining applications, nor in products or systems where failure or malfunction may result in personal injury, death, or severe property or environmental damage.

Information in this document supersedes and replaces all information previously supplied. www.powersemi.cc