

Notice for TAIYO YUDEN products

Please read this notice before using the TAIYO YUDEN products.

/!\ REMINDERS

Product Information in this Catalog

Product information in this catalog is as of October 2019. All of the contents specified herein and production status of the products listed in this catalog are subject to change without notice due to technical improvement of our products, etc. Therefore, please check for the latest information carefully before practical application or use of our products.

Please note that TAIYO YUDEN shall not be in any way responsible for any damages and defects in products or equipment incorporating our products, which are caused under the conditions other than those specified in this catalog or individual product specification sheets.

Approval of Product Specifications

Please contact TAIYO YUDEN for further details of product specifications as the individual product specification sheets are available. When using our products, please be sure to approve our product specifications or make a written agreement on the product specification with TAIYO YUDEN in advance.

Pre-Evaluation in the Actual Equipment and Conditions

Please conduct validation and verification of our products in actual conditions of mounting and operating environment before using our products.

Limited Application

1. Equipment Intended for Use

The products listed in this catalog are intended for generalpurpose and standard use in general electronic equipment (e.g., AV equipment, OA equipment, home electric appliances, office equipment, information and communication equipment including, without limitation, mobile phone, and PC) and other equipment specified in this catalog or the individual product specification sheets.

TAIYO YUDEN has the line-up of the products intended for use in automotive electronic equipment, telecommunications infrastructure and industrial equipment, or medical devices classified as GHTF Classes A to C (Japan Classes I to III). Therefore, when using our products for these equipment, please check available applications specified in this catalog or the individual product specification sheets and use the corresponding products.

2. Equipment Requiring Inquiry

Please be sure to contact TAIYO YUDEN for further information before using the products listed in this catalog for the following equipment (excluding intended equipment as specified in this catalog or the individual product specification sheets) which may cause loss of human life, bodily injury, serious property damage and/or serious public impact due to a failure or defect of the products and/or malfunction attributed thereto.

- (1) Transportation equipment (automotive powertrain control system, train control system, and ship control system, etc.)
- (2) Traffic signal equipment
- (3) Disaster prevention equipment, crime prevention equipment
- (4) Medical devices classified as GHTF Class C (Japan Class III)
- (5) Highly public information network equipment, dataprocessing equipment (telephone exchange, and base station, etc.)
- (6) Any other equipment requiring high levels of quality and/or reliability equal to the equipment listed above

3. Equipment Prohibited for Use

Please do not incorporate our products into the following equipment requiring extremely high levels of safety and/or reliability.

- (1) Aerospace equipment (artificial satellite, rocket, etc.)
- (2) Aviation equipment *1
- (3) Medical devices classified as GHTF Class D (Japan Class IV), implantable medical devices *2

- (4) Power generation control equipment (nuclear power, hydroelectric power, thermal power plant control system, etc.)
- (5) Undersea equipment (submarine repeating equipment, underwater work equipment, etc.)
- (6) Military equipment
- (7) Any other equipment requiring extremely high levels of safety and/or reliability equal to the equipment listed above

*Notes:

- 1. There is a possibility that our products can be used only for aviation equipment that does not directly affect the safe operation of aircraft (e.g., in-flight entertainment, cabin light, electric seat, cooking equipment) if such use meets requirements specified separately by TAIYO YUDEN. Please be sure to contact TAIYO YUDEN for further information before using our products for such aviation equipment.
- Implantable medical devices contain not only internal unit which is implanted in a body, but also external unit which is connected to the internal unit.

4. Limitation of Liability

Please note that unless you obtain prior written consent of TAIYO YUDEN, TAIYO YUDEN shall not be in any way responsible for any damages incurred by you or third parties arising from use of the products listed in this catalog for any equipment that is not intended for use by TAIYO YUDEN, or any equipment requiring inquiry to TAIYO YUDEN or prohibited for use by TAIYO YUDEN as described above.

Safety Design

When using our products for high safety and/or reliability-required equipment or circuits, please fully perform safety and/or reliability evaluation. In addition, please install (i) systems equipped with a protection circuit and a protection device and/or (ii) systems equipped with a redundant circuit or other system to prevent an unsafe status in the event of a single fault for a failsafe design to ensure safety.

Intellectual Property Rights

Information contained in this catalog is intended to convey examples of typical performances and/or applications of our products and is not intended to make any warranty with respect to the intellectual property rights or any other related rights of TAIYO YUDEN or any third parties nor grant any license under such rights.

Limited Warranty

Please note that the scope of warranty for our products is limited to the delivered our products themselves and TAIYO YUDEN shall not be in any way responsible for any damages resulting from a failure or defect in our products. Notwithstanding the foregoing, if there is a written agreement (e.g., supply and purchase agreement, quality assurance agreement) signed by TAIYO YUDEN and your company, TAIYO YUDEN will warrant our products in accordance with such agreement

■ TAIYO YUDEN's Official Sales Channel

The contents of this catalog are applicable to our products which are purchased from our sales offices or authorized distributors (hereinafter "TAIYO YUDEN's official sales channel"). Please note that the contents of this catalog are not applicable to our products purchased from any seller other than TAIYO YUDEN's official sales channel.

Caution for Export

Some of our products listed in this catalog may require specific procedures for export according to "U.S. Export Administration Regulations", "Foreign Exchange and Foreign Trade Control Law" of Japan, and other applicable regulations. Should you have any questions on this matter, please contact our sales staff.

MULTILAYER CERAMIC CAPACITORS

MULTILAYER CERAMIC CAPACITORS



WAVE R

■PARTS NUMBER

			_		_		_	-			•					_
J	М	K	3	1	6	Δ	В	J	1	0	6	М	L	_	I	Δ
1	2	3		4		(5)	(6	3)		7		8	9	10	11)	12

(1)Rated	VO	ltaa	۵.
(I)Rateu	VO	ILag	æ

Code	Rated voltage[VDC]
Р	2.5
Α	4
J	6.3
L	10
E	16
Т	25
G	35
U	50
Н	100
Q	250
S	630
Х	2000

Series name

Z Series name	
Code	Series name
М	Multilayer ceramic capacitor
V	Multilayer ceramic capacitor for high frequency
W	LW reverse type multilayer capacitor

3End termination

Code	End termination
K	Plated
S	Cu Internal Electrodes (For High Frequency)

△=Blank space

4 Dimension (L × W)

4)Dimension (L × W)						
Туре	Dimensions (L×W)[mm]	EIA (inch)				
021	0.25 × 0.125	008004				
042	0.4 × 0.2	01005				
063	0.6 × 0.3	0201				
105	1.0 × 0.5	0402				
105	0.52 × 1.0 ※	0204				
107	1.6 × 0.8	0603				
107	0.8 × 1.6 ※	0306				
010	2.0 × 1.25	0805				
212	1.25 × 2.0 💥	0508				
316	3.2 × 1.6	1206				
325	3.2 × 2.5	1210				
432	4.5 × 3.2	1812				
	(=)					

5 Dimension tolerance

Code		L[mm]	W[mm]	T[mm]
	Туре			
	ALL	Standard	Standard	Standard
	063	0.6±0.05	0.3±0.05	0.3±0.05
	105	1.0±0.10	0.5±0.10	0.5±0.10
	107	1.6+0.15/-0.05	0.8+0.15/-0.05	0.8+0.15/-0.05
				0.45±0.05
Α	212	2.0+0.15/-0.05	1.25+0.15/-0.05	0.85±0.10
				1.25+0.15/-0.05
	316	3.2±0.20	1.6±0.20	0.85±0.10
	310	3.2 ± 0.20	1.0 ± 0.20	1.6±0.20
	325	3.2±0.30	2.5±0.30	2.5±0.30
	063	0.6±0.09	0.3±0.09	0.3±0.09
	105	1.0+0.15/-0.05	0.5+0.15/-0.05	0.5+0.15/-0.05
	107	1.6+0.20/-0	0.8+0.20/-0	0.45±0.05
В	107	1.0 + 0.20/ - 0	0.8 + 0.20/ - 0	0.8+0.20/-0
ь				0.45±0.05
	212	2.0+0.20/-0	1.25+0.20/-0	0.85±0.10
				1.25+0.20/-0
	316	3.2±0.30	1.6±0.30	1.6±0.30
С	105	1.0+0.20/-0	0.5+0.20/-0	0.5+0.20/-0
	063	0.6 + 0.25/- 0	0.3 + 0.25/- 0	0.3 + 0.25/ - 0
Е	105	1.0+0.30/-0	0.5+0.30/-0	0.5+0.30/-0

Note: cf. STANDARD EXTERNAL DIMENSIONS

Δ= Blank space

6Temperature characteristics code

■ High dielectric type (Excluding Super low distortion multilayer ceramic capacitor)

Code	Applicable standard		Temperature range[°C]	Ref. Temp.[°C]	Capacitance change	Capacitance tolerance	Tolerance code					
	JIS	В	-25 ~ + 85	20	±10%	±10%	K					
BJ	JIS	Ь	-25° + 65	20	± 10%	±20%	М					
ь	EIA	X5R	-55 ~ + 85	25	±15%	±10%	K					
	EIA	A ASK	_55~+ 85			±20%	М					
В7	EIA	X7R	V7D	V7D	Y7D	EIA V7D	V7D	-55 ~ +125	25	±15%	±10%	K
			33.9 T 123	25	±1570	±20%	М					
C6	EIA	EIA X6S	−55~+105	25	±22%	±10%	K					
						±20%	М					
C7	EIA	X7S	-55 ~ +125	25	±22%	±10%	K					
07	EIA	A/3	-55° +125	25	1 22 70	±20%	М					
1.0(\)		VED	FF. 1 0F	0.5	1.150/	±10%	К					
LD(※)	EIA X5	X5R −55~+	−55~+ 85	25	±15%	±20%	М					

Note : $\mbox{\ensuremath{\&.}LD}$ Low distortion high value multilayer ceramic capacitor

Δ= Blank space

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

for General Electronic Equipment

■Temperature compensating type

Code	Applicable standard		Temperature range[°C]	Ref. Temp.[°C]	Capacitance change	Capacitance tolerance	Tolerance code
			_			±0.05pF	Α
						±0.1pF	В
CG	EIA	C0G	-55 ~ +125	25	0 ± 30 ppm/°C	±0.25pF	С
						±0.5pF	D
						±5%	J
	JIS	UJ		20		±0.25pF	С
UJ	JIS	UJ	-55 ~ +125	20	$-750 \pm 120 \text{ppm/}^{\circ}\text{C}$	±0.5pF	D
	EIA	U2J		25		±5%	J
UK	JIS	UK	−55~+125	20	-750+250nnm/°C	±0.255E	С
UK	EIA U2K	U2K	-55~+125	25	−750±250ppm/°C	±0.25pF	

6 Series code

· Super low distortion multilayer ceramic capacitor

	·
Code	Series code
SD	Standard

• Medium-High Voltage Multilayer Ceramic Capacitor

Code	Series code
SD	Standard

Nominal capacitance

Code (example)	Nominal capacitance
0R5	0.5pF
010	1pF
100	10pF
101	100pF
102	1,000pF
103	10,000pF
104	0.1 <i>μ</i> F
105	1.0 <i>μ</i> F
106	10 μ F
107	100 μ F

Note: R=Decimal point

8Capacitance tolerance

Code	Capacitance tolerance
Α	±0.05pF
В	±0.1pF
С	±0.25pF
D	±0.5pF
F	±1pF
G	±2%
J	±5%
K	±10%
М	±20%
Z	+80/-20%

Thickness

Code	Thickness[mm]
K	0.125
Н	0.13
E	0.18
С	0.2
D	0.2
Р	0.2
Т	0.3
K	0.45(107type or more)
V	0.5
W	0.5
Α	0.8
D	0.85(212type or more)
F	1.15
G	1.25
L	1.6
N	1.9
Υ	2.0 max
М	2.5

10Special code

Code	Special code
_	Standard


11)Packaging


Packaging
ϕ 178mm Taping (2mm pitch)
ϕ 178mm Taping (4mm pitch)
\$\phi\$178mm Taping (4mm pitch, 1000 pcs/reel)
325 type (Thickness code M)
\$\phi\$178mm Taping (2mm pitch)105type only
(Thickness code E,H)
ϕ 178mm Taping(1mm pitch)021/042type only

12Internal code

UZINCENIAI COUE	
Code	Internal code
Δ	Standard

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).





LW reverse type

T/ FIA \		D	imension [mm]			
Type(EIA)	L	W	Т	*1	е	
□MK021 (008004)	0.25±0.013	0.125±0.013	0.125±0.013	K	0.0675±0.0275	
□VS021 (008004)	0.25±0.013	0.125±0.013	0.125±0.013	K	0.0675±0.0275	
□MK042(01005)	0.4±0.02	0.2±0.02	0.2±0.02	C D	0.1±0.03	
□VS042(01005)	0.4±0.02	0.2±0.02	0.2±0.02	С	0.1±0.03	
□MK063(0201)	0.6±0.03	0.3±0.03	0.3±0.03	P T	0.15±0.05	
			0.13±0.02	Н		
			0.18±0.02	Е		
☐MK105(0402)	1.0±0.05	0.5±0.05	0.2±0.02	С	0.25±0.10	
			0.3 ± 0.03	Р		
			0.5±0.05	٧		
□VK105(0402)	1.0±0.05	0.5±0.05	0.5±0.05	W	0.25±0.10	
□WK105(0204)※	0.52±0.05	1.0±0.05	0.3±0.05	Р	0.18±0.08	
□MK107(0603)	1.6±0.10	0.8±0.10	0.45±0.05	K	0.35±0.25	
□MK107(0003)	1.0 ± 0.10	0.6 ± 0.10	0.8 ± 0.10	Α	0.35±0.25	
□WK107(0306)※	0.8±0.10	1.6±0.10	0.5 ± 0.05	٧	0.25±0.15	
			0.45±0.05	K		
□MK212(0805)	2.0±0.10	1.25±0.10	0.85 ± 0.10	D	0.5 ± 0.25	
			1.25±0.10	G		
□WK212(0508)※	1.25±0.15	2.0±0.15	0.85 ± 0.10	D	0.3±0.2	
<u> </u>			0.85±0.10	D		
□MK316(1206)	3.2±0.15	1.6±0.15	1.15±0.10	F	0.5 + 0.35 / -0.25	
			1.6±0.20	L		
<u> </u>			0.85±0.10	D		
			1.15±0.10	F		
□MK325(1210)	3.2±0.30	2.5±0.20	1.9±0.20	N	0.6 ± 0.3	
			1.9+0.1/-0.2	Υ		
			2.5±0.20	М		
□MK432(1812)	45+040	3.2±0.30	2.0+0/-0.30	Υ	0.6±0.4	
□IVIN432(1812)	4.5±0.40	3.2±0.30	2.5±0.20	М	0.9±0.6	

Note: X. LW reverse type, *1.Thickness code

STANDARD QUANTITY

т	FIA (in ala)	Din	nension	Standard of	quantity[pcs]	
Туре	EIA (inch)	[mm]	Code	Paper tape	Embossed tape	
021	008004	0.125	К	_	50000	
042	01005	0.2	С	_	40000	
042	01003	0.2	D		40000	
063	0201	0.3	Р	15000	_	
003	0201	0.3	Т	13000		
		0.13	Н	_	20000	
		0.18	Е	_	15000	
	0402	0.2	С	20000	_	
105	0402	0.3	Р	15000	_	
		0.5	V			
		0.5	W	10000	_	
	0204 ※	0.30	Р			
	0603	0.45	K	4000	_	
107	0003	0.8	A	4000	_	
	0306 ※	0.50	V	_	4000	
		0.45	K	4000	_	
212	0805	0.85	D	4000		
212		1.25	G	_	3000	
	0508 ※	0.85	D	4000	_	
		0.85	D	4000	_	
316	1206	06 1.15		_	3000	
		1.6	L	_	2000	
		0.85	D			
		1.15	F	T _	2000	
325		1.9	N	7 -	2000	
		2.0 max	Y	7		
		2.5	M	_	1000	
420	1010	2.0 max	Y	_	1000	
432	1812	2.5	M	_	500	

Note : ※.LW Reverse type(□WK)

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

MULTILAYER CERAMIC CAPACITORS

Multilayer Ceramic Capacitors for High Frequency Applications (1GHz+)

021TYPE

[Temperature Characteristic CG: CG/C0G($-55\sim+125^{\circ}$ C)] 0.125mm thickness(K)

Visit Visi	Temperature Charac		Rated voltage	Tempe		Capacitance		Q (at 1GHz)	HTLT	Thickness*3 [mm]	Soldering R:Reflow
Trigon Colories	Part number 1	Part number 2	[V]	charact	eristics		Capacitance tolerance		Rated voltage x %	Thickness [mm]	W:Wave
TYSSIC CONTRILLER											R
Trigger Color Trigger Trig											R
Trops:											R
TYSSET COUNTY TYSSET COUNT											R
TYSSET COUNTY FOR TYSSET COUNTY TYSSET			-								R R
TYSSIC COLINE]N-W			1								R
TYSSEL COLINY -W											R
TYSSED COUNTY No.			1								R
TYROSIC CORRESTIVE W OC. COD. 2 p. ±006pf. ±01pf. ±026pf. 160 200 0.132±0.013 TYROSIC CORRESTIVE W OC. COD. 22 p. ±006pf. ±01pf. ±026pf. 160 200 0.132±0.013 TYROSIC CORRESTIVE W OC. COD. 22 p. ±006pf. ±01pf. ±026pf. 160 200 0.122±0.013 TYROSIC CORRESTIVE W OC. COD. 22 p. ±006pf. ±01pf. ±026pf. 160 200 0.122±0.013 TYROSIC CORRESTIVE W OC. COD. 22 p. ±006pf. ±01pf. ±026pf. 160 200 0.123±0.013 TYROSIC CORRESTIVE W OC. COD. 25 p. ±006pf. ±01pf. ±026pf. 160 200 0.123±0.013 TYROSIC CORRESTIVE W OC. COD. 25 p. ±006pf. ±01pf. ±026pf. 160 200 0.123±0.013 TYROSIC CORRESTIVE W OC. COD. 27 p. ±006pf. ±01pf. ±026pf. 160 200 0.123±0.013 TYROSIC CORRESTIVE W OC. COD. 32 p. ±006pf. ±01pf. ±026pf. 160 200 0.123±0.013 TYROSIC CORRESTIVE W OC. COD. 32 p. ±006pf. ±01pf. ±026pf. 160 200 0.123±0.013 TYROSIC CORRESTIVE W OC. COD. 32 p. ±006pf. ±01pf. ±026pf. 160 200 0.123±0.013 TYROSIC CORRESTIVE W OC. COD. 32 p. ±006pf. ±01pf. ±026pf. ±006pf. 160 200 0.123±0.013 TYROSIC CORRESTIVE W OC. COD. 32 p. ±006pf. ±01pf. ±026pf. ±006pf. 160 200 0.123±0.013 TYROSIC CORRESTIVE W OC. COD. 33 p. ±01pf. ±026pf. ±006pf. 160 200 0.123±0.013 TYROSIC CORRESTIVE W OC. COD. 33 p. ±01pf. ±026pf. ±006pf. 160 200 0.123±0.013 TYROSIC CORRESTIVE W OC. COD. 33 p. ±01pf. ±026pf. ±006pf. 160 200 0.123±0.013 TYROSIC CORRESTIVE W OC. COD. 34 p. ±01pf. ±026pf. ±006pf. 160 200 0.123±0.013 TYROSIC CORRESTIVE W OC. COD. 44 p. ±01pf. ±026pf. ±006pf. 160 200 0.123±0.013 TYROSIC CORRESTIVE W OC. COD. 44 p. ±01pf. ±026pf. ±006pf. 160 200 0.123±0.013 TYROSIC CORRESTIVE W OC. COD. 44 p. ±01pf. ±026pf. ±006pf. 160 200 0.123±0.013 TYROSIC CORRESTIVE W OC. COD. 44 p. ±01pf. ±026pf. ±006pf. 160 200 0.123±0.013 TYROSIC CORRESTIVE W OC. COD. 44 p. ±01pf. ±026pf. ±006pf. 160 200 0.123±0.013 TYROSIC CORRESTIVE W OC. COD. 44 p. ±01pf. ±026pf. ±006pf. 160 200 0.123±0.013 TYROSIC CORRESTIVE W OC. COD. 44 p. ±01pf. ±026pf. ±006pf. 160 200 0.123±0.013 TYROSIC CORRESTIVE W OC. COD. 44 p. ±01pf. ±026pf. ±006pf. 160 200 0.123±0.013 TYROSIC CORRESTIVE W OC. COD.											R
TYSSED COSTRIB_F.W	VS021 CG1R9∏K-W			CG	COG	1.9 p	±0.05pF, ±0.1pF, ±0.25pF	170	200	0.125±0.013	R
TYSSET COMPRESS: W				CG	COG	2 p		160	200	0.125±0.013	R
TYSSED COSPIE]K-W											R
TYSSET COMPREM: W											R
TYSSET CORPS K-W											R
TYSSIC CORPRE K-W											R R
TYSSED COSTRES K-W			1								R
TYSSIT COLORIS K-W											R
TYSSET COLORES W			1								R
TYSSET CORREST. W											R
TVSS211 GGARR K-W			25	CG	COG	3 p		120	200	0.125±0.013	R
TVSS2IT COSSRB] K-W CG]	CG	C0G			110		0.125±0.013	R
TYSSET GGARGIN-W		<u>-</u>	1								R
TYSS2I COARRI[K-W TYSS2I COARR			1								R
TYSS21 CGASRI[IW TYSS21 CGASRI			4								R
TYSS21 CGARRIN-W TYSS22 CGARRIN-W TYSS22 CGARRIN-W TYSS22 CGARRIN-W TYSS22 CGAR			1								R
TYSSE1 COARROIN-W CG			1								R R
TYSQ12 GGSRB[N-W TYSQ12 GGSRB[N-W TYSQ12 GGSRB[N-W TYSQ12 GGSRB (1)N-W GG COG GG 4 p ± 0.1pf, ±0.25pf, ±0.3pf 90 200 0.125±0.013 TYSQ12 GGSRB[N-W TYSQ12 GGSRB[N-W TYSQ12 GGSRB (2)N-W GG COG 4 l p ± 0.1pf, ±0.25pf, ±0.3pf 90 200 0.125±0.013 TYSQ12 GGSRB (2)N-W GG COG 4 2 p ± 0.1pf, ±0.25pf, ±0.3pf 90 200 0.125±0.013 TYSQ12 GGSRB (2)N-W GG COG 4 2 p ± 0.1pf, ±0.25pf, ±0.3pf 90 200 0.125±0.013 TYSQ12 GGSRB (2)N-W GG COG 4 3 p ± 0.1pf, ±0.25pf, ±0.3pf 90 200 0.125±0.013 TYSQ12 GGSRB (2)N-W GG COG 4 4 p ± 0.1pf, ±0.25pf, ±0.3pf 90 200 0.125±0.013 TYSQ12 GGSRB (2)N-W GG COG 4 4 p ± 0.1pf, ±0.25pf, ±0.3pf 90 200 0.125±0.013 TYSQ12 GGSRB (2)N-W GG COG 4 4 p ± 0.1pf, ±0.25pf, ±0.3pf 80 200 0.125±0.013 TYSQ12 GGSRB (2)N-W GG COG 4 p ± 0.1pf, ±0.25pf, ±0.3pf 80 200 0.125±0.013 TYSQ12 GGSRB (2)N-W GG COG 4 p ± 0.1pf, ±0.25pf, ±0.3pf 80 200 0.125±0.013 TYSQ12 GGSRB (2)N-W GG COG 4 p ± 0.1pf, ±0.25pf, ±0.3pf 80 200 0.125±0.013 TYSQ12 GGSRB (2)N-W GG COG 4 p ± 0.1pf, ±0.25pf, ±0.3pf 80 200 0.125±0.013 TYSQ12 GGSRB (2)N-W GG COG 4 p ± 0.1pf, ±0.25pf, ±0.3pf 80 200 0.125±0.013 TYSQ12 GGSRB (2)N-W GG COG 5 p ± 0.1pf, ±0.25pf, ±0.3pf 80 200 0.125±0.013 TYSQ12 GGSRB (2)N-W GG COG 5 p ± 0.1pf, ±0.25pf, ±0.3pf 80 200 0.125±0.013 TYSQ12 GGSRB (2)N-W GG COG 5 p ± 0.1pf, ±0.25pf, ±0.3pf 80 200 0.125±0.013 TYSQ12 GGSRB (2)N-W GG COG 5 p ± 0.1pf, ±0.25pf, ±0.3pf 80 200 0.125±0.013 TYSQ12 GGSRB (2)N-W GG COG 5 p ± 0.1pf, ±0.25pf, ±0.3pf 80 200 0.125±0.013 TYSQ12 GGSRB (2)N-W GG COG 5 p ± 0.1pf, ±0.25pf, ±0.3pf 80 200 0.125±0.013 TYSQ12 GGSRB (2)N-W GG COG 5 p ± 0.1pf, ±0.25pf, ±0.3pf 70 200 0.125±0.013 TYSQ12 GGSRB (2)N-W GG COG 5 p ± 0.1pf, ±0.25pf, ±0.3pf 70 200 0.125±0.013 TYSQ12 GGSRB (2)N-W GG COG 6 p ± 0.1pf, ±0.25pf, ±0.3pf 70 200 0.125±0.013 TYSQ12 GGSRB (2)N-W GG COG 6 p ± 0.1pf, ±0.25pf, ±0.3pf 70 200 0.125±0.013 TYSQ12 GGSRB (2)N-W GG COG 6 p ± 0.1pf, ±0.25pf, ±0.3pf 70 200 0.125±0.013 TYSQ12 GGSRB (2)N-W GG COG 6 p ± 0.1pf, ±0.25pf, ±0.3pf 80 200 0.125±0.013 TYSQ12 GGSRB (2)N-W GG COG 6 p ± 0.1pf, ±0.25pf, ±0.3pf 80 200 0.125±			1								R
TYSS21 CGGAPQ N-W TYSS21 CGGAP			1								R
TYSS22 GGARD N-W TYSS2 GGARD N-W TYSS22 GGARD N-W TYSS22 GGARD N-W TYSS22 GGARD			1								R
TYSS21 CGARS K-W TYSS21											R
TYS921 CGARGIN-W TYS921	VS021 CG4R2∏K-W		1	CG	C0G	4.2 p		90	200	0.125±0.013	R
TYSQ21 CG4R5[K-W CG	VS021 CG4R3∏K-W			CG	COG		±0.1pF, ±0.25pF, ±0.5pF	90	200	0.125±0.013	R
TYSQ12 CG4F8[]K-W											R
TYSQ21 CG4R7[]K-W											R
TYSQ12 CG4R8 K-W											R
TYSQ12 CGGRR K-W											R
TYSQ12 CGSRI K-W			1								R R
TYSQ12 CGSRQIK-W CG											R
ENSO21 CGSR2IK-W ENSO21 CGSR4IK-W ENSO21 CGSR6IK-W ENSO21			1								R
EVSQ21 CGSRG K-W CG											R
EVSD21 CGSR6[]K-W CG	VS021 CG5R3∏K-W			CG	C0G	5.3 p	±0.1pF, ±0.25pF, ±0.5pF	70	200	0.125±0.013	R
EVSD21 CGSR8[]K-W]			5.4 p					R
EVS021 GGSR7[K-W CG											R
EVSD21 GGSR8 K-W											R
EVSD21 GG8F8 [K-W CG CGG 5.9 p ±0.1pF, ±0.25pF, ±0.5pF 70 200 0.125±0.013 EVSD21 GG8R1 [K-W CG CGG 6.1 p ±0.1pF, ±0.25pF, ±0.5pF 70 200 0.125±0.013 EVSD21 GG8R3 [K-W CGG CGG 6.1 p ±0.1pF, ±0.25pF, ±0.5pF 70 200 0.125±0.013 EVSD21 GG8R3 [K-W CGG CGG 6.2 p ±0.1pF, ±0.25pF, ±0.5pF 60 200 0.125±0.013 EVSD21 GG8R4 [K-W CGG CGG 6.3 p ±0.1pF, ±0.25pF, ±0.5pF 60 200 0.125±0.013 EVSD21 GG8R6 [K-W CGG CGG 6.4 p ±0.1pF, ±0.25pF, ±0.5pF 60 200 0.125±0.013 EVSD21 GG8R6 [K-W CGG CGG 6.5 p ±0.1pF, ±0.25pF, ±0.5pF 60 200 0.125±0.013 EVSD21 GG8R6 [K-W CGG CGG 6.5 p ±0.1pF, ±0.25pF, ±0.5pF 60 200 0.125±0.013 EVSD21 GG8R8 [K-W CGG CGG 6.5 p ±0.1pF, ±0.25pF, ±0.5pF 60 200 0.125±0.013 EVSD21 GG8R8 [K-W CGG CGG 6.5 p ±0.1pF, ±0.25pF, ±0.5pF 60 200 0.125±0.013 EVSD21 GG8R8 [K-W CGG CGG 6.5 p ±0.1pF, ±0.25pF, ±0.5pF 60 200 0.125±0.013 EVSD21 GG8R8 [K-W CGG											R
EVS021 GG80E K-W CG			1								R R
EVS021 CG6R1											R
EVS021 CG6R2 K-W CG			1								R
EVS021 CG6R4 K-W								60			R
EVS021 CG6R6]K-W	/S021 CG6R3∏K-W			CG	C0G	6.3 p	±0.1pF, ±0.25pF, ±0.5pF	60	200	0.125±0.013	R
EVS021 CG6R6 K-W CG	/S021 CG6R4∏K-W			CG	COG	6.4 p	±0.1pF, ±0.25pF, ±0.5pF	60	200	0.125±0.013	R
EVS021 CG6R7 K-W CG											R
EVS021 CG6R8 K-W CG COG 6.8 p ±0.1pF, ±0.25pF, ±0.5pF 60 200 0.125±0.013 EVS021 CG0R9 K-W CG COG 6.9 p ±0.1pF, ±0.25pF, ±0.5pF 60 200 0.125±0.013 EVS021 CG7R1 K-W CG COG 7 p ±0.1pF, ±0.25pF, ±0.5pF 60 200 0.125±0.013 EVS021 CG7R3 K-W CG COG 7.2 p ±0.1pF, ±0.25pF, ±0.5pF 60 200 0.125±0.013 EVS021 CG7R3 K-W CG COG 7.2 p ±0.1pF, ±0.25pF, ±0.5pF 60 200 0.125±0.013 EVS021 CG7R5 K-W CG COG 7.4 p ±0.1pF, ±0.25pF, ±0.5pF 60 200 0.125±0.013 EVS021 CG7R6 K-W CG COG 7.4 p ±0.1pF, ±0.25pF, ±0.5pF 60 200 0.125±0.013 EVS021 CG7R6 K-W CG COG 7.6 p ±0.1pF, ±0.25pF, ±0.5pF 60 200 0.125±0.013 EVS021 CG7R6 K-W CG COG 7.6 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.			4								R
EVS021 CG6R9 □ K - W EVS021 CG070 □ K - W EVS021 CG7R1 □ K - W EVS021 CG7R2 □ K - W EVS021 CG7R3 □ K - W EVS021 CG7R5 □ K - W EVS021 CG7R6 □ K - W EVS021 CG7R7 □ K - W EVS021 CG7R6 □ K - W EVS021 CG7R7 □ K - W EVS021 C			4								R R
EVS021 CG070 □K-W EVS021 CG7R1 □K-W EVS021 CG7R2 □K-W EVS021 CG7R3 □K-W EVS021 CG7R3 □K-W EVS021 CG7R3 □K-W EVS021 CG7R3 □K-W EVS021 CG7R5 □K-W EVS021 CG7R5 □K-W EVS021 CG7R6 □K-W EVS021 CG7R7 □K-W EVS021 CG7R7 □K-W EVS021 CG7R6 □K-W EVS021 CG7R6 □K-W EVS021 CG7R7 □K-W EVS021 CG7R			1								R
To EVS021 CG7R1 K-W FVS021 CG7R2 K-W FVS021 CG7R2 K-W FVS021 CG7R3 K-W FVS021 CG7R3 K-W FVS021 CG7R3 K-W FVS021 CG7R5 K-W F			1								R
To To To To To To To To			1								R
EVS021 CG7R3 □K−W EVS021 CG7R4 □K−W EVS021 CG7R4 □K−W EVS021 CG7R5 □K−W EVS021 CG7R5 □K−W EVS021 CG7R6 □K−W EVS021 CG7R7 □K−W EVS021 CG7R □K−W EVS021 CG7R7 □K−W EVS021 CG7R7 □K−W EVS021 CG7R7 □K−W EVS021 CG7R □K−W EVS021 CG7R □K−W EVS021 CG7R7 □K−W EVS021 CG7R □K			1								R
EVS021 CG7R4 □K−W CG C0G 7.4 p ±0.1pF, ±0.25pF, ±0.5pF 60 200 0.125±0.013 EVS021 CG7R5 □K−W CG C0G 7.5 p ±0.1pF, ±0.25pF, ±0.5pF 60 200 0.125±0.013 EVS021 CG7R6 □K−W CG C0G 7.6 p ±0.1pF, ±0.25pF, ±0.5pF 60 200 0.125±0.013 EVS021 CG7R7 □K−W CG C0G 7.7 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG7R8 □K−W CG C0G 7.8 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG7R8 □K−W CG C0G 7.8 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG808 □K−W CG C0G 7.9 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG808 □K−W CG C0G 8 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG88 □K−W CG C0G 8.1 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG88 □K−W CG C0G 8.2 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R2 □K−W CG C0G 8.2 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R4 □K−W CG C0G 8.3 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R4 □K−W CG C0G 8.4 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R6 □K−W CG C0G 8.5 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R6 □K−W CG C0G 8.5 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R6 □K−W CG C0G 8.6 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R6 □K−W CG C0G 8.6 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R8 □K−W CG C0G 8.6 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R8 □K−W CG C0G 8.6 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R8 □K−W CG C0G 8.6 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R8 □K−W CG C0G 8.8 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R8 □K−W CG C0G 8.8 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R8 □K−W			16								R
EVS021 CG7R6 □K-W CG C0G 7.6 p ±0.1pF, ±0.25pF, ±0.5pF 60 200 0.125±0.013 EVS021 CG7R7 □K-W CG C0G 7.7 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG7R9 □K-W CG C0G 7.8 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG7R9 □K-W CG C0G 7.9 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R1 □K-W CG C0G 8 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R3 □K-W CG C0G 8.1 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R3 □K-W CG C0G 8.2 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R4 □K-W CG C0G 8.3 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R5 □K-W CG C0G 8.4 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013	VS021 CG7R4∏K-W]	CG	C0G	7.4 p		60			R
EVS021 CG7R7[K-W CG C0G 7.7 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG7R8[K-W CG C0G 7.8 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG7R9[K-W CG C0G 7.9 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG800[K-W CG C0G 8 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R1[K-W CG C0G 8.1 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R2[K-W CG C0G 8.1 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R3[K-W CG C0G 8.2 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R3[K-W CG C0G 8.3 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R4[K-W CG C0G 8.4 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R6[K-W CG C0G 8.5 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R5[K-W CG C0G 8.5 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R5[K-W CG C0G 8.5 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R7[K-W CG C0G 8.5 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R7[K-W CG C0G 8.7 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R8[K-W CG C0G 8.8 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R8[K-W CG C0G 8.8 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R8[K-W CG C0G 8.8 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R8[K-W CG C0G 8.8 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R8[K-W CG C0G S8.8 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013]								R
EVS021 CG7R8 □K-W CG COG 7.8 p ±0.1 pF, ±0.25 pF, ±0.5 pF 50 200 0.125±0.013 EVS021 CG7R9 □K-W CG COG 7.9 p ±0.1 pF, ±0.25 pF, ±0.5 pF 50 200 0.125±0.013 EVS021 CG808 □K-W CG COG 8 p ±0.1 pF, ±0.25 pF, ±0.5 pF 50 200 0.125±0.013 EVS021 CG8R2 □K-W CG COG 8.1 p ±0.1 pF, ±0.25 pF, ±0.5 pF 50 200 0.125±0.013 EVS021 CG8R3 □K-W CG COG 8.2 p ±0.1 pF, ±0.25 pF, ±0.5 pF 50 200 0.125±0.013 EVS021 CG8R4 □K-W CG COG 8.3 p ±0.1 pF, ±0.25 pF, ±0.5 pF 50 200 0.125±0.013 EVS021 CG8R6 □K-W CG COG 8.4 p ±0.1 pF, ±0.25 pF, ±0.5 pF 50 200 0.125±0.013 EVS021 CG8R7 □K-W CG COG 8.5 p ±0.1 pF, ±0.25 pF, ±0.5 pF 50 200 0.125±0.013 EVS021 CG8R7 □K-W CG COG 8.6 p ±0.1 pF, ±0.25 pF, ±0.5 pF 50 200 </td <td></td> <td></td> <td>1 </td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td>R</td>			1								R
EVS021 CG7R9 □K−W CG C0G 7.9 p ±0.1 pF, ±0.25 pF, ±0.5 pF 50 200 0.125±0.013 EVS021 CG080 □K−W CG C0G 8 p ±0.1 pF, ±0.25 pF, ±0.5 pF 50 200 0.125±0.013 EVS021 CG8R1 □K−W CG C0G 8.1 p ±0.1 pF, ±0.25 pF, ±0.5 pF 50 200 0.125±0.013 EVS021 CG8R3 □K−W CG C0G 8.2 p ±0.1 pF, ±0.25 pF, ±0.5 pF 50 200 0.125±0.013 EVS021 CG8R4 □K−W CG C0G 8.3 p ±0.1 pF, ±0.25 pF, ±0.5 pF 50 200 0.125±0.013 EVS021 CG8R5 □K−W CG C0G 8.4 p ±0.1 pF, ±0.25 pF, ±0.5 pF 50 200 0.125±0.013 EVS021 CG8R6 □K−W CG COG 8.5 p ±0.1 pF, ±0.25 pF, ±0.5 pF 50 200 0.125±0.013 EVS021 CG8R7 □K−W CG COG 8.6 p ±0.1 pF, ±0.25 pF, ±0.5 pF 50 200 0.125±0.013 EVS021 CG8R8 □K−W CG COG 8.6 p ±0.1 pF, ±0.25 pF, ±0.5 pF 50 200 </td <td></td> <td></td> <td>1 </td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td>R</td>			1								R
EVS021 CG080			4								R
EVS021 CG8R1 K-W CG C0G 8.1 p ±0.1 pF, ±0.25 pF, ±0.5 pF 50 200 0.125±0.013 EVS021 CG8R2 K-W CG C0G 8.2 p ±0.1 pF, ±0.25 pF, ±0.5 pF 50 200 0.125±0.013 EVS021 CG8R4 K-W CG C0G 8.3 p ±0.1 pF, ±0.25 pF, ±0.5 pF 50 200 0.125±0.013 EVS021 CG8R4 K-W CG C0G 8.4 p ±0.1 pF, ±0.25 pF, ±0.5 pF 50 200 0.125±0.013 EVS021 CG8R6 K-W CG C0G 8.5 p ±0.1 pF, ±0.25 pF, ±0.5 pF 50 200 0.125±0.013 EVS021 CG8R6 K-W CG COG 8.6 p ±0.1 pF, ±0.25 pF, ±0.5 pF 50 200 0.125±0.013 EVS021 CG8R8 K-W CG CG CG 8.7 p ±0.1 pF, ±0.25 pF, ±0.5 pF 50 200 0.125±0.013 EVS021 CG8R8 K-W CG CG CG 8.8 p ±0.1 pF, ±0.25 pF, ±0.5 pF 50 200 0.125±0.013 EVS021 CG8R8 K-W CG CG CG R.8 p ±			1								R R
EVS021 CG8R2 □K-W CG COG 8.2 p ±0.1 pF, ±0.25 pF, ±0.5 pF 50 200 0.125±0.013 EVS021 CG8R3 □K-W CG COG 8.3 p ±0.1 pF, ±0.25 pF, ±0.5 pF 50 200 0.125±0.013 EVS021 CG8R4 □K-W CG COG 8.4 p ±0.1 pF, ±0.25 pF, ±0.5 pF 50 200 0.125±0.013 EVS021 CG8R6 □K-W CG COG 8.5 p ±0.1 pF, ±0.25 pF, ±0.5 pF 50 200 0.125±0.013 EVS021 CG8R6 □K-W CG COG 8.6 p ±0.1 pF, ±0.25 pF, ±0.5 pF 50 200 0.125±0.013 EVS021 CG8R7 □K-W CG COG 8.7 p ±0.1 pF, ±0.25 pF, ±0.5 pF 50 200 0.125±0.013 EVS021 CG8R8 □K-W CG COG 8.8 p ±0.1 pF, ±0.25 pF, ±0.5 pF 50 200 0.125±0.013			1								R
EVS021 CG8R3 □ K−W CG COG 8.3 p ± 0.1 pF, ± 0.25 pF, ± 0.5 pF 50 200 0.125±0.013 EVS021 CG8R4 □ K−W CG COG 8.4 p ± 0.1 pF, ± 0.25 pF, ± 0.5 pF 50 200 0.125±0.013 EVS021 CG8R5 □ K−W CG COG 8.5 p ± 0.1 pF, ± 0.25 pF, ± 0.5 pF 50 200 0.125±0.013 EVS021 CG8R6 □ K−W CG COG 8.6 p ± 0.1 pF, ± 0.25 pF, ± 0.5 pF 50 200 0.125±0.013 EVS021 CG8R7 □ K−W CG COG 8.7 p ± 0.1 pF, ± 0.25 pF, ± 0.5 pF 50 200 0.125±0.013 EVS021 CG8R8 □ K−W CG COG 8.8 p ± 0.1 pF, ± 0.25 pF, ± 0.5 pF 50 200 0.125±0.013			1								R
EVS021 CG8R4[K-W CG C0G 8.4 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R5[K-W CG C0G 8.5 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R6[K-W CG C0G 8.6 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R7[K-W CG C0G 8.6 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R8[K-W CG C0G 8.8 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013			1								R
EVS021 CG8R5[K-W CG C0G 8.5 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R6[K-W CG C0G 8.6 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R7[K-W CG C0G 8.7 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG8R8[K-W CG C0G 8.8 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013			1 !								R
$ \begin{array}{c ccccccccccccccccccccccccccccccccccc$]								R
EVS021 CG8R8[K-W]								R
			1								R
EVEN21 CC00001K-W			4								R
	/S021 CG8R9∏K-W		1	CG	COG	8.9 p	±0.1pF, ±0.25pF, ±0.5pF	50	200	0.125±0.013	R
EVS021 GG990[K-W			4								R
EVS021 CG9R1 [K-W CG C0G 9.1 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013 EVS021 CG9R2 [K-W CG C0G 9.2 p ±0.1pF, ±0.25pF, ±0.5pF 50 200 0.125±0.013			1								R R
EVS021 CG9R2[K-W			1								R

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

Part number 1	Part number 2	Rated voltage [V]		erature eristics	Capacitance [F]	Capacitance tolerance	Q (at 1GHz) (min)	HTLT Rated voltage x %	Thickness*3 [mm]	Soldering R:Reflow W:Wave
EVS021 CG9R4∏K-W			CG	C0G	9.4 p	±0.1pF, ±0.25pF, ±0.5pF	50	200	0.125±0.013	R
EVS021 CG9R5∏K-W			CG	COG	9.5 p	±0.1pF, ±0.25pF, ±0.5pF	50	200	0.125±0.013	R
EVS021 CG9R6∏K-W			CG	COG	9.6 p	±0.1pF, ±0.25pF, ±0.5pF	50	200	0.125±0.013	R
EVS021 CG9R7∏K-W		16	CG	COG	9.7 p	± 0.1 pF, ± 0.25 pF, ± 0.5 pF	50	200	0.125±0.013	R
EVS021 CG9R8∏K-W			CG	COG	9.8 p	± 0.1 pF, ± 0.25 pF, ± 0.5 pF	40	200	0.125±0.013	R
EVS021 CG9R9∏K-W			CG	COG	9.9 p	± 0.1 pF, ± 0.25 pF, ± 0.5 pF	40	200	0.125±0.013	R
EVS021 CG100[K-W			CG	COG	10 p	±2%, ±5%	50	200	0.125±0.013	R

●042TYPE

		Rated voltage		erature	Capacitance		Q	HTLT		Soldering
Part number 1	Part number 2	[V]		erature teristics	[F]	Capacitance tolerance	(at 1GHz)	Rated voltage x %	Thickness*3 [mm]	R:Reflow
VS042 CG010∏C-W			CG	COG	1 p	±0.05pF, ±0.1pF, ±0.25pF	(min) 300	200	0.2±0.02	W:Wave R
VS042 CG1R1 C-W		-	CG	COG	1.1 p	±0.05pF, ±0.1pF, ±0.25pF	280	200	0.2±0.02	R
VS042 CG1R2[]C-W		1	CG	COG	1.2 p	±0.05pF, ±0.1pF, ±0.25pF	270	200	0.2±0.02	R
VS042 CG1R3[]C-W			CG	C0G	1.3 p	±0.05pF, ±0.1pF, ±0.25pF	260	200	0.2±0.02	R
VS042 CG1R4[]C-W] [CG	C0G	1.4 p	±0.05pF, ±0.1pF, ±0.25pF	250	200	0.2±0.02	R
VS042 CG1R5∏C-W		.	CG	COG	1.5 p	± 0.05 pF, ± 0.1 pF, ± 0.25 pF	240	200	0.2±0.02	R
VS042 CG1R6[]C-W		.	CG	C0G	1.6 p	±0.05pF, ±0.1pF, ±0.25pF	230	200	0.2±0.02	R
VS042 CG1R7[]C-W		-	CG	COG	1.7 p	±0.05pF, ±0.1pF, ±0.25pF	220	200	0.2±0.02	R
TVS042 CG1R8∏C-W TVS042 CG1R9∏C-W		-	CG	COG	1.8 p	±0.05pF, ±0.1pF, ±0.25pF	210	200	0.2±0.02	R
rvs042 cgrk9∐c-w		1	CG	C0G C0G	1.9 p 2 p	±0.05pF, ±0.1pF, ±0.25pF ±0.05pF, ±0.1pF, ±0.25pF	200 190	200 200	0.2±0.02 0.2±0.02	R R
VS042 CG2R1[]C-W		1	CG	COG	2.1 p	±0.05pF, ±0.1pF, ±0.25pF	185	200	0.2±0.02	R
VS042 CG2R2[]C-W		1	CG	COG	2.2 p	±0.05pF, ±0.1pF, ±0.25pF	180	200	0.2±0.02	R
VS042 CG2R3∏C-W		1	CG	C0G	2.3 p	±0.05pF, ±0.1pF, ±0.25pF	175	200	0.2±0.02	R
VS042 CG2R4[]C-W			CG	C0G	2.4 p	±0.05pF, ±0.1pF, ±0.25pF	170	200	0.2±0.02	R
VS042 CG2R5∏C-W] [CG	C0G	2.5 p	±0.05pF, ±0.1pF, ±0.25pF	160	200	0.2±0.02	R
VS042 CG2R6[]C-W		」	CG	COG	2.6 p	± 0.05 pF, ± 0.1 pF, ± 0.25 pF	155	200	0.2±0.02	R
VS042 CG2R7[]C-W		4	CG	C0G	2.7 p	± 0.05 pF, ± 0.1 pF, ± 0.25 pF	150	200	0.2±0.02	R
VS042 CG2R8[]C-W		-	CG	COG	2.8 p	±0.05pF, ±0.1pF, ±0.25pF	140	200	0.2±0.02	R
TVS042 CG2R9∏C-W		-{	CG	C0G	2.9 p	±0.05pF, ±0.1pF, ±0.25pF	135 130	200	0.2±0.02	R R
VS042 CG030∏C-W VS042 CG3R1∏C-W		- 	CG	C0G C0G	3 p 3.1 p	±0.05pF, ±0.1pF, ±0.25pF ±0.1pF, ±0.25pF	125	200 200	0.2±0.02 0.2±0.02	R
VS042 CG3R1[]C-W		- 	CG	COG	3.1 p	±0.1pF, ±0.25pF ±0.1pF, ±0.25pF	125	200	0.2±0.02	R
TVS042 CG3R3∏C-W		-	CG	COG	3.3 p	±0.1pF, ±0.25pF	120	200	0.2±0.02	R
「VS042 CG3R4∏C-W		<u> </u>	CG	COG	3.4 p	±0.1pF, ±0.25pF	120	200	0.2±0.02	R
「VS042 CG3R5∏C-W] [CG	C0G	3.5 p	±0.1pF, ±0.25pF	110	200	0.2±0.02	R
rvs042 cg3R6∏c-w			CG	C0G	3.6 p	±0.1pF, ±0.25pF	110	200	0.2 ± 0.02	R
rvs042 cg3R7∏c-w		_	CG	COG	3.7 p	±0.1pF, ±0.25pF	110	200	0.2 ± 0.02	R
VS042 CG3R8[]C-W		4	CG	C0G	3.8 p	±0.1pF, ±0.25pF	100	200	0.2±0.02	R
VS042 CG3R9[]C-W		-	CG	COG	3.9 p	±0.1pF, ±0.25pF	100	200	0.2±0.02	R
VS042 CG040∏C-W		-	CG	COG	4 p	±0.1pF, ±0.25pF ±0.1pF, ±0.25pF	90	200	0.2±0.02	R
VS042 CG4R1∏C-W VS042 CG4R2∏C-W		-	CG	C0G C0G	4.1 p 4.2 p	±0.1pF, ±0.25pF ±0.1pF, ±0.25pF	90 85	200 200	0.2±0.02 0.2±0.02	R R
VS042 CG4R3[]C-W		 	CG	COG	4.2 p	±0.1pF, ±0.25pF	85	200	0.2±0.02	R
VS042 CG4R4[]C-W		1	CG	COG	4.4 p	±0.1pF, ±0.25pF	85	200	0.2±0.02	R
VS042 CG4R5[]C-W		1	CG	COG	4.5 p	±0.1pF, ±0.25pF	85	200	0.2±0.02	R
VS042 CG4R6∏C-W			CG	C0G	4.6 p	±0.1pF, ±0.25pF	85	200	0.2±0.02	R
ΓVS042 CG4R7∏C−W		25	CG	C0G	4.7 p	±0.1pF, ±0.25pF	85	200	0.2 ± 0.02	R
VS042 CG4R8[]C-W		」	CG	COG	4.8 p	±0.1pF, ±0.25pF	80	200	0.2±0.02	R
rVS042 CG4R9∏C-W		4	CG	COG	4.9 p	±0.1pF, ±0.25pF	80	200	0.2±0.02	R
VS042 CG050[C-W		4	CG	COG	5 p	±0.1pF, ±0.25pF	80	200	0.2±0.02	R
TVS042 CG5R1 ☐ C-W TVS042 CG5R2 ☐ C-W		-	CG	C0G C0G	5.1 p 5.2 p	±0.1pF, ±0.25pF, ±0.5pF ±0.1pF, ±0.25pF, ±0.5pF	75 75	200 200	0.2±0.02 0.2±0.02	R R
VS042 CG5R3[]C-W		1	CG	COG	5.2 p	±0.1pF, ±0.25pF, ±0.5pF	75	200	0.2±0.02	R
VS042 CG5R4[]C-W		1	CG	COG	5.4 p	±0.1pF, ±0.25pF, ±0.5pF	70	200	0.2±0.02	R
VS042 CG5R5∏C-W		1	CG	COG	5.5 p	±0.1pF, ±0.25pF, ±0.5pF	70	200	0.2±0.02	R
VS042 CG5R6∏C-W		1	CG	C0G	5.6 p	±0.1pF, ±0.25pF, ±0.5pF	70	200	0.2±0.02	R
VS042 CG5R7[]C−W			CG	C0G	5.7 p	±0.1pF, ±0.25pF, ±0.5pF	70	200	0.2±0.02	R
VS042 CG5R8[]C-W		_ [CG	C0G	5.8 p	±0.1pF, ±0.25pF, ±0.5pF	70	200	0.2±0.02	R
rVS042 CG5R9∏C−W		<u> </u>	CG	COG	5.9 p	±0.1pF, ±0.25pF, ±0.5pF	65	200	0.2±0.02	R
TVS042 CG060∏C-W		-	CG	COG	6 p	±0.1pF, ±0.25pF, ±0.5pF	65 65	200	0.2±0.02	R
VS042 CG6R1 C-W		-{	CG	C0G	6.1 p	±0.1pF, ±0.25pF, ±0.5pF	65	200	0.2±0.02	R
VS042 CG6R2□C-W VS042 CG6R3□C-W		-{	CG	C0G C0G	6.2 p 6.3 p	±0.1pF, ±0.25pF, ±0.5pF ±0.1pF, ±0.25pF, ±0.5pF	65 65	200 200	0.2±0.02 0.2±0.02	R R
VS042 CG6R3∏C-W VS042 CG6R4∏C-W		-	CG	COG	6.4 p	±0.1pF, ±0.25pF, ±0.5pF ±0.1pF, ±0.25pF, ±0.5pF	65	200	0.2±0.02 0.2±0.02	R
VS042 CG6R5[]C-W		- 	CG	COG	6.5 p	±0.1pF, ±0.25pF, ±0.5pF ±0.1pF, ±0.25pF, ±0.5pF	65	200	0.2±0.02	R
VS042 CG6R6[]C-W		-	CG	COG	6.6 p	±0.1pF, ±0.25pF, ±0.5pF	60	200	0.2±0.02	R
VS042 CG6R7[]C-W		7 I	CG	COG	6.7 p	±0.1pF, ±0.25pF, ±0.5pF	60	200	0.2±0.02	R
VS042 CG6R8[]C-W		j l	CG	C0G	6.8 p	±0.1pF, ±0.25pF, ±0.5pF	60	200	0.2±0.02	R
VS042 CG6R9[]C-W] [CG	C0G	6.9 p	±0.1pF, ±0.25pF, ±0.5pF	60	200	0.2±0.02	R
VS042 CG070∏C-W		_ [CG	C0G	7 p	±0.1pF, ±0.25pF, ±0.5pF	60	200	0.2±0.02	R
VS042 CG7R1[]C-W		_	CG	COG	7.1 p	±0.1pF, ±0.25pF, ±0.5pF	60	200	0.2±0.02	R
VS042 CG7R2[]C-W		⊣ ∣	CG	COG	7.2 p	±0.1pF, ±0.25pF, ±0.5pF	60	200	0.2±0.02	R
VS042 CG7R3[]C-W		- I	CG	COG	7.3 p	±0.1pF, ±0.25pF, ±0.5pF	55	200	0.2±0.02	R
VS042 CG7R4[]C-W		-{	CG	C0G	7.4 p 7.5 p	±0.1pF, ±0.25pF, ±0.5pF ±0.1pF, ±0.25pF, ±0.5pF	55 55	200	0.2±0.02	R
VS042 CG7R5 C-W VS042 CG7R6 C-W		-{	CG	C0G C0G	7.5 p	±0.1pF, ±0.25pF, ±0.5pF ±0.1pF, ±0.25pF, ±0.5pF	55 55	200 200	0.2±0.02 0.2±0.02	R R
VS042 CG7R6[]C-W		- 	CG	COG	7.6 p 7.7 p	±0.1pF, ±0.25pF, ±0.5pF ±0.1pF, ±0.25pF, ±0.5pF	55	200	0.2±0.02 0.2±0.02	R
VS042 CG7R7 C-W		- 	CG	COG	7.7 p	±0.1pF, ±0.25pF, ±0.5pF	55	200	0.2±0.02	R
VS042 CG7R9[]C-W		┥	CG	COG	7.0 p	±0.1pF, ±0.25pF, ±0.5pF	55	200	0.2±0.02	R
VS042 CG080∏C-W		1	CG	COG	8 p	±0.1pF, ±0.25pF, ±0.5pF	55	200	0.2±0.02	R
VS042 CG8R1[]C-W		1	CG	COG	8.1 p	±0.1pF, ±0.25pF, ±0.5pF	55	200	0.2±0.02	R
VS042 CG8R2[]C-W]	CG	C0G	8.2 p	±0.1pF, ±0.25pF, ±0.5pF	50	200	0.2±0.02	R
VS042 CG8R3[]C-W	· · · · · · · · · · · · · · · · · · ·	_j [CG	C0G	8.3 p	±0.1pF, ±0.25pF, ±0.5pF	50	200	0.2±0.02	R
VS042 CG8R4∏C-W	-	1	CG	COG	8.4 p	±0.1pF, ±0.25pF, ±0.5pF	50	200	0.2 ± 0.02	R

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

Part number 1	Part number 2	Rated voltage [V]		erature eristics	Capacitance [F]	Capacitance tolerance	Q (at 1GHz) (min)	HTLT Rated voltage x %	Thickness*3 [mm]	Soldering R:Reflow W:Wave
TVS042 CG8R5∏C-W			CG	COG	8.5 p	± 0.1 pF, ± 0.25 pF, ± 0.5 pF	50	200	0.2 ± 0.02	R
TVS042 CG8R6∏C-W			CG	COG	8.6 p	$\pm 0.1 pF$, $\pm 0.25 pF$, $\pm 0.5 pF$	50	200	0.2 ± 0.02	R
TVS042 CG8R7∏C-W			CG	COG	8.7 p	$\pm 0.1 pF$, $\pm 0.25 pF$, $\pm 0.5 pF$	50	200	0.2 ± 0.02	R
TVS042 CG8R8∏C-W			CG	COG	8.8 p	±0.1pF, ±0.25pF, ±0.5pF	50	200	0.2 ± 0.02	R
TVS042 CG8R9∏C-W			CG	COG	8.9 p	±0.1pF, ±0.25pF, ±0.5pF	50	200	0.2 ± 0.02	R
TVS042 CG090[]C-W			CG	COG	9 p	±0.1pF, ±0.25pF, ±0.5pF	50	200	0.2 ± 0.02	R
TVS042 CG9R1∏C-W			CG	COG	9.1 p	±0.1pF, ±0.25pF, ±0.5pF	45	200	0.2 ± 0.02	R
TVS042 CG9R2∏C-W			CG	COG	9.2 p	±0.1pF, ±0.25pF, ±0.5pF	45	200	0.2 ± 0.02	R
TVS042 CG9R3∏C-W			CG	COG	9.3 p	±0.1pF, ±0.25pF, ±0.5pF	45	200	0.2 ± 0.02	R
TVS042 CG9R4∏C-W			CG	COG	9.4 p	±0.1pF, ±0.25pF, ±0.5pF	45	200	0.2 ± 0.02	R
TVS042 CG9R5∏C-W			CG	C0G	9.5 p	±0.1pF, ±0.25pF, ±0.5pF	45	200	0.2±0.02	R
TVS042 CG9R6∏C-W		25	CG	C0G	9.6 p	±0.1pF, ±0.25pF, ±0.5pF	45	200	0.2±0.02	R
TVS042 CG9R7∏C-W			CG	C0G	9.7 p	±0.1pF, ±0.25pF, ±0.5pF	45	200	0.2±0.02	R
TVS042 CG9R8∏C-W			CG	C0G	9.8 p	±0.1pF, ±0.25pF, ±0.5pF	45	200	0.2±0.02	R
TVS042 CG9R9∏C-W			CG	C0G	9.9 p	±0.1pF, ±0.25pF, ±0.5pF	45	200	0.2±0.02	R
TVS042 CG100[]C-W			CG	C0G	10 p	±2%, ±5%	45	200	0.2±0.02	R
TVS042 CG110JC-W			CG	C0G	11 p	±5%	40	200	0.2±0.02	R
TVS042 CG120JC-W			CG	C0G	12 p	±5%	40	200	0.2±0.02	R
TVS042 CG130JC-W		1	CG	COG	13 p	±5%	40	200	0.2±0.02	R
TVS042 CG150JC-W		1	CG	COG	15 p	±5%	40	200	0.2±0.02	R
TVS042 CG160JC-W		1	CG	COG	16 p	±5%	40	200	0.2±0.02	R
TVS042 CG180JC-W		1	CG	COG	18 p	±5%	40	200	0.2±0.02	R
TVS042 CG220JC-W		1	CG	COG	22 p	±5%	30	200	0.2±0.02	R

●105TYPE

[Temperature Characteristic CG : CG/C0G(-55~+125°C)] 0.5mm thickness(W)

Part number 1	Part number 2	Rated voltage	Tempe		Capacitance	Capacitance tolerance	Q (at 1GHz)	HTLT	Thickness*3 [mm]	Soldering R:Reflow
T dre Hamber 1	Ture number 2	[V]	charact	eristics	[F]	Capacitarios tolorarios	(min)	Rated voltage x %	THICKNESS [IIIII]	W:Wave
EVK105 CG0R3BW-F			CG	C0G	0.3 p	±0.1pF	300	200	0.5 ± 0.05	R
EVK105 CG0R4BW-F			CG	COG	0.4 p	±0.1pF	300	200	0.5 ± 0.05	R
EVK105 CG0R5BW-F			CG	COG	0.5 p	±0.1pF	300	200	0.5 ± 0.05	R
EVK105 CG0R6BW-F			CG	COG	0.6 p	±0.1pF	300	200	0.5 ± 0.05	R
EVK105 CG0R7BW-F			CG	COG	0.7 p	±0.1pF	300	200	0.5 ± 0.05	R
EVK105 CG0R8BW-F			CG	COG	0.8 p	±0.1pF	300	200	0.5 ± 0.05	R
EVK105 CG0R9BW-F			CG	COG	0.9 p	±0.1pF	300	200	0.5 ± 0.05	R
EVK105 CG010BW-F			CG	COG	1 p	±0.1pF	300	200	0.5 ± 0.05	R
EVK105 CG1R1BW-F			CG	COG	1.1 p	±0.1pF	280	200	0.5 ± 0.05	R
EVK105 CG1R2BW-F			CG	C0G	1.2 p	±0.1pF	270	200	0.5 ± 0.05	R
EVK105 CG1R3BW-F			CG	C0G	1.3 p	±0.1pF	260	200	0.5 ± 0.05	R
EVK105 CG1R5BW-F			CG	COG	1.5 p	±0.1pF	240	200	0.5 ± 0.05	R
EVK105 CG1R6BW-F		16	CG	COG	1.6 p	±0.1pF	230	200	0.5 ± 0.05	R
EVK105 CG1R8BW-F			CG	COG	1.8 p	±0.1pF	210	200	0.5 ± 0.05	R
EVK105 CG020BW-F			CG	COG	2 p	±0.1pF	190	200	0.5 ± 0.05	R
EVK105 CG2R2JW-F			CG	COG	2.2 p	±5%	180	200	0.5 ± 0.05	R
EVK105 CG2R4JW-F			CG	COG	2.4 p	±5%	170	200	0.5 ± 0.05	R
EVK105 CG2R7JW-F			CG	COG	2.7 p	±5%	150	200	0.5 ± 0.05	R
EVK105 CG030JW-F			CG	COG	3 р	±5%	130	200	0.5 ± 0.05	R
EVK105 CG3R3JW-F		ĺ	CG	C0G	3.3 p	±5%	120	200	0.5±0.05	R
EVK105 CG3R6JW-F		ĺ	CG	C0G	3.6 p	±5%	110	200	0.5±0.05	R
EVK105 CG3R9JW-F		ĺ	CG	C0G	3.9 p	±5%	99	200	0.5±0.05	R
EVK105 CG4R3JW-F		ĺ	CG	COG	4.3 p	±5%	84	200	0.5±0.05	R
EVK105 CG4R7JW-F		ĺ	CG	COG	4.7 p	±5%	84	200	0.5±0.05	R
EVK105 CG5R1JW-F		1	CG	COG	5.1 p	±5%	84	200	0.5 ± 0.05	R

[Temperature Characteristic CG: $CG/COG(-55\sim+125^{\circ}C)$] 0.5mm thickness(W)

[I emperature Charac	teristic GG : GG/G	04(-33.4	F 125 C,	0.511	im thicknes	S(W)				
Part number 1	Part number 2	Rated voltage	Tempe	erature	Capacitance	Capacitance tolerance	Q (at 1GHz)	HTLT	Thickness*3 [mm]	Soldering R:Reflow
Fart number 1	Fart number 2	[V]	charact	eristics	[F]	Capacitance tolerance		Rated voltage x %	Inickness [mm]	W:Wave
UVK105 CG0R3BW-F			CG	COG	0.3 p	±0.1pF	300	200	0.5±0.05	R
UVK105 CG0R4BW-F			CG	COG	0.4 p	±0.1pF	300	200	0.5 ± 0.05	R
UVK105 CG0R5BW-F			CG	COG	0.5 p	±0.1pF	300	200	0.5 ± 0.05	R
UVK105 CG0R6BW-F			CG	COG	0.6 p	±0.1pF	300	200	0.5 ± 0.05	R
UVK105 CG0R7BW-F			CG	COG	0.7 p	±0.1pF	300	200	0.5 ± 0.05	R
UVK105 CG0R8BW-F			CG	COG	0.8 p	±0.1pF	300	200	0.5 ± 0.05	R
UVK105 CG0R9BW-F			CG	COG	0.9 p	±0.1pF	300	200	0.5 ± 0.05	R
UVK105 CG010BW-F			CG	COG	1 p	±0.1pF	300	200	0.5 ± 0.05	R
UVK105 CG1R1BW-F			CG	COG	1.1 p	±0.1pF	280	200	0.5 ± 0.05	R
UVK105 CG1R2BW-F			CG	COG	1.2 p	±0.1pF	270	200	0.5 ± 0.05	R
UVK105 CG1R3BW-F			CG	COG	1.3 p	±0.1pF	260	200	0.5 ± 0.05	R
UVK105 CG1R5BW-F			CG	COG	1.5 p	±0.1pF	240	200	0.5 ± 0.05	R
UVK105 CG1R6BW-F		50	CG	COG	1.6 p	±0.1pF	230	200	0.5 ± 0.05	R
UVK105 CG1R8BW-F			CG	COG	1.8 p	±0.1pF	210	200	0.5 ± 0.05	R
UVK105 CG020BW-F			CG	COG	2 p	±0.1pF	190	200	0.5 ± 0.05	R
UVK105 CG2R2JW-F			CG	COG	2.2 p	±5%	180	200	0.5 ± 0.05	R
UVK105 CG2R4JW-F			CG	COG	2.4 p	±5%	170	200	0.5 ± 0.05	R
UVK105 CG2R7JW-F			CG	COG	2.7 p	±5%	150	200	0.5 ± 0.05	R
UVK105 CG030JW-F			CG	COG	3 p	±5%	130	200	0.5 ± 0.05	R
UVK105 CG3R3JW-F			CG	C0G	3.3 p	±5%	120	200	0.5 ± 0.05	R
UVK105 CG3R6JW-F			CG	C0G	3.6 p	±5%	110	200	0.5 ± 0.05	R
UVK105 CG3R9JW-F		1	CG	C0G	3.9 p	±5%	99	200	0.5±0.05	R
UVK105 CG4R3JW-F		1	CG	COG	4.3 p	±5%	84	200	0.5±0.05	R
UVK105 CG4R7JW-F			CG	COG	4.7 p	±5%	84	200	0.5±0.05	R
UVK105 CG5R1JW-F			CG	COG	5.1 p	±5%	84	200	0.5 ± 0.05	R

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

Multilayer Ceramic Capacitors

■PACKAGING

1 Minimum Quantity


Taped package	TILL		0, 1, 1	F 3
Type(EIA)	Thick mm	code	Paper tape	uantity [pcs] Embossed tape
□MK021(008004)	0.125	K	- парет саре	50000
□VS021(008004)	0.123	IX		30000
☐MK042(01005)	0.2	C, D	_	40000
□VS042(01005)	0.2	С	_	40000
☐MK063(0201)	0.3	P,T	15000	_
□WK105(0204) ※	0.3	Р	10000	_
	0.13	Н	_	20000
DM(105(0400)	0.18	E	_	15000
☐MK105(0402) ☐MF105(0402)	0.2	С	20000	_
MF 105(0402)	0.3	Р	15000	_
	0.5	V	10000	_
□VK105(0402)	0.5	W	10000	_
□MK107(0603)	0.45	K	4000	_
□WK107(0306) ※	0.5	V	_	4000
□MF107(0603)	0.8	Α	4000	_
□VS107(0603)	0.7	С	4000	_
□MJ107(0603)	0.8	Α	3000	3000
□MK212(0805)	0.45	K	4000	
□WK212(0508) ※	0.85	D	4000	_
□MF212(0805)	1.25	G	_	3000
□VS212(0805)	0.85	D	4000	_
	0.85	D	4000	_
□MJ212(0805)	1.25	G	_	2000
	0.85	D	4000	_
□MK316(1206)	1.15	F	_	3000
□MF316(1206)	1.6	L	_	2000
	1.15	F	_	3000
□MJ316(1206)	1.6	L	_	2000
	0.85	D		
	1.15	F	1	
☐MK325(1210)	1.9	N	1 -	2000
□MF325(1210)	2.0max.	Y	1	
	2.5	M	_	1000
[] 1 1005(1015)	1.9	N	_	2000
□MJ325(1210)	2.5	М	_	500(T), 1000(P)
□MK432(1812)	2.5	М	_	500

Note:

K LW Reverse type.

**No bottom tape for pressed carrier tape Card board carrier tape Top tape Base tape Sprocket hole Chip cavity Base tape Chip cavity

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).



3 Representative taping dimensions

 (0.079 ± 0.002)


Paper Tape (8mm wide) Pressed carrier tape (2mm pitch) Unit: mm(inch) Sprocket hole ϕ 1.5+0.1/-0 ϕ 1.75±0.1 ϕ 1.75±

Type(EIA)	Chip	Cavity	Insertion Pitch	Tape Th	nickness
Type(EIA)	Α	В	F	Т	T1
☐MK063(0201)	0.37	0.67		0.45max.	0.42max.
□WK105(0204) ※			2.0±0.05	0.45max.	0.42max.
□MK105(0402) (*1 C)	0.65	1.15	2.0 ± 0.03	0.4max.	0.3max.
□MK105(0402) (*1 P)				0.45max.	0.42max.


Note *1 Thickness, C:0.2mm ,P:0.3mm. * LW Reverse type.

 (0.157 ± 0.004)

Unit:mm



Type(EIA)	Chip (Cavity	Insertion Pitch	Tape Thickness
Type(EIA)	Α	В	F	Т
☐MK105 (0402)				
□MF105 (0402)	0.65	1.15	2.0 ± 0.05	0.8max.
□VK105 (0402)				
				Unit:mm




This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

Type(EIA)	Chip (Cavity	Insertion Pitch	Tape Thickness
Type(EIA)	Α	В	F	Т
☐MK107(0603)				
□WK107(0306) ※	1.0	1.8		1.1max.
☐MF107(0603)			40+01	
☐MK212(0805)	1.65	0.4	4.0±0.1	
□WK212(0508) ※	1.65	2.4		1.1max.
☐MK316(1206)	2.0	3.6		


Note: Taping size might be different depending on the size of the product. X LW Reverse type.

Unit:mm



Type(EIA)	Chip (Cavity	Insertion Pitch	Tape Th	nickness
Type(EIA)	Α	В	F	K	Т
□MK021(008004)	0.135	0.27			
□VS021(008004)	0.135	0.27	1.0±0.02	0.5max.	0.25max.
☐MK042(01005)	0.23	0.43	1.0 ± 0.02	u.amax.	0.25max.
□VS042(01005)	0.23	0.43			


Unit:mm



Type(EIA)	Chip (Cavity	Insertion Pitch	Tape Th	nickness
Type(EIA)	Α	В	F	K	Т
☐MK105(0402)	0.6	1.1	2.0±0.1	0.6max	0.2±0.1
□WK107(0306) ※	1.0	1.8		1.3max.	0.25±0.1
☐MK212(0805) ☐MF212(0805)	1.65	2.4			
☐MK316(1206) ☐MF316(1206)	2.0	3.6	4.0±0.1	3.4max.	0.6max.
☐MK325(1210) ☐MF325(1210)	2.8	3.6]		

Note: ※ LW Reverse type. Unit:mm


This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).




Type(EIA)	Chip (Cavity	Insertion Pitch	Tape Th	nickness
Type(EIA)	Α	В	F	K	Т
☐MK325(1210)	3.1	4.0	8.0±0.1	4.0max.	0.6max.
☐MK432(1812)	3.7	4.9	8.0±0.1	4.0max.	0.6max.

Unit:mm

4 Trailer and Leader



⑤Reel size




Α	В	С	D	Е	R
ϕ 178 ± 2.0	ϕ 50min.	ϕ 13.0 \pm 0.2	ϕ 21.0 ± 0.8	2.0±0.5	1.0

	T	W
4mm wide tape	1.5max.	5±1.0
8mm wide tape	2.5max.	10±1.5
12mm wide tape	2.5max.	14±1.5

Unit:mm

6Top Tape Strength

The top tape requires a peel-off force of 0.1 to 0.7N in the direction of the arrow as illustrated below.



This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

Multilayer Ceramic Capacitors

■RELIABILITY DATA

1.Operating 1	Temperature Range					
	Temperature	Standard		1.105°O		
	Compensating(Class1)	High Frequency Type	—55 to -	+ 125 C		
				Specification	Temperature Range	
			BJ	В	−25 to +85°C	
Specified			ВО	X5R	−55 to +85°C	
Value	High Permittivity (Class2	1	B7	X7R	−55 to +125°C	
	nigh Permittivity (Glassz)	C6	X6S	−55 to +105°C	
			C7	X7S	−55 to +125°C	
			LD(※)	X5R	−55 to +85°C	
			Note:	LD Low distortion h	nigh value multilayer ceramic capa	citor
			•			
2. Storage Co	onditions					
L. Otorugo o		Standard	1			
	Temperature		-55 to -	+125°C		
	Compensating(Class1)	High Frequency Type				-
				Specification	Temperature Range	
O .c. 1			BJ	В	−25 to +85°C	
Specified Value				X5R	−55 to +85°C	
value	High Permittivity (Class2)	B7	X7R	−55 to +125°C	
		,	C6	X6S	−55 to +105°C	
			C7	X7S	−55 to +125°C	
			LD(X)	X5R	−55 to +85°C	
			Note: 3	<u>XLD Low distortion has a limited in the limit</u>	nigh value multilayer ceramic capa	citor
3. Rated Volt	tage					
	Temperature	Standard	50VDC, 2	5VDC, 16VDC		
			50VDC 2	5VDC, 16VDC		
Specified Value	Compensating(Class1)	High Frequency Type	00 1 00, 2	,		
Specified Value	Compensating (Class1) High Permittivity (Class2)			•	C, 10VDC, 6.3VDC, 4VDC, 2.5VDC	;
•				•	C, 10VDC, 6.3VDC, 4VDC, 2.5VDC)
/alue)		•	C, 10VDC, 6.3VDC, 4VDC, 2.5VDC	

4. Withstanding	Voltage (Between terminal	s)				
0 15 1	Temperature	Standard				
Specified Value	Compensating(Class1)	High F	requency Type	No breakdown o	No breakdown or damage	
- Value	High Permittivity (Class2))				
T4			Cla	ass 1	Class 2	
Test Methods and	Applied voltage		Rated v	Rated voltage × 3 Rate		
Remarks	Duration	ration		1 to 5 sec.		
Remarks	Charge/discharge currer	nt		50mA	max.	

5. Insulation Re	5. Insulation Resistance						
	Temperature	Standard	10000 MΩ min.				
Specified	Compensating(Class1)	High Frequency Type	TOOOD WISE MIN.				
Value	High Permittivity (Class2) Note 1		$C \le 0.047$ F: 10000 MΩ min. C>0.047 μ F: 500MΩ • μ F				
Test	Applied voltage	: Rated voltage					
Methods and	Duration : 60±5 sec.						
Remarks	Charge/discharge current	: 50mA max.					

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

6. Capacitance	(Tolerance)					
Specified Value	Temperature	Standard	C	0.2pF≦C≦5pF 0.2pF≦C≦10pF C>10pF	: ±0.25pF : ±0.5pF : ±5% or ±10%	
	Compensating(Class1)	High Frequency Type	CG	0.2pF≦C≦2pF C>2pF	: ±0.1pF : ±5%	
	High Permittivity (Class2)			or ±20%		
			Class 1		Class 2	
- .		Standard	rd High Frequency Type		C≦10 <i>μ</i> F	C>10 μ F
Test Methods and Remarks	Preconditioning		None		Thermal treatment (at 150°C for 1hr) Note 2	
	Measuring frequency		1MHz	:±10%	1kHz±10%	120±10Hz
	Measuring voltage Nte		0.5 to	5Vrms	1±0.2Vrms	0.5±0.1Vrms
	Bias application				None	•

Specified Value	Temperature		Standard		0pF:Q≧400+20C 0pF:Q≧1000 (C:No	ominal capacitance)	
	Compensating(Class1)	High Frequency Type		Refer	to detailed specification		
	High Permittivity (Class2) Note 1			BJ, B7, C6, C7:2.5% max.			
				Class 1		Class 2	
			Standard		High Frequency Type	C≦10 <i>μ</i> F	C>10 μ F
	Preconditioning		None		Thermal treatment (at 150°C for 1hr) Note 2		
Test	Measuring frequency		1MHz±10%		1GHz	1kHz±10%	120±10Hz
Methods and	Measuring voltage Note	1		0.5 to 5Vrms		1±0.2Vrms	0.5±0.1Vrms
Remarks	Bias application			None			
	High Frequency Type						
	Measuring equipment	: HP	4291A				
	Measuring jig						

8. Temperature Characteristic (Without voltage application)									
			Tem	perature Charac	cteristic [ppm/°	C]	Tolerance [ppm/°C]		
		Standard	C□:	0	CG		G: ±30		
	Temperature Compensating(Class1)	Standard	U□: -750		UJ, UK		J:±120 K:±250		
		High Frequency Type		Temperature Characteristic [ppm/°C] C□: 0			Tolerance [ppm/°C] G: ±30		
Specified Value				Specification	Capacitance change	Refere tempera		Temperature Range	
			BJ	В	±10%	20°C	С	−25 to +85°C	l
			БО	X5R	±15%	temperature 20°C -25 to +85°C -55 to +85°C -55 to +85°C			
	High Permittivity (Class2))	B7	X7R	±15%	25°C	С	−55 to +125°C	
			C6	XS	±22%	25°C	С	-55 to +105°C	
			C7	X7S	±22%	25°C	С	−55 to +125°C	l
			LD(※)	X5R	±15%	25°C	С	-55 to +85°C	l
			Note:	LOW disto	ortion high value i	multilayer	cerami	c capacitor	

Class 1

Capacitance at 20° C and 85° C shall be measured in thermal equilibrium, and the temperature characteristic shall be calculated from the following equation.

$$\frac{-\frac{(C_{85}-C_{20})}{C_{20}\times\Delta T}\times 10^{6}(\text{ppm/°C})}{\Delta T\!=\!65}$$

Test Methods and

Remarks

Class 2

Capacitance at each step shall be measured in thermal equilibrium, and the temperature characteristic shall be calculated from the following equation.

Step	В	X5R, X7R, X6S, X7S				
1	Minimum operat	ting temperature				
2	20°C	25°C				
3	Maximum operating temperature					


 $\begin{array}{c|c} \hline (C-C_2) & C & : Capacitance in Step 1 or Step 3 \\ \hline C_2 & C_2 & : Capacitance in Step 2 \\ \end{array}$


This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

Specified Value	Temperature Compensating(Class1)		Standard	Appearance Capacitance change	: No abnormality : Within $\pm 5\%$ or ± 0.5 pF, whichever is larger.
			High Frequency Type	Appearance : No abnormality Capacitance change : Within±0.5 pF	
	High Permittivity (Class2)			Appearance Capacitance change	: No abnormality : Within ±12.5%
		021 0	Multilayer Ceram 42, 063, *105 Type	·	20,
	Board	021, 0	Glass epoxy-res	The other types sin substrate	Bo and R-230 Warp
Test Methods and	Thickness		0.8mm	1.6mm	
wethous and					

Remarks

	Multilayer Ceramic Capacitors						
	021, 042, 063, *105 Type	The other types					
Board	Glass epoxy-resin substrate						
Thickness	0.8mm	1.6mm					
Warp	1mm						
Duration	10 sec.						





Capacitance measurement shall be conducted with the board bent

10. Body Stren	10. Body Strength						
	Temperature	Standard	_				
Specified Value	Compensating(Class1)	High Frequency Type	No mechanical damage.				
valuo	High Permittivity (Class2)						
Test Methods and Remarks	High Frequency 105Type Applied force : 5N Duraton : 10 sec.	Pres ← A →	R0.5 Pressing Jig Chip O.6A A				

11. Adhesive St	11. Adhesive Strength of Terminal Electrodes							
	Temperature	Standard						
Specified Value	Compensating(Class1) High Frequency Type	No terminal separati	No terminal separation or its indication.				
value	High Permittivity (CI	ass2)						
T4		Multilayer Ceran	nic Capacitors					
Test Methods and		021, 042, 063 Type	105 Type or more					
Remarks	Applied force	2N	5N					
Remarks	Duration	30±5	sec.					

!				
Temperature	Standard			
Compensating(Class1)	High Frequency Type	At least 95% of terminal electrode is covered by		by new solder.
High Permittivity (Class2))			
	Eutectic so	older	Lead-free solder	
Solder type	H60A or H63A		Sn-3.0Ag-0.5Cu	
Solder temperature	230±5°	С	245±3℃	
Duration		4±1 sec.		
	Temperature Compensating(Class1) High Permittivity (Class2) Solder type Solder temperature	Temperature Compensating(Class1) High Frequency Type High Permittivity (Class2) Eutectic so Solder type H60A or H Solder temperature 230±5°	Temperature	Temperature

Finis catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/) .

Resistance	to Soldering				
Specified Value	Temperature	Standard	Appearance Capacitance change Q Insulation resistance Withstanding voltage	: No abnormality : Within ±2.5% or ±0 : Initial value : Initial value (between terminals)	0.25pF, whichever is larger. : No abnormality
	Compensating (Class1	High Frequency Type	Appearance Capacitance change Q Insulation resistance Withstanding voltage	: No abnormality : Within ±2.5% : Initial value : Initial value (between terminals)	: No abnormality
	High Permittivity(Cla	ss2) Note 1	Appearance Capacitance change Dissipation factor Insulation resistance Withstanding voltage	: No abnormality : Within ±7.5% : Initial value : Initial value (between terminals)	: No abnormality
			Class 1		
		021, 042, 063 Type	1	05 Type	
	Preconditioning		None		
	Preheating	150°C, 1 to 2 min.		00°C, 2 to 5 min. 00°C, 2 to 5 min.	
	Solder temp.		270±5°C		
	Duration		3±0.5 sec.		
Test	Recovery	6 to 24 hrs	6 to 24 hrs (Standard condition) Note 5		
Methods and Remarks				Class 2	
		021, 042, 063 Type	105, 1	107, 212 Type	316, 325, 432 Type
	Preconditioning		Thermal treatment	(at 150°C for 1 hr) No	ote 2
	Preheating	150°C, 1 to 2 min.		00°C, 2 to 5 min. 00°C, 2 to 5 min.	80 to 100°C, 5 to 10 min. 150 to 200°C, 5 to 10 min.
	Solder temp.				·
	Duration		3:	±0.5 sec.	
	Recovery		24±2 hrs (Star	ndard condition) Note	5

14. Temperatu	re Cycle (Thermal Shock)					
Specified Value	Temperature	Standard	Capacitance change : \Q : I Insulation resistance : I	: No abnormality : Within ±2.5% or ±0.25pF, whichever is larger. : Initial value : Initial value (between terminals) : No abnormality : No abnormality : Within ±0.25pF : Initial value : Initial value (between terminals) : No abnormality		
	Compensating(Class1)	High Frequency Type	Capacitance change : \Q : I Insulation resistance : I			
	High Permittivity(Class2) Note 1	Capacitance change : V Dissipation factor : In Insulation resistance : In			
			Class 1	Class 2		
	Preconditioning		None	Thermal treatment (at 150°C for 1 hr) Note 2		
Test Methods and Remarks	1 cycle	Step 1 2 3 4	Temperatur Minimum operating Normal temp Maximum operating Normal temp	g temperature perature g temperature perature	Time (min.) 30±3 2 to 3 30±3 2 to 3	
	Number of cycles		5	times		
	Recovery	6 to 24 hrs (Star	ndard condition)Note 5	24±2 hrs (Standard condition) Note 5		

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

15. Humidity (Steady State)					
	Temperature Compensating(Class1	Standard	Capacitance change Q	No abnormality Within $\pm 5\%$ or ± 0.5 pF, whichever is larger. $C<10$ pF: $Q\ge 200+10$ C $10\le C<30$ pF: $Q\ge 275+2.5$ C $C\ge 30$ pF: $Q\ge 350$ (C: Nominal capacitance) 000 M Ω min.		
Specified Value		High Frequency Type	Capacitance change	: No abnormality : Within $\pm 0.5 pF$, : $1000~M~\Omega$ min.		
	High Permittivity (Class2) Note 1		Capacitance change Dissipation factor	tance change : Within ±12.5% tion factor : 5.0% max.		
		Cla	ass 1	Class 2		
		Standard	High Frequency Type	All items		
Test	Preconditioning	N	lone	Thermal treatment (at 150°C for 1 hr) Note 2		
Methods and	Temperature	40±2°C	60±2°C	40±2°C		
Remarks	Humidity	90 to	95%RH	90 to 95%RH		
	Duration	500+2	4/-0 hrs	500+24/-0 hrs		
	Recovery	6 to 24 hrs (Stand	ard condition)Note 5	24±2 hrs(Standard condition)Note 5		

16. Humidity Lo	pading					
Specified Value	Temperature Compensating(Class1)	Standard	Appearance Capacitance change Q Insulation resistance	: Wit : C < C≧	abnormality thin $\pm 7.5\%$ or ± 0.75 pF, whichever is larger. 30 pF: $Q \ge 100 + 10$ C/3 ≥ 30 pF: $Q \ge 200$ (C: Nominal capacitance) 0 M Ω min.	
		High Frequency Type	$\begin{tabular}{lllllllllllllllllllllllllllllllllll$		≦2pF:Within ±0.4 pF 2pF:Within ±0.75 pF (C:Nominal capacitance)	
	High Permittivity (Class2) Note 1		$\begin{tabular}{lllllllllllllllllllllllllllllllllll$		thin ±12.5% % max.	
			Class 1		Class 2	
		Standard	High Frequency Ty	ре	All items	
	Preconditioning		None		Voltage treatment (Rated voltage are applied for 1 hour at 40°C) Note 3	
Test	Temperature	40±2°C	60±2°C		40±2°C	
Methods and	Humidity	90 t	to 95%RH		90 to 95%RH	
Remarks	Duration	500+	-24/-0 hrs		500+24/-0 hrs	
	Applied voltage	Rate	ed voltage		Rated voltage	
	Charge/discharge current	50r	mA max.		50mA max.	
	Recovery	6 to 24 hrs (Stan	dard condition)Note 5		24±2 hrs(Standard condition) Note 5	

		Appearance		: No abnormality			
			Capacitance change	: Within $\pm 3\%$ or ± 0.3 pF, whichever is larger.			
		0	Q	: C<10pF: Q≧200+10C		•	
		Standard		10≦C<30pF:	10≦C<30pF:Q≧275+2.5C		
	Temperature Compensating(Class1)				C≧30pF: Q≧350(C:Nominal capacitance)		
Cifind	Compensating (Glass I)		Insulation resistance	: 1000 MΩ min.			
Specified Value			Appearance	: No abnormality	/		
Value		High Frequency Type	Capacitance change		±0.3pF, whichever	is larger.	
		Insulation resistance		: 1000 MΩ min.			
			Appearance	: No abnormality			
	High Permittivity (Class2) Note 1		Capacitance change	: Within ±12.5%	ó		
			Dissipation factor	: 5.0% max.	1000 110		
			Insulation resistance : 50 M Ω μ F or 1000 M Ω , whichever is smaller.			er is smaller.	
		Clas			Class 2	1	
		Standard I	High Frequency Type	BJ, LD(※)	C6	B7, C7	
	Preconditioning	<u> </u>		Voltage treatment (Twice the rated voltage shall be applied for			
				1 hour at 85°C, 105°C or 125°C) Note 3, 4			
Test	Temperature	Maximum operati	• '	Maximum operating temperature			
Methods and	Duration	1000+48/-0 hrs		1000+48/-0 hrs			
Remarks	Applied voltage	Rated voltage	e × 2 Note 4	Rated voltage × 2 Note 4			
	Charge/discharge	50mA	may	50mA max.			
	current	0011171	max.	JUMA max.			
	Recovery	6 to 24hr (Standard	condition) Note 5	24±2 hrs(Standard condition)Note 5			

Note 1 The figures indicate typical specifications. Please refer to individual specifications in detail.

- Note 2 Thermal treatment : Initial value shall be measured after test sample is heat-treated at $150 \pm 0/-10^{\circ}$ C for an hour and kept at room temperature for 24 ± 2 hours.
- Note 3 Voltage treatment: Initial value shall be measured after test sample is voltage-treated for an hour at both the temperature and voltage specified in the test conditions, and kept at room temperature for 24±2hours.
- Note 4 150% of rated voltage is applicable to some items. Please refer to their specifications for further information.
- Note 5 Standard condition: Temperature: 5 to 35°C, Relative humidity: 45 to 85 % RH, Air pressure: 86 to 106kPa When there are questions concerning measurement results, in order to provide correlation data, the test shall be conducted under the following condition.
 - Temperature: $20\pm2^{\circ}$ C, Relative humidity: 60 to 70 % RH, Air pressure: 86 to 106kPa Unless otherwise specified, all the tests are conducted under the "standard condition".

[►] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

Precautions on the use of Multilayer Ceramic Capacitors

PRECAUTIONS

1. Circuit Design

- ◆Verification of operating environment, electrical rating and performance
 - 1. A malfunction of equipment in fields such as medical, aerospace, nuclear control, etc. may cause serious harm to human life or have severe social ramifications.

Therefore, any capacitors to be used in such equipment may require higher safety and reliability, and shall be clearly differentiated from them used in general purpose applications.

Precautions

- ◆Operating Voltage (Verification of Rated voltage)
- 1. The operating voltage for capacitors must always be their rated voltage or less.
 - If an AC voltage is loaded on a DC voltage, the sum of the two peak voltages shall be the rated voltage or less.
 - For a circuit where an AC or a pulse voltage may be used, the sum of their peak voltages shall also be the rated voltage or less.
- 2. Even if an applied voltage is the rated voltage or less reliability of capacitors may be deteriorated in case that either a high frequency AC voltage or a pulse voltage having rapid rise time is used in a circuit.

2. PCB Design

Precautions

- ◆Pattern configurations (Design of Land-patterns)
- 1. When capacitors are mounted on PCBs, the amount of solder used (size of fillet) can directly affect the capacitor performance. Therefore, the following items must be carefully considered in the design of land patterns:
 - (1) Excessive solder applied can cause mechanical stresses which lead to chip breaking or cracking. Therefore, please consider appropriate land-patterns for proper amount of solder.
 - (2) When more than one component are jointly soldered onto the same land, each component's soldering point shall be separated by solder-resist.
- ◆Pattern configurations (Capacitor layout on PCBs)

After capacitors are mounted on boards, they can be subjected to mechanical stresses in subsequent manufacturing processes (PCB cutting, board inspection, mounting of additional parts, assembly into the chassis, wave soldering of the boards, etc.). For this reason, land pattern configurations and positions of capacitors shall be carefully considered to minimize stresses.


◆Pattern configurations (Design of Land-patterns)


The following diagrams and tables show some examples of recommended land patterns to prevent excessive solder amounts.

- (1) Recommended land dimensions for typical chip capacitors
- Multilayer Ceramic Capacitors : Recommended land dimensions (unit: mm)

Wave-soldering

Туре		107	212	316	325
C:		1.6	2.0	3.2	3.2
Size	W	0.8	1.25	1.6	2.5
Α		0.8 to 1.0	1.0 to 1.4	1.8 to 2.5	1.8 to 2.5
В		0.5 to 0.8	0.8 to 1.5	0.8 to 1.7	0.8 to 1.7
С		0.6 to 0.8	0.9 to 1.2	1.2 to 1.6	1.8 to 2.5
С		0.6 to 0.8	0.9 to 1.2	1.2 to 1.6	1.8 to 2.5





Technical considerations

Reflow-soldering

110	IIOW 3	solucing								
Ту	фе	021	042	063	105	107	212	316	325	432
Size	L	0.25	0.4	0.6	1.0	1.6	2.0	3.2	3.2	4.5
Size	W	0.125	0.2	0.3	0.5	0.8	1.25	1.6	2.5	3.2
/	4	0.095~0.135	0.15~0.25	0.20~0.30	0.45~0.55	0.6~0.8	0.8~1.2	1.8~2.5	1.8~2.5	2.5~3.5
E	3	0.085~0.125	0.10~0.20	0.20~0.30	0.40~0.50	0.6~0.8	0.8~1.2	1.0~1.5	1.0~1.5	1.5~1.8
()	0.110~0.150	0.15~0.30	0.25~0.40	0.45~0.55	0.6~0.8	0.9~1.6	1.2~2.0	1.8~3.2	2.3~3.5

 $Note: Recommended \ land \ size \ might be \ different \ according \ to \ the \ allowance \ of \ the \ size \ of \ the \ product.$

●LWDC: Recommended land dimensions for reflow-soldering (unit: mm)

Туре		105	107	212	
C: L		0.52	0.8	1.25	
Size	W	1.0	1.6	2.0	
Ä		0.18~0.22	0.25~0.3	0.5~0.7	
В		0.2~0.25	0.3~0.4	0.4~0.5	
С		0.9~1.1	1.5~1.7	1.9~2.1	





Fig. This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).


(2) Examples of good and bad solder application



- ◆Pattern configurations (Capacitor layout on PCBs)
 - 1-1. The following is examples of good and bad capacitor layouts; capacitors shall be located to minimize any possible mechanical stresses from board warp or deflection.

Items	Not recommended	Recommended
Deflection of board		Place the product at a right angle to the direction of the anticipated mechanical stress.

1-2. The amount of mechanical stresses given will vary depending on capacitor layout. Please refer to diagram below.



1-3. When PCB is split, the amount of mechanical stress on the capacitors can vary according to the method used. The following methods are listed in order from least stressful to most stressful: push-back, slit, V-grooving, and perforation. Thus, please consider the PCB, split methods as well as chip location.


3. Mounting

- ◆Adjustment of mounting machine
 - 1. When capacitors are mounted on PCB, excessive impact load shall not be imposed on them.
 - 2. Maintenance and inspection of mounting machines shall be conducted periodically.
- ◆Selection of Adhesives Precautions
 - 1. When chips are attached on PCBs with adhesives prior to soldering, it may cause capacitor characteristics degradation unless the following factors are appropriately checked: size of land patterns, type of adhesive, amount applied, hardening temperature and hardening period. Therefore, please contact us for further information.

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/) .

◆Adjustment of mounting machine

- 1. When the bottom dead center of a pick-up nozzle is too low, excessive force is imposed on capacitors and causes damages. To avoid this, the following points shall be considerable.
 - (1) The bottom dead center of the pick-up nozzle shall be adjusted to the surface level of PCB without the board deflection.
 - (2) The pressure of nozzle shall be adjusted between 1 and 3 N static loads.
 - (3) To reduce the amount of deflection of the board caused by impact of the pick-up nozzle, supporting pins or back-up pins shall be used on the other side of the PCB. The following diagrams show some typical examples of good and bad pick-up nozzle placement:



Technical considerations

2. As the alignment pin is worn out, adjustment of the nozzle height can cause chipping or cracking of capacitors because of mechanical impact on the capacitors.

To avoid this, the monitoring of the width between the alignment pins in the stopped position, maintenance, check and replacement of the pin shall be conducted periodically.


◆Selection of Adhesives


Some adhesives may cause IR deterioration. The different shrinkage percentage of between the adhesive and the capacitors may result in stresses on the capacitors and lead to cracking. Moreover, too little or too much adhesive applied to the board may adversely affect components. Therefore, the following precautions shall be noted in the application of adhesives.

- (1) Required adhesive characteristics
 - a. The adhesive shall be strong enough to hold parts on the board during the mounting & solder process.
 - b. The adhesive shall have sufficient strength at high temperatures.
 - c. The adhesive shall have good coating and thickness consistency.
 - d. The adhesive shall be used during its prescribed shelf life.
 - e. The adhesive shall harden rapidly.
 - f. The adhesive shall have corrosion resistance.
 - g. The adhesive shall have excellent insulation characteristics.
 - h. The adhesive shall have no emission of toxic gasses and no effect on the human body.
- (2) The recommended amount of adhesives is as follows;

[Recommended condition]

Figure	212/316 case sizes as examples
а	0.3mm min
b	100 to 120 μ m
С	Adhesives shall not contact land





4. Soldering

Precautions

Technical

considerations

◆Selection of Flux

Since flux may have a significant effect on the performance of capacitors, it is necessary to verify the following conditions prior to use;

- (1) Flux used shall be less than or equal to 0.1 wt%(in Cl equivalent) of halogenated content. Flux having a strong acidity content shall not be applied.
- (2) When shall capacitors are soldered on boards, the amount of flux applied shall be controlled at the optimum level.
- (3) When water-soluble flux is used, special care shall be taken to properly clean the boards.

♦Soldering

Temperature, time, amount of solder, etc. shall be set in accordance with their recommended conditions.

Sn-Zn solder paste can adversely affect MLCC reliability.

Please contact us prior to usage of Sn-Zn solder.

◆Selection of Flux

- 1-1. When too much halogenated substance (Chlorine, etc.) content is used to activate flux, or highly acidic flux is used, it may lead to corrosion of terminal electrodes or degradation of insulation resistance on the surfaces of the capacitors.
- 1-2. Flux is used to increase solderability in wave soldering. However if too much flux is applied, a large amount of flux gas may be emitted and may adversely affect the solderability. To minimize the amount of flux applied, it is recommended to use a flux-bubbling system.
- 1-3. Since the residue of water-soluble flux is easily dissolved in moisture in the air, the residues on the surfaces of capacitors in high humidity conditions may cause a degradation of insulation resistance and reliability of the capacitors. Therefore, the cleaning methods and the capability of the machines used shall also be considered carefully when water-soluble flux is used.

methods and the


This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

♦Soldering


- · Ceramic chip capacitors are susceptible to thermal shock when exposed to rapid or concentrated heating or rapid cooling.
- · Therefore, the soldering must be conducted with great care so as to prevent malfunction of the components due to excessive thermal shock
- Preheating: Capacitors shall be preheated sufficiently, and the temperature difference between the capacitors and solder shall be within 130°C.
- · Cooling: The temperature difference between the capacitors and cleaning process shall not be greater than 100°C.

[Reflow soldering]

[Recommended conditions for eutectic




[Recommended condition for Pb-free




Caution

- 1The ideal condition is to have solder mass(fillet)controlled to 1/2 to 1/3 of the thickness of a capacitor.
- ②Because excessive dwell times can adversely affect solderability, soldering duration shall be kept as close to recommended times as possible. soldering for 2 times.




[Wave soldering]

[Recommended conditions for eutectic soldering]



[Recommended condition for Pb-free




Caution


①Wave soldering must not be applied to capacitors designated as for reflow soldering only. soldering for 1 times.


[Hand soldering]

[Recommended conditions for eutectic



[Recommended condition for Pb-free





Caution

- ①Use a 50W soldering iron with a maximum tip diameter of 1.0 mm.
- 2The soldering iron shall not directly touch capacitors. soldering for 1 times.

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

5. Cleaning Cleaning conditions 1. When PCBs are cleaned after capacitors mounting, please select the appropriate cleaning solution in accordance with the intended use Precautions of the cleaning. (e.g. to remove soldering flux or other materials from the production process.) 2. Cleaning condition shall be determined after it is verified by using actual cleaning machine that the cleaning process does not affect capacitor's characteristics. 1. The use of inappropriate cleaning solutions can cause foreign substances such as flux residue to adhere to capacitors or deteriorate their outer coating, resulting in a degradation of the capacitor's electrical properties (especially insulation resistance). 2. Inappropriate cleaning conditions (insufficient or excessive cleaning) may adversely affect the performance of the capacitors. In the case of ultrasonic cleaning, too much power output can cause excessive vibration of PCBs which may lead to the cracking of Technical considerations capacitors or the soldered portion, or decrease the terminal electrodes' strength. Therefore, the following conditions shall be carefully checked: 40 kHz or less Ultrasonic output: 20 W/Q or les Ultrasonic frequency: Ultrasonic washing period: 5 min. or less

6. Resin coating and mold

Precautions

- 1. With some type of resins, decomposition gas or chemical reaction vapor may remain inside the resin during the hardening period or while left under normal storage conditions resulting in the deterioration of the capacitor's performance.
- 2. When a resin's hardening temperature is higher than capacitor's operating temperature, the stresses generated by the excessive heat may lead to damage or destruction of capacitors. The use of such resins, molding materials etc. is not recommended.

7. Handling

◆Splitting of PCB

Precautions

- 1. When PCBs are split after components mounting, care shall be taken so as not to give any stresses of deflection or twisting to the board.
- 2. Board separation shall not be done manually, but by using the appropriate devices.

◆Mechanical considerations

Be careful not to subject capacitors to excessive mechanical shocks.

- (1) If ceramic capacitors are dropped onto a floor or a hard surface, they shall not be used.
- (2) Please be careful that the mounted components do not come in contact with or bump against other boards or components.

8. Storage conditions

- 1. To maintain the solderability of terminal electrodes and to keep packaging materials in good condition, care must be taken to control temperature and humidity in the storage area. Humidity should especially be kept as low as possible.
 - Recommended conditions

Precautions

Ambient temperature : Below 30°C Humidity: Below 70% RH

The ambient temperature must be kept below 40°C. Even under ideal storage conditions, solderability of capacitor is deteriorated as time passes, so capacitors shall be used within 6 months from the time of delivery.

- ·Ceramic chip capacitors shall be kept where no chlorine or sulfur exists in the air.
- 2. The capacitance values of high dielectric constant capacitors will gradually decrease with the passage of time, so care shall be taken to design circuits. Even if capacitance value decreases as time passes, it will get back to the initial value by a heat treatment at 150°C for

Technical considerations

If capacitors are stored in a high temperature and humidity environment, it might rapidly cause poor solderability due to terminal oxidation and quality loss of taping/packaging materials. For this reason, capacitors shall be used within 6 months from the time of delivery. If exceeding the above period, please check solderability before using the capacitors.

**RCR-2335B(Safety Application Guide for fixed ceramic capacitors for use in electronic equipment) is published by JEITA. Please check the guide regarding precautions for deflection test, soldering by spot heat, and so on.

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/) .