









TPS62130, TPS62130A, TPS62131, TPS62132, TPS62133

SLVSAG7E - NOVEMBER 2011 - REVISED AUGUST 2016


# TPS6213x 3-V to17-V, 3-A Step-Down Converter In 3x3 QFN Package

## Features

- DCS-Control<sup>™</sup> Topology
- Input Voltage Range: 3 to 17V
- Up to 3A Output Current
- Adjustable Output Voltage from 0.9 to 6V
- Pin-Selectable Output Voltage (nominal, + 5%)
- Programmable Soft Start and Tracking
- Seamless Power Save Mode Transition
- Quiescent Current of 17µA (typ.)
- Selectable Operating Frequency
- Power Good Output
- 100% Duty Cycle Mode
- Short Circuit Protection
- Over Temperature Protection
- Pin to Pin Compatible with TPS62140 and TPS62150
- Available in a 3 x 3 mm, QFN-16 Package

#### Applications 2

- Standard 12-V Rail Supplies
- POL Supply from Single or Multiple Li-Ion Battery
- Solid-State Disk Drives
- Embedded Systems
- LDO replacement
- Mobile PCs, Tablet, Modems, Cameras
- Server, Microserver
- Data Terminal, Point of Sales (ePOS)



Copyright © 2016, Texas Instruments Incorporated

#### Description 3

The TPS6213X family is an easy to use synchronous down step DC-DC converter optimized for applications with high power density. A high switching frequency of typically 2.5MHz allows the use of small inductors and provides fast transient response as well as high output voltage accuracy by use of the DCS-Control<sup>™</sup> topology.

With their wide operating input voltage range of 3V to 17V, the devices are ideally suited for systems powered from either a Li-Ion or other batteries as well as from 12V intermediate power rails. It supports up to 3A continuous output current at output voltages between 0.9V and 6V (with 100% duty cycle mode). The output voltage startup ramp is controlled by the soft-start pin, which allows operation as either a standalone power supply or in tracking configurations. Power sequencing is also possible by configuring the Enable and open-drain Power Good pins.


In Power Save Mode, the devices draw guiescent current of about 17µA from V<sub>IN</sub>. Power Save Mode, entered automatically and seamlessly if load is small, maintains high efficiency over the entire load range. In Shutdown Mode, the device is turned off and shutdown current consumption is less than 2µA.


The device, available in adjustable and fixed output voltage versions, is packaged in a 16-pin VQFN package measuring  $3 \times 3$  mm (RGT).

## Device Information<sup>(1)</sup>

PART NUMBER	PACKAGE	BODY SIZE (NOM)			
TPS6213x	VQFN (16)	3.00 mm × 3.00 mm			

(1) For all available packages, see the orderable addendum at the end of the datasheet.





## **Typical Application Schematic**



# **Table of Contents**

1	Feat	tures 1
2	Арр	lications 1
3	Des	cription 1
4		ision History 2
5		ice Comparison Table 4
6		Configuration and Functions 4
7	Spe	cifications5
	- 7.1	Absolute Maximum Ratings 5
	7.2	ESD Ratings 5
	7.3	Recommended Operating Conditions 5
	7.4	Thermal Information 5
	7.5	Electrical Characteristics 6
	7.6	Typical Characteristics 7
8	Deta	ailed Description8
	8.1	Overview
	8.2	Functional Block Diagram 8
	8.3	Feature Description
	8.4	Device Functional Modes 11
9	Арр	lication and Implementation 13

	9.1	Application Information	13
	9.2	Typical Application	13
	9.3	System Examples	25
10	Pow	er Supply Recommendations	29
11	Laye	out	30
	11.1	Layout Guidelines	30
	11.2	Layout Example	30
	11.3	Thermal Information	31
12	Dev	ice and Documentation Support	32
	12.1	Device Support	32
	12.2	Documentation Support	32
	12.3	Receiving Notification of Documentation Updates	32
	12.4	Related Links	32
	12.5	Community Resources	33
	12.6	Trademarks	33
	12.7	Electrostatic Discharge Caution	33
	12.8	Glossary	33
13	Мес	hanical, Packaging, and Orderable	
	Infor	mation	33

## **4** Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

C	hanges from Revision D (June 2016) to Revision E	Page
•	Changed the T <sub>J</sub> MAX value From: 125°C To: 150°C in the <i>Absolute Maximum Ratings</i>	5
•	Changed ( $T_J = -40^{\circ}C$ to 85°C) To: ( $T_J = -40^{\circ}C$ to 125°C) in the <i>Electrical Characteristics</i> conditions	6
•	Added a test condition for $I_Q$ at $T_A = -40^{\circ}$ C to +85°C in the <i>Electrical Characteristics</i>	6
•	Added Table 1 and Table 2	10

## Changes from Revision C (January 2015) to Revision D

•	Added "Pin to Pin Compatible with TPS62140 and TPS62150" to Features list	. 1
•	Added "Server, Microserver"; and, "Data Terminal, Point of Sales (ePOS)" to Applications list	. 1
•	Changed the Device Comparison Table format	. 4
•	Changed Thermal Information table	. 5
•	Added Switching Frequency graphs for 1.0-V, 1.8-V, and 5.0-V applications.	20
•	Corrected System Examples schematics.	25
•	Changed Layout Example pictorial	30
•	Added Community Resources section	33

## Changes from Revision B (June 2013) to Revision C

•	Added Device Information and ESD Rating tables, Feature Description section, Device Functional Modes, Programming section, Application and Implementation section, Power Supply Recommendations section, Layout section, Device and Documentation Support section, and Mechanical, Packaging, and Orderable Information section	1
•	Added "(PWM mode operation)" text string to V <sub>UVLO</sub> spec Test Conditions for clarification	6
•	Changed second paragraph of SS/TR description for clarification.	10



Page




Cł	hanges from Revision A (September 2012) to Revision B	Page
•	Added device TPS62130A to data sheet Header	1
•	Added device TPS62130A to Device Comparison table.	4
•	Added text to Power Good section regarding TPS63130A.	10
•	Added pin option to Footnote statement for Pin-Selectable Output Voltage (DEF) section	10
•	Added text to Frequency Selection (FSW) section regarding pin control	11
•	Added text to Tracking Function section for clarification	17
•	Added application example regarding TPS62130A device.	25

## 5 Device Comparison Table

PART NUMBER	OUTPUT VOLTAGE	Power Good Logic Level (EN=Low)
TPS62130	TPS62130 adjustable High Impedance	
TPS62130A adjustable		Low
TPS62131	TPS62131 1.8 V High Impedance	
TPS62132	3.3 V	High Impedance
TPS62133	5.0 V	High Impedance

## 6 Pin Configuration and Functions



#### **Pin Functions**

PIN <sup>(1)</sup> NO.   NAME		1/0	DESCRIPTION	
		1/0	DESCRIPTION	
1,2,3	SW	0	Switch node, which is connected to the internal MOSFET switches. Connect inductor between SW and output capacitor.	
4	PG	0	Output power good (High = $V_{OUT}$ ready, Low = $V_{OUT}$ below nominal regulation) ; open drain (requires pull-up resistor)	
5	FB	Ι	Voltage feedback of adjustable version. Connect resistive voltage divider to this pin. It is recommended to connect FB to AGND on fixed output voltage versions for improved thermal performance.	
6	AGND		Analog Ground. Must be connected directly to the Exposed Thermal Pad and common ground plane.	
7 FSW		Ι	Switching Frequency Select (Low $\approx$ 2.5MHz, High $\approx$ 1.25MHz <sup>(2)</sup> for typical operation) <sup>(3)</sup>	
8	DEF	Ι	Output Voltage Scaling (Low = nominal, High = nominal + 5%) <sup>(3)</sup>	
9 SS/TR		I	Soft-Start / Tracking Pin. An external capacitor connected to this pin sets the internal voltage reference rise time. It can be used for tracking and sequencing.	
10	AVIN	I	Supply voltage for control circuitry. Connect to same source as PVIN.	
11,12	PVIN	Ι	Supply voltage for power stage. Connect to same source as AVIN.	
13	EN	Ι	Enable input (High = enabled, Low = disabled) <sup>(3)</sup>	
14 VOS		Ι	Output voltage sense pin and connection for the control loop circuitry.	
15,16	PGND		Power Ground. Must be connected directly to the Exposed Thermal Pad and common ground plane.	
Exposed Thermal Pad			Must be connected to AGND (pin 6), PGND (pin 15,16) and common ground plane. See the <i>Layout Example</i> . Must be soldered to achieve appropriate power dissipation and mechanical reliability.	

(1) For more information about connecting pins, see Detailed Description and Application and Implementation sections.

(2) Connect FSW to V<sub>OUT</sub> or PG in this case.

(3) An internal pull-down resistor keeps logic level low, if pin is floating.



## 7 Specifications

## 7.1 Absolute Maximum Ratings<sup>(1)</sup>

over operating junction temperature range (unless otherwise noted)

		MIN	MAX	UNIT
	AVIN, PVIN	-0.3	20	V
Din voltage renge (2)	EN, SS/TR	-0.3	V <sub>IN</sub> +0.3	v
Pin voltage range <sup>(2)</sup>	SW	-0.3	V <sub>IN</sub> +0.3	V
	DEF, FSW, FB, PG, VOS	-0.3	7	V
Power Good sink current	PG		10	mA
Operating junction temper	ature, T <sub>J</sub>	-40	150	°C
Storage temperature, Tstq		-65	150	°C

(1) Stresses beyond those listed under absolute maximum ratings may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under recommended operating conditions is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

(2) All voltages are with respect to network ground terminal.

## 7.2 ESD Ratings

			VALUE	UNIT
		Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 <sup>(2)</sup>	±2000	
V <sub>(ESD)</sub>	Electrostatic discharge <sup>(1)</sup>	Charged-device model (CDM), per JEDEC specification JESD22-C101 $^{\rm (3)}$	±500	V

(1) ESD testing is performed according to the respective JESD22 JEDEC standard.

(2) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

(3) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

## 7.3 Recommended Operating Conditions

over operating junction temperature range (unless otherwise noted)

	MIN	MAX	UNIT
Supply Voltage, V <sub>IN</sub> (at AVIN and PVIN)	3	17	V
Operating junction temperature, $T_J$	-40	125	°C

## 7.4 Thermal Information

	THERMAL METRIC <sup>(1)</sup>	TPS6213X	
		RGT 16 PINS	UNITS
$R_{\theta JA}$	Junction-to-ambient thermal resistance	45	
$R_{\theta JCtop}$	Junction-to-case(top) thermal resistance	53.6	
$R_{\theta JB}$	Junction-to-board thermal resistance	17.4	°C/W
ΨJT	Junction-to-top characterization parameter	1.1	C/VV
Ψјв	Junction-to-board characterization parameter	17.4	
$R_{\theta JCbot}$	Junction-to-case(bottom) thermal resistance	4.5	

(1) For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report.

## TPS62130, TPS62130A, TPS62131, TPS62132, TPS62133 SLVSAG7E – NOVEMBER 2011 – REVISED AUGUST 2016

www.ti.com

## 7.5 Electrical Characteristics

over operating junction temperature ( $T_J = -40^{\circ}C$  to 125°C), typical values at  $V_{IN} = 12$  V and  $T_A = 25^{\circ}C$  (unless otherwise noted)

PARAMETER		TEST CON	IDITIONS	MIN	TYP	MAX	UNIT
SUPPLY							
V <sub>IN</sub>	Input voltage range <sup>(1)</sup>			3		17	V
	Operating quiescent current	EN=High, I <sub>OUT</sub> = 0 mA,			17	30	
l <sub>Q</sub>	Operating quescent current	device not switching	$T_A = -40^{\circ}C \text{ to } +85^{\circ}C$		17	25	μA
I <sub>SD</sub>	Shutdown current <sup>(2)</sup>	EN=Low			1.5	25	μA
	Shudown current		$T_A = -40^{\circ}C$ to $+85^{\circ}C$		1.5	4	μΛ
V <sub>UVLO</sub>	Undervoltage lockout threshold	Falling Input Voltage (PV	VM mode operation)	2.6	2.7	2.8	V
		Hysteresis			200		mV
T <sub>SD</sub>	Thermal shutdown temperature				160		°C
	Thermal shutdown hysteresis				20		
CONTRO	L (EN, DEF, FSW, SS/TR, PG)			[			
V <sub>H</sub>	High level input threshold voltage (EN, DEF, FSW)			0.9	0.65		V
VL	Low level input threshold voltage (EN, DEF, FSW)				0.45	0.3	V
I <sub>LKG</sub>	Input leakage current (EN, DEF, FSW)	EN=V <sub>IN</sub> or GND; DEF, F	SW=V <sub>OUT</sub> or GND		0.01	1	μA
		Rising (%V <sub>OUT</sub> )		92%	95%	98%	
$V_{TH_PG}$	Power good threshold voltage	Falling (%V <sub>OUT</sub> )	87%	90%	94%		
V <sub>OL_PG</sub>	Power good output low	I <sub>PG</sub> =-2mA		0.07	0.3	V	
I <sub>LKG_PG</sub>	Input leakage current (PG)	V <sub>PG</sub> =1.8V		1	400	nA	
I <sub>SS/TR</sub>	SS/TR pin source current			2.3	2.5	2.7	μA
POWER S	SWITCH						
	High-side MOSFET ON-resistance	V <sub>IN</sub> ≥6V			90	170	mΩ
P	Thigh-side MOSTET ON-resistance	V <sub>IN</sub> =3V		120		1115.2	
R <sub>DS(ON)</sub>	Low-side MOSFET ON-resistance	V <sub>IN</sub> ≥6V			40	70	mΩ
		V <sub>IN</sub> =3V			50		1115.2
I <sub>LIMF</sub>	High-side MOSFET forward current limit <sup>(3)</sup>	V <sub>IN</sub> =12V, T <sub>A</sub> = 25°C		3.6	4.2	4.9	А
OUTPUT							
I <sub>LKG_FB</sub>	Input leakage current (FB)	TPS62130, V <sub>FB</sub> =0.8V			1	100	nA
	Output voltage range (TPS62130)	V <sub>IN</sub> ≥ V <sub>OUT</sub>		0.9		6.0	V
	DEF (Output voltage programming)	DEF=0 (GND)			V <sub>OUT</sub>		
		DEF=1 (V <sub>OUT</sub> )		Vo	<sub>UT</sub> +5%		
		PWM mode operation, V	IN ≥ V <sub>OUT</sub> +1V	785.6	800	814.4	
V <sub>OUT</sub> Initia	Initial output voltage accuracy <sup>(4)</sup>	PWM mode operation, V T <sub>A</sub> = $-10^{\circ}$ C to 85°C	788.0	800	812.8	mV	
		Power Save Mode opera	781.6	800	822.4		
	Tracking Feedback Voltage (TPS62130)	V <sub>SS/TR</sub> = 350mV		212.6	225	237.4	mV
	Load regulation <sup>(5)</sup>	V <sub>IN</sub> =12V, V <sub>OUT</sub> =3.3V, PV	VM mode operation		0.05		%/A
	Line regulation <sup>(5)</sup>	$3V \le V_{IN} \le 17V, V_{OUT}=3.$ mode operation	3V, I <sub>OUT</sub> = 1A, PWM		0.02		%/V

(1) The device is still functional down to Under Voltage Lockout (see parameter V<sub>UVLO</sub>).

(4) This is the accuracy provided at the FB pin for the adjustable V<sub>OUT</sub> version (line and load regulation effects are not included). For the fixed output voltage versions the (internal) resistive divider is included.


(5) Line and load regulation depend on external component selection and layout (see Figure 22 and Figure 23).

<sup>(2)</sup> Current into AVIN+PVIN pin.

<sup>(3)</sup> This is the static current limit. It can be temporarily higher in applications due to internal propagation delay (see Current Limit And Short Circuit Protection section).



## 7.6 Typical Characteristics





## 8 Detailed Description


## 8.1 Overview

The TPS6213X synchronous switched mode power converters are based on DCS-Control<sup>™</sup> (**D**irect **C**ontrol with **S**eamless Transition into Power Save Mode), an advanced regulation topology, that combines the advantages of hysteretic, voltage mode and current mode control including an AC loop directly associated to the output voltage. This control loop takes information about output voltage changes and feeds it directly to a fast comparator stage. It sets the switching frequency, which is constant for steady state operating conditions, and provides immediate response to dynamic load changes. To get accurate DC load regulation, a voltage feedback loop is used. The internally compensated regulation network achieves fast and stable operation with small external components and low ESR capacitors.

The DCS-Control<sup>™</sup> topology supports PWM (Pulse Width Modulation) mode for medium and heavy load conditions and a Power Save Mode at light loads. During PWM, it operates at its nominal switching frequency in continuous conduction mode. This frequency is typically about 2.5MHz or 1.25MHz with a controlled frequency variation depending on the input voltage. If the load current decreases, the converter enters Power Save Mode to sustain high efficiency down to very light loads. In Power Save Mode the switching frequency decreases linearly with the load current. Since DCS-Control<sup>™</sup> supports both operation modes within one single building block, the transition from PWM to Power Save Mode is seamless without effects on the output voltage.

Fixed output voltage versions provide smallest solution size and lowest current consumption, requiring only 4 external components. An internal current limit supports nominal output currents of up to 3A.

The TPS6213X family offers both excellent DC voltage and superior load transient regulation, combined with very low output voltage ripple, minimizing interference with RF circuits.



## 8.2 Functional Block Diagram


\* This pin is connected to a pull down resistor internally (see *Feature Description* section).

## Figure 5. TPS62130 and TPS62130A (Adjustable Output Voltage)

8



## Functional Block Diagram (continued)



<sup>\*</sup> This pin is connected to a pull down resistor internally (see *Feature Description* section).

Figure 6. TPS62131/2/3 (Fixed Output Voltage)

## 8.3 Feature Description

## 8.3.1 Enable / Shutdown (EN)

When Enable (EN) is set High, the device starts operation. Shutdown is forced if EN is pulled Low with a shutdown current of typically 1.5 $\mu$ A. During shutdown, the internal power MOSFETs as well as the entire control circuitry are turned off. The internal resistive divider pulls down the output voltage smoothly. The EN signal must be set externally to High or Low. An internal pull-down resistor of about 400k $\Omega$  is connected and keeps EN logic low, if Low is set initially and then the pin gets floating. It is disconnected if the pin is set High.

Connecting the EN pin to an appropriate output signal of another power rail provides sequencing of multiple power rails.

## 8.3.2 Soft Start / Tracking (SS/TR)

The internal soft start circuitry controls the output voltage slope during startup. This avoids excessive inrush current and ensures a controlled output voltage rise time. It also prevents unwanted voltage drops from high-impedance power sources or batteries. When EN is set to start device operation, the device starts switching after a delay of about 50 $\mu$ s and V<sub>OUT</sub> rises with a slope controlled by an external capacitor connected to the SS/TR pin. See Figure 40 and Figure 41 for typical startup operation.



## Feature Description (continued)

Using a very small capacitor (or leaving SS/TR pin un-connected) provides fastest startup behavior. There is no theoretical limit for the longest startup time. The TPS6213X can start into a pre-biased output. During monotonic pre-biased startup, both the power MOSFETs are not allowed to turn on until the device's internal ramp sets an output voltage above the pre-bias voltage. As long as the output is below about 0.5V a reduced current limit of typically 1.6A is set internally. If the device is set to shutdown (EN=GND), undervoltage lockout or thermal shutdown, an internal resistor pulls the SS/TR pin down to ensure a proper low level. Returning from those states causes a new startup sequence as set by the SS/TR connection.

A voltage supplied to SS/TR can be used for tracking a master voltage. The output voltage will follow this voltage in both directions up and down (see *Application and Implementation*).

## 8.3.3 Power Good (PG)

The TPS6213X has a built in power good (PG) function to indicate whether the output voltage has reached its appropriate level or not. The PG signal can be used for startup sequencing of multiple rails. The PG pin is an open-drain output that requires a pull-up resistor (to any voltage below 7 V). It can sink 2 mA of current and maintain its specified logic low level. With TPS62130 it is high impedance when the device is turned off due to EN, UVLO or thermal shutdown. TPS62130A features PG=Low in this case and can be used to actively discharge  $V_{OUT}$  (see Figure 47).  $V_{IN}$  must remain present for the PG pin to stay Low. See SLVA644 for application details. If not used, the PG pin should be connected to GND but may be left floating.

Davia	- State	PG Logic Status					
Devic	e State	High Impedance	Low				
Enable (EN=High)	$V_{FB} \ge V_{TH_PG}$	√					
	$V_{FB} \le V_{TH_PG}$		$\checkmark$				
Shutdown (EN=Low)		√					
UVLO	$0.7 \text{ V} < \text{V}_{\text{IN}} < \text{V}_{\text{UVLO}}$	√					
Thermal Shutdown	T <sub>J</sub> > T <sub>SD</sub>	√					
Power Supply Removal V <sub>IN</sub> < 0.7 V		√					

## Table 1. Power Good Pin Logic Table (TPS62130)

Dev	ing State	PG Logic Status					
Dev	ice State	High Impedance	Low				
Enchle (ENLLER)	V <sub>FB</sub> ≥ V <sub>TH_PG</sub>	$\checkmark$					
Enable (EN=High)	V <sub>FB</sub> ≤ V <sub>TH_PG</sub>		$\checkmark$				
Shutdown (EN=Low)			$\checkmark$				
UVLO	$0.7 \text{ V} < \text{V}_{\text{IN}} < \text{V}_{\text{UVLO}}$		$\checkmark$				
Thermal Shutdown	$T_J > T_{SD}$						
Power Supply Removal V <sub>IN</sub> < 0.7 V		$\checkmark$					

Table 2. Power Good Pin Logic Table (TPS62130A)

## 8.3.4 Pin-Selectable Output Voltage (DEF)

The output voltage of the TPS6213X devices can be increased by 5% above the nominal voltage by setting the DEF pin to High <sup>(1)</sup>. When DEF is Low, the device regulates to the nominal output voltage. Increasing the nominal voltage allows adapting the power supply voltage to the variations of the application hardware. More detailed information on voltage margining using TPS6213X can be found in SLVA489. A pull down resistor of about 400 k $\Omega$  is internally connected to the pin, to ensure a proper logic level if the pin is high impedance or floating after initially set to Low. The resistor is disconnected if the pin is set High.

(1) Maximum allowed voltage is 7 V. Therefore, it is recommended to connect it to V<sub>OUT</sub> or PG, not V<sub>IN</sub>.



## 8.3.5 Frequency Selection (FSW)

To get high power density with very small solution size, a high switching frequency allows the use of small external components for the output filter. However switching losses increase with the switching frequency. If efficiency is the key parameter, more than solution size, the switching frequency can be set to half (1.25 MHz typ.) by pulling FSW to High. It is mandatory to start with FSW=Low to limit inrush current, which can be done by connecting to V<sub>OUT</sub> or PG. Running with lower frequency a higher efficiency, but also a higher output voltage ripple, is achieved. Pull FSW to Low for high frequency operation (2.5 MHz typ.). To get low ripple and full output current at the lower switching frequency, it's recommended to use an inductor of at least 2.2 µH. The switching frequency can be changed during operation, if needed. A pull down resistor of about 400kOhm is internally connected to the pin, acting the same way as at the DEF Pin (see above).

## 8.3.6 Under Voltage Lockout (UVLO)

If the input voltage drops, the under voltage lockout prevents misoperation of the device by switching off both the power FETs. The under voltage lockout threshold is set typically to 2.7V. The device is fully operational for voltages above the UVLO threshold and turns off if the input voltage trips the threshold. The converter starts operation again once the input voltage exceeds the threshold by a hysteresis of typically 200mV.

## 8.3.7 Thermal Shutdown

The junction temperature (Tj) of the device is monitored by an internal temperature sensor. If Tj exceeds 160°C (typ), the device goes into thermal shut down. Both the high-side and low-side power FETs are turned off and PG goes high impedance. When Tj decreases below the hysteresis amount, the converter resumes normal operation, beginning with Soft Start. To avoid unstable conditions, a hysteresis of typically 20°C is implemented on the thermal shut down temperature.

## 8.4 Device Functional Modes

## 8.4.1 Pulse Width Modulation (PWM) Operation

The TPS6213X operates with pulse width modulation in continuous conduction mode (CCM) with a nominal switching frequency of 2.5 MHz or 1.25 MHz, selectable with the FSW pin. The frequency variation in PWM is controlled and depends on VIN, VOUT and the inductance. The device operates in PWM mode as long the output current is higher than half the inductor's ripple current. To maintain high efficiency at light loads, the device enters Power Save Mode at the boundary to discontinuous conduction mode (DCM). This happens if the output current becomes smaller than half the inductor's ripple current.

## 8.4.2 Power Save Mode Operation

The TPS6213X enters its built in Power Save Mode seamlessly if the load current decreases. This secures a high efficiency in light load operation. The device remains in Power Save Mode as long as the inductor current is discontinuous.

In Power Save Mode the switching frequency decreases linearly with the load current maintaining high efficiency. The transition into and out of Power Save Mode happens within the entire regulation scheme and is seamless in both directions.

TPS6213X includes a fixed on-time circuitry. An estimate for this on-time, in steady-state operation with FSW = Low, is:

$$t_{ON} = \frac{V_{OUT}}{V_{IN}} \cdot 400 ns \tag{1}$$

)

For very small output voltages, an absolute minimum on-time of about 80ns is kept to limit switching losses. The operating frequency is thereby reduced from its nominal value, which keeps efficiency high. Also the off-time can reach its minimum value at high duty cycles. The output voltage remains regulated in such case. Using  $t_{ON}$ , the typical peak inductor current in Power Save Mode can be approximated by:

**Device Functional Modes (continued)** 

$$I_{LPSM(peak)} = \frac{(V_{IN} - V_{OUT})}{L} \cdot t_{ON}$$

When  $V_{IN}$  decreases to typically 15% above  $V_{OUT}$ , the TPS6213X won't enter Power Save Mode, regardless of the load current. The device maintains output regulation in PWM mode.

#### 8.4.3 100% Duty-Cycle Operation

The duty cycle of the buck converter is given by  $D=V_{OUT}/V_{IN}$  and increases as the input voltage comes close to the output voltage. In this case, the device starts 100% duty cycle operation turning on the high-side switch 100% of the time. The high-side switch stays turned on as long as the output voltage is below the internal set point. This allows the conversion of small input to output voltage differences, e.g. for longest operation time of battery-powered applications. In 100% duty cycle mode, the low-side FET is switched off.

The minimum input voltage to maintain output voltage regulation, depending on the load current and the output voltage level, can be calculated as:

$$V_{IN(min)} = V_{OUT(min)} + I_{OUT} \left( R_{DS(on)} + R_L \right)$$

where

I<sub>OUT</sub> is the output current,

 $R_{\text{DS}(\text{on})}$  is the  $R_{\text{DS}(\text{on})}$  of the high-side FET and

 $R_L$  is the DC resistance of the inductor used.

#### 8.4.4 Current Limit And Short Circuit Protection

The TPS6213X devices have protection against heavy load and short circuit events. If a short circuit is detected ( $V_{OUT}$  drops below 0.5 V), the current limit is reduced to 1.6 A typically. If the output voltage rises above 0.5 V, the device runs in normal operation again. At heavy loads, the current limit determines the maximum output current. If the current limit is reached, the high-side FET is turned off. Avoiding shoot through current, then the low-side FET switches on to allow the inductor current to decrease. The low-side current limit is typically 3.5 A. The high-side FET turns on again only if the current in the low-side FET has decreased below the low-side current limit threshold.

The output current of the device is limited by the current limit (see *Electrical Characteristics*). Due to internal propagation delay, the actual current can exceed the static current limit during that time. The dynamic current limit can be calculated as follows:

$$I_{peak(typ)} = I_{LIMF} + \frac{V_L}{L} \cdot t_{PD}$$

where

ILIMF is the static current limit, specified in the *Electrical Characteristics*,

L is the inductor value,

 $V_L$  is the voltage across the inductor ( $V_{IN}$  -  $V_{OUT}$ ) and

-- )

t<sub>PD</sub> is the internal propagation delay.

The current limit can exceed static values, especially if the input voltage is high and very small inductances are used. The dynamic high-side switch peak current can be calculated as follows:

$$I_{peak(typ)} = I_{LIMF} + \frac{(V_{IN} - V_{OUT})}{L} \cdot 30ns$$

1---



(3)

(5)



(2)



## 9 Application and Implementation

## NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

## 9.1 Application Information

The TPS6213X is a switched mode step-down converter, able to convert a 3V to 17V input voltage into a 0.9V to 6V output voltage, providing up to 3A. It needs a minimum amount of external components. Apart from the LC output filter and the input capacitors, only the TPS62130 (TPS62130A) with adjustable output voltage needs an additional resistive divider to set the output voltage level.

## 9.2 Typical Application




Figure 7. 3A Step-Down Converter for Point-Of-Load Power Supply Using TPS62130

## 9.2.1 Design Requirements

The following design guideline provides a component selection to operate the device within the recommended operating conditions. Using the FSW pin, the design can be optimized for highest efficiency or smallest solution size and lowest output voltage ripple. For highest efficiency set FSW = High and the device operates at the lower switching frequency. For smallest solution size and lowest output voltage ripple set FSW = Low and the device operates with higher switching frequency. The typical values for all measurements are  $V_{IN} = 12$  V,  $V_{OUT} = 3.3$  V and T = 25°C, using the external components of Table 3.

The component selection used for measurements is given as follows:

Table 3	. List	Of Com	ponents <sup>(1)</sup>
---------	--------	--------	------------------------

REFERENCE	DESCRIPTION	MANUFACTURER
IC	17V, 3A Step-Down Converter, QFN	TPS62130RGT, Texas Instruments
L1	2.2µH, 0.165 x 0.165 in	XFL4020-222MEB, Coilcraft
C1	10µF, 25V, Ceramic, 1210	Standard
C3	22µF, 6.3V, Ceramic, 0805	Standard
C5	3300pF, 25V, Ceramic, 0603	Standard
C7	0.1µF, 25V, Ceramic, 0603	Standard
R1	depending on V <sub>OUT</sub>	
R2	depending on V <sub>OUT</sub>	
R3	100kΩ, Chip, 0603, 1/16W, 1%	Standard

(1) See Third-Party Products Disclaimer.



#### 9.2.2 Detailed Design Procedure

#### 9.2.2.1 Programming The Output Voltage

While the output voltage of the TPS62130 (TPS62130A) is adjustable, the TPS62131/2/3 are programmed to fixed output voltages. For fixed output voltage versions, the FB pin is pulled down internally and may be left floating. It is recommended to connect to AGND to improve thermal resistance. The adjustable version can be programmed for output voltages from 0.9 V to 6 V by using a resistive divider from V<sub>OUT</sub> to AGND. The voltage at the FB pin is regulated to 800mV. The value of the output voltage is set by the selection of the resistive divider from Equation 6. It is recommended to choose resistor values which allow a current of at least 2uA, meaning the value of R2 shouldn't exceed 400 k $\Omega$ . Lower resistor values are recommended for highest accuracy and most robust design. For applications requiring lowest current consumption, the use of fixed output voltage versions is recommended.

$$\mathsf{R}_1 = \mathsf{R}_2 \bigg( \frac{\mathsf{V}_{\mathsf{OUT}}}{0.8\mathsf{V}} - 1 \bigg) \tag{6}$$

In case the FB pin gets opened, the device clamps the output voltage at the VOS pin internally to about 7.4V.

#### 9.2.2.2 External Component Selection

The external components have to fulfill the needs of the application, but also the stability criteria of the devices control loop. The TPS6213X is optimized to work within a range of external components. The LC output filter's inductance and capacitance have to be considered together, creating a double pole, responsible for the corner frequency of the converter (see *Output Filter And Loop Stability*). Table 4 can be used to simplify the output filter component selection. Checked cells represent combinations that are proven for stability by simulation and lab test. Further combinations should be checked for each individual application. See SLVA463 for details.

	4.7µF	10µF	22µF	47µF	100µF	200µF	400µF
0.47µH							
1µH			$\checkmark$	$\checkmark$	$\checkmark$	$\checkmark$	
2.2µH		$\checkmark$	√(2)	$\checkmark$	$\checkmark$	$\checkmark$	
3.3µH		$\checkmark$	$\checkmark$	$\checkmark$	$\checkmark$		
4.7µH							

Table 4. Recommended LC Output Filter Combinations<sup>(1)</sup>

(1) The values in the table are nominal values. The effective capacitance was considered to vary by +20% and -50%.

(2) This LC combination is the standard value and recommended for most applications.

The TPS6213X can be run with an inductor as low as  $1\mu$ H. FSW should be set Low in this case. However, for applications running with the low frequency setting (FSW=High) or with low input voltages, 2.2 $\mu$ H is recommended.

#### 9.2.2.2.1 Inductor Selection

The inductor selection is affected by several effects like inductor ripple current, output ripple voltage, PWM-to-PSM transition point and efficiency. In addition, the inductor selected has to be rated for appropriate saturation current and DC resistance (DCR). Equation 7 and Equation 8 calculate the maximum inductor current under static load conditions.

$$I_{\rm L(max)} = I_{\rm OUT(max)} + \frac{\Delta I_{\rm L(max)}}{2}$$

(7)



where

$$\Delta I_{L(\max)} = V_{OUT} \cdot \left( \frac{1 - \frac{V_{OUT}}{V_{IN(\max)}}}{L_{(\min)} \cdot f_{SW}} \right)$$

I<sub>L</sub>(max) is the maximum inductor current,

 $\Delta I_L$  is the Peak to Peak Inductor Ripple Current,

L(min) is the minimum effective inductor value and

f<sub>SW</sub> is the actual PWM Switching Frequency.

Calculating the maximum inductor current using the actual operating conditions gives the minimum saturation current of the inductor needed. A margin of about 20% is recommended to add. A larger inductor value is also useful to get lower ripple current, but increases the transient response time and size as well. The following inductors have been used with the TPS6213X and are recommended for use:

Туре	Inductance [µH]	Current [A] <sup>(2)</sup>	Dimensions [LxBxH] mm	MANUFACTURER
XFL4020-102ME_	1.0 μH, ±20%	4.7	4 x 4 x 2.1	Coilcraft
XFL4020-152ME_	1.5 μH, ±20%	4.2	4 x 4 x 2.1	Coilcraft
XFL4020-222ME_	2.2 μH, ±20%	3.8	4 x 4 x 2.1	Coilcraft
IHLP1212BZ-11	1.0 μH, ±20%	4.5	3 x 3.6 x 2	Vishay
IHLP1212BZ-11	2.2 μH, ±20%	3.0	3 x 3.6 x 2	Vishay
SRP4020-3R3M	3.3µH, ±20%	3.3	4.8 x 4 x 2	Bourns
VLC5045T-3R3N	3.3μH, ±30%	4.0	5 x 5 x 4.5	TDK

Table 5. List Of Inductors<sup>(1)</sup>

(1) See Third-Party Products Disclaimer

(2) Lower of I<sub>RMS</sub> at 40°C rise or I<sub>SAT</sub> at 30% drop.

The inductor value also determines the load current at which Power Save Mode is entered:

$$I_{load(PSM)} = \frac{1}{2} \Delta I_L$$

(9)

Using Equation 8, this current level can be adjusted by changing the inductor value.

#### 9.2.2.2.2 Capacitor Selection

#### 9.2.2.2.2.1 Output Capacitor

The recommended value for the output capacitor is 22uF. The architecture of the TPS6213X allows the use of tiny ceramic output capacitors with low equivalent series resistance (ESR). These capacitors provide low output voltage ripple and are recommended. To keep its low resistance up to high frequencies and to get narrow capacitance variation with temperature, it's recommended to use X7R or X5R dielectric. Using a higher value can have some advantages like smaller voltage ripple and a tighter DC output accuracy in Power Save Mode (see SLVA463).

Note: In power save mode, the output voltage ripple depends on the output capacitance, its ESR and the peak inductor current. Using ceramic capacitors provides small ESR and low ripple.

#### 9.2.2.2.2.2 Input Capacitor

For most applications, 10µF will be sufficient and is recommended, though a larger value reduces input current ripple further. The input capacitor buffers the input voltage for transient events and also decouples the converter from the supply. A low ESR multilayer ceramic capacitor is recommended for best filtering and should be placed between PVIN and PGND as close as possible to those pins. Even though AVIN and PVIN must be supplied from the same input source, it's required to place a capacitance of 0.1µF from AVIN to AGND, to avoid potential noise coupling. An RC, low-pass filter from PVIN to AVIN may be used but is not required.

#### 9.2.2.2.2.3 Soft Start Capacitor

A capacitance connected between SS/TR pin and AGND allows a user programmable start-up slope of the output voltage. A constant current source supports 2.5µA to charge the external capacitance. The capacitor required for a given soft-start ramp time for the output voltage is given by:

$$C_{SS} = t_{SS} \cdot \frac{2.5 \mu A}{1.25 V} \quad [F]$$

(10)

## where

 $C_{SS}$  is the capacitance (F) required at the SS/TR pin and  $t_{SS}$  is the desired soft-start ramp time (s).

#### NOTE

**DC Bias effect:** High capacitance ceramic capacitors have a DC Bias effect, which will have a strong influence on the final effective capacitance. Therefore the right capacitor value has to be chosen carefully. Package size and voltage rating in combination with dielectric material are responsible for differences between the rated capacitor value and the effective capacitance.

#### 9.2.2.3 Tracking Function

If a tracking function is desired, the SS/TR pin can be used for this purpose by connecting it to an external tracking voltage. The output voltage tracks that voltage. If the tracking voltage is between 50mV and 1.2V, the FB pin will track the SS/TR pin voltage as described in Equation 11 and shown in Figure 8.

$$V_{FB} \approx 0.64 \cdot V_{SS/TR}$$

(11)





Figure 8. Voltage Tracking Relationship





Once the SS/TR pin voltage reaches about 1.2 V, the internal voltage is clamped to the internal feedback voltage and device goes to normal regulation. This works for rising and falling tracking voltages with the same behavior, as long as the input voltage is inside the recommended operating conditions. For decreasing SS/TR pin voltage, the device does not sink current from the output. So, the resulting decrease of the output voltage may be slower than the SS/TR pin voltage if the load is light. When driving the SS/TR pin with an external voltage, do not exceed the voltage rating of the SS/TR pin which is  $V_{IN}$  + 0.3 V.

If the input voltage drops into undervoltage lockout or even down to zero, the output voltage will go to zero, independent of the tracking voltage. Figure 9 shows how to connect devices to get ratiometric and simultaneous sequencing by using the tracking function.



Copyright © 2016, Texas Instruments Incorporated

Figure 9. Sequence For Ratiometric And Simultaneous Startup

The resistive divider of R1 and R2 can be used to change the ramp rate of  $V_{OUT2}$  faster, slower or the same as  $V_{OUT1}$ .

A sequential startup is achieved by connecting the PG pin of  $V_{OUT1}$  to the EN pin of  $V_{OUT2}$ . Ratiometric start up sequence happens if both supplies are sharing the same soft start capacitor. Equation 10 calculates the soft start time, though the SS/TR current has to be doubled. Details about these and other tracking and sequencing circuits are found in SLVA470.

Note: If the voltage at the FB pin is below its typical value of 0.8V, the output voltage accuracy may have a wider tolerance than specified.

#### 9.2.2.4 Output Filter And Loop Stability

The devices of the TPS6213X family are internally compensated to be stable with L-C filter combinations corresponding to a corner frequency to be calculated with Equation 12:

$$f_{LC} = \frac{1}{2\pi \sqrt{L \cdot C}}$$

(12)

Proven nominal values for inductance and ceramic capacitance are given in Table 4 and are recommended for use. Different values may work, but care has to be taken on the loop stability which will be affected. More information including a detailed LC stability matrix can be found in SLVA463.

The TPS6213X devices, both fixed and adjustable output voltage versions, include an internal 25pF feedforward capacitor, connected between the VOS and FB pins. This capacitor impacts the frequency behavior and sets a pole and zero in the control loop with the resistors of the feedback divider, per equation 13 and Equation 14:

$$f_{zero} = \frac{1}{2\pi \cdot R_1 \cdot 25 \, pF} \tag{13}$$
$$f_{pole} = \frac{1}{2\pi \cdot 25 \, pF} \cdot \left(\frac{1}{R_1} + \frac{1}{R_2}\right) \tag{14}$$

Though the TPS6213X devices are stable without the pole and zero being in a particular location, adjusting their location to the specific needs of the application can provide better performance in Power Save mode and/or improved transient response. An external feedforward capacitor can also be added. A more detailed discussion on the optimization for stability vs. transient response can be found in SLVA289 and SLVA466.




www.ti.com

(14)




## 9.2.3 Application Curves

 $V_{IN}$  = 12 V,  $V_{OUT}$  = 3.3 V,  $T_A$  = 25°C, (unless otherwise noted)






## TPS62130, TPS62130A, TPS62131, TPS62132, TPS62133 SLVSAG7E – NOVEMBER 2011 – REVISED AUGUST 2016










## TPS62130, TPS62130A, TPS62131, TPS62132, TPS62133 SLVSAG7E – NOVEMBER 2011 – REVISED AUGUST 2016


www.ti.com






#### TPS62130, TPS62130A, TPS62131, TPS62132, TPS62133 SLVSAG7E – NOVEMBER 2011–REVISED AUGUST 2016







#### TPS62130, TPS62130A, TPS62131, TPS62132, TPS62133 SLVSAG7E – NOVEMBER 2011 – REVISED AUGUST 2016





## 9.3 System Examples

## 9.3.1 LED Power Supply

The TPS62130 can be used as a power supply for power LEDs. The FB pin can be easily set down to lower values than nominal by using the SS/TR pin. With that, the voltage drop on the sense resistor is low to avoid excessive power loss. Since this pin provides 2.5µA, the feedback pin voltage can be adjusted by an external resistor per Equation 15. This drop, proportional to the LED current, is used to regulate the output voltage (anode voltage) to a proper level to drive the LED. Both analog and PWM dimming are supported with the TPS62130. Figure 46 shows an application circuit, tested with analog dimming:




Figure 46. Single Power LED Supply

The resistor at SS/TR sets the FB voltage to a level of about 300mV and is calculated from Equation 15.

$$V_{FB} = 0.64 \cdot 2.5 \mu A \cdot R_{SS/TR} \tag{15}$$


The device now supplies a constant current, set by the resistor at the FB pin, by regulating the output voltage accordingly. The minimum input voltage has to be rated according the forward voltage needed by the LED used. More information is available in the Application Note SLVA451.

## 9.3.2 Active Output Discharge

The TPS62130A pulls the PG pin Low, when the device is shut down by EN, UVLO or thermal shutdown. Connecting PG to  $V_{OUT}$  through a resistor can be used to discharge  $V_{OUT}$  in those cases (see Figure 47). The discharge rate can be adjusted by R3, which is also used to pull up the PG pin in normal operation. For reliability, keep the maximum current into the PG pin less than 10mA.



## System Examples (continued)





## 9.3.3 –3.3V Inverting Power Supply

The TPS62130 can be used as inverting power supply by rearranging external circuitry as shown in Figure 48. As the former GND node now represents a voltage level below system ground, the voltage difference between  $V_{IN}$  and  $V_{OUT}$  has to be limited for operation to the maximum supply voltage of 17V (see Equation 16).

$$V_{IN} + \left| V_{OUT} \right| \le V_{IN max}$$

(16)




Figure 48. -3.3 V Inverting Power Supply


The transfer function of the inverting power supply configuration differs from the buck mode transfer function, incorporating a Right Half Plane Zero additionally. The loop stability has to be adapted and an output capacitance of at least  $22\mu$ F is recommended. A detailed design example is given in SLVA469.

## 9.3.4 Various Output Voltages

The following example circuits show how to use the various devices and configure the external circuitry to furnish different output voltages at 3A.



## System Examples (continued)










Figure 50. 3.3V/3A Power Supply







## System Examples (continued)




Figure 52. 1.8V/3A Power Supply




Figure 53. 1.5V/3A Power Supply




Figure 54. 1.2V/3A Power Supply



## System Examples (continued)




Figure 55. 1V/3A Power Supply

## **10** Power Supply Recommendations

The TPS6213X are designed to operate from a 3-V to 17-V input voltage supply. The input power supply's output current needs to be rated according to the output voltage and the output current of the power rail application.



## 11 Layout

## 11.1 Layout Guidelines

A proper layout is critical for the operation of a switched mode power supply, even more at high switching frequencies. Therefore the PCB layout of the TPS6213X demands careful attention to ensure operation and to get the performance specified. A poor layout can lead to issues like poor regulation (both line and load), stability and accuracy weaknesses, increased EMI radiation and noise sensitivity.

See Figure 56 for the recommended layout of the TPS6213X, which is designed for common external ground connections. Therefore both AGND and PGND pins are directly connected to the Exposed Thermal Pad. On the PCB, the direct common ground connection of AGND and PGND to the Exposed Thermal Pad and the system ground (ground plane) is mandatory. Also connect the VOS pin in the shortest way to  $V_{OUT}$  at the output capacitor. To avoid noise coupling into the VOS line, this connection should be separated from the  $V_{OUT}$  power line/plane as shown in *Layout Example*.

Provide low inductive and resistive paths for loops with high di/dt. Therefore paths conducting the switched load current should be as short and wide as possible. Provide low capacitive paths (with respect to all other nodes) for wires with high dv/dt. Therefore the input and output capacitance should be placed as close as possible to the IC pins and parallel wiring over long distances as well as narrow traces should be avoided. Loops which conduct an alternating current should outline an area as small as possible, as this area is proportional to the energy radiated.

Sensitive nodes like FB and VOS need to be connected with short wires and not nearby high dv/dt signals (e.g. SW). As they carry information about the output voltage, they should be connected as close as possible to the actual output voltage (at the output capacitor). The capacitor on the SS/TR pin and on AVIN as well as the FB resistors, R1 and R2, should be kept close to the IC and connect directly to those pins and the system ground plane.

The Exposed Thermal Pad must be soldered to the circuit board for mechanical reliability and to achieve appropriate power dissipation.

The recommended layout is implemented on the EVM and shown in its Users Guide, SLVU437. Additionally, the EVM Gerber data are available for download here, SLVC394.

## 11.2 Layout Example




Figure 56. Layout Example



## **11.3 Thermal Information**

Implementation of integrated circuits in low-profile and fine-pitch surface-mount packages typically requires special attention to power dissipation. Many system-dependent issues such as thermal coupling, airflow, added heat sinks and convection surfaces, and the presence of other heat-generating components affect the power-dissipation limits of a given component.

Three basic approaches for enhancing thermal performance are listed below:

- Improving the power dissipation capability of the PCB design
- Improving the thermal coupling of the component to the PCB by soldering the Exposed Thermal Pad
- Introducing airflow in the system

For more details on how to use the thermal parameters, see the application notes: Thermal Characteristics Application Note (SZZA017), and (SPRA953).

The TPS6213X is designed for a maximum operating junction temperature  $(T_j)$  of 125°C. Therefore the maximum output power is limited by the power losses that can be dissipated over the actual thermal resistance, given by the package and the surrounding PCB structures. Since the thermal resistance of the package is fixed, increasing the size of the surrounding copper area and improving the thermal connection to the IC can reduce the thermal resistance. To get an improved thermal behavior, it's recommended to use top layer metal to connect the device with wide and thick metal lines. Internal ground layers can connect to vias directly under the IC for improved thermal performance.

If short circuit or overload conditions are present, the device is protected by limiting internal power dissipation. Experimental data, taken from the TPS62130 EVM, shows the maximum ambient temperature (without additional cooling like airflow or heat sink), that can be allowed to limit the junction temperature to at most 125°C (see Figure 44).

## **12 Device and Documentation Support**

## 12.1 Device Support

## 12.1.1 Third-Party Products Disclaimer

TI'S PUBLICATION OF INFORMATION REGARDING THIRD-PARTY PRODUCTS OR SERVICES DOES NOT CONSTITUTE AN ENDORSEMENT REGARDING THE SUITABILITY OF SUCH PRODUCTS OR SERVICES OR A WARRANTY, REPRESENTATION OR ENDORSEMENT OF SUCH PRODUCTS OR SERVICES, EITHER ALONE OR IN COMBINATION WITH ANY TI PRODUCT OR SERVICE.

## **12.2 Documentation Support**

- Application Report, Voltage Margining Using the TPS62130 SLVA489
- Application Report, Using the TPS62150 as Step-Down LED Driver With Dimming SLVA451
- Application Report, Using the TPS6215x in an Inverting Buck-Boost Topology SLVA469
- Application Report, Optimizing the TPS62130/40/50/60/70 Output Filter SLVA463
- Application Report, TPS62130/40/50 Sequencing and Tracking SLVA470
- Application Report, Optimizing Transient Response of Internally Compensated dc-dc Converters With Feedforward Capacitor SLVA289
- Application Report, Using a Feedforward Capacitor to Improve Stability and Bandwidth of TPS62130/40/50/60/70 SLVA466
- Application Report, Thermal Characteristics of Linear and Logic Packages Using JEDEC PCB Designs SZZA017
- Application Report, Semiconductor and IC Package Thermal Metrics SPRA953
- User's Guide, TPS62130EVM-505, TPS62140EVM-505, and TPS62150EVM-505 Evaluation Modules SLVU437
- EVM Gerber Data, SLVC394

## **12.3 Receiving Notification of Documentation Updates**

To receive notification of documentation updates, navigate to the device product folder on ti.com. In the upper right corner, click on *Alert me* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

## 12.4 Related Links

The table below lists quick access links. Categories include technical documents, support and community resources, tools and software, and quick access to sample or buy.

PARTS	PRODUCT FOLDER	SAMPLE & BUY	TECHNICAL DOCUMENTS	TOOLS & SOFTWARE	SUPPORT & COMMUNITY
TPS62130	Click here	Click here	Click here	Click here	Click here
TPS62130A	Click here	Click here	Click here	Click here	Click here
TPS62131	Click here	Click here	Click here	Click here	Click here
TPS62132	Click here	Click here	Click here	Click here	Click here
TPS62133	Click here	Click here	Click here	Click here	Click here

#### Table 6. Related Links



## 12.5 Community Resources

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

TI E2E<sup>™</sup> Online Community *TI's Engineer-to-Engineer (E2E) Community.* Created to foster collaboration among engineers. At e2e.ti.com, you can ask questions, share knowledge, explore ideas and help solve problems with fellow engineers.

**Design Support TI's Design Support** Quickly find helpful E2E forums along with design support tools and contact information for technical support.

## 12.6 Trademarks

DCS-Control, E2E are trademarks of Texas Instruments. All other trademarks are the property of their respective owners.

## 12.7 Electrostatic Discharge Caution



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

## 12.8 Glossary

SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.

## 13 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.



11-Aug-2017

## PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead/Ball Finish (6)	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
TPS62130ARGTR	ACTIVE	VQFN	RGT	16	3000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-2-260C-1 YEAR	-40 to 125	PA6I	Samples
TPS62130ARGTT	ACTIVE	VQFN	RGT	16	250	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-2-260C-1 YEAR	-40 to 125	PA6I	Samples
TPS62130RGTR	ACTIVE	VQFN	RGT	16	3000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-2-260C-1 YEAR	-40 to 125	PTSI	Samples
TPS62130RGTT	ACTIVE	VQFN	RGT	16	250	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-2-260C-1 YEAR	-40 to 125	PTSI	Samples
TPS62131RGTR	ACTIVE	VQFN	RGT	16	3000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-2-260C-1 YEAR	-40 to 125	QVX	Samples
TPS62131RGTT	ACTIVE	VQFN	RGT	16	250	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-2-260C-1 YEAR	-40 to 125	QVX	Samples
TPS62132RGTR	ACTIVE	VQFN	RGT	16	3000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-2-260C-1 YEAR	-40 to 125	QVY	Samples
TPS62132RGTT	ACTIVE	VQFN	RGT	16	250	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-2-260C-1 YEAR	-40 to 125	QVY	Samples
TPS62133RGTR	ACTIVE	VQFN	RGT	16	3000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-2-260C-1 YEAR	-40 to 125	QVZ	Samples
TPS62133RGTT	ACTIVE	VQFN	RGT	16	250	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-2-260C-1 YEAR	-40 to 125	QVZ	Samples

<sup>(1)</sup> The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

<sup>(2)</sup> RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

**RoHS Exempt:** TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <= 1000ppm threshold. Antimony trioxide based flame retardants must also meet the <= 1000ppm threshold requirement.

(3) MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.



11-Aug-2017

<sup>(4)</sup> There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

<sup>(5)</sup> Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

<sup>(6)</sup> Lead/Ball Finish - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

#### OTHER QUALIFIED VERSIONS OF TPS62130A :

• Automotive: TPS62130A-Q1

NOTE: Qualified Version Definitions:

• Automotive - Q100 devices qualified for high-reliability automotive applications targeting zero defects

# PACKAGE MATERIALS INFORMATION

www.ti.com

Texas Instruments

## TAPE AND REEL INFORMATION





## QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal												
Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TPS62130ARGTR	VQFN	RGT	16	3000	330.0	12.4	3.3	3.3	1.1	8.0	12.0	Q2
TPS62130ARGTT	VQFN	RGT	16	250	180.0	12.4	3.3	3.3	1.1	8.0	12.0	Q2
TPS62130RGTR	VQFN	RGT	16	3000	330.0	12.4	3.3	3.3	1.1	8.0	12.0	Q2
TPS62130RGTT	VQFN	RGT	16	250	180.0	12.5	3.3	3.3	1.1	8.0	12.0	Q2
TPS62131RGTR	VQFN	RGT	16	3000	330.0	12.4	3.3	3.3	1.1	8.0	12.0	Q2
TPS62131RGTT	VQFN	RGT	16	250	180.0	12.4	3.3	3.3	1.1	8.0	12.0	Q2
TPS62132RGTR	VQFN	RGT	16	3000	330.0	12.4	3.3	3.3	1.1	8.0	12.0	Q2
TPS62132RGTT	VQFN	RGT	16	250	180.0	12.4	3.3	3.3	1.1	8.0	12.0	Q2
TPS62133RGTR	VQFN	RGT	16	3000	330.0	12.4	3.3	3.3	1.1	8.0	12.0	Q2
TPS62133RGTT	VQFN	RGT	16	250	180.0	12.4	3.3	3.3	1.1	8.0	12.0	Q2

Texas Instruments

www.ti.com

# PACKAGE MATERIALS INFORMATION

14-Feb-2018



*All dimensions are nominal							
Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TPS62130ARGTR	VQFN	RGT	16	3000	552.0	367.0	36.0
TPS62130ARGTT	VQFN	RGT	16	250	552.0	185.0	36.0
TPS62130RGTR	VQFN	RGT	16	3000	338.0	355.0	50.0
TPS62130RGTT	VQFN	RGT	16	250	338.0	355.0	50.0
TPS62131RGTR	VQFN	RGT	16	3000	367.0	367.0	35.0
TPS62131RGTT	VQFN	RGT	16	250	210.0	185.0	35.0
TPS62132RGTR	VQFN	RGT	16	3000	367.0	367.0	35.0
TPS62132RGTT	VQFN	RGT	16	250	210.0	185.0	35.0
TPS62133RGTR	VQFN	RGT	16	3000	367.0	367.0	35.0
TPS62133RGTT	VQFN	RGT	16	250	210.0	185.0	35.0

# **GENERIC PACKAGE VIEW**

# VQFN - 1 mm max height PLASTIC QUAD FLATPACK - NO LEAD



Images above are just a representation of the package family, actual package may vary. Refer to the product data sheet for package details.




# **RGT0016C**



# **PACKAGE OUTLINE**

## VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



## NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M. 2. This drawing is subject to change without notice.
- 3. The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.




# **RGT0016C**

# **EXAMPLE BOARD LAYOUT**

# VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



NOTES: (continued)

4. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).

 Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.




# **RGT0016C**

# **EXAMPLE STENCIL DESIGN**

# VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



#### **IMPORTANT NOTICE**

Texas Instruments Incorporated (TI) reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete.

TI's published terms of sale for semiconductor products (http://www.ti.com/sc/docs/stdterms.htm) apply to the sale of packaged integrated circuit products that TI has qualified and released to market. Additional terms may apply to the use or sale of other types of TI products and services.

Reproduction of significant portions of TI information in TI data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such reproduced documentation. Information of third parties may be subject to additional restrictions. Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyers and others who are developing systems that incorporate TI products (collectively, "Designers") understand and agree that Designers remain responsible for using their independent analysis, evaluation and judgment in designing their applications and that Designers have full and exclusive responsibility to assure the safety of Designers' applications and compliance of their applications (and of all TI products used in or for Designers' applications) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to their applications, Designer has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any applications that include TI products, Designer will thoroughly test such applications and the functionality of such TI products as used in such applications.

TI's provision of technical, application or other design advice, quality characterization, reliability data or other services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using TI Resources in any way, Designer (individually or, if Designer is acting on behalf of a company, Designer's company) agrees to use any particular TI Resource solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

Designer is authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNER AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

Unless TI has explicitly designated an individual product as meeting the requirements of a particular industry standard (e.g., ISO/TS 16949 and ISO 26262), TI is not responsible for any failure to meet such industry standard requirements.

Where TI specifically promotes products as facilitating functional safety or as compliant with industry functional safety standards, such products are intended to help enable customers to design and create their own applications that meet applicable functional safety standards and requirements. Using products in an application does not by itself establish any safety features in the application. Designers must ensure compliance with safety-related requirements and standards applicable to their applications. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equipment includes, without limitation, all medical devices identified by the U.S. Food and Drug Administration as Class III devices and equivalent classifications outside the U.S.

TI may expressly designate certain products as completing a particular qualification (e.g., Q100, Military Grade, or Enhanced Product). Designers agree that it has the necessary expertise to select the product with the appropriate qualification designation for their applications and that proper product selection is at Designers' own risk. Designers are solely responsible for compliance with all legal and regulatory requirements in connection with such selection.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's noncompliance with the terms and provisions of this Notice.

> Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2018, Texas Instruments Incorporated